






Color:  white



Dimensions in mm



Dimensions in mm  
R = feed direction





PCB terminal block, 2061 Series, Push-in CAGE CLAMP®

This PCB terminal block (item number 2061-601/998-404) is designed for easy and secure connections. You can count on proven safety with these PCB terminal blocks, perfect for a wide variety of applications when designing your devices. Our PCB terminal block is rated for 320 V and is designed for use with a rated current of up to 17.5 A. It is therefore suitable for high-load applications. Strip lengths must be between 7 mm and 10 mm when connecting conductors to this PCB terminal block. This product features one conductor terminal and utilizes Push-in CAGE CLAMP®. Our Push-in CAGE CLAMP® is a universal, maintenance-free connection solution for all conductor types, boasting a key feature: It allows direct insertion of both solid and fine-stranded conductors with ferrules without needing tools. No preparation is required; for example, crimping the conductor's ferrule is not necessary. The item's dimensions are 5.7 x 5.6 x 15.8 mm (width x height x depth). This PCB terminal block is suitable for conductor cross sections ranging from 0.25 mm² to 1.5 mm². Up to one potential / one pole can be connected to this terminal block using one clamping point on one level. The contacts are made of copper alloy and the white housing is made of polyphthalamide (PPA GF) for insulation. The contact surface is coated with tin. This PCB terminal block is operated with a push-button. SMD is used to assemble the PCB terminal block. The conductor is designed to be inserted into the board at an angle of 0°..

Notes	
Note	<p>Application notes:</p> <p>Suitable for lead-free, reflow-soldering profiles per DIN EN 61760-1 and IEC 60068-2-58 up to max. 260°C peak temperature. Due to application-specific variables (component configuration and orientation, type of soldering machine, solder paste), trial runs are recommended to ensure product and process compatibility under actual manufacturing conditions.</p> <p>Depending on reflow soldering temperatures and times, color deviations may occur. These deviations will have no impact on functionality.</p>
Recommendation	<p>Recommendation for stencil:</p> <p>150 µm material thickness; Pattern layout identical to solder pad layout</p>



Electrical data						
Ratings per		IEC/EN 60664-1			Approvals per	
		UL 1059				
Overvoltage category	III	III	II	Use group	B	C
Pollution degree	3	2	2	Rated voltage	600 V	-
Nominal voltage	250 V	320 V	630 V	Rated current	10 A	-
Rated surge voltage	4 kV	4 kV	4 kV			5 A
Rated current	17.5 A	17.5 A	17.5 A			

Connection data			
Clamping units	1	<b>Connection 1</b>	
Total number of potentials	1	Connection technology	Push-in CAGE CLAMP®
Number of connection types	1	Actuation type	Push-button
Number of levels	1	Solid conductor	0.25 ... 1.5 mm² / 20 ... 16 AWG
		Fine-stranded conductor	0.5 ... 1.5 mm² / 20 ... 16 AWG
		Fine-stranded conductor; with insulated ferrule	0.5 ... 0.75 mm²
		Fine-stranded conductor; with uninsulated ferrule	0.5 ... 0.75 mm²
		Strip length	7 ... 10 mm / 0.28 ... 0.39 inches
		Conductor connection direction to PCB	0°
		Pole number	1

Physical data		
Pin spacing		6 mm / 0.24 inches
Width		5.7 mm / 0.224 inches
Height		5.6 mm / 0.22 inches
Height from the surface		5.6 mm / 0.22 inches
Depth		15.8 mm / 0.622 inches
Reel diameter of tape-and-reel packaging		330 mm
Tape width		24 mm

PCB contact		
PCB contact		SMD
Solder pin arrangement		over the entire terminal strip (in-line)
Number of solder pins per potential		2

Material data		
Note (material data)		<a href="#">Information on material specifications can be found here</a>
Color		white
Material group		I
Insulation material (main housing)		Polyphthalamide (PPA GF)
Flammability class per UL94		V0
Contact material		Copper alloy
Contact Plating		Tin
Fire load		0.014 MJ
Weight		0.5 g
MSL per J-STD 020D		1



Environmental requirements	
Limit temperature range	-60 ... +105 °C

Commercial data	
PU (SPU)	8100 (900) pcs
Packaging type	Box
Country of origin	CN
GTIN	4055143278065
Customs tariff number	85369010000

Product classification	
UNSPSC	39121409
eCl@ss 10.0	27-14-11-06
eCl@ss 9.0	27-14-11-06
ETIM 9.0	EC001284
ETIM 8.0	EC001284
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60947-7-4	NTR NL-7773
CCA DEKRA Certification B.V.	EN 60947-7-4	71-110254
CCA DEKRA Certification B.V.	EN 60838	NTR NL-7721
cURus Underwriters Laboratories Inc.	UL 1059	E45172
KEMA/KEUR DEKRA Certification B.V.	EN 60838	71-106232

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 2061-601/998-404	



Documentation

Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	

CAD/CAE-Data

CAD data
2D/3D Models 2061-601/998-404

CAE data
ZUKEN Portal 2061-601/998-404

PCB Design
Symbol and Footprint via SamacSys 2061-601/998-404
Symbol and Footprint via Ultra Librarian 2061-601/998-404

1 Compatible Products

1.1 Optional Accessories

1.1.1 Board-to-board link

1.1.1.1 Board-to-board link



**Item No.: 2061-901**  
Board-to-Board Link; Pin spacing 6 mm;  
1-pole; Length: 30 mm; white



**Item No.: 2061-901/034-000**  
Board-to-Board Link; Pin spacing 6 mm;  
1-pole; Length: 34 mm; white

1.1.2 Ferrule

1.1.2.1 Ferrule



**Item No.: 216-201**  
Ferrule; Sleeve for 0.5 mm² / 20 AWG; in-  
sulated; electro-tin plated; electrolytic  
copper; acc. to DIN 46228, Part 4/09.90;  
white



**Item No.: 216-241**  
Ferrule; Sleeve for 0.5 mm² / 20 AWG; in-  
sulated; electro-tin plated; electrolytic  
copper; gastight crimped; acc. to DIN  
46228, Part 4/09.90; white



**Item No.: 216-141**  
Ferrule; Sleeve for 0.5 mm² / 20 AWG; un-  
insulated; electro-tin plated; electrolytic  
copper; gastight crimped; acc. to DIN  
46228, Part 1/08.92



**Item No.: 216-101**  
Ferrule; Sleeve for 0.5 mm² / AWG 22; un-  
insulated; electro-tin plated; silver-colo-  
red



**Item No.: 216-242**  
Ferrule; Sleeve for 0.75 mm² / 18 AWG; in-  
sulated; electro-tin plated; electrolytic  
copper; gastight crimped; acc. to DIN  
46228, Part 4/09.90; gray



**Item No.: 216-262**  
Ferrule; Sleeve for 0.75 mm² / 18 AWG; in-  
sulated; electro-tin plated; electrolytic  
copper; gastight crimped; acc. to DIN  
46228, Part 4/09.90; gray



**Item No.: 216-202**  
Ferrule; Sleeve for 0.75 mm² / 18 AWG; in-  
sulated; electro-tin plated; gray



**Item No.: 216-142**  
Ferrule; Sleeve for 0.75 mm² / 18 AWG;  
uninsulated; electro-tin plated; electroly-  
tic copper; gastight crimped; acc. to DIN  
46228, Part 1/08.92



**Item No.: 216-102**  
Ferrule; Sleeve for 0.75 mm² / AWG 20; un-  
insulated; electro-tin plated; silver-colored

1.1.3 Tool

1.1.3.1 Operating tool



Item No.: 206-866  
Operating tool; for 2061 Series



Item No.: 2061-190  
Operating tool; made of insulating material


Installation Notes

Conductor termination



Inserting solid conductors via push-in termination.

Conductor termination



Easy conductor removal, e.g., via operating tool (206-861)