

## 499786-1 Product Details

Live Product Chat



### 499786-1

TE Part Number: 499786-1

Active

Add to Part List

### Pin and Pinless Headers (AMP-LATCH)

5 of 6 EU RoHS/ELV Compliant (Find RoHS Compliant Alternates/Statement of Compliance)

#### Product Highlights:

- Connector Type = Universal Ejection Pin Headers
- Standard Profile
- Number of Positions = 10
- 2.54 x 2.54 mm Centerline, Matrix
- PCB Mount Angle = Right Angle

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

## Documentation & Additional Information

### Product Drawings:

- [HEADER ASSY, UNIVERSAL, AMP-LATCH](#) (PDF, English)

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- [AMP-LATCH\\* and IDC Header Connectors, .100 x .100 In...](#) (PDF, English)

### Application Specifications:

- None Available

### Instruction Sheets:

- [AMP\\* INSTALLATION PROCEDURES FOR AMP-LATCH\\* UNIVERSA...](#) (PDF, English)

### CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version F)
- [3D Model](#) (IGES, Version F)
- [3D Model](#) (STEP, Version F)

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- [Connector Type](#) = Universal Ejection Pin Headers
- [Profile](#) = Standard
- [Number of Positions](#) = 10
- [PCB Mount Angle](#) = Right Angle
- [PCB Retention Feature](#) = No
- [Mating Polarization Method](#) = Center, Dual Polarizing Bar, Military
- [Mating Connector Lock](#) = With
- [Housing Style](#) = 4-Sided
- [Ejection Latches](#) = With
- [Post Size \(mm \[in\]\)](#) = 0.64 [.025]
- [Shrouded](#) = Yes
- [PCB Thickness \(mm \[in\]\)](#) = 1.57 [0.062]
- [Mating Polarization](#) = With
- [Latch Type](#) = Long
- [Mating Connector Lock Type](#) = Latch
- [Comment](#) = Pin headers in 10- and 14-position sizes have only one slot for snap-in polarizer (military polarization), located as shown.; Pin headers in 10-position size have only slot for dual polarization, located as shown.

### Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 2.79 [0.110]
- [Solder Tail Contact Plating](#) = Tin-Lead

### Body Related Features:

- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]

### Contact Related Features:

- [Contact Mating Area Plating Material](#) = Gold (15)
- [Contact Shape](#) = Square

### Housing Related Features:

- [Housing Material](#) = Thermoplastic
- [Housing Flammability Rating](#) = UL 94V-0
- [Housing Color](#) = Black

### Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

### Conditions for Usage:

- [Temperature Rating](#) = Standard

### Other:

- [Brand](#) = AMP

[Provide Website Feedback](#) | [Need Help?](#)