

This document is the property of Berg Electronics. The design and specifications disclosed hereon are proprietary and shall not be reproduced, copied or used for manufacture or sale of devices without expressed written authorization.

PART NO.

28JR175-1

MATERIAL

BODY: BERYLLIUM COPPER, QQ-C-530, ALLOY 173, 1/2 HD
CONTACT: TFE FLUOROCARBON, ASTM-D1710, TYPE 1, GRADE 1
INSULATOR: PROPRIETARY BRIGHT NICKEL (IP23)
CONTACT: GOLD



IMPEDANCE:

50 OHMS
FREQUENCY RANGE: DC-4 GHZ
VOLTAGE RATING: 500 VRMS
INSULATION RESISTANCE: 5,000 MEGOHMS
V.S.W.R.: 1.30 MAX. TO 4 GHZ

FINISH: CONNECTOR MEETS M39012

COVER DRAWING

15/32-32 UNS-2A



SCALE X 4 (1902)

TOLERANCES
(EXCEPT AS NOTED)

DIM. .XX ±.020
.XXX ±.005
ANGLES ±1°
CONC. .005 TIR
SURF. 64 √

FSCM NO. 24931

DRAWN BY:

T.L.BROWNING

DATE:

10/2/92

SCALE:

CAD FILE:

TITLE:

BNC JACK

RECEPTACLE

SINGLE HOLE MT.

P.C.B. MOUNT

PART NO.

SHT. 1 OF 1

28JR175-1

APPROVED