
D2RV

Miniature Basic Switch

High Reliability for Micro Load Applications, Even in Adverse Atmospheres (Dust, High Humidity, Silicon Gas, etc.)

- **The reed switch offers exceptional contact reliability in micro load applications.**
- **Same mounting pitch as for the V Miniature Basic Switch.**
- **High durability with a bounce time of 1 ms max.**



Model Number Legend

D2RV-[1][2]

1. Actuator

None : Pin plunger model
L11 : Short hinge lever
L : Hinge lever
L13 : Simulated roller lever
L22 : Short hinge roller lever
L2 : Hinge roller lever

2. Maximum Operating Force (OF)

None : 0.49 N {50 gf}
E : 0.25 N {25 gf}
(for pin plungers only)
G : 0.98 N {100 gf}


Note. These values are for the pin plunger models.

List of Models

Actuator	Maximum Operating Force (OF)	Model
Pin plunger	0.25 N {25 gf}	**D2RV-E**
	0.49 N {50 gf}	**D2RV**
	0.98 N {100 gf}	**D2RV-G**
Short hinge lever	0.49 N {50 gf}	**D2RV-L11**
	0.98 N {100 gf}	**D2RV-L11G**
Hinge lever	0.25 N {25 gf}	**D2RV-L**
	0.49 N {50 gf}	**D2RV-LG**
Simulated roller lever	0.25 N {25 gf}	**D2RV-L13**
	0.49 N {50 gf}	**D2RV-L13G**
Short hinge roller lever	0.49 N {50 gf}	**D2RV-L22**
	0.98 N {100 gf}	**D2RV-L22G**
Hinge roller lever	0.25 N {25 gf}	**D2RV-L2**
	0.49 N {50 gf}	**D2RV-L2G**

Contact Form

●SPST-NO



Ratings

Switching voltage	100 VDC (max.)
Switching current	0.25 ADC (max.)
Contact capacity	10 WDC (max.)

Note. The above rating values apply under the following test conditions.
(1) Ambient temperature: 20±2°C
(2) Ambient humidity: 65±5%
(3) Operating frequency: 30 operations/min

Characteristics


Permissible operating speed		0.1mm to 1 m/s (for pin plunger models)
Permissible operating frequency	Mechanical	200 operations/min
	Electrical	200 operations/min
Insulation resistance		100 MΩ min. (at 500 VDC with insulation tester)
Contact resistance (initial value)		150 mΩ max.
Dielectric strength * 1	Between terminals of the same polarity	200 VDC 1 min
	Between current-carrying metal parts and ground	500 VAC 50/60 Hz for 1 min
	Between each terminal and non-current-carrying metal parts	500 VAC 50/60 Hz for 1 min
Vibration resistance * 2	Malfunction	10 to 55 Hz, 1.5 mm double amplitude
Shock resistance	Destruction	500 m/s² {approx. 50G} max.
	Malfunction * 2	200 m/s² {approx. 20G} max.
Durability * 3	Mechanical	10,000,000 operations min. (60 operations/min)
	Electrical	3,000,000 operations min. (30 operations/min)
Degree of protection		IEC IP40
Ambient operating temperature		−10°C to +60°C (at ambient humidity of 60% max.) (with no icing or condensation)
Ambient operating humidity		80% max. (for +5°C to +35°C)
Weight		Approx. 7g (for pin plunger models)

Note. The data given above are initial values.
*1. The values for dielectric strength shown are for models with a Separator (refer to "**Basic Switch Common Accessories**").
*2. For the pin plunger models, the above values apply for use at the free position and total travel position. For the lever models, they apply at the total travel position. Close or open circuit of the contact is 1ms max.
*3. For testing conditions, consult your OMRON sales representative.


Separator (Sold Separately), Actuator (Sold Separately), Terminal Connector (Sold Separately) ➡ Refer to **"Basic Switch Common Accessories"**

Downloaded from Arrow.com.

Terminals/Appearances (Unit:mm)




Mounting Holes (Unit: mm)



Dimensions (Unit: mm) /Operating Characteristics

●Pin Plunger
D2RV-E
D2RV
D2RV-G






Operating characteristics \ Model		D2RV-E	D2RV	D2RV-G
Operating Force	OF Max.	0.25 N {25 gf}	0.49 N {50 gf}	0.98 N {100 gf}
Pretravel	PT Max.	1.6 mm		
Overtravel	OT Min.	0.6 mm		
Movement Differential	MD Max.	0.8 mm		
Operating Position	OP	14.4±0.6 mm		

●Short Hinge Lever
D2RV-L11
D2RV-L11G






Operating characteristics \ Model		D2RV-L11	D2RV-L11G
Operating Force	OF Max.	0.49 N {50 gf}	0.98 N {100 gf}
Pretravel	PT Max.	1.8 mm	
Overtravel	OT Min.	0.4 mm	
Movement Differential	MD Max.	1.0 mm	
Operating Position	OP	15.0±0.6 mm	


●Hinge Lever Models
D2RV-L
D2RV-LG






Operating characteristics \ Model		D2RV-L	D2RV-LG
Operating Force	OF Max.	0.25 N {25 gf}	0.49 N {50 gf}
Pretravel	PT Max.	4.0 mm	
Overtravel	OT Min.	1.0 mm	
Movement Differential	MD Max.	1.6 mm	
Operating Position	OP	14.4±1.2 mm	

●Simulated Roller Lever Models
D2RV-L13
D2RV-L13G






Operating characteristics \ Model		D2RV-L13	D2RV-L13G
Operating Force	OF Max.	0.25 N {25 gf}	0.49 N {50 gf}
Pretravel	PT Max.	4.0 mm	
Overtravel	OT Min.	1.0 mm	
Movement Differential	MD Max.	1.6 mm	
Operating Position	OP	18.1±1.2 mm	


Note 1. Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.
Note 2. The operating characteristics are for operation in the A direction (⬇).

Downloaded from Arrow.com.

●Short Hinge Roller Lever Models

D2RV-L22
D2RV-L22G






Operating characteristics	Model	D2RV-L22	D2RV-L22G
Operating Force	OF Max.	0.49 N {50 gf}	0.98 N {100 gf}
Pretravel	PT Max.	1.8 mm	
Overtravel	OT Min.	0.4 mm	
Movement Differential	MD Max.	1.0 mm	
Operating Position	OP	20.4±0.6 mm	

●Hinge Roller Lever Models

D2RV-L2
D2RV-L2G





Operating characteristics	Model	D2RV-L2	D2RV-L2G
Operating Force	OF Max.	0.25 N {25 gf}	0.49 N {50 gf}
Pretravel	PT Max.	4.0 mm	
Overtravel	OT Min.	1.0 mm	
Movement Differential	MD Max.	1.6 mm	
Operating Position	OP	19.9±1.2 mm	

Note 1. Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.
Note 2. The operating characteristics are for operation in the A direction (⬇).

Precautions

★Please refer to "Basic Switches Common Precautions" for correct use.

Cautions

●Handling

Do not drop the Switch or apply strong shock. It may result in internal mechanism damages and may deteriorate the characteristics of the inner Reed Switch.

●Effect of the External Vibration

When a vibration of 1 kHz or higher is applied, note that false switching operations may occur due to resonant frequency, even with a low acceleration.

●Soldering

- Terminal connections
  Complete the soldering at the iron tip temperature between 250 to 350°C (60W) within 5 seconds, and do not apply any external force for 1 minute after soldering.
  Apply minimum amount of flux required. It may result in contact failure once the flux penetrates into the internal part of the Switch.

Correct Use

●Effect of the External Magnetic Fields

- If two or more switch units are closely installed, mutual interference due to the fringing field will occur, resulting in malfunction. Be sure to keep the gap between the switch units 8 mm or more.
- If you install the switch unit on the iron plate, each operating characteristic will change. Therefore, confirm that the interval between the switch units should be 2 mm or more.
- Do not use the switch in some area where a strong external magnetic field would be applied, otherwise malfunction will be caused.
- Use nonmagnetic brass or stainless steel (SUS304 alloy) screws for installation. Do not use any iron screw.

Downloaded from Arrow.com.

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact

Americas
https://components.omron.com/us

Europe
https://components.omron.com/eu

Asia-Pacific
https://components.omron.com/ap

China
https://components.omron.com.cn

Korea
https://components.omron.com/kr

Japan
https://components.omron.com/jp

© OMRON Corporation 2007-2022 All Rights Reserved.
In the interest of product improvement, specifications are subject to change without notice.

Cat. No. B056-E1-05
1122 (0207)

Downloaded from Arrow.com.