



[kingston.com/ssd](https://kingston.com/ssd)

## NV2 PCIe 4.0 NVMe SSD

# Substantial performance upgrade in high capacity

Kingston's NV2 PCIe 4.0 NVMe SSD is a substantial next-gen storage solution powered by a Gen 4x4 NVMe controller. NV2 delivers read/write speeds up to 3,500/2,800MB/s<sup>1</sup> with lower power requirements and lower heat to help optimize your system's performance and deliver value without sacrifice. The compact single-sided M.2 2280 (22x80mm) design expands storage up to 4TB<sup>2</sup> while saving space for other components, making NV2 ideal for thinner notebooks, small form factor (SFF) systems, and DIY motherboards.

Available in capacities from 250GB – 4TB<sup>2</sup> to give you all the space you need for applications, documents, photos, videos, and more.

- › Gen 4x4 NVMe PCIe Performance
- › Ideal for Laptops & Small Form Factor PCs
- › Capacities up to 4TB<sup>2</sup>

[more >>](#)

## FEATURES / BENEFITS

**Gen 4x4 NVMe PCIe Performance** — Delivers read/write speeds up to 3,500/2,800MB/s<sup>1</sup> for an overall faster system.

**Ideal for Systems with Limited Space** — Easily integrate into designs with M.2 connectors. Perfect for thin laptops and small form factor PCs.

**Extended Capacities** — Available in a range of high capacities up to 4TB<sup>2</sup> to meet your data storage requirements.

## SPECIFICATIONS

### Form Factor

M.2 2280

### Interface

PCIe 4.0 x4 NVMe

### Capacities<sup>2</sup>

250GB, 500GB, 1TB, 2TB, 4TB

### Sequential Read/Write<sup>1</sup>

250GB – 3,000/1,300MB/s    500GB – 3,500/2,100MB/s  
1TB – 3,500/2,100MB/s    2TB - 4TB – 3,500/2,800MB/s

### Nand

3D

### Endurance (Total Bytes Written)<sup>3</sup>

250GB – 80TB    500GB – 160TB    1TB – 320TB  
2TB – 640TB    4TB – 1280TB

### Storage Temperature

-40°C~85°C

### Operating Temperature

0°C~70°C

### Dimensions

22mm x 80mm x 2.2mm

### Weight

7g (All capacities)

### Vibration Operating

2.17G (7-800 Hz)

### Vibration Non-operating

20G (20-1000Hz)

### MTBF

2,000,000 hours

### Warranty/Support<sup>4</sup>

Limited 3-year warranty with free technical support



## KINGSTON PART NUMBERS

### NV2 PCIe 4.0 NVMe SSD

SNV2S/250G

SNV2S/500G

SNV2S/1000G

SNV2S/2000G

SNV2S/4000G

This SSD is designed for use in desktop and notebook computer workloads and is not intended for Server environments.

1. Based on "out-of-box performance" using a PCIe 4.0 motherboard. Speed may vary due to host hardware, software, and usage.
2. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash memory guide at [kingston.com/flashguide](http://kingston.com/flashguide).
3. Total Bytes Written (TBW) is derived from the JEDEC Client Workload (JESD219A).
4. Limited warranty based on 3 years or "Percentage Used" which can be found using the Kingston SSD Manager ([Kingston.com/SSDManager](http://Kingston.com/SSDManager)). For NVMe SSDs, a new unused product will show a Percentage Used value of 0, whereas a product that reaches its warranty limit will show a Percentage Used value of greater than or equal to one hundred (100). See [Kingston.com/wa](http://Kingston.com/wa) for detail.



THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.  
©2023 Kingston Technology Corporation, 17600 Newhope Street, Fountain Valley, CA 92708 USA. All rights reserved.  
All trademarks and registered trademarks are the property of their respective owners. MKD-453.3 US

**Kingston**  
TECHNOLOGY