



Part Number : [357460310](#)
Product Description : VersaBlade Female Crimp
Terminal, Double 20+20, 20+18 or 18+18 AWG, Type A
Series Number : 35746
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

[357460310_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS_ENG-000.pdf](#)

[351500000AS_KOR-000.pdf](#)

[PK-35151-002-001.pdf](#)

[PS-35182-003-001.pdf](#)

[PS-35150-001-001.pdf](#)

[351800400-001.pdf](#)

[351800600-001.pdf](#)

Tooling Specifications

[CS-35745-001-001.pdf](#)

[CS-35745-001-002.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	35746
Description	VersaBlade Female Crimp Terminal, Double 20+20, 20+18 or 18+18 AWG, Type A
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	800754378482

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	0.346/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.80mm + 2.80mm max.
Wire Size (AWG)	18+18, 20+20, 20+18
Wire Size mm ²	2(0.50-0.85)

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural	<u>351500300</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Blue	<u>351500304</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	<u>351500309</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural	<u>351500310</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue	<u>351500314</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	<u>351500319</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural	<u>351500400</u>
VersaBlade Hybrid Receptacle	<u>351500404</u>

Housing, without Mounting Ears, 4 Circuits, Blue	
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>351500409</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Natural	<u>351500410</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Red	<u>351500412</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue	<u>351500414</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>351500419</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural	<u>351500600</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Blue	<u>351500604</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	<u>351500609</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural	<u>351500610</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Red	<u>351500612</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue	<u>351500614</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	<u>351500619</u>

VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Yellow, Glow-Wire Capable	<u>351503309</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Yellow, Glow-Wire Capable	<u>351503319</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Yellow, Glow-Wire Capable	<u>351503419</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	<u>351503609</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	<u>351503619</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue, Glow-Wire Capable	<u>351504319</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue, Glow-Wire Capable	<u>351504419</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue, Glow-Wire Capable	<u>351504619</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	<u>2026500909</u>
VersaBlade Multi-Module 2-2 Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>2041020429</u>
VersaBlade Multi-Module 4-2 Hybrid Receptacle Housing, 6 Circuits, Natural, Glow-Wire Capable	<u>2041020609</u>
VersaBlade Multi-Module Hybrid	<u>2041020209</u>

Plug Housing, 2 Circuits, Friction Lock, Natural, Glow-Wire Capable	
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>2041020219</u>
VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Friction Lock, Natural, Glow-Wire Capable	<u>2041020409</u>
VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>2041020419</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type A, Natural	<u>351810200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Natural	<u>359650200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Blue	<u>359650204</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Natural	<u>359650210</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Blue	<u>359650214</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Natural, Glow-Wire Capable	<u>359659200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Yellow, Glow-Wire Capable	<u>359659203</u>
VersaBlade Hybrid Plug Housings	<u>35151</u>
VersaBlade Multi-Module Hybrid Receptacle Housings	<u>35180</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u>35524</u>

Application Tooling

Global

Description	Part Number
Extraction and Activation Tool	<u>638132700</u>
Hand Crimp Tool for 1.80mm-Wide Crimp Terminals	<u>638190700</u>
T2 Terminator Die	<u>638529200</u>
FineAdjust Applicator	<u>638629200</u>
FineAdjust Applicator for VersaBlade .070 Male and Female Terminals, 20+20AWG, 20+18 AWG and 18+18 AWG	<u>639044000</u>

This document was generated on May 14, 2026