

# SPECIFICATION (Reference sheet)

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor

- Samsung P/N : **CL02C4R3BO2ANNC**
- Description : **CAP, 4.3pF, 16V, ±0.1pF, C0G, 01005**

## A. Samsung Part Number

**CL**   **02**   **C**   **4R3**   **B**   **O**   **2**   **A**   **N**   **N**   **C**  
 ①   ②   ③   ④   ⑤   ⑥   ⑦   ⑧   ⑨   ⑩   ⑪

① Series	Samsung Multi-layer Ceramic Capacitor				
② Size	01005 (inch code)	L: 0.4 ± 0.02	mm	W: 0.2 ± 0.02	mm
③ Dielectric	C0G	⑧ Inner electrode	Pd		
④ Capacitance	4.3 pF	Termination	Ag		
⑤ Capacitance tolerance	±0.1 pF	Plating	Sn 100% (Pb Free)		
⑥ Rated Voltage	16 V	⑨ Product	Normal		
⑦ Thickness	0.2 ± 0.02 mm	⑩ Special	Reserved for future use		
		⑪ Packaging	Cardboard Type, 7" reel		

## B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
<b>Capacitance</b>	Within specified tolerance	1MHz±10%      0.5~5Vrms
<b>Q</b>	486 min	
<b>Insulation Resistance</b>	10,000Mohm or 100Mohm·μF Whichever is Smaller	Rated Voltage      60~120 sec.
<b>Appearance</b>	No abnormal exterior appearance	Microscope (×20)
<b>Withstanding Voltage</b>	No dielectric breakdown or mechanical breakdown	300% of the rated voltage
<b>Temperature Characterisitcs</b>	C0G (From -55℃ to 125℃, Capacitance change should be within ±30PPM/℃)	
<b>Adhesive Strength of Termination</b>	No peeling shall be occur on the terminal electrode	100g·F, for 10±1 sec.
<b>Bending Strength</b>	Capacitance change : within ±5% or ±0.5pF whichever is larger	Bending to the limit (1mm) with 1.0mm/sec.
<b>Solderability</b>	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245±5℃, 3±0.3sec. (preheating : 80~120℃ for 10~30sec.)
<b>Resistance to Soldering heat</b>	Capacitance change : within ±2.5% or ±0.25pF whichever is larger Tan δ, IR : initial spec.	Solder pot : 270±5℃, 10±1sec.

	Performance	Test condition
<b>Vibration Test</b>	Capacitance change : within $\pm 2.5\%$ or $\pm 0.25\text{pF}$ whichever is larger Tan $\delta$ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
<b>Moisture Resistance</b>	Capacitance change : within $\pm 7.5\%$ or $\pm 0.75\text{pF}$ whichever is larger Q : 114.33 min IR : 500Mohm or $25\text{Mohm} \cdot \mu\text{F}$ Whichever is Smaller	With rated voltage $40 \pm 2^\circ\text{C}$ , 90~95%RH, 500+12/-0hrs
<b>High Temperature Resistance</b>	Capacitance change : within $\pm 3\%$ or $\pm 0.3\text{pF}$ whichever is larger Q : 243 min IR : 1000Mohm or $50\text{Mohm} \cdot \mu\text{F}$ Whichever is Smaller	With 200% of the rated voltage Max. operating temperature 1000+48/-0hrs
<b>Temperature Cycling</b>	Capacitance change : within $\pm 2.5\%$ or $\pm 0.25\text{pF}$ whichever is larger Tan $\delta$ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow 25^\circ\text{C}$ $\rightarrow$ Max. operating temperature $\rightarrow 25^\circ\text{C}$  5 cycle test

### C. Recommended Soldering method :

Reflow ( Reflow Peak Temperature :  $260 \pm 0/-5^\circ\text{C}$ , 10sec. Max )



Product specifications included in this catalogue are effective as of March 1, 2013.  
Please be advised that they are standard product specifications for reference only.  
We may change, modify or discontinue the product specifications without notice at any time.  
So, you need to approve the product specifications before placing an order.  
Should you have any question regarding the product specifications,  
please contact our sales personnel or application engineers.