


COAXIAL CONNECTOR, SMB, 50 Ohm, Right angle PCB jack (female)

85_SMB-Z50-0-19/111_N

Properties

- Snap-on mechanism provides a fast and reliable connection
- Ideal for applications with high packaging density
- Applicable in frequencies up to 4 GHz

**Product configuration**

Interface type	Gender	Standard
SMB	jack	IEC 60169-10_MIL-STD-348A/311_CECC 22130

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Zinc Alloy	SUCOPRO Plating
Body	Zinc Alloy	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data

Weight	0.0021 kg
Mating cycles	500
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	8.6 mm
Height of stand off HS	0.5 mm

Engagement / Disengagement force

	Engagement	Disengagement
Interface force min	8 N	8 N
Interface force max	63 N	63 N

COAXIAL CONNECTOR, SMB, 50 Ohm, Right angle PCB jack (female)

85_SMB-Z50-0-19/111_N

Environmental data	
Operation temperature	-40 °C ... 100 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84041359	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
23010999	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84041359	85_SMB-Z50-0-19/111_NE	Single
23010999	85_SMB-Z50-0-19/111_NH	Bulk 100 pcs

Additional Information	
Remarks	PCB connector with stand-offs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1263 / Date of publication: 12.07.2025 / uncontrolled copy