




Connectors > Lighting Connectors > Street Lighting Controls > Street Lighting Base Assemblies



Product Diameter: 76 mm [3 in]
Lighting Connector Features Included: Not Vented
Number of Positions: 7
Sealable: Yes
Circuit Application: Power & Signal

Features

Product Type Features

Sealable	Yes
----------	-----

Configuration Features

Lighting Connector Features Included	Not Vented
Number of Positions	7

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Current Rating (Max)	15 A
Contact Mating Area Plating Material	Gold (Au)

Dimensions

Product Diameter	76 mm[3 in]
------------------	-------------

Usage Conditions



Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-ST833-P5663
Photo Control Cover



TE Part # CAT-Z23-DRE
LUMAWISE Endurance N Poke-In:
Streetlight Dimming Receptacles



Also in the Series | LUMAWISE Endurance N



Street Lighting Accessories(6)




Street Lighting Base Assemblies(18)



Street Lighting Open & Shorting Caps (1)



Street Lighting Power Management(6)



Street Lighting Receptacles(24)

Customers Also Bought



TE Part #206038-1
CPC RECPT ASSEMBLY SIZE 17-28



TE Part #1-1903128-1
DYNAMIC 1100D TAB HSG 22P P/M



TE Part #2306128-1
COVER, LIGHT CONTROLLER, 76MM DIA,SHORT

Documents

Product Drawings

LUMAWISE ENDURANCE N SHRTNG CAP BASE ASM

English

CAD Files

Customer View Model

ENG_CVM_CVM_2325661-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2325661-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2325661-1_A.2d_dxf.zip

English

3D PDF



3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

LUMAWISE STREET LIGHT DIMMING AND CONTROL QUICK REFERENCE GUIDE

English

LUMAWISE ENDURANCE N CONTROL BASE, SLEEVE AND COVER

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English