



NOTE:
ONLY SUITABLE FOR RT360 SERIES 1804 and 1802 LAYOUT
CONNECTOR



SECTION A-A

- NOTES: (UNLESS OTHERWISE SPECIFIED)
- MATERIAL:
 - CONTACT BODY: COPPER ALLOY.
 - POSITIONING CLIP: COPPER ALLOY.
 - CROWN SPRING: COPPER ALLOY.
 - SPECIFICATIONS:
 - CURRENT RATING: 65A(MAX).
 - TERMINATION TYPE: CRIMPING.
 - WIRE RANGE: 8 AWG.
 - SUITABLE CONTACT : MP10A25x-8A.
 - RoHS COMPLIANT.
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



P/N	CONTACT PLATING(MATING AREA)
MS10A25F-8A	GOLD FLASH PLATING OVER NICKEL.
MS10A25S-8A	SILVER PLATING OVER NICKEL.

		SEE PART NUMBER CHART			
QUANTITY		PART NUMBER		DESCRIPTION	
				ITEM	
MATERIALS LIST					
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference = X		SIGNATURES DRAWN: RONALD CHECKED: JOE ENGINEER: APPROVAL: TOMMY CUSTOMER:		DATE 26/Jul/23 27/Jul/23 28/Jul/23	
MATERIAL SPECIFICATIONS:				Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		EcoMate RM, SOCKET CONTACT, Ø3.6mm, CRIMP 8 AWG	
NEXT ASS'Y:				SIZE B	TYPE C-
				DWG NO: MS10A25x-8A	REVISION A1
		SCALE: NONE		SHEET 1 OF 1	

TITLE: EcoMate RM, SOCKET CONTACT, Ø3.6mm, CRIMP 8 AWG

DWG NO:

MS10A25x-8A

REV: A1

SH: 1

OF: 1