




## NOTES:



1. SOLDER CUP SOCKET CONTACTS ARE INSTALLED (SHOWN)
2. ALL DIMENSIONS ARE FOR REFERENCE.

ASS'Y P/N	EPOXY
W7882-10SG-300	NO
W7882-10SG-3ES	YES

CUSTOMER PRINT


FACE VIEW  
7882-10SG-300 SHOWN

WIRE VIEW

ASSEMBLED VIEW  
FOR CUSTOMER REFERENCE

PART NUMBER:

W7882-10SG-3XX

RECOMMENDED  
PANEL CUT-OUT  
TOLERANCE: ±.003

## CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT/INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: \_\_\_\_\_  
DATE: \_\_\_\_\_

RoHS COMPLIANT

0A	AM	04/05/16	FIRST DRAWN
REV.	INIT.	DATE	DESCRIPTION
ORIG. DRAWN BY: AM 04/05/16			DATE: 04/05/16
CHECKED BY: _____			CONXALL
APPROVED BY: _____			TITLE: PANEL CONNECTOR ASSEMBLY (10) #22 SOCKET CONTACT, SOLDER MINI-CON-X
SCALE NTS	SIZE B	SHEET 1 OF 1	CUSTOMER: STANDARD PRODUCT
FILE: SLW	DIRECTORY: SLW	PART NUMBER: W7882-10SG-3XX	REV 0A