
DIMENSIONS IN INCHES (MILLIMETERS)
DO NOT SCALE DRAWING .....

Dwg. No.
GRS-4011-1600

PANEL PIERCING



MATERIAL:
- ROCKER KNOB– Nylon 94V–2
- HOUSING– Nylon 94V–2
- TERMINAL/STATIONARY/MOVING CONTACT– Copper alloy, and/or copper alloy silver plated.
- SPRING– music wire
- PLUNGER– plated steel

PERFORMANCE STANDARDS–
- Endurance– 100,000 cycles, no load, minimum
  25,000 cycles at rated load minimum up to 16A 125 VAC
  10,000 cycles at rated load minimum at 16A 250 VAC
- Contact Resistance– less than .01 Ohm at 10 mA (initial)
- Operating Temperature– 105° C maximum
- High Voltage Dielectric Withstanding Voltage– 2,500 V, 60 Hz for 1 minute between mounting surface and circuit connections

HUMIDITY– Insulation resistance > 10^3 MOhms after 100 hours at 95% R.H. and 50° C followed by 1 hour dry at ambient room conditions

ELECTRICAL RATING–
16A 125–250VAC , 10A 14V (T)
3/4 H.P. 125–250VAC , 3A 125V (L)
10(4) 250 ~ μ

LISTING AGENCIES– , ,

REVISIONS		
0	RELEASED. DGW 9-10-93 RBK SEP. 16, 1993	
1	REDRAWN. ADDED RADIUS ON BOTTOM OF CLAW. DGW 4-26-2005 CH APR. 26, 2005	

B-FORMAT 2002

PDF FILE MADE

CW INDUSTRIES
Southampton, Pa. 18966

TOLERANCES UNLESS OTHERWISE SPECIFIED

2 Place Decimal ±.010	METRIC
3 Place Decimal ±.005	1 Place Dec. ±.25mm
Angles ..... ±1°	2 Place Dec. ±.13mm

Made for: CW IND.
Drawn by: DGW 9-10-93
Checked by: CH 4/26/05
Approval: BF 4/26/5

Title: ROCKER SWIDGET ASSEMBLY (POP-IN) S.P.-S.T.

Division: SWITCH

Dwg. No. GRS-4011-1600

Downloaded from Arrow.com.