


REV.	DATE	ECR NO.	DESCRIPTION
A	11/25/09	-----	RELEASE TO MFG.



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	AMPHENOL CONNEX			
					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm $\pm$ 0.20mm 8 - 30mm $\pm$ 0.40mm 30 - 120mm $\pm$ 0.50mm	DRAWN CLEMENT	11/25/09				
5	INSULATOR C	TEFLON	NATURAL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = $\pm$ 0.007" .315 - 1.180 = $\pm$ 0.015" 1.180 - 4.724 = $\pm$ 0.020"	CHECKED		PART DESCRIPTION			
4	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1		ISSUED		BNC R/A P.C. JACK, 75 OHMS			
3	INSULATOR B	DERLIN	NATURAL	1		SHEET 1 OF 1		PART NO.			
2	INSULATOR A	DERLIN	NATURAL	1				112762			
1	BODY	ZINC	NICKEL	1				DWG. NO. 112762.DWG			
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/112/112762.DWG	REV. A	SIZE A	SCALE NA	