

Part Number : 1000570105


Product Description : Temp-Flex High-Performance Flat-Ribbon Cable, 24 Circuits, 1.27mm Pitch, 26 AWG, Silver Plated Copper, UL 20424, 7/34 Stranded Extruded FEP, Rainbow

Series Number : 100057

Status : Active

Product Category : Specialty Wire and Cable

Engineering Number : F2607S-24-050-R



## Documents & Resources

### Drawings

[1000570105\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

### Part Details

#### General

Status	Active
Category	Specialty Wire and Cable
Series	100057
Description	Temp-Flex High-Performance Flat-Ribbon Cable, 24 Circuits, 1.27mm Pitch, 26 AWG, Silver Plated Copper, UL 20424, 7/34 Stranded Extruded FEP, Rainbow
Product Name	Temp-Flex
UPC	889056598972

#### Electrical

Current - Maximum per Contact	1.8A
Voltage - Maximum	300V AC

#### Physical

Cable Length	100 ft/spool, 10 ft min length, 2 lengths/spool max
Circuits (Loaded)	24
Color - Cable Jacket	Rainbow
Insulation	FEP
Material - Outer Jacket	FEP
Material - Plating Mating	Silver
Net Weight	22.358/g
Packaging Type	Spool
Pitch - Mating Interface	1.27mm
Temperature Range - Operating	-55° to +200°C
Wire/Cable Type	7/34 Stranded, High-Performance Flat-Ribbon, UL 20424
Wire Size (AWG)	26

## Use with Part(s)

Description	Part Number
Use With	Molex Picoflex

---

This document was generated on Mar 03, 2025