Part Number : 1205050107
Product Description : Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female Mini-Change (Straight) to Male M12 L-Coded (Straight), 16 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length
Series Number : 120505
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 1LP5030B66M100



Documents and Resources

Drawings

1205050107_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3; 10(a) per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:ada69fc2-dd99-413d-858a-a2179e545a0b
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120505
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female Mini-Change (Straight) to Male M12 L-Coded (Straight), 16 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12),Mini-Change
Type	Double Ended
UPC	195842918245

Agency

UL	E152210

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	63V

Physical

Cable Diameter	8.60mm (.338")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black

Downloaded from Arrow.com.

Connector End A	Mini-Change
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	L-Coded
LED Indicator	None
Material - Cable Jacket	WSOR TPU
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	1272.000/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	16

Downloaded from Arrow.com.