

3SBH1230A2 Product Details

[Share](#) [Print](#) [Email](#)


3SBH1230A2
(2-1617076-5)

TE Internal Number: 2-1617076-5

[Active](#)

Military/Aerospace High Performance Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- 3SBH 1/5-Size Relay Series
- Input Voltage = 26.5 VDC
- Contact Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact - Rated Current = 2 A
- Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [RELAY](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Series](#) = 3SBH 1/5-Size Relay
- Termination Type = Solder Hook Terminals

Electrical Characteristics:

- Input Voltage (VDC) = 26.5
- Contact - Rated Current (A) = 2
- Coil Polarity Protection Diode = Without
- Transistor Driver = Without
- Coil Resistance (Ω) = 720
- MOSFET Driver = Without
- Coil Power Measurement = Milliwatts
- Coil - Rated Power (mW) = 975
- Actuating System = DC
- Shock = 75 G's, 6ms
- Vibration = 30G's, 10 to 3000Hz

Contact Features:

- Mounting Options = Chassis Mount
- Enclosure Type = Hermetically Sealed

Configuration Features:

- [Contact Arrangement](#) = 4 Form C, 4PDT, 4 C/O
- Coil - Magnetic System = Non Polarized, Monostable
- Coil Suppression Diode = Without

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M39016/53-011M
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing
- Approved Standards = M39016 Qualified, M Level

Conditions for Usage:

- Temperature Range ($^{\circ}\text{C}$) = -65 - +125

Other:

- Brand = CII

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

