



Cable Assemblies > RF Cable Assemblies



Cable Assembly Type: 4.3 – 10 to 4.3 – 10

Cable Assembly (End A): 4.3 – 10 Series RF Plug

Cable Assembly (End B): 4.3 – 10 Series RF Plug

Cable Assembly Length: 1 m [3.28 ft]

Impedance: 50 Ω

Features

Product Type Features

Cable Assembly Type	4.3 – 10 to 4.3 – 10
Cable Assembly (End A)	4.3 – 10 Series RF Plug
Cable Assembly (End B)	4.3 – 10 Series RF Plug

Electrical Characteristics

Insulation Resistance	5000 MΩ
Impedance	50 Ω

Body Features

Jacket Material	Polyethylene (PE)
Cable Color	Black

Dimensions

Outside Cable Diameter	13 mm[.512 in]
------------------------	----------------

Operation/Application

Operating Frequency Range	6 GHz
---------------------------	-------

Other

Cable Assembly Length	1 m[3.28 ft]
-----------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | RF 4.3 – 10




RF Cable Assemblies(1)


Customers Also Bought



TE Part #446853-5
3ROW BOX REC 165P 100CLSEALED



TE Part #448007-2
3 ROW BOX PIN 210 POS R/A



TE Part #448008-1
3 ROW BOX PIN 180 POS R/A S/L




TE Part #1617122-6
JMACD-18XLS = M39016/15-104L




TE Part #4-1617352-0
JMGSCD-6MW=M39016/42-050M




TE Part #5-1617352-3
JMGSCDD-5PW=M39016/43-049P



TE Part #1757964-2
A600 SZ 2 RCPT 150/150/13C2



TE Part #6-5174215-4
AMPLIMITE.050 PLUG ASS'Y (V) 60P
PB-FREE



TE Part #3-1437193-0
FST140569621 FST-24A-22V4

Documents

Product Drawings

CA,4310 STR PLUG TO STR PLUG,1-2SF,1M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2081975-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2081975-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2081975-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English