

Terminal Part Number: 15493063

Surface Plating: SN

Material Thickness [mm]: 0,30

Cross Section [mm²]: 0,80 | 1,00

Cable Type codes: 1005

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 1,85 - 2,40

Seal(s): 15324976 | 15324973

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 0,80 / 15324976		2,03	90	1,25	0,05	2,10	0,10	3,90	0,10	4,00	0,10
1005 1,00 / 15324973		2,23	120	1,35	0,05	2,15	0,10	3,90	0,10	4,10	0,10

Cable type code legend:

1005:



Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, PVDF, XLPE

Insul. Wall Designator: THIN



Terminal Part Number: 15493063
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 0,80

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*


Cable Type codes: 1025
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,85 - 2,18
Seal(s): 15324976

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1025 0,80 / 15324976		2,02	90	1,25	0,05	2,10	0,10	3,90	0,10	4,00	0,10

Cable type code legend:

1025:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: SN
Insul. Material: FLUORPOLYM, HDPE, PBT, PE, PVC, XLPE
Insul. Wall Designator: THIN



Crimp Information Sheet

DELPHI

Terminal Part Number: 15493063
 Surface Plating: SN
 Material Thickness [mm]: 0,30
 Cross Section [mm²]: 0,50 | 0,75 | 1,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2010
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,30 - 2,10
 Seal(s): 15404535 | 15327860 | 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,50 / 15404535		1,50	75	1,10	0,05	2,05	0,10	3,60	0,10	4,00	0,10
2010 0,75 / 15327860		1,75	120	1,30	0,05	2,05	0,10	4,10	0,10	4,10	0,10
2010 0,75 / 15324974		1,75	120	1,30	0,05	2,05	0,10	4,10	0,10	4,10	0,10
2010 1,00 / 15327860		1,95	160	1,40	0,05	2,05	0,10	4,20	0,10	4,10	0,10
2010 1,00 / 15324974		1,95	160	1,40	0,05	2,05	0,10	4,20	0,10	4,10	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 15493063
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 0,75 | 1,00

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 2017
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,60 - 2,10
Seal(s): 15327860 | 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2017 0,75 / 15324974		1,75	120	1,30	0,05	2,05	0,10	4,10	0,10	4,10	0,10
2017 0,75 / 15327860		1,75	120	1,30	0,05	2,05	0,10	4,10	0,10	4,10	0,10
2017 1,00 / 15327860		1,95	160	1,40	0,05	2,05	0,10	4,20	0,10	4,10	0,10
2017 1,00 / 15324974		1,95	160	1,40	0,05	2,05	0,10	4,20	0,10	4,10	0,10

Cable type code legend:

2017: FLR41X-B, FLRY-A
Industry Designator: DIN
Conductor Material: COPPER
Conductor Plating: SN
Insul. Material: PA, PP, PVC, XLPE
Insul. Wall Designator: THIN



Terminal Part Number: 15493063
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 0,75

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 2019
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,50 - 1,90
Seal(s): 15324976

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2019 0,75 / 15324976		1,70	85	1,30	0,05	2,10	0,10	3,70	0,10	4,00	0,10

Cable type code legend:

2019: FL7Y 179, FLR7Y, FLR7Y-A, FLR7Y-B, FLU7Y
Industry Designator: DIN
Conductor Material: COPPER
Conductor Plating: SN
Insul. Material: ETFE
Insul. Wall Designator: THIN



Terminal Part Number: 15493063
Surface Plating: SN
Material Thickness [mm]: 0,30
Cross Section [mm²]: 0,75

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2051
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,50 - 1,60
Seal(s): 15327860

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2051 0,75 / 15327860		1,55	120	1,30	0,05	2,05	0,10	4,00	0,10	4,10	0,10

Cable type code legend:

2051: FLU7Y-A
Industry Designator: ISO
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: ETFE
Insul. Wall Designator: ULTRA THIN

