

Part Number : [936000028](#)

Product Description : Heavy-Duty Metal Cable Gland - 5 Bar, for 14.00-21.00mm Cable, M32x1.5 Thread

Series Number : 93600

Status : Active

Product Category : Heavy-Duty Cable Glands

Engineering Part Number : 7000.6833.0




Documents and Resources

Drawings

[936000028_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026) SCIP:a8b6af20-e731-45d8-9f93-e8688a3aac82
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland - 5 Bar, for 14.00-21.00mm Cable, M32x1.5 Thread
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Product Name	Heavy-Duty Connectors
UPC	887191822600

Physical

Cable Diameter	14.00-21.00mm
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	117.000/g
Packaging Type	Bag
Panel Cutout Diameter	32.50mm
Temperature Range - Operating	-40° to +125°C
Thread Size	M32x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Industrial connector hoods and housings

This document was generated on Apr 23, 2026