





TDK item description C1005NP01H150JT\*\*\*\*

Applications	 Commercial Grade Please refer to Part No. <a href="#">CGA2B2NP01H150J050BA</a> for Automotive use.
Feature	 150°C High Temperature Application
Series	C1005 [EIA 0402]
Status	 Production
Brand	TDK








Size	
Length(L)	1.00mm ±0.05mm
Width(W)	0.50mm ±0.05mm
Thickness(T)	0.50mm ±0.05mm
Terminal Width(B)	0.10mm Min.
Terminal Spacing(G)	0.30mm Min.
Recommended Land Pattern (PA)	0.30mm to 0.50mm
Recommended Land Pattern (PB)	0.35mm to 0.45mm
Recommended Land Pattern (PC)	0.40mm to 0.60mm

Electrical Characteristics	
Capacitance	15pF ±5%
Rated Voltage	50VDC
Temperature Characteristic	NP0(0±30ppm/°C)
Q (Min.)	700
Insulation Resistance (Min.)	10000MΩ

Other	
Soldering Method	Reflow
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000pcs

## Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



## Associated Images

