

G8408

TABLE I

SHELL SIZE	SHELL SIZE CODE - REF	A THREAD ISO METRIC	B DIA MAX	C DIA	APPROX WT. (GRAMS)
9	A	M12 X 1 - 6H	.618 (15.7)	.269 (6.83)	3.0
11	B	M15 X 1 - 6H	.736 (18.7)	.397 (10.08)	3.8
13	C	M18 X 1 - 6H	.858 (21.8)	.511 (12.98)	4.9
15	D	M22 X 1 - 6H	.984 (25.0)	.636 (16.15)	5.7
17	E	M25 X 1 - 6H	1.114 (28.3)	.761 (19.33)	6.4
19	F	M28 X 1 - 6H	1.201 (30.5)	.857 (21.77)	8.6
21	G	M31 X 1 - 6H	1.327 (33.7)	.982 (24.94)	9.6
23	H	M34 X 1 - 6H	1.528 (38.8)	1.107 (28.12)	11.2
25	J	M37 X 1 - 6H	1.575 (40.0)	1.232 (31.29)	12.5

REVISIONS

SYM.	DESCRIPTION	DATE	APPROVED
C	REDRAWN & REVISED PER DCN 21237	08/01/03	T.L.

TABLE II

SYM	FINISH DESCRIPTION
B	CADMIUM PLATE/OLIVE DRAB
C	ANODIZE/BLACK
M	ELECTROLESS NICKEL
N	CADMIUM PLATE/OLIVE DRAB OVER NICKEL
NF	CAD/O. D. OVER ELECTROLESS NICKEL (500 HOUR SALT SPRAY)


PART NUMBER DEVELOPMENT

EXAMPLE: G8408 - 17 B

BASIC NO

SHELL SIZE, TABLE I

FINISH SYM, TABLE II



NOTES:

- ASSEMBLY IDENTIFIED WITH MANUFACTURER'S NAME AND P/N, SPACE PERMITTING.
- UNLESS OTHERWISE SPECIFIED. ALL DIMENSIONS ARE IN MILLIMETERS (mm).
- GLENAIR 600 SERIES BACKSHELL ASSEMBLY TOOLS ARE RECOMMENDED FOR ASSEMBLY AND INSTALLATION.
- MATERIAL/FINISH:
ADAPTER, COUPLING NUT - AL ALLOY/SEE TABLE II

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONS $\pm 1/16$ DECIMALS .XX $\pm .03$.XXX $\pm .015$ ANGLES $\pm 2^\circ$	DRAWN T. LE 08/01/03	GLENAIR, INC. CAD 2993 ^Q 1211 AIR WAY - GLENDALE - CALIFORNIA 91201			
	CHECK P. OAKES 08/01/03				
	ENGR R. PAINTER 08/01/03	ADAPTER FOR MIL-C-38999 SERIES III & IV CONNECTORS			
DO NOT SCALE THIS DRAWING	RELEASE DATE 08/01/03 ORIGINAL RELEASE DATE 02/11/77	CODE IDENT. NO. 06324	SIZE C	G8408	REV. C
B/F 03-2892 P/C 61	NON REPARABLE COMMERCIAL ITEM	SCALE N/A	WEIGHT N/A		