




PRODUCT NUMBER	PITCH
HPxx30x000J0G	3.81 mm



Material:

- Item ① Insulating body: Thermoplastic (UL94V-0)
- Item ② Insulating lever: Thermoplastic (UL94V-0) Orange(RAL 2011/P)
- Item ③ Female contact: PhBz (CuSn) Tin plated

Electrical: cULus

- Voltage rating:300V
- Current rating:5A
- Wire range:
- Solid wire(AWG):20-22
- Stranded wire(AWG):20-22
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: cULus

N=Number of poles
 Dim A=(N-1)x3.81+4.6
 Dim B=(N-1)x3.81

Poles	Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.25
19P-24P	±0.30

PART NO.: HP xx 30 x 0 00J0 G

Solid block
 No. of poles
 02 2 poles
 03 3 poles
 ...
 24 24 poles

Color
 0 Black (RAL9005)
 2 Red (RAL3001/D)
 3 Orange(RAL2011/P)
 4 Yellow(RAL1018/A)
 5 Green(RAL6018/T)
 6 Blue (RAL5015/A)
 8 Grey(RAL7035/D)
 9 White(RAL1102)
 C Green(RAL6018/U)

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK			
					angles		title			
					Ø		TERMINAL BLOCK			
					X*±1"		SPRING CLAMP, IDC TYPE, PLUGGABLE PLUG			
					dr		dwg no			
					enr		sheet 1 of 1			
					chr		HPxx30x000J0G			
					appd		type			
							CUSTOMER Drawing			
sheet index	revision	A		1						