



Part number description :

10134325-XXXLF

LF: Lead Free, RoHs compliant, see note

XXX : Color ref or/and version



PN	Colour	Version
10134325-001LF	grey	(A) multiple
10134325-002LF	blue	(A) multiple
10134325-003LF	yellow-green	(A) multiple

TECHNICAL DATA / DIMENSIONS

Dimensions	
Width mm	30.0
Length mm	47.6
Height mm	38.0
Mounting type (EN 60715)	Omega TH35
Technical data	
Maximum load current	Cu 320A Al 290A
Insulating material	PA
Self-extinguishing degree acc. to UL94	V2
Nominal Voltage	1000V
Nominal Current	320A
Connection data	
Conductor cross-section solid min/max	1.5 / 50 mm ²
Stripping length	max 15 mm
Screw – recessed Allen screw	M10 – SW5
Tightening torque: 1.5-2.5 mm ²	1.5 Nm
Tightening torque: 4-10 mm ²	5 Nm
Tightening torque: 16-50 mm ²	10 Nm


APPROVALS

UL1059

600V – Cu300A / Al 240A

EN60947-7-1

1000V – Cu320A / Al290A



Note : THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS PER GS-47-0004

ACCESSORIES

Item	Description
DIN RAIL system - Mounting and Installation material	
10134392-001LF	Steel Omega Rail TH35x7,5mm -2mt length
10134393-001LF	Slotted Steel Omega Rail TH35x7,5mm -2mt length
10134394-001LF	Steel Omega Rail TH35x15mm -2mt length
10134395-001LF	Slotted Steel Omega Rail TH35x15mm -2mt length
10134387-001LF	Angled support bracket
10134389-001LF	End Bracket for TH35 Omega rail -Width 9mm
10134390-001LF	End Bracket for TH35 Omega rail -Width 6mm

spec ref	dir Aymeric Soudy	29-06-2015	projection	size A3	scale
tolerance std	eng Aymeric Soudy	29-06-2015	mm	ecn no	size out of scale
ISO 406	chr			rel level	
ISO 1101	appr Aymeric Soudy	29-06-2015	product family DIN Terminal Block		
surface ✓	linear	0.X ± 0.3	FCJ	title	rev
		0.XX ± 0.1		SCREW Terminal block	A
		0.XXX ± 0.05		Higt current 50 - Multiple	
ISO 1302	angular	0° ± 2°	www.fcicom	cat. no.	
				Product customer drawing	sheet 1 of 1

PDS: Rev :A

STATUS:Released

Printed: Jul 17, 2015