



Color: ■ gray



Dimensions in mm  
L = (pole no. – 1) x pin spacing + 10.35 mm



PCB terminal block, 2606 Series, with 7.5 mm pin spacing

Connecting conductors is quick and easy with this PCB terminal block (item number 2606-3104/020-000). It offers the flexibility needed for different mounting types. Our PCB terminal block is rated for 1000 V and is designed for use with a rated current of up to 41 A. As such, it is suitable for high-load applications. Ensure that the strip lengths are between 11 mm and 13 mm when connecting conductors to this PCB terminal block. This product features one conductor terminal and utilizes Push-in CAGE CLAMP®. Push-in CAGE CLAMP® technology provides a universal connection solution for all conductor types. It allows both solid and fine-stranded conductors with ferrules to be inserted directly into the clamping point without the need for tools. The dimensions are 32.85 x 31 x 24 mm (width x height x depth). This PCB terminal block is suitable for conductor cross sections ranging from 0.2 mm² to 10 mm². Up to four potentials / four poles can be connected to this terminal strip using four clamping points on one level. The clamping spring is made of chrome-nickel spring steel (CrNi), the gray housing is made of polyamide (PA66) for insulation, and the contacts are made of electrolytic copper (ECu). The contact surface is coated with tin. This PCB terminal block is operated with a lever. THT is used to assemble the PCB terminal block. Insert the conductor at a 90° angle. The solder pins measure 1.5 x 1.2 mm in cross-section and 4 mm in length and are laid out over the entire terminal strip (staggered). There are one solder pin per potential.

Notes	
Variants:	Other pole numbers Direct marking Other colors Other versions (or variants) can be requested from WAGO Sales or configured at <a href="https://configurator.wago.com/">https://configurator.wago.com/</a> .



Electrical data						
Ratings per		IEC/EN 60664-1			Approvals per	
		UL 1059				
Overvoltage category	III	III	II	Use group	B	C
Pollution degree	3	2	2	Rated voltage	600 V	600 V
Nominal voltage	800 V	1000 V	1000 V	Rated current	31 A	31 A
Rated surge voltage	8 kV	8 kV	8 kV			
Rated current	41 A	41 A	41 A			

Approvals per		CSA		
Use group	B	C	D	
Rated voltage	600 V	600 V	-	
Rated current	31 A	31 A	-	

Connection data			
Clamping units	4	Connection 1	
Total number of potentials	4	Connection technology	Push-in CAGE CLAMP®
Number of connection types	1	Actuation type	Lever
Number of levels	1	Solid conductor	0.2 ... 10 mm² / 24 ... 8 AWG
		Fine-stranded conductor	0.2 ... 10 mm² / 24 ... 8 AWG
		Fine-stranded conductor; with insulated ferrule	0.2 ... 6 mm²
		Fine-stranded conductor; with uninsulated ferrule	0.5 ... 6 mm²
		Fine-stranded conductor; with twin ferrule	0.25 ... 2.5 mm²
		Strip length	11 ... 13 mm / 0.43 ... 0.51 inches
		Conductor connection direction to PCB	90 °
		Pole number	4

Physical data		
Pin spacing	7.5 mm / 0.295 inches	
Width	32.85 mm / 1.293 inches	
Height	31 mm / 1.22 inches	
Height from the surface	27 mm / 1.063 inches	
Depth	24 mm / 0.945 inches	
Solder pin length	4 mm	
Solder pin dimensions	1.5 x 1.2 mm	
Drilled hole diameter with tolerance	2 (+0.1) mm	

PCB contact	
PCB contact	THT
Solder pin arrangement	over the entire terminal strip (staggered)
Number of solder pins per potential	1



Material data		
Note (material data)		<a href="#">Information on material specifications can be found here</a>
Color		gray
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Clamping spring material		Chrome-nickel spring steel (CrNi)
Contact material		Electrolytic copper (E <sub>Cu</sub> )
Contact Plating		Tin
Fire load		0.14 MJ
Actuator color		orange
Weight		17.2 g

Environmental requirements		
Limit temperature range		-60 ... +105 °C
Processing temperature		-35 ... +60 °C
Continuous operating temperature		-60 ... +105 °C

Commercial data		
PU (SPU)		48 pcs
Packaging type		Box
Country of origin		PL
GTIN		4066966396195
Customs tariff number		85369010000

Product classification		
UNSPSC		39121409
eCl@ss 10.0		27-44-04-01
eCl@ss 9.0		27-44-04-01
ETIM 9.0		EC002643
ETIM 8.0		EC002643
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

## Approvals / Certificates

### General approvals



Approval	Standard	Certificate Name
CB DEKRA Certification B.V.	IEC 60947-7-4	NL-103311
CSA CSA Group	C22.2	70146882
UL Underwriters Laboratories Inc.	UL 1059	UL-US- L45172-6187172-92117102-1



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance  
2606-3104/020-000

↓

Documentation

Additional Information

Technical Section  
03.04.2019  
pdf  
2027.26 KB

↓

CAD/CAE-Data

CAD data

2D/3D Models  
2606-3104/020-000

↓

CAE data

ZUKEN Portal  
2606-3104/020-000

↓

PCB Design

Symbol and Footprint  
via SamacSys  
2606-3104/020-000

↓

Symbol and Footprint  
via Ultra Librarian  
2606-3104/020-000


↓

1 Compatible Products


1.1 Optional Accessories

1.1.1 Ferrule


1.1.1.1 Ferrule




[Item No.: 216-263](#)  
Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red




[Item No.: 216-264](#)  
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black




[Item No.: 216-266](#)  
Ferrule; Sleeve for 2.5 mm² / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue



[Item No.: 216-267](#)  
Ferrule; Sleeve for 4 mm² / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray




[Item No.: 216-208](#)  
Ferrule; Sleeve for 6 mm² / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow



[Item No.: 216-108](#)  
Ferrule; Sleeve for 6 mm² / AWG 10; un-insulated; electro-tin plated; silver-colored

## Installation Notes

### Conductor termination



Insert fine-stranded conductors – and remove all conductors – via operating tool.

### Conductor termination



Insert solid conductors via push-in termination.