






TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-26-271532	05MAR2026	SA	GH



SECTION A-A



TEPN		DESCRIPTION		SIZE	øD	ød	E	PKG TYPE	PKG QTY
CHLOROPRENE	NBR	CHLOROPRENE	NBR						
1SNG609035R0000	1SNG609045R0000	ECR-WG-PG7-BL-A	ENBR-WG-PG7-BL-A	PG 7	16.8±0.3	11.8 ^{+0.2} _{-0.3}	1.5±0.3	BAG	500
1SNG609036R0000	1SNG609046R0000	ECR-WG-PG9-BL-A	ENBR-WG-PG9-BL-A	PG 9	21.8±0.3	14.5 ^{+0.2} _{-0.3}	1.5±0.3	BAG	500
1SNG609037R0000	1SNG609047R0000	ECR-WG-PG11-BL-A	ENBR-WG-PG11-BL-A	PG 11	25.8±0.3	17.5 ^{+0.2} _{-0.3}	1.5±0.3	BAG	500
1SNG609038R0000	1SNG609048R0000	ECR-WG-PG135-BL-A	ENBR-WG-PG135-BL-A	PG 13.5	26.0±0.3	18.5 ^{+0.2} _{-0.3}	1.5±0.2	BAG	500
1SNG609039R0000	1SNG609049R0000	ECR-WG-PG16-BL-A	ENBR-WG-PG16-BL-A	PG 16	29.8±0.3	21.8 ^{+0.2} _{-0.3}	1.5±0.3	BAG	500
1SNG609040R0000	1SNG609050R0000	ECR-WG-PG21-BL-A	ENBR-WG-PG21-BL-A	PG 21	35.8±0.3	27.0 ^{+0.2} _{-0.3}	1.5±0.3	BAG	200
1SNG609041R0000	1SNG609051R0000	ECR-WG-PG29-BL-A	ENBR-WG-PG29-BL-A	PG 29	46.8±0.3	35.5 ^{+0.2} _{-0.3}	1.5±0.3	BAG	200
1SNG609042R0000	1SNG609052R0000	ECR-WG-PG36-BL-A	ENBR-WG-PG36-BL-A	PG 36	59.0±0.5	45.5 ^{+0.3} _{-0.5}	1.5±0.3	BAG	100
1SNG609043R0000	1SNG609053R0000	ECR-WG-PG42-BL-A	ENBR-WG-PG42-BL-A	PG 42	66.8±0.5	52.8 ^{+0.3} _{-0.5}	1.5±0.3	BAG	100
1SNG609044R0000	1SNG609054R0000	ECR-WG-PG48-BL-A	ENBR-WG-PG48-BL-A	PG 48	71.8±0.5	57.8 ^{+0.3} _{-0.5}	1.5±0.3	BAG	100

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN RAJAN N KASI 15FEB2022

CHK RAFAEEQ MOHD 15FEB2022

APVD RAFAEEQ MOHD 15FEB2022

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

PG-WASHER

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1SNP061327-0100

-


SCALE 1:1

SHEET 1 OF 1

REV A1

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
DIN ISO 3302-1 M1-C0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

SEE TABLE

FINISH

-