




HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY
NT-MIL-1/2-0-SP

[Raychem](#) | [SP](#)

NT-MIL-1/2-0-SP

TE Internal Number: C32412-000
Mil-Spec: M23053/1-103-0 , M23053/1-203-0
Alias ID: 9-1200620-2

[Converted to EU RoHS/ELV Compliant](#)

Wall Type **Single**

Resistant To **Abrasion, Fluids, Strain**

Low Outgassing **No**

Product Source **US**

Packaging Method **Piece**

Catalog Pages/Data Sheets

[1654025_Sec3_NT-MIL](#)

PDF
English

[Flexible, Rugged, Modified Elastomeric Heat-Shrinkable Tubing](#)

PDF
English

Product Specifications

Product Specification

[Raychem NT-MIL Tubing Modified Chlorinated Polyolefin, Elastomeric, Flexible, Flame Retarded, Heat-Shrinkable](#)

PDF
English

[Tubing Customer Specification Report](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Wall Type

Single

Product Family

NT-MIL

Body Features

Material Systems Code

20

Shrink Ratio

1.75:1

	Color	Black
	Flexibility	Flexible
	Material	Chlorinated Polyolefin
	Fluid Type	Aviation Fuel, Chemicals/Solvents, Ground Vehicle Fuels, Hydraulic Fluid, Lubricating Oil, Water
Dimensions	Recovered Wall Thickness (Nominal)	1.21 mm [.0476 in]
	Recovered Inside Diameter (Max)	7.3 mm [.287 in]
	Expanded Inside Diameter (Min)	12.7 mm [.5 in]
Usage Conditions	Resistant To	Abrasion, Fluids, Strain
	Recovery Temperature (°C)	135
	Operating Temperature Range (°C)	-70 – 121
	Flammability	Flame-Retardant
	Fluid Resistance	Splash Protection
	Shrink Temperature (Min) (°C)	135
Packaging Features	Packaging Method	Piece
Other	Low Outgassing	No
	Product Source	US
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	

No compatible products found for NT-MIL-1/2-0-SP

