
**Part Number :** 462070024
**Product Description :** Mini-Fit Jr. Reflow Solder Capable Header, 4.20mm Pitch, Dual Row, Vertical, 24 Circuits, 1.57mm PCB Thickness, with PCB Pegs, LCP Housing, with Tin (Sn) Plating, Glow-Wire Capable, Tray
**Series Number :** 46207
**Status :** Active
**Product Category :** PCB Headers and Receptacles



## Documents and Resources

### Drawings

462070024_sd.pdf

PK-46207-001-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

SYM-46207-0024-001.zip

### Specifications

PS-45750-001-001.pdf

55560004-PS-CH-000.pdf

55560004-PS-ES-000.pdf

55560004-PS-SK-000.pdf

PS-5556-004-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |

Downloaded from Arrow.com.

| | |
|---|---|
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 46207 |
| Description | Mini-Fit Jr. Reflow Solder Capable Header, 4.20mm Pitch, Dual Row, Vertical, 24 Circuits, 1.57mm PCB Thickness, with PCB Pegs, LCP Housing, with Tin (Sn) Plating, Glow-Wire Capable, Tray |
| Application | Power, Wire-to-Board |
| Comments | Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit Plus HCS Crimp Terminal Crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current de-rating information. |

Downloaded from Arrow.com.

| | |
|---|---|
| | This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options. |
| Component Type | PCB Header |
| Product Name | Mini-Fit Jr. |
| UPC | 800756675800 |

## Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

## Electrical

| | |
|---|---|
| Current - Maximum per Contact | 13.0A |
| Voltage - Maximum | 600V AC (RMS)/DC |

Downloaded from Arrow.com.

## Physical

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 24 |
| Circuits (maximum) | 24 |
| Color - Resin | Black |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Glow-Wire Capable | Yes |
| Guide to Mating Part | No |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Matte Tin |
| Material - Plating Termination | Matte Tin |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 8.067/g |
| Number of Rows | 2 |
| Orientation | Vertical |
| Packaging Type | Tray |
| PCB Locator | No |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.57mm |
| PC Tail Length | 3.66mm |
| Pitch - Mating Interface | 4.20mm |
| Pitch - Termination Interface | 4.20mm |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Shrouded |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Through Hole |

## Solder Process Data

Downloaded from Arrow.com.

| | |
|---|---|
| Max-Duration | 30 |
| Lead-Free Process Capability | SMC&WAVE |
| Max-Cycle | 3 |
| Max-Temp | 265 |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Receptacle Housings | 172708 |
| Mini-Fit Jr. Receptacle Housings | 5557 |



Downloaded from Arrow.com.