


CPW6-1700-Z010A

Gen 6 Silicon Carbide Schottky Diode

Description

This is the 6th generation of high voltage, high performance Z-Rec[®] silicon carbide Schottky diode in a packageless bare die format to be implemented into any custom module design. The lower forward voltage, smaller reverse leakage current, zero reverse recovery, and high thermal conductivity make this schottky diode ideal for high frequency switching applications including high density DC to DC converters. This schottky diode can be used in conjunction with either IGBT or MOSFET as an anti-parallel diode, or as a rectifier.



Topside View
(Anode)



Package Type: Bare Die
PN: CPW6-1700-Z010A

Features

- 1700V Schottky Rectifier
- Zero Reverse Recovery
- Zero Forward Recovery
- High-Frequency Operation
- Temperature-Independent Switching Behavior
- Extremely Fast Switching
- Positive Temperature Coefficient on V_F

Applications

- Solar Inverters
- Motor Drives
- EV Chargers
- UPS
- Industrial Power Supplies

Absolute Maximum Ratings ($T_j = 25^\circ\text{C}$ unless otherwise specified)

Stress beyond those listed under absolute maximum ratings may damage the device

Parameter	Symbol	Rating	Unit	Comments
Repetitive Peak Reverse Voltage	V_{RRM}	1700	V	
Continuous Forward Current	I_F	40	A	$T_c = 25^\circ\text{C}$
		22	A	$T_c = 100^\circ\text{C}$
		11	A	$T_c = 160^\circ\text{C}$
Repetitive Peak Forward Surge Current	I_{FRM}	59	A	$T_c = 25^\circ\text{C}$, $t_p = 10\text{ms}$, Half Sine Pulse
		33	A	$T_c = 110^\circ\text{C}$, $t_p = 10\text{ms}$, Half Sine Pulse
Non-repetitive Forward Surge Current	I_{FSM}	148	A	$T_c = 25^\circ\text{C}$, $t_p = 10\text{ms}$, Half Sine Pulse
		93	A	$T_c = 110^\circ\text{C}$, $t_p = 10\text{ms}$, Half Sine Pulse
Operating Junction and Storage Temperature	T_{vj} , T_{stg}	-55 to +175	$^\circ\text{C}$	
Processing Temperature	T_{proc}	325	$^\circ\text{C}$	Non-reactive ambient

Note -All above notation to T_c specifies case temperature from die packaged in TO-247, with $R_{th(j-c)} < 0.73^\circ\text{C/W}$



Electrical Characteristics

Parameter	Symbol	Typical	Max	Unit	Test Conditions
Forward Voltage	V_F	1.45		V	$I_F = 10A, T_{vj} = 25^{\circ}C$
		1.95			$I_F = 10A, T_{vj} = 175^{\circ}C$
Reverse Current	I_R	0.44		μA	$V_R = 1700V, T_{vj} = 25^{\circ}C$
		2.88			$V_R = 1700V, T_{vj} = 175^{\circ}C$
Total Capacitive Charge	Q_C	126		nC	$V_R = 1700V, T_{vj} = 25^{\circ}C$
Total Capacitance	C	1227		pF	$V_R = 0V, T_{vj} = 25^{\circ}C, f = 1MHz$
		53			$V_R = 800V, T_{vj} = 25^{\circ}C, f = 1MHz$
		52			$V_R = 1700V, T_{vj} = 25^{\circ}C, f = 1MHz$
Capacitance Stored Energy	E_C	79		μJ	$V_R = 1700V$

Note:

All 175°C values are guaranteed by design and characterization

Thermal Characteristics

Parameter	Symbol	Typical	Unit
Thermal Resistance from Junction to Case ¹	$R_{th(j-c)}$	0.62	$^{\circ}C/W$

Note:

¹Tested in TO-247 package

Mechanical Parameters

Parameter	Typical	Units
Die Size	2.97 x 2.97	mm
Anode Pad Opening	2.07 x 2.07	mm
Die Thickness	360	μm
Topside Anode Metalization (Al)	4	μm
Backside Cathode Metalization (Ni)	0.8	μm
Backside Cathode Metalization (Au)	0.01	μm
Frontside Passivation (polymide)	7.3	μm

Typical Performance




Figure 1

Typical Forward Characteristics




Figure 2

Typical Reverse Characteristics




Figure 3

Typical Capacitance vs Reverse Voltage




Figure 4

Typical Recovery Charge vs Reverse Voltage




Figure 5

Typical Capacitance Stored Energy vs
Reverse Voltage





Figure 6

Typical Thermal Impedance Characteristics



Product Dimensions CPW6-1700-Z010A (Package Type — Bare Die)





Product Ordering Information

Order Number	Description	Package
CPW6-1700-Z010A-FA6	Gen6 1700V 10A Schottky Diode, Full Wafer, Multiple Fab	Bare Die Product

Revision History

Revision History	Date of Change	Brief Summary
1	07/01/2022	Initial Release



Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Cree. No communication from any employee or agent of Cree or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Cree for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Cree.

Notwithstanding any application-specific information, guidance, assistance, or support that Cree may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree representative or from the Product Documentation sections of www.cree.com.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Cree representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Contact info:

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfspeed.com/power