

Harvatek Surface Mount LED Data Sheet HT-159R Series

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 1/26

DISCLAIMER	3
PRODUCT SPECIFICATIONS	4
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	6
LABEL SPECIFICATIONS	7
PRODUCT CHARACTERISTICS	13
ABSOLUTE MAXIMUM RATINGS	13
ELECTRO-OPTICAL CHARACTERISTICS	14
PACKAGE OUTLINE DIMENSION	15
RECOMMENDED SOLDERING PATTERN FOR REFLOW SOLDERING	15
CHARACTERISTIC CURVES FOR YG, Y, D, SD AND UR	16
CHARACTERISTIC CURVES FOR UYG, UY, UD, URO AND USD	17
CHARACTERISTIC CURVES FOR NB, NG, AND TW	18
CHARACTERISTIC CURVES FOR ALL COLORS (RADIATION PATTERN)	19
PACKAGING	20
TAPE DIMENSION	20
REEL DIMENSION	21
PACKING	22
DRY PACK	23
REFLOW SOLDERING	24
PRECAUTIONS	25
REWORKING	25
CLEANING	25
RELIABILITY	26
REVISION HISTORY	27

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 2/26

DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

LIFE SUPPORT POLICY

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 3/26

Product Specifications

Product	Emission Color	Technology	Test Current I_F (mA)	Luminous Intensity I_V (mcd)	Forward Voltage V_F (V)	Orderable Part Number
HT-159RYG	Yellow Green	GaP	20	100 typ	2.2 typ	HT-159RYG-ZZZZ
HT-159RY	Yellow	GaAsP	20	100 typ	2.1 typ	HT-159RY-ZZZZ
HT-159RD	Orange	GaAsP	20	100 typ	2.1 typ	HT-159RD-ZZZZ
HT-159RSD	Red	GaAsP	20	100 typ	2.1 typ	HT-159RSD-ZZZZ
HT-159RUR	Bright Red	AlGaAs	20	100 typ	1.8 typ	HT-159RUR-ZZZZ
HT-159RUYG	Ultra Bright Yellow Green	AlInGaP	20	600 typ	2.0 typ	HT-159RUYG-ZZZZ
HT-159RUY	Ultra Bright Yellow	AlInGaP	20	500 typ	1.9 typ	HT-159RUY-ZZZZ
HT-159RUD	Ultra Bright Orange	AlInGaP	20	700 typ	1.9 typ	HT-159RUD-ZZZZ
HT-159RUSD	Ultra Bright Red	AlInGaP	20	900 typ	1.9 typ	HT-159RUSD-ZZZZ
HT-159RURO	Ultra Deep Red	AlInGaP	20	1000 typ	1.9 typ	HT-159RURO-ZZZZ
HT-159RNB	Blue	InGaN	20	850 typ	3.3 typ	HT-159RNB-ZZZZ
HT-159RNG	True Green	InGaN	20	2000 typ	3.3 typ	HT-159RNG-ZZZZ
HT-159RTW	White	InGaN	20	2500 typ	3.3 typ	HT-159RTW-ZZZZ

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 4/26

	Specification	Material	Quantity
Resin	Water clear	Epoxy resin	
Carrier tape	Per EIA 481-1A specs	Conductive black tape	2000pcs per reel
Reel	Per EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	220x240mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 5/26

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of I_V , λ_D and V_f . Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Compliance and Certification

RoHS compliant and IS9002, QS9000 and ISO14001 certified.



ATTENTION: Electrostatic Discharge (ESD) protection




The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 6/26

Label Specifications

HARVATEK			Date: yyyy/mm/dd
CUSTOMER P/N: 			
HARVATEK P/N: 		QTY: PCS 	
LOT NO: 		QC	
IV BIN:	COLOR BIN:	VF:	

Harvatek P/N:

H T - 1 5 9 R XXX - ZZZZ

Series Name	Emitting Color	Customer Code
HT-159R	XXX	ZZZZ
HT: Harvatek	YG: Yellow Green Y: Yellow	Customer Product Code (TBD)
159: Reverse Mountable 1206 series with 1.6mm Dome Lens	D: Orange SD: Red	
Reverse Mount Taping	UR: Bright Red	
3.2 (L) x 1.6 (W) x 1.85 (H) mm	UYG: Ultra Bright Yellow Green UY: Ultra Bright Yellow UD: Ultra Bright Orange USD: Ultra Bright Red URO: Ultra Deep Red NB: Blue NG: True Green TW: White	

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 7/26

Lot P/N:

1 2 3 4 5 6 7 8 9 10
P 1 2 2 3 0 A - D T

Code 1	Code 2	Code 3	Code 4, 5	Code 6, 7	Code 9	Code 10
	Mfg. Year	Mfg. Month	Mfg. Date	Lots	Resin Color	Packaging
Internal Tracing Code	Z: 2000 1: 2001 2: 2002 3: 2003	1: Jan. 2: Feb. 9: Sep. A: Oct. B: Nov. C: Dec.	1~31/ (30)	01~99, A,B,C...	C: Clear D: Diffused	T: Tape & Reel

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 8/26

■ Luminous Intensity (Iv) Bin:

Bin	Luminous Intensity Range (mcd)		Bin	Luminous Intensity Range (mcd)	
	Minimum	Maximum		Minimum	Maximum
L1	11.2	14.2	L2	14.2	18.0
M1	18.0	22.5	M2	22.5	28.5
N1	28.5	36.0	N2	36.0	45.0
P1	45.0	57.0	P2	57.0	71.5
Q1	71.5	90.0	Q2	90.0	112.5
R1	112.5	142.0	R2	142.0	180.0
S1	180.0	227.0	S2	227.0	285.0
T1	285.0	320.0	T2	320.0	360.0
U1	360.0	400.0	U2	400.0	450.0
V1	450.0	500.0	V2	500.0	560.0
W1	560.0	630.0	W2	630.0	715.0
X1	715.0	800.0	X2	800.0	900.0
Y1	900.0	1000.0	Y2	1000.0	1125.0
Z1	1125.0	1270.0	Z2	1270.0	1440.0
AA1	1440.0	1610.0	AA2	1610.0	1800.0
AB1	1800.0	2010.0	AB2	2010.0	2250.0
AC1	2250.0	2530.0	AC2	2530.0	2850.0

@20mA / Ta=25^o C, Tolerance: ± 10%

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 9/26

■ Wavelength (λ_D) Bin:

Bin	Wavelength Range (nm)									
	Bright Red (UR)		Red (SD)		Orange (D)		Yellow (Y)		Yellow Green (YG)	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
-	635.0	650.0	615.0	635.0						
A					597.0	600.0	582.0	584.5	561.5	564.5
B					600.0	603.0	584.6	587.0	564.5	567.5
C					603.0	606.0	587.0	589.5	567.5	570.5
D					606.0	609.0	589.5	592.0	570.5	573.5
E					609.0	612.0	592.0	594.5	573.5	576.5
F					612.0	615.0	594.5	597.0		
H										
J										

@20mA / Ta=25° C, Tolerance: ± 0.5 nm

Bin	Wavelength Range (nm)									
	Red (USD)		Deep Red (URO)		Orange (UD)		Yellow (UY)		Yellow Green (UYG)	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
-	615.0	630.0	630.0	650.0						
A					597.0	600.0	582.0	584.5	561.5	564.5
B					600.0	603.0	584.6	587.0	564.5	567.5
C					603.0	606.0	587.0	589.5	567.5	570.5
D					606.0	609.0	589.5	592.0	570.5	573.5
E					609.0	612.0	592.0	594.5	573.5	576.5
F					612.0	615.0	594.5	597.0		
H										
J										

@20mA / Ta=25° C, Tolerance: ± 0.5 nm

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 10/26

Bin	Wavelength Range (nm)			
	True Green (NG)		Blue (NB)	
	Min	Max	Min	Max
-				
A	515.0	520.0	460.0	464.0
B	520.0	525.0	464.0	468.0
C	525.0	530.0	468.0	472.0
D	530.0	535.0	472.0	476.0
E	535.0	540.0	476.0	480.0
F			480.0	485.0
H				
J				

@20mA / Ta=25°C, Tolerance: $\pm 0.5\text{nm}$

■ Forward Voltage (V_F) Bin:

Color	Bin Code	Spec. Range
Blue (NB) Green (NG)	G8	2.7-2.9 V
	H7	2.9-3.1 V
	H8	3.1-3.3 V
	J7	3.3-3.5 V
	J8	3.5-3.7 V
	K7	3.7-3.9 V
Ultra Bright (UYG, UY, UD, USD, and URO)	-	2.4 V max
Standard Bright (YG, Y, D, SD)	-	2.6 V max
Bright Red (UR)	-	2.2 V max

@20mA / Ta=25°C, Tolerance: $\pm 0.05\text{ V}$

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 11/26


■ Chromaticity Bin (for TW only):

	Rank C1			
x	0.2500	0.2700	0.2700	0.2500
y	0.2500	0.2775	0.2325	0.2050

	Rank D1			
x	0.2900	0.3100	0.3100	0.2900
y	0.3050	0.3325	0.2875	0.2600

	Rank C2			
x	0.2700	0.2900	0.2900	0.2700
y	0.2775	0.3050	0.2600	0.2325

	Rank D2			
x	0.3100	0.3300	0.3300	0.3100
y	0.3325	0.3600	0.3150	0.2875



Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 12/26

Product Characteristics

Absolute Maximum Ratings

Product	Emission Color	P _d (mW)	I _F (mA)	I _{FP} * (mA)	V _R (V)	T _{OP} (°C)	T _{ST} (°C)
HT-159RYG	Yellow Green	65	25	100	5	-30°C~+80°C	-40°C~+85°C
HT-159RY	Yellow						
HT-159RD	Orange						
HT-159RSD	Red						
HT-159RUR	Bright Red	66	30	100			
HT-159RUYG	Ultra Bright Yellow Green	72	30	100			
HT-159RUY	Ultra Bright Yellow						
HT-159RUD	Ultra Bright Orange						
HT-159RUSD	Ultra Bright Red						
HT-159RURO	Ultra Deep Red						
HT-159RNB	Blue	117	30	100			
HT-159RNG	True Green						
HT-159RTW	White						

* Condition for I_{FP} is pulse of 1/10 duty and 0.1msec width

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 13/26

Electro-Optical Characteristics

(T_a = 25 °C)

Product	Emission Color	I _F (mA)	V _F (V)		λ(nm)			I _V (mcd)	
			typ	max	λ _D	λ _P	Δλ	min	typ
HT-159RYG	Yellow Green	20	2.2	2.6	573	568	30	45	100
HT-159RY	Yellow	20	2.1	2.6	590	589	35	45	100
HT-159RD	Orange	20	2.1	2.6	608	610	35	45	100
HT-159RSD	Red	20	2.1	2.6	629	642	35	45	100
HT-159RUR	Bright Red	20	1.8	2.2	643	660	20	45	100
HT-159RUYG	Ultra Bright Yellow Green	20	2.0	2.4	573	574	20	180	600
HT-159RUY	Ultra Bright Yellow	20	1.9	2.4	591	593	15	180	500
HT-159RUD	Ultra Bright Orange	20	1.9	2.4	605	609	17	180	700
HT-159RUSD	Ultra Bright Red	20	1.9	2.4	622	636	17	180	900
HT-159URO	Ultra Deep Red	20	1.9	2.4	632	645	22	180	1000
HT-159RNB	Blue	20	3.3	3.9	470	468	40	500	850
HT-159RNG	True Green	20	3.3	3.9	527	520	40	900	2000
HT-159RTW	White	20	3.3	3.9	---	---	35	1000	2500

* Per NIST standards

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 14/26

Package Outline Dimension


Recommended Soldering Pattern for Reflow Soldering

Unit: mm Tolerance: +/-0.1

Outline Dimension	Solder Pattern
<p>Package outline dimensions and soldering pattern for the HT-159R LED package. The top view shows a 1.60mm wide package with a 1.60mm wide LED die and a 3.20mm wide soldering area. The side view shows a 1.85mm high package with a 0.30mm thick PCB and a 0.50mm high soldering area. The bottom view shows a 1.60mm wide package with a 1.60mm wide LED die and a 3.20mm wide soldering area. The soldering pattern shows a 1.60mm wide package with a 1.60mm wide LED die and a 3.20mm wide soldering area. The soldering pattern also shows the polarity for all colors other than UR (Cathode) and for UR (Anode).</p>	<p>Soldering pattern for the HT-159R LED package. The pattern shows a 1.60mm wide package with a 1.60mm wide LED die and a 3.20mm wide soldering area. The soldering pattern also shows the polarity for all colors other than UR (Cathode) and for UR (Anode).</p>
Soldering terminals may shift in the x, y direction.	Unit: mm


Official Product	Product: HT-159R Series	Data Sheet No.
Tentative Product	*****	HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov. 14, 2007	Version of 1.2
		Page 15/26

Characteristic Curves for YG, Y, D, SD and UR




Official Product	Product: HT-159R Series	Data Sheet No.
Tentative Product	*****	HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov. 14, 2007	Version of 1.2
		Page 16/26

Characteristic Curves for UYG, UY, UD, URO, and USD




Official Product	Product: HT-159R Series	Data Sheet No.
Tentative Product	*****	HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov. 14, 2007	Version of 1.2
		Page 17/26

Characteristic Curves for NB, NG, and TW



Official Product	Product: HT-159R Series	Data Sheet No.
Tentative Product	*****	HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov. 14, 2007	Version of 1.2
		Page 18/26


Characteristic Curves for All Colors (Radiation Pattern)



Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 19/26

Packaging

Tape Dimension




Part No.	Dim. A	Dim. B	Dim. C	Q'ty/Reel
HT-159R	3.30±0.10	1.70±0.10	2.2±0.10	2K

Unit: mm


Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 20/26

Reel Dimension



Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 21/26

Packing



5 boxes per carton is available depending on shipment quantity.

	Specification	Material	Quantity
Carrier tape	Per EIA 481-1A specs	Conductive black tape	2000pcs per reel
Reel	Per EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	220x240mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified
Others:			
Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, λ_D and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.			


Official Product	Product: HT-159R Series		Data Sheet No.
Tentative Product	*****		HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov. 14, 2007	Version of 1.2	Page 22/26

Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

Upon request, a humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:




Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 23/26


Reflow Soldering

- Recommended tin glue specifications: melting temperature in the range of 178~192 °C
- The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):

Lead Solder Profile



Lead-free Solder Profile



Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 24/26

Precautions

1. Avoid exposure to moisture at all times during transportation or storage.
2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlInGaP products.
3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
5. Avoid direct contact with the surface through which the LED emits light.
6. If possible, assemble the unit in a clean room or dust-free environment.

Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 °C max, <3min

Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electro-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 25/26

Reliability

Item	Frequency/ lots/ samples/ failures	Standards Reference	Conditions
Precondition	For all reliability monitoring tests according to JEDEC Level 2	J-STD-020	1.) Baking at 85°C for 24hrs 2.) Moisture storage at 85°C/ 60% R.H. for 168hrs
Solderability	1Q/ 1/ 22/ 0	JESD22-B102-B And CNS-5068	Accelerated aging 155°C/ 24hrs Tinning speed: 2.5+0.5cm/s Tinning: A: 215°C/ 3+1s or B: 260°C/ 10+1s
Resistance to soldering heat		CNS-5067	Dipping soldering terminal only Soldering bath temperature A: 260+/-5°C; 10+/-1s B: 350+/-10°C; 3+/-0.5s
Operating life test	1Q/ 1/ 40/ 0	CNS-11829	1.) Precondition: 85°C baking for 24hrs 85°C/ 60%R.H. for 168hrs 2.) Tamb25°C; IF=20mA; duration 1000hrs
High humidity, high temperature bias	1Q/ 1/ 45/ 0	JESD-A101-B	Tamb: 85°C Humidity: 85% R.H., IF=5mA Duration: 1000hrs
High temperature bias	1Q/ 1/ 20	HT specs.	Tamb: 55°C IF=20mA Duration: 1000hrs
Pulse life test	1Q/ 1/ 40/ 0		Tamb25°C, If=20mA,, Ip=100mA, Duty cycle=0.125 (tp=125 μs, T=1sec) Duration 500hrs)
Temperature cycle	1Q/ 1/ 76/ 0	JESD-A104-A IEC 68-2-14, Nb	A cycle: -40 degree C 15min; +85 degree C 15min Thermal steady within 5 min.. 300 cycles 2 chamber/ Air-to-air type
High humidity storage test	1Q/ 1/ 40/ 0	CNS-6117	60+3°C 90+5/-10% R.H. for 500hrs
High temperature storage test	1Q/ 1/ 40/ 0	CNS-554	100+10°C for 500hrs
Low temperature storage test	1Q/ 1/ 40/ 0	CNS-6118	-40+5°C for 500hrs

Official Product	Product: HT-159R Series			Data Sheet No.
Tentative Product	*****			HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 14, 2007	Version of 1.2	Page 26/26

Revision History

Changes since last revision	Page	Version No.	Revision Date
New format		1.0	05-07-2007
White Color being added to the series		1.1	9-07-2007
Added URO and revised brightness spec		1.2	11-14-2007

Official Product	Product: HT-159R Series		Data Sheet No.
Tentative Product	*****		HT-159R Series
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov. 14, 2007	Version of 1.2	Page 27/26