

PrimePACK™3+ B-series module with Trench/Fieldstop IGBT5, enlarged emitter controlled 5 diode and NTC

Features

- Electrical features
 - $V_{CES} = 1700\text{ V}$
 - $I_{C\text{ nom}} = 1700\text{ A} / I_{CRM} = 3400\text{ A}$
 - Low switching losses
 - High current density
 - High surge current capability
 - Enlarged diode
 - $T_{vj,op} = 175^{\circ}\text{C}$
- Mechanical features
 - High power and thermal cycling capability
 - High power density
 - High creepage and clearance distances
 - Package with CTI > 400



Potential applications

- Wind turbines
- High-power converters
- Motor drives
- Traction drives

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description






Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	3
3	Diode, Inverter	5
4	NTC-Thermistor	6
5	Characteristics diagrams	7
6	Circuit diagram	12
7	Package outlines	13
8	Module label code	14
	Revision history	15
	Disclaimer	16

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 60 \text{ s}$	4.0	kV
Material of module baseplate			Cu	
Creepage distance	d_{Creep}	terminal to heatsink	36.0	mm
Creepage distance	d_{Creep}	terminal to terminal	28.0	mm
Clearance	d_{Clear}	terminal to heatsink	21.0	mm
Clearance	d_{Clear}	terminal to terminal	19.0	mm
Comparative tracking index	CTI		> 400	

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{sCE}			10		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_C = 25 \text{ °C}$, per switch		0.12		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_C = 25 \text{ °C}$, per switch		0.13		mΩ
Storage temperature	T_{stg}		-40		150	°C
Maximum baseplate operation temperature	T_{BPmax}				150	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	M5, Screw	3	6	Nm
Terminal connection torque	M	- Mounting according to valid application note	M4, Screw	1.8	2.1	Nm
			M8, Screw	8	10	
Weight	G			1400		g

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = 25 \text{ °C}$	1700	V
Implemented collector current	I_{CN}			1700	A
Continuous DC collector current	I_{CDC}	$T_{vj \text{ max}} = 175 \text{ °C}$	$T_C = 75 \text{ °C}$	1700	A

(table continues...)

Table 3 (continued) Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\ op}$	3400	A
Gate-emitter peak voltage	V_{GES}		± 20	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 1700\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$	1.95	2.33	V
			$T_{vj} = 125\ ^\circ C$	2.35	2.79	
			$T_{vj} = 175\ ^\circ C$	2.55	2.97	
Gate threshold voltage	V_{GEth}	$I_C = 57\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$	5.35	5.80	6.25	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CC} = 900\ V$		6.75		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\ ^\circ C$		0.92		Ω
Input capacitance	C_{ies}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		81		nF
Reverse transfer capacitance	C_{res}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		3		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1700\ V, V_{GE} = 0\ V$	$T_{vj} = 125\ ^\circ C$		10	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$			400	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 1700\ A, V_{CC} = 900\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.39\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.260		μs
			$T_{vj} = 125\ ^\circ C$	0.275		
			$T_{vj} = 175\ ^\circ C$	0.285		
Rise time (inductive load)	t_r	$I_C = 1700\ A, V_{CC} = 900\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.39\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.145		μs
			$T_{vj} = 125\ ^\circ C$	0.165		
			$T_{vj} = 175\ ^\circ C$	0.170		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 1700\ A, V_{CC} = 900\ V, V_{GE} = \pm 15\ V, R_{Goff} = 1.1\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.680		μs
			$T_{vj} = 125\ ^\circ C$	0.765		
			$T_{vj} = 175\ ^\circ C$	0.820		
Fall time (inductive load)	t_f	$I_C = 1700\ A, V_{CC} = 900\ V, V_{GE} = \pm 15\ V, R_{Goff} = 1.1\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.120		μs
			$T_{vj} = 125\ ^\circ C$	0.315		
			$T_{vj} = 175\ ^\circ C$	0.425		
Turn-on energy loss per pulse	E_{on}	$I_C = 1700\ A, V_{CC} = 900\ V, L_\sigma = 30\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 0.39\ \Omega, di/dt = 9300\ A/\mu s (T_{vj} = 175\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$	400		mJ
			$T_{vj} = 125\ ^\circ C$	590		
			$T_{vj} = 175\ ^\circ C$	720		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-off energy loss per pulse	E_{off}	$I_C = 1700\text{ A}$, $V_{CC} = 900\text{ V}$, $L_\sigma = 30\text{ nH}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 1.1\text{ }\Omega$, $dv/dt = 2650\text{ V}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	335		mJ
			$T_{vj} = 125\text{ }^\circ\text{C}$	460		
			$T_{vj} = 175\text{ }^\circ\text{C}$	540		
SC data	I_{SC}	$V_{GE} \leq 15\text{ V}$, $V_{CC} = 1000\text{ V}$, $V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$	$t_P \leq 10\text{ }\mu\text{s}$, $T_{vj} \leq 175\text{ }^\circ\text{C}$	7200		A
Thermal resistance, junction to case	R_{thJC}	per IGBT			19.2	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per IGBT, $\lambda_{grease} = 1\text{ W}/(\text{m}\cdot\text{K})$		10.5		K/kW
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	$^\circ\text{C}$

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25\text{ }^\circ\text{C}$	1700	V
Continuous DC forward current	I_F		1700	A
Repetitive peak forward current	I_{FRM}	$t_P = 1\text{ ms}$	3400	A
I^2t - value	I^2t	$t_P = 10\text{ ms}$, $V_R = 0\text{ V}$	$T_{vj} = 125\text{ }^\circ\text{C}$	kA ² s
			$T_{vj} = 175\text{ }^\circ\text{C}$	
Maximum power dissipation	P_{RQM}	$T_{vj} = 175\text{ }^\circ\text{C}$	2100	kW

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 1700\text{ A}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ }^\circ\text{C}$	1.65	1.91	V
			$T_{vj} = 125\text{ }^\circ\text{C}$	1.60	1.96	
			$T_{vj} = 175\text{ }^\circ\text{C}$	1.55	1.89	
Peak reverse recovery current	I_{RM}	$V_{CC} = 900\text{ V}$, $I_F = 1700\text{ A}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 9750\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	1430		A
			$T_{vj} = 125\text{ }^\circ\text{C}$	1750		
			$T_{vj} = 175\text{ }^\circ\text{C}$	1870		

(table continues...)

Table 6 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Recovered charge	Q_r	$V_{CC} = 900 \text{ V}$, $I_F = 1700 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 9750 \text{ A}/\mu\text{s}$ ($T_{vj} = 175 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	340		μC
			$T_{vj} = 125 \text{ }^\circ\text{C}$	650		
			$T_{vj} = 175 \text{ }^\circ\text{C}$	865		
Reverse recovery energy	E_{rec}	$V_{CC} = 900 \text{ V}$, $I_F = 1700 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 9750 \text{ A}/\mu\text{s}$ ($T_{vj} = 175 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	175		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	375		
			$T_{vj} = 175 \text{ }^\circ\text{C}$	510		
Thermal resistance, junction to case	R_{thJC}	per diode			28.2	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot\text{K})$		11.5		K/kW
Temperature under switching conditions	$T_{vj op}$		-40		175	$^\circ\text{C}$

4 NTC-Thermistor

Table 7 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25 \text{ }^\circ\text{C}$		5		k Ω
Deviation of R_{100}	$\Delta R/R$	$T_{NTC} = 100 \text{ }^\circ\text{C}$, $R_{100} = 493 \text{ } \Omega$	-5		5	%
Power dissipation	P_{25}	$T_{NTC} = 25 \text{ }^\circ\text{C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15 \text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15 \text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15 \text{ K}))]$		3433		K


Note: For an analytical description of the NTC characteristics please refer to AN2009-10, chapter 4.

5 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 175\text{ °C}$



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


$V_{CE} = 20\text{ V}$



Gate charge characteristic (typical), IGBT, Inverter

$V_{GE} = f(Q_G)$


$I_C = 1700\text{ A}, T_{vj} = 25\text{ °C}$



5 Characteristics diagrams


Capacity characteristic (typical), IGBT, Inverter

$C = f(V_{CE})$
 $f = 100\text{ kHz}$, $V_{GE} = 0\text{ V}$, $T_{vj} = 25\text{ °C}$




Switching times (typical), IGBT, Inverter

$t = f(I_C)$
 $R_{Goff} = 1.1\text{ }\Omega$, $R_{Gon} = 0.39\text{ }\Omega$, $V_{GE} = \pm 15\text{ V}$, $V_{CC} = 900\text{ V}$, $T_{vj} = 175\text{ °C}$




Switching times (typical), IGBT, Inverter

$t = f(R_G)$
 $V_{GE} = \pm 15\text{ V}$, $I_C = 1700\text{ A}$, $V_{CC} = 900\text{ V}$, $T_{vj} = 175\text{ °C}$



Switching losses (typical), IGBT, Inverter


$E = f(I_C)$
 $R_{Goff} = 1.1\text{ }\Omega$, $R_{Gon} = 0.39\text{ }\Omega$, $V_{CC} = 900\text{ V}$, $V_{GE} = \pm 15\text{ V}$



5 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $V_{CC} = 900\text{ V}, V_{GE} = \pm 15\text{ V}, I_C = 1700\text{ A}$




Reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$
 $R_{Goff} = 1.1\ \Omega, V_{GE} = \pm 15\text{ V}, T_{vj} = 175\text{ }^\circ\text{C}$




Transient thermal impedance, IGBT, Inverter

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, Inverter


$I_F = f(V_F)$



5 Characteristics diagrams


Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$
 $R_{Gon} = R_{Gon}(IGBT) , V_{CC} = 900\text{ V}$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$
 $I_F = 1700\text{ A}, V_{CC} = 900\text{ V}$




Safe operating area (SOA), Diode, Inverter

$I_R = f(V_R)$
 $T_{vj} = 175^\circ\text{C}$



Transient thermal impedance, Diode, Inverter


$Z_{th} = f(t)$



5 Characteristics diagrams

Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



6 Circuit diagram




Figure 1

7 Package outlines




Figure 2

8 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
			
71549142846550549911530		71549142846550549911530	

Figure 3

Revision history

Document revision	Date of release	Description of changes
0.10	2022-05-17	Initial version
0.20	2023-01-24	Target datasheet
1.00	2023-05-31	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-05-31

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2023 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any
aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABE719-003

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.