
Final datasheet
CoolSiC™ 1200 V SiC Trench MOSFET



Halogen-free

Green

Lead-free

RoHS

AEC Qualified

Features
- V_{DSS} = 1200 V at T_{vj} = -55...175°C
- I_{DDC} = 69 A at T_C = 25°C
- New performance-optimized chip technology (Gen1p) with improved R_{DSon}* A FOM
- Increased recommended turn-on voltage ($V_{GS(on)}$ = 20 V) for lower $R_{DS(on)}$
- Best-in-class switching energy for lower switching losses and reduced cooling efforts
- Lowest device capacitances for higher switching speeds and higher power density
- A combination of low C_{rss}/C_{iss} ratio and high $V_{GS(th)}$ to avoid parasitic turn-on and enable unipolar gate driving
- Reduced total gate charge Q_{Gtot} for lower driving power and losses
- .XT die attach technology for best-in-class thermal performance
- Sense pin for optimized switching performance
- Minimum creepage distance of 7.07 mm to fit HV requirements

Potential applications
- On-board charger
- DC/DC converter
- Auxiliary drives

Product validation
- Qualified for Automotive Applications. Product Validation according to AEC-Q100/101


Description
Pin definition:

1 – drain

2 – source

3 – Kelvin sense contact

4 – gate



Type	Package	Marking
AIMZHN120R030M1T	PG-TO247-4-U05	A12M1N030

Downloaded from Arrow.com.

Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	**Package**	3
2	**MOSFET**	3
3	**Body diode (MOSFET)**	5
4	**Characteristics diagrams**	7
5	**Package outlines**	13
6	**Testing conditions**	14
	Revision history	15
	Disclaimer	16

Downloaded from Arrow.com.

1 Package

Table 1 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Storage temperature	T_{stg}		-55		150	°C
Soldering temperature	T_{sold}				260	°C
MOSFET/body diode thermal resistance, junction-case[1)]	$R_{th(j-c)}$			0.35	0.46	K/W

1) Not subject to production test. Parameter verified by design / characterization

2 MOSFET

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage[1)]	V_{DSS}	T_{vj} = -55...175 °C		1200	V
Continuous DC drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$[2)]	I_{DDC}	V_{GS} = 20 V	T_c = 25 °C	69	A
			T_c = 100 °C	49	
Peak drain current, t_p limited by $T_{vj(max)}$[2)]	I_{DM}	V_{GS} = 20 V		176	A
Gate-source voltage, max. transient voltage[3)]	V_{GS}	$t_p \leq 0.5$ µs, $D < 0.01$		-10...25	V
Gate-source voltage, max. static voltage[3)]	V_{GS}			-5...23	V
Avalanche energy, single pulse	E_{AS}	I_D = 20 A, V_{DD} = 50 V, L = 1.8 mH		361	mJ
Power dissipation, limited by $T_{vj(max)}$[2)]	P_{tot}		T_c = 25 °C	326	W
			T_c = 100 °C	163	

1) Tested at Tvj=25°C, verified by design/characterization over full temperature range
2) Not subject to production test. Parameter verified by design / characterization
3) **Important note:** The selection of positive and negative gate-source voltages impacts the long-term behavior of the device. The design guidelines described in Application Note AN2018-09 must be considered to ensure sound operation of the device over the planned lifetime.

Table 3 Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
Recommended turn-on gate voltage	$V_{GS(on)}$		20	V
Recommended turn-off gate voltage	$V_{GS(off)}$		0	V

Downloaded from Arrow.com.

Table 4 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on-state resistance	$R_{DS(on)}$	I_D = 27 A	T_{vj} = 25 °C, $V_{GS(on)}$ = 20 V		30	38	mΩ
			T_{vj} = 100 °C, $V_{GS(on)}$ = 20 V		42		
			T_{vj} = 175 °C, $V_{GS(on)}$ = 20 V		60		
			T_{vj} = 25 °C, $V_{GS(on)}$ = 18 V		33		
Gate-source threshold voltage	$V_{GS(th)}$	I_D = 8.6 mA, V_{DS} = V_{GS} (tested after 1 ms pulse at V_{GS} = 20 V)	T_{vj} = 25 °C	3.7	4.4	5.1	V
			T_{vj} = 175 °C		3.6		
Zero gate-voltage drain current	I_{DSS}	V_{DS} = 1200 V, V_{GS} = 0 V	T_{vj} = 25 °C		0.4	26	µA
			T_{vj} = 175 °C		50		
Gate leakage current	I_{GSS}	V_{DS} = 0 V	V_{GS} = 25 V			100	nA
			V_{GS} = -10 V			-100	
Forward transconductance	g_{fs}	I_D = 27 A, V_{DS} = 20 V			16.5		S
Short-circuit withstand time[1)]	t_{SC}	V_{DD} ≤ 800 V, $V_{DS,peak}$ < 1200 V, $T_{vj(start)}$ = 25 °C, $R_{G,ext}$ = 2 Ω	$V_{GS(on)}$ = 20 V		1.5		µs
			$V_{GS(on)}$ = 18 V		2		
			$V_{GS(on)}$ = 15 V		2.5		
Internal gate resistance	$R_{G,int}$	f = 1 MHz, V_{AC} = 25 mV			2.6		Ω
Input capacitance	C_{iss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			1738		pF
Output capacitance	C_{oss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			82		pF
Reverse transfer capacitance	C_{rss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			4.4		pF
C_{oss} stored energy	E_{oss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			34		µJ
Total gate charge	Q_G	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, turn-on pulse			57		nC
Plateau gate charge	$Q_{GS(pl)}$	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, turn-on pulse			15		nC
Gate-drain charge	Q_{GD}	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, turn-on pulse			10		nC
Turn-on delay time	$t_{d(on)}$	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, $R_{GS(on)}$ = 2 Ω, $R_{GS(off)}$ = 2 Ω, L_σ = 33 nH	T_{vj} = 25 °C		11		ns
			T_{vj} = 175 °C		11		

(table continues...)

Downloaded from Arrow.com.

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Rise time	t_r	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, $R_{GS(on)}$ = 2 Ω, $R_{GS(off)}$ = 2 Ω, L_σ = 33 nH	T_{vj} = 25 °C		9		ns
			T_{vj} = 175 °C		12		
Turn-off delay time	$t_{d(off)}$	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, $R_{GS(on)}$ = 2 Ω, $R_{GS(off)}$ = 2 Ω, L_σ = 33 nH	T_{vj} = 25 °C		21		ns
			T_{vj} = 175 °C		22		
Fall time	t_f	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, $R_{GS(on)}$ = 2 Ω, $R_{GS(off)}$ = 2 Ω, L_σ = 33 nH	T_{vj} = 25 °C		10		ns
			T_{vj} = 175 °C		10		
Turn-on energy	E_{on}	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, $R_{GS(on)}$ = 2 Ω, $R_{GS(off)}$ = 2 Ω, L_σ = 33 nH	T_{vj} = 25 °C		155		µJ
			T_{vj} = 175 °C		319		
Turn-off energy	E_{off}	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, $R_{GS(on)}$ = 2 Ω, $R_{GS(off)}$ = 2 Ω, L_σ = 33 nH	T_{vj} = 25 °C		70		µJ
			T_{vj} = 175 °C		73		
Total switching energy	E_{tot}	V_{DD} = 800 V, I_D = 27 A, V_{GS} = 0/20 V, $R_{GS(on)}$ = 2 Ω, $R_{GS(off)}$ = 2 Ω, L_σ = 33 nH	T_{vj} = 25 °C		225		µJ
			T_{vj} = 175 °C		392		
Virtual junction temperature	T_{vj}			-55		175	°C

1) verified by the design/characterization

***Note**: Dynamic test circuit see Fig. F.*
Characteristics at T_{vj} = 25°C, unless otherwise specified.

3 Body diode (MOSFET)

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage[1)]	V_{DSS}	T_{vj} = -55...175 °C		1200	V
Continuous reverse drain current for $R_{th(j\text{-}c,max)}$, limited by $T_{vj(max)}$[2)]	I_{SDC}		T_c = 25 °C	60	A
			T_c = 100 °C	36	

(table continues...)

Downloaded from Arrow.com.

Table 5 (continued) Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Peak reverse drain current, t_p limited by $T_{vj(max)}$ [2]	I_{SM}		V_{GS} = 0 V	61	A
			-5 V ≤ V_{GS} ≤ 0 V, t_p = 0.3 µs	80	
			-5 ≤ V_{GS} ≤ 0 V, Tvj ≤ 175°C; t_p ≤ 0.3 ms for accumulated conduction time < 5 s or t_p ≤ 1 ms for accumulated conduction time < 2.5 s [3]	207	

1) Tested at Tvj=25°C, verified by design/characterization
2) Not subject to production test. Parameter verified by design / characterization
3) Combination of t_p and Ism should not lead to $T_{vj(max)}$ > 175°C

Table 6 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source reverse voltage	V_{SD}	I_{SD} = 27 A	T_{vj} = 25 °C		3.9	5	V
			T_{vj} = 100 °C		3.8		
			T_{vj} = 175 °C		3.7		
MOSFET forward recovery charge	Q_{fr}	V_{DD} = 800 V, I_{SD} = 27 A, V_{GS} = 0 V, $-di_{SD}/dt$ = 2000 A/µs, Q_{fr} includes also Q_C	T_{vj} = 25 °C		203		nC
			T_{vj} = 175 °C		508		
MOSFET peak forward recovery current	I_{frm}	V_{DD} = 800 V, I_{SD} = 27 A, V_{GS} = 0 V, $-di_{SD}/dt$ = 2000 A/µs, Q_{fr} includes also Q_C	T_{vj} = 25 °C		18		A
			T_{vj} = 175 °C		33		
Virtual junction temperature	T_{vj}			-55		175	°C


Downloaded from Arrow.com.

4 Characteristics diagrams

Reverse bias safe operating area (RBSOA)


$I_D = f(V_{DS})$

$T_{vj} \leq 175$ °C, $V_{GS} = 0/20$ V, $T_c = 25$ °C




Power dissipation as a function of case temperature

$P_{tot} = f(T_c)$



Maximum DC drain to source current as a function of case temperature


$I_D = f(T_c)$



Maximum source to drain current as a function of case temperature

$I_{SD} = f(T_c)$


$V_{GS} = 0$ V



Downloaded from Arrow.com.


Typical transfer characteristic

$I_D = f(V_{GS})$
V_{DS} = 20 V, t_p = 20 µs




Typical gate-source threshold voltage as a function of junction temperature

$V_{GS(th)} = f(T_{vj})$
I_D = 8.6 mA




Typical output characteristic, V_{GS} as parameter

$I_D = f(V_{DS})$
T_{vj} = 25 °C, t_p = 20 µs



Typical output characteristic, V_{GS} as parameter


$I_D = f(V_{DS})$
T_{vj} = 175 °C, t_p = 20 µs



Downloaded from Arrow.com.


Typical on-state resistance as a function of junction temperature

$R_{DS(on)} = f(T_{vj})$
$I_D = 27$ A




Typical gate charge

$V_{GS} = f(Q_G)$
$I_D = 27$ A, $V_{DS} = 800$ V




Typical capacitance as a function of drain-source voltage

$C = f(V_{DS})$
$f = 100$ kHz, $V_{GS} = 0$ V



Typical C_{oss} stored energy

$E_{oss} = f(V_{DS})$
$f = 100$ kHz




Downloaded from Arrow.com.

Typical reverse drain voltage as function of junction temperature

$V_{SD} = f(T_{vj})$


I_{SD} = 27 A, V_{GS} = 0 V



Typical reverse drain current as function of reverse drain voltage, V_{GS} as parameter

$I_{SD} = f(V_{SD})$


T_{vj} = 25 °C, t_p = 20 µs



Typical reverse drain current as function of reverse drain voltage, V_{GS} as parameter

$I_{SD} = f(V_{SD})$


T_{vj} = 175 °C, t_p = 20 µs



Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(T_{vj})$

V_{GS} = 0/20 V, I_D = 27 A, $R_{G,ext}$ = 2 Ω, V_{DD} = 800 V




Downloaded from Arrow.com.

Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

E = f(I_D)


V_{GS} = 0/20 V, T_{vj} = 175 °C, $R_{G,ext}$ = 2 Ω, V_{DD} = 800 V



Typical switching energy as a function of drain voltage, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

E = f(V_{DS})


V_{GS} = 0/20 V, I_D = 27 A, T_{vj} = 175 °C, $R_{G,ext}$ = 2 Ω



Typical switching energy as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

E = f($R_{G,ext}$)


V_{GS} = 0/20 V, I_D = 27 A, T_{vj} = 175 °C, V_{DD} = 800 V



Typical switching times as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

t = f($R_{G,ext}$)

V_{GS} = 0/20 V, I_D = 27 A, T_{vj} = 175 °C, V_{DD} = 800 V




Downloaded from Arrow.com.

Typical reverse recovery current as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$I_{frm} = f(-di_{SD}/dt)$


V_{GS} = 0/20 V, I_{SD} = 27 A, V_{DD} = 800 V



Typ. transient thermal impedance (MOSFET/diode)


$Z_{th(j-c),typ} = f(t_p)$

$D = t_p/T$



Downloaded from Arrow.com.

5 Package outlines



PACKAGE - GROUP NUMBER:	PG-TO247-4-U05				
DIMENSIONS	**MILLIMETERS**		**DIMENSIONS**	**MILLIMETERS**	
	MIN.	MAX.		MIN.	MAX.
A	4.90	5.10	**E**	15.70	15.90
A1	2.31	2.51	**E1**	13.10	13.50
A2	1.90	2.10	**E2**	2.40	2.60
A3	0.90	1.10	**E3**	2.48	2.68
b	1.16	1.29	**E4**	3.82	4.02
b1	1.16	1.29	**e**	5.08	
b2		0.20	**e1**	2.54	
c	0.59	0.66	**N**	4	
D	22.30	22.50	**L**	18.40	18.70
D1	16.25	16.85	**L1**	24.97	25.27
D2	1.05	1.35	**øP**	3.50	3.70
D3	5.00	5.20	**øP1**		7.40
D4	3.22	3.42	**Q**	5.60	6.00
D5	1.60	1.80	**S**	6.00	6.30
			aaa	0.25	

NOTE: DIMENSIONS DO NOT INCLUDE MOLDFLASH; PROTRUSION OR GARE BURRS

Figure 1

Downloaded from Arrow.com.

6 Testing conditions




Figure A. **Definition of switching times**




Figure B. **Definition of body diode switching characteristics**




Figure C. **Definition of switching losses**




Figure D. **Definition of QGD**




Figure E. **Thermal equivalent circuit**




Figure F. **Dynamic test circuit**
Parasitic inductance L_σ,
Parasitic capacitor C_σ,

Figure 2

Downloaded from Arrow.com.

Revision history

Document revision	Date of release	Description of changes
0.10	2022-04-19	Target datasheet
0.20	2023-08-03	Preliminary datasheet
1.00	2023-12-01	Final datasheet
1.10	2025-10-15	Updated table values: g_{fs}, L_{σ} for switching parameters, $t_{d(on)}$, t_r, $t_{d(off)}$, t_f, E_{on}, E_{off}, E_{tot}, I_{SDC}, Q_{fr}, I_{frm}, condition $d_{isd/dt}$ for Q_{fr} and I_{frm} Added values: creepage distance value on p.1, Ism values for limited t_p Updated graphs: $I_{DS} = f(V_{DS})$, R_{on} (T_{vj}), I_{DS} (V_{GS}), $I_{SD} = f(_{VSD})$, $E = f(T_{vj})$, $E = f(RG, _{ext})$, $E=f(I_D)$, $t_{sw} = f(RG, _{ext})$, $Z_{th(j-c)} = f(t_p)$ Added graphs: $E_{sw} = f(V_{DS})$, $I_{frm} = f(di/dt)$ No change to the product, new/added values are based on additional assessments

Downloaded from Arrow.com.

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-10-15

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2025 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABE572-004

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Downloaded from Arrow.com.