




## STG5682

Low voltage dual SPDT switch  
with negative rail capability

### Features

- Distortion-free negative signal throughput down to  $V_{CC}-5.5V$
- Wide operating voltage range:  
 $V_{CC}$  (Opr) = 1.65V to 4.5V single supply
- Ultra low power dissipation:  
 $I_{CC} = 0.2\mu A$  (Max.) at  $t_A = 85^\circ C$
- Low "ON" resistance  $V_{IN} = 0V$ :  
 $R_{ON} = 0.5\Omega$  (max.  $t_A = 25^\circ C$ ) at  $V_{CC} = 4.3V$
- 4.3V tolerant and 1.8V compatible threshold on digital control input at  $V_{CC} = 1.65$  to 3.0V
- Latch-up performance exceeds 300mA (JESD 17)
- ESD performance exceeds JESD22
- 2000-V human-body model (A114-A)



### Description

The STG5682 is a high-speed CMOS low voltage dual analog S.P.D.T. (Single Pole Dual Throw) SWITCH or 2:1 Multiplexer /Demultiplexer Switch fabricated in silicon gate C<sup>2</sup>MOS technology. It is designed to operate from 1.65V to 4.5V, making this device ideal for portable applications.

Additional key features are fast switching speed, Break Before Make Delay Time and Ultra Low Power Consumption. All inputs and outputs are equipped with protection circuits against static discharge, giving them ESD immunity and transient excess voltage.

Table 1. Device summary

| Order code | Package                | Packaging     |
|------------|------------------------|---------------|
| STG5682QTR | QFN16L (2.6mm x 1.8mm) | Tape and reel |

# Contents

**1      Pin settings ..... 3**

    1.1    Pin connection ..... 3

    1.2    Pin description ..... 3

**2      Device summary ..... 4**

**3      Maximum rating ..... 5**

    3.1    Recommended operating conditions ..... 6

**4      Electrical characteristics ..... 7**

**5      Package mechanical data ..... 11**


**6      Revision history ..... 15**



# 1 Pin settings

## 1.1 Pin connection

Figure 1. Pin connection (top through view)



## 1.2 Pin description

Table 2. Pin description

| Pin N°          | Symbol                | Name and function       |
|-----------------|-----------------------|-------------------------|
| 4, 2,<br>10, 12 | 1S1, 1S2,<br>2S1, 2S2 | Independent channels    |
| 3, 11           | D1, D2                | Common channel          |
| 1, 9            | 1SEL, 2SEL            | Control                 |
| 7               | V <sub>CC</sub>       | Positive supply voltage |
| 8               | GND                   | Ground (0V)             |
| 5,6,13,14,15,16 | NC                    | No connect              |



### 3 Maximum rating

Stressing the device above the rating listed in the “Absolute Maximum Ratings” table may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in the Operating sections of this specification is not implied. Exposure to Absolute Maximum Rating conditions for extended periods may affect device reliability. Refer also to the STMicroelectronics SURE Program and other relevant quality documents.

**Table 4. Absolute maximum ratings**

| Symbol                | Parameter                                                | Value                                   | Unit       |
|-----------------------|----------------------------------------------------------|-----------------------------------------|------------|
| $V_{CC}$              | Supply voltage                                           | -0.5 to 5.5                             | V          |
| $V_I$                 | DC input voltage                                         | - ( $V_{CC} - 6.0V$ ) to $V_{CC} + 0.5$ | V          |
| $V_{IC}$              | DC control input voltage                                 | -0.5 to 5.5                             | V          |
| $V_O$                 | DC output voltage                                        | - ( $V_{CC} - 6.0V$ ) to $V_{CC} + 0.5$ | V          |
| $I_{IKC}$             | DC input diode current on control pin ( $V_{SEL} < 0V$ ) | -50                                     | mA         |
| $I_{IK}$              | DC input diode current ( $V_{SEL} < 0V$ )                | $\pm 50$                                | mA         |
| $I_{OK}$              | DC output diode current                                  | $\pm 20$                                | mA         |
| $I_O$                 | DC output current                                        | $\pm 150$                               | mA         |
| $I_{OP}$              | DC output current peak (pulse at 1ms, 10% duty cycle)    | $\pm 400$                               | mA         |
| $I_{CC}$ or $I_{GND}$ | DC $V_{CC}$ or ground current                            | $\pm 100$                               | mA         |
| $P_D$                 | Power dissipation at $T_A = 70^\circ C$ <sup>(1)</sup>   | 1120                                    | mW         |
| $T_{stg}$             | Storage temperature                                      | -65 to 150                              | $^\circ C$ |
| $T_L$                 | Lead temperature (10 sec)                                | 300                                     | $^\circ C$ |

1. Derate above  $70^\circ C$  by 18.5mW/ $^\circ C$

### 3.1 Recommended operating conditions

**Table 5. Recommended operating conditions**

| Symbol   | Parameter                              |                            | Value                      | Unit |
|----------|----------------------------------------|----------------------------|----------------------------|------|
| $V_{CC}$ | Supply voltage <sup>(1)</sup>          |                            | 1.65 to 4.5                | V    |
| $V_I$    | Input voltage                          |                            | $V_{CC} - 5.5$ to $V_{CC}$ | V    |
| $V_{IC}$ | Control input voltage                  |                            | 0 to 4.5                   | V    |
| $V_O$    | Output voltage                         |                            | $V_{CC} - 5.5$ to $V_{CC}$ | V    |
| $T_{op}$ | Operating temperature                  |                            | -40 to 85                  | °C   |
| dt/dv    | Input rise and fall time control input | $V_{CC} = 1.65V$ to $2.7V$ | 0 to 20                    | ns/V |
|          |                                        | $V_{CC} = 3.0$ to $4.3V$   | 0 to 10                    |      |

1. Truth Table guaranteed: 1.2V to 4.3V

## 4 Electrical characteristics

Table 6. DC specifications

| Symbol            | Parameter                                           | Test conditions     |                                                                                    | Value                 |      |      |                     |     | Unit |
|-------------------|-----------------------------------------------------|---------------------|------------------------------------------------------------------------------------|-----------------------|------|------|---------------------|-----|------|
|                   |                                                     | V <sub>CC</sub> (V) |                                                                                    | T <sub>A</sub> = 25°C |      |      | -40 to 85°C         |     |      |
|                   |                                                     |                     |                                                                                    | Min                   | Typ  | Max  | Min                 | Max |      |
| V <sub>IH</sub>   | High level input voltage                            | 1.65 -1.95          |                                                                                    | 0.65V <sub>CC</sub>   |      |      | 0.65V <sub>CC</sub> |     | V    |
|                   |                                                     | 2.3-2.5             |                                                                                    | 1.0                   |      |      | 1.4                 |     |      |
|                   |                                                     | 2.7-3.0             |                                                                                    | 1.1                   |      |      | 1.5                 |     |      |
|                   |                                                     | 3.3-4.3             |                                                                                    | 1.3                   |      |      | 1.6                 |     |      |
| V <sub>IL</sub>   | Low level input voltage                             | 1.65-1.95           |                                                                                    |                       |      | 0.5  |                     | 0.5 | V    |
|                   |                                                     | 2.3-2.5             |                                                                                    |                       |      | 0.5  |                     | 0.4 |      |
|                   |                                                     | 2.7-3.0             |                                                                                    |                       |      | 0.6  |                     | 0.5 |      |
|                   |                                                     | 3.3-4.3             |                                                                                    |                       |      | 0.7  |                     | 0.6 |      |
| R <sub>ON</sub>   | Switch ON resistance                                | 1.8                 | V <sub>S</sub> = V <sub>CC</sub> -5.5V to V <sub>CC</sub> ; I <sub>S</sub> = 100mA |                       | 3.20 | 4.0  |                     |     | Ω    |
|                   |                                                     | 2.7                 |                                                                                    |                       | 0.77 | 0.90 |                     |     |      |
|                   |                                                     | 3.0                 |                                                                                    |                       | 0.64 | 0.80 |                     |     |      |
|                   |                                                     | 3.6                 |                                                                                    |                       | 0.51 | 0.65 |                     |     |      |
|                   |                                                     | 4.3                 |                                                                                    |                       | 0.45 | 0.55 |                     |     |      |
| ΔR <sub>ON</sub>  | ON resistance match between channels <sup>(1)</sup> | 1.8                 | V <sub>S</sub> @ R <sub>ON</sub> Max<br>I <sub>S</sub> = 100mA                     |                       | 50   |      |                     |     | mΩ   |
|                   |                                                     | 2.7                 |                                                                                    |                       | 20   |      |                     |     |      |
|                   |                                                     | 3.0                 |                                                                                    |                       | 15   |      |                     |     |      |
|                   |                                                     | 3.6                 |                                                                                    |                       | 15   |      |                     |     |      |
|                   |                                                     | 4.3                 |                                                                                    |                       | 15   |      |                     |     |      |
| R <sub>FLAT</sub> | ON resistance flatness <sup>(2)</sup>               | 1.8                 | V <sub>S</sub> = V <sub>CC</sub> -5.5V to V <sub>CC</sub> ; I <sub>S</sub> = 100mA |                       | 3.0  |      |                     |     | Ω    |
|                   |                                                     | 2.7                 |                                                                                    |                       | 0.50 |      |                     |     |      |
|                   |                                                     | 3.0                 |                                                                                    |                       | 0.40 |      |                     |     |      |
|                   |                                                     | 3.6                 |                                                                                    |                       | 0.25 |      |                     |     |      |
|                   |                                                     | 4.3                 |                                                                                    |                       | 0.16 |      |                     |     |      |
| I <sub>OFF</sub>  | Sn OFF State Leakage Current                        | 4.3                 | V <sub>S</sub> = -1.2 to 4.3V<br>V <sub>D</sub> = 4.3 to -1.2V                     | -0.1                  |      | 0.1  | -1                  | 1   | μA   |
| I <sub>ON</sub>   | Sn ON State Leakage Current                         | 4.3                 | V <sub>S</sub> = -1.2 to 4.3V<br>V <sub>D</sub> = Open                             | -0.1                  |      | 0.1  | -1                  | 1   | μA   |

Table 6. DC specifications (continued)

| Symbol                            | Parameter                                    | Test conditions |                                                        | Value                 |     |     |             |      | Unit |
|-----------------------------------|----------------------------------------------|-----------------|--------------------------------------------------------|-----------------------|-----|-----|-------------|------|------|
|                                   |                                              | Vcc (V)         |                                                        | T <sub>A</sub> = 25°C |     |     | -40 to 85°C |      |      |
|                                   |                                              |                 |                                                        | Min                   | Typ | Max | Min         | Max  |      |
| I <sub>D</sub>                    | D ON State Leakage Current                   | 4.3             | V <sub>S</sub> = Open<br>V <sub>D</sub> = 4.3 to -1.2V | -0.1                  |     | 0.1 | -1          | 1    | μA   |
| I <sub>IH</sub> , I <sub>IL</sub> | SEL Leakage Current                          | 4.3             | V <sub>SEL</sub> =4.3V or GND                          | -0.1                  |     | 0.1 | -1          | 1    | μA   |
| I <sub>CCLV</sub>                 | Quiescent Supply Current Low Voltage Driving | 4.3             | V <sub>1SEL</sub> , V <sub>2SEL</sub> = 1.65V          |                       | ±37 | ±50 |             | ±100 | μA   |
|                                   |                                              |                 | V <sub>1SEL</sub> , V <sub>2SEL</sub> = 1.80V          |                       | ±33 | ±40 |             | ±50  |      |
|                                   |                                              |                 | V <sub>1SEL</sub> , V <sub>2SEL</sub> = 2.60V          |                       | ±12 | ±20 |             | ±30  |      |
| I <sub>CC</sub>                   | Quiescent Supply Current                     | 4.3             | V <sub>SEL</sub> = V <sub>CC</sub> or GND              |                       |     | ±50 |             | ±200 | nA   |

- Note 1:  $\Delta R_{on} = \max |m_{SN} - n_{SN}|$ , where  $m = 1..4$  and  $n = 1..4$ ,  $N = 1..2$
- Flatness is defined as the difference between the maximum and minimum value of on-resistance as measured over the specified analog signal ranges.

Table 7. AC electrical characteristics ( $C_L = 35\text{pF}$ ,  $R_L = 50\Omega$ ,  $t_r = t_f \leq 5\text{ns}$ )

| Symbol                              | Parameter                    | Test conditions |                                                                                      | Value                 |      |     |             |     | Unit |
|-------------------------------------|------------------------------|-----------------|--------------------------------------------------------------------------------------|-----------------------|------|-----|-------------|-----|------|
|                                     |                              | Vcc (V)         |                                                                                      | T <sub>A</sub> = 25°C |      |     | -40 to 85°C |     |      |
|                                     |                              |                 |                                                                                      | Min                   | Typ  | Max | Min         | Max |      |
| t <sub>PLH</sub> , t <sub>PHL</sub> | Propagation delay            | 1.65-1.95       |                                                                                      |                       | 0.45 |     |             |     | ns   |
|                                     |                              | 2.3-2.7         |                                                                                      |                       | 0.40 |     |             |     |      |
|                                     |                              | 3.0-3.3         |                                                                                      |                       | 0.30 |     |             |     |      |
|                                     |                              | 3.6-4.3         |                                                                                      |                       | 0.25 |     |             |     |      |
| t <sub>ON</sub>                     | Turn-ON time                 | 1.65-1.95       | V <sub>S</sub> = 0.8V                                                                |                       | 180  | 220 |             |     | ns   |
|                                     |                              | 2.3-2.7         | V <sub>S</sub> = 1.5V                                                                |                       | 100  | 130 |             |     |      |
|                                     |                              | 3.0-3.3         |                                                                                      |                       | 72   | 95  |             |     |      |
|                                     |                              | 3.6-4.3         |                                                                                      |                       | 58   | 80  |             |     |      |
| t <sub>OFF</sub>                    | Turn-OFF time                | 1.65-1.95       | V <sub>S</sub> = 0.8                                                                 |                       | 64   | 80  |             |     | ns   |
|                                     |                              | 2.3-2.7         | V <sub>S</sub> = 1.5V                                                                |                       | 41   | 60  |             |     |      |
|                                     |                              | 3.0-3.3         |                                                                                      |                       | 34   | 50  |             |     |      |
|                                     |                              | 3.6-4.3         |                                                                                      |                       | 33   | 50  |             |     |      |
| t <sub>D</sub>                      | Break before make time delay | 1.65-1.95       | C <sub>L</sub> = 35pF<br>R <sub>L</sub> = 50Ω<br>V <sub>S</sub> = V <sub>CC</sub> /2 | 1                     | 110  |     |             |     | ns   |
|                                     |                              | 2.3-2.7         |                                                                                      | 1                     | 58   |     |             |     |      |
|                                     |                              | 3.0-3.3         |                                                                                      | 1                     | 40   |     |             |     |      |
|                                     |                              | 3.6-4.3         |                                                                                      | 1                     | 23   |     |             |     |      |
| Q                                   | Charge injection             | 1.65-1.95       | C <sub>L</sub> = 100pF<br>V <sub>GEN</sub> = 0V                                      |                       | 55   |     |             |     | pC   |
|                                     |                              | 2.3-2.7         |                                                                                      |                       | 76   |     |             |     |      |
|                                     |                              | 3.0-3.3         |                                                                                      |                       | 94   |     |             |     |      |
|                                     |                              | 3.6-4.3         |                                                                                      |                       | 126  |     |             |     |      |

**Table 8. Analog switch characteristics** ( $C_L = 5\text{pF}$ ,  $R_L = 50\Omega$ ,  $T_A = 25^\circ\text{C}$ )

| Symbol          | Parameter                                 | Test conditions |                                                                                                   | Value                 |      |     |             |     | Unit |
|-----------------|-------------------------------------------|-----------------|---------------------------------------------------------------------------------------------------|-----------------------|------|-----|-------------|-----|------|
|                 |                                           | Vcc (V)         |                                                                                                   | T <sub>A</sub> = 25°C |      |     | -40 to 85°C |     |      |
|                 |                                           |                 |                                                                                                   | Min                   | Typ  | Max | Min         | Max |      |
| OIRR            | OFF Isolation <sup>(1)</sup>              | 2.7 - 4.3       | V <sub>S</sub> = 1V <sub>RMS</sub> , f = 100kHz                                                   |                       | -55  |     |             |     | dB   |
| Xtalk           | Crosstalk                                 | 2.7 - 4.3       | V <sub>S</sub> = 1V <sub>RMS</sub> , f = 100kHz                                                   |                       | -60  |     |             |     | dB   |
| THD             | Total harmonic distortion                 | 2.7 - 4.3       | R <sub>L</sub> = 32Ω<br>V <sub>IN</sub> = 0.5V <sub>PP</sub><br>DC Bias = 0<br>f = 20Hz to 20 kHz |                       | 0.01 |     |             |     | %    |
| BW              | -3dB bandwidth                            | 2.7 - 4.3       | R <sub>L</sub> = 50Ω<br>Signal = 0dBm                                                             |                       | 33   |     |             |     | MHz  |
| C <sub>IN</sub> | Control pin input capacitance             | 3.3             |                                                                                                   |                       | 6    |     |             |     | pF   |
| C <sub>D</sub>  | D Port capacitance when switch is enabled | 3.3             | f = 1MHz                                                                                          |                       | 290  |     |             |     |      |

1. Off Isolation =  $20\text{Log}_{10} (V_D/V_S)$ ,  $V_D$  = output.  $V_S$  = input to off switch.

## 5 Package mechanical data

In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a Lead-free second level interconnect . The category of second level interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: [www.st.com](http://www.st.com)

| Dim. | mm.  |      |      |
|------|------|------|------|
|      | Min  | Typ  | Max  |
| A    | 0.45 | 0.55 | 0.60 |
| A1   | 0    | 0.02 | 0.05 |
| b    | 0.15 | 0.20 | 0.25 |
| D    | 2.50 | 2.60 | 2.70 |
| E    | 1.70 | 1.80 | 1.90 |
| e    |      | 0.40 |      |
| L    | 0.35 | 0.40 | 0.45 |

- ### Figure 3. Foot print recommendation





Figure 4. Package information



[illegible]

## 6 Revision history

**Table 10. Revision history**

| Date        | Revision | Changes                                   |
|-------------|----------|-------------------------------------------|
| 15-Mar-2007 | 1        | First release                             |
| 16-Apr-2007 | 2        | Typo in cover page                        |
| 05-Jul-2007 | 3        | <a href="#">Table 6 on page 7</a> updated |

**Please Read Carefully:**

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

**UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.**

**UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.**

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

[www.st.com](http://www.st.com)