



## UA78L00 Series Positive-Voltage Linear Regulators

### 1 Features

- 3-Terminal Linear Regulators
- Output Current Up to 100 mA
- No External Components
- Internal Thermal-Overload Protection
- Internal Short-Circuit Current Limiting

### 2 Applications

- Computing and Servers
- On-Card Regulation
- Telecommunications
- White Goods
- Chemical or Gas Sensors
- Field Transmitter: Temperature Sensors
- Flow Meters

### 3 Description

The UA78L00 series of fixed-voltage linear regulators is designed for a wide range of applications. These applications include on-card regulation for elimination of noise and distribution problems associated with single-point regulation as well as for voltage regulation in major appliances. In addition, they can be used with power-pass elements to make high-current voltage regulators. One of these regulators can deliver up to 100 mA of output current. The internal limiting and thermal-shutdown features of these regulators help to protect the device from overload.


The UA78L00C and UA78L00AC series devices are characterized for operation over the virtual junction temperature range of 0°C to 125°C. The UA78L05AI device is characterized for operation over the virtual junction temperature range of –40°C to 125°C.

#### Device Information<sup>(1)</sup>

| PART NUMBER              | PACKAGE    | BODY SIZE (NOM)   |
|--------------------------|------------|-------------------|
| UA78L00D,<br>UA78L00AD   | SOIC (8)   | 4.90 mm × 3.91 mm |
| UA78L00LP,<br>UA78L00ALP | TO-92 (3)  | 4.30 mm × 4.30 mm |
| UA78L00PK,<br>UA78L00APK | SOT-89 (3) | 4.50 mm × 2.50 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

#### Simplified Schematic



Copyright © 2016, Texas Instruments Incorporated



## Table of Contents

|                                                |           |                                                                  |           |
|------------------------------------------------|-----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                        | <b>1</b>  | 7.1 Overview .....                                               | 10        |
| <b>2 Applications</b> .....                    | <b>1</b>  | 7.2 Functional Block Diagram .....                               | 10        |
| <b>3 Description</b> .....                     | <b>1</b>  | 7.3 Feature Description .....                                    | 10        |
| <b>4 Revision History</b> .....                | <b>2</b>  | 7.4 Device Functional Modes .....                                | 10        |
| <b>5 Pin Configuration and Functions</b> ..... | <b>3</b>  | <b>8 Applications and Implementation</b> .....                   | <b>11</b> |
| <b>6 Specifications</b> .....                  | <b>4</b>  | 8.1 Application Information .....                                | 11        |
| 6.1 Absolute Maximum Ratings .....             | 4         | 8.2 Typical Application .....                                    | 11        |
| 6.2 ESD Ratings .....                          | 4         | 8.3 System Examples .....                                        | 12        |
| 6.3 Recommended Operating Conditions .....     | 4         | <b>9 Power Supply Recommendations</b> .....                      | <b>13</b> |
| 6.4 Thermal Information .....                  | 4         | <b>10 Layout</b> .....                                           | <b>13</b> |
| 6.5 Electrical Characteristics: UA78L02 .....  | 5         | 10.1 Layout Guidelines .....                                     | 13        |
| 6.6 Electrical Characteristics: UA78L05 .....  | 5         | 10.2 Layout Example .....                                        | 13        |
| 6.7 Electrical Characteristics: UA78L06 .....  | 6         | <b>11 Device and Documentation Support</b> .....                 | <b>14</b> |
| 6.8 Electrical Characteristics: UA78L08 .....  | 6         | 11.1 Related Links .....                                         | 14        |
| 6.9 Electrical Characteristics: UA78L09 .....  | 7         | 11.2 Receiving Notification of Documentation Updates .....       | 14        |
| 6.10 Electrical Characteristics: UA78L10 ..... | 7         | 11.3 Community Resource .....                                    | 14        |
| 6.11 Electrical Characteristics: UA78L12 ..... | 8         | 11.4 Trademarks .....                                            | 14        |
| 6.12 Electrical Characteristics: UA78L15 ..... | 8         | 11.5 Electrostatic Discharge Caution .....                       | 14        |
| 6.13 Typical Characteristics .....             | 9         | 11.6 Glossary .....                                              | 14        |
| <b>7 Detailed Description</b> .....            | <b>10</b> | <b>12 Mechanical, Packaging, and Orderable Information</b> ..... | <b>14</b> |




## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision U (January 2014) to Revision V                                                                                                                                                                                                                                                                                                                                  | Page |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| • Added <i>Device Information</i> table, <i>ESD Ratings</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section ..... | 1    |
| • Added Applications .....                                                                                                                                                                                                                                                                                                                                                            | 1    |
| • Changed $\theta_{JA}$ values in <i>Thermal Information</i> table From: 97 To: 115 (D), From: 140 To: 143.6 (LP), and From: 52 To: 54.7 (PK) .....                                                                                                                                                                                                                                   | 4    |
| • Changed $\theta_{JC}$ values in <i>Thermal Information</i> table From: 39 To: 60.3 (D), From: 55 To: 74.4 (LP), and From: 9 To: 88.1 (PK) .....                                                                                                                                                                                                                                     | 4    |

| Changes from Revision T (May 2011) to Revision U                                                                   | Page |
|--------------------------------------------------------------------------------------------------------------------|------|
| • Deleted <i>Ordering Information</i> table; see <i>Product Option Addendum</i> at the end of the data sheet ..... | 1    |
| • Updated document to new TI data sheet format - no specification changes .....                                    | 1    |

## 5 Pin Configuration and Functions



**Pin Functions**

| PIN    |            |       |        | I/O | DESCRIPTION            |
|--------|------------|-------|--------|-----|------------------------|
| NAME   | SOIC       | TO-92 | SOT-89 |     |                        |
| COMMON | 2, 3, 6, 7 | 2     | 2      | —   | Ground                 |
| INPUT  | 8          | 3     | 3      | I   | Supply input           |
| OUTPUT | 1          | 1     | 1      | O   | Voltage output         |
| NC     | 4, 5       | —     | —      | —   | No internal connection |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                                     |                                              | MIN | MAX | UNIT |
|-------------------------------------|----------------------------------------------|-----|-----|------|
| Input voltage, $V_I$                | UA78L02AC, UA78L05C, UA78L09C, and UA78L10AC |     | 30  | V    |
|                                     | UA78L12C, UA78L12AC, UA78L15C, and UA78L15AC |     | 35  |      |
| Virtual junction temperature, $T_J$ |                                              |     | 150 | °C   |
| Storage temperature, $T_{stg}$      |                                              | –65 | 150 | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### 6.2 ESD Ratings

|                                     |                                                                                          | VALUE | UNIT |
|-------------------------------------|------------------------------------------------------------------------------------------|-------|------|
| $V_{(ESD)}$ Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>              | 1000  | V    |
|                                     | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> | 1000  |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.  
(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

|                                              |                               | MIN  | MAX | UNIT |
|----------------------------------------------|-------------------------------|------|-----|------|
| $V_I$ Input voltage                          | UA78L02AC                     | 4.75 | 20  | V    |
|                                              | UA78L05C and UA78L05AC        | 7    | 20  |      |
|                                              | UA78L06C and UA78L06AC        | 8.5  | 20  |      |
|                                              | UA78L08C and UA78L08AC        | 10.5 | 23  |      |
|                                              | UA78L09C and UA78L09AC        | 11.5 | 24  |      |
|                                              | UA78L10AC                     | 12.5 | 25  |      |
|                                              | UA78L12C and UA78L12AC        | 14.5 | 27  |      |
|                                              | UA78L15C and UA78L15AC        | 17.5 | 30  |      |
| $I_O$ Output current                         |                               |      | 100 | mA   |
| $T_J$ Operating virtual junction temperature | UA78L00C and UA78L00AC series | 0    | 125 | °C   |
|                                              | UA78L05AI                     | –40  | 125 |      |

### 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | UA78L00  |            |             | UNIT |
|-------------------------------|----------------------------------------------|----------|------------|-------------|------|
|                               |                                              | D (SOIC) | LP (TO-92) | PK (SOT-89) |      |
|                               |                                              | 8 PINS   | 3 PINS     | 3 PINS      |      |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance       | 115      | 143.6      | 54.7        | °C/W |
| $R_{\theta JC(top)}$          | Junction-to-case (top) thermal resistance    | 60.3     | 74.4       | 88.1        | °C/W |
| $R_{\theta JB}$               | Junction-to-board thermal resistance         | 55.6     | —          | 9.6         | °C/W |
| $\psi_{JT}$                   | Junction-to-top characterization parameter   | 16.2     | 24.2       | 6.2         | °C/W |
| $\psi_{JB}$                   | Junction-to-board characterization parameter | 55       | 120.9      | 9.7         | °C/W |
| $R_{\theta JC(bot)}$          | Junction-to-case (bottom) thermal resistance | —        | —          | 7.7         | °C/W |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 6.5 Electrical Characteristics: UA78L02

at specified virtual junction temperature,  $V_I = 9\text{ V}$ , and  $I_O = 40\text{ mA}$  (unless otherwise noted)<sup>(1)</sup>

| PARAMETER                   | TEST CONDITIONS <sup>(2)</sup>                                                         | MIN                                          | TYP  | MAX  | UNIT          |
|-----------------------------|----------------------------------------------------------------------------------------|----------------------------------------------|------|------|---------------|
| Output voltage <sup>f</sup> | $V_I = 4.75\text{ V to }20\text{ V}$ , and $I_O = 1\text{ mA to }40\text{ mA}$         | $T_J = 25^\circ\text{C}$                     | 2.5  | 2.6  | 2.7           |
|                             |                                                                                        | $T_J = 0^\circ\text{C to }125^\circ\text{C}$ | 2.45 |      | 2.75          |
|                             | $I_O = 1\text{ mA to }70\text{ mA}$ , and $T_J = 0^\circ\text{C to }125^\circ\text{C}$ | 2.45                                         |      | 2.75 |               |
| Input voltage regulation    | $V_I = 4.75\text{ V to }20\text{ V}$ , and $T_J = 25^\circ\text{C}$                    |                                              | 20   | 100  | mV            |
|                             | $V_I = 5\text{ V to }20\text{ V}$ , and $T_J = 25^\circ\text{C}$                       |                                              | 16   | 75   |               |
| Ripple rejection            | $V_I = 6\text{ V to }20\text{ V}$ , $f = 120\text{ Hz}$ , and $T_J = 25^\circ\text{C}$ | 43                                           | 51   |      | dB            |
| Output voltage regulation   | $I_O = 1\text{ mA to }100\text{ mA}$ , and $T_J = 25^\circ\text{C}$                    |                                              | 12   | 50   | mV            |
|                             | $I_O = 1\text{ mA to }40\text{ mA}$ , and $T_J = 25^\circ\text{C}$                     |                                              | 6    | 25   |               |
| Output noise voltage        | $f = 10\text{ Hz to }100\text{ kHz}$ , and $T_J = 25^\circ\text{C}$                    |                                              | 30   |      | $\mu\text{V}$ |
| Dropout voltage             | $T_J = 25^\circ\text{C}$                                                               |                                              | 1.7  |      | V             |
| Bias current                | $T_J = 25^\circ\text{C}$                                                               |                                              | 3.6  | 6    | mA            |
|                             | $T_J = 125^\circ\text{C}$                                                              |                                              |      | 5.5  |               |
| Bias current change         | $V_I = 5\text{ V to }20\text{ V}$ , and $T_J = 0^\circ\text{C to }125^\circ\text{C}$   |                                              |      | 2.5  | mA            |
|                             | $I_O = 1\text{ mA to }40\text{ mA}$ , and $T_J = 0^\circ\text{C to }125^\circ\text{C}$ |                                              |      | 0.1  |               |

(1) Applies to UA78L02AC.

(2) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a  $0.33\text{-}\mu\text{F}$  capacitor across the input and a  $0.1\text{-}\mu\text{F}$  capacitor across the output.

## 6.6 Electrical Characteristics: UA78L05

at specified virtual junction temperature,  $V_I = 10\text{ V}$ , and  $I_O = 40\text{ mA}$  (unless otherwise noted)

| PARAMETER                    | TEST CONDITIONS <sup>(1)</sup>                                                            |                           |                            | MIN  | TYP | MAX  | UNIT          |
|------------------------------|-------------------------------------------------------------------------------------------|---------------------------|----------------------------|------|-----|------|---------------|
| Output voltage               | $V_I = 7\text{ V to }20\text{ V}$ , and<br>$I_O = 1\text{ mA to }40\text{ mA}$            | $T_J = 25^\circ\text{C}$  | UA78L05C                   | 4.6  | 5   | 5.4  | V             |
|                              |                                                                                           |                           | UA78L05AC and<br>UA78L05AI | 4.8  | 5   | 5.2  |               |
|                              |                                                                                           | $T_J = \text{full range}$ | UA78L05C                   | 4.5  |     | 5.5  |               |
|                              |                                                                                           |                           | UA78L05AC and<br>UA78L05AI | 4.75 |     | 5.25 |               |
|                              | $I_O = 1\text{ mA to }70\text{ mA}$ , and<br>$T_J = \text{full range}$                    | UA78L05C                  |                            | 4.5  |     | 5.5  |               |
|                              |                                                                                           | UA78L05AC and UA78L05AI   |                            | 4.75 |     | 5.25 |               |
| Input voltage<br>regulation  | $V_I = 7\text{ V to }20\text{ V}$ , and<br>$T_J = 25^\circ\text{C}$                       | UA78L05C                  |                            |      | 32  | 200  | mV            |
|                              |                                                                                           | UA78L05AC and UA78L05AI   |                            |      | 32  | 150  |               |
|                              | $V_I = 8\text{ V to }20\text{ V}$ , and<br>$T_J = 25^\circ\text{C}$                       | UA78L05C                  |                            |      | 26  | 150  |               |
|                              |                                                                                           | UA78L05AC and UA78L05AI   |                            |      | 26  | 100  |               |
| Ripple rejection             | $V_I = 8\text{ V to }18\text{ V}$ , $f = 120\text{ Hz}$ ,<br>and $T_J = 25^\circ\text{C}$ | UA78L05C                  |                            | 40   | 49  | dB   |               |
|                              |                                                                                           | UA78L05AC and UA78L05AI   |                            | 41   | 49  |      |               |
| Output voltage<br>regulation | $I_O = 1\text{ mA to }100\text{ mA}$ , and $T_J = 25^\circ\text{C}$                       |                           |                            |      | 15  | 60   | mV            |
|                              | $I_O = 1\text{ mA to }40\text{ mA}$ , and $T_J = 25^\circ\text{C}$                        |                           |                            |      | 8   | 30   |               |
| Output noise voltage         | $f = 10\text{ Hz to }100\text{ kHz}$ , and $T_J = 25^\circ\text{C}$                       |                           |                            |      | 42  |      | $\mu\text{V}$ |
| Dropout voltage              | $T_J = 25^\circ\text{C}$                                                                  |                           |                            |      | 1.7 |      | V             |
| Bias current                 | $T_J = 25^\circ\text{C}$                                                                  |                           |                            |      | 3.8 | 6    | mA            |
|                              | $T_J = 125^\circ\text{C}$                                                                 |                           |                            |      |     | 5.5  |               |
| Bias current change          | $V_I = 8\text{ V to }20\text{ V}$ , and $T_J = \text{full range}$                         |                           |                            |      |     | 1.5  | mA            |
|                              | $I_O = 1\text{ mA to }40\text{ mA}$ , and<br>$T_J = \text{full range}$                    | UA78L05C                  |                            |      |     | 0.2  |               |
|                              |                                                                                           | UA78L05AC and UA78L05AI   |                            |      |     | 0.1  |               |

(1) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a  $0.33\text{-}\mu\text{F}$  capacitor across the input and a  $0.1\text{-}\mu\text{F}$  capacitor across the output. Full range for the UA78L05AC is  $T_J = 0^\circ\text{C to }125^\circ\text{C}$ , and full range for the UA78L05AI is  $T_J = -40^\circ\text{C to }125^\circ\text{C}$ .

## 6.7 Electrical Characteristics: UA78L06

at specified virtual junction temperature,  $V_I = 12\text{ V}$ , and  $I_O = 40\text{ mA}$  (unless otherwise noted)

| PARAMETER                 | TEST CONDITIONS <sup>(1)</sup>                                       |                                 |           | MIN  | TYP | MAX  | UNIT |
|---------------------------|----------------------------------------------------------------------|---------------------------------|-----------|------|-----|------|------|
| Output voltage            | V <sub>I</sub> = 8.5 V to 20 V,<br>I <sub>O</sub> = 1 mA to 40 mA    | T <sub>J</sub> = 25°C           | UA78L06C  | 5.7  | 6.2 | 6.7  | V    |
|                           |                                                                      |                                 | UA78L06AC | 5.95 | 6.2 | 6.45 |      |
|                           |                                                                      | T <sub>J</sub> = 0°C to 125°C   | UA78L06C  | 5.6  |     | 6.8  |      |
|                           |                                                                      |                                 | UA78L06AC | 5.9  |     | 6.5  |      |
|                           | T <sub>J</sub> = 0°C to 125°C, and I <sub>O</sub> = 1 mA to 70 mA    | UA78L06C                        | 5.6       |      | 6.8 |      |      |
|                           |                                                                      | UA78L06AC                       | 5.9       |      | 6.5 |      |      |
| Input voltage regulation  | T <sub>J</sub> = 25°C                                                | V <sub>I</sub> = 8.5 V to 20 V  | UA78L06C  |      | 35  | 200  | mV   |
|                           |                                                                      |                                 | UA78L06AC |      | 35  | 175  |      |
|                           |                                                                      | V <sub>I</sub> = 9 V to 20 V    | UA78L06C  |      | 29  | 150  |      |
|                           |                                                                      |                                 | UA78L06AC |      | 29  | 125  |      |
| Ripple rejection          | T <sub>J</sub> = 25°C, V <sub>I</sub> = 10 V to 20 V, and f = 120 Hz |                                 | UA78L06C  | 39   | 48  | dB   |      |
|                           |                                                                      |                                 | UA78L06AC | 40   | 48  |      |      |
| Output voltage regulation | T <sub>J</sub> = 25°C                                                | I <sub>O</sub> = 1 mA to 100 mA |           |      | 16  | 80   | mV   |
|                           |                                                                      | I <sub>O</sub> = 1 mA to 40 mA  |           |      | 9   | 40   |      |
| Output noise voltage      | T <sub>J</sub> = 25°C, and f = 10 Hz to 100 kHz                      |                                 |           |      | 46  |      | μV   |
| Dropout voltage           | T <sub>J</sub> = 25°C                                                |                                 |           |      | 1.7 |      | V    |
| Bias current              | T <sub>J</sub> = 25°C                                                |                                 |           |      | 3.9 | 6    | mA   |
|                           | T <sub>J</sub> = 125°C                                               |                                 |           |      |     | 5.5  |      |
| Bias current change       | T <sub>J</sub> = 0°C to 125°C                                        | V <sub>I</sub> = 9 V to 20 V    |           |      |     | 1.5  | mA   |
|                           |                                                                      | I <sub>O</sub> = 1 mA to 40 mA  | UA78L06C  |      |     | 0.2  |      |
|                           |                                                                      |                                 | UA78L06AC |      |     | 0.1  |      |

(1) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a  $0.33\text{-}\mu\text{F}$  capacitor across the input and a  $0.1\text{-}\mu\text{F}$  capacitor across the output.

## 6.8 Electrical Characteristics: UA78L08

at specified virtual junction temperature,  $V_I = 14\text{ V}$ , and  $I_O = 40\text{ mA}$  (unless otherwise noted)

| PARAMETER                 | TEST CONDITIONS <sup>(1)</sup>                                       |                                 |           | MIN  | TYP | MAX  | UNIT |
|---------------------------|----------------------------------------------------------------------|---------------------------------|-----------|------|-----|------|------|
| Output voltage            | V <sub>I</sub> = 10.5 V to 23 V,<br>I <sub>O</sub> = 1 mA to 40 mA   | T <sub>J</sub> = 25°C           | UA78L08C  | 7.36 | 8   | 8.64 | V    |
|                           |                                                                      |                                 | UA78L08AC | 7.7  | 8   | 8.3  |      |
|                           |                                                                      | T <sub>J</sub> = 0°C to 125°C   | UA78L08C  | 7.2  |     | 8.8  |      |
|                           |                                                                      |                                 | UA78L08AC | 7.6  |     | 8.4  |      |
|                           | I <sub>O</sub> = 1 mA to 70 mA                                       | T <sub>J</sub> = 0°C to 125°C   | UA78L08C  | 7.2  |     | 8.8  |      |
|                           |                                                                      |                                 | UA78L08AC | 7.6  |     | 8.4  |      |
| Input voltage regulation  | T <sub>J</sub> = 25°C                                                | V <sub>I</sub> = 10.5 V to 23 V | UA78L08C  |      | 42  | 200  | mV   |
|                           |                                                                      |                                 | UA78L08AC |      | 42  | 175  |      |
|                           |                                                                      | V <sub>I</sub> = 11 V to 23 V   | UA78L08C  |      | 36  | 150  |      |
|                           |                                                                      |                                 | UA78L08AC |      | 36  | 125  |      |
| Ripple rejection          | V <sub>I</sub> = 13 V to 23 V, f = 120 Hz, and T <sub>J</sub> = 25°C |                                 | UA78L08C  | 36   | 46  |      | dB   |
|                           |                                                                      |                                 | UA78L08AC | 37   | 46  |      |      |
| Output voltage regulation | T <sub>J</sub> = 25°C                                                | I <sub>O</sub> = 1 mA to 100 mA |           |      | 18  | 80   | mV   |
|                           |                                                                      | I <sub>O</sub> = 1 mA to 40 mA  |           |      | 10  | 40   |      |
| Output noise voltage      | f = 10 Hz to 100 kHz, and T <sub>J</sub> = 25°C                      |                                 |           |      | 54  |      | μV   |
| Dropout voltage           | T <sub>J</sub> = 25°C                                                |                                 |           |      | 1.7 |      | V    |
| Bias current              | T <sub>J</sub> = 25°C                                                |                                 |           |      | 4   | 6    | mA   |
|                           | T <sub>J</sub> = 125°C                                               |                                 |           |      |     | 5.5  |      |

(1) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a  $0.33\text{-}\mu\text{F}$  capacitor across the input and a  $0.1\text{-}\mu\text{F}$  capacitor across the output.

## Electrical Characteristics: UA78L08 (continued)

at specified virtual junction temperature,  $V_I = 14$  V, and  $I_O = 40$  mA (unless otherwise noted)

| PARAMETER           | TEST CONDITIONS <sup>(1)</sup>                 |                       | MIN | TYP       | MAX | UNIT |
|---------------------|------------------------------------------------|-----------------------|-----|-----------|-----|------|
| Bias current change | $T_J = 0^\circ\text{C}$ to $125^\circ\text{C}$ | $V_I = 11$ V to 23 V  |     |           | 1.5 | mA   |
|                     |                                                | $I_O = 1$ mA to 40 mA |     | UA78L08C  | 0.2 |      |
|                     |                                                |                       |     | UA78L08AC | 0.1 |      |

## 6.9 Electrical Characteristics: UA78L09

at specified virtual junction temperature,  $V_I = 16$  V, and  $I_O = 40$  mA (unless otherwise noted)

| PARAMETER                 | TEST CONDITIONS <sup>(1)</sup>                                       |                                 |           | MIN  | TYP  | MAX  | UNIT |
|---------------------------|----------------------------------------------------------------------|---------------------------------|-----------|------|------|------|------|
| Output voltage            | V <sub>I</sub> = 12 V to 24 V,<br>I <sub>O</sub> = 1 mA to 40 mA     | T <sub>J</sub> = 25°C           | UA78L09C  | 8.3  | 9    | 9.7  | V    |
|                           |                                                                      |                                 | UA78L09AC | 8.6  | 9    | 9.4  |      |
|                           |                                                                      | T <sub>J</sub> = 0°C to 125°C   | UA78L09C  | 8.1  |      | 9.9  |      |
|                           |                                                                      |                                 | UA78L09AC | 8.55 |      | 9.45 |      |
|                           | I <sub>O</sub> = 1 mA to 70 mA, and T <sub>J</sub> = 0°C to 125°C    | UA78L09C                        | 8.1       |      | 9.9  |      |      |
|                           |                                                                      | UA78L09AC                       | 8.55      |      | 9.45 |      |      |
| Input voltage regulation  | T <sub>J</sub> = 25°C                                                | V <sub>I</sub> = 12 V to 24 V   | UA78L09C  |      | 45   | 225  | mV   |
|                           |                                                                      |                                 | UA78L09AC |      | 45   | 175  |      |
|                           |                                                                      | V <sub>I</sub> = 13 V to 24 V   | UA78L09C  |      | 40   | 175  |      |
|                           |                                                                      |                                 | UA78L09AC |      | 40   | 125  |      |
| Ripple rejection          | V <sub>I</sub> = 15 V to 25 V, f = 120 Hz, and T <sub>J</sub> = 25°C |                                 | UA78L09C  | 36   | 45   | dB   |      |
|                           |                                                                      |                                 | UA78L09AC | 38   | 45   |      |      |
| Output voltage regulation | T <sub>J</sub> = 25°C                                                | I <sub>O</sub> = 1 mA to 100 mA |           |      | 19   | 90   | mV   |
|                           |                                                                      | I <sub>O</sub> = 1 mA to 40 mA  |           |      | 11   | 40   |      |
| Output noise voltage      | f = 10 Hz to 100 kHz, and T <sub>J</sub> = 25°C                      |                                 |           |      | 58   |      | μV   |
| Dropout voltage           | T <sub>J</sub> = 25°C                                                |                                 |           |      | 1.7  |      | V    |
| Bias current              | T <sub>J</sub> = 25°C                                                |                                 |           |      | 4.1  | 6    | mA   |
|                           | T <sub>J</sub> = 125°C                                               |                                 |           |      |      | 5.5  |      |
| Bias current change       | T <sub>J</sub> = 0°C to 125°C                                        | V <sub>I</sub> = 13 V to 24 V   |           |      |      | 1.5  | mA   |
|                           |                                                                      | I <sub>O</sub> = 1 mA to 40 mA  | UA78L09C  |      |      | 0.2  |      |
|                           |                                                                      |                                 | UA78L09AC |      |      | 0.1  |      |

(1) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a 0.33- $\mu\text{F}$  capacitor across the input and a 0.1- $\mu\text{F}$  capacitor across the output.

## 6.10 Electrical Characteristics: UA78L10

at specified virtual junction temperature,  $V_I = 14$  V, and  $I_O = 40$  mA (unless otherwise noted)<sup>(1)</sup>

| PARAMETER                 | TEST CONDITIONS <sup>(2)</sup>                                             |                                                | MIN | TYP | MAX  | UNIT          |
|---------------------------|----------------------------------------------------------------------------|------------------------------------------------|-----|-----|------|---------------|
| Output voltage            | $V_I = 13$ V to 25 V, and $I_O = 1$ mA to 40 mA                            | $T_J = 25^\circ\text{C}$                       | 9.6 | 10  | 10.4 | V             |
|                           |                                                                            | $T_J = 0^\circ\text{C}$ to $125^\circ\text{C}$ | 9.5 |     | 10.5 |               |
|                           | $T_J = 0^\circ\text{C}$ to $125^\circ\text{C}$ , and $I_O = 1$ mA to 70 mA |                                                | 9.5 |     | 10.5 |               |
| Input voltage regulation  | $T_J = 25^\circ\text{C}$                                                   | $V_I = 13$ V to 25 V                           |     | 51  | 175  | mV            |
|                           |                                                                            | $V_I = 14$ V to 25 V                           |     | 42  | 125  |               |
| Ripple rejection          | $T_J = 25^\circ\text{C}$ , $V_I = 15$ V to 25 V, and $f = 120$ Hz          |                                                | 37  | 44  |      | dB            |
| Output voltage regulation | $T_J = 25^\circ\text{C}$                                                   | $I_O = 1$ mA to 100 mA                         |     | 20  | 90   | mV            |
|                           |                                                                            | $I_O = 1$ mA to 40 mA                          |     | 11  | 40   |               |
| Output noise voltage      | $T_J = 25^\circ\text{C}$ , and $f = 10$ Hz to 100 kHz                      |                                                |     | 62  |      | $\mu\text{V}$ |
| Dropout voltage           | $T_J = 25^\circ\text{C}$                                                   |                                                |     | 1.7 |      | V             |

(1) Applies to UA78L10AC.

(2) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a 0.33- $\mu\text{F}$  capacitor across the input and a 0.1- $\mu\text{F}$  capacitor across the output.

## Electrical Characteristics: UA78L10 (continued)

at specified virtual junction temperature,  $V_I = 14$  V, and  $I_O = 40$  mA (unless otherwise noted)<sup>(1)</sup>

| PARAMETER           | TEST CONDITIONS <sup>(2)</sup>                 |                       | MIN | TYP | MAX | UNIT |
|---------------------|------------------------------------------------|-----------------------|-----|-----|-----|------|
| Bias current        | $T_J = 25^\circ\text{C}$                       |                       |     | 4.2 | 6   | mA   |
|                     | $T_J = 125^\circ\text{C}$                      |                       |     |     | 5.5 |      |
| Bias current change | $T_J = 0^\circ\text{C}$ to $125^\circ\text{C}$ | $V_I = 14$ V to 25 V  |     |     | 1.5 | mA   |
|                     |                                                | $I_O = 1$ mA to 40 mA |     |     | 0.1 |      |

## 6.11 Electrical Characteristics: UA78L12

at specified virtual junction temperature,  $V_I = 19$  V, and  $I_O = 40$  mA (unless otherwise noted)

| PARAMETER                 | TEST CONDITIONS <sup>(1)</sup>                                       |                                               |           | MIN  | TYP  | MAX  | UNIT |
|---------------------------|----------------------------------------------------------------------|-----------------------------------------------|-----------|------|------|------|------|
| Output voltage            | V <sub>I</sub> = 14 V to 27 V, and<br>I <sub>O</sub> = 1 mA to 40 mA | T <sub>J</sub> = 25°C                         | UA78L12C  | 11.1 | 12   | 12.9 | V    |
|                           |                                                                      |                                               | UA78L12AC | 11.5 | 12   | 12.5 |      |
|                           |                                                                      | T <sub>J</sub> = 0°C to 125°C                 | UA78L12C  | 10.8 |      | 13.2 |      |
|                           |                                                                      |                                               | UA78L12AC | 11.4 |      | 12.6 |      |
|                           | T <sub>J</sub> = 0°C to 125°C, and I <sub>O</sub> = 1 mA to 70 mA    | UA78L12C                                      | 10.8      |      | 13.2 |      |      |
|                           |                                                                      | UA78L12AC                                     | 11.4      |      | 12.6 |      |      |
| Input voltage regulation  | T <sub>J</sub> = 25°C                                                | V <sub>I</sub> = 14.5 V to 27 V               |           |      | 55   | 250  | mV   |
|                           |                                                                      | V <sub>I</sub> = 16 V to 27 V                 |           |      | 49   | 200  |      |
| Ripple rejection          | T <sub>J</sub> = 25°C                                                | V <sub>I</sub> = 15 V to 25 V, and f = 120 Hz | UA78L12C  | 36   | 42   |      | dB   |
|                           |                                                                      |                                               | UA78L12AC | 37   | 42   |      |      |
| Output voltage regulation | T <sub>J</sub> = 25°C                                                | I <sub>O</sub> = 1 mA to 100 mA               |           |      | 22   | 100  | mV   |
|                           |                                                                      | I <sub>O</sub> = 1 mA to 40 mA                |           |      | 13   | 50   |      |
| Output noise voltage      | T <sub>J</sub> = 25°C, and f = 10 Hz to 100 kHz                      |                                               |           |      | 70   |      | μV   |
| Dropout voltage           | T <sub>J</sub> = 25°C                                                |                                               |           |      | 1.7  |      | V    |
| Bias current              | T <sub>J</sub> = 25°C                                                |                                               |           |      | 4.3  | 6.5  | mA   |
|                           | T <sub>J</sub> = 125°C                                               |                                               |           |      |      | 6    |      |
| Bias current change       | T <sub>J</sub> = 0°C to 125°C                                        | V <sub>I</sub> = 16 V to 27 V                 |           |      |      | 1.5  | mA   |
|                           |                                                                      | I <sub>O</sub> = 1 mA to 40 mA                | UA78L12C  |      |      | 0.2  |      |
|                           |                                                                      |                                               | UA78L12AC |      |      | 0.1  |      |

(1) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a 0.33- $\mu\text{F}$  capacitor across the input and a 0.1- $\mu\text{F}$  capacitor across the output.

## 6.12 Electrical Characteristics: UA78L15

at specified virtual junction temperature,  $V_I = 23$  V, and  $I_O = 40$  mA (unless otherwise noted)

| PARAMETER                | TEST CONDITIONS <sup>(1)</sup>                                         |                                                      |           | MIN   | TYP   | MAX   | UNIT |
|--------------------------|------------------------------------------------------------------------|------------------------------------------------------|-----------|-------|-------|-------|------|
| Output voltage           | V <sub>I</sub> = 17.5 V to 30 V,<br>and I <sub>O</sub> = 1 mA to 40 mA | T <sub>J</sub> = 25°C                                | UA78L15C  | 13.8  | 15    | 16.2  | V    |
|                          |                                                                        |                                                      | UA78L15AC | 14.4  | 15    | 15.6  |      |
|                          |                                                                        | T <sub>J</sub> = 0°C to 125°C                        | UA78L15C  | 13.5  |       | 16.5  |      |
|                          |                                                                        |                                                      | UA78L15AC | 14.25 |       | 15.75 |      |
|                          | T <sub>J</sub> = 0°C to 125°C, and I <sub>O</sub> = 1 mA to 70 mA      | UA78L15C                                             | 13.5      |       | 16.5  |       |      |
|                          |                                                                        | UA78L15AC                                            | 14.25     |       | 15.75 |       |      |
| Input voltage regulation | T <sub>J</sub> = 25°C                                                  | V <sub>I</sub> = 17.5 V to 30 V                      |           |       | 65    | 300   | mV   |
|                          |                                                                        | V <sub>I</sub> = 20 V to 30 V                        |           |       | 58    | 250   |      |
| Ripple rejection         | T <sub>J</sub> = 25°C                                                  | V <sub>I</sub> = 18.5 V to 28.5 V,<br>and f = 120 Hz | UA78L15C  | 33    | 39    |       | dB   |
|                          |                                                                        |                                                      | UA78L15AC | 34    | 39    |       |      |

(1) Pulse-testing techniques maintain  $T_J$  as close to  $T_A$  as possible. Thermal effects must be taken into account separately. All characteristics are measured with a 0.33- $\mu\text{F}$  capacitor across the input and a 0.1- $\mu\text{F}$  capacitor across the output.

## Electrical Characteristics: UA78L15 (continued)

at specified virtual junction temperature,  $V_I = 23\text{ V}$ , and  $I_O = 40\text{ mA}$  (unless otherwise noted)

| PARAMETER                 | TEST CONDITIONS <sup>(1)</sup>                                      |                                                                           | MIN | TYP | MAX | UNIT          |
|---------------------------|---------------------------------------------------------------------|---------------------------------------------------------------------------|-----|-----|-----|---------------|
| Output voltage regulation | $T_J = 25^\circ\text{C}$                                            | $I_O = 1\text{ mA to }100\text{ mA}$                                      |     | 25  | 150 | mV            |
|                           |                                                                     | $I_O = 1\text{ mA to }40\text{ mA}$                                       |     | 15  | 75  |               |
| Output noise voltage      | $T_J = 25^\circ\text{C}$ , and $f = 10\text{ Hz to }100\text{ kHz}$ |                                                                           |     | 82  |     | $\mu\text{V}$ |
| Dropout voltage           | $T_J = 25^\circ\text{C}$                                            |                                                                           |     | 1.7 |     | V             |
| Bias current              | $T_J = 25^\circ\text{C}$                                            |                                                                           |     | 4.6 | 6.5 | mA            |
|                           | $T_J = 125^\circ\text{C}$                                           |                                                                           |     |     | 6   |               |
| Bias current change       | $T_J = 0^\circ\text{C to }125^\circ\text{C}$                        | $V_I = 10\text{ V to }30\text{ V}$<br>$I_O = 1\text{ mA to }40\text{ mA}$ |     |     | 1.5 | mA            |
|                           |                                                                     |                                                                           |     |     | 0.2 |               |
|                           |                                                                     |                                                                           |     |     | 0.1 |               |

## 6.13 Typical Characteristics




Figure 1. Bias Current vs Load Current




Figure 2. Bias Current vs Input Voltage




Figure 3. Line Regulation





Figure 4. Load Regulation

## 7 Detailed Description

### 7.1 Overview

The UA78L00 series of fixed-voltage integrated-circuit voltage regulators is designed for a wide range of applications. Each of these regulators can deliver up to 100 mA of output current at a fixed output voltage depending on the device variant.

### 7.2 Functional Block Diagram



NOTE: Resistor values shown are nominal.

### 7.3 Feature Description

The UA78L00 series of linear regulators are easy-to-use, fixed-output voltage regulators. The devices enable up to 100 mA of current and feature short-circuit current limiting and thermal overload protection.

### 7.4 Device Functional Modes

#### 7.4.1 Fixed-Output Mode

These devices are available in fixed-output voltages. Table 1 describes the typical output voltage provided by each device variation.

**Table 1. UA78L00 Typical Device Voltage Outputs**

| DEVICE  | TYPICAL OUTPUT VOLTAGE (V) |
|---------|----------------------------|
| UA78L02 | 2.6                        |
| UA78L05 | 5                          |
| UA78L06 | 6.2                        |
| UA78L08 | 8                          |
| UA78L09 | 9                          |
| UA78L10 | 10                         |
| UA78L12 | 12                         |
| UA78L15 | 15                         |

## 8 Applications and Implementation

### NOTE


Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### 8.1 Application Information

The UA78L00 devices are ideal for use as linear regulators with only a few external components needed. The UA78L00 devices can also be used to clean power supply noise by attenuating ripple on the input signal.

### 8.2 Typical Application

The UA78L00 devices are typically used as fixed-output linear regulators, sourcing current up to 100 mA into a load.



Copyright © 2016, Texas Instruments Incorporated

**Figure 5. Fixed Output Regulator**


#### 8.2.1 Design Requirements

The COMMON pin must be tied to ground to set the OUTPUT pin to the desired fixed output voltage.

Although not required, a 0.33-μF bypass capacitor is recommended on the input, and a 0.1-μF bypass capacitor is recommended on the output.

#### 8.2.2 Detailed Design Procedure

Occasionally, the input voltage to the regulator can collapse faster than the output voltage. For example, this can occur when the input supply is crowbarred during an output overvoltage condition. If the output voltage is greater than approximately 7 V, the emitter-base junction of the series-pass element (internal or external) could break down and be damaged. To prevent this, a diode shunt can be employed as shown in [Figure 6](#).




Copyright © 2016, Texas Instruments Incorporated

**Figure 6. Reverse-Bias-Protection Circuit**

## Typical Application (continued)


In many cases, a regulator powers a load that is not connected to ground, but instead, is connected to a voltage source of opposite polarity (for example, operational amplifiers, level-shifting circuits, and so on). In these cases, a clamp diode should be connected to the regulator output as shown in Figure 7. This protects the regulator from output polarity reversals during startup and short-circuit operation.



Copyright © 2016, Texas Instruments Incorporated

**Figure 7. Output Polarity-Reversal-Protection Circuit**


## 8.2.3 Application Curves



**Figure 8. Output Voltage vs Input Voltage**

## 8.3 System Examples

### 8.3.1 Positive Regulator in Negative Configuration



Copyright © 2016, Texas Instruments Incorporated

**Figure 9. Positive Regulator in Negative Configuration ( $V_I$  Must Float)**


### 8.3.2 Current Limiter Circuit

Figure 10 shows an example of using the UA78L00 as a current limiter. The output current limit is set by Equation 1.

$$I_O = \left( \frac{V_O}{R1} \right) + I_O \text{ Bias Current}$$

(1)

## System Examples (continued)



Copyright © 2016, Texas Instruments Incorporated

Figure 10. Current Limiter Example

## 9 Power Supply Recommendations

See [Recommended Operating Conditions](#) for the recommended power supply voltages for each variation of the UA78L00. Note that each device variant may have a different recommended maximum operating voltage.

## 10 Layout

### 10.1 Layout Guidelines

Keep trace widths large enough to eliminate problematic  $I \times R$  voltage drops at the input and output terminals. Bypass capacitors should be placed as close to the UA78L00 as possible. Additional copper and vias connected to ground facilitate additional thermal dissipation, preventing the device from reaching thermal overload.

### 10.2 Layout Example




Figure 11. Example Layout for PK Package

## 11 Device and Documentation Support

### 11.1 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

**Table 2. Related Links**

| PARTS    | PRODUCT FOLDER             | SAMPLE & BUY               | TECHNICAL DOCUMENTS        | TOOLS & SOFTWARE           | SUPPORT & COMMUNITY        |
|----------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| UA78L02A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L05  | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L05A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L06A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L08A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L09A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L10A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L12A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |
| UA78L15A | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> | <a href="#">Click here</a> |

### 11.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 11.3 Community Resource

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

**TI E2E™ Online Community** *TI's Engineer-to-Engineer (E2E) Community*. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

### 11.4 Trademarks

E2E is a trademark of Texas Instruments.  
All other trademarks are the property of their respective owners.

### 11.5 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 11.6 Glossary

**SLYZ022** — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

## 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UA78L02ACD       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L02A                  | <a href="#">Samples</a> |
| UA78L02ACDG4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L02A                  | <a href="#">Samples</a> |
| UA78L02ACLP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L02AC                 | <a href="#">Samples</a> |
| UA78L02ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L02AC                 | <a href="#">Samples</a> |
| UA78L05ACD       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05A                  | <a href="#">Samples</a> |
| UA78L05ACDE4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05A                  | <a href="#">Samples</a> |
| UA78L05ACDG4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05A                  | <a href="#">Samples</a> |
| UA78L05ACDR      | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU   CU SN       | Level-1-260C-UNLIM   | 0 to 125     | 78L05A                  | <a href="#">Samples</a> |
| UA78L05ACDRE4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05A                  | <a href="#">Samples</a> |
| UA78L05ACDRG4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05A                  | <a href="#">Samples</a> |
| UA78L05ACLP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05AC                 | <a href="#">Samples</a> |
| UA78L05ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05AC                 | <a href="#">Samples</a> |
| UA78L05ACLPM     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05AC                 | <a href="#">Samples</a> |
| UA78L05ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05AC                 | <a href="#">Samples</a> |
| UA78L05ACLPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05AC                 | <a href="#">Samples</a> |
| UA78L05ACLPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05AC                 | <a href="#">Samples</a> |
| UA78L05ACPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F5                      | <a href="#">Samples</a> |

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UA78L05ACPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F5                      | <a href="#">Samples</a> |
| UA78L05AID       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AIDG4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AIDR      | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AIDRE4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AIDRG4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AILP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AILPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AILPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AILPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | -40 to 125   | 78L05AI                 | <a href="#">Samples</a> |
| UA78L05AIPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | -40 to 125   | J5                      | <a href="#">Samples</a> |
| UA78L05AIPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | -40 to 125   | J5                      | <a href="#">Samples</a> |
| UA78L05CD        | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |
| UA78L05CDG4      | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |
| UA78L05CDR       | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |
| UA78L05CDRE4     | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |
| UA78L05CDRG4     | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |
| UA78L05CLP       | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UA78L05CLPE3     | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |
| UA78L05CLPR      | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L05C                  | <a href="#">Samples</a> |
| UA78L05CPK       | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | B5                      | <a href="#">Samples</a> |
| UA78L05CPKG3     | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | B5                      | <a href="#">Samples</a> |
| UA78L06ACLP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L06AC                 | <a href="#">Samples</a> |
| UA78L06ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L06AC                 | <a href="#">Samples</a> |
| UA78L06ACLPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L06AC                 | <a href="#">Samples</a> |
| UA78L06ACLPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L06AC                 | <a href="#">Samples</a> |
| UA78L06ACPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F6                      | <a href="#">Samples</a> |
| UA78L06ACPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F6                      | <a href="#">Samples</a> |
| UA78L08ACD       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L08A                  | <a href="#">Samples</a> |
| UA78L08ACDG4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L08A                  | <a href="#">Samples</a> |
| UA78L08ACDR      | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU   CU SN       | Level-1-260C-UNLIM   | 0 to 125     | 78L08A                  | <a href="#">Samples</a> |
| UA78L08ACDRG4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L08A                  | <a href="#">Samples</a> |
| UA78L08ACLP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L08AC                 | <a href="#">Samples</a> |
| UA78L08ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L08AC                 | <a href="#">Samples</a> |
| UA78L08ACLPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L08AC                 | <a href="#">Samples</a> |
| UA78L08ACLPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L08AC                 | <a href="#">Samples</a> |

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UA78L08ACPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F8                      | <a href="#">Samples</a> |
| UA78L08ACPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F8                      | <a href="#">Samples</a> |
| UA78L09ACD       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L09A                  | <a href="#">Samples</a> |
| UA78L09ACDG4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L09A                  | <a href="#">Samples</a> |
| UA78L09ACDR      | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L09A                  | <a href="#">Samples</a> |
| UA78L09ACDRE4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L09A                  | <a href="#">Samples</a> |
| UA78L09ACLP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L09AC                 | <a href="#">Samples</a> |
| UA78L09ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L09AC                 | <a href="#">Samples</a> |
| UA78L09ACLPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L09AC                 | <a href="#">Samples</a> |
| UA78L09ACLPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L09AC                 | <a href="#">Samples</a> |
| UA78L09ACPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F9                      | <a href="#">Samples</a> |
| UA78L09ACPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | F9                      | <a href="#">Samples</a> |
| UA78L10ACD       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L10A                  | <a href="#">Samples</a> |
| UA78L10ACDG4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L10A                  | <a href="#">Samples</a> |
| UA78L10ACDR      | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L10A                  | <a href="#">Samples</a> |
| UA78L10ACDRE4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L10A                  | <a href="#">Samples</a> |
| UA78L10ACDRG4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L10A                  | <a href="#">Samples</a> |
| UA78L10ACLP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L10AC                 | <a href="#">Samples</a> |

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UA78L10ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L10AC                 | <a href="#">Samples</a> |
| UA78L10ACLPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L10AC                 | <a href="#">Samples</a> |
| UA78L10ACLPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L10AC                 | <a href="#">Samples</a> |
| UA78L10ACPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | FA                      | <a href="#">Samples</a> |
| UA78L10ACPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | FA                      | <a href="#">Samples</a> |
| UA78L12ACD       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L12A                  | <a href="#">Samples</a> |
| UA78L12ACDG4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L12A                  | <a href="#">Samples</a> |
| UA78L12ACDR      | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU   CU SN       | Level-1-260C-UNLIM   | 0 to 125     | 78L12A                  | <a href="#">Samples</a> |
| UA78L12ACDRE4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L12A                  | <a href="#">Samples</a> |
| UA78L12ACDRG4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L12A                  | <a href="#">Samples</a> |
| UA78L12ACLP      | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L12AC                 | <a href="#">Samples</a> |
| UA78L12ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L12AC                 | <a href="#">Samples</a> |
| UA78L12ACLPM     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L12AC                 | <a href="#">Samples</a> |
| UA78L12ACL PME3  | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L12AC                 | <a href="#">Samples</a> |
| UA78L12ACLPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L12AC                 | <a href="#">Samples</a> |
| UA78L12ACLPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L12AC                 | <a href="#">Samples</a> |
| UA78L12ACPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | FC                      | <a href="#">Samples</a> |
| UA78L12ACPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | FC                      | <a href="#">Samples</a> |

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| UA78L15ACD       | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L15A                  | <a href="#">Samples</a> |
| UA78L15ACDE4     | ACTIVE        | SOIC         | D                  | 8    | 75             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L15A                  | <a href="#">Samples</a> |
| UA78L15ACDR      | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L15A                  | <a href="#">Samples</a> |
| UA78L15ACDRE4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L15A                  | <a href="#">Samples</a> |
| UA78L15ACDRG4    | ACTIVE        | SOIC         | D                  | 8    | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 125     | 78L15A                  | <a href="#">Samples</a> |
| UA78L15ACLCP     | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L15AC                 | <a href="#">Samples</a> |
| UA78L15ACLPE3    | ACTIVE        | TO-92        | LP                 | 3    | 1000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L15AC                 | <a href="#">Samples</a> |
| UA78L15ACLPR     | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L15AC                 | <a href="#">Samples</a> |
| UA78L15ACLPRE3   | ACTIVE        | TO-92        | LP                 | 3    | 2000           | Pb-Free<br>(RoHS)          | CU SN                   | N / A for Pkg Type   | 0 to 125     | 78L15AC                 | <a href="#">Samples</a> |
| UA78L15ACPK      | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | FF                      | <a href="#">Samples</a> |
| UA78L15ACPKG3    | ACTIVE        | SOT-89       | PK                 | 3    | 1000           | Green (RoHS<br>& no Sb/Br) | CU SN                   | Level-2-260C-1 YEAR  | 0 to 125     | FF                      | <a href="#">Samples</a> |

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

---

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| UA78L05ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L05ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.8               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L05ACDRG4 | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L05ACPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L05AIDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L05AIPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L05CDR    | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L05CPK    | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L06ACPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L08ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L08ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.8               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L08ACDRG4 | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L08ACPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L09ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L09ACPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L10ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L10ACPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L12ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.8               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| UA78L12ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L12ACDRG4 | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L12ACPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |
| UA78L15ACDR   | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| UA78L15ACPK   | SOT-89       | PK              | 3    | 1000 | 180.0              | 12.4               | 4.91    | 4.52    | 1.9     | 8.0     | 12.0   | Q3            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal


| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| UA78L05ACDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L05ACDR   | SOIC         | D               | 8    | 2500 | 364.0       | 364.0      | 27.0        |
| UA78L05ACDRG4 | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L05ACPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L05AIDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L05AIPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L05CDR    | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L05CPK    | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L06ACPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L08ACDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L08ACDR   | SOIC         | D               | 8    | 2500 | 364.0       | 364.0      | 27.0        |
| UA78L08ACDRG4 | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |

---

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| UA78L08ACPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L09ACDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L09ACPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L10ACDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L10ACPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L12ACDR   | SOIC         | D               | 8    | 2500 | 364.0       | 364.0      | 27.0        |
| UA78L12ACDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L12ACDRG4 | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L12ACPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |
| UA78L15ACDR   | SOIC         | D               | 8    | 2500 | 340.5       | 338.1      | 20.6        |
| UA78L15ACPK   | SOT-89       | PK              | 3    | 1000 | 340.0       | 340.0      | 38.0        |

PK (R-PSSO-F3)

PLASTIC SINGLE-IN-LINE PACKAGE



4040234/D 02/2006

- NOTES:
- All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - This drawing is subject to change without notice.
  - The center lead is in electrical contact with the tab.
  - Body dimensions do not include mold flash or protrusion. Mold flash and protrusion not to exceed 0.15 per side.
- $\triangle E$  Thermal pad contour optional within these dimensions.
- $\triangle F$  Falls within JEDEC TO-243 variation AA, except minimum lead length, pin 2 minimum lead width, minimum tab width.

# PK (R-PDSO-G3)




4208221/A 09/06

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate designs.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

LP (O-PBCY-W3)

PLASTIC CYLINDRICAL PACKAGE




4040001-2/E 08/13

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Lead dimensions are not controlled within this area.
  - Falls within JEDEC TO-226 Variation AA (TO-226 replaces TO-92).
  - E. Shipping Method:  
 Straight lead option available in bulk pack only.  
 Formed lead option available in tape & reel or ammo pack.  
 Specific products can be offered in limited combinations of shipping mediums and lead options.  
 Consult product folder for more information on available options.

LP (O-PBCY-W3)


PLASTIC CYLINDRICAL PACKAGE



- NOTES:
- All linear dimensions are in inches (millimeters).
  - This drawing is subject to change without notice.
  - Tape and Reel information for the Formed Lead Option package.

D (R-PDSO-G8)

PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - $\triangle C$  Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
  - $\triangle D$  Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
  - E. Reference JEDEC MS-012 variation AA.

D (R-PDSO-G8)

PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate designs.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated