
TMPIM 650 V 50 A Converter-Inverter-PFCs Module

Product Preview

NXH50M65L4C2SG



DIP27 73.2x40.2
CASE 184AA

The NXH50M65L4C2SG is a transfer−molded power module with AI2O3 substrate containing a converter−inverter−PFC circuit consisting of single phase converter with four 75 A, 1600 V rectifiers, six 50 A, 600 V IGBTs with inverse diodes, 2−Channel interleaved PFC containing two 75 A, 650 V PFC IGBT with inverse diode, two 50 A, 650 V PFC diode, and an NTC thermistor.


Features

- 2−Channel Interleaved PFC with Wide Switching Frequency 18 kHz ~ 65 kHz
- 6 mm Clearance Distance between Pin to Heatsink
- Compact 73 mm x 40 mm x 8 mm Package
- Solderable Pins
- Thermistor
- These Devices are Pb−Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- HVAC
- Industrial Motor Drives
- Servo Drives

MARKING DIAGRAM



XXX = Specific Device Code
ZZZ = Assembly Lot Code
AT = Assembly & Test Location
Y = Year
WW = Work Week

ORDERING INFORMATION

See detailed ordering and shipping information on page 18 of this data sheet.

This document contains information on a product under development. **onsemi** reserves the right to change or discontinue this product without notice.




Figure 1. NXH50M65L4C2SG Schematic Diagram

Downloaded from Arrow.com.

PIN CONFIGURATION TABLE

Pin	Name
1	N1.1
2	L1−
3	EL1
4	GL1
5	L2−
6	EL2
7	GL2
8	U−
9	GuL
10	V−
11	GvL
12	W−
13	GwL
14	T1
15	T2
16	Gwh
17	W
18	Gvh
19	V
20	Guh
21	U
22	DCP.1
23	L2
24	L1
25	P1.1
26	N
27	L




Figure 2. Pin Configuration

Downloaded from Arrow.com.

MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
INVERTER IGBT (T3 − T8)			
Collector−Emitter Voltage	V_{CES}	650	V
Gate−Emitter Voltage	V_{GE}	±20	V
Continuous Collector Current @ T_c = 80°C (Tv_{Jmax} = 175°C)	I_C	50	A
Pulsed Collector Current	I_{Cpulse}	150	A
INVERTER INVERSE DIODE (D9 − D14)			
Peak Repetitive Reverse Voltage	V_{RRM}	600	V
Continuous Forward Current @ T_c = 80°C (Tv_{Jmax} = 175°C)	I_F	30	A
Repetitive Peak Forward Current	I_{FRM}	90	A
PFC IGBT (T1, T2)			
Collector−Emitter Voltage	V_{CES}	650	V
Gate−Emitter Voltage	V_{GE}	±20	V
Continuous Collector Current @ T_c = 80°C (Tv_{Jmax} = 175°C)	I_C	65	A
Pulsed Collector Current	I_{Cpulse}	195	A
PFC INVERSE DIODE (D5, D6)			
Peak Repetitive Reverse Voltage	V_{RRM}	650	V
Continuous Forward Current @ T_c = 80°C (Tv_{Jmax} = 175°C)	I_F	15	A
Repetitive Peak Forward Current	I_{FRM}	45	A
PFC DIODE (D7, D8)			
Peak Repetitive Reverse Voltage	V_{RRM}	650	V
Continuous Forward Current @ T_c = 80°C (Tv_{Jmax} = 175°C)	I_F	50	A
Repetitive Peak Forward Current	I_{FRM}	150	A
CONVERTER DIODE (D1 − D4)			
Peak Repetitive Reverse Voltage	V_{RRM}	1600	V
Continuous Forward Current @ T_c = 80°C (Tv_{Jmax} = 150°C)	I_F	74	A
Repetitive Peak Forward Current	I_{FRM}	222	A
I^2t Value (10 ms Single Half−sine Wave) @ 150°C	I^2t	1200	A^2s
Surge Current (10 ms sin 180°) @ 25°C	IFSM	635	A
THERMAL PROPERTIES			
Storage Temperature Range	T_{stg}	−40 to 125	°C
INSULATION PROPERTIES			
Isolation Test Voltage, t = 1 s, 50 Hz	V_{is}	3000	V_{RMS}
Internal Isolation		AI2O3	
Creepage Distance		6.0	mm
Clearance Distance		6.0	mm
Comperative Tracking Index	CTI	>400	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters.

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Parameter	Test Condition	Symbol	Min	Typ	Max	Unit
INVERTER IGBT CHARACTERISTICS (T3 − T8)						
Collector−Emitter Cutoff Current	V_{GE} = 0 V, V_{CE} = 600 V	I_{CES}	–	–	250	μA
Collector−Emitter Saturation Voltage	V_{GE} = 15 V, I_C = 50 A, T_J = 25°C	$V_{CE(sat)}$	–	1.6	2	V
	V_{GE} = 15 V, I_C = 50 A, T_J = 150°C		–	1.8	–	
Gate−Emitter Threshold Voltage	V_{GE} = V_{CE}, I_C = 50 mA	$V_{GE(TH)}$	3.8	4.7	5.7	V
Gate Leakage Current	V_{GE} = 20 V, V_{CE} = 0 V	I_{GES}	–	–	400	nA
Turn−on Delay Time	T_J = 25°C V_{CE} = 350 V, I_C = 21 A V_{GE} = +15 V / −8 V, R_G = 25 Ω	$t_{d(on)}$	–	41	–	ns
Rise Time		t_r	–	24	–	
Turn−off Delay Time		$t_{d(off)}$	–	184	–	
Fall Time		t_f	–	78	–	
Turn−on Switching Loss per Pulse		E_{on}	–	270	–	μJ
Turn off Switching Loss per Pulse		E_{off}	–	450	–	
Turn−on Delay Time	T_J = 125 °C V_{CE} = 350 V, I_C = 21 A V_{GE} = +15 V / −8 V, R_G = 25 Ω	$t_{d(on)}$	–	52.8	–	ns
Rise Time		t_r	–	25.2	–	
Turn−off Delay Time		$t_{d(off)}$	–	232	–	
Fall Time		t_f	–	140.2	–	
Turn−on Switching Loss per Pulse		E_{on}	–	390	–	μJ
Turn off Switching Loss per Pulse		E_{off}	–	710	–	
Input Capacitance	V_{CE} = 20 V. V_{GE} = 0 V. f = 1 MHz	C_{ies}	–	2608	–	pF
Output Capacitance		C_{oes}	–	77	–	
Reverse Transfer Capacitance		C_{res}	–	21	–	
Total Gate Charge	V_{CE} = 480 V, I_C = 50 A, V_{GE} = −15 V~+15 V	Q_g	–	122	–	nC
Temperature under switching conditions		Tvj op	−40		150	°C
Thermal Resistance − Chip−to−Case		R_{thJC}	–	0.73	–	°C/W
Thermal Resistance − Chip−to−Heatsink	Thermal grease, Thickness ≈ 3mil, λ = 2.8 W/mK	R_{thJH}	–	1.13	–	°C/W
INVERTER INVERSE DIODE CHARACTERISTICS (D9 − D14)						
Diode Forward Voltage	I_F = 30 A, T_J = 25°C	V_F	–	1.9	2.7	V
	I_F = 30 A, T_J = 150°C		–	1.6	–	
Reverse Recovery Time	T_J = 25 °C V_{CE} = 350 V, I_C = 21 A V_{GE} = +18 V / −8 V, R_G = 25 Ω	t_{rr}	−	34	−	ns
Reverse Recovery Charge		Q_{rr}	–	210	–	nC
Peak Reverse Recovery Current		I_{RRM}	–	11	–	A
Reverse Recovery Energy		E_{rr}	–	37	–	μJ
Reverse Recovery Time	T_J = 125 °C V_{CE} = 350 V, I_C = 21 A V_{GE} = +15 V / −8 V, R_G = 25 Ω	t_{rr}		46		ns
Reverse Recovery Charge		Q_{rr}	–	472	–	nC
Peak Reverse Recovery Current		I_{RRM}	–	16	–	A
Reverse Recovery Energy		E_{rr}	–	82	–	μJ
Temperature under Switching Conditions		Tvj op	−40		150	°C
Thermal Resistance − Chip−to−Case		R_{thJC}	–	1.03	–	°C/W
Thermal Resistance − Chip−to−Heatsink	Thermal grease, Thickness ≈ 3 mil, λ = 2.8 W/mK	R_{thJH}	–	1.42	–	°C/W

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted) (continued)

Parameter	Test Condition	Symbol	Min	Typ	Max	Unit
PFC IGBT CHARACTERISTICS (T1, T2)						
Collector−Emitter Cutoff Current	V_{GE} = 0 V, V_{CE} = 650 V	I_{CES}	–	–	250	μA
Collector−Emitter Saturation Voltage	V_{GE} = 15 V, I_C = 75 A, T_J = 25°C	$V_{CE(sat)}$	–	1.4	2.2	V
	V_{GE} = 15 V, I_C = 75 A, T_J = 150°C		–	1.6	–	
Gate−Emitter Threshold Voltage	V_{GE} = V_{CE}, I_C = 75 mA	$V_{GE(TH)}$	3.8	4.5	5.7	V
Gate Leakage Current	V_{GE} = 20 V, V_{CE} = 0 V	I_{GES}	–	–	400	nA
Turn−on Delay Time	T_J = 25°C V_{CE} = 400 V, I_C = 24 A V_{GE} = +15 V / −8 V, R_G = 10 Ω	$t_{d(on)}$	–	47	–	ns
Rise Time		t_r	–	12	–	
Turn−off Delay Time		$t_{d(off)}$	–	190	–	
Fall Time		t_f	–	8	–	
Turn−on Switching Loss per Pulse		E_{on}	–	240	–	μJ
Turn off Switching Loss per Pulse		E_{off}	–	250	–	
Turn−on Delay Time	T_J = 125 °C V_{CE} = 400 V, I_C = 24 A V_{GE} = +15 V / −8 V, R_G = 10 Ω	$t_{d(on)}$	–	45	–	ns
Rise Time		t_r	–	14	–	
Turn−off Delay Time		$t_{d(off)}$	–	218	–	
Fall Time		t_f	–	25	–	
Turn−on Switching Loss per Pulse		E_{on}	–	390	–	μJ
Turn off Switching Loss per Pulse		E_{off}	–	350	–	
Input Capacitance	V_{CE} = 20 V, V_{GE} = 0 V, f = 10 kHz	C_{ies}	–	4877	–	pF
Output Capacitance		C_{oes}	–	77	–	
Reverse Transfer Capacitance		C_{res}	–	21	–	
Total Gate Charge	V_{CE} = 480 V, I_C = 75 A, V_{GE} = 0 V~+15 V	Q_g	–	151	–	nC
Temperature under Switching Conditions		Tvj op	−40		150	°C
Thermal Resistance − Chip−to−Case		R_{thJC}	–	0.63	–	°C/W
Thermal Resistance − Chip−to−Heatsink	Thermal grease, Thickness ≈ 3 mil, λ = 2.8 W/mK	R_{thJH}	–	1.02	–	°C/W
PFC IGBT INVERSE DIODE CHARACTERISTICS (D5, D6)						
Rectifier Forward Voltage	I_F = 15 A, T_J = 25°C	V_F	–	1.9	2.4	V
	I_F = 15 A, T_J = 150°C		–	1.8	–	
Temperature under Switching Conditions		Tvj op	−40		150	°C
Thermal Resistance − Chip−to−Case		R_{thJC}	–	2.35	–	°C/W
Thermal Resistance − Chip−to−Heatsink	Thermal grease, Thickness ≈ 3 mil, λ = 2.8 W/mK	R_{thJH}	–	2.83	–	°C/W
PFC DIODE CHARACTERISTICS (D7, D8)						
Rectifier Reverse Leakage Current	V_R = 650 V	I_R	–	−	200	μA
Rectifier Forward Voltage	I_F = 50 A, T_J = 25°C	V_F	–	2.1	2.8	V
	I_F = 50 A, T_J = 150°C		–	1.7	–	
Reverse Recovery Time	T_J = 25 °C V_{CE} = 400 V, I_C = 24 A V_{GE} = +15 V / −8 V, R_G = 10 Ω	t_{rr}	−	24	−	ns
Reverse Recovery Charge		Q_{rr}	–	456	–	nC
Peak Reverse Recovery Current		I_{RRM}	–	32	–	A
Reverse Recovery Energy		E_{rr}	–	109	–	μJ

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted) (continued)

Parameter	Test Condition	Symbol	Min	Typ	Max	Unit
PFC DIODE CHARACTERISTICS (D7, D8)						
Reverse Recovery Time	T_J = 125 °C V_{CE} = 400 V, I_C = 24 A V_{GE} = +15 V / −8 V, R_G = 10 Ω	t_{rr}		36		ns
Reverse Recovery Charge		Q_{rr}	–	902	–	nC
Peak Reverse Recovery Current		I_{RRM}	–	42	–	A
Reverse Recovery Energy		E_{rr}	–	209	–	μJ
Temperature under Switching Conditions		Tvj op	−40		150	°C
Thermal Resistance − Chip−to−Case		R_{thJC}	–	0.75	–	°C/W
Thermal Resistance − Chip−to−Heatsink	Thermal grease, Thickness ≈ 3 mil, λ = 2.8 W/mK	R_{thJH}	–	1.12	–	°C/W
CONVERTER DIODE CHARACTERISTICS (D1−D4)						
Rectifier Reverse Leakage Current	V_R = 1600 V	I_R	–	−	200	μA
Rectifier Forward Voltage	I_F = 75 A, T_J = 25°C	V_F	–	1.3	1.7	V
	I_F = 75 A, T_J = 150°C		–	1.4	–	
Temperature under Switching Conditions		Tvj op	−40		150	°C
Thermal Resistance − Chip−to−Case		R_{thJC}	–	0.54	–	°C/W
Thermal Resistance − Chip−to−Heatsink	Thermal grease, Thickness ≈ 3 mil, λ = 2.8 W/mK	R_{thJH}	–	0.87	–	°C/W
THERMISTOR CHARACTERISTICS						
Nominal Resistance	T = 25°C	R_{25}	–	5	–	kΩ
Nominal Resistance	T = 100°C	R_{100}	–	493.3	–	Ω
Deviation of R25		ΔR/R	−5	–	5	%
Power Dissipation		P_D	–	20	–	mW
Power Dissipation Constant			–	1.4	–	mW/K
B−value	B (25/50), tolerance ±2%		–	3375	–	K
B−value	B (25/100), tolerance ±2%		–	3455	–	K

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − T3 − T8 INVERTER IGBT & D9−D14 INVERSE DIODE




Figure 3. IGBT Typical Output Characteristics




Figure 4. IGBT Typical Output Characteristics




Figure 5. Typical Transfer Characteristics




Figure 6. Diode Typical Forward Characteristics




Figure 7. Typical Turn ON Loss vs. IC




Figure 8. Typical Turn ON Loss vs. RG

Downloaded from Arrow.com.




Figure 9. Typical Turn OFF Loss vs. IC




Figure 10. Typical Turn OFF Loss vs. RG




Figure 11. Typical Reverse Recovery Energy Loss vs. IC




Figure 12. Typical Reverse Recovery Energy Loss vs. RG




Figure 13. Typical Turn−Off Switching Time vs. IC




Figure 14. Typical Turn−Off Switching Time vs. Rg

Downloaded from Arrow.com.




Figure 15. Typical Turn−On Switching Time vs. IC




Figure 16. Typical Turn−Off Switching Time vs. Rg




Figure 17. Typical Reverse Recovery Time vs. IC




Figure 18. Typical Reverse Recovery Time vs. RG




Figure 19. Typical Reverse Recovery Charge vs. IC




Figure 20. Typical Reverse Recovery Charge vs. Rg

Downloaded from Arrow.com.




Figure 21. Typical Reverse Recovery Peak Current vs. IC




Figure 22. Typical Reverse Recovery Peak Current vs. RG




Figure 23. Typical di/dt Current Slope vs. IC




Figure 24. Typical di/dt Current Slope vs. RG




Figure 25. IGBT Junction−to−Case Transient Thermal Impedance

Downloaded from Arrow.com.




Figure 26. Diode Junction−to−Case Transient Thermal Impedance




Figure 27. IGBT FBSOA




Figure 28. IGBT RBSOA




Figure 29. IGBT Gate Voltage vs. Gate Charge




Figure 30. IGBT Capacitance vs. Collector−Emitter Voltage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − T1 − T2 PFC IGBT & D5 − D6 INVERSE DIODE




Figure 31. IGBT Typical Output Characteristic




Figure 32. IGBT Typical Output Characteristic




Figure 33. IGBT Typical Transfer Characteristic




Figure 34. Diode Typical Forward Characteristic




Figure 35. Typical Turn ON Loss vs. IC




Figure 36. Typical Turn ON Loss vs. Rg

Downloaded from Arrow.com.




Figure 37. Typical Turn OFF Loss vs. IC




Figure 38. Typical Turn OFF Loss vs. RG




Figure 39. Typical Reverse Recovery Energy Loss vs. IC




Figure 40. Typical Reverse Recovery Energy Loss vs. RG




Figure 41. Typical Turn−Off Switching Time vs. IC




Figure 42. Typical Turn−Off Switching Time vs. Rg

Downloaded from Arrow.com.




Figure 43. Typical Turn−On Switching Time vs. IC




Figure 44. Typical Turn−Off Switching Time vs. Rg




Figure 45. Typical Reverse Recovery Time vs. IC




Figure 46. Typical Reverse Recovery Time vs. RG




Figure 47. Typical Reverse Recovery Charge vs. IC




Figure 48. Typical Reverse Recovery Charge vs. Rg

Downloaded from Arrow.com.




Figure 49. Typical Reverse Recovery Peak Current vs. IC




Figure 50. Typical Reverse Recovery Peak Current vs. RG




Figure 51. Typical di/dt Current Slope vs. IC




Figure 52. Typical di/dt Current Slope vs. RG




Figure 53. IGBT Junction−to−Case Transient Thermal Impedance

Downloaded from Arrow.com.




Figure 54. Diode Junction−to−Case Transient Thermal Impedance




Figure 55. IGBT FBSOA




Figure 56. IGBT RBSOA




Figure 57. IGBT Gate Voltage vs. Gate Charge




Figure 58. IGBT Capacitance vs. Collector−Emitter Voltage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − D7, D8 PFC DIODE & D1 − D4 CONVERTER DIODE




Figure 59. PFC Diode Forward Characteristics




Figure 60. Converter Diode Forward Characteristics




Figure 61. PFC Diode Junction−to−Case Transient Thermal Impedance




Figure 62. Converter Diode Junction−to−Case Transient Thermal Impedance

Downloaded from Arrow.com.


ORDERING INFORMATION

Device Order Number	Specific Device Marking	Package Type	Shipping
NXH50M65L4C2SG	NXH50M65L4C2SG	DIP27 73.2x40.2 (Pb−Free)	6 Units / Tube

Downloaded from Arrow.com.


MECHANICAL CASE OUTLINE
PACKAGE DIMENSIONS

ON Semiconductor®




DIP27 73.2x40.2
CASE 184AA
ISSUE B


DATE 15 JUL 2021



SIDE VIEW




TOP VIEW




END VIEW

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	15.50	16.00	16.50
A2	7.80	8.00	8.20
A3		6.00 REF	
b	1.10	1.20	1.30
c	0.70	0.80	0.90
D	72.70	73.20	73.70
D1	67.30	67.80	68.30
D2		57.30 REF	
E	39.70	40.20	40.70
E1	46.70	47.20	47.70
E2		33.87 REF	
e		2.54 BSC	
F	4.00	4.20	4.40
L		8.00 REF	
L1	3.50	4.00	4.50
M	4°	5°	6°



SIDE VIEW




BOTTOM VIEW

NOTES:

1. Dimensioning and tolerancing as per ASME Y14.5M, 2009
2. Controlling Dimension: Millimeters
3. Dimensions are exclusive of Burrs, Mold Flash, and Tiebar extrusions
4. Dimensions ”b” and ”c” apply to plated leads
5. Position of the leads is determine at the root of the lead where it exits the package body

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code
ZZZ = Assembly Lot Code
A = Assembly Site
T = Test Site
Y = Year
WW = Work Week

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON23070H**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**DIP27 73.2x40.2**	**PAGE 1 OF 1**

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2018

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.