



## HF/VHF/UHF RF power N-channel MOSFETs

Datasheet - production data



**Figure 1. Pin connection**



### Features

- Gold metalization
- Excellent thermal stability
- Common source configuration
- $P_{OUT} = 300 \text{ W min.}$  with 20 dB gain @ 30 MHz
- Thermally enhanced packaging for lower junction temperatures

### Description

The SD2933 is a gold metalized N-channel MOS field-effect RF power transistor, intended for use in 50 V dc large signal applications up to 150 MHz. Its special low thermal resistance package makes it ideal for ISM applications, where reliability and ruggedness are critical factors.

**Table 1. Device summary**

| Order code | Marking               | Package | Packaging    |
|------------|-----------------------|---------|--------------|
| SD2933W    | SD2933 <sup>(1)</sup> | M177    | Plastic tray |

1. For more details please refer to [Chapter 6: Marking, packing and shipping specifications](#).

Contents

1      **Electrical data** ..... 3

    1.1    Maximum rating ..... 3

    1.2    Thermal data ..... 3

2      **Electrical characteristics** ..... 4

3      **Impedance** ..... 5

4      **Typical performance (30 MHz)** ..... 6

    4.1    Test circuit (30 MHz) ..... 9

5      **Package information** ..... 12

6      **Marking, packing and shipping specifications** ..... 14

7      **Revision history** ..... 15



# 1 Electrical data

## 1.1 Maximum rating

$T_{CASE} = 25\text{ }^{\circ}\text{C}$

**Table 2. Absolute maximum ratings**

| Symbol         | Parameter                                                                                | Value       | Unit               |
|----------------|------------------------------------------------------------------------------------------|-------------|--------------------|
| $V_{(BR)DSS}$  | Drain source voltage                                                                     | 125         | V                  |
| $V_{DGR}$      | Drain-gate voltage ( $R_{GS} = 1\text{M}\Omega$ )                                        | 125         | V                  |
| $V_{GS}$       | Gate-source voltage                                                                      | $\pm 40$    | V                  |
| $I_D$          | Drain current                                                                            | 40          | A                  |
| $P_{DISS}$     | Power dissipation                                                                        | 648         | W                  |
| $E_{AS}$       | Avalanche energy, single pulse<br>( $I_D = 53\text{ A}$ , $800\text{ }\mu\text{H}$ coil) | 1100        | mJ                 |
| $E_{AR}^{(1)}$ | Avalanche energy, repetitive                                                             | 50          | mJ                 |
| $T_J$          | Max. operating junction temperature                                                      | 200         | $^{\circ}\text{C}$ |
| $T_{STG}$      | Storage temperature                                                                      | -65 to +150 | $^{\circ}\text{C}$ |

1. Repetitive rating: Pulse width limited by maximum junction temperature / repetitive avalanche causes additional power losses that can be calculated as:  $P_{AV} = E_{AR} * f$

## 1.2 Thermal data

**Table 3. Thermal data**

| Symbol      | Parameter                           | Value | Unit                 |
|-------------|-------------------------------------|-------|----------------------|
| $R_{thJ-C}$ | Junction to case thermal resistance | 0.27  | $^{\circ}\text{C/W}$ |

## 2 Electrical characteristics

$T_{CASE} = 25\text{ }^{\circ}\text{C}$

**Table 4. Static**

| Symbol            | Test conditions        |                          |                    | Min.                                                  | Typ. | Max. | Unit          |
|-------------------|------------------------|--------------------------|--------------------|-------------------------------------------------------|------|------|---------------|
| $V_{(BR)DSS}$     | $V_{GS} = 0\text{ V}$  | $I_{DS} = 200\text{ mA}$ |                    | 125                                                   |      |      | V             |
| $I_{DSS}$         | $V_{GS} = 0\text{ V}$  | $V_{DS} = 50\text{ V}$   |                    |                                                       |      | 100  | $\mu\text{A}$ |
| $I_{GSS}$         | $V_{GS} = 20\text{ V}$ | $V_{DS} = 0\text{ V}$    |                    |                                                       |      | 500  | nA            |
| $V_{GS(Q)}^{(1)}$ | $V_{DS} = 10\text{ V}$ | $I_D = 250\text{ mA}$    |                    | 1.5                                                   |      | 4    | V             |
| $V_{DS(ON)}$      | $V_{GS} = 10\text{ V}$ | $I_D = 20\text{ A}$      |                    |                                                       |      | 3.0  | V             |
| $G_{FS}^{(1)}$    | $V_{DS} = 10\text{ V}$ | $I_D = 10\text{ A}$      |                    | see <a href="#">Table 5: <math>G_{FS}</math> sort</a> |      |      | mho           |
| $C_{ISS}$         | $V_{GS} = 0\text{ V}$  | $V_{DS} = 50\text{ V}$   | $f = 1\text{ MHz}$ |                                                       | 1000 |      | pF            |
| $C_{OSS}$         | $V_{GS} = 0\text{ V}$  | $V_{DS} = 50\text{ V}$   | $f = 1\text{ MHz}$ |                                                       | 372  |      | pF            |
| $C_{RSS}$         | $V_{GS} = 0\text{ V}$  | $V_{DS} = 50\text{ V}$   | $f = 1\text{ MHz}$ |                                                       | 29   |      | pF            |

1.  $V_{GS(Q)}$  and  $G_{FS}$  sorted with alpha/numeric code marked on unit.

**Table 5.  $G_{FS}$  sort**

| $G_{FS}$ sort | Value      |
|---------------|------------|
| A             | 10 - 10.99 |
| B             | 11 - 11.99 |
| C             | 12 - 12.99 |
| D             | 13 - 13.99 |
| E             | 14 - 14.99 |
| F             | 15 - 15.99 |
| G             | 16 - 16.99 |
| H             | 17 - 18    |

**Table 6. Dynamic**

| Symbol        | Test Conditions                                                                                                  | Min. | Typ. | Max. | Unit |
|---------------|------------------------------------------------------------------------------------------------------------------|------|------|------|------|
| $P_{OUT}$     | $V_{DD} = 50\text{ V}$ $I_{DQ} = 250\text{ mA}$ $f = 30\text{ MHz}$                                              | 300  | 400  |      | W    |
| $G_{PS}$      | $V_{DD} = 50\text{ V}$ $I_{DQ} = 250\text{ mA}$ $P_{OUT} = 300\text{ W}$ $f = 30\text{ MHz}$                     | 20   | 23.5 |      | dB   |
| $\eta_D$      | $V_{DD} = 50\text{ V}$ $I_{DQ} = 250\text{ mA}$ $P_{OUT} = 150\text{ W}$ $f = 30\text{ MHz}$                     | 50   | 65   |      | %    |
| Load mismatch | $V_{DD} = 50\text{ V}$ $I_{DQ} = 250\text{ mA}$ $P_{OUT} = 300\text{ W}$ $f = 30\text{ MHz}$<br>all phase angles | 3:1  |      |      | VSWR |

3 Impedance

Figure 2. Impedance data schematic




Table 7. Impedance data

| f       | $Z_{IN} (\Omega)$ | $Z_{DL} (\Omega)$ |
|---------|-------------------|-------------------|
| 30 MHz  | $1.8 - j 0.2$     | $2.8 + j 2.3$     |
| 108 MHz | $1.9 + j 0.2$     | $1.6 + j 1.4$     |
| 175 MHz | $1.9 + j 0.3$     | $1.5 + j 1.6$     |

4 Typical performance (30 MHz)

Figure 3. Capacitance vs. drain voltage




Figure 4. Drain current vs. gate voltage




Figure 5. Gate-source voltage vs. case temperature




Figure 6. Maximum thermal resistance vs. case temperature




Figure 7. Transient thermal impedance




Figure 8. Transient thermal impedance model




Figure 9. Output power vs. input power




Figure 10. Output power vs. input power (at different temperature)




Figure 11. Power gain vs. output power




Figure 12. Efficiency vs. output power




Figure 13. Output power vs. supply voltage





Figure 14. Output power vs. gate voltage





# 4.1 Test circuit (30 MHz)

Figure 15. 30 MHz test circuit schematic




Table 8. Transmission line dimensions

| Dim. | Inch  | mm    |
|------|-------|-------|
| A    | 0.532 | 13.51 |
| B    | 0.250 | 6.35  |
| C    | 0.181 | 4.59  |
| D    | 0.383 | 9.37  |
| E    | 0.351 | 8.91  |
| F    | 0.633 | 16.08 |
| G    | 0.477 | 12.12 |
| H    | 0.438 | 11.12 |
| J    | 0.200 | 5.08  |
| K    | 0.164 | 4.16  |
| L    | 0.174 | 4.42  |
| M    | 0.817 | 20.75 |
| N    | 0.350 | 8.89  |
| P    | 0.779 | 19.79 |
| R    | 0.639 | 16.23 |

Table 8. Transmission line dimensions (continued)

| Dim. | Inch  | mm    |
|------|-------|-------|
| S    | 0.165 | 4.19  |
| T    | 1.017 | 25.84 |
| U    | 0.375 | 9.52  |
| V    | 0.456 | 11.58 |
| W    | 0.325 | 8.24  |
| X    | 0.650 | 16.50 |

Table 9. 30 MHz test circuit part list

| Component          | Description                                                                                                                             |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| C1,C9              | 0.01 $\mu$ F / 500 V surface mount ceramic chip capacitor                                                                               |
| C2, C3             | 750 pF ATC 700B surface mount ceramic chip capacitor                                                                                    |
| C4                 | 300 pF ATC 700B surface mount ceramic chip capacitor                                                                                    |
| C5,C10,C11,C14,C16 | 10000 pF ATC 200B surface mount ceramic chip capacitor                                                                                  |
| C6                 | 510 pF ATC 700B surface mount ceramic chip capacitor                                                                                    |
| C7                 | 300 pF ATC 700B surface mount ceramic chip capacitor                                                                                    |
| C8                 | 175-680 pF type 46 standard trimmer capacitor                                                                                           |
| C12                | 47 $\mu$ F / 63 V aluminum electrolytic radial lead capacitor                                                                           |
| C13                | 1200 pF ATC 700B surface mount ceramic chip capacitor                                                                                   |
| C15                | 100 $\mu$ F / 63 V aluminum electrolytic radial lead capacitor                                                                          |
| R1,R3              | 1 K OHM 1 W surface mount chip resistor                                                                                                 |
| R2                 | 560 OHM 2 W wire-wound axis lead resistor                                                                                               |
| T1                 | HF 2-30 MHz surface mount 9:1 transformer                                                                                               |
| T2                 | RG - 142B/U 50 OHM coaxial cable OD = 0.165[4.18] L 15"[381.00] covered with 15"[381.00] tinned copper tubular brand 13/65" [5.1] width |
| L1                 | 1 3/4 turn air-wound 16 AWG ID = 0.219 [5.56] poly-coated magnet wire                                                                   |
| L2                 | 1 3/4 turn air-wound 12 AWG ID = 0.250 [6.34] bus bar wire                                                                              |
| RFC1,RFC2          | 3 turns 14 AWG wire through ferrite toroid                                                                                              |
| FB1                | Surface mount EMI shield bead                                                                                                           |
| FB2                | Toroid                                                                                                                                  |
| PCB                | ULTRALAM 2000. 0.030" THK, $\epsilon_r = 2.55$ , 2 Oz ED CU both sides                                                                  |

Figure 16. 30 MHz test circuit photomaster






Figure 17. 30 MHz test circuit



## 5 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

**Figure 18. M177 package outline<sup>(a)</sup>**



a. Controlling dimensions in inches.

Table 10. M177 (.500 dia 4/L N/HERM W/FLG) package mechanical data

| Dim. | mm    |      |       | Inch  |      |       |
|------|-------|------|-------|-------|------|-------|
|      | Min.  | Typ. | Max.  | Min.  | Typ. | Max.  |
| A    | 5.72  | -    | 5.97  | 0.225 | -    | 0.235 |
| B    | 6.73  |      | 6.96  | 0.265 |      | 0.275 |
| C    | 21.84 |      | 22.10 | 0.860 |      | 0.870 |
| D    | 28.70 |      | 28.96 | 1.130 |      | 1.140 |
| E    | 13.84 |      | 14.10 | 0.545 |      | 0.555 |
| F    | 0.08  |      | 0.18  | 0.003 |      | 0.007 |
| G    | 2.49  |      | 2.74  | 0.098 |      | 0.108 |
| H    | 3.81  |      | 4.32  | 0.150 |      | 0.170 |
| I    |       |      | 7.11  |       |      | 0.280 |
| J    | 27.43 |      | 28.45 | 1.080 |      | 1.120 |
| K    | 15.88 |      | 16.13 | 0.625 |      | 0.635 |

## 6 Marking, packing and shipping specifications

Table 11. Packing and shipping specifications

| Order code | Packaging    | Pcs per tray | Dry pack humidity | GFS code  | Lot code  |
|------------|--------------|--------------|-------------------|-----------|-----------|
| SD2933W    | Plastic tray | 25           | < 10%             | Not mixed | Not mixed |

Figure 19. Marking layout for SD2933W




Table 12. Marking specifications

| Symbol | Description                    |
|--------|--------------------------------|
| W      | Wafer process code             |
| X      | G <sub>FS</sub> sort           |
| CZ     | Assembly plant                 |
| xxx    | Last 3 digits of diffusion lot |
| VY     | Diffusion plant                |
| MAR    | Country of origin              |
| CZ     | Test and finishing plant       |
| y      | Assembly year                  |
| yy     | Assembly week                  |

## 7 Revision history

**Table 13. Document revision history**

| Date        | Revision | Changes                                                                                                                                                                              |
|-------------|----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 30-Jul-2004 | 9        |                                                                                                                                                                                      |
| 22-Sep-2011 | 10       | Inserted <i>Section 6: Marking, packing and shipping specifications</i> .<br>Updated EAS in <i>Table 2: Absolute maximum ratings</i> .<br>Minor text changes to improve readability. |
| 03-Oct-2011 | 11       | Updated parameter $Z_{IN}$ in <i>Table 7: Impedance data</i> .                                                                                                                       |
| 17-Nov-2011 | 12       | Inserted <i>Figure 7: Transient thermal impedance</i> and <i>Figure 8: Transient thermal impedance model</i> .                                                                       |
| 10-Jan-2012 | 13       | Updated <i>Figure 7: Transient thermal impedance</i> .                                                                                                                               |
| 30-Sep-2013 | 14       | – Added row for “Avalanche energy, repetitive” and footnote to <i>Table 2: Absolute maximum ratings</i><br>– Minor text and formatting changes                                       |
| 14-Jul-2016 | 15       | – Updated $V_{GS}$ in <i>Table 2: Absolute maximum ratings</i> .<br>– Minor text changes.                                                                                            |

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved