


Common Sockets

CSM_common_sockets_DS_E_6_9

A Wide Variety of Square and Round Sockets in Front-mounting and Back-mounting Models





- Models available with finger protection.
- Hold-down Clips and Short Bars for PYFZ/PYF Sockets are also available.
- New screwless models available.










For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Square Sockets

Model	P2RF (front-mounting), page 9 to 10	
Number of pins		
5 pins	P2RFZ-05 Approx. 30 g 	P2RFZ-05-E*1 Approx. 30 g 
8 pins	P2RFZ-08 Approx. 38 g 	P2RFZ-08-E*1 Approx. 38 g 




















Model	P2R (back-mounting), pages 13 to 14			P7TF (front-mounting), page 14
Number of pins	Solder terminals	PCB terminals		
5 pins	P2R-05A*2 Approx. 5 g	P2R-05P Approx. 5 g	P2R-057P Approx. 5.5 g	P7TF-05 Approx. 28 g
				
8 pins	P2R-08A*2 Approx. 5 g	P2R-08P Approx. 5 g	P2R-087P Approx. 5.5 g	—
				

Note: 1. The structure of □-E models provides finger protection. Round terminals cannot be used. Use forked crimp terminals.

2. To remove the Relay, pull the lever on the Socket with your fingers supporting the lever and the opposite side of the Relay case, and jiggle the Relay.

*1. Use a #1 Phillips screwdriver to tighten the screws on this Socket.















*2. This is not a flux-tight structure. We recommend manual soldering for this product.

Model Number of pins	PYF (front-mounting), page 15		PY (back-mounting), pages 18 to 19				
			Solder terminals		Wrapping terminals		PCB terminals
8 pins	PYFZ-08 Approx. 32 g	PYFZ-08-E *3 Approx. 32 g	PY08 Approx. 8 g	PY08-Y1 PY08-Y3	PY08QN Approx. 12 g PY08QN2	PY08QN-Y1 PY08QN2-Y1	PY08-02 *2 Approx. 7.2 g
	 PYF08M Approx. 26 g		 		 		
11 pins	PYF11A Approx. 43 g		PY11 Approx. 9 g	PY11-Y1	PY11QN PY11QN2	PY11QN-Y1 PY11QN2-Y1	PY11-02 *2
			 		 		
14 pins	PYFZ-14 Approx. 50 g	PYFZ-14-E *1 Approx. 50 g	PY14 Approx. 10 g	PY14-Y1 PY14-Y3	PY14QN Approx. 14 g PY14QN2	PY14QN-Y1 PY14QN2-Y1 PY14QN-Y3 PY14QN2-Y3	PY14-02 *2
	 		 		 		

Note: The structure of □-E models provides finger protection. Round terminals cannot be used. Use forked crimp terminals.

*1. Use a #1 Phillips screwdriver to tighten the screws on this Socket.


*2. The structure does not resist flux. Manual soldering is recommended for this product.

Model Number of pins	PTF (front-mounting), pages 20 to 21	PT (back-mounting), pages 22 to 23		
		Solder terminals	Wrapping terminals	PCB terminals
8 pins	PTF08A Approx. 47 g  PTFZ-08-E *1 Approx. 46 g 	PT08 Approx. 11 g 	PT08QN Approx. 10.4 g 	PT08-0 *2 Approx. 8 g 
11 pins	PTF11A Approx. 61 g 	PT11 Approx. 13 g 	PT11QN 	PT11-0 *2 Approx. 12.2 g 
14 pins	PTF14A Approx. 77 g  PTFZ-14-E *1 Approx. 74 g 	PT14 Approx. 17 g 	PT14QN Approx. 20 g 	PT14-0 *2 Approx. 16.2 g 

Note: The structure of □-E models provides finger protection. Round terminals cannot be used. Use forked crimp terminals.
























*1. Use a #1 Phillips screwdriver to tighten the screws on this Socket.

*2. The structure does not resist flux. Manual soldering is recommended for this product.

Model Number of pins	P7LF (front-mounting), page 23
6 pins	P7LF-06 Approx. 60 g 


Note: Refer to *Models with Standards Certification* for detailed information on the models of Common Sockets that are certified for standards.

Round Sockets

Model Number of pins	PF (front-mounting), page 24	P2CF (front-mounting), page 25	PFA (front-mounting), page 26	P3G (back-mounting), page 27	PL (back-mounting), page 28		
					Solder terminals	Wrapping terminals	PCB terminals
8 pins	PF083A Approx. 34 g  PF083A-E *  PF085A Approx. 40 g 	P2CF-08 Approx. 55 g  P2CF-08-E 	8PFA Approx. 57 g  8PFA1 Approx. 66 g 	P3G-08 Approx. 40g  Note: The Y92A-48G Terminal Cover can be used to provide finger protection.	PL08 Approx. 14 g 	PL08-Q Approx. 15 g 	PLE08-0 Approx. 10.6g 
	PF113A Approx. 47 g  PF113A-E * 	P2CF-11 Approx. 70g  P2CF-11-E 	11PFA Approx. 74 g 	P3GA-11 Approx. 47 g  Note: The Y92A-48G Terminal Cover can be used to provide finger protection.	PL11 Approx. 15 g 	PL11-Q Approx. 18.5A 	PLE11-0 Approx. 10.8 g 
14 pins	—	—	14PFA Approx. 104 g 	—	PL15 Approx. 28 g 	—	—
20 pins	—	—	—	—	PL20 Approx. 17 g 	—	—

Note: The structure of □-E models provides finger protection. Round terminals cannot be used. Use forked crimp terminals.
 * Use a #1 Phillips screwdriver to tighten the screws on this Socket.

Terminal Cover

Model	Y92A-48G
Appearance	

Note: Refer to Models with Standards Certification for detailed information on the models of Common Sockets that are certified for standards.

Hold-down Clips For Square Sockets

(Unit: mm)

PKC One Set (2 Clips) 	PTC-1 	PYC-A1 Approx. 0.54 g One Set (2 Clips) 	PYC-E1 One Set (2 Clips) 	PYC-P Approx. 1.4 g 	PYC-P2 Approx. 1.2 g
PYC-S Approx. 1.8 g 	PYC-1 Approx. 6 g 	PYC Approx. 0.2 g 	Y92H-1 One Set (2 Clips) 	Y92H-3 One Set (2 Clips) 	Y92H-4

For Round Sockets

PFC-A1 Approx. 2.2 g One Set (2 Clips) 	PFC-A6 Approx. 2.4 g One Set (2 Clips) 	PFC-A7 Approx. 3.0 g One Set (2 Clips) 	PLC Approx. 2.4 g One Set (2 Clips) 	PLC-1 Approx. 2.6 g One Set (2 Clips) 	PLC-7 Approx. 3.0 g One Set (2 Clips)
PLC-8 Approx. 6.4 g One Set (2 Clips) 	PLC-10 Approx. 2.0 g One Set (2 Clips) 	PLC-12 Approx. 5.4 g One Set (2 Clips) 			

Applicable Hold-down Clips For Square Sockets

Sockets Applicable models	PYF(Z) Series	PTF(Z) Series	PYF08M	PY□(QN)	PT□(QN)	PY□-02	PT□-0
MY□, MY□N, MY□-D, MY2□-CR, MY4□-CR, MY4Z□-CR, MY□-TU, MY2K, MY□N-D2, MYQ□, G3F(D) Series, G3FM	PYC-A1	---	PYC PYC-P	PYC-P	---	PYC-P	---
LY□, LY□N, LY□-TU, G3H(D) Series, G9H	---	PYC-A1	---	---	PYC-P	---	PYC-P
MY□I *	PYC-A1	---	---	PYC-P2	---	PYC-P2	---
LY□I	---	PYC-A1	---	---	PYC-P2	---	PYC-P2
MY4H	PYC-A1	---	---	PYC-P	---	PYC-P	---
MY2Z□-CR, MY3□-CR	Y92H-3	---	---	PYC-1	---	PYC-1	---
LY□-CR	---	Y92H-3	---	---	PYC-1	---	---
G7K	---	PKC	---	---	---	---	---
H3Y	Y92H-3	---	Y92H-4	---	---	Y92H-4	---

Note: The □ in the model number is replaced with 08, 11, or 14.

* If you use a Hold-down Clip with the MY2I, you cannot use the PYFZ-08.
Use the PYFZ-14.

For Round Sockets

Sockets Applicable models	PF083A PF113A	PL08 (-Q) PL11 (-Q)	PLE08-0 PLE11-0	P2CF-11
61F-03B, -04B	PFC-A1	PLC	PLC-10	---
61F-LS, 61F-AO, 61F-WL	PFC-N8	PHC-5		
MK2P Series, MK2KP, MK3P□(-US)	PFC-A1	PLC		
MK3ZP MK3LP		PLC-1		
MYA-NA1, -NB1 MYA-LA1, -LB1 MYA-NA2, -NB2 MYA-LA2, -LB2	PFC-A6	PLC-7	---	---
MYA-LA12, -LB12	PFC-A7	PLC-8	---	---
APR-S	PFC-A6	PLC-7	---	---
APR-S380/-S440	---	---	---	Y92H-1
LG2	PFC-A7	PLC-8	---	---

Note: 1. The 8PFA(1), 11PFA, and 14PFA are held with hooks.

2. The PL15, PL20, and PF202, as well as models not given in the above table, require panel processing for installation.

3. The PF085A Hold-down Clip is included with the H3M and H2A. It is an option (sold separately) for the H2C.

Specifications

Socket Characteristics

Model	Rated carry current	Dielectric strength	Insulation resistance*1	Remarks
P2RFZ-05(-E)	10 A	Between contact terminals of same polarity: 1,000 VAC for 1 min Between coil terminals and contact terminals: 4,000 VAC for 1 min	1,000 MΩ min.	
P2RFZ-08(-E)	6 A	Between contact terminals of different polarity: 3,000 VAC for 1 min Between contact terminals of same polarity: 1,000 VAC for 1 min Between coil terminals and contact terminals: 4,000 VAC for 1 min	1,000 MΩ min.	
P2R-05P	10 A	Between contact terminals of same polarity: 1,000 VAC for 1 min Between coil terminals and contact terminals: 4,000 VAC for 1 min	1,000 MΩ min.	
P2R-08P	5 A	Between contact terminals of different polarity: 3,000 VAC for 1 min Between contact terminals of same polarity: 1,000 VAC for 1 min Between coil terminals and contact terminals: 4,000 VAC for 1 min	1,000 MΩ min.	
P2R-057P	10 A	Between contact terminals of same polarity: 1,000 VAC for 1 min Between coil terminals and contact terminals: 5,000 VAC for 1 min	1,000 MΩ min.	
P2R-087P	5 A	Between contact terminals of different polarity: 3,000 VAC for 1 min Between contact terminals of same polarity: 1,000 VAC for 1 min Between coil terminals and contact terminals: 5,000 VAC for 1 min	1,000 MΩ min.	
P2R-05A	10 A	Between contact terminals of same polarity: 1,000 VAC for 1 min Between ground terminals: 1,500 VAC for 1 min Between coil terminals and contact terminals: 4,000 VAC for 1 min	1,000 MΩ min.	
P2R-08A	5 A	Between contact terminals of different polarity: 3,000 VAC for 1 min Between contact terminals of same polarity: 1,000 VAC for 1 min Between ground terminals: 1,500 VAC for 1 min Between coil terminals and contact terminals: 4,000 VAC for 1 min	1,000 MΩ min.	
P7TF-05	5 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
PYFZ-08(-E)	10 A	Between contact terminals of different polarity: 2,250 VAC for 1 min Between contact terminals of same polarity: 2,250 VAC for 1 min Between coil terminals and contact terminals: 2,250 VAC for 1 min	1,000 MΩ min.	
PYF11A	5 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
PYFZ-14(-E)	6 A	Between contact terminals of different polarity: 2,250 VAC for 1 min Between contact terminals of same polarity: 2,250 VAC for 1 min Between coil terminals and contact terminals: 2,250 VAC for 1 min	1,000 MΩ min.	
PY08(-Y1)(-Y3)	7 A	Between terminals: 1,500 VAC for 1 min	1,000 MΩ min.	
PY08QN(-Y1)	7 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PY08-02	7 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PY11(-Y1)	5 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PY11QN(-Y1)	5 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PY11-02	5 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PY14(-Y1)(-Y3)	3 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PY14QN(-Y1)	3 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PY14-02	3 A	Between terminals: 1,500 VAC for 1 min	100 MΩ min.	
PTFZ-□□-E	12 A (@70°C) 15 A (@50°C)	Between contact terminals of different polarity: 2,500 VAC for 1 min Between contact terminals of same polarity: 2,500 VAC for 1 min Between ground terminals: 2,500 VAC for 1 min Between coil terminals and contact terminals: 2,500 VAC for 1 min	1,000 MΩ min.	
PTF□□A(-E)	10 A	Between terminals: 2,000 VAC for 1 min	100 MΩ min.	
PT□□	10 A	Between terminals: 2,000 VAC for 1 min	100 MΩ min.	
PT□□QN	10 A	Between terminals: 2,000 VAC for 1 min	100 MΩ min.	
PT□□-0	10 A	Between terminals: 2,000 VAC for 1 min	100 MΩ min.	
P7LF-06	30 A	Between contact terminals of different polarity: 2,000 VAC for 1 min Between contact terminals of same polarity: 2,000 VAC for 1 min Between coil terminals and contact terminals: 4,000 VAC for 1 min	1,000 MΩ min.	
PF□□□A	5 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
P2CF-□(-E)	5 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
8PFA(1)	10 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
11PFA(1)	10 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
P3G(A)-□	6 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
PL□(-Q)	10 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	
PLE□□-0	10 A	Between terminals: 2,000 VAC for 1 min	1,000 MΩ min.	

*1. The insulation resistance was measured with a 500-VDC insulation resistance meter at the same places as those used for measuring the dielectric strength.

*2. However, do not exceed the continuous carry current of the socket to be mounted.







Safety Precautions







Refer to *Common Relay Precautions* for general precautions.

Dimensions

P2RF









(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
P2RFZ-05 (One Pole)  <p>Technical drawing of the P2RFZ-05 socket. It includes a front view showing a 5-M3.5x8 screw, a 7mm width, and a 39.5mm height. A side view shows a 1.5mm thickness, a 4mm diameter hole, and a 30mm width. A top view shows a 71.5mm max. length, a 4.2mm width, and a 19.5mm max. width. A bottom view shows a 54mm max. length and a 26.5mm max. width.</p>	 <p>(Top View)</p>	 <p>(Top View)</p> <p>M3 or 3.2-dia. hole Recommended mounting screw: M3 x 16 mm or larger</p> <p>Note: Track mounting is also possible.</p>
P2RFZ-05-E (One Pole) (Finger Protection Structure)  <p>Technical drawing of the P2RFZ-05-E socket. It includes a front view showing a 5-M3X8 screw, a 78.5mm max. height, and a 3.5-dia. hole. A side view shows a 6mm thickness, a 48mm max. length, and a 2mm width. A top view shows a 39.5mm height, a 35.5mm width, and a 17.2mm width. A bottom view shows a 61mm max. length and a 31mm max. width.</p>	 <p>(Top View)</p> <p>Note: Figures in parentheses indicate DIN standard numbers.</p>	 <p>(Top View)</p> <p>M3 or 3.5-dia. hole</p> <p>Note: Track mounting is also possible.</p>


Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
P2RFZ-08 (Two Poles)  <p>Front view dimensions: 71.5 max., 39.5, 19.5 max., 4.2, 1, 7, 8-M3.5x8.</p> <p>Side view dimensions: 1.5, 4 dia., 30, 35.5, 13.8, 26.5 max., 54 max.</p>	 <p>(Top View)</p>	 <p>(Top View)</p> <p>M3 or 3.2-dia. hole Recommended mounting screw: M3 x 16 mm or larger</p> <p>Note: Track mounting is also possible.</p>
P2RFZ-08-E (Two Poles) (Finger Protection Structure)  <p>Front view dimensions: 78.5 max., 16 max., 4, 3.5-dia. hole, 8-M3X8, 2.</p> <p>Side view dimensions: 48 max., 2, 39.5, 35.5, 17.2, 31 max., 61 max., 6.</p>	 <p>(Top View)</p> <p>Note: Figures in parentheses indicate DIN standard numbers.</p>	 <p>(Top View)</p> <p>M3 or 3.5-dia. hole</p> <p>Note: Track mounting is also possible.</p>

Note: If an I/O SSR or Indicator Module is used, the polarity of terminal 1 is negative.

For Screw Terminal Sockets Short Bars



Applicable sockets	Pitch	Appearance	Dimensions (mm)	Number of poles	Insulation color	Short Bars Model	Maximum carry current	Minimum order (set)
P2RFZ-08-E for shorting contact COM terminals	6.8 mm			20	Blue(S)	P2DN-6.8-100S	20 A	1
P2RFZ-05-E P2RFZ-08-E	15.7 mm			10		P2DN-15.7-100S		
P2RFZ-08 for shorting contact COM terminals	8.5 mm			20	Blue(S)	P2DN-8.5-100S	20 A	1
P2RFZ-05 P2RFZ-08	19.4 mm			10		P2DN-19.4-100S		

Note: 1. Select an applicable type of short bars by checking applicable socket type, appearance, and dimensions.
 2. Use the Short Bars for crossover wiring within one Socket or between Sockets.
 3. Use the short bars on the lower section of the socket.
 When using the short bars on the upper section of the socket, insert them so that their heads are pointed upwards (see the figure below).
 Otherwise, short bars may interfere with the socket, leading to improper wiring and contact failure.




* One set (order unit) contains 10 short bars and 20 caps.

Accessories for Short Bars (P2DN) Cap


Short Bars Models	Appearance	Dimensions (mm)	Model
P2DN-8.5-100S P2DN-19.4-100S P2DN-6.8-100S P2DN-15.7-100S			P2DN-CP100

Note: Use for insulation when using a cut short bar.





For Screw Terminal Sockets (P2RFZ-05/P2RFZ-08)
Terminal Covers for

Applicable models	Appearance	Model
P2RFZ-05 P2RFZ-08		P2CZ-C

Note: 1. Use these covers in a combination with P2RFZ-05 and P2RFZ-08.
2. Do not install short bars (optional) on the upper section (see the figure below).
Short bars may interfere with the terminal cover, making the terminal cover unusable.



Dimensions with terminal cover

<div><p>P2RFZ-05</p></div>	<div><p>P2RFZ-08</p></div>
---	---

P2R






(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	PCB Dimensions
P2R-05P (One Pole) 	 (Bottom View)	 (Bottom View)
P2R-08P (Two Poles) 	 (Bottom View)	 (Bottom View)
P2R-057P (One Pole) 	 (Bottom View)	 (Bottom View)
P2R-087P (Two Poles) 	 (Bottom View)	 (Bottom View)

Note: If an I/O SSR or Indicator Module is used, the polarity of terminal 1 is negative.

P2R




(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
P2R-05A (One Pole) 	 <p>(Bottom View)</p>	 <p>(Use panel with thickness of 1.6 to 2.0 mm.)</p>
P2R-08A (Two Poles) 	 <p>(Bottom View)</p>	<p>(Use panel with thickness of 1.6 to 2.0 mm.)</p>

Note: If an I/O SSR or Indicator Module is used, the polarity of terminal 1 is negative.

P7TF





(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
P7TF-05 	 <p>(Top View)</p>	 <p>(Top View)</p> <p>Note: Track mounting is also possible. * We recommend that you use washers if you use M3 bolts or screws. Washers are not required with M4 bolts or screws.</p>

Note: If an I/O SSR or Indicator Module is used, the polarity of terminal 1 is positive.









Relay Sockets and Short Bars for PYFZ/PYF

Bridges within the Same Socket

Pitch	Applicable models	Appearance	Dimensions (mm)	Model	Specifications
7 mm	PYFZ-14			PYD-020B□(2P)	Max. carry current: 20 A (18 A at 70°C) Ambient operating temperature: -40 to 70°C (with no icing or condensation) Ambient operating humidity: 45% to 85% (with no icing or condensation) Conductor material: Brass Conductor surface treatment: Nickel plating Package qty: 50/bag
				PYD-030B□(3P)	



Note: The □ in the model number is replaced with the insulation color specification code. B: Black, Y: Yellow

Bridges between Adjacent Sockets

Pitch	Applicable models	Appearance	Dimensions (mm)	Model *1	Specifications
22 mm	PYFZ-08			PYD-025B□(2P)	Max. carry current: 20 A (18 A at 70°C) Ambient operating temperature: -40 to 70°C (with no icing or condensation) Ambient operating humidity: 45% to 85% (with no icing or condensation) Conductor material: Brass Conductor surface treatment: Nickel plating Package qty: 10/bag
				PYD-085B□(8P)	
29 mm	PYFZ-14			PYD-026B□(2P)	Max. carry current: 20 A (18 A at 70°C) Ambient operating temperature: -40 to 70°C (with no icing or condensation) Ambient operating humidity: 45% to 85% (with no icing or condensation) Conductor material: Brass Conductor surface treatment: Nickel plating Package qty: 10/bag
				PYD-086B□(8P)	

***1.** The □ in the model number is replaced with the insulation color specification code. B: Black, S: Blue, R: Red

For Screw Terminal Sockets (PYFZ-08/PYFZ-14)
Terminal Covers for


Applicable models	Appearance	Model
PYFZ-08		PYCZ-C08 (2 pcs/set)
PYFZ-14		PYCZ-C14 (1 pcs/set)

Note: Use these covers in a combination with PYFZ-08 and PYFZ-14.


Dimensions with terminal cover

(Unit: mm)

PYCZ-C08



PYCZ-C14



PY

(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting hole and PCB dimensions
<p>PY08 PY08-Y1 (L = 42 max.) PY08-Y13 (L = 60 max.)</p> <p>*The PY08-Y1 includes the part outlined by the dashed lines above.</p>		
<p>PY08QN PY08QN2 PY08QN-Y1 PY08QN2-Y1</p> <p>*1. The PY08QN(2)-Y1 includes the part outlined by the dashed lines above. *2. The figures in the parentheses are for the PY08QN2(-Y1).</p>	<p>(Bottom View)</p>	
<p>PY08-02</p> <p>* The structure does not resist flux. Manual soldering is recommended for this product.</p>		
<p>PY11 PY11-Y1</p> <p>*The PY11-Y1 includes the part outlined by the dashed lines above.</p>		
<p>PY11QN PY11QN2 PY11QN-Y1 PY11QN2-Y1</p> <p>*1. The PY11QN(2)-Y1 includes the part outlined by the dashed lines above. *2. The figures in the parentheses are for the PY11QN2(-Y1).</p>	<p>(Bottom View)</p>	
<p>PY11-02</p> <p>* The structure does not resist flux. Manual soldering is recommended for this product.</p>		





Dimensions	Terminal Arrangement/ Internal Connections	Mounting hole and PCB dimensions
<p>PY14 PY14-Y1 (L = 42 max.) PY14-Y3 (L = 60 max.)</p> <p>*The PY14-Y□ includes the part outlined by the dashed lines above.</p>	<p>(Bottom View)</p>	
<p>PY14QN PY14QN2 PY14QN-Y1 (L = 42 max.) PY14QN2-Y1 (L = 42 max.) PY14QN-Y3 (L = 60 max.) PY14QN2-Y3 (L = 60 max.)</p> <p>*1. The PY14QN-Y□ and PY14QN2-Y□ include the part outlined by the dashed lines above. *2. The figures in the parentheses are for the PY14QN2(-Y□).</p>		
<p>PY14-02</p> <p>* The structure does not resist flux. Manual soldering is recommended for this product.</p>		

- Note:**
1. Use a panel with a thickness of 1 to 2 mm when mounting a Socket on it.
 2. You can use the PY14-Y1 or PY14QN-Y1 for the MY4 Series, MY4H, MYQ4(Z), or MY2K.
 3. You can use the PY14-Y3 or PY14QN-Y3 for H3Y Timers.

PTF

(Unit: mm)













Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
PTF08A 	<p>(Top View)</p>	<p>(Top View)</p> <p>Note: Track mounting is also possible.</p>
PTFZ-08-E (Finger Protection Structure) 	<p>(Top View)</p>	<p>(Top View)</p> <p>Note: Track mounting is also possible.</p>
PTF11A 	<p>(Top View)</p>	<p>(Top View)</p> <p>Note: Track mounting is also possible.</p>







Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
<div><p>PTF14A</p></div>	<div><p>(Top View)</p></div>	<div><p>(Top View)</p><p>Note: Track mounting is also possible.</p></div>
<div><p>PTFZ-14-E (Finger Protection Structure)</p></div>		

Note: If you use the PTF08A, or PT08 with an LY1 Relay, connect the following terminal pairs: 1-2, 3-4, and 5-6 (for usage at 10 A or higher).

PT

(Unit: mm)

Dimensions		Terminal Arrangement/ Internal Connections	Mounting hole and PCB dimensions
PT08 	PT08QN 	 (Bottom View)	
	PT08-0 		
PT11 	PT11QN 	 (Bottom View)	
	PT11-0 		

Dimensions		Terminal Arrangement/ Internal Connections	Mounting hole and PCB dimensions
PT14	PT14QN	 <p>(Bottom View)</p>	
			
PT14-0	 <p>*Maintain a sufficient distance from the pattern when using double-sided PCBs. • The structure does not resist flux. • Manual soldering is recommended for this product.</p>		

Note: Use a panel with a thickness of 1 to 2 mm when mounting a Socket on it.

P7LF

(Unit: mm)

Dimensions		Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
P7LF-06		<p>(Top View)</p>	

PF

(Unit: mm)











Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
PF083A 		
PF083A-E 	 (Top View)	 Note: Track mounting is also possible.
PF085A 	 (Top View)	
PF113A 		
PF113A-E 	 (Top View)	 Note: Track mounting is also possible.

Note: 1. For the PF083A and PF113A, the Socket key slot is on the top. (Applicable model: MK)

2. The structure of □-E models provides finger protection. Round terminals cannot be used. Use forked crimp terminals.

P2CF

(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
<p>P2CF-08</p> 	 <p>(Top View)</p>	 <p>Two M4 or 4.5-dia. holes 40±0.2</p>
<p>P2CF-08-E</p> 	 <p>(Top View)</p>	<p>Note: Track mounting is also possible.</p>
<p>P2CF-11</p> 	 <p>(Top View)</p>	 <p>Two M4 or 4.5-dia. holes 40±0.2</p>
<p>P2CF-11-E</p> 	 <p>(Top View)</p>	<p>Note: Track mounting is also possible.</p>





PFA

(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
8PFA 	 (Top View)	 Two M4 or 4.5-dia. holes 40±0.2
8PFA1 	 (Top View)	 Two M4 or 4.5-dia. holes 40±0.2 Note: Track mounting is also possible.
11PFA 	 (Top View)	 Two M4 or 4.5-dia. holes 40±0.2 Note: Track mounting is also possible.
14PFA 	 (Top View)	 Two, 4.5 dia. or M4 mounting holes 60±0.2 Note: Track mounting is also possible.



P3G/P3GA

(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting Hole Dimensions
P3G-08  <p>Note: The Y92A-48G Terminal Cover can be used to implement finger protection.</p>	 <p>(Bottom View)</p>	—
P3GA-11  <p>Note: The Y92A-48G Terminal Cover can be used to implement finger protection.</p>	 <p>(Bottom View)</p>	—

Terminal Cover

(Unit: mm)

Appearance	Dimensions
	Y92A-48G  <p>Twelve, 6.4 dia.</p> <p>34</p> <p>47.7 × 47.7</p> <p>48 × 48</p> <p>16.5</p> <p>24.6</p> <p>27.6</p> <p>47.4</p> <p>UP</p>

PL

(Unit: mm)

Dimensions	Terminal Arrangement/ Internal Connections	Mounting hole and PCB dimensions (bottom view)
PL08 		<p>Two, 3.5 dia. or M3 device mounting holes</p> <p>Two, 3.5 or M3 Socket mounting holes</p> <p>31-dia. hole</p> <p>40±0.3</p> <p>L = 40 mm MK2(Z)P</p> <p>L = 74 mm PU, AMD-S, MM2(X)P, CZ, STP, H3L, TDS, DTS, DSP, TDF, TDV</p> <p>L = 86 mm 61F-LS/-AO/-WL, G4Q-212S, RD2P, RDA, TDA, AGF, SE, SAD, K2CU, SDV-F</p>
PL08-Q 	<p>(Bottom View)</p>	<p>Two 3.5-dia. or two M3 Socket mounting holes</p> <p>31-dia. hole</p> <p>40±0.3</p> <p>MK2(Z)P</p>
PLE08-0 		<p>Two 3.5-dia. Hold-down Clip mounting holes</p> <p>45°</p> <p>27.7±0.5 dia.</p> <p>40±0.1</p> <p>Eight, 2.5-dia. holes</p> <p>MK2(Z)P</p>
PL11 		<p>Two, 3.5 dia. or M3 device mounting /Hold-down Clip mounting holes</p> <p>Two, 3.5 dia. or M3 Socket mounting holes</p> <p>31-dia. hole</p> <p>40±0.3</p> <p>L = 40 mm MK3P MK2KP</p> <p>L = 74 mm MM3P MK2(X)KP</p>
PL11-Q 	<p>(Bottom View)</p>	<p>L = 42 mm MK3ZP MK3LP</p>
PLE11-0 		<p>Two, 3.5-dia. holes</p> <p>Applicable model/Hold-down Clip mounting holes</p> <p>360°</p> <p>28.7±0.5</p> <p>L</p> <p>Eleven, 2.5-dia. holes</p> <p>L = 40 mm MK3P MK2KP</p> <p>L = 42 mm MK3ZP MK3LP</p>
PL15 	<p>(Bottom View)</p>	<p>Two, 3.5 dia. or M3 device mounting holes</p> <p>Two, 3.5 dia. or M3 Socket mounting holes</p> <p>4.2-dia. hole</p> <p>74</p> <p>53</p> <p>MM3XP MM4(X)P MM3(X)KP MM4(X)KP</p>

Dimensions	Terminal Arrangement/ Internal Connections	Mounting hole and PCB dimensions (bottom view)
PL20 <p>Two, 3.5-dia. holes</p> <p>46.5 max.</p> <p>31 max.</p> <p>Two, 2 dia.</p> <p>3.9</p> <p>36.5 max.</p> <p>23 max.</p>	<p>(Bottom View)</p>	<p>Two, 4.5-dia. Relay mounting holes</p> <p>Two, 4-dia. Socket mounting holes</p> <p>33-dia. hole</p> <p>56±0.2</p> <p>38±0.2</p> <p>* Relay mounting holes are not required for the LDNP.</p>

Note: When mounting, pay due attention to the direction of the key groove of applicable Relays.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See <http://www.omron.com/global/> or contact your Omron representative for published information.

Limitation on Liability: Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.