
HIGH ACCURACY, LARGE CURRENT, HIGH BANDWIDTH CURRENT SENSOR

Description

The AHC1773 series is an open-loop Hall current sensing chip that combines high accuracy, high bandwidth, high response, high linearity, and low temperature drift. AHC1773 provides 0 to 200A large current measurement range. AHC1773 can also do -40°C to +125°C full temperature range of typical sensitivity temperature drift ±0.2% of the performance indicators. It provides a new solution for the high accuracy and high-performance current sensor area. AHC1773 adapts to strong electromagnetic and high isolation current detection environment.


Pin Assignments

(Top View)




Features

- 3.3V Supply Operation
- High Accuracy, Large Current
  - 0 to 200A Current Sensor
  - Ultra-Low Primary Conductor Resistance: 100μΩ
  - Offset Temperature Drift: ±5mV
  - Sensitivity Total Output Error: ±1%
  - Typical Sensitivity Temperature Drift: ±0.2%
  - Typical Linearity Error: ±0.2%
- High Bandwidth, Fast Response
  - Typical Bandwidth: 200kHz
  - Typical Response Time: 1.8μs
- High Anti-Interference, High Insolation
  - The integrated magnetic core resists stray magnetic field interference
  - Isolated Voltage: 5000Vrms
  - Ratiometric Output
- TUV IEC 62368-1:2018 Certification No. B 133928 0002 Rev. 00
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/**



PTH5



SMP5


Applications

- Photovoltaic inverters
- Industrial inverters
- Commercial air conditioning
- Charging stations
- Welding machines
- Server power, PSU, PDU, UPS
- Balancing cars


Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Functional Block Diagram



Typical Applications Circuit (Note 4)



Note: 4. The AHC1773 outputs an analog signal, VOUT, that changes proportionally with the bi-directional AC or DC primary sensed current, IP, within the specified measurement range.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Pin Descriptions

Packages: PTH5 and SMP5

Pin Number	Pin Name	Function
1	VCC	Device Power Supply Terminal Pin
2	GND	Signal Ground Terminal
3	VOUT	Analog Output Signal
4	IP+	Terminals for Current Being Sensed
5	IP-	Terminals for Current Being Sensed

Selection Guide

Part Number	I_{PR} (A)	Sens (Typ) at V_{CC} = 3.3V (mV/A)	Available Package	T_A (°C)	Packing
AHC1773-050U	50	52.8	PTH5/SMP5	-40 to +125	34 pieces per tube
AHC1773-050B	±50	26.4	PTH5/SMP5		
AHC1773-100U	100	26.4	PTH5/SMP5		
AHC1773-100B	±100	13.2	PTH5/SMP5		
AHC1773-150U	150	17.6	PTH5/SMP5	-40 to +85	
AHC1773-150B	±150	8.8	PTH5/SMP5		
AHC1773-200U	200	13.2	PTH5/SMP5		
AHC1773-200B	±200	6.6	PTH5/SMP5		

Absolute Maximum Ratings (T_A = +25°C, unless otherwise specified.)

Symbol	Characteristic	Value	Unit
V_{CC}	Supply Voltage	-0.3 to 6.5	V
V_{OUT}	Output Voltage	-0.3 to VCC + 0.3	V
I_{OUT}	Output Current	-45 to 45	mA
T_A	Operating Ambient Temperature	-40 to +125	°C
$T_{J(max)}$	Junction Temperature	+165	°C
T_{STG}	Storage Temperature	-55 to +155	°C
ESD HBM	Electrostatic Discharge Withstand Capability—Human Body Model	6	kV
ESD CDM	Electrostatic Discharge Withstand Capability—Charged Device Model	1	kV

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Isolation Characteristics

Symbol	Characteristics	Conditions	Rating	Unit
V_{SURGE}	Dielectric Surge Strength Test Voltage	Tested ±5 pulses at 2/minute in compliance to IEC 61000-4-5 1.2µs (rise) / 50µs (width).	8000	V
V_{ISO}	Dielectric Strength Test Voltage	60s, 50Hz isolation withstand voltage parameters, according to UL62368-1, test 6kV/1s before delivery to verify the insulation performance, and verify the partial discharge is less than 5pc	5000	V_{RMS}
V_{WVBI}	Working Voltage for Basic Isolation	Maximum approved working voltage for basic (single) isolation according to UL 60950-1 (edition 2).	1800	V_{PK} or VDC
			1272	V_{RMS}
V_{WVRI}	Working Voltage for Reinforced Isolation	Maximum approved working voltage for reinforced isolation according to UL 60950-1 (edition 2).	900	V_{PK} or VDC
			636	V_{RMS}
DTI	Minimum Distance Through Insulation	Minimum distance through insulation from IP leads to signal leads.	4.0	mm

Typical Overcurrent Capability

Symbol	Characteristic	Conditions	Value	Unit
I_{POC}	Maximum Current Test	T_A = +25°C, Current On 1s, off 99s, Apply 100 pulses	1200	A
		T_A = +85°C, Current On 1s, off 99s, Apply 100 pulses	900	
		T_A = +125°C, Current On 1s, off 99s, Apply 100 pulses	600	

Thermal Characteristics

Symbol	Characteristics	Conditions	Rating	Unit
$R_{\theta JA}$	Package Thermal Resistance (Junction to Ambient)	Mounted on the Diodes Incorporated's evaluation board with 1972mm^2 of 4oz. copper on each side, connected to pins 1 and 2, and to pins 3 and 4, with thermal vias connecting the layers. Performance values include the power consumed by the PCB.	17	°C/W
$R_{\theta JL}$	Package Thermal Resistance (Junction to Lead)	Mounted on the Diodes Incorporated's AHC1773 evaluation board.	5.5	°C/W

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Common Electrical Characteristics (Valid through the full range of T_A, V_{CC} = 3.3V, C_{BYPASS} = 100nF C_L = 0.47nF, unless otherwise specified.) (Note 5)

Symbol	Characteristic	Test Conditions	Min	Typ	Max	Unit
V_{CC}	Supply Voltage	—	3	3.3	3.6	V
I_{CC}	Supply Current	V_{CC} = 3.3V, no load	—	6	12	mA
R_P	Primary Conductor Resistance	T_A = +25°C	—	0.1	—	mΩ
t_{PO}	Power-On Time	Chip power-on（V_{CC} > 3.0V）	—	1.8	—	ms
t_R	Rise Time	The time reaches 10% to 90% of its full-scale value	—	1.5	—	μs
t_{PROP}	Propagation Delay	—	—	1.2	—	μs
$t_{RESPONSE}$	Response Time	—	—	2.0	—	μs
C_L	Output Capacitive Load	V_{OUT} - V_{GND}	—	0.47	10	nF
R_L	Output Resistive Load	—	4.7	—	—	kΩ
R_{OUT}	DC Output Resistance	—	—	1	—	Ω
UVLOD	Undervoltage-Lockout	Undervoltage protection rising threshold	—	2.3	—	V
UVLOE		Undervoltage protection falling threshold	—	2.1	—	V
t_{UVLOD}	Undervoltage-Lockout	Undervoltage protection rise time	—	900	—	μs
t_{UVLOE}		Undervoltage protection fall time	—	50	—	μs
V_S	Output Voltage Range	R_L = 10kΩ to VCC or GND	0.1	—	V_{CC}-0.1	V
BW	Internal Bandwidth	200A range, small-signal measurement	—	200	—	kHz
E_{SYM}	Sensitivity Symmetry Error	—	-0.1	±0.01	0.1	%
S_{ERR}	Ratiometric Output Sensitivity Error	V_{CC} = 3.15V to 3.45V	—	±0.5	—	%
E_{LIN}	Nonlinearity	≤ 100A	-0.8	±0.3	0.8	%
		≤ 200A	--0.9	±0.5	0.9	
dS_{ERR}	Sensitivity Temperature Drift	T_A = +85°C to +125°C	-1.0	±0.2	1.0	%
		T_A = +25°C to +85°C	-0.8	±0.2	0.8	
		T_A = -40°C to +25°C	-1.0	±0.2	1.0	
$V_{OUT(Q)TC}$	Offset Temperature Drift	T_A = +25°C to +125°C	—	±5	—	mV
		T_A = -40°C to +25°C	—	±5	—	

Note: 5. AHC1773 is production tested and guaranteed to T_A = +125°C, maximum junction temperature, $T_{J(MAX)}$, cannot be exceeded. See *Absolute Maximum Ratings* and *Thermal Application Information* for more information.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

AHC1773-050U (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	0	—	50	A
Sensitivity	Sens	$I_{PRmin} < I_{PR} < I_{PRmax}$	—	52.8	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Uni-directional , I_{PR} = 0	—	V_{CC}*0.1	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	7	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	0.4	—	mV
		I_P = 0	—	10	—	mA
Total Output Error	E_{TOT}	$I_P = I_{PRmax}$	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: $E_{TOT} = (V_{OUT} - V_{OUT\ Ideal}) / (Sens_{Ideal} \times I_P) \times 100\%$						
Sensitivity Error	E_{SENS}	$I_P = I_{PRmax}$, T_A = +25°C to +125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

AHC1773-050B (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	-50	—	50	A
Sensitivity	Sens	$I_{PRmin} < I_{PR} < I_{PRmax}$	—	26.4	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Bi-directional , I_{PR} = 0	—	V_{CC}*0.5	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	7	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	0.4	—	mV
		I_P = 0	—	10	—	mA
Total Output Error	E_{TOT}	$I_P = I_{PRmax}$	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: $E_{TOT} = (V_{OUT} - V_{OUT\ Ideal}) / (Sens_{Ideal} \times I_P) \times 100\%$						
Sensitivity Error	E_{SENS}	$I_P = I_{PRmax}$, T_A = +25°C to +125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

Note: 6. Typical values are ±3 sigma values.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

AHC1773-100U (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	0	—	100	A
Sensitivity	Sens	$I_{PRmin} < I_{PR} < I_{PRmax}$	—	26.4	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Uni-directional, I_{PR} = 0	—	V_{CC}*0.1	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	5	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	0.6	—	mV
		I_P = 0	—	30	—	mA
Total Output Error	E_{TOT}	$I_P = I_{PRmax}$	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: $E_{TOT} = (V_{OUT} - V_{OUT\ Ideal}) / (Sens_{Ideal} \times I_P) \times 100\%$						
Sensitivity Error	E_{SENS}	$I_P = I_{PRmax}$, T_A = +25°C to +125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

AHC1773-100B (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	-100	—	100	A
Sensitivity	Sens	$I_{PRmin} < I_{PR} < I_{PRmax}$	—	13.2	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Bi-directional, I_{PR} = 0	—	V_{CC}*0.5	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	5	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	0.6	—	mV
		I_P = 0	—	30	—	mA
Total Output Error	E_{TOT}	$I_P = I_{PRmax}$	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: $E_{TOT} = (V_{OUT} - V_{OUT\ Ideal}) / (Sens_{Ideal} \times I_P) \times 100\%$						
Sensitivity Error	E_{SENS}	$I_P = I_{PRmax}$, T_A = +25°C to +125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

Note: 6. Typical values are ±3 sigma values.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

AHC1773-150U (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	0	—	150	A
Sensitivity	Sens	$I_{PRmin} < I_{PR} < I_{PRmax}$	—	17.6	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Uni-directional, I_{PR} = 0	—	V_{CC}*0.1	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	4	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	0.8	—	mV
		I_P = 0	—	60	—	mA
Total Output Error	E_{TOT}	$I_P = I_{PRmax}$	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: $E_{TOT} = (V_{OUT} - V_{OUT\ Ideal}) / (Sens_{Ideal} \times I_P) \times 100\%$						
Sensitivity Error	E_{SENS}	$I_P = I_{PRmax}$, T_A = +25°C to 125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

AHC1773-150B (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	-150	—	150	A
Sensitivity	Sens	$I_{PRmin} < I_{PR} < I_{PRmax}$	—	8.8	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Bi-directional, I_{PR} = 0	—	V_{CC}*0.5	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	4	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	0.8	—	mV
		I_P = 0	—	60	—	mA
Total Output Error	E_{TOT}	$I_P = I_{PRmax}$	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: ETOT = $(V_{OUT} - V_{OUT\ Ideal}) / (Sens_{Ideal} \times I_P) \times 100\%$						
Sensitivity Error	E_{SENS}	$I_P = I_{PRmax}$, T_A = +25°C to +125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

Note: 6. Typical values are ±3 sigma values.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

AHC1773-200U (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	0	—	200	A
Sensitivity	Sens	I_{PRmin} < IPR < I_{PRmax}	—	13.2	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Uni-directional, I_{PR} = 0	—	V_{CC}*0.1	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	3	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	1	—	mV
		I_P = 0	—	100	—	mA
Total Output Error	E_{TOT}	I_P = I_{PRmax}	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: ETOT = (V_{OUT} - $V_{OUT\ Ideal}$) / ($Sens_{Ideal}$ × I_P) × 100%						
Sensitivity Error	E_{SENS}	I_P = I_{PRmax}, T_A = +25°C to +125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

AHC1773-200B (T_A = +25°C, V_{CC} = 3.3V, C_{BYPASS} = 100nF, C_L = 0.47nF, unless otherwise specified.) (Note 6)

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
NOMINAL PERFORMANCE						
Current Sensing Range	I_{PR}	—	-200	—	200	A
Sensitivity	Sens	I_{PRmin} < I_{PR} < I_{PRmax}	—	6.6	—	mV/A
Zero Current Output Voltage	$V_{OUT(Q)}$	Bi-directional, I_{PR} = 0	—	V_{CC}*0.5	—	V
ACCURACY PERFORMANCE						
Noise	V_N	—	—	3	—	mVrms
Magnetic Offset Error	I_{ERROM}	I_P = 0	—	1	—	mV
		I_P = 0	—	100	—	mA
Total Output Error	E_{TOT}	I_P = I_{PRmax}	-1.2	±0.5	1.2	%
TOTAL OUTPUT ERROR COMPONENTS: ETOT = (V_{OUT} - $V_{OUT\ Ideal}$) / ($Sens_{Ideal}$ × I_P) × 100%						
Sensitivity Error	E_{SENS}	I_P = I_{PRmax}, T_A = +25°C to +125°C	-1.5	±0.5	1.5	%
Offset Error	V_{OE}	I_P = 0, T_A = +25°C to +125°C	-10	±0.2	10	mV
		I_P = 0, T_A = +25°C	-5	±0.2	5	
		I_P = 0, T_A = -40°C to +125°C	-10	±0.2	10	
LIFETIME DRIFT CHARACTERISTICS						
Sensitivity Error Lifetime Drift	E_{SENS_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%
Total Output Error Lifetime Drift	E_{TOT_drift}	After reliability test, T_A = +25°C	—	±0.5	—	%

Note: 6. Typical values are ±3 sigma values.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Definitions of Accuracy Characteristics

Sensitivity Sens

The change in sensor IC output in response to a 1 A change through the primary conductor. The sensitivity is the product of the magnetic circuit sensitivity (G / A) (1 G = 0.1 mT) and the linear IC amplifier gain (mV/G). The linear IC amplifier gain is programmed at the factory to optimize the sensitivity (mV/A) for the full-scale current of the device.

Sensitivity Error E_{SENS}

Sensitivity error E_{SENS} refers to the percentage deviation between the actual measured sensitivity and the ideal sensitivity.

For example, when V_{CC} = 3.3V,

$$E_{SENS} = \left\{\frac{Sens_{Meas(3.3V)} - Sens_{Ideal(3.3V)}}{Sens_{Ideal(3.3V)}}\right\} \times 100\%$$

The Sensitivity Temperature Drift of dS_{ERR}

Over the entire operating temperature range is defined as:

$$dS_{ERR} = \left\{\frac{Sens_{(TA)} - Sens_{(25\,℃)}}{Sens_{(25\,℃)}}\right\} \times 100\%$$

Saturation Output Voltage $V_{OUT\text{-}SAT(H/L)}$

$V_{OUT\text{-}SAT(H)}$ is the maximum output of the chip under the positive current.

$V_{OUT_SAT(L)}$ is the maximum output of the chip under the negative current

Zero Current Output Voltage $V_{OUT(Q)}$

I_P = 0, output voltage of the sensor $V_{OUT(Q)}$.

For bi-directional devices, the output voltage $V_{OUT(Q)} = V_{CC} \times 0.5$,

For uni-directional devices, the output voltage $V_{OUT(Q)} = V_{CC} \times 0.1$

Variation in $V_{OUT(Q)}$ can be attributed to the resolution of the linear IC quiescent voltage trim and thermal drift.

Offset Voltage V_{OE}

Used to measure the influence of external non-magnetic factors. Under zero-current conditions, in ratiometric output mode, it is the difference between the actual output voltage and the theoretical output voltage.

Offset Temperature Drift $V_{OUT(Q)TC}$

$V_{OUT(Q)TC}$ refers to the Temperature Coefficient of the Quiescent Output Voltage $V_{OUT(Q)}$, which is the sensor's output voltage when zero current flows. It measures how the zero-current offset voltage drifts with temperature.

$$V_{OUT(Q)TC} = V_{OUT(Q)(TA)} - V_{OUT(Q)(25\,℃)}$$

Noise V_N

Noise is the macroscopic sum of thermal noise and shot noise inside the current sensor. Dividing the noise (mV) by the sensitivity (mV/A) gives the smallest current that the device can resolve.

Symmetry E_{SYM}

Definition: The relationship between the actual output voltage $V_{OUT(Q)}$ and the forward half-range $V_{OUT\text{-}POSHALF}$ and reverse half-range $V_{OUT\text{-}NEGHALF}$ outputs

$$E_{SYM} = \left\{1 - \left(\frac{V_{OUT-POSHALF} - V_{OUT(Q)}}{V_{OUT(Q)} - V_{OUT-NEGHALF}}\right)\right\} \times 100(\%)$$

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Definitions of Accuracy Characteristics (continued)

Nonlinearity (E_{LIN})

The design output of the device varies linearly with the measured current. Ideally, under the same supply voltage and ambient temperature conditions, the output sensitivity of the device is the same for two different current sizes I1 (half scale current) and I2 (full scale current). In practical application, there is a difference in sensitivity for the measurement of two different current sizes I1 and I2, and nonlinear sensitivity error E_{LIN} describes the difference digitally. In the chip, positive current nonlinearity E_{LINPOS} and negative current nonlinearity E_{LINNEG} are defined as follows:

I_{POSx} and I_{NEGx} are positive current and negative current.

$$I_{POS2} = 2 \times I_{POS1}$$

$$I_{NEG2} = 2 \times I_{NEG1}$$

$$E_{LINPOS} = \left\{1 - \left(\frac{V_{OUT(IPOS2)} - V_{OUT(Q)}}{V_{OUT(IPOS1)} - V_{OUT(Q)}}\right)\right\} \times 100(\%)$$

$$E_{LINPOS} = \left\{1 - \left(\frac{V_{OUT(IPOS2)} - V_{OUT(Q)}}{V_{OUT(IPOS1)} - V_{OUT(Q)}}\right)\right\} \times 100(\%)$$

$$E_{LINNEG} = \left\{1 - \left(\frac{V_{OUT(INEGS2)} - V_{OUT(Q)}}{V_{OUT(INEG1)} - V_{OUT(Q)}}\right)\right\} \times 100(\%)$$

Proportional Output Sensitivity Error S_{ERR}

The proportion output sensitivity error S_{ERR} is defined based on the supply voltage VCC.

$$S_{ERR} = \left\{1 - \left(\frac{Sens_{VCC}/Sens_{3.3V}}{VCC/3.3V}\right)\right\} \times 100(\%)$$

Proportional Output Error of Static Voltage V_{0zero}

Error between the ratio of VOUT1 and VOUT0 value at VCC = 3.3V and the theoretical ratio when VCC varies from 3.0V to 3.3V

$$V_{0zero} = \left\{1 - \left(\frac{VOUT1/VOUT0}{VCC/3.3V}\right)\right\} \times 100(\%)$$

Total Output Error E_{TOT}

The difference between the current measurement from the sensor IC and the actual current (I_P), relative to the actual current. This is equivalent to the difference between the ideal output voltage and the actual output voltage, divided by the ideal sensitivity, relative to the current flowing through the primary conduction path.

$$V_{OUTideal} = V_{OUT(Q)} + (Sens_{Ideal} \times I_P)$$

$$E_{TOT} = \frac{V_{OUT} - V_{OUTIdeal}}{Sens_{Ideal} \times I_P} \times 100(\%)$$

At relatively large current, E_{TOT} is mainly sensitivity error, while at relatively small current, E_{TOT} is mainly zero current sensitivity error voltage V_{OE}. As I_P approaches zero, E_{TOT} approaches infinity due to the bias voltage.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Response Characteristics Definitions and Performance Data

Response Time ($t_{RESPONSE}$)

The time interval between a) when the sensed input current reaches 90% of its final value, and b) when the sensor output reaches 90% of its full-scale value.

Propagation Delay (t_{PROD})

The time interval between a) when the sensed input current reaches 20% of its full-scale value, and b) when the sensor output reaches 20% of its full-scale value.

Rise Time (t_R)

The time interval between a) when the sensor reaches 10% of its full-scale value, and b) when it reaches 90% of its full-scale value.




Figure 1. Response Time, Propagation Delay, Rise Time

Power-On Functional Description and Performance Data

Power-On Time (t_{PO})

When the supply is ramped to its operating voltage, the device requires a finite amount of time to power its internal components before responding to an input magnetic field. Power-On Time (t_{PO}) is defined as the time interval between a) when the power supply has reached its minimum specified operating voltage (VCC(min)), and b) when the sensor output has settled within ±10% of its steady-state value under an applied magnetic field.




Figure 2. Powe-On Time (t_{PO})

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Thermal Application Information




Figure 3. Thermal Curve




Figure 4. Derating Curve

Notes: 7. This chart shows the measured rise in steady-state die temperature of the AHC1773 versus continuous current at an ambient temperature T_A = +25°C.
8. Products above 200A are only used for transient current detection. If you need to work for a long time, please add additional heat dissipation.

Layout Guidelines

Test information on the demo board.

The capacitors should set the chip pins as close as possible. C_L = 0.47nF, C_{BYPASS} = 100nF.

The IP heat dissipation copper thickness of the demo board is 4oz, the heat dissipation area is 2 x 986 (mm^2), and the test wiring uses Kelvin sense (4-wire measuring) to avoid the voltage drop caused by GND impedance.




Figure 5. Demo Board (Top Side)





Figure 6. Demo Board (Bottom Side)

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Ordering Information (Note 9)



Orderable Part Number	Package Code	Package	Packing	
			Qty.	Carrier
AHC1773-050UPTH5-U	PTH5	PTH5	34	Tube
AHC1773-050BPTH5-U	PTH5	PTH5	34	Tube
AHC1773-100UPTH5-U	PTH5	PTH5	34	Tube
AHC1773-100BPTH5-U	PTH5	PTH5	34	Tube
AHC1773-150UPTH5-U	PTH5	PTH5	34	Tube
AHC1773-150BPTH5-U	PTH5	PTH5	34	Tube
AHC1773-200UPTH5-U	PTH5	PTH5	34	Tube
AHC1773-200BPTH5-U	PTH5	PTH5	34	Tube
AHC1773-050USMP5-U	SMP5	SMP5	34	Tube
AHC1773-050BSMP5-U	SMP5	SMP5	34	Tube
AHC1773-100USMP5-U	SMP5	SMP5	34	Tube
AHC1773-100BSMP5-U	SMP5	SMP5	34	Tube
AHC1773-150USMP5-U	SMP5	SMP5	34	Tube
AHC1773-150BSMP5-U	SMP5	SMP5	34	Tube
AHC1773-200USMP5-U	SMP5	SMP5	34	Tube
AHC1773-200BSMP5-U	SMP5	SMP5	34	Tube


Note: 9. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Marking Information

(1) Package Type: PTH5

(Top View)




YY : Year : 00 to 99 (ex : 26 = 2026)
WW : Week : 01 to 52, 52 represents week 52 and 53
XX : Internal Code

Orderable Part Number	Package	Identification Code
AHC1773-050UPTH5-U	PTH5	C73-050U
AHC1773-050BPTH5-U	PTH5	C73-050B
AHC1773-100UPTH5-U	PTH5	C73-100U
AHC1773-100BPTH5-U	PTH5	C73-100B
AHC1773-150UPTH5-U	PTH5	C73-150U
AHC1773-150BPTH5-U	PTH5	C73-150B
AHC1773-200UPTH5-U	PTH5	C73-200U
AHC1773-200BPTH5-U	PTH5	C73-200B

(2) Package Type: SMP5

(Top View)



YY : Year : 00 to 99 (ex : 26 = 2026)
WW : Week : 01 to 52, 52 represents week 52 and 53
XX : Internal Code


Orderable Part Number	Package	Identification Code
AHC1773-050USMP5-U	SMP5	C73-050U
AHC1773-050BSMP5-U	SMP5	C73-050B
AHC1773-100USMP5-U	SMP5	C73-100U
AHC1773-100BSMP5-U	SMP5	C73-100B
AHC1773-150USMP5-U	SMP5	C73-150U
AHC1773-150BSMP5-U	SMP5	C73-150B
AHC1773-200USMP5-U	SMP5	C73-200U
AHC1773-200BSMP5-U	SMP5	C73-200B

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

PTH5



PTH5			
Dim	**Min**	**Max**	**Typ**
A1	3.30	3.70	3.50
A2	6.90	7.10	7.00
b	0.41	0.61	0.51
b2	3.80	4.20	4.00
c	0.33	0.43	0.38
c2	1.40	1.60	1.50
D	13.80	14.20	14.00
D1	9.90	10.10	10.00
E1	12.90	13.10	13.00
E2	17.30	17.70	17.50
e	1.70	2.10	1.90
e1	20.40	22.40	21.40
H1	4.30	4.50	4.40
k	5.80	6.20	6.00
θ1	0°	10°	5°
θ2	-1°	3°	1°
All Dimensions in mm			


© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Package Outline Dimensions (continued)

Please see http://www.diodes.com/package-outlines.html for the latest version.

SMP5



SMP5			
Dim	**Min**	**Max**	**Typ**
A1	0.00	1.00	0.50
A2	6.90	7.10	7.00
b	0.41	0.61	0.51
b2	3.80	4.20	4.00
c	0.33	0.43	0.38
c2	1.40	1.60	1.50
D	13.80	14.20	14.00
D1	9.90	10.10	10.00
E1	12.90	13.10	13.00
e	1.70	2.10	1.90
H1	4.30	4.50	4.40
k	5.80	6.20	6.00
L	1.90	2.90	2.40
L1	9.00	10.00	9.50
L2	3.30	4.30	3.80
L3	9.10	10.10	9.60
T	6.90	7.10	7.00
θ1	0°	8°	4°
All Dimensions in mm			


© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SMP5



Dimensions	Value (in mm)
X	1.28
X1	6.05
X2	16.00
Y	4.50
Y1	5.04
Y2	33.27

Mechanical Data

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish – Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 e3
- Weight: 4.5 grams (Approximate)

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2026 Diodes Incorporated. All Rights Reserved.

www.diodes.com

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.