




SPECIFICATIONS

CUSTOMER	:	CDE021
SAMPLE CODE (Ver.)	:	PS320240WRF-HE9H08 (Ver.0)
MASS PRODUCTION CODE (Ver.)	:	PG320240WRFHE9HP9Q (Ver.0)
DRAWING NO. (Ver.)	:	PG-03104-229 (Ver.0)

Customer Approved

Date:

Approved	QC Confirmed	Designer
		

☒ Approval For Specifications Only.

* This specification is subject to change without notice.

Please contact Powertip or it's representative before designing your product based on this specification.

☐ Approval For Specifications and Sample.

POWERTIP TECH. CORP.

Headquarters:

No.8, 6th Road, Taichung Industrial Park,
Taichung, Taiwan
台中市 407 工業區六路 8 號

TEL: 886-4-2355-8168

FAX: 886-4-2355-8166

E-mail: sales@powertip.com.tw

Http://www.powertip.com.tw

NO.PT-A-005-7

RECORDS OF REVISION

Date	Ver.	Description	Page	Design by
2006/01/17	0	Mass Production (Short,JF,JDS-1,JMS-1,JCK-1)	-	PETER

Total : 23 Page

Contents

1. SPECIFICATIONS

- 1.1 Features
- 1.2 Mechanical Specifications
- 1.3 Absolute Maximum Ratings
- 1.4 DC Electrical Characteristics
- 1.5 Optical Characteristics
- 1.6 Backlight Characteristics

2. MODULE STRUCTURE

- 2.1 Counter Drawing
- 2.2 Interface Pin Description
- 2.3 Timing Characteristics
- 2.4 Command Table

3. QUALITY ASSURANCE SYSTEM

- 3.1 Quality Assurance Flow Chart
- 3.2 Inspection Specification

4. RELIABILITY TEST

- 4.1 Reliability Test Condition

5. PRECAUTION RELATING PRODUCT HANDLING

- 5.1 Safety
- 5.2 Handling
- 5.3 Storage
- 5.4 Terms of Warranty

Appendix :

- 1. LCM drawing
- 2. Package

Note : For detailed information please refer to IC data sheet : Epson S1D13700

1. SPECIFICATIONS

1.1 Features

Item	Standard Value
Display Type	320 * 240 Dots
LCD Type	FSTN, Positive, Transflective
Driver Condition	LCD Module: 1/240 Duty, 1/14 Bias
Viewing Direction	6 O'clock
Backlight	LED B/L
Weight	120g
Interface	8 bit parallel data input
Controller IC	S1D13700
ROHS	THIS PRODUCT CONFORMS THE ROHS OF PTC Detail information please refer web side : http://www.powertip.com.tw/news/LatestNews.asp

1.2 Mechanical Specifications

Item	Standard Value	Unit
Outline Dimension	92.0 (L) * 71.3 (w) * 9.0(H)(Max)	mm
Viewing Area	78.78 (L) * 59.58 (w)	mm
Active Area	76.78 (L) * 57.58 (w)	mm
Dot Size	0.22 (L) * 0.22 (w)	mm
Dot Pitch	0.24 (L) * 0.24 (w)	mm

Note : For detailed information please refer to LCM drawing

1.3 Absolute Maximum Ratings

Item	Symbol	Condition	Min.	Max.	Unit
Power Supply Voltage	V _{DD}	-	V _{SS} -0.3	+7.0	V
LCD Driver Supply Voltage	V _{EE}	-	V _{SS} -0.3	+25.0	V
Input Voltage	V _{IN}	-	V _{SS} -0.3	V _{DD} +0.5	V
Operating Temperature	T _{OP}	-	-20	70	°C
Storage Temperature.	T _{ST}	-	-30	80	°C
Storage Humidity	H _D	Ta < 40	20	90	%RH

1.4 DC Electrical Characteristics


$V_{DD} = 5\text{ V} \pm 10\%$, $V_{SS} = 0\text{ V}$, $T_a = 25^\circ\text{C}$

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
Logic Supply Voltage	V_{DD}	-	4.5	5	5.5	V
“H” Input Voltage	V_{IH}	-	3.5	-	-	V
“L” Input Voltage	V_{IL}	-	-	-	1.0	V
“H” Output Voltage	V_{OH}	-	$V_{DD}-0.4$	-	-	V
“L” Output Voltage	V_{OL}	-	-	-	0.4	V
Supply current	I_{DD}	$V_{DD} = 5.0\text{ V}$	-	14.0	50.0	mA
LCM driving voltage	V_{OP} (V_{C9})	-20°C	21.5	21.7	21.9	V
		25°C	20.7	20.9	21.1	
		70°C	19.6	19.8	20.0	

1.5 Optical Characteristics

LCD Panel: 1/240 Duty, 1/15 Bias, $V_{LCD} = 22.0\text{ V}$, $T_a = 25^\circ\text{C}$


Item	Symbol	Conditions	Min.	Typ.	Max.	Reference
View Angle	θ	$C \geq 2.0$, $\varnothing = 270^\circ$	-40°	-	40°	Notes 1
Contrast Ratio	C	$\theta = -5^\circ$, $\varnothing = 270^\circ$	2	5	-	Note 3
Response Time(rise)	t_r	$\theta = -5^\circ$, $\varnothing = 270^\circ$	-	110 ms	165 ms	Note 2
Response Time(fall)	t_f	$\theta = -5^\circ$, $\varnothing = 270^\circ$	-	260 ms	390 ms	




Note 1.

Optical characteristics-2

Viewing angle




Viewing angle




Note 2.

Optical characteristics-3

Fig.2 Definition of response time





Electrical characteristics-2

2 Drive waveform

V_{op} : Drive voltage


f_F : Frame frequency

$1/B$: Bias


f_D : Drive frequency

N : Duty

(1) Selected waveform




(2) Non- Selected waveform




Note:

Frame frequency is defined as follows: Common side supply voltage peak - to - peak / 2 = 1 period




Note 3. : Definition of Vth



	Vth1	Vth2
View direction	10°	40°
Drive waveform	(Selected waveform)	(No selected waveform)
Transmittance	50%	73%

1 Contrast ratio
= (Brightness in OFF state) / (Brightness in ON state)

Outline of Electro-Optical Characteristics Measuring System



Measuring System: Autronic DMS-803

1.6 Backlight Characteristics

LCD Module with LED Backlight

Maximum Ratings

Item	Symbol	Conditions	Min.	Max.	Unit
Forward Current	IF	Ta =25	-	120	mA
Reverse Voltage	VR	Ta =25	-	5	V
Power Dissipation	PO	Ta =25	-	0.51	W

Electrical / Optical Characteristics

Ta =25

Item	Symbol	Conditions	Min.	Typ.	Max.	Unit
Forward Voltage	VF	If= 120mA	-	3.7	4.2	V
Reverse Current	IR	VR=5 V	-	-	10	μA
Average Brightness (with LCD) *1	IV	If=120 mA	15.0	20.0	-	cd/m ²
CIE Color Coordinate (With LCD) *1	x	IF=120mA	0.25	0.31	0.37	-
	Y		0.27	0.33	0.39	
Uniformity *2	B	IF=120mA	70	-	-	%
Color	white					

*1 This vaule will be changed while mass production.

*2 : B=B(min) / B(max)


2. MODULE STRUCTURE

2.1 Counter Drawing

2.1.1 LCM Mechanical Diagram

* See Appendix

2.1.2 Block Diagram




2.2 Interface Pin Description

Pin No.	Symbol	Function
1	V _{SS}	Ground
2	V _{DD}	Power Supply
3	Adj1	Contrast adjustment.
4	/RD	Data read (read data from the module at "L")
5	/WR	Data write (write data to the module at "L")
6	A0	Command/data select
7~14	DB0~DB7	Data bus (DB0=LSB, DB7=MSB)
15	/CS	Chip select. Active "L"
16	/RES	Reset input. Active "L".
17	NC	Not connection. Must be open.
18	NC	Not connection. Must be open.
19	BL_A	Power supply for LED backlight. (Anode)
20	BL_K	Power supply for LED backlight. (Cathode)

Built in negative voltage generator circuit and temperature compensation circuit.


Built in Timing mode for 8080 family.

Contrast adjustment





2.3 Timing Characteristics




Symbol	Parameter	Min	Max	Unit
t1	/CS setup time	5	--	ns
t3	DB[7:0] setup time to /WR rising edge (write cycle)	Note2	--	ns
t4	/RD falling edge to DB[7:0] driven (read cycle)	3	--	ns
t5	/CS hold time	7	--	ns
t7	DB[7:0] hold time from /WR rising edge (write cycle)	5	--	ns
t8	DB[7:0] hold time from /RD rising edge (read cycle)	3	14	ns
t9	/RD falling edge to valid data (read cycle)	--	Note3	ns
t10	/RD, /WR cycle time	Note4	--	ns
t11	/RD, /WR pulse active time	5	--	Ts
t12	/RD, /WR pulse inactive time	Note5	--	ns

Note:

1. Ts = System clock period
2. t3min = 2Ts + 5
3. t9max = 4Ts + 20
4. t10min = 6Ts (for a read cycle followed by a read or write cycle)
= 7Ts + 2 (for a write cycle followed by a write cycle)
= 10Ts + 2 (for a write cycle followed by a read cycle)
5. t12min = 1Ts (for a read cycle followed by a read or write cycle)
= 2Ts + 2 (for a write cycle followed by a write cycle)
= 5Ts + 2 (for a write cycle followed by a read cycle)


Reset Timing



2.4 Display Command


Class	Command	Code											Hex	Command description	Command read Parameters
		RD	WR	A0	D7	D6	D5	D4	D3	D2	D1	D0			Number of bytes
System control	SYSTEM SET	1	0	1	0	1	0	0	0	0	0	0	40	Initialize device and display	8
	SLEEP IN	1	0	1	0	1	0	1	0	0	1	1	53	Enter standby mode	0
Display control	DISP ON/OFF	1	0	1	0	1	0	1	1	0	0	D	58.59	Enable and disable display and display flashing	1
	SCROLL	1	0	1	0	1	0	0	0	1	0	0	44	Set display start address and display regions	10
	CSRFORM	1	0	1	0	1	0	1	1	1	0	1	5D	Set cursor type	2
	CGRAM ADR	1	0	1	0	1	0	1	1	1	0	0	5C	Set start address of character generator RAM	2
	CSRDIR	1	0	1	0	1	0	0	1	1	CD 1	CD 0	4C to 4F	Set direction of cursor movement	0
	HDOT SCR	1	0	1	0	1	0	1	1	0	1	0	5A	Set horizontal scroll position	1
	OVLAY	1	0	1	0	1	0	1	1	0	1	1	5B	Set display overlay format	1
Drawing control	CSRW	1	0	1	0	1	0	0	0	1	1	0	46	Set cursor address	2
	CSRR	1	0	1	0	1	0	0	0	1	1	1	47	Read cursor address	2
--	Gray Scale	1	0	1	0	1	1	0	0	0	0	0	60	Set Grayscale depth	1
Memory control	MWRITE	1	0	1	0	1	0	0	0	0	1	0	42	Write to display memory	-
	MRAD	1	0	1	0	1	0	0	0	0	1	1	43	Read from display memory	-


Notes



3. QUALITY ASSURANCE SYSTEM

3.1 Quality Assurance Flow Chart





Item	Customer	Sales	R&D	Q.A	Manufacturing	Product control	Purchase	Inventory control
Sales Service	<pre>graph TD; Info[Info] --> Claim[Claim]; Claim --> Failure[Failure analysis]; Failure --> Analysis[Analysis report]; Failure --> Corrective[Corrective action]; Corrective --> Tracking[Tracking];</pre>							
Q.A Activity	<div>1. ISO 9001 Maintenance Activities</div> <div>3. Equipment calibration</div> <div>5. Standardization Management</div> <div>2. Process improvement proposal</div> <div>4. Education And Training Activities</div>							

3.2 Inspection Specification

Inspection Standard : MIL-STD-105E Table Normal Inspection Single Sampling Level

Equipment : Gauge、MIL-STD、Powertip Tester、Sample。


IQC Defect Level : Major Defect AQL 0.4; Minor Defect AQL 1.5。

FQC Defect Level : 100% Inspection。

OUT Going Defect Level : Sampling。


Specification :

NO	Item	Specification	Judge	Level
1	Part Number	The part number is inconsistent with work order of production	N.G.	Major
2	Quantity	The quantity is inconsistent with work order of production	N.G.	Major
3	Electronic characteristics of LCM $A = (L + W) \div 2$	The display lacks of some patterns.	N.G.	Major
		Missing line.	N.G.	Major
		The size of missing dot, A is $> 1/2$ Dot size	N.G.	Major
		There is no function.	N.G.	Major
		Output data is error	N.G.	Major
4	Appearance of LCD $A = (L + W) \div 2$ Dirty particle (Including scratch、bubble)	Material is different with work order of production	N.G.	Major
		LCD is assembled in inverse direction	N.G.	Major
		Bezel is assembled in inverse direction	N.G.	Major
		Shadow is within LCD viewing area + 0.5 mm	N.G.	Major
		The diameter of dirty particle, A is > 0.4 mm	N.G.	Minor
		Dirty particle length is > 3.0 mm, and 0.01 mm $<$ width 0.05 mm	N.G.	Minor
		Display is without protective film	N.G.	Minor
		Conductive rubber is over bezel 1mm	N.G.	Minor
		Polarizer exceeds over viewing area of LCD	N.G.	Minor
		Area of bubble in polarizer, A > 1.0 mm, the number of bubble is > 1 piece.	N.G.	Minor
5	Appearance of PCB $A = (L + W) \div 2$	0.4mm $<$ Area of bubble in polarizer, A < 1.0 mm, the number of bubble is > 4 pieces.	N.G.	Minor
		Burned area or wrong part number is on PCB	N.G.	Major
		The symbol, character, and mark of PCB are unidentifiable.	N.G.	Minor
		The stripped solder mask , A is > 1.0 mm	N.G.	Minor
		0.3 mm $<$ stripped solder mask or visible circuit, A < 1.0 mm, and the number is 4 pieces	N.G.	Minor
		There is particle between the circuits in solder mask	N.G.	Minor
		The circuit is peeled off or cracked	N.G.	Minor
		There is any circuits risen or exposed.	N.G.	Minor
		0.2 mm $<$ Area of solder ball, A is 0.4 mm	N.G.	Minor
		The number of solder ball is 3 pieces	N.G.	Minor
		The magnitude of solder ball, A is > 0.4 mm.	N.G.	Minor

NO	Item	Specification	Judge	Level
6	Appearance of molding $A = (L + W) \div 2$	The shape of modeling is deformed by touching.	N.G.	Major
		Insufficient epoxy: Circuit or pad of IC is visible	N.G.	Minor
		Excessive epoxy: Diameter of modeling is $> 20\text{mm}$ or height is $> 2.5\text{mm}$	N.G.	Minor
		The diameter of pinhole in modeling, A is $> 0.2\text{mm}$.	N.G.	Minor
7	Appearance of frame $A = (L + W) \div 2$	The folding angle of frame must be $> 45^\circ + 10^\circ$	N.G.	Minor
		The area of stripped electroplate in top-view of frame, A is $> 1.0\text{mm}$.	N.G.	Minor
		Rust or crack is (Top view only)	N.G.	Minor
		The scratched width of frame is $> 0.06\text{mm}$. (Top view only)	N.G.	Minor
8	Electrical characteristic of backlight $A = (L + W) \div 2$	The color of backlight is nonconforming	N.G.	Major
		Backlight can't work normally.	N.G.	Major
		The LED lamp can't work normally	N.G.	Major
		The unsoldering area of pin for backlight, A is $> 1/2$ solder joint area.	N.G.	Minor
		The height of solder pin for backlight is $> 2.0\text{mm}$	N.G.	Minor
10	Assembly parts $A = (L + W) \div 2$	The mark or polarity of component is unidentifiable.	N.G.	Minor
		The height between bottom of component and surface of the PCB is floating $> 0.7\text{mm}$	N.G.	Minor
		$D > 1/4W$ 	N.G.	Minor
		End solder joint width, D' is $> 50\%$ width of component termination or width of pad	N.G.	Minor
		Side overhang, D is $> 25\%$ width of component termination.	N.G.	Minor
		Component is cracked, deformed, and burned, etc.	N.G.	Minor
		The polarity of component is placed in inverse direction.	N.G.	Minor
		Maximum fillet height of solder extends onto the component body or minimum fillet height is $< 0.5\text{mm}$.	N.G.	Minor

4. RELIABILITY TEST

4.1 Reliability Test Condition

NO	Item	Test Condition	
1	High Temperature Storage	Storage at 80 ± 2 96~100 hrs Surrounding temperature, then storage at normal condition 4hrs	
2	Low Temperature Storage	Storage at -30 ± 2 96~100 hrs Surrounding temperature, then storage at normal condition 4hrs	
3	High Temperature /Humidity Storage	1.Storage 96~100 hrs 60 ± 2 , 90~95%RH surrounding temperature, then storage at normal condition 4hrs. (Excluding the polarizer). or 2.Storage 96~100 hrs 40 ± 2 , 90~95%RH surrounding temperature, then storage at normal condition 4 hrs.	
4	Temperature Cycling	<div style="text-align: center;"> -20 25 70 25 $(30mins)$ $(5mins)$ $(30mins)$ $(5mins)$  10 Cycle </div>	
5	Vibration	10~55Hz (1 minute) 1.5mm X,Y and Z direction * (each 2hrs)	
6	ESD Test	Air Discharge: Apply 6 KV with 5 times discharge for each polarity +/-	Contact Discharge: Apply 250V with 5 times discharge for each polarity +/-
		Testing location: Around the face of LCD	Testing location: 1.Apply to bezel. 2.Apply to Vdd, Vss.
7	Drop Test	Packing Weight (Kg)	Drop Height (cm)
		0 ~ 45.4	122
		45.4 ~ 90.8	76
		90.8 ~ 454	61
		Over 454	46

5. PRECAUTION RELATING PRODUCT HANDLING

5.1 SAFETY

- 5.1.1 If the LCD panel breaks , be careful not to get the liquid crystal to touch your skin.
- 5.1.2 If the liquid crystal touches your skin or clothes , please wash it off immediately by using soap and water.

5.2 HANDLING

- 5.2.1 Avoid any strong mechanical shock which can break the glass.
- 5.2.2 Avoid static electricity which can damage the CMOS LSI—When working with the module , be sure to ground your body and any electrical equipment you may be using.
- 5.2.3 Do not remove the panel or frame from the module.
- 5.2.4 The polarizing plate of the display is very fragile. So , please handle it very carefully ,do not touch , push or rub the exposed polarizing with anything harder than an HB pencil lead (glass , tweezers , etc.)
- 5.2.5 Do not wipe the polarizing plate with a dry cloth , as it may easily scratch the surface of plate.
- 5.2.6 Do not touch the display area with bare hands , this will stain the display area.
- 5.2.7 Do not use ketonics solvent & aromatic solvent. Use with a soft cloth soaked with a cleaning naphtha solvent.

5.3 STORAGE

- 5.3.1 Store the panel or module in a dark place where the temperature is 25 ±5 and the humidity is below 65% RH.
- 5.3.2 Do not place the module near organics solvents or corrosive gases.
- 5.3.3 Do not crush , shake , or jolt the module.


5.4 TERMS OF WARRANTY

5.4.1 Applicable warrant period


The period is within thirteen months since the date of shipping out under normal using and storage conditions.

5.4.2 Unaccepted responsibility

This product has been manufactured to your company's specification as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment , we cannot take responsibility if the product is used in nuclear power control equipment , aerospace equipment , fire and security systems or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required.



- NOTE:
- 1.The tolerance unless classified $\pm 0.3\text{mm}$
 - 2.LCD type : FSTN
 - 3.LCD mode : Positive / Transflective
 - 4.T_{op}: -20°C~70°C , T_{st}: -30°C~80°C
 - 5.Viewing Direction : 6 O'clock



DOTS DETAIL
SCALE:20/1

FFC dimensions

久正光電股份有限公司 POWER TIP TECHNOLOGY CORPORATION				APPROVED		CHECKER		DRAWN	
				SCALE:1/1		UNIT:mm		PAGE:1/1	
				圖面名稱		PG320240WRFHE9HP9Q			
				圖面編號		PG-03104-229		EDI 0	
				DATE					
				DESCRIPTION					
				REV					


1.包裝材料規格表 (Packaging Material) : (per carton)

No.	Item	Model	Dimensions (mm)	Quantity
1	成品 (LCM)	PG320240WRFHE9HP9Q	92.0 X 71.3	96
2	靜電袋(1)	BAG150120ARABA	150 X 120	96
3	氣泡袋(2)	BAG170150AWBBA	170 X 150	96
4	A2隔板(3)	BX29300070BMBA	293 X 70 X 2.5	66
5	B2隔板(4)	BX24500070BLBA	245 X 70 X 2.5	18
6	海綿墊(5)	OTFOAM00006ABA	290 X 240 X 10	12
7	C3內盒(6)Product Box	BX31025510AABA	310 X 255 X 100	6
8	外紙箱(7)Carton	BX52732536CCBA	527 X 325 X 360	1
9				

2.單箱數量規格表 (Packaging Specifications and Quantity) :

(1)Quantity Of Spacer : A2隔板 X 11 , B2隔板 X 3

(2)Total LCM quantity in carton : quantity per box 16 x no of boxes 6 = 96



特 記 事 項 (REMARK)

1. Label Specifications :

MODEL:

LOT NO:

QUANTITY:

CHECK:

2. 每放兩片模組空一格放置格。
(如放置格示意圖)

3.放置格示意圖:

1. 模組

2. 空格