



Very high accuracy (20 μ V), zero-drift, rail-to-rail output, 3 MHz, 36 V op amp



MiniSO8



SO8

Features

- Very low offset voltage: 20 μ V max. @ 25 °C
- Rail-to-rail output
- Wide supply voltage: 4 to 36 V
- Gain bandwidth product: 3 MHz
- Slew rate: 2 V/ μ s
- Low noise: 24 nV/ $\sqrt{\text{Hz}}$
- EMI hardened
- High ESD tolerance: 4 kV HBM
- Extended temperature range: -40 °C to 125 °C
- AEC-Q100 qualified

Applications

- Industrial
- Power supplies
- Automotive

Maturity status link

[TSB182](#)

Related products

TSB612	For lower current consumption
TSB622	For lower speed
TSB572	For rail-to-rail inputs
TSB712	For higher speed, precision, and rail-to-rail inputs

Description

The **TSB182** is a very high precision dual operational amplifier with a maximum guaranty of 20 μ V on input offset voltage. It can operate over an extended supply voltage operating range and features rail-to-rail output. It offers an excellent speed/power consumption ratio with 3 MHz gain bandwidth product while consuming 650 μ A typically per operational amplifier on a large supply voltage range.

The **TSB182** operates over a wide temperature range from -40 °C to 125 °C making this device ideal for industrial and automotive applications with the associated qualification.

Thanks to its small package size, the **TSB182** can be used in applications where space on the board is limited. It can thus reduce the overall cost of the PCB.

1 Pin description

Figure 1. Pin connections (top view)




Table 1. Pin description

Pin	Pin name	Description
1	OUT1	Output
2	IN1 -	Negative input voltage
3	IN1 +	Positive input voltage
4	VCC -	Negative supply voltage
5	IN2 +	Positive input voltage
6	IN2 -	Negative input voltage
7	OUT2	Output
8	VCC +	Positive supply voltage

2 Absolute maximum ratings and operating conditions

Table 2. Absolute maximum ratings

Symbol	Parameter	Value	Unit
Vcc	Supply voltage ⁽¹⁾	40	V
Vid	Differential input voltage ⁽²⁾	± 0.7	V
Vin	Input voltage	(Vcc-) -0.3 to (Vcc+) +0.3	V
Iin	Input current ⁽³⁾	10	mA
Tstg	Storage temperature	-65 to 150	°C
Tj	Junction temperature	150	°C
Rth-ja	Thermal resistance junction-to-ambient ^{(4) (5)}		°C/W
	SO8	125	
	MiniSO8	190	
ESD	Human Body Model (HBM) ⁽⁶⁾	4000	V
	Machine Model (MM) ⁽⁷⁾	200	
	Charged Device Model (CDM) ⁽⁸⁾	1500	

1. All voltage values, except differential voltage, are with respect to network ground terminal.
2. The differential voltage is the difference between inverting and non-inverting terminal voltage.
3. Input current must be limited by a resistor in series with the inputs.
4. Rth are typical values.
5. Short-circuits can cause excessive heating and destructive dissipation.
6. According to JEDEC standard JESD22-A114F.
7. According to JEDEC standard JESD22-A115A.
8. According to ANSI/ESD STM 5.3.1.

Table 3. Operating conditions

Symbol	Parameter	Value	Unit
Vcc	Supply voltage	4 to 36	V
Vicm	Common mode voltage on input pins	(Vcc-) to (Vcc+) -2	V
T	Operating free-air temperature range	-40 to 125	°C

3 Electrical characteristics

Table 4. Electrical characteristics $V_{CC} = 5\text{ V}$, $V_{icm} = V_{CC}/2$, $R_L = 10\text{ k}\Omega$ connected to $V_{CC}/2$ (unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
DC performance						
V _{IO}	Input offset voltage	V _{icm} = V _{CC} /2				μV
		T = 25 °C	-20		+20	
		Tmin < T < Tmax	-30		+30	
		V _{icm} = 0 V				
		T = 25 °C	-20		+20	
		Tmin < T < Tmax	-30		+30	
Δ V _{IO} /ΔT	Input offset voltage drift	Tmin < T < Tmax		30	100	nV/°C
I _{IB}	Input bias current	T = 25 °C			400	pA
		Tmin < T < Tmax			400	
I _{IO}	Input offset current	T = 25 °C			600	
		Tmin < T < Tmax			600	
CMR	Common mode rejection ratio	V _{icm} = 0 to V _{CC} -2 V, V _{out} = V _{CC} /2	105	130		dB
		Tmin < T < Tmax	97			
A _{vd}	Large signal voltage gain	V _{OUT} = 0.5 to (V _{CC} -0.5 V)	105	130		dB
		Tmin < T < Tmax	96			
V _{OL}	Output swing from negative rail	T = 25 °C		30	50	mV
		Tmin < T < Tmax			80	
V _{OH}	Output swing from positive rail	T = 25 °C		20	40	
		Tmin < T < Tmax			60	
I _{OUT}	Isink	V _{OUT} = V _{OL}				mA
		T = 25 °C	20	27		
		Tmin < T < Tmax	10			
	Isource	V _{OUT} = V _{OH}				
		T = 25 °C	20	29		
		Tmin < T < Tmax	10			
I _{CC}	Supply current (per channel)	No load, V _{OUT} = V _{CC} /2		650	850	μA
		Tmin < T < Tmax			900	
AC performance						
GBP	Gain bandwidth product	R _L = 10 kΩ, C _L = 100 pF	1.8	3		MHz
		Tmin < T < Tmax	1.6			
SR	Slew rate	T = 25 °C	0.85	2		V/μs
		Tmin < T < Tmax	0.75			
Φ _m	Phase margin	R _L = 10 kΩ, C _L = 100 pF		58		°
G _m	Gain margin			15		dB
En	Equivalent input noise voltage	f = 1 kHz		27		nV/√Hz
		0.1 to 10 Hz		700		nVpp

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
THD+N	Total harmonic distortion + noise	$f = 1 \text{ kHz}$, $G = 1$, $V_{OUT} = 1 \text{ Vpp}$		0.005		%
Cs	Channel separation	$f = 1 \text{ kHz}$		130		dB
trec	Overload recovery time	$G = -10$		2		μs
Ts	Settling time	0.1% to final value, $G = 1$, 1 V step		18		μs
Cload	Capacitive load drive	No sustained oscillation		1		nF

Table 5. Electrical characteristics $V_{CC} = 12\text{ V}$, $V_{icm} = V_{CC}/2$, $R_L = 10\text{ k}\Omega$ connected to $V_{CC}/2$ (unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
DC performance						
V _{IO}	Input offset voltage	V _{icm} = V _{CC} /2				μV
		T = 25 °C	-20		+20	
		Tmin < T < Tmax	-30		+30	
		V _{icm} = 0 V				
		T = 25 °C	-20		+20	
		Tmin < T < Tmax	-30		+30	
Δ V _{IO} /ΔT	Input offset voltage drift	Tmin < T < Tmax		25	100	nV/°C
I _{IB}	Input bias current	T = 25 °C			400	pA
		Tmin < T < Tmax			400	
I _{IO}	Input offset current	T = 25 °C			600	
		Tmin < T < Tmax			600	
CMR	Common mode rejection ratio	V _{icm} = 0 to V _{CC} - 2 V, V _{OUT} = V _{CC} /2	116	140		dB
		Tmin < T < Tmax	107			
A _{vd}	Large signal voltage gain	V _{OUT} = 0.5 to (V _{CC} - 0.5 V)	113	135		dB
		Tmin < T < Tmax	106			
V _{OL}	Output swing from negative rail	T = 25 °C		60	90	mV
		Tmin < T < Tmax			120	
V _{OH}	Output swing from positive rail	T = 25 °C		40	70	
		Tmin < T < Tmax			90	
I _{OUT}	Isink	V _{OUT} = V _{OL}				mA
		T = 25 °C	20	26		
		Tmin < T < Tmax	10			
	Isource	V _{OUT} = V _{OH}				
		T = 25 °C	20	29		
		Tmin < T < Tmax	10			
I _{CC}	Supply current (per channel)	No load, V _{OUT} = V _{CC} /2		650	850	μA
		Tmin < T < Tmax			900	
AC performance						
GBP	Gain bandwidth product	R _L = 10 kΩ, C _L = 100 pF	1.8	3		MHz
		Tmin < T < Tmax	1.6			
SR	Slew rate	T = 25 °C	0.8	1.8		V/μs
		Tmin < T < Tmax	0.75			
Φ _m	Phase margin	R _L = 10 kΩ, C _L = 100 pF		55		°
G _m	Gain margin			12		dB
E _n	Equivalent input noise voltage	f = 1 kHz		25		nV/√Hz
		0.1 to 10 Hz		650		nVpp
THD+N	Total harmonic distortion + noise	f = 1 kHz, Gain = 1, V _{OUT} = 1 Vpp		0.004		%
C _s	Channel separation	f = 1 kHz		130		dB

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
t_{rec}	Overload recovery time	$G = -10$		1		μs
T_s	Settling time	0.1% to final value, $G = 1$, 10 V step		7		μs
C_{load}	Capacitive load drive	No sustained oscillation		1		nF

Table 6. Electrical characteristics $V_{CC} = 36\text{ V}$, $V_{icm} = V_{CC}/2$, $R_L = 10\text{ k}\Omega$ connected to $V_{CC}/2$ (unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit	
DC performance							
V _{IO}	Input offset voltage	V _{icm} = V _{CC} /2				μV	
		T = 25 °C	-20		+20		
		Tmin < T < Tmax	-30		+30		
		Vicm = 0 V					
		T = 25 °C	-20		+20		
		Tmin < T < Tmax	-30		+30		
Δ V _{IO} /ΔT	Input offset voltage drift	Tmin < T < Tmax		20	100	nV/°C	
I _{IB}	Input bias current	T = 25 °C			500	pA	
		Tmin < T < Tmax			500		
I _{IO}	Input offset current	T = 25 °C			800		
		Tmin < T < Tmax			800		
CMR	Common mode rejection ratio	V _{icm} = 0 to V _{CC} -2 V, V _{OUT} = V _{CC} /2		127	150	dB	
		Tmin < T < Tmax		120			
SVR	Supply voltage rejection ratio	V _{CC} = 4 to 36 V		127	138	dB	
		Tmin < T < Tmax		120			
A _{vd}	Large signal voltage gain	V _{OUT} = 0.5 to (V _{CC} -0.5 V)		124	145	dB	
		Tmin < T < Tmax		115			
V _{OL}	Output swing from negative rail	T = 25 °C			140	mV	
		Tmin < T < Tmax			270		
V _{OH}	Output swing from positive rail	T = 25 °C			130	mV	
		Tmin < T < Tmax			300		
I _{OUT}	Isink	V _{OUT} = V _{OL}				mA	
		T = 25 °C		20	24		
		Tmin < T < Tmax		12			
	Isource	V _{OUT} = V _{OH}					
		T = 25 °C		20	27		
		Tmin < T < Tmax		12			
I _{CC}	Supply current (per channel)	No load, V _{OUT} = V _{CC} /2			670	850	μA
		Tmin < T < Tmax				900	
AC performance							
GBP	Gain bandwidth product	R _L = 10 kΩ, C _L = 100 pF		1.8	3		MHz
		Tmin < T < Tmax		1.8			
SR	Slew rate	T = 25 °C		0.8	1.7		V/μs
		Tmin < T < Tmax		0.6			
Φ _m	Phase margin	R _L = 10 kΩ, C _L = 100 pF			54		°
G _m	Gain margin				11		dB
En	Equivalent input noise voltage	f = 1 kHz			24		nV/√Hz
		0.1 to 10 Hz			620		nVpp

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
THD+N	Total harmonic distortion + noise	$f = 1 \text{ kHz}$, $G = 1$, $V_{OUT} = 2 \text{ Vpp}$		0.002		%
C_s	Channel separation	$f = 1 \text{ kHz}$		130		dB
t_{rec}	Overload recovery time	$G = -10$		1		μs
T_s	Settling time	0.1% to final value, $G = 1$, 10 V step		7		μs
C_{load}	Capacitive load drive	No sustained oscillation		1		nF

4 Typical performance characteristics





Figure 2. Input offset voltage distribution at $V_{CC} = 5\text{ V}$

Figure 3. Input offset voltage distribution at $V_{CC} = 12\text{ V}$

Figure 4. Input offset voltage distribution at $V_{CC} = 36\text{ V}$ and $V_{icm} = 0\text{ V}$

Figure 5. Input offset voltage distribution at $V_{CC} = 36\text{ V}$ and $V_{icm} = V_{CC}/2$








Figure 6. Input offset voltage vs. input common mode voltage at $V_{CC} = 5\text{ V}$

Figure 7. Input offset voltage vs. input common mode voltage at $V_{CC} = 12\text{ V}$

Figure 8. Input offset voltage vs. input common mode voltage at $V_{CC} = 36\text{ V}$

Figure 9. Input offset voltage vs. supply voltage

Figure 10. Input offset voltage vs. temperature

Figure 11. Input offset drift distribution








Figure 12. Supply current vs. input common mode voltage at $V_{CC} = 5\text{ V}$

Figure 13. Supply current vs. input common mode voltage at $V_{CC} = 12\text{ V}$

Figure 14. Supply current vs. input common mode voltage at $V_{CC} = 36\text{ V}$

Figure 15. Supply current vs. supply voltage

Figure 16. Input bias current vs. input common mode voltage at $V_{CC} = 5\text{ V}$

Figure 17. Input bias current vs. input common mode voltage at $V_{CC} = 12\text{ V}$








Figure 18. Input bias current vs. input common mode voltage at $V_{CC} = 36\text{ V}$

Figure 19. Output current vs. output voltage at $V_{CC} = 5\text{ V}$

Figure 20. Output current vs. output voltage at $V_{CC} = 12\text{ V}$

Figure 21. Output current vs. output voltage at $V_{CC} = 36\text{ V}$

Figure 22. Output linearity at $V_{CC} = 36\text{ V}$

Figure 23. CMRR and PSRR vs. frequency at $V_{CC} = 5\text{ V}$








Figure 24. CMRR and PSRR vs. frequency at $V_{CC} = 12\text{ V}$

Figure 25. CMRR and PSRR vs. frequency at $V_{CC} = 36\text{ V}$

Figure 26. Bode plot at $V_{CC} = 5\text{ V}$

Figure 27. Bode plot at $V_{CC} = 36\text{ V}$

Figure 28. Slew rate vs. input common mode voltage at $V_{CC} = 5\text{ V}$

Figure 29. Slew rate vs. input common mode voltage at $V_{CC} = 36\text{ V}$








Figure 30. Output voltage vs. input voltage at $V_{CC} = 5\text{ V}$

Figure 31. Output voltage vs. input voltage at $V_{CC} = 36\text{ V}$

Figure 32. Output drop voltage V_{OH} vs. supply voltage

Figure 33. Output drop voltage V_{OL} vs. supply voltage

Figure 34. Noise vs. time at $V_{CC} = 36\text{ V}$

Figure 35. Voltage noise density vs. frequency








Figure 36. Small signal response at $V_{CC} = 36\text{ V}$

Figure 37. Large signal response at $V_{CC} = 36\text{ V}$

Figure 38. Settling time on negative input step

Figure 39. Settling time on positive input step

Figure 40. Small step overshoot vs. load capacitance

Figure 41. Small step overshoot vs. R_{ISO}









Figure 42. Settling time vs. R_{iso}

Figure 43. THD vs. frequency

Figure 44. Channel separation vs. frequency

Figure 45. EMI rejection vs. frequency

Figure 46. Positive overvoltage recovery

Figure 47. Negative overvoltage recovery


Figure 48. Startup behavior at $V_{CC} = 36\text{ V}$


5 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

5.1 SO8 package information

Figure 49. SO8 package outline





Table 7. SO8 package mechanical data

Dim	mm		
	Min.	Typ.	Max.
A			1.75
A1	0.10		0.25
A2	1.25		
b	0.31		0.51
b1	0.28		0.48
c	0.10		0.25
c1	0.10		0.23
D	4.80	4.90	5.00
E	5.80	6.00	6.20
E1	3.80	3.90	4.00
e		1.27	
h	0.25		0.50
L	0.40		1.27
L1		1.04	
L2		0.25	
k	0°		8°
ccc			0.10

Figure 50. SO8 recommended footprint



5.2 MiniSO8 package information

Figure 51. MiniSO8 package outline





Table 8. MiniSO8 package mechanical data

Dim	mm			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A			1.1			0.043
A1	0		0.15	0		0.006
A2	0.75	0.85	0.95	0.03	0.033	0.037
b	0.22		0.4	0.009		0.016
c	0.08		0.23	0.003		0.009
D	2.8	3	3.2	0.11	0.118	0.126
E	4.65	4.9	5.15	0.183	0.193	0.203
E1	2.8	3	3.1	0.11	0.118	0.122
e		0.65			0.026	
L	0.4	0.6	0.8	0.016	0.024	0.031
L1		0.95			0.037	
L2		0.25			0.01	
k	0°		8°	0°		8°
ccc			0.1			0.004

Figure 52. MiniSO8 recommended footprint



6 Ordering information

Table 9. Order code

Order code	Package	Packing	Marking
TSB182IDT	SO8	Tape and reel	TSB182I
TSB182IYDT ⁽¹⁾			TSB182IY
TSB182IST	MiniSO8		K238
TSB182IYST ⁽¹⁾			K239

1. Qualified and characterized according to AEC Q100 and Q003 or equivalent, advanced screening according to AEC Q001 & Q002 or equivalent.

Revision history

Table 10. Document revision history

Date	Revision	Changes
07-Jul-2023	1	Initial release.

Contents

1	Pin description	2
2	Absolute maximum ratings and operating conditions	3
3	Electrical characteristics.....	4
4	Typical performance characteristics	10
5	Package information.....	19
5.1	SO8 package information.....	20
5.2	MiniSO8 package information	22
6	Ordering information	24
	Revision history	25

List of tables

Table 1.	Pin description	2
Table 2.	Absolute maximum ratings	3
Table 3.	Operating conditions	3
Table 4.	Electrical characteristics $V_{CC} = 5\text{ V}$, $V_{icm} = V_{CC}/2$, $R_L = 10\text{ k}\Omega$ connected to $V_{CC}/2$ (unless otherwise specified) . . .	4
Table 5.	Electrical characteristics $V_{CC} = 12\text{ V}$, $V_{icm} = V_{CC}/2$, $R_L = 10\text{ k}\Omega$ connected to $V_{CC}/2$ (unless otherwise specified) . .	6
Table 6.	Electrical characteristics $V_{CC} = 36\text{ V}$, $V_{icm} = V_{CC}/2$, $R_L = 10\text{ k}\Omega$ connected to $V_{CC}/2$ (unless otherwise specified) . .	8
Table 7.	SO8 package mechanical data	20
Table 8.	MiniSO8 package mechanical data	22
Table 9.	Order code	24
Table 10.	Document revision history	25

List of figures

Figure 1.	Pin connections (top view)	2
Figure 2.	Input offset voltage distribution at $V_{CC} = 5\text{ V}$	10
Figure 3.	Input offset voltage distribution at $V_{CC} = 12\text{ V}$	10
Figure 4.	Input offset voltage distribution at $V_{CC} = 36\text{ V}$ and $V_{icm} = 0\text{ V}$	10
Figure 5.	Input offset voltage distribution at $V_{CC} = 36\text{ V}$ and $V_{icm} = V_{CC}/2$	10
Figure 6.	Input offset voltage vs. input common mode voltage at $V_{CC} = 5\text{ V}$	11
Figure 7.	Input offset voltage vs. input common mode voltage at $V_{CC} = 12\text{ V}$	11
Figure 8.	Input offset voltage vs. input common mode voltage at $V_{CC} = 36\text{ V}$	11
Figure 9.	Input offset voltage vs. supply voltage	11
Figure 10.	Input offset voltage vs. temperature	11
Figure 11.	Input offset drift distribution	11
Figure 12.	Supply current vs. input common mode voltage at $V_{CC} = 5\text{ V}$	12
Figure 13.	Supply current vs. input common mode voltage at $V_{CC} = 12\text{ V}$	12
Figure 14.	Supply current vs. input common mode voltage at $V_{CC} = 36\text{ V}$	12
Figure 15.	Supply current vs. supply voltage	12
Figure 16.	Input bias current vs. input common mode voltage at $V_{CC} = 5\text{ V}$	12
Figure 17.	Input bias current vs. input common mode voltage at $V_{CC} = 12\text{ V}$	12
Figure 18.	Input bias current vs. input common mode voltage at $V_{CC} = 36\text{ V}$	13
Figure 19.	Output current vs. output voltage at $V_{CC} = 5\text{ V}$	13
Figure 20.	Output current vs. output voltage at $V_{CC} = 12\text{ V}$	13
Figure 21.	Output current vs. output voltage at $V_{CC} = 36\text{ V}$	13
Figure 22.	Output linearity at $V_{CC} = 36\text{ V}$	13
Figure 23.	CMRR and PSRR vs. frequency at $V_{CC} = 5\text{ V}$	13
Figure 24.	CMRR and PSRR vs. frequency at $V_{CC} = 12\text{ V}$	14
Figure 25.	CMRR and PSRR vs. frequency at $V_{CC} = 36\text{ V}$	14
Figure 26.	Bode plot at $V_{CC} = 5\text{ V}$	14
Figure 27.	Bode plot at $V_{CC} = 36\text{ V}$	14
Figure 28.	Slew rate vs. input common mode voltage at $V_{CC} = 5\text{ V}$	14
Figure 29.	Slew rate vs. input common mode voltage at $V_{CC} = 36\text{ V}$	14
Figure 30.	Output voltage vs. input voltage at $V_{CC} = 5\text{ V}$	15
Figure 31.	Output voltage vs. input voltage at $V_{CC} = 36\text{ V}$	15
Figure 32.	Output drop voltage V_{OH} vs. supply voltage	15
Figure 33.	Output drop voltage V_{OL} vs. supply voltage	15
Figure 34.	Noise vs. time at $V_{CC} = 36\text{ V}$	15
Figure 35.	Voltage noise density vs. frequency	15
Figure 36.	Small signal response at $V_{CC} = 36\text{ V}$	16
Figure 37.	Large signal response at $V_{CC} = 36\text{ V}$	16
Figure 38.	Settling time on negative input step	16
Figure 39.	Settling time on positive input step	16
Figure 40.	Small step overshoot vs. load capacitance	16
Figure 41.	Small step overshoot vs. R_{ISO}	16
Figure 42.	Settling time vs. R_{ISO}	17
Figure 43.	THD vs. frequency	17
Figure 44.	Channel separation vs. frequency	17
Figure 45.	EMI rejection vs. frequency	17
Figure 46.	Positive overvoltage recovery	17
Figure 47.	Negative overvoltage recovery	17
Figure 48.	Startup behavior at $V_{CC} = 36\text{ V}$	18
Figure 49.	SO8 package outline	20

Figure 50.	SO8 recommended footprint.	21
Figure 51.	MiniSO8 package outline	22
Figure 52.	MiniSO8 recommended footprint.	23

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2023 STMicroelectronics – All rights reserved