








RECOMMENDED PCB LAYOUT: COMPONENT SIDE



NOTES:

- MATERIAL:
HSG: NYLON, GLASS-FILLED, UL94V-0, COLOR: BLACK
CAP: NYLON, GLASS-FILLED, UL94V-0, COLOR: BLACK
PIN: 0.64MM SQ, COPPER ALLOY
- PLATING TYPE:
(1) GOLD FLASH OVER
1.25µm MIN. NICKEL OVERALL.
(2) GOLD FLASH ON CONTACT AND
2.50µm MIN. TIN ON SOLDER TAIL OVER
1.25µm MIN. NICKEL OVERALL.
(4) 0.38µm MIN. GOLD PLATE ON CONTACT AND
2.00µm MIN. TIN ON SOLDER TAIL OVER
1.25µm MIN. NICKEL OVERALL.
(5) 0.75µm MIN. GOLD PLATE ON CONTACT AND
2.00µm MIN. TIN ON SOLDER TAIL OVER
1.25µm MIN. NICKEL OVERALL.
(6) 2.50µm MIN. TIN OVERALL
1.25µm MIN. NICKEL OVERALL
- PRODUCT SPECIFICATION: PS-87920-019
- PACKAGING TYPE: SEE TABLE
- PACKAGING SPEC:
TUBE WITH CAP VERSION: PK-89990-558
TUBE W/O CAP VERSION: PK-89990-545
TRAY W/O CAP: PK-89990-489
EMBOSS TAPE WITH CAP: PK-89990-486 AND PK-87898-400
- WAFER TO BE FLAT WITHIN 0.003 mm/mm
- BEND DEPRESSION IS ACCEPTED SO LONG AS IT DOES NOT AFFECT THE OVERALL COPLANARITY OF TAIL
- COPLANARITY IS TO BE MEASURED BY RESTING THE SOLDER TAIL ON A FLAT SURFACE
- IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN BODY IS NOT ACCEPTABLE
- CAP LOCATION IS CENTERED ALONG THE MATING ENDS AS SHOWN. TOP SURFACE OF CAP TO BE FLAT FOR THE PURPOSE OF PICK & PLACE BY VACUUM SUCTION NOZZLE
- RECOMMENDED PCB THICKNESS IS 1.60mm±0.10
- THE ABOVE CKT 6 IS FOR ILLUSTRATION PURPOSE ONLY
- TUBE LENGTH AS PER STANDARD 560mm



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex	
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 745488 DRWN: SUAIFR 2023/02/15 CHK'D: SUAIFR 2023/04/10 APPR: MRAMAKRISHNA 2023/04/10 INITIAL REVISION: DRWN: GGUNAGI 2016/11/09 APPR: ISHWARG 2016/12/06					
	MM	INCH							
4 PLACES	±		±						
3 PLACES	±		±						
2 PLACES	±	0.2	±						
1 PLACE	±		±						
0 PLACES	±		±						
ANGULAR TOL				±		3.0 °			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A3-SIZE		87898	
				MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				SEE TABLE		GENERAL MARKET		1 OF 21	

	10	9	8	7	6	5	4	3	2	1										
F	PACKAGING OPTION PART NO.						CTKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					CAP (SEE SHEET-16)	REFER TO LAST SHEET FOR 2CKT SIZE				
	TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				A	B	G	F	M						
	87898-0301	-----	-----	-----	-----	-----				3	-----	1	7.62	5.08			10.81	9.65	5.84	1
	87898-0302	-----		-----	-----	-----				3	-----	2	7.62	5.08			10.81	9.65	5.84	1
	87898-0304	-----	-----	-----	-----	87898-0314				3	-----	4	7.62	5.08			10.81	9.65	5.84	1
	87898-0305	-----	-----	-----	-----	87898-0315				3	-----	5	7.62	5.08			10.81	9.65	5.84	1
	87898-0306	-----	-----	-----	-----	87898-0316				3	-----	6	7.62	5.08			10.81	9.65	5.84	1
	87898-0307	-----	-----	-----	-----	87898-0320				3	-----	6	7.62	5.08			10.81	9.65	5.84	1
	-----	-----	-----	-----	-----	87898-0317				3	-----	6	7.62	5.08			10.81	9.65	5.84	1
	-----	-----	-----	-----	-----	87898-0321				3	-----	6	7.62	5.08			10.81	9.65	5.84	1
	-----	-----	-----	-----	-----	87898-0318				3	-----	5	7.62	5.08			10.81	9.65	5.84	1
	-----	-----	-----	-----	-----	87898-0310				3	-----	6	7.62	5.08			14.91	13.91	10.10	1
	-----	-----	-----	-----	-----	87898-0309				3	-----	6	7.62	5.08			14.81	13.81	10.00	1
E	-----	-----	87898-0370	-----	-----	-----	3	-----	6	7.62	5.08	----	13.91	10.10	1					
D																				
C																				
B																				
A																				
DOCUMENT STATUS		P1	RELEASE DATE	2023/04/10	07:46:21															
Downloaded from Arrow.com		8		7		6		5		4		3		2		1				

10		9		8		7		6		5		4		3		2		1																																																																																																																																																																																																																																																																																																																	
PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	MODIFIED MATING CKT	MODIFIED MATING LENGTH	DIMENSION					CAP (SEE SHEET-16)																																																																																																																																																																																																																																																																																																																			
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP						A	B	G	F	M																																																																																																																																																																																																																																																																																																																				
F	-----	-----	87898-0421	87898-0431	-----	87898-0451	4	-----	1	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0422	87898-0432	-----	87898-0452	4	-----	2	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0424	87898-0434	-----	87898-0454	4	-----	4	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0425	87898-0435	-----	87898-0455	4	-----	5	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0426	87898-0436	-----	87898-0456	4	-----	6	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0428	87898-0437	-----	87898-0460	4	-----	6	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898-0457	4	-----	6	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898-0458	4	-----	5	-----	-----	10.16	7.62	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898 - 0480	4	CKT# 4	5	-----	-----	10.16	7.62	14.70	13.65	9.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898 - 0481	4	-----	5	CKT # 1, 2 & 3	1.00	10.16	7.62	17.70	16.65	12.84	1																																																																																																																																																																																																																																																																																																																		
E	87898 - 0482	-----	-----	-----	-----	-----	4	-----	---	CKT # 1, 2 & 3	1.00	10.16	7.62	---	16.65	12.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898 - 0483	4	-----	---	CKT # 1, 2 & 3	1.00	10.16	7.62	14.70	13.65	9.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0427	-----	-----	-----	4	-----	---	-----	-----	10.16	7.62	---	11.87	8.06	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898 - 0488	4	-----	5	-----	-----	10.16	7.62	17.78	16.74	12.93	1																																																																																																																																																																																																																																																																																																																		
D	-----	-----	87898-0521	87898-0531	-----	87898-0551	5	-----	1	-----	-----	12.70	10.16	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0522	87898-0532	-----	87898-0552	5	-----	2	-----	-----	12.70	10.16	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0524	87898-0534	-----	87898-0554	5	-----	4	-----	-----	12.70	10.16	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0525	87898-0535	-----	87898-0555	5	-----	5	-----	-----	12.70	10.16	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0526	87898-0536	87898-0583	87898-0556	5	-----	6	-----	-----	12.70	10.16	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0528	87898-0538	87898-0584	87898-0558	5	-----	6	-----	-----	12.70	10.16	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	87898-0581	-----	-----	-----	-----	-----	5	-----	4	-----	-----	12.70	10.16	---	24.18	20.25	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898-0576	5	-----	5	-----	-----	12.70	10.16	14.35	13.31	9.50	1																																																																																																																																																																																																																																																																																																																		
C	-----	-----	87898-0621	87898-0631	-----	87898-0651	6	-----	1	-----	-----	15.24	12.70	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0622	87898-0632	-----	87898-0652	6	-----	2	-----	-----	15.24	12.70	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0624	87898-0634	-----	87898-0654	6	-----	4	-----	-----	15.24	12.70	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0625	87898-0635	-----	87898-0655	6	-----	5	-----	-----	15.24	12.70	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0626	87898-0636	-----	87898-0656	6	-----	6	-----	-----	15.24	12.70	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0628	87898-0638	-----	87898-0658	6	-----	6	-----	-----	15.24	12.70	10.81	9.65	5.84	1																																																																																																																																																																																																																																																																																																																		
	87898-0607	-----	-----	-----	-----	87898-0657	6	-----	6	-----	-----	15.24	12.70	16.47	15.31	11.50	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	-----	-----	-----	87898-0605	6	-----	5	-----	-----	15.24	12.70	12.98	11.94	8.13	1																																																																																																																																																																																																																																																																																																																		
	-----	-----	87898-0604	-----	-----	-----	6	----	5	-----	-----	15.24	12.70	---	13.31	9.50	1																																																																																																																																																																																																																																																																																																																		

10	9	8	7	6	5	4	3	2	1
PACKAGING OPTION PART NO.						CAP (SEE SHEET-16)			
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				
-----	-----	87898-0721	87898-0731	-----	87898-0751	1			
-----	-----	87898-0722	87898-0732	-----	87898-0752	2			
-----	-----	87898-0724	87898-0734	-----	87898-0754	4			
-----	-----	87898-0725	87898-0735	-----	87898-0755	5			
-----	-----	87898-0726	87898-0736	-----	87898-0756	6			
-----	-----	87898-0727	87898-0737	-----	87898-0758	6			
-----	-----	-----	-----	87898-0757	-----	6			
-----	-----	-----	-----	87898-0759	-----	6			
-----	-----	87898-0720	-----	-----	-----	5			
-----	-----	87898-0767	-----	-----	-----	5			
-----	-----	87898-0821	87898-0831	-----	87898-0851	1			
-----	-----	87898-0822	87898-0832	-----	87898-0852	2			
-----	-----	87898-0824	87898-0834	-----	87898-0854	4			
-----	-----	87898-0825	87898-0835	-----	87898-0855	5			
-----	-----	87898-0826	87898-0836	-----	87898-0856	6			
-----	-----	87898-0827	87898-0837	-----	87898-0857	6			
87898-0881	-----	-----	-----	-----	-----	4			
-----	-----	87898-0921	87898-0931	-----	87898-0951	1			
-----	-----	87898-0922	87898-0932	-----	87898-0952	2			
-----	-----	87898-0924	87898-0934	-----	87898-0954	4			
-----	-----	87898-0925	87898-0935	-----	87898-0955	5			
-----	-----	87898-0926	87898-0936	-----	87898-0956	6			

	10	9	8	7	6	5	4	3	2	1						
F	PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					CAP (SEE SHEET-16)	
	TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				A	B	G	F	M		
	-----	-----	87898-1021	87898-1031	-----	87898-1051	10	-----	1	25.40	22.86	10.81	9.65	5.84	1	
	-----	-----	87898-1022	87898-1032	-----	87898-1052	10	-----	2	25.40	22.86	10.81	9.65	5.84	1	
	-----	-----	87898-1024	87898-1034	-----	87898-1054	10	-----	4	25.40	22.86	10.81	9.65	5.84	1	
	-----	-----	87898-1025	87898-1035	-----	87898-1055	10	-----	5	25.40	22.86	10.81	9.65	5.84	1	
	-----	-----	87898-1026	87898-1036	-----	87898-1056	10	-----	6	25.40	22.86	10.81	9.65	5.84	1	
	-----	-----	87898-1027	87898-1037	-----	87898-1057	10	-----	6	25.40	22.86	10.81	9.65	5.84	1	
	-----	-----	87898-1003	-----	-----	-----	10	-----	5	25.40	22.86	---	9.81	6.00	1	
E																
	-----	-----	87898-1121	87898-1131	-----	87898-1151	11	-----	1	27.94	25.40	10.81	9.65	5.84	1	
	-----	-----	87898-1122	87898-1132	-----	87898-1152	11	-----	2	27.94	25.40	10.81	9.65	5.84	1	
	-----	-----	87898-1124	87898-1134	-----	87898-1154	11	-----	4	27.94	25.40	10.81	9.65	5.84	1	
	-----	-----	87898-1125	87898-1135	-----	87898-1155	11	-----	5	27.94	25.40	10.81	9.65	5.84	1	
	-----	-----	87898-1126	87898-1136	-----	87898-1156	11	-----	6	27.94	25.40	10.81	9.65	5.84	1	
D																
	-----	-----	87898-1221	87898-1231	-----	87898-1251	12	-----	1	30.48	27.94	10.81	9.65	5.84	1	
	-----	-----	87898-1222	87898-1232	-----	87898-1252	12	-----	2	30.48	27.94	10.81	9.65	5.84	1	
	-----	-----	87898-1224	87898-1234	-----	87898-1254	12	-----	4	30.48	27.94	10.81	9.65	5.84	1	
	-----	-----	87898-1225	87898-1235	-----	87898-1255	12	-----	5	30.48	27.94	10.81	9.65	5.84	1	
	-----	87898-1226	87898-1236	-----	87898-1256	12	-----	6	30.48	27.94	10.81	9.65	5.84	1		
C																
B																
A																
DOCUMENT STATUS		P1	RELEASE DATE	2023/04/10	07:46:21											
Downloaded from Arrow.com			8	7	6	5	4	3	2	1						

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	±
2 PLACES	± 0.2	±
1 PLACE	±	±
0 PLACES	±	±
ANGULAR TOL	± 3.0 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

A3-SIZE

SERIES

87898

CURRENT REV DESC:

EC NO: 745488
DRWN: SUAIFR
CHK'D: SUAIFR
APPR: MRAMAKRISHNA

2023/02/15
2023/04/10
2023/04/10

INITIAL REVISION:

DRWN: GGUNAGI
APPR: ISHWARG

2016/11/09
2016/12/06

DOCUMENT NUMBER

SD-87898-001

DOC TYPE

PSD

DOC PART

000

REVISION

B26

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

CUSTOMER

SHEET NUMBER

2.54MM PITCH SINGLE ROW SINGLE WAFER SMT
HEADER

SEE TABLE

GENERAL MARKET

5 OF 21

molex

CUSTOM HEADER
2.54MM PITCH SINGLE ROW SINGLE WAFER SMT
HEADER

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

CUSTOMER

SHEET NUMBER

2.54MM PITCH SINGLE ROW SINGLE WAFER SMT
HEADER

SEE TABLE

GENERAL MARKET

5 OF 21

Downloaded from [Arrow.com](https://arrow.com)

DATE: 2023/01/14

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	±
2 PLACES	± 0.2	±
1 PLACE	±	±
0 PLACES	±	±
ANGULAR TOL	± 3.0 °	

DRAFT WHERE APPLICABLE

MUST REMAIN

WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 745488

DRWN: SUAIFR

CHK'D: SUAIFR

APPR: MRAMAKRISHNA

2023/02/15

2023/04/10

2023/04/10

INITIAL REVISION:

DRWN: GGUNAGI

APPR: ISHWARG

2016/11/09

2016/12/06

DOCUMENT NUMBER

SD-87898-001

DOC TYPE

PSD

DOC PART

000

REVISION

B26

PRODUCT CUSTOMER DRAWING

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

5 OF 21

THIRD ANGLE PROJECTION

DRAWING

A3-SIZE

SERIES

87898

molex

CUSTOM HEADER

2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER

Downloaded from [Arrow.com](https://arrow.com)

DATE: 2023/01/14

[illegible]

10	9	8	7	6	5	4	3	2	1
PACKAGING OPTION PART NO.						CAP (SEE SHEET-16)			
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				
-----	-----	87898-1621	87898-1631	-----	87898-1651	16			
-----	-----	87898-1622	87898-1632	-----	87898-1652	16			
-----	-----	87898-1624	87898-1634	-----	87898-1654	16			
-----	-----	87898-1625	87898-1635	-----	87898-1655	16			
-----	-----	87898-1626	87898-1636	-----	87898-1656	16			
-----	-----	87898-1627	87898-1637	-----	87898-1657	16			
-----	-----	87898-1721	87898-1731	-----	87898-1751	17			
-----	-----	87898-1722	87898-1732	-----	87898-1752	17			
-----	-----	87898-1724	87898-1734	-----	87898-1754	17			
-----	-----	87898-1725	87898-1735	-----	87898-1755	17			
-----	-----	87898-1726	87898-1736	-----	87898-1756	17			
-----	-----	87898-1821	87898-1831	-----	87898-1851	18			
-----	-----	87898-1822	87898-1832	-----	87898-1852	18			
-----	-----	87898-1824	87898-1834	-----	87898-1854	18			
-----	-----	87898-1825	87898-1835	-----	87898-1855	18			
-----	-----	87898-1826	87898-1836	-----	87898-1856	18			
-----	-----	87898-1827	87898-1837	-----	87898-1857	18			

10

9

8

7

6

5

4

3

2

1

DOCUMENT STATUS

P1

RELEASE DATE

2023/04/10 07:46:21

10

9

8

7

6

5

4

3

2

1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

MM

INCH

4 PLACES

±

±

3 PLACES

±

±

2 PLACES

±

0.2

±

1 PLACE

±

±

0 PLACES

±

±

ANGULAR TOL

±

3.0 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 745488

DRWN: SUAIFR

CHK'D: SUAIFR

APPR: MRAMAKRISHNA

2023/02/15

2023/04/10

2023/04/10

INITIAL REVISION:

DRWN: GGUNAGI

APPR: ISHWARG

2016/11/09

2016/12/06

THIRD ANGLE PROJECTION

DRAWING

A3-SIZE

SERIES

87898

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

7 OF 21

molex

CUSTOM HEADER

2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

SD-87898-001

DOC TYPE

PSD

DOC PART

000

REVISION

B26

Downloaded from [Arrow.com](#)

DATE: 2023/01/14

[illegible]

10	9	8	7	6	5	4	3	2	1
PACKAGING OPTION PART NO.						CAP (SEE SHEET-16)			
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				
-----	-----	87898-2221	87898-2231	-----	-----	1			
-----	-----	87898-2222	87898-2232	-----	-----	2			
-----	-----	87898-2224	87898-2234	-----	-----	4			
-----	-----	87898-2225	87898-2235	-----	-----	5			
-----	-----	87898-2226	87898-2236	-----	-----	6			
-----	-----	87898-2321	87898-2331	-----	-----	1			
-----	-----	87898-2322	87898-2332	-----	-----	2			
-----	-----	87898-2324	87898-2334	-----	-----	4			
-----	-----	87898-2325	87898-2335	-----	-----	5			
-----	-----	87898-2326	87898-2336	-----	-----	6			
-----	-----	87898-2421	87898-2431	-----	-----	1			
-----	-----	87898-2422	87898-2432	-----	-----	2			
-----	-----	87898-2424	87898-2434	-----	-----	4			
-----	-----	87898-2425	87898-2435	-----	-----	5			
-----	-----	87898-2426	87898-2436	-----	-----	6			
-----	-----	87898-2427	87898-2437	-----	-----	6			

[illegible]

10	9	8	7	6	5	4	3	2	1
PACKAGING OPTION PART NO.						CAP (SEE SHEET-16)			
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				
-----	-----	87898-2821	87898-2831	-----	-----	1			
-----	-----	87898-2822	87898-2832	-----	-----	2			
-----	-----	87898-2824	87898-2834	-----	-----	4			
-----	-----	87898-2825	87898-2835	-----	-----	5			
-----	-----	87898-2826	87898-2836	-----	-----	6			
-----	-----	87898-2921	87898-2931	-----	-----	1			
-----	-----	87898-2922	87898-2932	-----	-----	2			
-----	-----	87898-2924	87898-2934	-----	-----	4			
-----	-----	87898-2925	87898-2935	-----	-----	5			
-----	-----	87898-2926	87898-2936	-----	-----	6			
-----	-----	87898-3021	87898-3031	-----	-----	1			
-----	-----	87898-3022	87898-3032	-----	-----	2			
-----	-----	87898-3024	87898-3034	-----	-----	4			
-----	-----	87898-3025	87898-3035	-----	-----	5			
-----	-----	87898-3026	87898-3036	-----	-----	6			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

MM

INCH

4 PLACES

±

±

3 PLACES

±

±

2 PLACES

±

0.2

±

1 PLACE

±

±

0 PLACES

±

±


ANGULAR TOL

±

3.0 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION



DRAWING

A3-SIZE

SERIES

87898

CURRENT REV DESC:

EC NO: 745488

DRWN: SUAIFR

CHK'D: SUAIFR

APPR: MRAMAKRISHNA

2023/02/15

2023/04/10

2023/04/10

INITIAL REVISION:

DRWN: GGUNAGI

APPR: ISHWARG

2016/11/09

2016/12/06

DOCUMENT NUMBER

SD-87898-001

DOC TYPE

PSD

DOC PART

000

REVISION

B26

CUSTOMER

GENERAL MARKET

SHEET NUMBER

11 OF 21

PRODUCT CUSTOMER DRAWING

DOCUMENT STATUS

P1

RELEASE DATE

2023/04/10

07:46:21




[illegible]

10	9	8	7	6	5	4	3	2	1
PACKAGING OPTION PART NO.						CAP (SEE SHEET-16)			
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				
-----	-----	87898-3421	87898-3431	-----	-----	1			
-----	-----	87898-3422	87898-3432	-----	-----	2			
-----	-----	87898-3424	87898-3434	-----	-----	4			
-----	-----	87898-3425	87898-3435	-----	-----	5			
-----	-----	87898-3426	87898-3436	-----	-----	6			
-----	-----	87898-3521	87898-3531	-----	-----	1			
-----	-----	87898-3522	87898-3532	-----	-----	2			
-----	-----	87898-3524	87898-3534	-----	-----	4			
-----	-----	87898-3525	87898-3535	-----	-----	5			
-----	-----	87898-3526	87898-3536	-----	-----	6			
-----	-----	87898-3621	87898-3631	-----	-----	1			
-----	-----	87898-3622	87898-3632	-----	-----	2			
-----	-----	87898-3624	87898-3634	-----	-----	4			
-----	-----	87898-3625	87898-3635	-----	-----	5			
-----	-----	87898-3626	87898-3636	-----	-----	6			




10		9		8		7		6		5		4		3		2		1	
PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					CAP (SEE SHEET-16)					
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				A	B	G	F	M						
-----	-----	87898-3721	87898-3731	-----	-----	37	-----	1	93.98	91.44	10.81	9.65	5.84	1					
-----	-----	87898-3722	87898-3732	-----	-----	37	-----	2	93.98	91.44	10.81	9.65	5.84	1					
-----	-----	87898-3724	87898-3734	-----	-----	37	-----	4	93.98	91.44	10.81	9.65	5.84	1					
-----	-----	87898-3725	87898-3735	-----	-----	37	-----	5	93.98	91.44	10.81	9.65	5.84	1					
-----	-----	87898-3726	87898-3736	-----	-----	37	-----	6	93.98	91.44	10.81	9.65	5.84	1					
-----	-----	87898-3821	87898-3831	-----	-----	38	-----	1	96.52	93.98	10.81	9.65	5.84	1					
-----	-----	87898-3822	87898-3832	-----	-----	38	-----	2	96.52	93.98	10.81	9.65	5.84	1					
-----	-----	87898-3824	87898-3834	-----	-----	38	-----	4	96.52	93.98	10.81	9.65	5.84	1					
-----	-----	87898-3825	87898-3835	-----	-----	38	-----	5	96.52	93.98	10.81	9.65	5.84	1					
-----	-----	87898-3826	87898-3836	-----	-----	38	-----	6	96.52	93.98	10.81	9.65	5.84	1					
-----	-----	87898-3921	87898-3931	-----	-----	39	-----	1	99.06	96.52	10.81	9.65	5.84	1					
-----	-----	87898-3922	87898-3932	-----	-----	39	-----	2	99.06	96.52	10.81	9.65	5.84	1					
-----	-----	87898-3924	87898-3934	-----	-----	39	-----	4	99.06	96.52	10.81	9.65	5.84	1					
-----	-----	87898-3925	87898-3935	-----	-----	39	-----	5	99.06	96.52	10.81	9.65	5.84	1					
-----	-----	87898-3926	87898-3936	-----	-----	39	-----	6	99.06	96.52	10.81	9.65	5.84	1					

10	9	8	7	6	5	4	3	2	1			
PACKAGING OPTION PART NO.						CAP (SEE SHEET-16)						
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP							
-----	-----	87898-4021	87898-4031	-----	-----							
-----	-----	87898-4022	87898-4032	-----	-----							
-----	-----	87898-4024	87898-4034	-----	-----							
-----	-----	87898-4025	87898-4035	-----	-----							
-----	-----	87898-4026	87898-4036	-----	-----							


CAP ORIENTATION (CAP - 1)




CAP ORIENTATION (CAP - 2)





PART ORIENTATION IN TUBE





PART WITHOUT CAP PART WITH CAP


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex CUSTOM HEADER 2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER				
mm		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 745488 DRWN: SUAIFR 2023/02/15 CHK'D: SUAIFR 2023/04/10 APPR: MRAMAKRISHNA 2023/04/10				PRODUCT CUSTOMER DRAWING				
	MM		INCH									
4 PLACES	±		±									
3 PLACES	±		±									
2 PLACES	±	0.2	±									
1 PLACE	±		±	INITIAL REVISION: DRWN: GGUNAGI 2016/11/09 APPR: ISHWARG 2016/12/06				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
0 PLACES	±		±					SD-87898-001		PSD	000	B26
ANGULAR TOL ± 3.0 °												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
				A3-SIZE		87898	SEE TABLE		GENERAL MARKET		16 OF 21	



















RECOMMENDED PCB LAYOUT




NOTES:

1. MATERIAL:
HSG: NYLON, GLASS-FILLED, UL94V-0, COLOR: BLACK
PIN: 0.64MM SQ, COPPER ALLOY
2. PLATING TYPE:
(1) GOLD FLASH OVER
1.25µm MIN. NICKEL OVERALL.
(2) GOLD FLASH ON CONTACT AND
2.50µm MIN. TIN ON SOLDERTAIL OVER
1.25µm MIN. NICKEL OVERALL.
(4) 0.38µm MIN. GOLD PLATE ON CONTACT AND
2.00µm MIN. TIN ON SOLDERTAIL OVER
1.25µm MIN. NICKEL OVERALL.
(5) 0.75µm MIN. GOLD PLATE ON CONTACT AND
2.00µm MIN. TIN ON SOLDERTAIL OVER
1.25µm MIN. NICKEL OVERALL.
(6) 2.50µm MIN. TIN OVERALL
1.25µm MIN. NICKEL OVERALL
3. PRODUCT SPECIFICATION: PS-87920-019
4. PACKAGING TYPE: SEE TABLE
5. PACKAGING SPEC: PK-89990-545(TUBE), PK-89990-486(T&R)
& PK-87898-400 (T&R)
6. WAFER TO BE FLAT WITHIN 0.003 mm/mm
7. BEND DEPRESSION IS ACCEPTED SO LONG AS IT DOES NOT AFFECT THE OVERALL COPLANARITY OF TAIL
8. COPLANARITY IS TO BE MEASURED BY RESTING THE SOLDER TAIL ON A FLAT SURFACE
9. IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION IS PERMISSIBLE.CUTTING OR CHIPPING OF THE MAIN BODY IS NOT ACCEPTABLE
10. TUBE LENGTH AS PER STANDARD 560mm
11. RECOMMENDED PCB THICKNESS IS 1.60mm±0.10
12. THE ABOVE CKT 6 IS FOR ILLUSTRATION PURPOSE ONLY
13. CAP LOCATION IS CENTERED ALONG THE MATING ENDS AS SHOWN. TOP SURFACE OF CAP TO BE FLAT FOR THE PURPOSE OF PICK & PLACE BY VACUUM SUCTION NOZZLE.




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex	
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 698212 DRWN: DANUSA 2022/03/03 CHK'D: DANUSA 2022/03/04 APPR: MRAMAKRISHNA 2022/03/04				CUSTOM HEADER 2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER	
		MM	INCH						
4 PLACES	±		±	INITIAL REVISION: DRWN: SKLIM01 2005/10/26 APPR: PTLIM 2005/11/07				PRODUCT CUSTOMER DRAWING	
3 PLACES	±		±						
2 PLACES	±	0.2	±	DOCUMENT NUMBER SD-87898-003				DOC TYPE PSD	
1 PLACE	±		±					DOC PART 001	
0 PLACES	±		±	SHEET NUMBER 1 OF 17				REVISION C1	
ANGULAR TOL		± 3.0 °							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING A3-SIZE	SERIES 87898	MATERIAL NUMBER SEE TABLE	CUSTOMER GENERAL MARKET


PART WITHOUT CAP
IN TUBE
ORIENTATION



PART WITH CAP
IN TUBE
ORIENTATION




CKT	DIMENSION						QTY/REEL
	Bo	Ao	Ko	F	So	W	
3	8.02	5.20	13.60	11.50	--	24.00	320
4	10.51	5.79	15.05	14.20	28.40	32.00	250
5	13.10	5.20	13.60	11.50	---	24.00	320




NOTES:


1. LEADER AND TRAILER TAPE



2. PEELING OFF FORCE OF THE TOP TAPE: 20 - 80gf. (PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)



3. MATERIAL: BLACK P.S CONDUCTIVE, BLACK
4. MEASURED FROM CENTRELINE OF SPROCKET HOLE TO CENTRELINE OF POCKET
5. CUMULATIVE TOLERANCE OF 10 SPROCKET HOLE IS $\pm 0.20\text{mm}$
6. A0 AND B0 ARE MEASURE FROM ABOVE POCKET BASE 0.30mm
7. TAPE AND REEL SPECIFICATION IS AS PER EIA-481.
8. THE TAPE IS TREATED FOR ANTI-STATIC.
9. ALL RADIUS ARE 0.30MM UNLESS SPECIFY
10. SURFACE RESISTIVITY 10^3 TO 10 OHMS.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		NTS													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 698212 DRWN: DANUSA 2022/03/03 CHK'D: DANUSA 2022/03/04 APPR: MRAMAKRISHNA 2022/03/04				CUSTOM HEADER 2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER							
	MM	INCH													
4 PLACES	±	±													
3 PLACES	±	±													
2 PLACES	±	0.2	±												
1 PLACE	±	±		INITIAL REVISION:				PRODUCT CUSTOMER DRAWING							
0 PLACES	±	±													
ANGULAR TOL ± 3.0 °															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING A3-SIZE		SERIES 87898		MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 3 OF 17	

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/04	09:00:56
-----------------	----	--------------	------------	----------

9		8		7		6		5		4		3		2		1	
E	PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION							
	TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				A	B	F	M				
	-----	-----	87898-0761	-----	-----	-----	7	----	1	17.78	15.24	11.94	8.13				
	-----	-----	87898-0762	-----	-----	-----	7	----	2	17.78	15.24	11.94	8.13				
	-----	-----	87898-0764	-----	-----	-----	7	----	4	17.78	15.24	11.94	8.13				
	-----	-----	87898-0765	-----	-----	-----	7	----	5	17.78	15.24	11.94	8.13				
-----	-----	87898-0766	-----	-----	-----	7	----	6	17.78	15.24	11.94	8.13					
D																	
	-----	-----	87898-0861	-----	-----	-----	8	----	1	20.32	17.78	11.94	8.13				
	-----	-----	87898-0862	-----	-----	-----	8	----	2	20.32	17.78	11.94	8.13				
	-----	-----	87898-0864	-----	-----	-----	8	----	4	20.32	17.78	11.94	8.13				
	-----	-----	87898-0865	-----	-----	-----	8	----	5	20.32	17.78	11.94	8.13				
-----	-----	87898-0866	-----	-----	-----	8	----	6	20.32	17.78	11.94	8.13					
C																	
	-----	-----	87898-0961	-----	-----	-----	9	----	1	22.86	20.32	11.94	8.13				
	-----	-----	87898-0962	-----	-----	-----	9	----	2	22.86	20.32	11.94	8.13				
	-----	-----	87898-0964	-----	-----	-----	9	----	4	22.86	20.32	11.94	8.13				
	-----	-----	87898-0965	-----	-----	-----	9	----	5	22.86	20.32	11.94	8.13				
-----	-----	87898-0966	-----	-----	-----	9	----	6	22.86	20.32	11.94	8.13					
B																	
A																	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS mm SCALE NTS GENERAL TOLERANCES (UNLESS SPECIFIED) MM INCH 4 PLACES ± ± 3 PLACES ± ± 2 PLACES ± 0.2 ± 1 PLACE ± ± 0 PLACES ± ± ANGULAR TOL ± 3.0 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS THIRD ANGLE PROJECTION DRAWING A3-SIZE SERIES 87898 MATERIAL NUMBER SEE TABLE CUSTOMER GENERAL MARKET SHEET NUMBER 6 OF 17 CURRENT REV DESC: EC NO: 698212 DRWN: DANUSA2022/03/03 CHK'D: DANUSA2022/03/04 APPR: MRAMAKRISHNA2022/03/04 INITIAL REVISION: DRWN: SKLIM012005/10/26 APPR: PTLIM2005/11/07 molex CUSTOM HEADER 2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-87898-003 DOC TYPE PSD DOC PART 001 REVISION C1 DOCUMENT STATUS P1 RELEASE DATE 2022/03/04 09:00:56																	
8		7		6		5		4		3		2		1			

Downloaded from

Arrow.com

DATE: 2018/01/19

[illegible]

9		8		7		6		5		4		3		2		1					
E	PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
	TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				A	B	F	M								
	-----	-----	87898-2261	-----	-----	-----				22	----	1	55.88	53.34	11.94	8.13					
	-----	-----	87898-2262	-----	-----	-----				22	----	2	55.88	53.34	11.94	8.13					
	-----	-----	87898-2264	-----	-----	-----				22	----	4	55.88	53.34	11.94	8.13					
	-----	-----	87898-2265	-----	-----	-----				22	----	5	55.88	53.34	11.94	8.13					
D	-----	-----	87898-2266	-----	-----	-----	22	----	6	55.88	53.34	11.94	8.13								
	-----	-----	87898-2361	-----	-----	-----	23	----	1	58.42	55.88	11.94	8.13								
	-----	-----	87898-2362	-----	-----	-----	23	----	2	58.42	55.88	11.94	8.13								
	-----	-----	87898-2364	-----	-----	-----	23	----	4	58.42	55.88	11.94	8.13								
C	-----	-----	87898-2365	-----	-----	-----	23	----	5	58.42	55.88	11.94	8.13								
	-----	-----	87898-2366	-----	-----	-----	23	----	6	58.42	55.88	11.94	8.13								
	-----	-----	87898-2461	-----	-----	-----	24	----	1	60.96	58.42	11.94	8.13								
	-----	-----	87898-2462	-----	-----	-----	24	----	2	60.96	58.42	11.94	8.13								
A	-----	-----	87898-2464	-----	-----	-----	24	----	4	60.96	58.42	11.94	8.13								
	-----	-----	87898-2465	-----	-----	-----	24	----	5	60.96	58.42	11.94	8.13								
	-----	-----	87898-2466	-----	-----	-----	24	----	6	60.96	58.42	11.94	8.13								
DOCUMENT STATUS		P1	RELEASE DATE	2022/03/04	09:00:56	8		7		6		5		4		3		2		1	
Downloaded from Arrow.com		8		7		6		5		4		3		2		1					

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	±
2 PLACES	± 0.2	±
1 PLACE	±	±
0 PLACES	±	±
ANGULAR TOL	± 3.0 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

A3-SIZE

SERIES

87898

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

11 OF 17

CURRENT REV DESC:

EC NO: 698212

DRWN: DANUSA

CHK'D: DANUSA

APPR: MRAMAKRISHNA

2022/03/03

2022/03/04

2022/03/04

INITIAL REVISION:

DRWN: SKLIM01

APPR: PTLIM

2005/10/26

2005/11/07

DOCUMENT NUMBER

SD-87898-003

DOC TYPE

PSD

DOC PART

001

REVISION

C1

molex

CUSTOM HEADER

2.54MM PITCH SINGLE ROW SINGLE WAFER SMT
HEADER

PRODUCT CUSTOMER DRAWING

9		8		7		6		5		4		3		2		1				
PACKAGING OPTION PART NO.														CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION			
TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP	A	B	F	M											
-----	-----	87898-3161	-----	-----	-----	31	----	1	78.74	76.20	11.94	8.13								
-----	-----	87898-3162	-----	-----	-----	31	----	2	78.74	76.20	11.94	8.13								
-----	-----	87898-3164	-----	-----	-----	31	----	4	78.74	76.20	11.94	8.13								
-----	-----	87898-3165	-----	-----	-----	31	----	5	78.74	76.20	11.94	8.13								
-----	-----	87898-3166	-----	-----	-----	31	----	6	78.74	76.20	11.94	8.13								
-----	-----	87898-3261	-----	-----	-----	32	----	1	81.28	78.74	11.94	8.13								
-----	-----	87898-3262	-----	-----	-----	32	----	2	81.28	78.74	11.94	8.13								
-----	-----	87898-3264	-----	-----	-----	32	----	4	81.28	78.74	11.94	8.13								
-----	-----	87898-3265	-----	-----	-----	32	----	5	81.28	78.74	11.94	8.13								
-----	-----	87898-3266	-----	-----	-----	32	----	6	81.28	78.74	11.94	8.13								
-----	-----	87898-3361	-----	-----	-----	33	----	1	83.82	81.28	11.94	8.13								
-----	-----	87898-3362	-----	-----	-----	33	----	2	83.82	81.28	11.94	8.13								
-----	-----	87898-3364	-----	-----	-----	33	----	4	83.82	81.28	11.94	8.13								
-----	-----	87898-3365	-----	-----	-----	33	----	5	83.82	81.28	11.94	8.13								
-----	-----	87898-3366	-----	-----	-----	33	----	6	83.82	81.28	11.94	8.13								

9		8		7		6		5		4		3		2		1	
E	PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION							
	TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				A	B	F	M				
	-----	-----	87898-3461	-----	-----	-----	34	----	1	86.36	83.82	11.94	8.13				
	-----	-----	87898-3462	-----	-----	-----	34	----	2	86.36	83.82	11.94	8.13				
	-----	-----	87898-3464	-----	-----	-----	34	----	4	86.36	83.82	11.94	8.13				
	-----	-----	87898-3465	-----	-----	-----	34	----	5	86.36	83.82	11.94	8.13				
-----	-----	87898-3466	-----	-----	-----	34	----	6	86.36	83.82	11.94	8.13					
D																	
	-----	-----	87898-3561	-----	-----	-----	35	----	1	88.90	86.36	11.94	8.13				
	-----	-----	87898-3562	-----	-----	-----	35	----	2	88.90	86.36	11.94	8.13				
	-----	-----	87898-3564	-----	-----	-----	35	----	4	88.90	86.36	11.94	8.13				
	-----	-----	87898-3565	-----	-----	-----	35	----	5	88.90	86.36	11.94	8.13				
-----	-----	87898-3566	-----	-----	-----	35	----	6	88.90	86.36	11.94	8.13					
C																	
	-----	-----	87898-3661	-----	-----	-----	36	----	1	91.44	88.90	11.94	8.13				
	-----	-----	87898-3662	-----	-----	-----	36	----	2	91.44	88.90	11.94	8.13				
	-----	-----	87898-3664	-----	-----	-----	36	----	4	91.44	88.90	11.94	8.13				
	-----	-----	87898-3665	-----	-----	-----	36	----	5	91.44	88.90	11.94	8.13				
-----	-----	87898-3666	-----	-----	-----	36	----	6	91.44	88.90	11.94	8.13					
B																	
A																	
DOCUMENT STATUS		P1	RELEASE DATE		2022/03/04	09:00:56											
8		7		6		5		4		3		2		1			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

NTS

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	±
2 PLACES	± 0.2	±
1 PLACE	±	±
0 PLACES	±	±
ANGULAR TOL	± 3.0 °	

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

THIRD ANGLE PROJECTION

DRAWING

A3-SIZE

SERIES

87898

MATERIAL NUMBER

SEE TABLE

CUSTOMER

GENERAL MARKET

SHEET NUMBER

15 OF 17

CURRENT REV DESC:

EC NO: 698212

DRWN: DANUSA

CHK'D: DANUSA

APPR: MRAMAKRISHNA

2022/03/03

2022/03/04

2022/03/04

INITIAL REVISION:

DRWN: SKLIM01

APPR: PTLIM

2005/10/26

2005/11/07

DOCUMENT NUMBER

SD-87898-003

DOC TYPE

PSD

DOC PART

001

REVISION

C1

molex

CUSTOM HEADER

2.54MM PITCH SINGLE ROW SINGLE WAFER SMT
HEADER

PRODUCT CUSTOMER DRAWING

Downloaded from [Arrow.com](#)

DATE: 20180119

9	8	7	6	5	4	3	2	1																																																																																													
E	<table><tr><th colspan="6">PACKAGING OPTION PART NO.</th><th rowspan="2">CKT SIZE</th><th rowspan="2">VOID POSITION</th><th rowspan="2">PLATING TYPE</th><th colspan="4">DIMENSION</th></tr><tr><th>TRAY WITHOUT CAP</th><th>TRAY WITH CAP</th><th>TUBE WITHOUT CAP</th><th>TUBE WITH CAP</th><th>TAPE & REEL WITHOUT CAP</th><th>TAPE & REEL WITH CAP</th><th>A</th><th>B</th><th>F</th><th>M</th></tr><tr><td>-----</td><td>-----</td><td>87898-4061</td><td>-----</td><td>-----</td><td>-----</td><td>40</td><td>-----</td><td>1</td><td>101.6</td><td>99.06</td><td>11.94</td><td>8.13</td></tr><tr><td>-----</td><td>-----</td><td>87898-4062</td><td>-----</td><td>-----</td><td>-----</td><td>40</td><td>-----</td><td>2</td><td>101.6</td><td>99.06</td><td>11.94</td><td>8.13</td></tr><tr><td>-----</td><td>-----</td><td>87898-4064</td><td>-----</td><td>-----</td><td>-----</td><td>40</td><td>-----</td><td>4</td><td>101.6</td><td>99.06</td><td>11.94</td><td>8.13</td></tr><tr><td>-----</td><td>-----</td><td>87898-4065</td><td>-----</td><td>-----</td><td>-----</td><td>40</td><td>-----</td><td>5</td><td>101.6</td><td>99.06</td><td>11.94</td><td>8.13</td></tr><tr><td>-----</td><td>-----</td><td>87898-4066</td><td>-----</td><td>-----</td><td>-----</td><td>40</td><td>-----</td><td>6</td><td>101.6</td><td>99.06</td><td>11.94</td><td>8.13</td></tr></table>												PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP	A	B	F	M	-----	-----	87898-4061	-----	-----	-----	40	-----	1	101.6	99.06	11.94	8.13	-----	-----	87898-4062	-----	-----	-----	40	-----	2	101.6	99.06	11.94	8.13	-----	-----	87898-4064	-----	-----	-----	40	-----	4	101.6	99.06	11.94	8.13	-----	-----	87898-4065	-----	-----	-----	40	-----	5	101.6	99.06	11.94	8.13	-----	-----	87898-4066	-----	-----	-----	40	-----	6	101.6	99.06	11.94	8.13	E
	PACKAGING OPTION PART NO.						CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																											
	TRAY WITHOUT CAP	TRAY WITH CAP	TUBE WITHOUT CAP	TUBE WITH CAP	TAPE & REEL WITHOUT CAP	TAPE & REEL WITH CAP				A	B	F	M																																																																																								
	-----	-----	87898-4061	-----	-----	-----	40	-----	1	101.6	99.06	11.94	8.13																																																																																								
	-----	-----	87898-4062	-----	-----	-----	40	-----	2	101.6	99.06	11.94	8.13																																																																																								
	-----	-----	87898-4064	-----	-----	-----	40	-----	4	101.6	99.06	11.94	8.13																																																																																								
-----	-----	87898-4065	-----	-----	-----	40	-----	5	101.6	99.06	11.94	8.13																																																																																									
-----	-----	87898-4066	-----	-----	-----	40	-----	6	101.6	99.06	11.94	8.13																																																																																									
D													D																																																																																								
C													C																																																																																								
B													B																																																																																								
A	<table><tr><td colspan="4">DOCUMENT STATUS</td><td>P1</td><td colspan="2">RELEASE DATE</td><td>2022/03/04</td><td>09:00:56</td></tr></table> THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION <table><tr><td colspan="2">DIMENSION UNITS</td><td colspan="2">SCALE</td><td colspan="4" rowspan="2">CURRENT REV DESC:</td><td colspan="4" rowspan="2"> molex CUSTOM HEADER 2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER </td></tr><tr><td colspan="2">mm</td><td colspan="2">NTS</td></tr><tr><td colspan="4">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2"></td><td colspan="2" rowspan="6">EC NO: 698212 DRWN: DANUSA 2022/03/03 CHK'D: DANUSA 2022/03/04 APPR: MRAMAKRISHNA 2022/03/04 INITIAL REVISION: DRWN: SKLIM01 2005/10/26 APPR: PTLIM 2005/11/07</td><td colspan="4" rowspan="2">PRODUCT CUSTOMER DRAWING</td></tr><tr><td colspan="2"></td><td>MM</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>±</td><td></td><td>±</td></tr><tr><td>3 PLACES</td><td>±</td><td></td><td>±</td></tr><tr><td>2 PLACES</td><td>±</td><td>0.2</td><td>±</td></tr><tr><td>1 PLACE</td><td>±</td><td></td><td>±</td></tr><tr><td>0 PLACES</td><td>±</td><td></td><td>±</td></tr><tr><td colspan="2">ANGULAR TOL</td><td colspan="2">± 3.0 °</td><td colspan="4" rowspan="2"> THIRD ANGLE PROJECTION </td><td colspan="2">DRAWING</td><td>SERIES</td><td>MATERIAL NUMBER</td><td>CUSTOMER</td><td>SHEET NUMBER</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">A3-SIZE</td><td>87898</td><td>SEE TABLE</td><td>GENERAL MARKET</td><td>17 OF 17</td></tr></table> Downloaded from Arrow.com DATE: 2018/1/19 8 7 6 5 4 3 2 1												DOCUMENT STATUS				P1	RELEASE DATE		2022/03/04	09:00:56	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex CUSTOM HEADER 2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER				mm		NTS		GENERAL TOLERANCES (UNLESS SPECIFIED)						EC NO: 698212 DRWN: DANUSA 2022/03/03 CHK'D: DANUSA 2022/03/04 APPR: MRAMAKRISHNA 2022/03/04 INITIAL REVISION: DRWN: SKLIM01 2005/10/26 APPR: PTLIM 2005/11/07		PRODUCT CUSTOMER DRAWING						MM	INCH	4 PLACES	±		±	3 PLACES	±		±	2 PLACES	±	0.2	±	1 PLACE	±		±	0 PLACES	±		±	ANGULAR TOL		± 3.0 °		THIRD ANGLE PROJECTION				DRAWING		SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				A3-SIZE		87898	SEE TABLE	GENERAL MARKET	17 OF 17	A			
DOCUMENT STATUS				P1	RELEASE DATE		2022/03/04	09:00:56																																																																																													
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex CUSTOM HEADER 2.54MM PITCH SINGLE ROW SINGLE WAFER SMT HEADER																																																																																													
mm		NTS																																																																																																			
GENERAL TOLERANCES (UNLESS SPECIFIED)						EC NO: 698212 DRWN: DANUSA 2022/03/03 CHK'D: DANUSA 2022/03/04 APPR: MRAMAKRISHNA 2022/03/04 INITIAL REVISION: DRWN: SKLIM01 2005/10/26 APPR: PTLIM 2005/11/07		PRODUCT CUSTOMER DRAWING																																																																																													
		MM	INCH																																																																																																		
4 PLACES	±		±																																																																																																		
3 PLACES	±		±																																																																																																		
2 PLACES	±	0.2	±																																																																																																		
1 PLACE	±		±																																																																																																		
0 PLACES	±		±																																																																																																		
ANGULAR TOL		± 3.0 °		THIRD ANGLE PROJECTION				DRAWING		SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																																																																																								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								A3-SIZE		87898	SEE TABLE	GENERAL MARKET	17 OF 17																																																																																								
8	7	6	5	4	3	2	1																																																																																														