

# Power Connectors & Interconnection Systems



## Table of Contents

|                   |     |
|-------------------|-----|
| <b>Technology</b> | 4-9 |
|-------------------|-----|

### Section 1 — Board-to-Board Products

|                                                                            |        |
|----------------------------------------------------------------------------|--------|
| MULTI-BEAM XL and MULTI-BEAM XLE Power Distribution Connector Systems      | 10-29  |
| MULTI-BEAM XL Power Distribution Connector Systems                         | 12-14  |
| “NEW” MULTI-BEAM XLE Connectors                                            | 15, 16 |
| MULTI-BEAM XL Current Pass-Thru Power Distribution Connector System        | 17, 18 |
| MULTI-BEAM XL Power Distribution Connector System                          |        |
| Cable Receptacle Assemblies                                                | 19-25  |
| Cable Plug Assemblies                                                      | 26-28  |
| MULTI-BEAM XL and MULTI-BEAM XLE Connectors Custom Configuration Worksheet | 29     |
| MINIPAK High-Density Board-to-Board Power Connectors                       | 30-39  |
| “NEW” MINIPAK HDL Connectors                                               | 34, 35 |
| MINIPAK HD Connectors                                                      | 36, 37 |
| MINIPAK HDE Connectors                                                     | 38, 39 |
| FLATPAQ Modular Board-to-Board Power Connectors                            | 40-44  |
| ICCON Single Pole Power Connectors                                         | 45-49  |
| Mini Power Modules                                                         | 50-59  |
| MULTIGIG RT Power Modules                                                  | 52     |
| Universal Power Modules (UPM)                                              | 53-55  |
| “NEW” Low Profile Universal Power Module                                   | 54     |
| Slim UPM Product                                                           | 53, 55 |
| Z-PACK 2 mm Futurebus+ Power Modules                                       | 56, 57 |
| Backplane and Co-Planar Guide Modules                                      | 58, 59 |
| Z1 Power Connector for AdvancedTCA Zone 1 Applications                     | 60, 61 |

### Section 2 — Cable Mounted Products

|                                                                             |          |
|-----------------------------------------------------------------------------|----------|
| MULTI-BEAM XL Products (see Board-to-Board Products Section 1, pages 10-29) |          |
| ELCON High Power Drawer Connectors                                          | 62-82    |
| AMP Low Power Drawer Connectors                                             | 83-101   |
| Miniature Power Drawer (MPD) Connectors                                     | 83, 84   |
| Hybrid Blind-Mate Drawer Connectors                                         | 85-87    |
| Special Blind-Mate Drawer Connectors                                        | 88-91    |
| Standard Blind-Mate Drawer Connectors                                       | 92-95    |
| Hybrid Mini-Drawer Connectors                                               | 96-101   |
| ET Power Connector                                                          | 102-104  |
| AMP-DUAC PL Product                                                         | 105-107  |
| AMP-DUAC PL-II Connectors                                                   | 108, 109 |
| AMP-DUAC UPC Connectors                                                     | 110, 111 |
| Contacts for AMP-DUAC, PL-II and UPC Connectors                             | 112, 113 |
| Other Soft Shell Pin & Socket Connectors                                    | 114-116  |
| AMPINNERGY Products                                                         | 117-124  |
| Circular (CPC) Connectors for Commercial Signal and Power Applications      | 125-127  |
| High Current Products (LOUVERTAC Contacts)                                  | 128-139  |
| AMP Power Series Connectors                                                 | 140-154  |
| Domino Series Connectors                                                    | 155-161  |
| HTS Power Connectors                                                        | 162, 163 |
| RAPID LOCK Quick Connect/Disconnect Bus Bar Connectors                      | 164-167  |
| AMP Power Taps                                                              | 168-172  |

### Section 3 — Card Edge Products

|                                                    |          |
|----------------------------------------------------|----------|
| Introduction to High Current Card Edge Connectors  | 173, 174 |
| CROWN EDGE Card Edge-style High Current Connectors | 175-181  |
| SEC-II Power Products                              | 182-184  |
| Standard Edge II Card Edge Connectors              | 185-187  |

### Section 4 — Voltage Regulation Module (VRM) Connectors

|                                                       |          |
|-------------------------------------------------------|----------|
| Voltage Regulation Module (VRM) Connectors            | 188, 189 |
| VR 372 Power POD Connector — for Intel MONTECITO VRMs | 190      |
| Mini CROWN EDGE Connector Configurations              | 191, 192 |
| SEC-II Connectors with Latches for VRMs               | 193      |

#### Disclaimer

While TE has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2012, 2010, 2007 and 2005  
Tyco Electronics Corporation.  
All Rights Reserved.

ACTION PIN, AMP, AMP-DUAC, AMP-DUAC PL, AMP-DURAGOLD, AMPINNERGY, AMP-LEAF, AMP-O-LECTRIC, AMPPOWER, CORCOM, CROWN BAND, CROWN CLIP, CROWN EDGE, CROWN LINE, ELCON, FASTON, FLATPAQ, HTS, ICCON, ISOLAMES, LOUVERTAC, MATE-N-LOK, MINIPAK, MULTI-BEAM XL, MULTIGIG RT, PRO-CRIMPER, RAPID LOCK, SIMEL, SLIMLINE ICCON, Z-PACK, Z-PACK TinMan, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

AdvancedTCA, AdvancedTCA 300, CompactPCI, MicroTCA and PICMG are trademarks of PICMG-PCI Industrial Computer Manufacturers Group Incorporated.

FUTUREBUS+ is a trademark of Institute of Electrical and Electronics Engineers, Inc.

ITANIUM and MONTECITO are trademarks of Intel Corporation.

NEMA is a trademark of the National Electrical Manufacturers Association.

VITA and VITA logo are trademarks of VITA in the United States and other countries.

Duracell and Matsushita Battery are trademarks of their respective owners.

Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

## Table of Contents (Continued)

### Section 5 — Bus Bar Products

|                                                                                    |          |
|------------------------------------------------------------------------------------|----------|
| ELCON Drawer Series Connectors (see Cable Mounted Products Section 2, pages 62-82) |          |
| CROWN CLIP Series Sockets .....                                                    | 194-199  |
| CROWN CLIP II Sockets .....                                                        | 196      |
| Dual CROWN CLIP Sockets.....                                                       | 197      |
| CROWN CLIP Junior Sockets .....                                                    | 198-199  |
| Pluggable Bus Bar Connectors .....                                                 | 200-202  |
| CROWN LINE Power Distribution System .....                                         | 203, 204 |

|                                                     |         |
|-----------------------------------------------------|---------|
| <b>Section 6 — AMPPOWER Wave Crimp System</b> ..... | 205-216 |
|-----------------------------------------------------|---------|

### Section 7 — Bulk Cable

|                                 |     |
|---------------------------------|-----|
| ISOLAMES Flexible Bus Bar ..... | 217 |
|---------------------------------|-----|

### Section 8 — AC Inputs

|                                      |         |
|--------------------------------------|---------|
| Convenience Outlets .....            | 219-222 |
| CORCOM EMI/RFI Filter Products ..... | 223     |
| CORCOM DB Products .....             | 224-226 |

### Section 9 — Laptops/Portables

|                                 |          |
|---------------------------------|----------|
| Battery Interconnects .....     | 227-232  |
| Coin Cell Battery Holders ..... | 233      |
| DC Power Jacks .....            | 234, 235 |

### Section 10 — Custom Cable Assemblies

|                               |     |
|-------------------------------|-----|
| Custom Cable Assemblies ..... | 236 |
|-------------------------------|-----|

|                                  |         |
|----------------------------------|---------|
| <b>Application Tooling</b> ..... | 237-239 |
|----------------------------------|---------|

|                                                                      |          |
|----------------------------------------------------------------------|----------|
| <b>How To Compute Circular Mil Area of Various Wire Shapes</b> ..... | 240, 241 |
|----------------------------------------------------------------------|----------|

|                                |         |
|--------------------------------|---------|
| <b>Part Number Index</b> ..... | 242-244 |
|--------------------------------|---------|

|                              |     |
|------------------------------|-----|
| <b>Global Contacts</b> ..... | 247 |
|------------------------------|-----|

### Need more information?

Call Technical Support at the numbers listed below.

Technical Support is staffed with specialists well versed in all TE products. They can provide you with:

- Technical Support
- Catalogs
- Technical Documents
- Product Samples
- TE Authorized Distributor Locations

### Restriction on the use of Hazardous Substances (RoHS)

At TE, we're ready to support your RoHS requirements. We've assessed more than 1.5 million end items/components for RoHS compliance, and issued new part numbers where any change was required to eliminate the restricted materials. Part numbers in this catalog are identified as:

**RoHS Compliant** — Part numbers in this catalog are RoHS Compliant, unless marked otherwise. These products comply with European Union Directive 2002/95/EC as amended 1 January 2006 that restricts the use of lead, mercury, cadmium, hexavalent chromium, PBB, and PBDE in certain electrical and electronic products sold into the EU as of 1 July 2006.

**NOTE:** For purposes of this Catalog, included within the definition of RoHS Compliant are products that are clearly "Out of Scope" of the RoHS Directive such as hand tools and other non-electrical accessories.

**5 of 6 Compliant** — A "●" symbol identifies these part numbers. These products do not fully comply with the European Union Directive 2002/95/EC because they contain lead in solderable interfaces (they do not contain any of the other five restricted substances above allowable limits). However, these products may be suitable for use in RoHS applications where there is an application-based exception for lead in solders, such as the server, storage, or networking infrastructure exemption.

**NOTE:** Information regarding RoHS compliance is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information provided by our suppliers. This information is subject to change. For latest compliance status, refer to our website referenced at right.

### Getting the Information You Need

Our comprehensive on-line RoHS Customer Support Center provides a forum to answer your questions and support your RoHS needs. A RoHS FAQ (Frequently Asked Questions) is available with links to more detailed information. You can also submit RoHS questions and receive a response within 24 hours during a normal work week. The Support Center also provides:

- Cross-Reference from Non-compliant to Compliant Products
- Ability to browse RoHS Compliant Products in our on-line catalog
- Downloadable Technical Data Customer Information Presentation
- More detailed information regarding the definitions used above
- So whatever your questions when it comes to RoHS, we've got the answers at [www.te.com/leadfree](http://www.te.com/leadfree)

**RoHS**  
Customer  
Support  
Center

## Products Listed in this Catalog

### Integrated Backplane Power Systems Pages 50-61

- Universal Power Modules
- Slim UPM Product
- MINIPAK HDE Connectors
- Z-PACK Futurebus+ Power Modules
- MULTIGIG RT Power Modules
- Guide Hardware
- Z1 Power AdvancedTCA Connectors

### Mezzanine/Stacking Pages 191-192

- Mini CROWN EDGE Products

### Bus Bar-to-Board

- CROWN EDGE Products
- CROWN CLIP Series Sockets
- CROWN CLIP Junior
- CROWN LINE
- ICCON Connectors
- ELCON DRAWER Series Connectors

### Power — Board-to-Board Pages 10-61

- MULTI-BEAM XL and MULTI-BEAM XLE Connectors
- FLATPAQ Modular Connectors
- MINIPAK Connectors
- MINIPAK HD (MicroTCA) Connectors
- CROWN EDGE Connectors
- SEC-II Power Products
- ICCON Connectors
- MINIPAK HDL Connectors

### Power — Cable-to-Cable/Board Pages 62-172

- MULTI-BEAM XL Cable Assemblies
- ELCON DRAWER Series
- AMP DRAWER Series
- AMP-DUAC PL Products
- AMP-DUAC UPC Connectors
- Universal MATE-N-LOK Family
- AMPINERGY Product
- AMP Power Series
- CPC
- Mini Power Drawer (MPD)
- AMPOWER Wave Crimp System
- RAPID LOCK Connectors
- AMP Power Tap
- Domino Series Connectors
- HTS Power Connectors
- ET Connector

### VRM/Power PODs Pages 188-193


- SEC-II, Mini CROWN EDGE (32 Bit) Connectors
- VR372 Power POD Connector

### Laptops/Portable Pages 227-235

- Battery Interconnects
- Coin Cell Battery Holder
- Multi-Directional Interface (MDI) Connectors
- DC Power Jacks

### Input/Output Power Pages 219-226, 236

- Convenience Outlets
- CORCOM EMI/RFI Filter Products
- Custom Cable Assemblies



AdvancedTCA and MicroTCA are trademarks of PICMG-PCI Industrial Computer Manufacturers Group, Inc.

## Product Selection Chart

| Product Listing                               | Application Style |               |                |           | Battery |   | Application Type |                | Current Level |                  |                                 |                            | Special Features |            |                | Standards                       | Page |
|-----------------------------------------------|-------------------|---------------|----------------|-----------|---------|---|------------------|----------------|---------------|------------------|---------------------------------|----------------------------|------------------|------------|----------------|---------------------------------|------|
|                                               | Wire-to-Wire      | Wire-to-Board | Board-to-Board | Card Edge |         |   | Power Only       | Power & Signal | Low Current   |                  | Middle Current Contacts 25A-50A | High Current Contacts >50A | True Hot-Plug    | Blind-Mate | Low Inductance | Industry Standard               |      |
|                                               |                   |               |                |           |         |   |                  |                | Contacts <10A | Contacts 10A-25A |                                 |                            |                  |            |                |                                 |      |
| AdvancedTCA Z1 Power Connectors               | X                 |               | X              |           |         |   |                  | X              |               | X                |                                 |                            |                  |            |                | PICMG 3.0                       | 60   |
| AMP DUAC PL Product                           |                   | X             |                |           |         |   | X                | X              | X             |                  |                                 |                            |                  |            |                |                                 | 104  |
| AMPINERGY Connectors                          | X                 | X             |                |           |         |   | X                |                | X             | X                |                                 |                            |                  |            |                |                                 | 115  |
| AMP Power Series Connectors                   | X                 |               |                |           |         |   | X                |                |               | X                | X                               | X                          |                  |            |                |                                 | 138  |
| AMP Power Taps                                |                   | X             |                |           |         |   | X                |                | X             | X                |                                 |                            |                  |            |                |                                 | 166  |
| AMPOWER Wave Crimp System                     | X                 | X             |                |           |         |   | X                | X              |               |                  | X                               |                            |                  | X          |                |                                 | 204  |
| Battery Interconnects                         |                   | X             | X              |           | X       |   | X                |                | X             |                  |                                 |                            |                  |            |                |                                 | 227  |
| Circular Plastic Connectors (CPC)             | X                 |               |                |           |         |   | X                | X              |               |                  | X                               |                            |                  |            |                | VDE Standard 0627               | 123  |
| Coin Cell Battery Holders                     |                   |               |                |           | X       | X | X                |                | X             |                  |                                 |                            |                  |            |                |                                 | 233  |
| Commercial Pin & Socket                       | X                 |               |                |           |         |   | X                |                |               | X                |                                 |                            |                  |            |                |                                 | 113  |
| CROWN CLIP Series                             |                   |               |                | X         |         | X | X                |                |               |                  |                                 | X                          | X                | X          |                |                                 | 192  |
| CROWN EDGE Product                            |                   |               |                | X         |         | X |                  | X              |               |                  | X                               |                            | X                |            |                |                                 | 173  |
| CROWN LINE Connectors                         |                   |               |                | X         |         | X | X                |                |               |                  |                                 | X                          |                  | X          |                |                                 | 202  |
| DC Power Jack                                 |                   | X             |                |           |         |   | X                |                |               | X                |                                 |                            |                  |            |                |                                 | 234  |
| Domino Product                                | X                 | X             |                |           |         |   |                  | X              | X             | X                | X                               | X                          | X                | X          |                |                                 | 153  |
| ELCON Drawer Connectors                       | X                 | X             |                |           |         |   |                  | X              | X             | X                | X                               | X                          | X                | X          |                |                                 | 62   |
| ET Power Connectors                           |                   | X             |                |           |         |   | X                |                |               |                  | X                               |                            |                  |            |                |                                 | 102  |
| FLATPAQ Product <sup>1</sup>                  |                   |               | X              |           |         |   |                  | X              |               |                  | X                               |                            | X                | X          |                |                                 | 40   |
| Grace Inertia Connectors                      | X                 |               |                |           |         |   | X                |                | X             |                  |                                 |                            |                  |            |                |                                 | 113  |
| HTS Connectors                                | X                 | X             |                |           |         |   | X                |                |               | X                | X                               |                            | X                |            |                |                                 | 160  |
| Hybrid Blind-Mate Drawer                      | X                 |               |                |           |         |   |                  | X              | X             |                  |                                 |                            |                  | X          |                |                                 | 85   |
| Hybrid Mini-Drawer                            |                   | X             |                |           |         |   |                  | X              |               | X                |                                 |                            |                  |            |                |                                 | 96   |
| ICCON Products <sup>1</sup>                   |                   | X             | X              |           |         |   | X                |                |               |                  | X                               |                            |                  |            |                |                                 | 45   |
| MATE-N-LOK                                    | X                 | X             | X              |           |         |   | X                |                |               | X                |                                 |                            |                  |            |                |                                 | 115  |
| Micro MATE-N-LOK Connectors                   | X                 | X             |                |           |         |   | X                |                | X             |                  |                                 |                            |                  |            |                |                                 | 113  |
| Mini CROWN EDGE Product                       |                   |               |                | X         |         |   |                  | X              |               | X                |                                 |                            |                  |            | X              | VRM 10.2, 11                    | 189  |
| Mini Power Drawer (MPD)                       |                   | X             |                |           |         |   | X                |                |               | X                |                                 |                            | X                | X          |                |                                 | 83   |
| Mini Universal MATE-N-LOK                     | X                 | X             |                |           |         |   | X                |                | X             |                  |                                 |                            |                  |            |                |                                 | 114  |
| MINIPAK HD Connectors                         |                   |               | X              |           |         |   |                  | X              |               | X                |                                 |                            | X                |            |                | AMC 1.0                         | 36   |
| MINIPAK HDE Connectors                        |                   |               | X              |           |         |   | X                |                |               | X                |                                 |                            | X                |            |                |                                 | 38   |
| MINIPAK HDL                                   |                   |               | X              |           |         |   |                  | X              |               | X                |                                 |                            | X                | X          |                |                                 | 34   |
| MULTI-BEAM XL/XLE Connectors <sup>1</sup>     | X                 | X             | X              |           |         |   | X                | X              |               | X                | X                               |                            | X                | X          |                | SSI (MPS, DPS)                  | 10   |
| MULTIGIG RT Power Product                     |                   |               | X              |           |         |   | X                |                | X             | X                |                                 |                            |                  |            |                |                                 | 52   |
| Power Double Lock                             | X                 | X             |                |           |         |   | X                |                |               | X                |                                 |                            |                  |            |                |                                 | 114  |
| RAPID LOCK Product                            |                   | X             |                |           |         | X | X                |                |               |                  |                                 | X                          |                  |            |                |                                 | 162  |
| Special Blind-Mate Drawer                     | X                 | X             |                |           |         |   |                  | X              | X             |                  |                                 |                            |                  | X          | X              |                                 | 88   |
| Standard Blind-Mate Drawer                    | X                 | X             |                |           |         |   |                  | X              | X             | X                |                                 |                            |                  | X          |                |                                 | 92   |
| Standard Edge II Card Edge <sup>1</sup>       |                   |               | X              | X         |         |   | X                | X              | X             | X                | X                               |                            |                  |            |                | VRM 8.5-10.1, ISA               | 183  |
| Universal MATE-N-LOK                          | X                 | X             |                |           |         |   | X                |                |               | X                |                                 |                            |                  |            |                | U.L. Standard 1410, MIL STD 202 | 115  |
| Universal Power Module (UPM)                  | X                 |               | X              |           |         |   | X                |                |               | X                |                                 |                            | X                |            |                | PICMG EXP.0                     | 53   |
| VAL-U-LOK                                     | X                 | X             |                |           |         |   | X                |                |               | X                |                                 |                            |                  |            |                |                                 | 114  |
| VR 372 Power POD Connector for MONTECITO VRMs |                   |               | X              |           |         |   |                  | X              |               |                  |                                 | X                          |                  |            |                | VR372                           | 188  |
| Z-PACK 2 mm Futurebus+ Product                | X                 |               | X              |           |         |   | X                |                | X             |                  |                                 |                            |                  |            |                | IEC 61076-4-0X                  | 56   |

<sup>1</sup>Co-planar products

AdvancedTCA is a trademark of PICMG-PCI Industrial Computer Manufacturers Group, Inc.  
MONTECITO is a trademark of Intel Corporation.

## Power Distribution Connector Overview

### TE Power Connector Technology

For years, TE has pioneered the development of new power interconnect technologies. As the industry leader in Power Interconnects, TE produces power connectors used in laptops through super computers, automobiles, telecommunications base stations, consumer appliances, power utility, industrial controls, locomotives and many other applications.

The products in this catalog are focused on the higher performing power connectors used in the Computer and Telecommunications industries.

Some key factors in the design of these new connectors are the selection of the right contact and housing materials, platings and contact designs. Many of the older single or dual point of contact intercon-

nects have been replaced with new/next generation designs which can offer significant reductions in contact resistance, insertion/mating force, connector size and total applied cost. In addition, several of the newest designs have significant increases in current and signal density all combined into a single power distribution connector.

As power delivery applications vary widely, TE also produces many variations of the products listed in this catalog for unique applications. If you don't find the product needed for your application, please feel free to contact our Product Information Center or your local TE Sales Engineers.

### High Performance Started with the ELCON CROWN BAND Power Contact Technology



One of the popular technologies used in high current connects is based on the ELCON CROWN BAND Power Contact Technology. Made from high conductivity alloys and used with solid screw machined pin and socket contacts, these contacts deliver superior performance. Many of the high current Drawer Connectors in this catalog use this technology.


- 1/4th to 1/10th the Contact Resistance
- Maximum Contact Surface Area
- Low Voltage Drop, Low Temperature Rise
- Higher Cycle Durability
- Used in High Performance Pin & Socket Drawer Connectors
- Safety Agency Approved Hot-Plug Contacts Available



### CROWN BAND Performance in Stamped & Formed Configurations


FLATPAQ Connectors, MINIPAK Connectors, CROWN EDGE Connectors, Mini CROWN EDGE Connectors, MULTI-BEAM XL Connectors, AMPPOWER Wave Crimp Products, CROWN CLIP Sockets, Pluggable Bus Bar Products.

These product lines all utilize the multiple point of contact design. With the 6, 8, 10, 12 or more contact points per stamping, the contact resistance remains very low and the mating cycle durability remains high.




## Extensive Product Qualification

TE has played a major role in influencing the industry to evaluate power connectors based upon End-Of-Design-Life conditions. This involves a variety of accelerated life tests used to determine the expected results of the power connectors after years of use in demanding applications.




Temperature Rise charts using a single contact have been replaced with more useful data taken from tests of actual fully loaded connectors carrying their maximum current.

The tests are run with pre-stressed (end-of-life) connectors to provide worst case results based on the environmental exposure the connectors will see.




In many cases the common safety agency approvals are also provided. While these tests are typically far less stringent than TE's internal test sequences,

they provide additional safety/regulatory information for end users to help them make the connector selection easier.




### Shock & Vibration

Shock and vibration testing is used to verify the mechanical integrity of the connector system. Shock capability to test half-sine, saw-tooth, and trapezoidal waveforms up to 3000 g's. Vibration capability to test sinusoidal, random, sine-on-random, and narrow band random-on-random profiles up to 2000 Hz.



### Thermal Image

Thermography is used to optimize the design and to pinpoint the exact hot spot on the contacts — to measure the true worst case temperature-rise. Then thermocouples are placed on the hot spot to confirm the temperature at the end-of-life conditions.




### Durability and Hot-Plug Set-Up

Current Interrupt (hot-plug) tests are performed to customer-specific requirements to determine the ability of the connector to sustain repeated make & break cycles under load. Power generation capability up to 600 VDC.

Durability tests are performed in accordance with both industry (EIA 364-70) standards and TE documented test sequences. With this, the user knows exactly what was tested and how it was tested, in order to achieve the specified durability rating.



## TE Delivers Both Industry Standard and Application-Specific Power Connectors



### Industry or De-Facto Standard Products

- MULTI-BEAM XL Connectors (SSI and AdvancedTCA 300 Standards)
- Z1 Power Connector (AdvancedTCA)
- MINIPAK HD Connector (MicroTCA)
- Universal MATE-N-LOK Connectors
- VRM Card Edge Connectors (VRM 8.5 – 11.0)
- Universal Power Module (CPCI Express)
- Power Series (50 – 350 Amp DC power)
- CORCOM EMI/RFI Filter Products (IEC 320)

### Application Specific Products

- Drawer Series (Top Drawer — Mini Drawer)
- CROWN EDGE & Mini CROWN EDGE Connectors
- FLATPAQ Connectors
- MINIPAK Connectors
- CROWN CLIP Connectors
- ICCON Connectors
- RAPID LOCK Connectors

## Standards Activities / Safety Agency Approvals

TE has a broad line of power interconnects meeting the industry's most stringent safety standards:

TE End-Of-Design-Life (EODL) accelerated life testing has influenced many new standards for power interconnects.

**CompactPCI®**

**AdvancedTCA®**



**VITA**  
Open Standards, Open Markets

**EIA**  
Electronic Components Association

**UL**

**CSA**

**μTCA™**



AdvancedTCA, AdvancedTCA 300, CompactPCI, MicroTCA and PICMG are trademarks of PICMG-PCI Industrial Computer Manufacturers Group Incorporated.

VITA and VITA logo are trademarks of VITA in the United States and other countries.

## Current Carrying Capabilities

TE offers a wide range of power contacts, which handle up to 500 Amps. The total current capacity of each contact in a given connector is dependent upon the heat rise resulting from the combination of electrical loads of the contacts in the connector arrangement and the maximum ambient temperature in which the connector will be operating. Caution must be taken so that this combination of conditions does not cause the internal temperature of the connector to exceed the maximum operating temperature of the housing material. Several variables which must be considered when determining this maximum current capability for your application are:


■ **Wire Size** — Larger wire will carry more current since it has less internal resistance to current flow and generates less heat. The wire also conducts heat away from the connector.

■ **Connector Size** — In general, with more circuits in a connector, less current per contact can be carried.

■ **Current Load Distribution** — Spreading those lines with greater current loads throughout the connector, particularly around the outer perimeter, will enhance heat dissipation.

■ **Ambient Temperature** — With higher ambient temperatures, less current can be carried.

**Note:** The current ratings in this chart are based upon single contact loading and a 30° C temperature rise. More useful "fully loaded" ratings are available and are dependent upon the variables listed above.



## Application-Specific Designs

### In the shortest time to market in the industry.

If none of our standard products satisfies your requirements, TE can develop a design specific to your application. We will work closely with your engineers to fully understand the design requirements and develop an interconnect solution that meets your exact needs. After the concept and design stages, TE produces prototypes that perform both electrically and mechanically the same as production parts. These machined parts are used for testing, regulatory agency evaluations, and even as pre-production components, allowing the shortest lead time from concept to manufacturing in the industry.

#### Concept

TE engineers work closely with the customer to fully understand the design requirements of the application.



#### Design

A sketch drawing of the design concept is created for customer review, and the design is finalized only when it fully meets the requirements of the customer.




#### Prototypes

Once the design is frozen, and while TE works on the molds and the connector assembly processes, TE builds prototypes that are identical to the production parts.



#### Production

By the time both TE and the customer are ready for mass production, all requirements for release to production, such as qualification testing and regulatory agency approval, have been cleared.



## MULTI-BEAM XL and MULTI-BEAM XLE Power Distribution Connector Systems

### Board-Mount Connectors

#### Product Facts

- Single-piece molded housings
- Custom configurable modular design
- AC and DC power in the same connector — Meets UL safety requirements
- Current Interrupt ratings per UL 1977 — for “Hot-Plug” applications
- Compact size — suitable for distributed DC power applications
- Molded-in guide pins provide generous blind-mateability
- Up to 3 levels of contact sequencing:
  - 1st — Pwr/Gnd
  - 2nd — Pwr & Signals
  - 3rd — Trigger Signals
- Low Mating and Un-mating force
- Solder or press-fit termination to PCB
- Meets SSI power connector requirements for DPS, MPS and HPS applications
- 30 micro-inch [0.76 micro-meters] gold post-plated contacts for high reliability
- All MULTI-BEAM XL and MULTI-BEAM XLE products in this section are RoHS compliant



The MULTI-BEAM XL and MULTI-BEAM XLE modules are a blind-mateable board-to-board power distribution connector system. With a variety of available power contacts and a modular design, customers are able to customize this connector to their exact needs. In addition to selecting the number of power and signal contacts, customers are also able to choose the mating sequence of contacts they need for their specific application.

MULTI-BEAM XL connectors feature dual-beam and four-beam power contacts,

rated at 35A. The new MULTI-BEAM connector features a true hot-plug designed three-beam contact, rated at 43A.

The product is also available in versions complying with the Server Systems Infrastructure (SSI) Standard. MULTI-BEAM XL and MULTI-BEAM XLE products offer high reliability and high current density in a package designed specifically for modular hot-swappable power distribution systems. They are ideal for blind-mating in modular and rack mounted systems. The high perform-

ance design and heavy gold plated contacts meet requirements across many applications including power distribution for compact (1U) computer servers through high-end servers, fault-tolerant computers, networking equipment, telecommunication switches, medical instrumentation, and industrial control equipment.

The compact design also meets the I/O standard of modern modular and hot-swappable redundant (N+1) power supplies and uninterruptible power supplies.

### Technical Documents

#### Product Specification

108-1973

#### Application Specification

114-13038



File # E28476



File # LR7189

### For More Information

Check out product information at:  
<http://mbxl.te.com>

Technical Support Center  
 1-800-522-6752

## MULTI-BEAM XL and MULTI-BEAM XLE Power Distribution Connector Systems (Continued)

### MULTI-BEAM XL Connector

- Expandable length to accommodate up to 36 power contacts
- Contact spacings are expandable to accommodate higher voltages and/or higher current requirements
- 4-beam or dual beam power contacts available
- Base metal made from high conductivity copper alloy (over 98% copper) offers superior performance compared to alternative materials

### MULTI-BEAM XLE Connector

- Features new 3-beam power contact
- Two hot-pluggable power contacts to choose from:
  - 50A High power contact (35% increase compared to MULTI-BEAM XL connector)
  - 20A Low power contact (occupies 50% less PCB space than MULTI-BEAM XL power contact)
- Slimmer housing design allows 40% more current in the same space
- Over 40% lower mating force than original MULTI-BEAM XL connector
- Vented housing allows for better air flow

### Evolution of MULTI-BEAM Power Contacts



#### Dual-Beam Contact

- Original design
- .017" thick stock



#### 4-Beam Contact


- .017" thick stock
- 35A current rating
- Features eight independent beams
- Parallel current paths yield a lower contact resistance
- Tuned beam design provides lower mating forces and higher durability life cycles




#### 3-Beam Contact

- Offered on new MULTI-BEAM XLE connector
- .020" Thick Stock
- 50A Current Rating
- Improved design offers lowest mating force available in MULTI-BEAM product line
- True hot-plug design preserves the separable contact interface to provide long term reliability after hot-mate and un-mate cycles

### Power Contacts



### Signal Contacts



### Contact Wipe

| Contact Type             | Description                  | Sequence | Minimum Wipe     |
|--------------------------|------------------------------|----------|------------------|
| Power (or GND) Contact   | Make First Break Last (MFBL) | 1        | 0.200" [5.08 mm] |
| Power Contact            | Standard                     | 2        | 0.150" [3.81 mm] |
| Signal Contact           | Standard                     | 2        | 0.150" [3.81 mm] |
| Signal (trigger) Contact | Make Last Break First (MLBF) | 3        | 0.100" [2.54 mm] |

The MLBF power contact and the Standard Signal contact are sequenced to mate at the same time ... sequence #2.

### Product Configurations and Part Numbers

The connector configuration is described by reading Left-to-Right on the Plug mating interface and Right-to-Left on the Receptacle mating interface. Custom configurations can be produced due to the modular design of the product.

**Configuration Description:** ACP indicates AC Power, P indicates DC Power, HDP indicates High Density Power, LP indicates Low Power (MULTI-BEAM XLE connector only), S indicates Signal. The corresponding contact spacing and voltage ratings are shown below.

| ACP                      | P                        | HDP                         | LP                      | S                     |
|--------------------------|--------------------------|-----------------------------|-------------------------|-----------------------|
| 0.300" [7.62 mm] spacing | 0.250" [6.35 mm] spacing | 0.200" [5.08 mm] spacing    | .115" [3.81 mm] spacing | 0.100" [2.54 mm] grid |
| 300 Volts*               | 200 Volts*               | Connection to same voltage* | 200 Volts*              | 60 Volts*             |

\* With circuit board designed to UL 1950, IEC 60950

## MULTI-BEAM XL Power Distribution Connector Systems

### Board-Mount Connectors

#### Right-Angle Receptacles



| Configuration * | Part Number | Application                   | Overall Length " and [mm] | PCB Tail Type (Solder, Press-Fit) | Power Contact Sequencing |
|-----------------|-------------|-------------------------------|---------------------------|-----------------------------------|--------------------------|
| 1P/24S/1P       | 6450160-3   | SSI "DPS"                     | 1.925" [48.90 mm]         | Solder                            | No                       |
| 2P/24S/2P       | 1-6450160-0 | Distributed DC Power + Signal | 2.250" [57.15 mm]         | Solder                            | No                       |
| 3P/24S/3P       | 6450570-2   | Distributed DC Power + Signal | 2.750" [69.85 mm]         | Press-fit                         | Yes                      |
| 3ACP/24S/6P     | 6450170-8   | AC and DC Power + Signal      | 3.650" [92.71 mm]         | Solder                            | Yes                      |
| 5P/24S/6P       | 6450160-5   | SSI "MPS"                     | 4.350" [110.49 mm]        | Solder                            | No                       |
| 7P/32S/7P       | 6450560-4   | Distributed DC Power + Signal | 4.350" [110.49 mm]        | Press-fit                         | No                       |
| 8P/28S          | 6450172-2   | Distributed DC Power + Signal | 3.350" [85.09 mm]         | Solder                            | Yes                      |
| 8P/32S/8P       | 6450160-1   | AC and DC Power + Signal      | 5.450" [138.43 mm]        | Solder                            | No                       |
| 3ACP            | 6450173-1   | AC Power                      | 1.550" [39.37 mm]         | Solder                            | Yes                      |
| 8P              | 6450163-2   | DC Power                      | 2.650" [67.31 mm]         | Solder                            | No                       |
| 14P/32S         | 6450172-1   | Distributed DC Power + Signal | 4.950" [125.73 mm]        | Solder                            | Yes                      |
| 16S/4P          | 6450161-1   | Distributed DC Power + Signal | 2.050" [52.07 mm]         | Solder                            | No                       |
| 24S/6P          | 6450161-2   | Distributed DC Power + Signal | 2.750" [69.85 mm]         | Solder                            | No                       |
| 24S/8P          | 6450161-6   | Distributed DC Power + Signal | 3.250" [82.55 mm]         | Solder                            | No                       |

\* Custom configurations are available — see page 29 for instructions to have TE build your custom part.

#### Vertical Receptacles



| Configuration * | Part Number | Application                   | Overall Length " and [mm] | PCB Tail Type (Solder, Press-Fit) | Power Contact Sequencing |
|-----------------|-------------|-------------------------------|---------------------------|-----------------------------------|--------------------------|
| 1P/24S/1P       | 6450540-1   | SSI "DPS"                     | 1.925" [48.90 mm]         | Press-fit                         | No                       |
| 2P/24S/2P       | 6450140-5   | Distributed DC Power + Signal | 2.250" [57.15 mm]         | Solder                            | No                       |
| 3P/24S/3P       | 1-6450140-0 | Distributed DC Power + Signal | 2.750" [69.85 mm]         | Solder                            | No                       |
| 4P/24S/4P       | 6450150-6   | Distributed DC Power + Signal | 3.350" [85.09 mm]         | Solder                            | Yes                      |
| 4P/24S/3ACP     | 6450150-3   | AC and DC Power + Signal      | 3.150" [80.01 mm]         | Solder                            | Yes                      |
| 5P/24S/6P       | 6450540-2   | SSI "DPS"                     | 4.350" [110.49 mm]        | Press-fit                         | No                       |
| 6P/24S/6P       | 4-6450550-5 | Distributed DC Power + Signal | 4.250" [107.95 mm]        | Press-fit                         | No                       |
| 10P/24S/12P     | 3-6450550-2 | Distributed DC Power + Signal | 5.800" [147.32 mm]        | Press-fit                         | Yes                      |
| 3P              | 6450543-1   | DC Power                      | 1.400" [35.56 mm]         | Press-fit                         | No                       |
| 3ACP            | 6450543-6   | AC Power                      | 1.550" [39.37 mm]         | Press-fit                         | No                       |
| 4P              | 6450543-5   | DC Power                      | 1.650" [41.91 mm]         | Press-fit                         | No                       |
| 6P              | 6450553-2   | DC Power                      | 2.050" [52.07 mm]         | Press-fit                         | Yes                      |
| 7P              | 6450543-3   | DC Power                      | 2.400" [60.96 mm]         | Press-fit                         | No                       |
| 8P/28S          | 6450142-3   | Distributed DC Power + Signal | 3.350" [85.09 mm]         | Solder                            | No                       |
| 14P/32S         | 6450152-1   | Distributed DC Power + Signal | 4.950" [125.73 mm]        | Solder                            | Yes                      |
| 24S/6P          | 6450551-1   | Distributed DC Power + Signal | 2.750" [69.85 mm]         | Press-fit                         | Yes                      |
| 24S/3ACP        | 6450151-3   | Distributed DC Power + Signal | 2.200" [55.88 mm]         | Solder                            | Yes                      |
| 24S/8P          | 6450541-5   | Distributed DC Power + Signal | 3.250" [82.55 mm]         | Press-fit                         | No                       |

\* Custom configurations are available — see page 29 for instructions to have TE build your custom part.

**Note:** All part numbers are RoHS compliant.

## MULTI-BEAM XL Power Distribution Connector Systems (Continued)

### Board-Mount Connectors

#### Right-Angle Plugs



| Configuration * | Part Number | Application                   | Overall Length " and [mm] | PCB Tail Type (Solder, Press-Fit) | Signal Contact Sequencing |
|-----------------|-------------|-------------------------------|---------------------------|-----------------------------------|---------------------------|
| 1P/24S/1P       | 6450330-1   | SSI "DPS"                     | 1.925" [48.90 mm]         | Solder                            | Yes                       |
| 2P/24S/2P       | 6450120-2   | Distributed DC Power + Signal | 2.250" [57.15 mm]         | Solder                            | No                        |
| 3P/24S/3P       | 6450130-6   | Distributed DC Power + Signal | 2.750" [69.85 mm]         | Solder                            | Yes                       |
| 4P/24S/3ACP     | 6450130-4   | AC and DC Power + Signal      | 3.150" [80.01 mm]         | Solder                            | Yes                       |
| 3ACP/24S/6P     | 1-6450130-4 | AC and DC Power + Signal      | 3.650" [92.71 mm]         | Solder                            | Yes                       |
| 5P/24S/6P       | 6450230-1   | SSI "DPS"                     | 4.350" [110.49 mm]        | Solder                            | Yes                       |
| 5P/32S/5P       | 2-6450120-4 | Distributed DC Power + Signal | 3.950" [100.33 mm]        | Solder                            | No                        |
| 6P/24S/6P       | 2-6450120-7 | Distributed DC Power + Signal | 4.250" [107.95 mm]        | Solder                            | No                        |
| 8P/32S/8P       | 6450120-1   | Distributed DC Power + Signal | 5.450" [138.43 mm]        | Solder                            | No                        |
| 10P/24S/12P     | 4-6450130-6 | Distributed DC Power + Signal | 5.800" [147.32 mm]        | Solder                            | Yes                       |
| 16S/4P          | 6450231-1   | Distributed DC Power + Signal | 2.050" [52.07 mm]         | Solder                            | Yes                       |
| 24S/6P          | 6450131-7   | Distributed DC Power + Signal | 2.750" [69.85 mm]         | Solder                            | Yes                       |
| 24S/3ACP        | 6450121-3   | Distributed DC Power + Signal | 2.200" [55.88 mm]         | Solder                            | No                        |
| 3ACP            | 6450123-3   | AC Power                      | 1.550" [39.37 mm]         | Solder                            | N/A                       |
| 3P              | 6450123-1   | DC Power                      | 1.400" [35.56 mm]         | Solder                            | N/A                       |
| 4P              | 6450123-2   | DC Power                      | 1.650" [41.91 mm]         | Solder                            | N/A                       |
| 6P              | 6450523-2   | DC Power                      | 2.050" [52.07 mm]         | Press-fit                         | N/A                       |
| 7P              | 6450123-5   | DC Power                      | 2.400" [60.96 mm]         | Solder                            | N/A                       |
| 8P/28S          | 6450132-3   | Distributed DC Power + Signal | 3.350" [85.09 mm]         | Solder                            | Yes                       |
| 14P/32S         | 6450132-4   | Distributed DC Power + Signal | 4.950" [125.73 mm]        | Solder                            | Yes                       |

\* Custom configurations are available — see page 29 for instructions to have TE build your custom part.

#### Vertical Plugs



| Configuration * | Part Number | Application                   | Overall Length " and [mm] | PCB Tail Type (Solder, Press-Fit) | Signal Contact Sequencing |
|-----------------|-------------|-------------------------------|---------------------------|-----------------------------------|---------------------------|
| 1P/16S/1P       | 6600333-9   | Distributed DC Power + Signal | 1.650" [41.91 mm]         | Press-fit                         | Yes                       |
| 1P/24S/1P       | 6600330-4   | SSI "DPS"                     | 1.925" [48.90 mm]         | Solder                            | Yes                       |
| 2P/16S/2P       | 1-6600333-0 | Distributed DC Power + Signal | 2.150" [54.61 mm]         | Press-fit                         | Yes                       |
| 2P/24S/2P       | 1-6600333-2 | Distributed DC Power + Signal | 2.250" [57.15 mm]         | Press-fit                         | Yes                       |
| 3P/16S/3P       | 6600333-7   | Distributed DC Power + Signal | 2.650" [67.31 mm]         | Press-fit                         | Yes                       |
| 3ACP/24S/3ACP   | 1-6600333-1 | AC Power + Signal             | 3.150" [80.01 mm]         | Press-fit                         | No                        |
| 4P/24S/4P       | 6600333-6   | Distributed DC Power + Signal | 3.350" [85.09 mm]         | Press-fit                         | Yes                       |
| 5ACP/24S/5ACP   | 6600333-1   | Distributed DC Power + Signal | 4.350" [110.49 mm]        | Press-fit                         | Yes                       |
| 7P/32S/7P       | 6600330-5   | Distributed DC Power + Signal | 4.350" [110.49 mm]        | Solder                            | No                        |
| 24S/8P          | 6600323-2   | Distributed DC Power + Signal | 3.250" [82.55 mm]         | Press-fit                         | No                        |
| 3ACP            | 6450503-3   | AC Power                      | 1.550" [39.37 mm]         | Press-fit                         | N/A                       |
| 8P              | 6600303-1   | DC Power                      | 2.650" [67.31 mm]         | Press-fit                         | N/A                       |

\* Custom configurations are available — see page 29 for instructions to have TE build your custom part.

**Note:** All part numbers are RoHS compliant.

## MULTI-BEAM XL Power Distribution Connector Systems (Continued)

### Board-Mount Connectors

#### Specifications

##### Materials

**Housing** — High temperature thermoplastic, UL 94V-0

**Power Contacts** — High conductivity Copper alloy

**Signal Contacts** — Copper alloy

**Boardlocks** — Phosphor bronze

##### Finish

**Power and Signal Contacts** — 30 microinches [76 micrometers] min. gold over 50 microinches [1.27 micrometers] min. nickel on mating surfaces, 100 microinches [2.54 micrometers] min. tin over 50 microinches [1.27 micrometers] min. nickel at PCB terminations

**Note:** Tin-lead plating also available on press-fit connectors

#### Performance Specifications

Up to 55 Amps per power contact, de-rated to 35 Amps in equally energized (8 adjacent positions) connector.

Up to 4 Amps per signal contact, de-rated to 1.5 Amps in equally energized 24-position pin field.


**Maximum Continuous Operating Temperature** — 105°C.

**Contact Resistance** — 0.7 milli-ohm


**Durability** — 250 cycle

**Radial Mis-alignment Capability** — ± 0.075" [1.91 mm]


Minimum of 0.100" [2.45 mm] of contact wipe on shortest signal contact



#### Performance @ 30 Amps per Contact



See Cable Connectors on Pages 19-28



## “NEW” MULTI-BEAM XLE Connectors

# NEW

### Product Facts

- Two NEW hot-pluggable power contacts to choose from:
  - 50 Amp high power contact
  - 20 Amp low power contact
- Over 35% lower mating force than original MULTI-BEAM XL connectors
- Over 40% more current in the same over all PCB space
- Low-wear contact design passes Telcordia environmental exposure requirements
- New design allows more angular mis-alignment

TE's new MULTI-BEAM XLE connectors are the latest addition to the MULTI-BEAM XL power connector product family. MULTI-BEAM XLE connectors feature a new 3-beam contact, made from a thicker/higher conductivity material than the original single beam or 4-beam designs.

The new 3-beam design allows for a greater angular mis-alignment between mating connectors and offers a lower mating force. In addition, MULTIBEAM XLE connectors offer a slimmer

housing design that reduces the overall PCB footprint and has the option of using a low power contact — the industry proven Universal Power Module (UPM) contact.

The new contacts and housing design allows more power in the same footprint — over 35% more current in the same space. MULTI-BEAM XLE connectors are as modular as the original MULTI-BEAM XL connectors in that they can be designed to fit specific customer needs.

### Applications

- Modular Hot-Swappable Power Supplies
- 1U / 2U Servers
- High-end Computer & Telecommunications

### Equipment

- Power Distribution Circuit Boards
- Power Distribution Cable Assemblies



## “NEW” MULTI-BEAM XLE Connectors (Continued)

### Specifications

#### Materials

**Housing** — High temperature thermo-plastic, UL 94V-0

**Power Contacts** — High conductivity Copper alloy


**Signal Contacts** — Copper alloy

**Boardlocks** — Phosphor bronze


#### Finish

**Power and Signal Contacts** — 30 microinches [.76 micrometers] min. gold over 50 microinches [1.27 micrometers] min. nickel on mating surfaces, 100 microinches [2.54 micrometers] min. tin over 50 microinches [1.27 micrometers] min. nickel at PCB terminations

Part Number 6450830-2  
Right-Angle Plug



Part Number 6450880-1  
Right-Angle Receptacle



### MULTI-BEAM XLE Connector Part Numbers

| Available Configurations | Part Numbers      |                |                        | Mating Part Numbers    |                     |
|--------------------------|-------------------|----------------|------------------------|------------------------|---------------------|
|                          | Right-Angle Plugs | Vertical Plugs | Overall Length of Plug | Right-Angle Receptacle | Vertical Receptacle |
| 1P/24S/1P                | 6450840-7         | 6450820-2      | 1.54" [39.12 mm]       | 6450870-5              | 6450850-3           |
| 2LP/8S/2LP               | 6450830-1         | —              | 1.175" [29.84 mm]      | —                      | 6450860-1           |
| 6LP/24S/3P               | 6450830-2         | —              | 2.555" [64.89 mm]      | 6450880-1              | 6450850-2           |
| 2P/32S/2LP               | 6450830-4         | —              | 2.020" [51.30 mm]      | 6450870-1              | —                   |
| 2P/24S/2P                | 6450830-5         | —              | 2.040" [51.81 mm]      | 6450870-3              | —                   |
| 3P/24S/3P                | 6450830-9         | —              | 2.54" [64.52 mm]       | 6450870-4              | —                   |
| 3P/32S/3P                | 6450820-3         | —              | 2.79" [70.87 mm]       | 6450870-8              | —                   |
| 32S/4LP                  | 6450831-1         | —              | 1.750" [44.45 mm]      | 6450871-1              | —                   |
| 6LP/24S/10P              | 1-6450830-0       | —              | 3.86" [97.92 mm]       | —                      | 6450860-5           |
| 12P/48S/8LP              | 6450840-3         | —              | 5.600" [142.24 mm]     | 6450880-4              | 6450860-3           |
| 4ACP/48S/12HDP           | 6450840-4         | 6450810-1      | 5.390" [136.90 mm]     | 6450880-3              | 6450860-2           |

### Electrical

#### Current Carrying Capacity:

- 50 Amp high power contact (over 35% increase compared to MULTI-BEAM XL product)
- 20 Amp low power contact (occupies 50% PCB space than MULTI-BEAM XL power contact)

**Contact resistance:** 0.7 milliohm per contact at rated current

### Configuration Description

| ACP                     | P                       | HDP                     | LP                      | S                       |
|-------------------------|-------------------------|-------------------------|-------------------------|-------------------------|
| .300" [7.62 mm] spacing | .250" [6.35 mm] spacing | .200" [5.08 mm] spacing | .115" [2.92 mm] spacing | .100" [2.54 mm] spacing |
| 300 Volts               | 200 Volts               | 50 Volts                | 200 Volts               | 50 Volts                |

ACP indicates the high power contact on 300 VAC spacing.

P indicates the high power contact on 200 VDC spacing.

LP indicates the low power contact on 200 VDC spacing.

S indicates the signal contact on 60 VDC spacing.

### Application Tooling

#### Right-Angle Plugs:

Flat-rock seating tools (no unique tools required)

#### Right-Angle Receptacles:

Flat-rock seating tools (no unique tools required)

#### Vertical Plugs:

Contact TE for required seating tools

#### Vertical Receptacles:

Flat-rock seating tools (no unique tools required)

**Note:** All part numbers are RoHS compliant.

## MULTI-BEAM XL Current Pass-Thru Power Distribution Connector System

### Product Facts

- Combines PCB and cable mounted contacts
- Ideal for separating AC input from DC input
- Eliminates FASTON tab interface at the back of the connector housing
- Requires less space than two housing designs
- Terminates 12 AWG and 10 AWG wire
- Mates with TE vertical and right-angle PCB plugs
- High strength housing materials
- RoHS Compliant

### Technical Documents

#### Product Specification

108-1973 and 108-2157

#### Application Specification

114-13038



The Cable Pass-Thru MULTI-BEAM XL receptacles securely terminate up to a 10 AWG wire directly into MULTI-BEAM XL PCB mounted receptacles. The design includes a “terminal position assurance” (TPA) feature that confirms the manually inserted wires are fully seated. The product offers a unique way of using the MULTI-BEAM XL PCB receptacles as a sort of “docking” connector. A single docking connector is far easier to mate to and to design around in a blind-mate application, than multiple power and signal connectors. By separating

some circuits to be cable terminated and some to be PCB terminated it allows both high voltage (AC) and low voltage (DC) power to pass through the same connector.

This separation of the AC and DC power eliminates the concerns of high voltage power running through circuit boards better suited to carry only low voltage circuitry. Additional applications may include designs where the power is better routed directly to a different PCB, through cables, yet passes through a single docking connector for ease in system design.

The Cable Pass-Thru connector is offered in both right-angle or vertical PCB-mount orientations and is supplied with either press-fit or solder pc tails. The connector is mate-able to either PCB mounted or cable mounted MULTI-BEAM XL or MULTI-BEAM XLE plugs.

All MULTI-BEAM XL cable connectors are supplied pre-assembled by TE.


## MULTI-BEAM XL Current Pass-Thru Power Distribution Connector System (Continued)

| Available Configurations | Part Numbers                      |                          |                                |                       |
|--------------------------|-----------------------------------|--------------------------|--------------------------------|-----------------------|
|                          | Pass-Thru Right-Angle Receptacles | Mating Right-Angle Plugs | Pass-Thru Vertical Receptacles | Mating Vertical Plugs |
| 3CP/1P/24S/2P            | 6450178-1                         | 6450130-2                | —                              | —                     |
| 3CP/24S/2P               | 6450178-2                         | 2-6450130-6              | —                              | —                     |
| 3CP/24S/3ACP             | 1888179-1                         | 2-6450330-6              | —                              | —                     |
| 3CP/4P/24S               | 6450578-1                         | 1-6450132-3              | 6450558-1                      | 6600310-5             |
| 3ACP/24S/6P              | —                                 | 1-6450130-4              | 6450558-2                      | —                     |
| 3CP/8P/12S               | 1888132-1                         | —                        | —                              | —                     |
| 3CP/20S/10P              | 6450578-2                         | 6-6450130-2              | —                              | —                     |
| 3CP/16S                  | 6450668-1                         | 6450622-1                | —                              | —                     |

**Note:** Receptacles are the only MULTI-BEAM XL parts with Pass-Thru capability.

### Configuration Description

| CP                           | ACP                        | P                          | HDP                        | S                       |
|------------------------------|----------------------------|----------------------------|----------------------------|-------------------------|
| AC Power                     | AC Power                   | DC Power                   | High Density Power         | Signal                  |
| Cable Power<br>.300" spacing | PCB-Mount<br>.300" spacing | PCB-Mount<br>.250" spacing | PCB-Mount<br>.200" spacing | PCB-Mount<br>.100" grid |



### MULTI-BEAM XL Coax Pass-Thru Connector — Combine power, coax and signal all in one connector

| Right-Angle Plug | Cable Receptacle |
|------------------|------------------|
| 292495-1         | 292491-1         |

The following coax contacts may be used with the coax pass-thru housings:

| Pin Contact | Socket Contact |
|-------------|----------------|
| 5221980-5   | 5221981-5      |


**Note:** All part numbers are RoHS compliant.

## MULTI-BEAM XL Power Distribution Connector System Cable Receptacle Assemblies

### Cable Receptacle Assemblies

#### Product Facts

- Single one-piece housing design
- Terminal Position Assurance (TPA) Secondary Locks on contacts help prevent contact back-out
- Pre-assembled made-to-order cable assemblies
- Installation to panel provides float in X, Y and Z directions
- Insulation crimp on all contacts
- 30 microinch (.76 micrometers) gold plated contacts for high reliability
- Touch-safe design passes UL1977 and IEC 60950 finger probe test
- AC and DC power in the same connector — meets UL & IEC safety requirements
- All MULTI-BEAM XL products in this section are RoHS compliant



MULTI-BEAM XL Cable Assemblies allow designers freedom to connect power supplies and power distribution subassemblies in a wide variety of applications. Expanding beyond board-to-board applications the cable assemblies are available for both cable-to-board or panel-mount applications and can terminate 8-16 AWG and 22-26 AWG wires all in one connector, without using adapter circuit boards. In addition, the power contacts are designed to be able to accept two-wire terminations which can further reduce harness complexity by reducing or eliminating mid-wire splices.

The use of high temperature glass filled housing retention and high conductivity contact materials allows the use of this connector in very high current density applications. The features work together to result in a highly durable and compact power connector, which offers industry leading minimum millivolt drop through the connection. The connector was designed to pass the UL 1977 and IEC 60950 finger probe test which makes the connector touch-safe. The insulation crimp adds further safety by keeping the insulation from being pulled away from the termination point.

These features eliminate the need for a secondary cable clamp which often can be size prohibitive.

The cable connectors are designed to mate to the de-facto standard TE MULTI-BEAM XL right-angle or vertical PCB plugs. The combination of PCB and cable connections, both with mixed power and signal arrangements provides a universal power distribution connector systems.

The cable assemblies are all RoHS compliant, designed to specific customer requirements and manufactured in TE's cable assembly manufacturing facilities.

#### Technical Documents

Product Specification  
108-2157

Application Specification  
114-13112

#### For More Information

Internet <http://te.com>

Check out product information at: <http://mbxl.te.com>

Technical Support Center 1-800-522-6752


## MULTI-BEAM XL Power Distribution Connector System

### Cable Receptacle Assemblies (Continued)

#### Configurations/Applications


##### Floating XYZ Panel-Mount Receptacle

- 0.060" [1.52] Nominal float in X, Y and Z direction
- For modular installation of large power distribution systems
- Single connector replaces multiple power and signal connectors




##### Slide-to-Lock Receptacle

- 0.030" [0.76] nominal float in X and Y direction
- Ideal for modular installation of smaller systems requiring less space and less float — such as fan trays
- Replaces connectors which use multiple low power contacts to carry the total current
- Power only or Power Plus signal mixed



##### Cable-to-Board Receptacle

- Easy to mate/disconnect with squeeze-to-release latches
- Mates to right-angle or vertical MULTI-BEAM XL STR plugs
- Replaces two traditional connectors (1 signal and 1 power) with just 1 connector



## MULTI-BEAM XL Power Distribution Connector System


### Cable Receptacle Assemblies (Continued)

#### Panel-Mount Receptacles


##### Product Facts

- High strength glass-filled housing materials
- Expandable/modular housing design
- PMT Series floats  $\pm 0.060"$  [1.52] in X, Y and Z directions
- STL series floats 0.030" [0.76] in X and Y directions
- Mounting Hardware Kits:  
Part Number 1600914-1 — Standard  
Part Number 1600914-3 — High Force

Part numbers shown identify the main receptacle connector housing. Additional components (contacts, contact locks, etc.) are used to complete the cable assembly. See page 23 for contacts, secondary locks and application equipment information.




X, Y, Z Floating Receptacle




Slide-to-Lock Receptacle

#### Power and Signal Module Specifications

| Power Module Widths:      | Module Designation | Maximum Wire Size<br>AWG [mm <sup>2</sup> ] | Max. Insulation Dia.<br>inches [mm] |
|---------------------------|--------------------|---------------------------------------------|-------------------------------------|
| 0.300 [7.62] (ACP)        | 300 (ACP)          | 8 [10.5]                                    | 0.272 [6.91]                        |
| 0.250 [6.35] (P)          | 250 (P)            | 10 [6.6]                                    | 0.215 [5.46]                        |
| 0.200 [5.08] (HDP)        | 200 (HDP)          | 12 [2.6]                                    | 0.156 [3.96]                        |
| Signal Module Width       | Module Designation | Wire Range<br>AWG [mm <sup>2</sup> ]        | Insulation Range<br>inches [mm]     |
| 0.200 [5.08] (8 Contacts) | Signals            | 22-26 [0.14-0.32]                           | 0.036-0.054 [0.91-1.37]             |



Power Module



Signal Module

#### Configurations/Part Numbers

| Available Configurations | Part Numbers |            |                  |             |
|--------------------------|--------------|------------|------------------|-------------|
|                          | XYZ Series   | STL Series | Mating PCB Plugs |             |
|                          |              |            | Vertical         | Right-Angle |
| 3ACP                     | 1600606-2    | 292499-1   | 6600303-7        | 6450123-3   |
| 4P                       | —            | 292499-4   | 6600303-2        | 6450123-2   |
| 4ACP                     | —            | 292499-3   | 6600303-3        | —           |
| 5P                       | 1600606-1    | 1761419-2  | —                | 6450123-6   |
| 6P                       | —            | 292499-8   | 6600303-6        | —           |
| 1P/16S/1P                | 1-1600636-3  | 1761819-4  | 6600333-9        | —           |
| 1P/24S/1P                | 1600636-9    | —          | 6600330-4        | 6450330-1   |
| 2P/16S/2P                | 1-1600636-0  | —          | 1-6600333-0      | —           |
| 2P/24S/2P                | 1600636-2    | 1761819-2  | 6600333-5        | 1-6450330-4 |
| 3P/16S/3P                | 1600636-8    | —          | 6600333-7        | —           |
| 3ACP/24S/3ACP            | 1-1600636-4  | —          | 1-6600333-1      | —           |
| 4P/24S/4P                | 1-1600636-5  | —          | 6600333-6        | —           |
| 4ACP/24S/12P             | 1600636-6    | —          | —                | 2-6450120-6 |
| 5ACP/24S/5ACP            | 1600636-1    | —          | 6600333-1        | 5-6450130-0 |
| 7P/48S/7P                | 1-1600636-6  | —          | —                | 3-6450120-4 |

**Note:** All part numbers are RoHS compliant.


## MULTI-BEAM XL Power Distribution Connector System

### Cable Receptacle Assemblies (Continued)

#### Cable-to-Board Squeeze-to-Release Receptacles

##### Product Facts

- High strength glass-filled housing
- Pre-installed squeeze-to-release latches
- Expandable/modular housing design
- Mates to TE vertical or right-angle PCB plugs




STR Series


#### Power and Signal Module Specifications

| Power Module Widths:      | Module Designation | Maximum Wire Size<br>AWG [mm <sup>2</sup> ] | Max. Insulation Dia.<br>inches [mm] |
|---------------------------|--------------------|---------------------------------------------|-------------------------------------|
| 0.300 [7.62] (ACP)        | 300 (ACP)          | 8 [10.5]                                    | .272 [6.91]                         |
| 0.250 [6.35] (P)          | 250 (P)            | 10 [6.6]                                    | .215 [5.46]                         |
| 0.200 [5.08] (HDP)        | 200 (HDP)          | 12 [2.6]                                    | .156 [3.96]                         |
| Signal Module Width       | Module Designation | Wire Range<br>AWG [mm <sup>2</sup> ]        | Insulation Range<br>inches [mm]     |
| 0.200 [5.08] (8 Contacts) | Signals            | 22-26 [0.14-0.32]                           | .036-.054 [0.91-1.37]               |

See page 23 for contacts, secondary locks and application equipment information.



Power Module



Signal Module

#### Configurations/Part Numbers

| Available Configurations | STR Series  | Part Numbers |             |
|--------------------------|-------------|--------------|-------------|
|                          |             | Vertical     | Right-Angle |
| 2ACP                     | 1600798-2   | 6600393-1    | 6450129-1   |
| 3P                       | 1600798-3   | 6600393-2    | 6450129-2   |
| 3ACP                     | 1600798-5   | —            | —           |
| 4P                       | 1600798-4   | 6600390-1    | 6450129-3   |
| 6P                       | 1600798-1   | 6600393-3    | 6450129-5   |
| 1P/24S/1P                | 1600788-8   | 6600380-2    | 6450128-1   |
| 2P/8S/2P                 | 1-1600788-3 | —            | 6450128-6   |
| 2P/16S/2P                | 1-1600788-0 | 6600383-5    | —           |
| 2P/24S/2P                | 1600788-1   | 6600383-3    | 6450128-2   |
| 3ACP/24S/3ACP            | 1-1600788-2 | 6600383-6    | —           |
| 4P/24S/4P                | 1-1600788-4 | 6600383-7    | 6450128-5   |
| 4ACP/24S/4ACP            | 1-1600788-5 | 6600383-9    | —           |
| 6P/24S/6P                | 1-1600788-7 | —            | 6450128-8   |
| 6P/32S/6P                | 1600788-7   | 6600383-1    | —           |

**Note:** All part numbers are RoHS compliant.

## MULTI-BEAM XL Power Distribution Connector System

### Cable Receptacle Assemblies (Continued)

#### Cable Receptacle Components

##### Material and Finish

**Body** — 50 micro inches nickel over high conductivity copper alloy

**Mating Area** — 30 micro inches gold


#### Technical Documents

##### Product Specification

108-2157-1

##### Application Specification

114-13164



Power Contact

#### Power Contacts



| Wire Size Range<br>AWG | Insulation<br>Diameter   | Housing<br>Width               | Part Number                            | Applicator Tool | Hand Tool |
|------------------------|--------------------------|--------------------------------|----------------------------------------|-----------------|-----------|
| 12                     | .156 Max.<br>[3.96]      | .200 or .250<br>[5.08 or 6.35] | 1-1600961-7<br>(make-first-break-last) | 1385635-3       | 2063500-1 |
|                        | .156-.176<br>[3.96-4.47] | .250<br>[6.35]                 |                                        | 1385636-3       |           |
| 14                     | .120-.156<br>[3.05-3.96] | .200 or .250<br>[5.08 or 6.35] | 1-1600961-8<br>(Standard)              | 1385635-3       | 2063500-1 |
|                        | .090 Max.<br>[2.29]      | .250<br>[6.35]                 |                                        | 1385636-3       |           |
| 2 @ 16                 | .090 Max.<br>[2.29]      | .250<br>[6.35]                 |                                        | 1385636-3       |           |

| Wire Size Range<br>AWG | Insulation<br>Diameter   | Housing<br>Width               | Part Number                            | Applicator Tool | Hand Tool |
|------------------------|--------------------------|--------------------------------|----------------------------------------|-----------------|-----------|
| 8                      | .215-.272<br>[5.46-6.91] | .300<br>[7.62]                 | 1-1600960-7<br>(make-first-break-last) | 1385637-3       | N/A       |
| 10                     | .176-.215<br>[4.47-5.46] | .200 or .300<br>[6.35 or 7.62] |                                        | 1385638-3       |           |
| 2 @ 12                 | .130<br>[3.30] Max.      | .300<br>[7.62]                 | 1-1600960-8<br>(Standard)              | 1385637-3       |           |
| 2 @ 14                 | .137<br>[3.48] Max.      | .300<br>[7.62]                 |                                        | 1385637-3       |           |

Extraction Tool: Part Number 2063080-1

**Note:** Check the customer drawing for the applicable MULTI-BEAM XL housing to confirm the quantity of standard or make-first-break-last contacts needed. Standard and make-first-break-last contacts cannot be interchanged within the housing.



Secondary Power Locks:  
Part Number 1600903-1

**Note:** One secondary lock needed for each power contact.



SDA SA Hand Tool  
Part Number 2063500-1

**Note:** All part numbers are RoHS compliant.


## MULTI-BEAM XL Power Distribution Connector System

### Cable Receptacle Assemblies (Continued)

#### Cable Receptacle Components (Continued)

##### Material and Finish


**Contact** — Phosphor bronze plated gold over nickel in mating area



Insulation Barrel

Wire Barrel


Locking Lance



#### Signal Contacts

| Wire Size Range<br>AWG | Insulation<br>Diameter   | Version       | Part Number      | Extraction Tool | Hand Tool | Applicator |
|------------------------|--------------------------|---------------|------------------|-----------------|-----------|------------|
| 22-26                  | .036-.054<br>[0.91-1.37] | Low Pressure  | 5531216-5 (reel) | 91156-2         | 91531-1   | 1426685-2  |
|                        | .036-.054<br>[0.91-1.37] | High Pressure | 5531224-6 (reel) |                 |           |            |

#### Secondary Locks



**Note:** One secondary lock needed for each column of signal contacts



Secondary Signal Locks:  
Part Number 1600902-1



Panel Mount  
Alignment Key



Float-Mount Hardware Kit  
Part Number 1600914-1

(Standard Force)

Part Number 1600914-3  
(High Force)

1 Kit / Cable Assembly;  
Kit includes 2 screws, 2 washers  
and 2 springs

**Note:** Kit not needed for STR or STL housings



CERTI-CRIMP Hand Tool  
Part Number 91531-1

**Note:** All part numbers are RoHS compliant.

## MULTI-BEAM XL Power Distribution Connector System Cable Receptacle Assemblies (Continued)

### Specifications


#### Product Specifications

**Power Contacts** —  
50 Amps on single 8 AWG wire

**Signal Contacts** —  
5 Amps on single 22 AWG wire  
0.050" [1.27] minimum float in X,  
Y and Z direction


**Sequenced Mating** —  
3 Levels Pwr/Grnd, Pwr & Signal,  
Signal 250 Cycle Durability

### Installed Connector Illustration



XYZ Series

STL Series




STR Series

Additional temperature-rise data available, contact TE Product Engineering.

Current/temperature rise data shown — from End-Of-Life qualification test.

#### MULTI-BEAM XL Product T-Rise Data



For more information see the product website @ <http://mbxl.te.com>

## MULTI-BEAM XL Power Distribution Connector System Cable Plug Assemblies

### Cable Plug Assemblies

#### Product Facts

- High strength housing materials
- Hot-Pluggable
- Installation provides float in X, Y and Z directions
- Sequenced mating
- RoHS complaint
- Modular mold design provides configuration flexibility
- Integral cable clamp supports contacts and provides strain relief in minimum amount of space
- 30 microinch (0.76 micrometers) gold plated contacts for high reliability
- Sold only as part of a pre-assembled cable assembly



The newest addition to the MULTI-BEAM XL cable assemblies are the cable mounted plugs. Produced with modular molds, the connectors can be made in a wide variety of sizes. The PCB mounted MULTI-BEAM XL plugs are typically rigidly mounted to hot-swappable power supplies and the systems they connect with. The "float blind-mate drawer connector" design of the MULTI-BEAM XL cable connectors helps eliminate the concern of an inadequately aligned chassis. The connector can accept mating parts misaligned by as much as 3 mm ( $\pm 1.5$  mm), and still mate

without applying stress to solder or complaint pin terminations. The MULTI-BEAM cable plugs can terminate 8-14 AWG and 22-26 AWG wires all in one connector, without using adapter circuit boards. The use of high temperature glass filled housing materials, redundant contact retention and high conductivity contact materials allows the use of this connector in very high density applications.

The cable assemblies are all RoHS compliant designed to specific customer requirements and manufactured in TE's internal cable assembly manufacturing facilities.

#### Technical Documents

##### Product Specification

108-2157-1

##### Application Specification

114-13164

#### For More Information

##### Internet

<http://te.com>

##### Check out product

information at:

<http://mbxl.te.com>


##### Technical Support Center

1-800-522-6752


## MULTI-BEAM XL Power Distribution Connector System

### Cable Plug Assemblies (Continued)


#### Configurations/ Part Numbers



PMT



STL



STR

#### Power Module Widths:


0.300" (ACP)  
0.250" (P)  
0.200" (HDP)



| Module Designation | Maximum Wire Size |                 | Max. Insulation Dia. |
|--------------------|-------------------|-----------------|----------------------|
|                    | AWG               | mm <sup>2</sup> |                      |
| 300 (ACP)          | 8                 | 10.5            | .272<br>6.91         |
| 250 (P)            | 10                | 6.6             | .215<br>5.46         |
| 200 (HDP)          | 12                | 2.6             | .156<br>3.96         |

#### Signal Module Width:

0.200" (8 Contacts)



| Module Designation | Maximum Wire Size |                 | Max. Insulation Dia.   |
|--------------------|-------------------|-----------------|------------------------|
|                    | AWG               | mm <sup>2</sup> |                        |
| Signals            | 22-26             | 0.14-0.32       | .036-.054<br>0.91-1.37 |

| Configuration | PMT Series Plug | STL Series Plug | Mating Receptacles* |             | STR Series Plug | Mating Receptacles Vertical |
|---------------|-----------------|-----------------|---------------------|-------------|-----------------|-----------------------------|
|               |                 |                 | Vertical            | Right-Angle |                 |                             |
| 3 ACP         | —               | 1761421-1       | 6450543-6           | 6450173-1   | —               | —                           |
| 4 P           | —               | 1761421-3       | 6450543-5           | —           | 1600814-2       | —                           |
| 1P/16S/1P     | 1600236-5       | 1600820-2       | —                   | 2-6450170-0 | 1600238-4       | 6450740-4                   |
| 1P/24S/1P     | 1600236-4       | 1600820-1       | 6450540-1           | 6450160-3   | 1600238-3       | 6450740-5                   |
| 2P/24S/2P     | 1600236-6       | 1600820-3       | 5-6450540-9         | 2-6450170-1 | 1600238-5       | 6450740-6                   |
| 3ACP/24S/3ACP | 1600236-7       | 1600820-4       | 4-6450550-1         | 2-6450170-2 | 1600238-6       | 6450740-7                   |

PMT Series — Panel-Mount with total 3 mm float in X,Y and Z directions

STL Series — Panel-Mount with total 1.5 mm float in X and Y directions

STR Series — Squeeze-to-Release for removeable Cable-to-Board / I/O Applications

\*Specifications on mating PCB mountable receptacles:

Product Specification 108-2157-1

Application Specification 114-13164

**Note:** All part numbers are RoHS compliant.

## MULTI-BEAM XL Power Distribution Connector System

### Cable Plug Assemblies (Continued)

#### Connector Styles

Intermateable with TE MULTI-BEAM XL PCB mounted receptacles

#### Specifications

**Wire Gauge** — 8 AWG – 14 AWG

**Sequenced Mating** — 3 Levels:  
Pwr/Gnd, Pwr & Signal, Signal

**Current Carrying Capacity** —  
Power Contacts — 45 Amps\* on single  
8 AWG wire  
Signal Contacts — 4 Amps on single 22  
AWG wire

**Durability** — 250 Cycle

**Temperature Range** —  
40°C – 105°C

**Float** — 1.5 mm float in X, Y, and Z  
Direction\*\*

**RoHS Compliant**


**UL, CSA, VDE Approvals Pending**

\*Based on End-of-Design Life  
Qualification Tests

\*\*Mated to TE MULTI-BEAM XL recepta-  
cles only


#### PMT (Panel-Mount) for True X, Y, Z Floating

- Single-piece contact design — eliminates multiple contact interfaces
- Insulation crimp on all contacts
- Installation to panel provides float in X, Y and Z directions




#### STL (Slide-to-Lock) — Most Economical — Still Offering X and Y Floating

- Single-piece contact design — eliminates multiple contact interfaces
- Insulation crimp on all contacts
- Installation to panel provides float in X and Y directions





#### STR (Squeeze-to-Release) — To Connect Sub-assemblies

- Single-piece contact design — eliminates multiple contact interfaces
- Insulation crimp on all contacts
- Easy to mate/disconnect with squeeze-to-release latches




- Offered as pre-assembled, fully tested cable assemblies, as shown below
- Combines multiple power and signal connectors into a single Power I/O Connector

#### MULTI-BEAM XL Cable Plug T-Rise Data\*



## MULTI-BEAM XL and MULTI-BEAM XLE Connectors Custom Configuration Worksheet

### PCB-Mount



### Cable-Mount

XYZ Floating

Slide-to-Lock

### Plugs

XYZ Floating

Squeeze-to-Release

To create a unique configuration for MULTI-BEAM connectors simply complete this worksheet and forward it to your TE sales engineer.

|                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                                   |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------|
| <b>1. Performance Grade</b>            | <input type="checkbox"/> MULTI-BEAM XL Connector                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | <input type="checkbox"/> MULTI-BEAM XLE Connector |
| <b>2. Application</b>                  | <input type="checkbox"/> Board-to-Board                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | <input type="checkbox"/> Cable-to-Board           |
| <b>3. Gender</b>                       | <input type="checkbox"/> Plug (Male)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | <input type="checkbox"/> Receptacle (Female)      |
| <b>4. Orientation</b>                  | Cable Only → <input type="checkbox"/> Blind-Mate specify Floating or Slide-to-Lock Receptacle <input type="checkbox"/> Latching<br>PCB Only → <input type="checkbox"/> Right-Angle <input type="checkbox"/> Vertical                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |                                                   |
| <b>5. Termination</b>                  | (Cable Only) Power <input type="checkbox"/> 8 AWG <input type="checkbox"/> 10 AWG <input type="checkbox"/> 12 AWG <input type="checkbox"/> 14 AWG<br>Signal <input type="checkbox"/> 22 AWG <input type="checkbox"/> 24 AWG <input type="checkbox"/> 26 AWG                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                   |
| <b>6. Termination Style (PCB Only)</b> | <input type="checkbox"/> Solder Tail .135" [3.43 mm] <input type="checkbox"/> Press-Fit .120" [3.05 mm]<br><input type="checkbox"/> Solder Tail .165" [4.19 mm] <input type="checkbox"/> Press-Fit .135" [3.43 mm]<br><input type="checkbox"/> Press-Fit .165" [4.19 mm]                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                                                   |
| <b>7. Mounting to PCB</b>              | <input type="checkbox"/> Hold Downs (one on either end)<br><input type="checkbox"/> .122" [3.10 mm] Mounting holes (Accepts #4 screws, right-angle connectors only)<br><input type="checkbox"/> .150" [3.81 mm] Mounting holes (Accepts #6 screws, right-angle connectors only)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                                   |
| <b>8. Select # of Contacts</b>         | Section A: (Power Contacts) <input type="checkbox"/> Enter Power Contact Type (LP - Low Power, HP - High Power)<br><input type="checkbox"/> Enter # of Power Contacts (Loaded with standard length Power Contacts)<br><input type="checkbox"/> Enter the position(s) to be loaded with Pre-mate contact (Receptacles only) (Mate-First-Break-Last) (i.e. #1, #3, etc.)<br>Contact Centerline Spacings: <input type="checkbox"/> .200" [5.08 mm] (for High Power only)<br><input type="checkbox"/> .250" [6.35 mm] (for High Power only)<br><input type="checkbox"/> .300" [7.62 mm] (for High Power only)<br>Section B: (Signal Contacts) <input type="checkbox"/> Enter # of Signal Contacts (Multiples of 8 are standard, i.e. 16, 24, 32...)<br><input type="checkbox"/> Enter the positions with Post-Mate Contacts (Mate-Last-Break-First, Plugs only)<br>Note: Row A is standard (i.e. A1, A3, etc.)<br>Section C: (Power Contacts) <input type="checkbox"/> Enter Power Contact Type (LP - Low Power, HP - High Power)<br><input type="checkbox"/> Enter # of Power Contacts (Loaded with standard length Power Contacts)<br><input type="checkbox"/> Enter the positions to be loaded with Pre-Mate Contacts (Receptacles only) (Mate-First-Break-Last, i.e. #1, #3, etc.)<br>Contact Centerline Spacings: <input type="checkbox"/> .200" [5.08 mm] (HDP) <input type="checkbox"/> .250" [6.35 mm] (P) <input type="checkbox"/> .300" [7.62 mm] (ACP) |                                                   |
| <b>9. Additional Requirements</b>      | <hr/> <hr/> <hr/>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |                                                   |

### 10. Customer Information

Name: \_\_\_\_\_ Company: \_\_\_\_\_ Location: \_\_\_\_\_

Phone: \_\_\_\_\_ Fax: \_\_\_\_\_ e-mail: \_\_\_\_\_

(Submit to your local TE Sales Engineer)

MULTI-BEAM XL, MULTI-BEAM XLE, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

## MINIPAK High-Density Board-to-Board Power Connectors

### Product Facts

- High current per linear inch
- Various configurations to meet requirements using less board space
- Built-in alignment feature
- Shrouded insulator design
- Meets safety regulatory requirements
- All MINIPAK products in this section are RoHS compliant

### Typical Applications

- Telecom and computer applications
- Routers
- Servers, mini and supercomputers
- Removable battery packs
- Uninterruptible power systems (UPS)
- Hot-swap N+1 power distribution



MINIPAK connectors are a family of board-to-board power connectors designed to deliver more current using less board real estate.

### Product Varieties

This product family includes **MINIPAK high-density power connectors**, which are custom configurable and offer a combination of alignment guides, signal contacts, and DualBlade power contacts to meet different requirements. Following the PICMG  $\mu$ TCA.0 Standard, the **MINIPAK HD** connector is also available

in this product line and is ideal for hot-plug telecommunications applications. With a two-row configuration, the **MINIPAK HDE** connector, designed to serve in both PCB-to-PCB and backplane power systems, occupies minimal PCB edge space. For applications needing a low profile solution, TE offers **MINIPAK HDL**, a blind-mateable board-to-board connector, which stands only 8 mm off the edge of the printed circuit board.

### Wide Selection of Configurations

MINIPAK connectors are available in numerous configurations. Which MINIPAK connector is most suited to your application will depend on requirements such as AC input current and voltage, DC output currents and voltages, board-mount style, and available board space. TE will work with you to help determine the best solution to your application and can custom tool MINIPAK configurations if needed.

## MINIPAK High-Density Board-to-Board Power Connectors (Continued)



### MINIPAK High-Density Power Connectors

- 32 Amps per contact, fully loaded
- Features an innovative Dual Blade contact that allows splitting 4.5 mm pitch contacts into multiple voltage rails
- Various alignment guides, signal contacts, and power contacts available to use on 4.5 mm, 6.0 mm, and 7.5 mm pitches



### MINIPAK HDL Connectors

- High density blind-mateable connector
- Low profile-stands just 8.0 mm off the PCB
- Solder and press-fit tails available
- Current rating of 17A
- Low contact resistance with mating forces less than 0.3lbs per contact



### MINIPAK HD Connectors

- Designed to the PICMG MicroTCA.0 Standard
- Combines 24 power contacts and 72 high density signal contacts
- Rugged contact design helps provide long-term reliability
- Hot-plug design controls arc during hot mate/unmate cycles
- 3 mating levels



### MINIPAK HDE Connectors


- Very high current density
- Two row configuration saves PCB space
- Two levels of contact sequencing available for mate-first-break-last operation
- Uses a hot-plug contact approved by UL for current interrupt applications

## MINIPAK High-Density Board-to-Board Power Connectors (Continued)



| Right-Angle PCB Plug |                |                |                    |        | Mating Pair<br>Overall<br>Length | Vertical PCB Receptacle |                     |                 |
|----------------------|----------------|----------------|--------------------|--------|----------------------------------|-------------------------|---------------------|-----------------|
| Part Number          | No. 30A<br>Pwr | No. 15A<br>Pwr | Signal<br>Contacts | Tails  |                                  | Mating<br>Part Number   | Tails               | Special Feature |
| 6651672-2            | 3              | 2              | 6                  | Solder | 1.38<br>35.00                    | 6651673-1               | Compliant Press-Fit | DualBlade       |
| 6651670-1            | 3              | 2              | 24                 | Solder | 2.87<br>73.00                    | 6651671-1               | Compliant Press-Fit | DualBlade       |
| 6651742-1            | 8              | 12             | 58                 | Solder | 3.78<br>96.00                    | 6651743-1               | Compliant Press-Fit | Stacked         |
| 6651668-1            | 21             | 0              | 24                 | Solder | 5.71<br>145.00                   | 6651669-1               | Compliant Press-Fit | —               |
| 6651380-1            | 6              | 5              | 36                 | Solder | 4.50<br>114.50                   | 6651381-2               | Compliant Press-Fit | DualBlade       |


\*The remaining power contacts are 30 Amps each



**DualBlade Contact**  
DualBlade Contact provides two  
15 Amp contacts in the space of one  
30 Amp contact



**DualBlade Contact  
Housing Assembly**




**Stacked MINIPAK Connector**

### Co-Planar Stacked MINIPAK Connector

| Right-Angle PCB Plug |                |                |                    |        | Mating Pair<br>Overall<br>Length | Right-Angle PCB Receptacle |        |                 |
|----------------------|----------------|----------------|--------------------|--------|----------------------------------|----------------------------|--------|-----------------|
| Part Number          | No. 30A<br>Pwr | No. 15A<br>Pwr | Signal<br>Contacts | Tails  |                                  | Mating<br>Part Number      | Tails  | Special Feature |
| 1766056-1            | 2              | 6              | 36                 | Solder | 1.55<br>39.30                    | 1766057-1                  | Solder | Stacked         |

### Custom MINIPAK Connector Configurations

If the standard MINIPAK connector configuration does not meet your application requirements, TE may be able to tool a custom MINIPAK connector solution depending on your requirements and production volume. Please consult Customer Service for details.



**Note:** All part numbers are RoHS compliant.

## MINIPAK High-Density Board-to-Board Power Connectors (Continued)

|                                       |                                                                            |
|---------------------------------------|----------------------------------------------------------------------------|
| <b>Material</b>                       |                                                                            |
| Insulators                            | PPA, UL 94V-0 flammability rated, color black                              |
| Socket contacts                       | Phosphor bronze alloy                                                      |
| Signal pins                           | Brass alloy                                                                |
| Power blades                          | Copper alloy                                                               |
| <b>Plating</b>                        |                                                                            |
| Contacts                              | Selective 30 microinches gold over nickel                                  |
| Terminals                             | Tin over nickel                                                            |
| <b>Environmental/Mechanical</b>       |                                                                            |
| Connector operating temperature range | -40°C to +130°C                                                            |
| Mating forces                         | Power: 1.5lb/contact typical<br>Signal: 0.2lb/contact typical              |
| <b>Electrical</b>                     |                                                                            |
| Contact current rating                | Individual power contact: 65A max. <sup>1</sup>                            |
| Voltage ratings                       | AC Power: 125/250VAC, signal & DC power: up to 60V                         |
| Insulation resistance                 | 5000Ω at 500V DC for 2 minutes, per MIL-STD 1344, Method 3003              |
| Dielectric strength                   | Power 1,500VAC, signal 250VAC; for 1 minute, per MIL-STD 1344, Method 3001 |


<sup>1</sup> This is the UL rating for an individual power contact. Current rating for any given configuration with multiple contacts will depend on contact layout, quantity and spacing.

### Contact Current Ratings

The graph to the right shows the current carrying capabilities of an individual power contact, and that of multiple contacts at 4.5, 6.0 and 7.5 mm contact spacing.


### Safety Regulatory Agency Compliance

MINIPAK connectors have been evaluated and found to comply with the UL1977 standard and the CSA standard C22.2 No.182.3-M1987. TE will work with customers to obtain application-specific regulatory certifications if needed.




### Connector Mounting


#### Termination Tails



Compliant Press-fit  
for .093" min. thick PCB




Solder Tail



Mating Condition

| Dimension "A"              |                            |
|----------------------------|----------------------------|
| Long Tail                  | Short Tail                 |
| .180 ± .020<br>4.57 ± 0.51 | .120 ± .020<br>3.07 ± 0.51 |



## “NEW” MINIPAK HDL Connectors

# NEW

### Product Facts

- High-density, low profile, power/signal, blind-mate connector
- Developed to meet next generation 1U application by reducing airflow impedance
- Design is customizable
- Serves both solder reflow and press-fit applications with the same contact

### Applications

- 1U Servers
- High End Servers
- Telecommunications Switches, requiring low profile
- Hot-pluggable power supplies


### Technical Documents

#### Product Specification

108-2325

#### Application Specification

114-13215




TE's new MINIPAK HDL connector combines a high-density power interface into a blind-mateable board-to-board connector, which stands only 8 mm off the edge of the printed circuit board.

The MINIPAK HDL product consists of a right-angle plug and right-angle receptacle, which utilizes an eye of the needle tail that can be used in both solder and press-fit applications. The contact offers a current rating of 17 amps, low contact resistance, and mating forces less than 0.3 pounds per contact.


The connector is designed and manufactured to be mass-customizable, allowing the customer to select a wide array of configurations and layouts. MINIPAK HDL connectors also contain three levels of mating sequences. This product is designed specifically for modular hot-swappable power distribution systems. The MINIPAK HDL connector offers 20% more current density in a smaller package than other products currently offered in the market.

### Temperature Rise Chart

MINIPAK HDL  
Temperature Rise Vs Current  
8 Circuits 2 oz 2 Layer



### Simulated Side View of 1U Chassis



## “NEW” MINIPAK HDL Connectors (Continued)


### Contacts

**Plating** — Gold over nickel, or gold over palladium-nickel in mating area


### Performance Data

**Current Rating** — 16 Amps

**Max. Operating Temperature** — 120°C




**Right-Angle Receptacle**  
Part Number 2-1926733-5





**Right-Angle Plug**  
Part Number 2-1926732-5


| Configuration | Part Numbers     |                        |
|---------------|------------------|------------------------|
|               | Right-Angle Plug | Right-Angle Receptacle |
| 25S X 8P      | 1-1926732-8      | 1-1926733-8            |
| 25S X 10P     | 2-1926732-5      | 2-1926733-5            |
| 25S X 16P     | 4-1926732-6      | 4-1926733-6            |
| 40S X 24P     | 7-1926732-7      | 7-1926733-7            |
| 2P X 15S X 2P | 1926720-2        | 1926721-2              |
| 6P X 15S X 6P | 1-1926720-6      | 1-1926721-6            |
| 8P X 25S X 8P | 2-1926720-5      | 2-1926721-5            |



**Part Number 2-1926720-5**



**Part Number 2-1926721-5**




**Note:** All part numbers are RoHS compliant.

## MINIPAK HD Connectors

### Product Facts

- Designed to the PICMG MicroTCA.0 Standard
- 30 microinches gold plating over nickel
- RoHS compliant
- 24 high current density power contacts, able to carry up to 14.5 Amps per contact when fully loaded
- Industry proven Universal Power Module (UPM) power contacts
- Hot-plug contact design controls arc during hot mate/unmate cycles
- 3 mating levels




TE supplies the Power Entry Module (PEM) connector specified in the PICMG MicroTCA.0 Standard. The PICMG MicroTCA.0 Standard is one of the latest standards addressing future telecommunications needs. The MINIPAK HD connector combines 24 power contacts and 72 high density signal contacts. The power contacts are the industry proven contacts utilized in

the Universal Power Module (UPM) and are capable of carrying 14.5 Amps per contact when fully energized. Rugged contact design ensures long-term reliability and sacrificed contact tip, controls arcing during hot mate/unmate cycles. The MINIPAK HD also features 3 levels of mating and selective gold plating on contacts.

### Contact Blades Product Facts

- Designed for Hot Swap applications
- Extended sacrificial contact tip absorbs arc
- Main contacts stay free of contaminants



MINIPAK HD Contact Blades

### Technical Documents

**Product Specification**  
108-2253

**Application Specification**  
114-13182

**Industry Standard**  
PICMG MicroTCA R1.0

MicroTCA and PICMG are trademarks of PICMG-PCI Industrial Computer Manufacturers Group, Inc.

## MINIPAK HD Connectors (Continued)


### MicroTCA Connectors — MINIPAK HD Board-to- Board Connector

#### Vertical Receptacle, Compliant Press-Fit


**Part Number 1469920-1**  
(Tin-lead PCB Tails)

**Part Number 1469920-2**  
(Tin Plated PCB Tails)

The vertical connector consists of 72 2 mm pin and 24 Universal Power Module (UPM) receptacle contacts. The contacts have compliant pin tails for press-fit applications.



**PCB Seating Tool**  
**Part Number 1901650-1**



**Part Number 1469920-1**


### Right-Angle Plug, Solder Tail or Compliant Press-Fit

**Part Number 1469921-1**  
(Solder Tail)

**Part Number 1469922-1**  
(Press-Fit)

**Part Number 1469922-2**  
(Press-Fit, Tin-Lead PCB  
Tails)

The right-angle connector consists of 72 high density signal pins and 24 right-angle UPM blades that feature 2 mating lengths for the mate first/break last ground sequencing. The right-angle connectors come in 2 piece tail variations, press-fit and solder.



**Part Number 1469921-1**

**Note:** All part numbers are RoHS compliant.

## MINIPAK HDE Connectors

### Product Facts

- Compatible with 2 mm equipment practices per IEC 61076-4-101
- One-piece molded housing — fewer parts to assemble to PCB
- Very high current density — 18 Amps per contact on each contact in an 8-position (2 x 4) connector
- 4 PCB tails distributes the current with just 4.5 amps per plated through hole
- Hot-pluggable contact design reduces contact degradation associated with live PCB insertions / extractions
- Two-levels of contact sequencing for mate-first-break-last operation



### Technical Documents

#### Product Specification

108-2289

#### Instruction Sheet

408-10157

The new MINIPAK HDE connector is the latest high current power module designed to serve in both backplane power distribution and general PCB-to-PCB applications. It was designed to complement the most popular high-speed backplane connectors offered by TE, including HM-Zd, Z-PACK TinMan and MULTIGIG RT connectors.

The two-row configuration offers a benefit to the PCB designer. The power can be fed from either the top or bottom row, with the return path routed through the other remaining row. Alternatively, the same voltage rail can be routed to

both the top and bottom rows and the return path can be routed to both the top and bottom rows of adjacent contacts.

The two row configuration offers the additional benefit of occupying just half the linear PCB edge space of other types of board-to-board power modules.

The low mating force contact reduces the moment / stresses on the connector during mating and reduces the plating wear for long-term reliability.

The MINIPAK HDE connector has two-levels of blade lengths to provide mate-first-break-last operation

for hot swap operation.

In addition, in the event the connector is used to mate or un-mate to a live load, the sacrificial contact tip absorbs the arc to keep the remaining contact mating surfaces free of damage. This "hot-plug" contact design has been approved by UL for current interrupt applications.

All MINIPAK HDE connectors are easily applied to the PCB with common "flat-rock" seating tools. The connector mates with TE's Universal Power Module connectors found on page 55.

## MINIPAK HDE Connectors (Continued)

### Contacts

Industry proven Universal Power Module (UPM) style contacts

### Performance Data


**Current Rating** — 18 Amps on each contact in the 8-position (2x4) connector

**Low Level Contact Resistance** — 2 milli-ohms max

**Operating Temperature** — -40°C to +105°C

### Technical Documents


**Product Specification**  
108-2289



| Description | Part Number | Dimension L   | Mating Connector* |
|-------------|-------------|---------------|-------------------|
| 2 x 3       | 1926223-1   | .472" [12.00] | 5-5223955-2       |
| 2 x 4       | 1926224-1   | .590" [15.00] | 120953-1          |
| 2 x 5       | 1926225-1   | .708" [18.00] | 120953-2          |
| 2 x 6       | 1926226-1   | .826" [21.00] | 120953-3          |
| 2 x 7       | 1926227-1   | .944" [24.00] | 120953-4          |
| 2 x 8       | 1926228-1   | 1.06" [27.00] | 120953-5          |
| 2 x 9       | 1926229-1   | 1.18" [30.00] | 120953-6          |
| 2 x 10      | 1926271-1   | 1.30" [33.00] | 120953-7          |
| 2 x 11      | 1926272-1   | 1.42" [36.00] | 120953-8          |
| 2 x 12      | 1926273-1   | 1.54" [39.00] | 120953-9          |

\*Mating connectors are single row, MINIPAK HDE requires 2 x mating connectors.

**Note:** For more information on the mating connector please see page 52.  
Receptacle Seating Tool Part Number 1585309-X.



**Note:** All part numbers are RoHS compliant.


## FLATPAQ Modular Board-to-Board Power Connectors — Our Most Modular Board-to-Board Power Connector

### Product Facts

- 32 Amp high-performance ELCON CROWN BAND power contacts
- True hot-plug power contacts available for current interruption under load
- Versatile modular design allows customized configuration to meet your specific application requirements
- Perpendicular, parallel and co-planar styles available
- Sequenced mating of power and signal contacts
- Solder and compliant press-fit termination to the board
- Unique active guide modules double as alignment guide and power contact
- All FLATPAQ products in this section are RoHS compliant

### Typical Applications

- Board-to-board power interconnections
- Hot-swap N+1 power distribution for telecommunications, servers and mini-computers
- Uninterruptible power systems (UPS)
- Removable battery packs



FLATPAQ connectors provide hot-pluggable AC and DC power in board-to-board applications. Customized configurations of up to 45A power contacts, signal & logic lines, and guides (both active and passive) are enabled by the assembly of various standard modules. This allows the designer to specify guidance for blind-mating situations, contact mating sequence, spacing for voltage ratings, and current interruption under load (true hot-plug), to meet custom design requirements without incurring any tooling expense.

### Product Highlights Highly Configurable

FLATPAQ connectors are custom configurable using standard modules that can be arranged in any order to meet the application requirements. It is even possible to have both power blades and power sockets in the same connector side. Using off-the-shelf, modular components enables quick turnaround of sample requests, typically within one week, to allow your design to move forward on schedule.

### High-performance ELCON Power Contacts

FLATPAQ socket modules use proven CROWN BAND technology, for low insertion and extraction forces, minimal voltage drop and reduced temperature rise. The latest generation contacts are 45A USR rated (32.5A CNR) and can handle even higher currents when mounted on boards with 5 oz copper traces or on bus bars.

hot-pluggable socket contacts are rated at 35A USR, 20A CNR. Both hot-plug and regular sockets can be mixed in the same connector (as can both power blades and power sockets).

Standard power modules utilize the same contacts as the MINIPAK connectors for cost effectiveness. The original "float" mounted blade modules are still available where physically isolating the blade from the PCB solder joints is desired.

24-position straight mount Signal socket modules are now available in a cost effective 1A design.

### Power and Signal Sequencing

Power contacts are available in Standard, Premate and Postmate lengths to meet your power sequencing requirements. Signal contacts have Standard and Premate length options, consult Customer Service for details.

## FLATPAQ Modular Board-to-Board Power Connectors — Our Most Modular Board-to-Board Power Connector (Continued)

### Various Contact Termination Styles

All connectors are available in two lengths of solder termination, .115" (2.9 mm) nominal for 0.062" (1.6 mm) thick boards, and 0.177" (4.5 mm) for 0.093" (2.4 mm) and 0.125" (3.18 mm) boards.

Straight mount socket connectors are also available with compliant 'Eye of the Needle' design press-fit terminals for 0.093" (2.4 mm) minimum thickness boards and bus

bars. TE will provide details of the recommended pressing fixture for each assembly.

All terminations fit 0.040 +/- .0030" (1.02 +/- .08 mm) diameter plated through holes.

### Alignment Guides and Mounting Ears

FLATPAQ connector alignment guides improve gatherability in blind-mate situations and can be either electrically active (35A rated) or passive. Passive

guides should be used in conjunction with mounting ears when placed at the end of the connector. Mounting ears should also be considered on right-angle mounted connectors.

### Finished Connector Drawing

TE will provide a customer drawing showing all envelope dimensions and PCB mounting pattern based on the configuration indicated using the layout sheet available at [www.te.com](http://www.te.com). See page 44 for details on completing

the layout sheet. A drawing with general contact sequencing and alignment information is available; please contact Customer Service for a copy.


### Safety Regulatory Agency Compliance

FLATPAQ connector has been evaluated by safety regulatory agencies for use in data, signal, control and power applications. Consult Customer Service for details.


### Electrical Performance

The graphs below show the performance of the FLATPAQ contact design in terms of temperature rise against current. Tests were performed on 250 V power modules mounted on PC boards with 2 oz, 3 oz, and 5 oz copper traces.

#### Temperature Rise



#### Voltage Drop



## FLATPAQ Connector Product Specifications



### Materials

|                                               |                                                          |
|-----------------------------------------------|----------------------------------------------------------|
| Insulators                                    | PPA, UL 94V-0 flammability rated, color black            |
| Power Blades                                  | Copper alloy                                             |
| Power Sockets                                 | Phosphor Bronze                                          |
| Hot-Plug Power Sockets & Active Guide Sockets | Crown Bands: Beryllium Copper<br>Holder: Phosphor Bronze |
| Signal Pin Contacts                           | Solder termination: Brass<br>Press-fit: Phosphor Bronze  |
| Signal Socket Contacts                        | 1 Amp: Phosphor Bronze<br>3 Amp: Beryllium Copper        |
| Passive Guide Pin                             | Brass                                                    |
| Active Guide Pin                              | Copper alloy                                             |

### Finishes

|                   |                                                                                            |
|-------------------|--------------------------------------------------------------------------------------------|
| Contacts          | Selectively plated gold (30 microinches minimum) with tin on terminations, all over nickel |
| Passive Guide Pin | Nickel                                                                                     |
| Active Guide Pin  | Silver                                                                                     |

### Electrical


|                                         |         |                                                                                                                    |
|-----------------------------------------|---------|--------------------------------------------------------------------------------------------------------------------|
| Current Rating                          | UL      | 45 Amp                                                                                                             |
| Power Contacts                          | CUR/CSA | 32.5 Amp                                                                                                           |
| Current Rating, Hot-Plug Power Contacts | UL      | 35 Amp at 250V, 50 cycles                                                                                          |
| Signal Contacts, 1 Amp                  | CUR/CSA | 20 Amp at 250V, 50 cycles                                                                                          |
|                                         | UL      | 1 Amp, 250 VAC                                                                                                     |
|                                         | CUR/CSA | 1 Amp, 250 VAC                                                                                                     |
| Signal Contacts, 3 Amp                  | UL      | 3 Amp, 250 VAC                                                                                                     |
|                                         | CUR/CSA | 2.5 Amp, 250 VAC                                                                                                   |
| Contact resistance                      | Power   | 2 mΩ maximum initial, (3 mΩ maximum after 500 cycles durability), at 35A per MIL-STD-1344, Method 3004             |
|                                         | Signal  | 15 mΩ maximum initial, (30 mΩ maximum after 500 cycles durability), at 100mA, 20 mV, per MIL-STD-1344, Method 3002 |
| Insulation Resistance                   |         | 5,000 MΩ minimum at 500VDC for 2 minutes, per MIL-STD-1344, Method 3003                                            |
| Dielectric Strength                     |         | 1,500 VDC for 1 minute, per MIL-STD-1344, Method 3001                                                              |

### Mechanical


|                                  |                 |                                                                                                                                                                                                                                  |
|----------------------------------|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Insertion Force                  | Power<br>Signal | 4.0 lbf (17.8 N) maximum<br>5.0 ozf (1.4 N) maximum, using .0305" (.775 mm) diameter steel test pin                                                                                                                              |
| Extraction Force                 | Power<br>Signal | 1.0 lbf (4.4 N) minimum<br>0.5 ozf (0.1 N) minimum, using .0295" (.749 mm) diameter steel test pin                                                                                                                               |
| Contact Retention (in insulator) | Power<br>Signal | 10.0 lbf (44.4 N) minimum<br>5.0 lbf (22.2 N) minimum                                                                                                                                                                            |
| Durability                       |                 | 500 Cycles, per MIL-STD-1344, Method 2016                                                                                                                                                                                        |
| Operating Temperature            |                 | -40 to +105° C                                                                                                                                                                                                                   |
| Recommended PCB Hole             |                 | Finished hole: 0.040 +/- .0030" dia. (1.02 +/- .08 mm dia.)<br>Drilled hole: 0.0453 +/- .0005" dia. (1.15 +/- .013 mm dia.)<br>Copper Plate: 0.0010" (.025 mm) min. per surface<br>Tin Plate: 0.0003" (.008 mm) min. per surface |
| Press-Fit Tooling                |                 | Press fixture is recommended for compliant press-fit assemblies.<br>Consult TE for tool drawing                                                                                                                                  |
| Marking                          |                 | Connectors are marked with manufacturer's logo, part number and lot code                                                                                                                                                         |

## FLATPAQ Connectors


**Part Number 6646465-1**  
**FLATPAQ 250V Straight**  
**Socket Connector**  
**4 Power, 24 Signal Contacts**



**Part Number 6646597-1**  
**FLATPAQ 250V**  
**Straight Socket Connection**  
**with Active Guide Pin**  
**2 (250V) Power,**  
**2 amps Signal Contacts**



**Part Number 6646722-1**  
**FLATPAQ 600v**  
**Right-Angle Pin Connector**  
**with Guide Socket**  
**7 (600V) Power,**  
**6 Signal Contacts**



**Note:** All part numbers are RoHS compliant.

## How to Specify Your Modular FLATPAQ Connector

In order to build your Modular FLATPAQ connector, it is necessary to specify all application-specific requirements such as required modules, their order, termination, and sequencing. For this purpose, a Modular FLATPAQ Connector layout form such as the one shown below is available. Just complete the form and send it to TE Customer Service. We will generate a Customer Drawing for you to check and approve prior to connector production. Samples are also available upon request.

- 1 Enter your contact information, including signature and date.
- 2 Indicate the connector layout by filling in the FP number of each module required in the boxes, one per box. Use one form per mated pair. The left to right order of the modules should match the mating face views of the connector. When laying out right-angle assemblies, make sure that you look at the mating face with the termination tails facing downwards.
- 3 For solder terminated assemblies, indicate the tail length for each half of the connector using the checkboxes to the right of the layout grid.

### Sample Modular FLATPAQ Connector Layout Form

#### Instructions

1. Indicate the connector layout by filling in the FP number of each module required in the boxes, one per box. Use one form per mated pair.
2. The left to right order of the modules should match the **mating face views** of the connector. **When laying out right-angle assemblies**, make sure you look at the mating face with the termination tails facing downwards.
3. **For solder terminated assemblies**, indicate the tail length for each half of the connector using the checkboxes to the right of the layout grid.
4. Sign, date and send the completed form to your local TE Sales Engineer.

**Upon receipt of this form, TE will generate a Customer Drawing for you to check and approve prior to connector production.**

Write the "FP" numbers to indicate the layout of one half of the connector assembly, matching the left to right order with the mating face view of the connector (right-angle assembly tails facing downwards).

| ENTER CUSTOMER INFORMATION                                                                          |  |  |  |  |  |  |              |  |  |  |  |  |  |
|-----------------------------------------------------------------------------------------------------|--|--|--|--|--|--|--------------|--|--|--|--|--|--|
| Company                                                                                             |  |  |  |  |  |  | Location     |  |  |  |  |  |  |
| Contact Name                                                                                        |  |  |  |  |  |  | Title        |  |  |  |  |  |  |
| Telephone                                                                                           |  |  |  |  |  |  | Fax          |  |  |  |  |  |  |
| Email Address                                                                                       |  |  |  |  |  |  |              |  |  |  |  |  |  |
| I am: <input type="checkbox"/> End user <input type="checkbox"/> Contract manufacturer (end user: ) |  |  |  |  |  |  |              |  |  |  |  |  |  |
| Signature                                                                                           |  |  |  |  |  |  | Today's Date |  |  |  |  |  |  |
| Annual Quantity Required                                                                            |  |  |  |  |  |  |              |  |  |  |  |  |  |

Submit to your local TE Sales Engineer.

Write the "FP" numbers to indicate the layout of the mate of the above assembly, matching the left to right order with the mating face view of the connector (right-angle assembly tails facing downwards).

| Solder Tail Options                                         |  |  |  |  |  |  |  |  |  |  |  |  |  |
|-------------------------------------------------------------|--|--|--|--|--|--|--|--|--|--|--|--|--|
| <input type="checkbox"/> .115" (2.9 mm); .062" thick boards |  |  |  |  |  |  |  |  |  |  |  |  |  |
| <input type="checkbox"/> .177" (4.5 mm); .093/.125" boards  |  |  |  |  |  |  |  |  |  |  |  |  |  |

#### Right-Angle Mount

| 250 V Power Modules                                 |                                                   |                                                     |                          |                        |
|-----------------------------------------------------|---------------------------------------------------|-----------------------------------------------------|--------------------------|------------------------|
|                                                     |                                                   |                                                     |                          |                        |
| FP151<br>Standard Blade<br>FP105<br>Float, Standard | FP152<br>Premate Blade<br>FP106<br>Float, Premate | FP153<br>Postmate Blade<br>FP107<br>Float, Postmate | FP104<br>Hot-Plug Socket | FP512<br>Spacer, 250 V |

| Signal Modules  |                        |                |                       |
|-----------------|------------------------|----------------|-----------------------|
|                 |                        |                |                       |
| FP302<br>24-Pin | FP303<br>24-Pin Socket | FP314<br>6-Pin | FP315<br>6-Pin Socket |

| 600 V Power Modules                                 |                                                   |                                                     |                          |                        |
|-----------------------------------------------------|---------------------------------------------------|-----------------------------------------------------|--------------------------|------------------------|
|                                                     |                                                   |                                                     |                          |                        |
| FP155<br>Standard Blade<br>FP121<br>Float, Standard | FP156<br>Premate Blade<br>FP122<br>Float, Premate | FP157<br>Postmate Blade<br>FP123<br>Float, Postmate | FP120<br>Hot-Plug Socket | FP514<br>Spacer, 600 V |

| Mounts                     |                             | Guides                                        |                                           |
|----------------------------|-----------------------------|-----------------------------------------------|-------------------------------------------|
|                            |                             |                                               |                                           |
| FP500<br>Left Flange Mount | FP501<br>Right Flange Mount | FP506<br>Passive<br>Right-Angle Guide Sockets | FP507<br>Passive<br>Right-Angle Guide Pin |

#### Straight Mount

| 250 V Power Modules                                                                                                |                                                     |                                                   |                                                     |                        |
|--------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|---------------------------------------------------|-----------------------------------------------------|------------------------|
|                                                                                                                    |                                                     |                                                   |                                                     |                        |
| FP150<br>Socket, Solder<br>FP250<br>Socket, Press-fit<br>FP100<br>Hot-Plug, Solder<br>FP200<br>Hot-Plug, Press-fit | FP161<br>Standard Blade<br>FP101<br>Float, Standard | FP162<br>Premate Blade<br>FP102<br>Float, Premate | FP163<br>Postmate Blade<br>FP103<br>Float, Postmate | FP511<br>Spacer, 250 V |

| Signal Modules                                           |                                                                                                                                 |                                             |                                                                        |
|----------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------|------------------------------------------------------------------------|
|                                                          |                                                                                                                                 |                                             |                                                                        |
| FP300<br>24-Pin, Press-fit<br>FP400<br>24-Pin, Press-fit | FP318<br>24-Pin Socket<br>FP418<br>24-Pin Skt, Press-fit<br>FP301<br>24-Pin Skt, 3A Rated<br>FP401<br>24-Pin Skt, 3A, Press-fit | FP312<br>6-Pin<br>FP412<br>6-Pin, Press-fit | FP313<br>6-Pin Socket<br>3A rated<br>FP413<br>6-Pin Skt, 3A, Press-fit |

| 600 V Power Modules                                                                                                |                                                     |                                                   |                                                     |                        |
|--------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|---------------------------------------------------|-----------------------------------------------------|------------------------|
|                                                                                                                    |                                                     |                                                   |                                                     |                        |
| FP154<br>Socket, Solder<br>FP254<br>Socket, Press-fit<br>FP216<br>Hot-Plug, Solder<br>FP216<br>Hot-Plug, Press-fit | FP165<br>Standard Blade<br>FP117<br>Float, Standard | FP166<br>Premate Blade<br>FP118<br>Float, Premate | FP167<br>Postmate Blade<br>FP119<br>Float, Postmate | FP513<br>Spacer, 600 V |

| Mounts                     |                             | Guides                                 |                                                                                |
|----------------------------|-----------------------------|----------------------------------------|--------------------------------------------------------------------------------|
|                            |                             |                                        |                                                                                |
| FP500<br>Left Flange Mount | FP501<br>Right Flange Mount | FP502<br>Straight Passive Guide Socket | Straight Guide Pins<br>FP503 Passive<br>FP515 Active, M3<br>FP517 Active, 4-40 |

**Note:** All modules are solder tail termination unless indicated as compliant Press-fit. Select solder tail length using checkboxes to the right of the connector layout grid above. 0.093" or thicker boards are recommended for compliant Press-fit termination style. Consult TE for signal module sequencing. See Catalog 1773096 for benefits of Hot-Plug and Float options.

### How to Obtain Modular FLATPAQ Connector Layout Forms

Modular FLATPAQ Connector layout forms can be obtained directly from Customer Service or through your TE Sales Engineer. They can also be downloaded from the website; at <http://www.te.com>.


## ICCON Single Pole Power Connectors

### Product Facts

- Uses high-performance Crown contact
- 35A current rating
- True compliant press-fit and solder tails
- Pin locking feature option
- Standard DIP footprint .300 x .100 and ICCON SLIMLINE connector .100 x .100
- Insulator rated at 105°C, UL 94V-0
- Meets safety regulatory requirements
- #8 AWG wire size
- Parallel and perpendicular
- Sequencing capability
- All ICCON products in this section are RoHS compliant

### Typical Applications

- Power distribution
- Board-to-board interconnection
- Board-to-busbar interconnection
- Board-to-wire interconnection
- High-density power designs
- Board stacking



ICCON connectors provide a reliable high current power interconnection with quick connect/disconnect function for space constrained motherboard-daughterboard, cable-board and board-busbar power delivery applications.



### Product Highlights

#### High Performance Contact

ICCON connectors use ELCON CROWN BAND Contact, a multifingered spring which provides a greater surface contact area, thus ensuring small millivolt drop, minimum heat generation and very low insertion and extraction forces.

#### Optional Locking Feature

The optional locking feature provides minimum 5 lbs. (2.21kg) retention force to improve connection integrity, securing against accidental unmating in harsh mechanical conditions.

#### Support for Multiple Mounting Styles

ICCON connectors are available with press-fit or solder tails for mounting on both PC boards and bus bars. TE uses eye of the needle true compliant tails for the most reliable mounting using solderless techniques. Each ICCON connector has a 10 pin DIP footprint for convenient industry standard mounting. Through hole socket connectors can be used in "bottom entry" applications.

### Mating with Discrete Contacts

For further versatility, ICCON connector products can mate with discrete contacts, available in a variety of termination types.

#### ICCON SLIMLINE Connectors

With a footprint close to 30% smaller than the standard ICCON connector products, the ICCON SLIMLINE connector products allow integrating more components in less board real estate, providing substantial space savings compared to connectors of this type in the same performance range.


#### Stacked ICCON

Designed for motherboard-to-daughtercard power distribution systems, the Stacked ICCON combined power/guide module occupies significantly less PCB edge space than separate modules. Providing more than 200 Amps/inch, this right-angle mounted connector is ideal for applications needing high current density.

## ICCON Standard DIP Connectors (.300 x .100 footprint)


### Right-Angle Receptacle

Part Number 6643232-1 Solder  
Part Number 6643272-1 Compliant




### Right-Angle Pin

For Part Numbers and "A" Dimension  
See Table Below




### Vertical Receptacle

Part Number 6643264-1 Through Hole, Solder  
Part Number 6643219-1 Closed, Solder  
Part Number 6643269-1 Through Hole, Compliant



### Vertical Pin

For Part Numbers and "A" Dimension  
See Table Below



| Right-Angle Pins<br>Solder Tail | Compliant | Locking Style | Length "A"    |
|---------------------------------|-----------|---------------|---------------|
| 6643281-1                       | 6643275-1 | Non-Lock      | .470 [11.93]  |
| 6643276-1                       | 6643273-1 | Lock          | .470 [11.93]  |
| 6643431-1                       | 6643442-1 | Non-Lock      | .570 [14.48]  |
| 6643432-1                       | 6643443-1 | Non-Lock      | .750 [19.05]  |
| 6643433-1                       | 6643444-1 | Non-Lock      | 1.000 [25.40] |
| 6643434-1                       | 6643445-1 | Non-Lock      | 1.250 [31.75] |
| 6650785-1                       | 6643446-1 | Non-Lock      | 1.500 [38.10] |
| 6643435-1                       | 6643447-1 | Non-Lock      | 1.750 [44.45] |


| Vertical Pins<br>Solder Tail | Compliant | Locking Style | Length "A"    |
|------------------------------|-----------|---------------|---------------|
| 6643283-1                    | 6643274-1 | Non-Lock      | .470 [11.93]  |
| 6643266-1                    | 6643271-1 | Lock          | .470 [11.93]  |
| 6643436-1                    | 6643449-1 | Non-Lock      | .570 [14.48]  |
| 6643437-1                    | 6643450-1 | Non-Lock      | .750 [19.05]  |
| 6643438-1                    | 6643451-1 | Non-Lock      | 1.000 [25.40] |
| 6643439-1                    | 6766439-1 | Non-Lock      | 1.250 [31.75] |
| 6643440-1                    | 6766440-1 | Non-Lock      | 1.500 [38.10] |
| 6643441-1                    | 6766441-1 | Non-Lock      | 1.750 [44.45] |

**Note:** All part numbers are RoHS compliant.

## ICCON Discrete Contacts

### Crimp Socket

Part Number 6648317-1 #8 AWG




### Crimp Pins

Part Number 1766163-1  
#8 AWG Non-Lock


Part Number 1766160-1  
#8 AWG Lock

Part Number 1766816-1  
#10 AWG Non-Lock

Part Number 1766161-1  
#10 AWG Lock


### Board-Mount Pin — Floating



Part Number 6643252-1  
"A" = 1.250 (31.75)

Part Number 6643253-1  
"A" = 1.350 (34.29)


### Mating PCB-Mount

Part Number 6643248-1


#### Mounted Example:



PCB-Mount Receptacle  
for Increased Gatherability  
(for Use with Floating Pin) ± 2.5 mm


### Board-Mount Pin

Part Number 1766815-1  
"A" = 1.250 (31.75)

Part Number 1766157-1  
"A" = 1.350 (34.29)


### Double-Ended Board-Mount Pin

Part Number 1766817-1





**Note:** All part numbers are RoHS compliant.

## ICCON Connector Electrical Performance


### Stacked ICCON

#### 2-Position Right-Angle Socket Assembly


25 Amps per socket  
Part Number 2085181-1







### Stacked ICCON Pins



| Dim. A        | Part Number |
|---------------|-------------|
| .630<br>16.00 | 1766663-1   |
| .709<br>18.00 | 1766663-2   |
| .787<br>20.00 | 1766663-6   |



## Electrical Performance




**Note:** All part numbers are RoHS compliant.

## ICCON SLIMLINE Connectors (.100 x .100 Footprint)


### Parallel Pin

Part Number 6643228-1 Solder  
Part Number 6643227-1  
Solder w/Locking Feature  
Part Number 6643222-1 Compliant  
Part Number 6643223-1  
Compliant w/ Locking Feature




### Parallel Socket

Part Number 6643229-1 Solder  
Part Number 6643220-1 Press-Fit



### Connector Mounting

The ICCON SLIMLINE Connector is optimized for a board thickness of .093" (2.38 mm), but can be successfully used on boards from .062" to .125" (1.58 mm to 3.17 mm)




### Specifications

| Finishes                  |                                             |
|---------------------------|---------------------------------------------|
| Crowns                    | 30 microinches Gold plated over nickel      |
| Pin Contacts              | Silver over nickel                          |
| Material                  |                                             |
| Housing                   | Polyester, 30% glass-filled, UL 94V-0 black |
| Body and pin contacts     | Copper alloy                                |
| Crowns                    | Copper alloy                                |
| Electrical                |                                             |
| Ratings                   | UL (USR) 35A at 250V                        |
|                           | UL (CNR) 25A at 250V                        |
| Voltage drop at UL rating | 27.2mV                                      |

### Contact System Performance, ICCON SLIMLINE Connector Current Ratings vs. mV Drop/Temperature Rise

Non-locking version, mounted on 2 oz. and 5 oz. copper boards




**Note:** All part numbers are RoHS compliant.

## Mini Power Modules

### Product Facts

- Hard Metric design compatible with Z-PACK 2 mm HM, Z-PACK HM-Zd, MULTIGIG RT and Futurebus+ Connectors
- Sequenced contact options for "make-first-break-last" applications
- Compliant press-fit connections to PCB
- High Durability  
200 Cycles — MULTIGIG RT, UPM Connectors  
100 Cycles — Futurebus+ Connectors
- Optional Guide Pins & Sockets for blind-mate applications
- Bellcore approved (contact TE for specific part numbers)
- Recognized to US and Canadian requirements under the Component Recognition program of Underwriters Laboratories, File #E28476
- Produced under a Quality Management System certified to ISO 9001

A copy of the certificate is available upon request.



The TE Mini Power Module family of products are designed specifically to complement the Hard Metric board-to-board backplane interconnects. These products include, MULTIGIG RT, Z-PACK 2 mm HM, Z-PACK HM-Zd, Futurebus+ and other Connectors. Available in "Standard" and "Reverse" orientations, the power modules can provide touch-safe protection (per IEC 60950) to either side of the connection (backplane or daughter card.)

Both the headers and receptacle offer compliant pin connections to the PCB. The Universal Power Module and MULTIGIG RT Connectors use the ACTION PIN Contact compliant design to provide maximum surface connection to the plated through hole. The range of products offers power contacts rated as low as 3 amps per contact (Futurebus+ Connectors) up through 20 Amps per contact

(MULTIGIG RT Connectors). In addition, the newest products offer high conductivity contacts which improve the current carrying capacity by as much as 50%.

The low contact normal force, available lubricated surface coating (UPM) and high conductivity materials combine to produce a high durability cycle rating and high current density. In addition, the high temperature housing and contact materials make these power modules suitable for a wide variety of applications including modular hot-swap power supplies used in computer, telecommunications, medical, and industrial equipment.

Generous alignment features designed into the housings on the Mini Power Drawer Connector and optional guidance hardware make these Power Modules ideal for blind-mating applications.

### Need more information?

Call Technical Support at the numbers listed below.


Technical Support is staffed with specialists well versed in all TE products. They can provide you with:

- Technical Support
- Catalogs
- Technical Documents
- Product Samples
- TE Authorized Distributor Locations

## Mini Power Modules for PCB-to-PCB Power Distribution

### MULTIGIG RT Power Modules


The newest of the power modules. Designed specifically for use with TE 2 mm Backplane Connectors. Suitable for 0.8 mm Card Spacing and made from high conductivity copper alloys, these power modules offer improved power density and high cycle life. The distribution to the PCB is through **six ACTION PIN compliant tails** which offer maximum surface area contact to the plated through hole. The design offers electrical protection with its sacrificial contact design and mechanical protection by recessing the power contacts. Contacts are rated for up to 20 Amps per contact, which delivers up to **120 Amps per linear inch**. Three contact mating lengths are available, in 1.5 mm sequence levels.



- Designed for Hot-Plug Operation
- 6 PCB tails per contact

### Universal Power Module (UPM)


Also designed to complement TE 2 mm Backplane Connectors, the design meets IEC 60950 touch-safe requirements by reversing the orientation as compared to the Futurebus+ Power Modules. The touch-safe receptacle is applied to the "hot" side, which is typically the backplane side of the connection. Offered in both a Standard Power grade, rated at 10 Amps per contact and High Power grade which carries 16 Amps per contact — resulting in up to **100 Amps per linear inch**. Hot-plug design and low normal force provide high durability and high reliability. Three contact mating lengths are available in 1.6 mm sequence levels. Multiple contact sequence patterns are available.



- Lubricated for Environmental Protection
- Designed for Hot-Plug
- 4 PCB Tails per Contact

### Z-PACK 2 mm Futurebus+ Power Modules

The power modules, designed to IEC 61076-4-OX, are used along with TE Futurebus+ Backplane Connectors. The contacts are rated for 3 Amps and fully loaded will carry approx. 50 Amps per linear inch. Three contact mating lengths available in 0.75 mm increments.





## Universal Power Module (UPM)

### Right-Angle Plug

#### Material and Finish

**Housing** — PBT

Natural color UL 94V-0

**Contacts** —

**Standard Power** —


Phosphor Bronze

**High Power** —


High Conductivity Copper Alloy

**Plating** — 0.00127 [0.00050] min. gold in mating area, 0.0050 [0.00020] min. tin-lead on ACTION PIN post area, with entire contact underplated 0.00127 [0.00050] min. nickel

**Notes:** 1. Environmental lubrication pre-applied  
2. RoHS compliant parts have tin plated ACTION PIN posts



Slim UPM Plug



#### Related Product Data

**Durability** — 250 cycles

**Guiding Hardware (Optional)** — pages 58 and 59

**Seating Tooling** —  
**Header**

Seating Tool 224441-X

Board Support Fixture 224442-1

**Receptacle**

Seating Tool 224421-X

Board Support Fixture 217602-1

#### Technical Documents

##### Product Specification

108-1651

##### SLIM UPM Product Specification

108-78387

##### Application Specification

114-1103

##### Instruction Sheet

408-4169 (Receptacle

Seating Tool 224421-X)

| Number of Positions | Dimension L  | Standard Power 10 Amps/Contact Sequence* Pattern | Part Number | High Power 16 Amps/Contact Sequence* Pattern | Part Number |
|---------------------|--------------|--------------------------------------------------|-------------|----------------------------------------------|-------------|
| 3                   | .472 [12.0]  | L,L,L                                            | 5223961-1   | L,L,L                                        | 5-5223961-1 |
|                     |              | M,L,M                                            | 5223963-1   | M,L,M                                        | 5-5223963-1 |
| 4                   | .591 [15.0]  | **                                               | **          | **                                           | **          |
|                     |              | L,L,L,L                                          | 5646954-1   | L,L,L,L                                      | 120954-1    |
| 5                   | .709 [18.0]  | S,M,L,S                                          | 5646954-2   | L,M,S,S                                      | 120954-2    |
|                     |              | **                                               | **          | **                                           | **          |
| 6                   | .827 [21.0]  | L,L,L,L,L                                        | 5646955-1   | L,L,L,L,L                                    | 120955-1    |
|                     |              | M,M,M,M,L                                        | 5646955-2   | M,M,L,M,M                                    | 120955-2    |
| 7                   | .945 [24.0]  | **                                               | **          | **                                           | **          |
|                     |              | L,L,L,L,L,L                                      | 5646956-1   | L,L,L,L,L,L                                  | 120956-1    |
| 8                   | 1.063 [27.0] | L,M,M,M,M,L                                      | 5646956-2   | L,M,S,S,S,S                                  | 120956-2    |
|                     |              | **                                               | **          | **                                           | **          |
| 9                   | 1.163 [29.5] | L,L,L,L,L,L,L                                    | 5646957-1   | L,L,L,L,L,L,L                                | 120957-1    |
|                     |              | **                                               | **          | L,S,S,L,S,S,L                                | 120957-2    |
| 10                  | 1.263 [32.1] | L,L,L,L,L,L,L,L                                  | 5646958-1   | L,L,L,L,L,L,L,L                              | 120958-1    |
|                     |              | L,S,L,S,L,S,L,S                                  | 5646958-2   | L,M,S,S,S,S,S,S                              | 120958-2    |

\*Sequencing Reads left-to-right along mating face.

L (long) = 0.429 [10.9], M (medium) = 0.366 [9.3], S (short) = 0.302 [7.68]

\*\*Other sequence patterns available. See on-line customer drawing.

#### Slim UPM Right-Angle Plug

| Number of Positions | Width       | Part Number |
|---------------------|-------------|-------------|
| 4                   | 0.335 [8.5] | 1903977-1   |
|                     |             | 1903977-2   |

**Note:** All part numbers are RoHS compliant.

Catalog 1773096

Revised 4-12

www.te.com

Dimensions are shown for reference purposes only. Specifications subject to change.

Dimensions are in inches and millimeters unless otherwise specified.  
USA: +1 (800) 522-6752

Canada: +1 (905) 475-6222  
Mexico/C. Am.: +52 (0) 55-1106-0800  
Latin/S. Am.: +54 (0) 11-4733-2200  
Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666  
France: +33 (0) 1-3420-8686  
Netherlands: +31 (0) 73-6246-999  
China: +86 (0) 400-820-6015

## Universal Power Module (UPM) (Continued)

### Vertical Plug

#### Material and Finish

**Housing** — PBT

Natural color UL 94V-0

**Contacts** —

**Standard Power** —

Phosphor Bronze

**High Power** —

High Conductivity Copper Alloy

**Plating** — 0.00127 [0.00050] min. gold in mating area, 0.0050 [0.00020] min. tin-lead on ACTION PIN post area, with entire contact underplated 0.00127 [0.00050] min. nickel

**Notes:** 1. Environmental lubrication pre-applied  
2. RoHS compliant parts have tin plated ACTION PIN posts

#### Related Product Data

**Durability** — 250 cycles

**Guiding Hardware (Optional)** — pages 58 and 59

**Seating Tooling** —

**Header**


Seating Tool 224441-X

Board Support Fixture 224442-1

**Receptacle**

Seating Tool 224421-X

Board Support Fixture 217602-1



Recommended PCB Layout

| Number of Positions | Dimension L   | Part Numbers       |                    |
|---------------------|---------------|--------------------|--------------------|
|                     |               | 15 mm Stack Height | 18 mm Stack Height |
| 3                   | .470 [11.95]  | 1645498-1          | 1645499-1          |
| 4                   | .589 [14.95]  | 1645498-2          | 1645499-2          |
| 5                   | .707 [17.95]  | 1645498-3          | 1645499-3          |
| 6                   | .825 [20.95]  | 1645498-4          | 1645499-4          |
| 7                   | .943 [23.95]  | 1645498-5          | 1645499-5          |
| 8                   | 1.061 [26.95] | 1645498-6          | 1645499-6          |
| 9                   | 1.179 [29.95] | 1645498-7          | 1645499-7          |

# NEW

### “NEW” Low Profile Universal Power Module

#### Material and Finish


**Housing** — LCP

**Contacts** —


High Conductivity Copper Alloy

**Current Rating** —

18 Amps per contact



Right-Angle Plug  
Part Number 1982260-5



Vertical Receptacle  
Part Number 1982257-5

**Note:** All part numbers are RoHS compliant.

## Universal Power Module (UPM) (Continued)

### Vertical and Right-Angle Receptacles

#### Material and Finish

**Housing** — PBT

Natural color

UL 94V-0

**Contacts** —

**Standard Power** —



Phosphor Bronze

**High Power** —

High Conductivity Copper Alloy

**Plating** — 0.00127 (.000050) min. gold in mating area, 0.0050 (.000020) min. tin-lead on ACTION PIN post area, with entire contact underplated 0.00127 (.000050) min. nickel

**Notes:** 1. Environmental lubrication pre-applied  
2. RoHS compliant parts have tin plated ACTION PIN posts



#### Related Product Data

**Durability** — 250 cycles

**Mating Force** — 1.0N per contact

**Unmating Force** — .5N per contact

**Guiding Hardware (Optional)** — pages 58 and 59

**Seating Tooling** —

**Header**



Seating Tool 224441-X

Board Support Fixture 224442-1

**Receptacle**

Seating Tool 224421-X

Board Support Fixture 217602-1



**Right-Angle**  
**Part Number 120943**



**Part Number 1903978**

#### Technical Documents

**Product Specification**

108-1651 (UPM)

108-78387 (Slim UPM)

**Application Specification**

114-1103

**Instruction Sheet**

408-4169 (Receptacle)

Seating Tool 224421-X)

**New short PCB tail available.**  
**Contact TE for more information.**

| No. of Circuit Positions | Vertical                                          |                                               | Right-Angle                                   |
|--------------------------|---------------------------------------------------|-----------------------------------------------|-----------------------------------------------|
|                          | Standard Power<br>10 Amps/Contact<br>Part Numbers | High Power<br>16 Amps/Contact<br>Part Numbers | High Power<br>16 Amps/Contact<br>Part Numbers |
| 3                        | 5223955-2                                         | 5-5223955-2                                   | 120943-1                                      |
| 4                        | 5223995-1                                         | 120953-1                                      | 120943-2                                      |
| 5                        | 5223995-2                                         | 120953-2                                      | 120943-3                                      |
| 6                        | 5223995-3                                         | 120953-3                                      | 120943-4                                      |
| 7                        | 5223995-4                                         | 120953-4                                      | 120943-5                                      |
| 8                        | 5223995-5                                         | 120953-5                                      | 120943-6                                      |
| 9                        | 5223995-6                                         | 120953-6                                      | 120943-7                                      |



**Seating Tool**

#### Slim UPM Vertical Receptacle

| Number of Positions | Width          | Part Number            |
|---------------------|----------------|------------------------|
| 4                   | .236<br>[6.00] | 1903978-1<br>1903978-2 |

**Note:** All part numbers are RoHS compliant.

## Z-PACK 2 mm Futurebus+ Power Modules

### Vertical Pin Assemblies with Solder Leads and Compliant Press-Fit Leads

#### Material and Finish

**Housing** — Liquid crystal polymer

**Pin Contacts** — Phosphor bronze, mating surface plating conforms to all testing specified for Telcordia Uncontrolled Environment, with entire contact underplated with 0.00127 min. nickel. See customer drawing for specific lead plating.

#### Related Product Data

**Current Rating** — 5 Amps per contact

**Mating Force** — 2.4N per contact max.

**Unmating Force** — 0.3N per contact max.

**Durability** — 250 cycles

#### Technical Documents

##### Product Specification


108-1441

##### Application Specification


114-1075

##### Instruction Sheets


408-6927, 408-4157, 408-4488




4 Row




5 Row




Solder Leads



Solder Leads



Recommended PC Board Hole Layout per IPC-D-300, Type II, Class C (Component Side)



Recommended PC Board Hole Layout per IPC-D-300, Type II, Class C (Component Side)

<sup>1</sup>Dimensions apply to solder lead versions only.

<sup>1</sup>Dimensions apply to solder lead versions only.

Reference specification 114-1075 for plated through hole requirements.



| Number of Positions | Mating Post Lengths | Part Numbers     |                 |           |                |
|---------------------|---------------------|------------------|-----------------|-----------|----------------|
|                     |                     | 4.25 Solder Lead | 3.2 Solder Lead | Press-Fit | Housing Shroud |
| 8                   | .256 [6.50]         | 5536600-1        | 5536628-1       | 5536603-1 | 536565-X       |
|                     | .285 [7.25]         | 5536625-1        | —               | —         |                |
|                     | .315 [8.00]         | 5536623-1        | —               | 5536620-1 |                |
| 10                  | .256 [6.50]         | —                | —               | 5536642-1 | 223041-X       |
|                     | .315 [8.00]         | —                | —               | 5536642-7 |                |

**Note:** All part numbers are RoHS compliant.

## Z-PACK 2 mm Futurebus+ Power Modules (Continued)

### Right-Angle Receptacle Assemblies with Solder Leads and Compliant Press-Fit Leads

#### Material and Finish

**Housing** — Liquid crystal polymer


**Receptacle Contacts** — Phosphor bronze, mating surface plating conforms to all testing specified for Telcordia Uncontrolled Environment, with entire contact underplated with 0.00127 min. nickel. See customer drawing for specific lead plating.

#### Technical Documents


**Product Specification**  
108-1441

**Application Specification**  
114-1075




**Instruction Sheets**  
408-6927




4 Row



5 Row



Recommended PC Board Hole Layout  
per IPC-D-300, Type II, Class C  
(Component Side)



Recommended PC Board Hole Layout  
per IPC-D-300, Type II, Class C  
(Component Side)

Reference specification 114-1075 for plated through hole requirements.



| Number of Positions | Part Numbers       |              |                           | Seating Tool                |
|---------------------|--------------------|--------------|---------------------------|-----------------------------|
|                     | Solder Tail Length |              | Press-Fit<br>0.140 [3.56] |                             |
|                     | 0.107 [2.73]       | 0.139 [3.53] |                           |                             |
| 8                   | 5536607-1          | 5536613-1    | 5536614-1                 | Industry Standard Flat Rock |
| 10                  | 5223092-1          | 5223093-1    | 5536649-1                 | Industry Standard Flat Rock |



**Note:** All part numbers are RoHS compliant.

## Backplane and Co-Planar Guide Modules

### Un-keyed Guide Modules

Stainless Steel Pin  
Die Cast Receptacle  
Multiple thread lengths available  
Gatherability +/-0.100"

Seating Tool — Part Number 224440-1  
Board Support Fixture —  
Part Number 217603-1



Vertical Guide




Vertical Spacer

| Type                        | Dim. L        | Part Number        |                                            |                       |                        |
|-----------------------------|---------------|--------------------|--------------------------------------------|-----------------------|------------------------|
|                             |               | Vertical Guide Pin | Right-Angle Guide Module                   | Vertical Guide Module | Vertical Spacer Module |
| M4, 6.2 mm Thread Length    | 1.235 [31.36] | 223956-1           | 5223957-1<br>(As Shown)                    | 1934988-1             | 1645545-1<br>(15 mm)   |
| M4, 7.5 mm Thread Length    | 1.269 [32.23] | 223982-1           |                                            |                       |                        |
| M4, 12.7 mm Thread Length   | 1.491 [37.86] | 223969-1           | 5223979-1<br>(with Dual Mounting Position) |                       | 1645545-2<br>(18 mm)   |
| 8-32, 12.7 mm Thread Length | 1.491 [37.86] | 223969-4           |                                            |                       |                        |
| M4, 9.2 mm Thread Length    | 1.353 [34.36] | 223969-7           |                                            |                       |                        |
| M4, Internal Thread         | 1.378 [35.00] | 1857988-1          |                                            |                       |                        |

### Keyed Guide Modules


Die Cast Pin and Receptacle  
Keyed to prevent mis-mating daughter cards  
Multiple thread lengths available  
Gatherability +/-0.100"



| Type | Part Number              |           |              |
|------|--------------------------|-----------|--------------|
|      | Right-Angle Guide Module |           | Vertical Pin |
|      | 4-40                     | M2.5      |              |
| 0°   | 5223986-1                | 5120913-1 | 5223985-1    |
| 90°  | 5223986-3                | 5120913-3 |              |
| 180° | 5223986-5                | 5120913-5 |              |
| 225° | 5223986-6                | 5120913-6 |              |

### AdvancedTCA Guide Modules

Die Cast Pins and Receptacles  
Keyed to prevent mis-mating daughter cards  
Twin Pins — provide more keying options  
Meets PICMG 3.0 Specifications  
Gatherability +/-0.50"



| Type                     | Part Number        |                                         |            | AdvancedTCA Module Designation |
|--------------------------|--------------------|-----------------------------------------|------------|--------------------------------|
|                          | Both Pins Keyed 0° | Top Pin Keyed 270° Bottom Pin Keyed 90° | Not Keyed  |                                |
| Right-Angle Pin Long     | 1-1469372-1        | 3-1469372-7                             | —          | A2                             |
| Vertical Pin Short       | 1-1469387-1        | 3-1469387-7                             | —          | A1                             |
| Vertical Pin Long        | 1-1469388-1        | 3-1469388-7                             | —          | A2                             |
| Right-Angle Receptacle   | 1-1469373-1        | 3-1469373-7                             | 1469374-1  | K1/K2                          |
| Single Pin Rear Assembly | —                  | —                                       | 1469269-X* | rK1                            |

\*-X identified by PCB thickness. See customer drawing for details.

AdvancedTCA is a trademark of  
PICMG-PCI Industrial Computer  
Manufacturers Group, Inc.

**Note:** All part numbers are RoHS compliant.

## Backplane and Co-Planar Guide Modules (Continued)

### 10.8 Guide Modules

Rugged design — to support heavier cards

Better gatherability +/-3.5 mm


10.8 mm width

Die Cast Pin

Die Cast Receptacle

ESD Ground Option

Finish: Nickel plated



| Type | Part Number |             |                      |                    |
|------|-------------|-------------|----------------------|--------------------|
|      | Right-Angle |             | Vertical Pin         |                    |
|      | With ESD    | Without ESD | Internal M3.5 Thread | External M5 Thread |
| 0    | 1-1410297-1 | 1-1410546-1 |                      |                    |
| 90   | 1-1410297-3 | 1-1410546-3 |                      |                    |
| 180  | 1-1410297-5 | 1-1410546-5 | 1410548-3            | 1-1410773-2        |
| 225  | 1-1410297-6 | 1-1410546-6 |                      |                    |

\*See customer drawing for dash numbers

### 9.0 VITA 46 Guide Modules


Die Cast Pins and Receptacles

Keyed to prevent mis-mating daughter cards

Meets VITA 46 Specification

Gatherability +/-3.5 mm

Finish: Silver plated



| Type         | Part Number |
|--------------|-------------|
| Double-Ended | 1410956-1   |

| Type     | Part Number  |                           |             |             |
|----------|--------------|---------------------------|-------------|-------------|
|          | Right-Angle* | Vertical Pin Thread Depth |             |             |
|          |              | 10 mm                     | 11.6 mm     | 13.1 mm     |
| 0°       | 1-1469492-1  |                           |             |             |
| 45°      | 1-1469492-2  |                           |             |             |
| 90°      | 1-1469492-3  |                           |             |             |
| 270°     | 1-1469492-7  | 1-1469491-2               | 1-1469491-3 | 1-1469491-4 |
| 315°     | 1-1469492-8  |                           |             |             |
| Un-keyed | 1-1469492-9  |                           |             |             |

\*Mounting screw Part Number 1410946-X required


### VITA 41 Guide Modules

Die Cast Pins and Receptacles

Meets VITA 41 Specification

Gatherability +/-2 mm

Finish: Clear Chromate



| Key  | Part Number        |                   |                    |
|------|--------------------|-------------------|--------------------|
|      | Vertical Short Pin | Vertical Long Pin | Right-Angle Module |
| 0°   | 1410962-1          | 1410963-1         | 1410465-1          |
| 270° | 1410962-7          | 1410963-7         | 1410465-7          |


### 7.2 Thin Guide Modules

Die Cast Pin and Receptacle

7.2 mm width

Gatherability +/-2.5 mm

Finish: Trivalent Chromium



| Right-Angle | Part Number                |             |
|-------------|----------------------------|-------------|
|             | Vertical Pin Thread Length |             |
|             | 8.7 mm                     | 11.6 mm     |
|             | 1410714-3                  | 1-1410710-1 |
|             |                            | 1-1410710-3 |

**Note:** All part numbers are RoHS compliant.

## Z1 Power Connector for AdvancedTCA Zone 1 Applications

### Product Facts

- Designed to PICMG 3.0 Standard
- High conductivity copper alloy on Size 16 power contacts
- .76 micro-meters [30 microinch] gold over 1.27 micrometers [50 microinch] nickel plating at contact interface
- Gold-thickness controlled on inside of socket and outside of pin — at contact interface points
- RoHS compliant
- Stainless steel spring provides contact normal force — resists relaxation at elevated temperatures
- Eye of the needle compliant press-fit termination
- No special tools needed to seat connectors to PCB — standard Flat-Rock seating tools
- Additional PCB retention hardware not required

### Technical Documents

#### Product Specification


108-2216

#### Application Specification

114-13156

#### Industry Standard

PICMG 3.0, Rev. 2.0



### Introduction

TE supplies both the power and the signal connectors specified in the Advanced Telecommunications Computer Architecture (AdvancedTCA) Standard. This standard (PICMG 3.0) is one of the latest standards addressing future telecommunications needs. The AdvancedTCA Power Connector, designated for use in Zone 1 per PICMG 3.0, combines 8 High Conductivity Size 16 pin & socket contacts along with 22 Size 22 pin & socket contacts, plus guidance into a compact interface. Both connector halves feature proven compliant press-fit contacts for easy solder-less termination to printed circuit boards.

Based on years of reliable long-term field installations the power contact design is based upon TE's famous Type III+ contact design. By adding the use of a high conductivity copper alloy and the low-force Eye-Of-Needle compliant pin sec-

tion, the new contact delivers both ease of installation (with flat-rock seating tools) as well as industry-leading current carrying capability. The power contacts are capable of carrying 20 amps per contact and the signals are capable of carrying 2 amps per contact.

The housing design also offers improvements compared to other industry alternatives. The lead-in design for the contact cavities provides better resistance from contact stubbing. The contact retention has also been designed to eliminate the need for additional hardware sometimes used to hold the connectors to the PCB after pressing in to the PCB.

The result is a connector which is easy to install, meets all the PICMG 3.0 performance requirements and stays retained to the PCB without the additional labor required to add hardware.

### Typical Electrical Properties

**Current Ratings** — tested in accordance with CSA C22.2 No. 182.3-M1987 and IEC 60512-3, Test 5a requirements:

Positions 1–24, 27, 32 — 1 Amp each, per the PICMG 3.0 Specification

Positions 25, 26, 28–31, and 34 — 20 Amps each, exceeds the PICMG 3.0 Specification

#### Dielectric Withstanding Voltage —

Positions 1–16 — 1000 Volts rms

Positions 17–24 — 2000 Volts rms

Positions 25–34 — 2000 Volts rms

### Environmental Parameters

#### Maximum Continuous Operating

**Temperature** — 105°C

**Durability Rating** — 250 cycles, per PICMG 3.0

AdvancedTCA and PICMG are trademarks of the PICMG-PCI Industrial Computer Manufacturers Group, Inc.

## Z1 Power Connector for AdvancedTCA Zone 1 Applications (Continued)

### Material and Finish

**Insulators** — Thermoplastic, glass reinforced, UL 94V-0



**Signal Pins** — Copper alloy

**Power Contacts** — High conductivity copper alloy, plated 0.00076 [.000030] min. gold in mating area over 0.00127 [.000050] min. nickel



**Compliant PCB Tails** — 0.0030 – 0.0043 [.000120 – .000170] tin plated, matte finish

### Notes:

1. Mounting hardware — self tapping screw (customer supplied) can be used but not required on receptacle
2. Positions 1–4 not populated and reserved for future use for 308 22 position connectors.



| Right-Angle Plug Part Number | Power Contacts | Signal Contacts | Tail Type      |
|------------------------------|----------------|-----------------|----------------|
| 1766502-1                    | 8              | 14              | Sn Press-Fit   |
| 1766502-2                    |                |                 | SnPb Press-Fit |
| 1766500-1                    |                | 22              | Sn Press-Fit   |
| 1766500-2                    |                |                 | SnPb Press-Fit |
| 1888803-1                    |                | 26              | Sn Press-Fit   |
| 1888803-2                    |                |                 | SnPb Press-Fit |



| Vertical Receptacle Part Number | Power Contacts | Signal Contacts | Tail Type      |
|---------------------------------|----------------|-----------------|----------------|
| 1766503-1                       | 8              | 14              | Sn Press-Fit   |
| 1766503-2                       |                |                 | SnPb Press-Fit |
| 1766501-1                       |                | 22              | Sn Press-Fit   |
| 1766501-2                       |                |                 | SnPb Press-Fit |
| 1888804-1                       |                | 26              | Sn Press-Fit   |
| 1888804-2                       |                |                 | SnPb Press-Fit |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors

### True Hot-Plug, Blind-Mating Mixed Signal and Power Connectors

#### Product Facts

- Wide variety of contact sizes and styles from 1 Amp signals up to power contacts rated at up to 200 Amps each
- Sequenced contacts for "mate-first-break-last" operation
- Floating panel-mount connectors float up to +/- 2 mm
- High durability specific products ranging from 100 to 1000 mate/un-mate cycles
- Customizable products allow the freedom to add or remove power or signal contacts to meet specific application requirement
- Most products recognized to US and Canadian requirements under the Component Recognition program of Underwriters Laboratories File No. E28476




#### Typical Applications

- Low noise power supplies
- Switch-mode power supplies (SMPS)
- Power factor-correcting (PFC) power supplies
- Systems requiring mounting to backplane or chassis
- Redundant (N + 1) power systems
- "Live" hot-plug power supplies
- All ELCON drawer connectors in this section are RoHS compliant

#### Technical Documents

**Product Specification**  
108-2285

**Application Specification**  
114-13206



TE offers a wide selection of blind-mateable "drawer" connectors to suit modular equipment designs. The term "drawer connector" was created to describe a cabinet drawer where the connector is installed at the back of the drawer and is mated by closing the drawer. Since the "drawer" is often times made with a somewhat loose fit — to enable easy opening and closing, the drawer connector must provide sufficient self-alignment and ideally a floating connection to the cabinet or drawer to keep the connection from binding.

The power drawer connectors in this catalog are divided into two separate categories: high power drawers and low power drawers. Specifically, the product line names in these two categories are:

#### High Power Drawer Connectors

- **ELCON Drawer Series Connectors**

#### Low Power Drawer Connectors

- **AMP Drawer Series Connectors**
  - **Mini Power Drawer**
  - **Blind-mate Drawer Connectors**
  - **Hybrid Mini Drawer Connectors**

Some of the benefits of the power drawer connectors from TE are the robustness of the housing designs and the durability of the contacts. High-end applications such as networking switches and servers want the lowest possible voltage drop across the connector. For these applications the high conductivity screw-machined contacts with either gold or silver plating offer the best performance. The contacts are the core

of the ELCON drawer series connectors. For cost sensitive applications the different hybrid drawer connectors offer a wide variety of shapes and sizes aimed at keeping cost minimized and still providing a reliable separable interface.

Regardless of the application, TE offers a wide variety of power & signal blind-mateable drawer connectors.

#### Need more information?


Call Technical Support at the numbers listed below.

Technical Support is staffed with specialists well versed in all TE products. They can provide you with:

- Technical Support
- Catalogs
- Technical Documents
- Product Samples
- TE Authorized Distributor Locations

## ELCON Drawer Series Connectors

### True Hot-Plug, Blind-Mating Mixed Signal and Power Connectors (Continued)



3 mm Diameter Test Probe in  
Accordance with IEC 435  
Protective Cap (insulator)

#### Probe-proof Double CROWN BAND Contacts

The size #0 contacts used in the Top Drawer, Double Drawer, DualPower and QuadPower connectors are also available in a probe-proof double CROWN BAND version. These contacts are specially suited for operator-serviced power supplies that require extra safety protection.

#### Signal/Power Sequencing

All signal and some power contacts are available in various lengths to allow multiple levels of sequencing, thus giving the engineer further design flexibility.

#### Mating Polarization

To provide for positive housing mating of connectors, polarization is provided in the form of molded-in guide posts or pre-installed guide pins.

#### Regulatory Agency Certifications

TE ELCON drawer series connectors have been evaluated and found to comply with the UL1977 standard and the CSA standard C22.2 No. 182.3-M1987.

TE can also work with the customer to obtain application-specific regulatory certifications if needed.



#### Wide Array of Standard Contacts

ELCON drawer connectors support various termination styles, including crimp for cable, solder tail and compliant press-fit for mounting

to PCB, and internal/external threads for termination to lugs and/or busbars. See table below for details.

| Contact Size | Termination |           |       |          |          |
|--------------|-------------|-----------|-------|----------|----------|
|              | PC Tail     | Press-fit | Crimp | Threaded |          |
|              |             |           |       | Internal | External |
| #20          | •           | •         | •     |          |          |
| #16          | •           | •         | •     |          |          |
| #12          | •           | •         | •     |          |          |
| #8           | •           | •         | •     | •        | •        |
| #4           |             |           | •     | •        | •        |
| #0           |             |           | •     | •        | •        |

#### Application-Specific Designs

If none of our standard drawer connectors satisfies your requirements, TE can develop an ELCON connector design specific to your application. We will work

closely with your engineers to fully understand the design requirements and develop an interconnect solution that meets your stated needs. After the con-

cept and design stages, TE produces prototypes that perform both electrically and mechanically the same as production parts. These machined parts are used for

testing, regulatory agency evaluations and even as pre-production components, allowing the shortest lead time from concept to manufacturing in the industry.

#### Concept

TE engineers work closely with the customer to fully understand the design requirements.



#### Design

A sketch drawing of the design concept is created for customer review, and the design is finalized only when it fully meets the requirements of the customer.




#### Prototypes

The design is frozen and work on the mold tools starts. Meanwhile, TE builds prototypes that are identical to the production parts.



#### Production

By the time the customer is ready for production, all requirements for release to production, such as qualification and regulatory agency approval, have been cleared.



## How to Tailor Your ELCON Drawer Connector

If you selected a standard drawer connector for your application, before placing an order you need to specify your application-specific requirements, such as housing type, contact loading, and termination style. Layout forms for all standard drawer connectors, such as the one shown below, are available online at <http://www.te.com> or can be obtained from TE customer service for this purpose.

Complete a form for the pin and socket side of your connector as indicated in the instructions and fax it to your TE sales engineer. We will issue a unique part number specific to your configuration, which you can then use to place orders. Samples and customer drawings are also available upon request.


### Pin Assembly

- Choose one housing from the **Pin Housing Selection Menu** table. Place an X in the appropriate guide pin circles, if guide pins are required.
- Write the total quantity of each pin contact you require for **each pin assembly** in the **Qty** column of the **Pin Contact Selection Menu** table.
- Crimp contacts are shipped uninstalled. Threaded and PCB tail contacts are installed by TE; enter the letter reference of the desired contact in the appropriate contact positions on the drawing: e.g., if you need a size #20 premate PCB tail standard contact to be installed in contact position #10, write "Q" in circle #10.
- Sign, date and send the completed form to your local TE Sales Engineer.

#### Pin Connector (Rear Face)

Pin Contact Insertion Side

Pin Connector Rear Face Cavity Identification



Top Assembly Part Number  
Assigned by TE

### ENTER CUSTOMER INFORMATION

|                                                                                                        |                          |
|--------------------------------------------------------------------------------------------------------|--------------------------|
| Company                                                                                                | Location                 |
| Contact Name                                                                                           | Title                    |
| Telephone                                                                                              | Fax                      |
| Email Address                                                                                          |                          |
| I am: <input type="checkbox"/> End user<br><input type="checkbox"/> Contract manufacturer (end user: ) |                          |
| Signature                                                                                              | Today's Date             |
|                                                                                                        | Annual Quantity Required |

Submit to your local TE Sales Engineer.

### Pin Housing Selection Menu

| Part Number | Description                           | Check One |
|-------------|---------------------------------------|-----------|
| 1648183-1   | Housing without guides                |           |
|             | Housing with guides (#6-32 thread)    |           |
|             | Housing with guides (M3 x 0.5 thread) |           |

### Pin Contact Selection Menu

| Size         | Ref. | Part Number | Termination Style & Pin Length      | Qty. |
|--------------|------|-------------|-------------------------------------|------|
| #0           | A =  | 1766811-1   | Crimp                               |      |
|              | B =  | 1766819-1   | Probe Proof, crimp                  |      |
|              | C =  | 1766230-1   | 1/4-20 Internal Thread              |      |
|              | D =  | 1766274-1   | M6 x 1 Internal Thread              |      |
|              | E =  | 1766269-1   | Probe Proof, 1/4-20 Internal Thread |      |
|              | F =  | 1766275-1   | Probe Proof, M6 x 1 Internal Thread |      |
|              | G =  | 1766268-1   | 1/4-20 External Thread              |      |
|              | H =  | 1766231-1   | M6 x 1 External Thread              |      |
|              | J =  | 1766270-1   | Probe Proof, 1/4-20 External Thread |      |
|              | K =  | 1766276-1   | Probe Proof, M6 x 1 External Thread |      |
| #20          | L =  | 1650155-1   | Crimp, standard                     |      |
|              | M =  | 1650161-1   | Crimp, premate                      |      |
|              | N =  | 1650162-2   | Crimp, postmate                     |      |
|              | P =  | 1650283-1   | PCB tail, standard                  |      |
|              | Q =  | 1650065-1   | PCB tail, premate                   |      |
|              | R =  | 1650226-1   | PCB tail, postmate                  |      |
| #16          | S =  | 1766196-1   | Crimp, standard                     |      |
|              | T =  | 1766198-1   | Crimp, premate                      |      |
|              | U =  | 1766199-2   | Crimp, postmate                     |      |
|              | V =  | 1766222-1   | PCB tail, standard                  |      |
|              | W =  | 1766223-1   | PCB tail, premate                   |      |
|              | X =  | 1766818-1   | PCB tail, postmate                  |      |
| #12          | Y =  | 1766193-1   | Crimp, standard                     |      |
|              | Z =  | 1766195-1   | Crimp, premate                      |      |
|              | AA = | 1766196-1   | Crimp, postmate                     |      |
|              | AB = | 1766245-1   | PCB tail, standard                  |      |
|              | AC = | 1766250-1   | PCB tail, premate                   |      |
|              | AD = | 1766249-1   | PCB tail, postmate                  |      |
| #12 Hot-Plug | AE = | 1650153-2   | Crimp, standard, Hot-Plug           |      |
|              | AF = | 1650156-2   | Crimp, premate, Hot-Plug            |      |
|              | AG = | 1650060-2   | PCB tail, standard, Hot-Plug        |      |
|              | AH = | 1650074-3   | PCB tail, premate, Hot-Plug         |      |

Crimp and Threaded contacts are removable. PCB tail contacts are non-removable.

### Float-Mount Shoulder Screw

| Part Number | Description            | Qty. |
|-------------|------------------------|------|
| 1650399-1   | Screw, No 10-32 UNC 2A |      |
| 1650401-1   | Screw, M5 x 0.8        |      |


## ELCON Drawer Connector Mounting

All ELCON drawer series connectors can be fix-mounted or float-mounted using the designated shoulder screws to allow improved gatherability for blind-mating of the connector. Panel cut out dimensions are shown on the customer drawing specific to your ELCON drawer connector.

### Panel Float Mounting

When float-mounting to a panel or chassis, use the stainless steel shoulder screws specified in the layout sheet or customer drawing specific to your ELCON drawer connector. Shown in the sketch below is an example of how the Top Drawer connector is float-mounted to a panel.

Float-Mount of Top Drawer (Example)



| Screw Description      | Part Number | Used On                                                                 |
|------------------------|-------------|-------------------------------------------------------------------------|
| #10-32 UNF 2A Thread   | 1650399-1   | Top and Double Drawer, Dual and QuadPower, In-Line QuadPower, W5 Drawer |
| M5 x 0.8 Metric Thread | 1650401-1   |                                                                         |
| #8-32 UNF 2A Thread    | 1650402-1   |                                                                         |
| #6-32 UNF 2A Thread    | 1650106-1   | All Other Drawers                                                       |
| M4 x 0.7 Metric Thread | 1650589-1   |                                                                         |

### Panel Fix Mounting

As a rule of thumb, ELCON drawer connectors can be fix-mounted to a panel, in two ways: (1) by attaching a screw through the top and bottom mounting flange of the housing; or (2) by attaching a screw into a threaded guide pin (for those connectors that have one). An example of each case is shown in the sketches below.



#### Screw Through Mounting Flange of Housing

Fix to the panel by attaching a commercially available screw and a washer through the top and bottom mounting flange of the housing.



#### Screw Into Thread of Guide Pin (When Applicable)

You can optionally fix-mount housings that have a guide pin by attaching a commercially available screw and washer into the thread on the back of the guide pin, as shown in the figures below.




**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Connector Mounting (Continued)

### Strain Relief and Wire Dress


If required, wires can be bundled together and supported with cable ties. Wires must not be stretched or confined in any way that would restrict the floating action of the connectors. Therefore, the wires must remain perpendicular to the connector and avoid an excessively sharp bend radius. The minimum recommended distance for the cable tie, and the minimum bend radius of a wire bundle are shown in the figure to the right.




### PCB Fix Mounting

When mounting to a PC board, the connector standoffs must be seated on the board. Hold-downs are recommended to provide stability during the soldering procedure. PCB-mount hole patterns are shown on the customer drawing specific to your ELCON drawer connector.

Flush PCB-Mount Drawer Connectors





Drawer Connectors with Cabled AC IN




### Connector Engagement

To provide for proper mating of the connector when the power supply unit is fully engaged into the system, the gap between the pin and socket (shown as dimension "A" in the sketch below) must be within the limit specified in the customer drawing for your ELCON drawer connector. Failure to meet this requirement may compromise contact wipe. Refer to the customer drawing for details. ELCON drawer connectors are polarized and will only mate in the correct orientation (see sketch below).



## ELCON Drawer Connector Tooling

**Insertion/Removal (I/R) Tools:** Industry standard plastic I/R tooling is compatible with all crimp contacts for pin and socket removal. The following tools are available from TE.




### I/R Tools

| Part Numbers | Size                 | Color Code   |
|--------------|----------------------|--------------|
| 1643917-1    | Size #20 I/R tool    | Red/White    |
| 1643916-1    | Size #16 I/R tool    | Blue/White   |
| 1643915-1    | Size #12 I/R tool    | Yellow/White |
| 1643914-1    | Size #8 removal tool | Red          |
| 1643922-1    | Size #4 removal tool | Blue         |
| 1643921-1    | Size #0 removal tool | Light Yellow |

**Note:** PCB tail contacts are non-removable.

**Wire strip length:** If inserting stranded wire into crimp style contacts, please use the table below to determine the proper strip length of the wire.



| Contact Size | Wire Size AWG | "L" + .020 [0.51] |       |
|--------------|---------------|-------------------|-------|
|              |               | inches            | mm    |
| #20          | #24 - #20     | 0.210             | 5.33  |
| #16          | #20 - #16     | 0.270             | 6.86  |
| #12          | #14 - #12     | 0.270             | 6.86  |
| #8           | #10* - #8     | 0.500             | 12.70 |
| #4           | #6* - #4      | 0.500             | 12.70 |
| #0           | #2* - #0      | 0.600             | 15.24 |

\*Ref: MS3348 "Contact Bushing, Electric, Wire Barrel"

**Crimp Tools:** The following table lists applicable MIL-STD crimp tools for contacts



| Size    | Type                | MIL-STD      | Part Number |
|---------|---------------------|--------------|-------------|
| 12 - 24 | Crimp Tool          | M22520/1-01  | 601967-1    |
|         | Turret head/locator | M22520/1-02  | 601967-2    |
| 8 - 10  | Crimp Tool          | M22520/23-01 | —           |
|         | Indenter head       | M22520/23-02 | —           |
|         | Locator             | M22520/23-09 | —           |
| 4       | Crimp Tool          | M22520/23-01 | —           |
|         | Indenter head       | M22520/23-04 | —           |
|         | Locator             | M22520/23-11 | —           |
| 0       | Crimp Tool          | M22520/23-01 | —           |
|         | Indenter head       | M22520/23-05 | —           |
|         | Locator             | M22520/23-13 | —           |

**Crimp Termination Wire Sizes:** The following table shows crimp rear release contacts and their respective wire sizes when crimped with applicable industry standard terminal tools.

| Contact Size | Wire Range       |                 |
|--------------|------------------|-----------------|
|              | AWG              | mm <sup>2</sup> |
| #20          | 20 - 24          | 0.241 - 0.616   |
| #16          | 16 - 18          | 0.963 - 1.23    |
| #12          | 12 - 14          | 1.94 - 2.98     |
| #8           | 10 - 8           | 4.74 - 8.61     |
| #4           | 4 <sup>(1)</sup> | 21.60           |
| #0           | 1/0              | 53.00           |

**Note:** <sup>(1)</sup> Consult TE for smaller wire sizes in #4 contacts

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Product Specifications

| Materials                                                 |                                                       |                |         |
|-----------------------------------------------------------|-------------------------------------------------------|----------------|---------|
| Housing                                                   | Polyester, 30% glass-filled, UL 94V-0 black           |                |         |
| Crimp Contacts                                            | High conductivity copper alloy                        |                |         |
| PCB Tails                                                 | Brass                                                 |                |         |
| Socket Contact Hoods (when applicable)                    | 305 corrosion resistant steel                         |                |         |
| Size #12 hoods, Hot-Plug                                  | Beryllium copper                                      |                |         |
| Crown contacts                                            | Beryllium copper                                      |                |         |
| Plating                                                   |                                                       |                |         |
| Size #20 and #12HP                                        | Gold plated over nickel                               |                |         |
| Sizes #0, #4, #8, #16 and non-HP #12                      | Silver plated over nickel                             |                |         |
| Hot-Plug hoods and pin contacts                           | Gold plated over nickel                               |                |         |
| Socket Contact Hoods (when applicable)                    | Passivated                                            |                |         |
| Mechanical                                                |                                                       |                |         |
| Typical<br>Insertion Forces<br>of individual<br>contacts  | Size #20                                              | 0.2 lb.        | 0.09 kg |
|                                                           | Size #16                                              | 2.3 lb.        | 1.04 kg |
|                                                           | Size #12                                              | 2.9 lb.        | 1.32 kg |
|                                                           | Size #12 Hot-Plug                                     | 2.9 lb.        | 1.32 kg |
|                                                           | Size #8                                               | 4.4 lb.        | 2.00 kg |
|                                                           | Size #4                                               | 3.8 lb.        | 1.72 kg |
|                                                           | Size #0                                               | 4.7 lb.        | 2.13 kg |
|                                                           | Size #0 w/double Crown                                | 4.8 lb.        | 2.18 kg |
| Typical<br>Extraction Forces<br>of individual<br>contacts | Size #20                                              | 0.1 lb.        | 0.05 kg |
|                                                           | Size #16                                              | 0.7 lb.        | 0.32 kg |
|                                                           | Size #12                                              | 1.9 lb.        | 0.86 kg |
|                                                           | Size #12 Hot-Plug                                     | 1.9 lb.        | 0.86 kg |
|                                                           | Size #8                                               | 2.4 lb.        | 1.07 kg |
|                                                           | Size #4                                               | 3.0 lb.        | 1.36 kg |
|                                                           | Size #0                                               | 3.0 lb.        | 1.36 kg |
|                                                           | Size #0 w/double Crown                                | 3.5 lb.        | 1.59 kg |
| Electrical                                                |                                                       |                |         |
| Typical<br>Voltage drop<br>of individual<br>contacts      | Size #20                                              | 1.7 mV at 5A   |         |
|                                                           | Size #16                                              | 3 mV at 15A    |         |
|                                                           | Size #12                                              | 4.2 mV at 35A  |         |
|                                                           | Size #12 Hot-Plug                                     | 4.7 mV at 35A  |         |
|                                                           | Size #8                                               | 6.5 mV at 75 A |         |
|                                                           | Size #4                                               | 8.4 mV at 125A |         |
|                                                           | Size #0                                               | 6.3 mV at 200A |         |
|                                                           | Size #0 w/double Crown                                | 5.6 mV at 200A |         |
| Insulator dielectric strength                             | 1,500 VDC for 1 minute, per MIL-STD 1344, Method 3001 |                |         |

## Regulatory Agency Evaluations

| Contacts                            | CSA-22.2 No. 0-M91 182.30<br>M1987 (CNR) | UL 498 and UL 1977 (USR)   |
|-------------------------------------|------------------------------------------|----------------------------|
| AWG #20                             | 4A / 250V                                | 5A / 250V                  |
| AWG #16                             | 10A / 250V                               | 15A / 250V                 |
| AWG #12 Top Drawer                  | 25A / 600V                               | 35A / 600V                 |
| AWG #12 Others                      | 25A / 250V                               | 35A / 250V                 |
| AWG #12 with sockets                | 25A / 250V                               | 35A / 250V                 |
| Size #12 hot-plug                   | 25A / 250V                               | 25A / 250VAC<br>35A / 120V |
| Size #8                             | 55A / 250V                               | 75A / 250V                 |
| Size #0 with single or double Crown | 150A / 250V                              | 200A / 250V                |
| Size #0 using bus bar               | —                                        | 200A / 250V                |
| Size #4                             | 100A / 250V                              | 125A / 250V                |

## ELCON Drawer Series Connectors

### Mini Drawer

#### Dimensions —

2.99" x 0.79" (75.9 x 20.1 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

#### Available Contacts —

Size 12 / 16 x 6 contacts

Size 20 x 16 contacts

**Current Rating** — Up to 35 Amps per size 12 contact

**Contact Features** — Hot-Plug size 12 contact option


**Contact Sequencing** — Multi-level for power and signal

#### Contact Terminations —

Size 12: Crimp and PCB tail

Size 16: Crimp and PCB tail

Size 20: Crimp and PCB tail



### Base Housing Part Numbers

| Pin Housing |                             | Socket Housing |                             |
|-------------|-----------------------------|----------------|-----------------------------|
| 1648110-1   | Size 12 + Size 20 + Size 12 | 1648115-1      | Size 12 + Size 20 + Size 12 |
| 1648111-1   | Size 16 + Size 20 + Size 16 | 1648116-1      | Size 16 + Size 20 + Size 16 |
| 1648112-1   | Size 12 + Size 20 + Size 16 | 1648117-1      | Size 12 + Size 20 + Size 16 |

### Lower Drawer

#### Dimensions —

3.26" x 1.34" (82.8 x 34.0 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

#### Available Contacts —

Size 12 / 16 x 8 contacts

Size 20 x 21 contacts

**Current Rating** — Up to 35 Amps per size 12 contact

**Contact Features** — Hot-Plug size 12 contact option


**Contact Sequencing** — Multi-level for power and signal

#### Contact Terminations —

Size 12: Crimp and PCB tail

Size 16: Crimp and PCB tail

Size 20: Crimp and PCB tail



### Base Housing Part Numbers

| Pin Housing |                             | Socket Housing |                             |
|-------------|-----------------------------|----------------|-----------------------------|
| 1648203-1   | Size 12 + Size 20 + Size 12 | 1648206-1      | Size 12 + Size 20 + Size 12 |
| 1648204-1   | Size 16 + Size 20 + Size 16 | 1648207-1      | Size 16 + Size 20 + Size 16 |
| 1648205-1   | Size 12 + Size 20 + Size 16 | 1648208-1      | Size 12 + Size 20 + Size 16 |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### 75A Middle Drawer

#### Dimensions —

3.31" x 1.31" (84.1 x 33.3 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

#### Available Contacts —

Size 8 x 4 contacts

Size 12 x 9 contacts

Size 20 x 24 contacts

**Current Rating** — Up to 75 Amps per size 8 contact

**Contact Features** — Hot-Plug size 12 contact option


**Contact Sequencing** — Multi-level for power and signal

#### Contact Terminations —

Size 8: Crimp, internal/external thread and PCB tail

Size 12: Crimp and PCB tail

Size 20: Crimp and PCB tail



### Base Housing Part Numbers

| Pin Housing |             | Socket Housing |                                      |
|-------------|-------------|----------------|--------------------------------------|
| 1648162-1   | Float-Mount | 6648167-1      | Float-Mount w/<br>reinforced housing |
| 1648163-1   | PCB-Mount   | 1648168-1      | PCB-Mount                            |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### 125A Middle Drawer

#### Dimensions —

3.15" x 1.31" (80.0 x 33.3 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

#### Available Contacts —

Size 4 x 2 contacts

Size 12 x 6 contacts

Size 20 x 32 contacts

**Current Rating** — Up to 125 Amps per size 4 contact

**Contact Features** — Hot-Plug size 12 contact option


**Contact Sequencing** — Multi-level for power and signal

#### Contact Terminations —

Size 4: Crimp and internal/external thread

Size 12: Crimp and PCB tail

Size 20: Crimp and PCB tail



### Base Housing Part Numbers

| Pin Housing |             | Socket Housing |             |
|-------------|-------------|----------------|-------------|
| 1648151-1   | Float-Mount | 1648156-1      | Float-Mount |
| 1648152-1   | PCB-Mount   | 1648157-1      | PCB-Mount   |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### 200A Middle Drawer

#### Dimensions —

3.31" x 1.31" (84.1 x 33.3 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

#### Available Contacts —

Size 4 x 2 contacts

Size 8 x 6 contacts

Size 12 x 3 contacts

Size 20 x 14 contacts

**Current Rating** — Up to 125 Amps per size 4 contact

**Contact Features** — Hot-Plug size 12 contact option

**Contact Sequencing** — Multi-level for power and signal


#### Contact Terminations —

Size 4: Crimp and internal/external thread

Size 8: Crimp, internal/external thread and PCB tail

Size 12: Crimp and PCB tail

Size 20: Crimp and PCB tail



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648134-1   | 1648135-1      |

### Square Drawer

#### Dimensions —

2.76" x 1.24" (70.1 x 31.5 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

#### Available Contacts —

Size 12 x 4 contacts

Size 20 x 36 contacts

**Current Rating** — Up to 35 Amps per size 12 contact


**Contact Features** — Hot-Plug size 12 contact option

**Contact Sequencing** — Multi-level for power and signal

#### Contact Terminations —

Size 12: Crimp and PCB tail

Size 20: Crimp and PCB tail



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648132-1   | 1648133-1      |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### Top Drawer

#### Dimensions —

4.24" x 1.60" (107.8 x 40.7 mm)

**Housing Variations** — Various guide pin configurations available.

#### Guides and Polarization —

Optional Steel Guide Pins with either #6-32 or M3 internal thread

#### Available Contacts —

Size 0 x 2 contacts  
Size 12 x 6 contacts  
Size 16 x 12 contacts  
Size 20 x 32 contacts


**Current Rating** — Up to 200 Amps per size 0 contact

**Contact Features** — Hot-Plug size 12 contact option  
Probe-proof size 0 contact option

**Contact Sequencing** — Multi-level for power and signal

#### Contact Terminations —

Size 0: Crimp and internal/external thread  
Size 12: Crimp and PCB tail  
Size 16: Crimp and PCB tail  
Size 20: Crimp and PCB tail



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648183-1   | 1648186-1      |

Optional guide posts are available for improved alignment. Consult Customer Service for details.

### Double Drawer

**Dimensions** — 4.24" x 1.60" (107.8 x 40.7 mm)

**Housing Variations** — Various guide pin configurations available.

**Guides and Polarization** — Optional Steel Guide Pins with either #6-32 or M3 internal thread

#### Available Contacts —

Size 0 x 4 contacts  
Size 12 x 11 contacts  
Size 20 x 24 contacts


**Current Rating** — Up to 200 Amps per size 0 contact

**Contact Features** — Hot-Plug size 12 contact option  
Probe-proof size 0 contact option

**Contact Sequencing** — Multi-level for power and signal

#### Contact Terminations —

Size 0: Crimp and internal/external thread  
Size 12: Crimp and PCB tail  
Size 20: Crimp and PCB tail



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648552-1   | 1648578-1      |

Optional guide posts are available for improved alignment. Consult Customer Service for details.

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### DualPower Drawer

#### Dimensions —

1.80" x 1.60" (45.7 x 40.7 mm)

**Housing Variations** — Various guide pin configurations available.

#### Guides and Polarization —

Optional Steel Guide Pins with either #6-32 or M3 internal thread

**Available Contacts** — Size 0 x 2 contacts


**Current Rating** — Up to 200 Amps per contact

**Contact Features** — Probe-proof size 0 contact option

**Contact Sequencing** — Standard only

#### Contact Terminations —

Size 0: Crimp and internal/external thread



### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648549-1   | 1648575-1      |

Optional guide posts are available for improved alignment. Consult Customer Service for details.

### QuadPower Drawer

#### Dimensions —

2.50" x 1.60" (63.5 x 40.7 mm)

**Housing Variations** — Various guide pin configurations available.

#### Guides and Polarization —

Optional Steel Guide Pins with either #6-32 or M3 internal thread

**Available Contacts** — Size 0 x 4 contacts


**Current Rating** — Up to 200 Amps per contact

**Contact Features** — Probe-proof size 0 contact option

**Contact Sequencing** — Standard only

#### Contact Terminations —

Size 0: Crimp and internal/external thread



### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648548-1   | 1648574-1      |

Optional guide posts are available for improved alignment. Consult Customer Service for details.

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### In-Line QuadPower Drawer

**Dimensions** —

4.84" x 1.21" (122.8 x 30.7 mm)

**Housing Variations** — See Part Numbers


**Guides and Polarization** — Built in

**Available Contacts** — Size 0 x 4 contacts

**Current Rating** — Up to 200 Amps per contact

**Contact Features** — Probe-proof size 0 contact option

**Contact Sequencing** — Standard only

**Contact Terminations** —  
Size 0: Crimp and internal/external thread


### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 6651493-1   | 6651494-1      |

### W5 Power Drawer

**Dimensions** —

3.00" x 1.18" (76.2 x 30.0 mm)

**Housing Variations** — See Part Numbers


**Guides and Polarization** — Built in

**Available Contacts** — Size 4 x 5 contacts

**Current Rating** — Up to 100 Amps per contact

**Contact Features** — Probe-proof size 0 contact option

**Contact Sequencing** — Standard only

**Contact Terminations** —  
Size 4: Crimp and internal/external thread


### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 6651457-1   | 6651458-1      |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### P3S0 Drawer

**Dimensions —**

0.99" x 0.95" (25.0 x 24.0 mm)

**Housing Variations —** See Part Numbers

Cable Socket to Panel-Mount Pin

**Guides and Polarization —**

Polarization only

**Available Contacts —** Size 12 x 3 contacts




**Current Rating —** Up to 35 Amps per size 12 contact

**Contact Features —** Hot-Plug size 12 contact option

**Contact Sequencing —** Multi-level for power

**Contact Terminations —**

Size 12: Crimp only



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1766447-1   | 1766448-1      |

### P4S0 Drawer

**Dimensions —**

1.34" x .76" (34.0 x 19.4 mm)

**Housing Variations —** See Part Numbers

Cable Pin to PCB-Mount Socket

**Guides and Polarization —**

Polarization only




**Available Contacts —** Size 12 x 4 contacts

**Current Rating —** Up to 35 Amps per size 12 contact

**Contact Sequencing —** Standard only

**Contact Terminations —**

Size 12: Crimp Pin and PCB tail Socket

**Note:** Supplied as kit, including contacts


#### Base Housing Part Numbers

| Pin Side Kit | Socket Side Kit |
|--------------|-----------------|
| 6766014-1    | 6766015-1       |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### HV8P Drawer

**Dimensions** —

2.50" x 1.11" (63.5 x 28.2 mm)

**Housing Variations** — See Part Numbers

600 V High Voltage Design

**Guides and Polarization** — Built in

**Available Contacts** — Size 12 x 8 contacts


**Current Rating** — Up to 35 Amps per size 12 contact

**Contact Features** — Hot-Plug size 12 contact option

**Contact Sequencing** — Multi-level for power

**Contact Terminations** —

Size 12: Crimp and PCB tail



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648127-1   | 1648128-1      |

### P10S0 Drawer

**Dimensions** —

2.96" x 1.00" (75.0 x 25.4 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

**Available Contacts** — Size 12 x 10 contacts


**Current Rating** — Up to 35 Amps per size 12 contact

**Contact Features** — Hot-Plug size 12 contact option

**Contact Sequencing** — Multi-level for power

**Contact Terminations** —

Size 12: Crimp and PCB tail



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648568-1   | 1648596-1      |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### P6S18 Drawer

**Dimensions** —

5.45" x 1.35" (138.4 x 34.3 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

**Available Contacts** —

Size 4 x 6 contacts

Size 20 x 18 contacts

**Current Rating** — Up to 100 Amps per size 4 contact


**Contact Features** — Standard

**Contact Sequencing** — Multi-level for power and signal

**Contact Terminations** —

Size 4: Crimp and internal/external thread

Size 20: Crimp and PCB tail



### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 6766615-1   | 6651810-1      |

### P10S22 Drawer

**Dimensions** —

4.12" x 0.79" (104.5 x 20.1 mm)

**Housing Variations** — See Part Numbers

**Guides and Polarization** — Built in

**Available Contacts** —

Size 12 x 10 contacts

Size 20 x 22 contacts

**Current Rating** — Up to 35 Amps per size 12 contact


**Contact Features** — Hot-Plug size 12 contact option

**Contact Sequencing** — Multi-level for power and signal

**Contact Terminations** —

Size 12: Crimp and PCB tail

Size 20: Crimp and PCB tail



### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1648211-1   | 1648212-1      |

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Series Connectors (Continued)

### P12S12 Drawer

**Dimensions —**

4.31" x 0.70" (109.5 x 17.8 mm)

**Housing Variations —** See Part Numbers

**Guides and Polarization —** Built in

**Available Contacts —**

Size 16 x 12 contacts

Size 20 x 12 contacts

**Current Rating —** Up to 15 Amps per size 16 contact


**Contact Features —** Standard only

**Contact Sequencing —** Multi-level for power and signal

**Contact Terminations —**

Size 16: Crimp and PCB tail

Size 20: Crimp and PCB tail



#### Base Housing Part Numbers

| Pin Housing | Socket Housing |
|-------------|----------------|
| 1651202-1   | 1651203-1      |

### POS30 Drawer

**Dimensions —**

3.22" x 0.70" (81.8 x 17.8 mm)

**Housing Variations —** See Part Numbers

**Guides and Polarization —** Built in

**Available Contacts —** Size 20 x 30 contacts


**Current Rating —** Up to 5 Amps per size 20 contact

**Contact Features —** Standard only

**Contact Sequencing —** Multi-level for signal

**Contact Terminations —**

Size 20: Crimp and PCB tail



#### Base Housing Part Numbers


| Pin Housing | Socket Housing |
|-------------|----------------|
| 6651204-1   | 6651205-1      |

**Note:** All part numbers are RoHS compliant.


## ELCON Drawer Standard Contacts

The ELCON drawer series connectors use standard contacts across the product line. This section shows the standard contacts available in different sizes and various lengths and termination styles, with their respective part numbers.


### Pin Side Contacts




Contact Size #20




Contact Size #16



Contact Size #12



Contact Size #8



Contact Size #4

**Note:** All part numbers are RoHS compliant.

#### Contact Size #20 — For use in most drawer connectors

| Termination Type   | Contact Part Number | Dimensions                                                                          | A    |         |
|--------------------|---------------------|-------------------------------------------------------------------------------------|------|---------|
|                    |                     |                                                                                     | in   | mm      |
| Crimp, standard    | 1650155-1           |  | 0.32 | [8.12]  |
| Crimp, premate     | 1650161-1           |                                                                                     | 0.47 | [11.93] |
| Crimp, postmate    | 1650162-2           |                                                                                     | 0.27 | [6.85]  |
| PCB tail, standard | 1650283-1           |  | 0.32 | [8.12]  |
| PCB tail, premate  | 1650065-1           |                                                                                     | 0.47 | [11.93] |
| PCB tail, postmate | 1650226-1           |                                                                                     | 0.27 | [6.85]  |

#### Contact Size #16 — For use in Mini Drawer, Lower Drawer, Top Drawer, and P12S12

| Termination Type   | Contact Part Number | Dimensions                                                                          | A    |         |
|--------------------|---------------------|-------------------------------------------------------------------------------------|------|---------|
|                    |                     |                                                                                     | in   | mm      |
| Crimp, standard    | 1766194-1           |  | 0.33 | [8.38]  |
| Crimp, premate     | 1766198-1           |                                                                                     | 0.48 | [12.19] |
| Crimp, postmate    | 1766199-1           |                                                                                     | 0.29 | [7.36]  |
| PCB tail, standard | 1766222-1           |  | 0.33 | [8.38]  |
| PCB tail, premate  | 1766223-1           |                                                                                     | 0.48 | [12.19] |
| PCB tail, postmate | 1766818-1           |                                                                                     | 0.29 | [7.36]  |

#### Contact Size #12 — For use in Mini Drawer, Lower Drawer, 75A, 125A and 200A Middle Drawer; Square Drawer, TOP Drawer & Double Drawer; P3S0 and P4S0, HV8P, P10S0, P10S22

| Termination Type   | Contact Part Number |               | Dimensions                                                                            | A    |         |
|--------------------|---------------------|---------------|---------------------------------------------------------------------------------------|------|---------|
|                    | Gold Plated         | Silver Plated |                                                                                       | in   | mm      |
| Crimp, standard    | 1650153-2           | 1766193-1     |  | 0.43 | [10.92] |
| Crimp, premate     | 1650156-2           | 1766195-1     |                                                                                       | 0.46 | [11.68] |
| Crimp, postmate    | 1650158-2           | 1766196-1     |                                                                                       | 0.39 | [9.90]  |
| PCB tail, standard | 1650060-2           | 1766245-1     |  | 0.43 | [10.92] |
| PCB tail, premate  | 1650074-3           | 1766250-1     |                                                                                       | 0.46 | [11.68] |
| PCB tail, postmate | 1650073-3           | 1766249-1     |                                                                                       | 0.39 | [9.90]  |

**Note:** For applications using the #12 hot-plug socket use of gold plated pins are recommended.

#### Contact Size #8 - For use in 75A and 200 A Middle Drawer


| Termination Type   | Contact Part Number | Dimensions                                                                            | A    |         |
|--------------------|---------------------|---------------------------------------------------------------------------------------|------|---------|
|                    |                     |                                                                                       | in   | mm      |
| Crimp, standard    | 1766192-1           |  | 0.43 | [10.92] |
| Crimp, premate     | 1766197-1           |                                                                                       | 0.48 | [12.19] |
| Crimp, postmate    | 1766821-1           |                                                                                       | 0.33 | [8.38]  |
| PCB tail, standard | 1766262-1           |  | 0.43 | [10.92] |
| PCB tail, premate  | 1766263-1           |                                                                                       | 0.48 | [12.19] |

#### Contact Size #4 - For use in 125A and 200A Middle Drawer. P6S18 Drawer, W5 Power Drawer


| Termination Type                        | Contact Part Number | Dimensions                                                                            | A    |         |
|-----------------------------------------|---------------------|---------------------------------------------------------------------------------------|------|---------|
|                                         |                     |                                                                                       | in   | mm      |
| Crimp, Standard                         | 1766232-1           |  | 0.51 | [12.95] |
| 1/4 - 20 x .050 DP External Thread      | 1766812-1           |  | 0.51 | [12.95] |
| M5 x 0.8 x 9.6 mm DP M5 Internal Thread | 1766283-1           |  | 0.51 | [12.95] |

## ELCON Drawer Standard Contacts (Continued)

### Pin Side Contacts (Continued)



Contact Size #0



Contact Size #0  
Probe-proof

### Contact Size #0<sup>1</sup> - For use in Top Drawer, Double Drawer, DualPower & QuadPower, In-Line QuadPower


| Termination Type                                             | Contact Part Number | Dimensions                                                                          | A     |         |
|--------------------------------------------------------------|---------------------|-------------------------------------------------------------------------------------|-------|---------|
|                                                              |                     |                                                                                     | in    | mm      |
| Crimp                                                        | 1766811-1           |  | 0.495 | [12.57] |
| Probe-proof crimp <sup>2</sup>                               | 1766819-1           |                                                                                     | 0.430 | [10.92] |
| 1/4 - 20 x .050 DP Internal thread                           | 1766230-1           |                                                                                     | 0.495 | [12.57] |
| M6 x 1 x 12.7 mm DP Internal thread                          | 1766274-1           |  | 0.495 | [12.57] |
| 1/4 - 20 x .050 DP Probe-proof/internal thread <sup>2</sup>  | 1766269-1           |                                                                                     | 0.430 | [10.92] |
| M6 x 1 x 12.7 mm DP Probe-proof/internal thread <sup>2</sup> | 1766275-1           |                                                                                     | 0.430 | [10.92] |
| 1/4 - 20 x .050 DP External thread                           | 1766268-1           |  | 0.495 | [12.57] |
| M6 x 1 x 12.7 mm DP External thread                          | 1766231-1           |                                                                                     | 0.495 | [12.57] |
| 1/4 - 20 x .050 DP Probe-proof/external thread <sup>2</sup>  | 1766270-1           |                                                                                     | 0.430 | [10.92] |
| M6 x 1 x 12.7 mm DP Probe-proof/external thread <sup>2</sup> | 1766276-1           |                                                                                     | 0.430 | [10.92] |

**Notes:** <sup>1</sup>Contact TE for alternate contact terminations.


<sup>2</sup>Use only with probe-proof socket contacts.

<sup>3</sup>Crimp and threaded contact are insertable/removable.


### Socket Side Contacts



Contact Size #20



Contact Size #16



Contact Size #12

### Contact Size #20

| Termination Type | Contact Part Number |
|------------------|---------------------|
| Crimp            | 1648325-1           |
| PCB Tail         | 1648382-1           |

### Contact Size #16

| Termination Type | Contact Part Number |
|------------------|---------------------|
| Crimp            | 6648319-1           |
| PCB Tail         | 6648383-1           |

### Contact Size #12


| Termination Type  | Contact Part Number |
|-------------------|---------------------|
| Crimp             | 6648318-1           |
| Hot-Plug Crimp    | 1648384-1           |
| PCB Tail          | 6648374-1           |
| Hot-Plug PCB Tail | 1648387-1           |

**Note:** For applications using the #12 hot-plug socket, the use of gold plated pins are recommended (see page 80).

**Note:** All part numbers are RoHS compliant.

## ELCON Drawer Standard Contacts (Continued)


### Socket Side Contacts



Contact Size #8

#### Contact Size #8


| Termination Type | Contact Part Number |
|------------------|---------------------|
| Crimp            | 6648317-1           |
| PCB Tail         | 6648400-1           |



Contact Size #4

#### Contact Size #4

| Termination Type                        | Contact Part Number |
|-----------------------------------------|---------------------|
| Crimp, Standard                         | 6648434-1           |
| 1/4 - 20 x .050 DP External Thread      | 6648435-1           |
| M5 x 0.8 x 9.6 mm DP M5 Internal Thread | 6648335-1           |



Contact Size #0

#### Contact Size #0<sup>1</sup>

| Termination Type                                             | Contact Part Number |
|--------------------------------------------------------------|---------------------|
| Crimp                                                        | 6648405-1           |
| Probe-proof crimp <sup>2</sup>                               | 6648418-1           |
| 1/4 - 20 x .050 DP Internal thread                           | 6648416-1           |
| M6 x 1 x 12.7 mm DP Internal thread                          | 6648428-1           |
| 1/4 - 20 x .050 DP Probe-proof/internal thread <sup>2</sup>  | 6648419-1           |
| M6 x 1 x 12.7 mm DP Probe-proof/internal thread <sup>2</sup> | 6648429-1           |
| 1/4 - 20 x .050 DP External thread                           | 6648417-1           |
| M6 x 1 x 12.7 mm DP External thread                          | 6648430-1           |
| 1/4 - 20 x .050 DP Probe-proof/external thread <sup>2</sup>  | 6648420-1           |
| M6 x 1 x 12.7 mm DP Probe-proof/external thread <sup>2</sup> | 6648431-1           |

**Notes:** <sup>1</sup>Contact TE for alternate contact terminations.

<sup>2</sup>Use only with probe-proof Pin contacts.

<sup>3</sup>Crimp and threaded contact are insertable/removable.

### Non-Standard Contacts

Contacts with pin lengths and terminations other than standard are available. Consult customer service if your design requires contacts different from the ones shown in this catalog.

**Note:** All part numbers are RoHS compliant.

## AMP Miniature Power Drawer (MPD) Connectors

### Product Facts

- High mating cycle life
- Low Mating and Un-mating force (< 0.2lbs per contact)
- Single-piece molded housing
- Molded-in guide pins provide generous blind-mateability
- Sizes: 3 – 10 positions
- Compact size is ideal for distributed DC power applications
- Two Levels of contact sequencing
- One contact for either solder or press-fit termination
- Hardware — Less or traditional shoulder bolt mounting
- Minimum of 3 mm contact wipe on shortest power contact
- All MPD connectors in this section are RoHS compliant

### Specifications

Up to 16 Amps per contact  
 250 mating cycle durability  
 +/- 1.25 mm radial mis-alignment capability. (Total float is 2.5 mm!)

1.6 mm sequencing distance — ideal for modular sheet metal construction applications

Minimum of 3 mm contact wipe on shortest power contact

Maximum continuous operating temperature — 105°C

UL 94 V-0 High-temperature thermoplastic housings


### Technical Documents

#### Product Specification

108-1998

#### Application Specification

114-13067



The miniature power drawer connector combines a high density power interface in a blind-mateable wire-to-board connector. The MPD contact interface has been previously qualified to requirements similar to BellCore GR-1217 in board-to-board applications. Now available in a crimp-to-wire version, the contacts are rated for up to 15 Amps on 14 AWG wire. In addition, the MPD contacts are designed to meet UL 1977 hot-plug requirements for up to 7.8 Amps at 48VDC.

The connection consists of a vertical pcb mountable receptacle and a panel-mounted floating plug. The vertical receptacle pcb tails are designed for use in either through hole solder or press-fit applications. The float-mount plug is easily installed from the inside of the chassis without any additional hardware, lending itself to easy assembly of pre-made cable assemblies. Additionally, the staggered wire exit pattern permits the maximum number of contact interfaces in the least amount of connector volume.

The compact design is ideal for bringing power to small rack-mounted devices such as 1U computer servers and telecommunications switches. The 3 mm center-line satisfies UL 1977 safety requirements for 48 VDC distributed power applications. For higher voltage applications such as AC input, the contacts can be selectively loaded to handle up to 300 V AC or DC.

## AMP Miniature Power Drawer (MPD) Connectors (Continued)

### Crimp Contacts

#### Current Ratings

**Standard Power** — 10 Amps

**High Power** — 16 Amps

#### Material and Finish

**Standard Power:**

**Crimp Blade Contacts** — Brass

**Receptacle Contacts** —  
Phos. Bronze.

**Finish** — 0.38µm Gold over 1.27µm Nickel

**High Power:**

**Blades** — High Conductivity Cu Alloy

**Receptacle** — High Conductivity Cu Alloy

**Finish** — 1.27µm Gold over 1.27µm Nickel

**Contact Mating Length (Min.)** —


Type A — 4.6 mm

Type B — 3.0 mm

**Hot-Pluggability (With High Current Contacts only)** —

**250 Cycles** — 7.8 Amps @ 48VDC

**Note:** All contacts are Sn plated in the crimp barrel or Sn in pcb interface



**PRO-CRIMPER Hand Tool**  
Part Number 91363-1

### Crimp Blade Contacts

| Wire Size | Type           | Cycles | Mating Length | Part Number Strip Form | Applicator | Hand Tool |
|-----------|----------------|--------|---------------|------------------------|------------|-----------|
| 16-20 AWG | Standard Power | 100    | A             | 1489128-8              | 1385248-3  | 91363-1   |
|           |                |        | B             | 1489128-7              |            |           |
|           | High Power     | 250    | A             | 1-1489128-0            |            |           |
|           |                |        | B             | 1489128-9              |            |           |

Heavy Duty Miniature (HDM) Applicator for AMP-O-LECTRIC Model G Machine - #1385248-3.  
PRO-CRIMPER Hand Tool #354940-1, Die set # 91363-2



### Plugs and Receptacles

#### Materials

UL 94V-0 Thermoplastic

105°C Max. Operating temperature

**Note:** Vertical PCB Mt. Receptacles supplied with press-fit ACTION PIN contacts.



| Number of Positions | Part Number      |               |                       |              |
|---------------------|------------------|---------------|-----------------------|--------------|
|                     | Panel-Mount Plug |               | PCB-Mount Receptacles |              |
|                     | Snap-In          | Shoulder Bolt | Standard Power        | High Current |
| 3                   | 1489127-1        | —             | 1489715-1             | 1-1489715-1  |
| 4                   | 1489127-2        | 1489701-1     | 1489715-2             | 1-1489715-2  |
| 5                   | 1489127-3        | —             | 1489715-3             | 1-1489715-3  |
| 6                   | 1489127-4        | —             | 1489715-4             | 1-1489715-4  |
| 7                   | 1489127-5        | —             | 1489715-5             | 1-1489715-5  |
| 8                   | 1489127-6        | —             | 1489715-6             | 1-1489715-6  |
| 9                   | 1489127-7        | —             | 1489715-7             | 1-1489715-7  |
| 10                  | 1489127-8        | —             | 1489715-8             | 1-1489715-8  |

**Note:** All part numbers are RoHS compliant.

## Hybrid Blind-Mate Drawer Connectors

### Product Facts

- High current circuits and signal circuits can be mixed in the same connector
- High current circuits use MIC connector contacts located at four corners of the housing
- Signal circuits use Standard Drawer Connector contacts
- 24 positions
- Hermaphroditic housing can be mated with top and bottom turned while maintaining polarity



Hybrid Drawer Connectors offer high current and signal circuits mixed in the same connector system.

High current circuits use MIC connector contacts which are located at the four corners of the housing. Signal circuits use the same

hermaphroditic crimp snap-in contacts that are used in the Standard Drawer Connector.

The hermaphroditic housings are available in a popular 24-position size. These housings can be mated with top and bottom turned while maintaining polarity.

### Performance Specifications

**Voltage Rating** — 250 VAC

**Current Rating (Max.)** —

Signal Circuit (Drawer);  
4 Amps — 24 AWG [0.2 mm<sup>2</sup>] Wire  
5 Amps — 22 AWG [0.3-0.4 mm<sup>2</sup>] Wire  
7 Amps — 20 AWG [0.5-0.6 mm<sup>2</sup>] Wire  
Power Circuit (MIC);  
10 Amps

**Low Level Resistance** —

Signal Circuit (Drawer);  
10 milliohms max. (Initial)  
20 milliohms max. (Final)  
Power Circuit (MIC);  
3 milliohms (Initial)  
6 milliohms (Final)

**Dielectric Withstanding Voltage** —

5000 milliohms (Initial)  
2000 milliohms (Final)

**Operating Temperature** —

-20°C to +120°C

## Hybrid Blind-Mate Drawer Connectors (Continued)

### Housings (Hermaphroditic), 24 Positions

#### Material

**Housing** — Glass-filled polybutylene terephthalate (PBT), blue

**Bushing** — Brass, zinc-plated

#### Related Product Data



**Performance Specifications** —  
page 85

**MIC Contacts** — page 87

**Crimp Snap-In Contacts** — page 87



#### Technical Documents

**Product Specification**  
108-5371



**Note:** Reverse figures show circuit numbers.


(Example = A1 81B. The hole used for No. 1 circuit is used for No. 13 on the reverse side.)



| Floating of Bushing                                             | Housing Part Numbers |
|-----------------------------------------------------------------|----------------------|
| Up- and downward = 0.05 [.002]<br>Circumferential = 0.14 [.006] | 5176916-1            |
| Up- and downward = 0.30 [.012]<br>Circumferential = 0.80 [.031] | 5176916-2            |

Upward and downward = Axial clearance  
Circumferential = Floating

### Recommended Panel Cutout



\*Dimensions applicable for rear mounting.

**Note:** All part numbers are RoHS compliant.

## Hybrid Blind-Mate Drawer Connectors (Continued)

### MIC Contacts (Used for Power Circuits)

#### Material and Finish

Phosphor bronze, plated .000030 [0.00076] gold in contact area, remainder of contact gold flash, with entire contact underplated nickel

#### Related Product Data


**Performance Specifications—**  
page 85

**Housings—**page 86

#### Technical Documents

##### Instruction Sheets

408-089J, 408-369J, 408-370J



| Wire Size Range |                 | Insulation Diameter    | Part Numbers       |             |                       |            |
|-----------------|-----------------|------------------------|--------------------|-------------|-----------------------|------------|
| AWG             | mm <sup>2</sup> |                        | Receptacle Contact |             | Hand Tool             | Applicator |
|                 |                 |                        | Strip Form         | Loose Piece |                       |            |
| 20-14           | 0.5-2.0         | .087-.134<br>2.20-3.40 | 170286-4           | 170289-3    | 755338-1*<br>755339-1 | 567151-X** |

\*Part Number 755338-1 is used on wire for automotive application; Part Number 755339-1 is used on other types of wire.


\*\*Call TE for applicators.

Extraction Tool Part Number 723735-1

### Crimp Snap-In Contacts (Hermaphroditic, Used for Signal Circuits)

#### Material and Finish

Phosphor bronze, plated gold in contact area (for length of .236 [6.0] from tip), with entire contact underplated nickel



| Wire Size Range |                 | Insulation Diameter    | Part Numbers |             |                                        |           |
|-----------------|-----------------|------------------------|--------------|-------------|----------------------------------------|-----------|
| AWG             | mm <sup>2</sup> |                        | Contact      |             | Applicator for AMP-O-ELECTRIC Machine* | Hand Tool |
|                 |                 |                        | Strip Form   | Loose Piece |                                        |           |
| 24-20           | 0.2-0.6         | .060-.077<br>1.50-1.95 | 170311-1     | 170313-1    | 567324-2                               | 91591-1   |
| 20-16           | 0.5-1.4         | .071-.130<br>1.80-3.30 | 170484-1     | 170485-1    | 567241-2                               | 91590-1   |

\*Applicators are for Model "K" machines. Consult TE for applicators for other bench machines and lead-making machines.


**Notes:** For applicable wire, use wire specified in UL 1015 or 1007.

Extraction Tool Part Number 723986-1

### Tab Contacts

#### Material and Finish

Brass, plated .000030 [0.00076] gold in contact area, with entire contact underplated nickel



| Wire Size Range |                 | Insulation Diameter    | Part Numbers |             |                       |
|-----------------|-----------------|------------------------|--------------|-------------|-----------------------|
| AWG             | mm <sup>2</sup> |                        | Tab Contact  |             | Hand Tool             |
|                 |                 |                        | Strip Form   | Loose Piece |                       |
| 20-14           | 0.5-2.0         | .087-.134<br>2.20-3.40 | 170221-4     | 170222-3    | 755338-1*<br>755339-1 |

\*Part Number 755338-1 is used on wire for automotive application; Part Number 755339-1 is used on other types of wire.

Extraction Tool Part Number 724763-1

**Note:** All part numbers are RoHS compliant.

## Special Blind-Mate Drawer Connectors (uses AMP-LEAF Contacts)


### Product Facts

- Blind-mate connectors accept AMP-LEAF crimp snap-in and solder dip contacts
- Contacts are phosphor bronze, gold-over-nickel plated
- 6 and 10 positions
- Housings made of polybutylene terephthalate (PBT)




Special blind-mate drawer connectors are available in 6- and 10-position configurations and provide wire-to-board and wire-to-wire connection capabilities. These connectors offer the integrity of AMP-LEAF contacts with maximum travel wiping action.

Housings feature molded-in guide pins and diagonally aligned sockets for correct polarization and to facilitate blind-mating. The PC header guide pins extend through the PC board to secure the header to the board prior to soldering.



**6-Position Socket Housing**  
(Accepts AMP-LEAF  
Crimp Snap-In Contacts)



**6-Position PC Board Header Housing**  
(Fully loaded with AMP-LEAF  
Solder Dip Contacts)



**10-Position Socket Housing**  
(Accepts AMP-LEAF  
Crimp Snap-In Contacts)



**10-Position Header Housing**  
(Accepts AMP-LEAF  
Crimp Snap-In and  
Solder Dip Contacts)

### Performance Specifications

**Current Rating** —  
4 Amps (max.) — 26-22 AWG  
[0.12-0.4 mm<sup>2</sup>] wire

**Voltage Rating** — 50 VDC


**Temperature Rating** —  
-10°C to +80°C

### Mounting Screw (2 Required per Socket Housing)

**Part Number 343404-1**

### Material and Finish

Steel, plated bright zinc chromate



**Note:** All part numbers are RoHS compliant.

## Special Blind-Mate Drawer Connectors (Continued)

### Socket Housing, 6 Positions



Part Number 343886-1

Accepts the following AMP-LEAF  
Crimp Snap-In Contacts:

Part Number 583990-3 (loose piece)

Part Number 583204-2 (strip form)



Contacts must be ordered  
separately.



Recommended Panel Cutout

### Material

Glass-filled polybutylene terephthalate  
(PBT), black





### PC Board Header Housing, 6 Positions with Board Retention

Part Number 343887-1

Accepts AMP-LEAF Crimp Snap-In  
Contact Part Number 343371-1  
and Solder Dip Contact  
Part Number 583294-2



Contacts must be ordered  
separately; refer to contact  
specification pages for details.



Recommended PC Board Layout

### Material

Glass-filled polybutylene terephthalate  
(PBT), black



**Note:** All part numbers are RoHS compliant.

## Special Blind-Mate Drawer Connectors (Continued)



### Socket Housing, 10 Positions

Part Number 343348-1


Accepts the following AMP-LEAF  
Crimp Snap-In Contacts:

Part Number 343371-1 (strip form)  
Part Number 583204-2 (strip form)

Contacts must be ordered  
separately.




Recommended Panel Cutout



### Material

Glass-filled polybutylene terephthalate  
(PBT), black





### Header Housing, 10 Positions


Part Number 343347-1

Accepts AMP-LEAF Crimp Snap-In  
Contact Part Number 343371-1  
and Solder Dip Contact  
Part Number 583294-2

Contacts must be ordered  
separately: refer to contact  
specification pages for details.




Recommended Panel Cutout



### Material

Glass-filled polybutylene terephthalate  
(PBT), black



**Note:** All part numbers are RoHS compliant.

## Special Blind-Mate Drawer Connectors (Continued)

### Crimp, Snap-In Contacts

#### Material and Finish

Phosphor bronze, plated as follows:

**Plating A** — .000100-.000200 [0.00254-0.00508] tin (lubricant must be used)


**Plating B** — .000030 [0.00076] min. gold in mating area, gold flash on remainder of contact, with entire contact underplated .000050 [0.00127] min. nickel

**Plating C** — .000015 [0.00038] min. gold in mating area, gold flash on remainder of contact, with entire contact underplated .000050 [0.00127] min. nickel

**Plating D** — .000030 [0.00076] min. gold over .000050 [0.00127] min. nickel in mating area, remainder of contact gold flash over .000015 [0.00038] min. nickel

**Plating E** — .000030 [0.00076] min. gold in mating area, with entire contact underplated .000050 [0.00127] min. nickel

**Plating F** — .000015 [0.00038] min. gold in mating area, with entire contact underplated .000050 [0.00127] min. nickel



| Wire Range<br>AWG/mm² | Insulation Range<br>Single Wire<br>Double Wire | Part Numbers           |               |                   |          | Applicator for<br>AMP-O-LECTRIC<br>Machine* | Hand<br>Tool                                             |
|-----------------------|------------------------------------------------|------------------------|---------------|-------------------|----------|---------------------------------------------|----------------------------------------------------------|
|                       |                                                | Contact                |               | Contact<br>Finish |          |                                             |                                                          |
|                       |                                                | Loose<br>Piece         | Strip<br>Form |                   |          |                                             |                                                          |
| 26-22<br>0.12-0.4     | .050-.064<br>1.27-1.63                         | —                      | 583990-3      | B                 | 466366-2 |                                             | 90028-3                                                  |
|                       |                                                |                        | —             | D                 |          |                                             |                                                          |
| 22-18<br>0.3-0.9      | .055-.080<br>1.40-2.03                         | .120<br>3.05<br>Max.   | —             | A                 | 466367-2 |                                             | 90017-3 (1 #22-20)<br>90028-3 (2 #22)<br>90101-3 (1 #20) |
|                       |                                                |                        | 583989-3      | B                 |          |                                             |                                                          |
|                       |                                                |                        | 583989-4      | C                 |          |                                             |                                                          |
|                       |                                                |                        | —             | E                 |          |                                             |                                                          |
|                       |                                                |                        | —             | F                 |          |                                             |                                                          |
| 16<br>1.25-1.40       | .108<br>2.74<br>Max.                           | .080-.160<br>2.03-4.06 | 583991-3      | B                 | 466368-2 |                                             | 90031-8 (2 #18)<br>90101-3 (2 #20)<br>90101-3 (1 #16)    |

\*Applicators are for AMP-O-LECTRIC Model "K" machines. Consult TE for applicators for other bench machines and lead-making machines.

**Notes:** 1. Shorting contacts are available, consult TE.

2. Contacts and housings to accommodate .093 [2.36] thick PC boards can be made available, consult TE.

#### Technical Documents

##### Product Specifications

108-9013, 108-9043

##### Application Specification

114-9003

##### Instruction Sheets

408-6591, 408-7045, 408-7622,  
408-7623, 408-7624, 408-7625,  
408-7626

##### Crimp Inspection Sheet

CI 8050-33

#### Hand Crimping Tool



#### Contact Extraction Tool




| Part Number        |                       |
|--------------------|-----------------------|
| Extraction<br>Tool | Used with<br>Housings |
| 465195-1           | 480110-2, -5          |
|                    | 480142-2, -3          |
|                    | 582140-5              |
|                    | 582147-5              |
|                    | 582264-2              |
|                    | 582500-2              |
|                    | 582963-2              |
|                    | 583167-3              |
|                    | 583280-1              |
|                    | 583617-1              |
|                    | 583680-1              |
|                    | 583685-1              |
|                    | 583722-1              |
|                    | 583723-1              |
|                    | 583724-1              |
| 465195-2           | 583725-1              |
|                    | 583726-1              |
|                    | 480133-2              |

#### Dummy Contact

#### Material

Phosphor bronze



Plain Finish—

**Part Number 66084-1**

Tin Finish—

**Part Number 66084-2**

Gold Finish—

**Part Number 66084-3**

#### Technical Documents


Instruction Sheet 408-7037

**Note:** All part numbers are RoHS compliant.

## Standard Blind-Mate Drawer Connectors

### Product Facts

- Designed for rack and panel applications
- Durable—withstands multiple mating/unmating
- Low insertion and withdrawal force
- Hermaphroditic contacts
- Accepts signal and power contacts
- Provides excellent creep distance
- Mated connectors dust-proof
- Configurations available in 8, 12, 16, 20 and 24 positions
- Contacts accept wire sizes 24-14 AWG [0.2-2.0 mm<sup>2</sup>]
- Accept wire insulation diameter — .059-.154 [1.5-3.9]
- Recognized under the Component Program of the Underwriters Laboratories Inc. 



Drawer connectors are designed as an economical rack and panel connector. They are used in copying machines, control panels, power distribution boards, industrial equipment, power supplies and other electronic equipment.

Blind-mate drawer connectors feature excellent durability and provide low insertion and withdrawal force. Leaf-type hermaphroditic contacts ensure reliable, positive contact.

Contacts are on .197 [5.00] centerlines for signal circuits, and .260 [6.60] centerlines for power circuits (2-circuits at each end of the double row of contacts) for a total of 4. Row-to-row spacing is .390 [9.90].

Housings are made of UL 94V-0 rated thermoplastic and feature molded-in guide pins and sockets for positive connector mating.

Other features include wire outlets which provide for sufficient creep distance, plus mated assemblies are completely dust-proof.

Additional economies are achieved through the use of strip-form contacts suitable for high-speed automatic machine terminations. For prototype, maintenance and repair applications, contacts are available in loose piece for easy termination with TE hand crimping tools.

### Performance Specifications

**Voltage Rating** — 250 VAC

#### Current Rating —

4 Amps — 24 AWG [0.2 mm<sup>2</sup>] Wire  
 5 Amps — 22 AWG [0.3-0.4 mm<sup>2</sup>] Wire  
 7 Amps — 20 AWG [0.5-0.6 mm<sup>2</sup>] Wire  
 8 Amps — 18 AWG [0.8-0.9 mm<sup>2</sup>] Wire  
 12 Amps — 16 AWG [1.25-1.4 mm<sup>2</sup>] Wire  
 15 Amps — 14 AWG [2.0 mm<sup>2</sup>] Wire

#### Contact Resistance —

10 milliohms max. (Initial)  
 20 milliohms max. (Final)

#### Insulation Resistance —

5000 milliohms min. (Initial)  
 2000 milliohms min. (Final)

**Dielectric Withstanding Voltage** —  
 2000 VAC/1 minute

#### Operating Temperature —

–20°C to +120°C (Includes T-Rise)

#### Insertion/Extraction Force —

Insertion—4 kg max. (Initial) —  
 16-position  
 Extraction—0.7 kg min. (Initial) —  
 16-position

#### Durability —

Tested to 1000 Mate/Unmate cycles

## Standard Blind-Mate Drawer Connectors (Continued)

### Plug Connectors, PCB-Mount

#### Material and Finish

**Housing** — Glass-filled polybutylene terephthalate (PBT), blue, 94V-0 rated

**Contacts** — Phosphor bronze, plated gold in contact area over nickel underplating; board-mount tails are brass, plated tin over steel underplating

#### Related Product Data:

**Performance Specifications** — page 92

**Mating Receptacles** — page 94


#### Technical Documents

**Product Specification**

108-5125


**Application Specification**

114-5044



| No. of Pos. | Dimensions    |               |               |              |   | Plug Connector Part Numbers |
|-------------|---------------|---------------|---------------|--------------|---|-----------------------------|
|             | A             | B             | C             | D            | E |                             |
| 8           | 2.016<br>51.2 | 1.500<br>38.0 | 1.055<br>26.8 | .197<br>5.00 | 1 | 172653-2                    |
| 12          | 2.409<br>61.2 | 1.890<br>48.0 | 1.449<br>36.8 | .591<br>15.0 | 3 | 172653-3                    |
| 16          | 2.803<br>71.2 | 2.283<br>58.0 | 1.843<br>46.8 | .984<br>25.0 | 5 | 172653-1                    |

**Note:** To ensure proper contact alignment, connectors must be mated during the soldering process.



Recommended PC Board Layout

**Note:** All part numbers are RoHS compliant.

## Standard Blind-Mate Drawer Connectors (Continued)

### Housings for Crimp Snap-In Contacts

#### Material

Polybutylene terephthalate (PBT), blue, 94V-0 rated

#### Related Product Data

**Performance Specifications** — page 92


**Crimp Snap-In Contacts** — page 95

**Panel Cutout** — page 95



#### Technical Documents

**Product Specification**  
108-5125


**Application Specification**  
114-5044



Receptacle



Plug



| No. of Pos. | Dimensions     |                |                |                |   |                | Receptacle            |              | Plug                      |              |
|-------------|----------------|----------------|----------------|----------------|---|----------------|-----------------------|--------------|---------------------------|--------------|
|             | A              | B              | C              | D              | E | F              | Floating Bushing Size | Part Numbers | Panel-Mount Hole Diameter | Part Numbers |
| 8           | 1.858<br>47.20 | 1.055<br>26.80 | 2.016<br>51.20 | 1.500<br>38.00 | 1 | .197<br>5.00   | .118<br>3.00          | 5172070-1    | .130<br>3.30              | 172063-1     |
|             |                |                |                |                |   |                | .157<br>4.00          | 5172070-3    | .169<br>4.30              | 172063-3     |
| 12          | 2.252<br>57.20 | 1.449<br>36.80 | 2.410<br>61.20 | 1.890<br>48.00 | 3 | .591<br>15.00  | .118<br>3.00          | 5172069-1    | .130<br>3.30              | 172061-1     |
|             |                |                |                |                |   |                | .157<br>4.00          | 5172069-3    | .169<br>4.30              | 172061-3     |
| 16          | 2.657<br>67.20 | 1.843<br>46.80 | 2.803<br>71.20 | 2.283<br>58.00 | 5 | .984<br>25.00  | .118<br>3.00          | 5172068-1    | .130<br>3.30              | 172059-1     |
|             |                |                |                |                |   |                | .157<br>4.00          | 5172068-3    | .169<br>4.30              | 172059-3     |
| 20          | 3.039<br>77.20 | 2.236<br>56.80 | 3.197<br>81.20 | 2.677<br>68.00 | 7 | 1.378<br>35.00 | .157<br>4.00          | 5173033-3    | .169<br>4.30              | 173032-3     |
| 24          | 3.433<br>87.20 | 2.630<br>66.80 | 3.591<br>91.20 | 3.071<br>78.00 | 9 | 1.772<br>45.00 | .118<br>3.00          | 5172625-1    | .130<br>3.30              | 172624-1     |
|             |                |                |                |                |   |                | .157<br>4.00          | 5172625-3    | .169<br>4.30              | 172624-3     |

**Note:** All part numbers are RoHS compliant.

## Standard Blind-Mate Drawer Connectors (Continued)

### Crimp Snap-In Contacts (Hermaphroditic)

#### Material and Finish

Phosphor bronze, plated gold in contact area (for length of .236 [6.0] from tip), with entire contact underplated nickel

#### Related Product Data



**Performance Specifications** — page 92

**Housings** — page 94

#### Technical Documents

##### Instruction Sheets

408-097J, 408-098J, 408-151J



**CERTI-CRIMP Hand Tool**  
Part Number 91591-1

| Wire Size Range |         | Insulation Dia. Range  | Part Numbers |             | Applicator for AMP-O-ELECTRIC Machine* | Hand Tool Numbers |
|-----------------|---------|------------------------|--------------|-------------|----------------------------------------|-------------------|
|                 |         |                        | Strip Form   | Loose Piece |                                        |                   |
| 24-20           | 0.2-0.6 | .059-.077<br>1.50-1.95 | 170311-1     | 170313-1    | 567324-2                               | 91591-1           |
| 20-16           | 0.5-1.4 | .071-.130<br>1.80-3.30 | 170484-1     | 170485-1    | 567241-2                               | 91590-1           |
| 18-14           | 0.8-2.0 | .091-.154<br>2.30-3.90 | 170312-1     | 170314-1    | 567325-2                               | 2063849-1         |


\*Applicators are for Model "K" machines. Consult TE for applicators for other bench machines and lead-making machines.

**Notes:** 1. For applicable wire, use wire specified in UL 1015 or 1007.

2. Contacts for 18-14 AWG [0.8-2.0 mm<sup>2</sup>] wire are used at the four corners of the connector as power contacts (8 required per assembly).

Extraction Tool **Part Number 723986-1**

### Recommended Panel Cutout



**Rear Panel-Mount**

| No. of Pos. | Rear Panel-Mount Dimensions |                |                |
|-------------|-----------------------------|----------------|----------------|
|             | J                           | K              | L              |
| 8           | 1.913<br>48.60              | 1.500<br>38.00 | 1.110<br>28.20 |
| 12          | 2.307<br>58.60              | 1.890<br>48.00 | 1.504<br>38.20 |
| 16          | 2.701<br>68.60              | 2.283<br>58.00 | 1.898<br>48.20 |
| 20          | 3.094<br>78.60              | 2.677<br>68.00 | 2.291<br>58.20 |
| 24          | 3.488<br>88.60              | 3.071<br>78.00 | 2.685<br>68.20 |


**Note:** Mounting holes of .209 [5.30] dia. are used when mounting receptacle housings with .157 [4.0] long floating bushings and the mating plug housings. Panel thickness is .063 [1.60]. Panel cutout shown above is for use with plug housings. For receptacle housings, use the mirror-image cutout.

**Note:** All part numbers are RoHS compliant.

## Hybrid Mini-Drawer Connectors

### Product Facts

- Combine signal circuits and power circuits into one connector
- Power circuits can be used for high current of up to 15A
- Signal circuits accept CT connector in the back, reducing harnessing costs
- Power circuits use crimp-type tab and receptacle contacts
- Meet requirements for creepage distance and spatial distance for primary power supply as set forth in IEC-950, safety specifications for business machines and OA equipment.  
Creepage distance on active power side: 5 mm  
Spatial distance on active power side: 4.5 mm



### Technical Documents

#### Product Specification

108-60022

#### Application Specification

114-5182

Hybrid mini-drawer connectors are designed for use in rack and panel application to serve as an I/O connector for copying machines, laser-beam printers and other OA equipment. They provide an economical means of combining into one connector signal circuits and power circuits which were packaged separately in the past.

A major design feature of these hybrid mini-drawer connectors is that mini-drawer connectors mate with one another on the connector mating side and in the back, signal circuits accept a pre-terminated CT receptacle connector.

Also, for power circuits, crimp-type power contacts are used by inserting them into the four corners of the mini-drawer connector.

The housing has an integrated guide-pin and socket to facilitate mating of the connector halves. Provision is also made to prevent dust from entering.

This product line includes:

- 12-position connector (4 positions for power and 8 positions for signal circuits)
- 24-position connector (4 positions for power and 20 positions for signal circuits)
- 32-position connector (4 positions for power and 28 positions for signal circuits)

Drawer connectors are available in the following types depending on application: (For details contact our sales department)

- Mini-drawer connectors
- Standard drawer connectors
- High current drawer connectors

### Performance Data

#### Voltage Rating —

250V AC (power)

30V AC (signal)

#### Current Rating —

15A max. (power)

2A max. (signal)

#### Contact Resistance —

10 mm  $\Omega$  max. (power)

40 mm  $\Omega$  max. (signal)

#### Insulation Resistance —

100M  $\Omega$  max.

#### Dielectric Withstanding Voltage —

1.8KV AC/min. (power)


1.0KV AC/min. (signal)

#### Durability — 3,000 cycles min.

## Hybrid Mini-Drawer Connectors (Continued)

### Standard Width

Plugs




Receptacles




| Type       | Part Number | Number of Power Contacts | Number of Signal Contacts | L             | W            |
|------------|-------------|--------------------------|---------------------------|---------------|--------------|
| Plug       | 292180-1    | 2                        | 4                         | 1.299 [33.00] | .646 [16.40] |
| Receptacle | 292184-1    | 2                        | 4                         | 1.299 [33.00] | .646 [16.40] |
| Plug       | 1-292183-2  | 6                        | 12                        | 2.638 [67.00] | .748 [19.00] |
| Receptacle | 1-292186-2  | 6                        | 12                        | 2.638 [67.00] | .748 [19.00] |

### Slim Width

Plugs



Receptacles



| Type       | Part Number | Number of Power Contacts | Number of Signal Contacts | L             | W            |
|------------|-------------|--------------------------|---------------------------|---------------|--------------|
| Plug       | 1-292187-2  | 3                        | 5                         | 1.870 [47.50] | .591 [15.00] |
| Receptacle | 2-292190-2  | 3                        | 5                         | 1.713 [43.50] | .472 [12.00] |
| Plug       | 3-292187-2  | 4                        | 5                         | 2.146 [54.50] | .531 [13.50] |
| Receptacle | 4-292190-2  | 4                        | 5                         | 1.988 [50.50] | .472 [12.00] |
| Plug       | 2-292189-3  | 3                        | 7                         | 2.028 [51.50] | .591 [15.00] |
| Receptacle | 1-292192-3  | 3                        | 7                         | 1.870 [47.50] | .472 [12.00] |

**Note:** All part numbers are RoHS compliant.

### Hybrid Mini-Drawer Connectors (Continued)

## Power Contacts

## Material

Copper alloy  
For finish, see table below.

### Finish Codes


- 1) Over nickel underplated, contact area: gold plated, crimp area: tin plated
- 2) Tin plated all over.

Hand Tool AWG #20-24

Part No. 934199-1 (411-5662)

AWG #16-20

Part No. 934198-1 (411-5661)




| Wire Range |                 | Wire<br>Ins. Dia. | Plating<br>Code | Receptacle Part Number | Tab Part Number |
|------------|-----------------|-------------------|-----------------|------------------------|-----------------|
| AWG        | mm <sup>2</sup> |                   |                 | Strip Form             | Strip Form      |
| 24-20      | 0.2-0.5         | 1.4-2.6           | 1               | 179317-2               | 179322-2        |
|            |                 |                   | 2               | 1-179317-2             | 1-179322-2      |
| 20-16      | 0.5-1.25        | 1.6-2.8           | 1               | 179316-2               | 179321-2        |
|            |                 |                   | 2               | 1-179316-2             | 1-179321-2      |

## Receptacle Assembly

## Material and Finish

**Housing** — Thermoplastic, black

**Contact** — Copper alloy, gold plated on mating side over nickel underplate, tin plated on CT mating side over nickel underplate.



| No. of Pos.<br>(Power/<br>Signal) | Dimensions |      |      |      |      |      |      |      | Mini-Drawer<br>Receptacle<br>Assembly Part No. | Required<br>Number of<br>Power Contact | Required<br>Number of<br>CT Connector |
|-----------------------------------|------------|------|------|------|------|------|------|------|------------------------------------------------|----------------------------------------|---------------------------------------|
|                                   | A          | B    | C    | D    | E    | F    | G    | H    |                                                |                                        |                                       |
| 12 (4-8)                          | 56.0       | 47.0 | 6.0  | 24.1 | 31.8 | 31.4 | 38.0 | 32.4 | 292185-8                                       | 4                                      | 4 Pos. x 2                            |
| 24 (4-20)                         | 68.0       | 59.0 | 18.0 | 36.1 | 43.8 | 43.4 | 50.0 | 44.4 | 2-292185-0                                     | 4                                      | 10 Pos. x 2                           |
| 32 (4-28)                         | 76.0       | 67.0 | 26.0 | 44.1 | 51.8 | 51.4 | 58.0 | 52.4 | 2-292185-8                                     | 4                                      | 14 Pos. x 2                           |

**Note:** All part numbers are RoHS compliant.


## Hybrid Mini-Drawer Connectors (Continued)

## Plug Assembly

## Material and Finish

**Housing** — Thermoplastic, black  
UL94V-0

**Contact** — Copper alloy, gold plated on mating side over nickel underplate, tin plated platen on CT mating side over nickel underplate.



| No. of Pos.<br>(Power/<br>Signal) | Dimensions |      |      |      |      |      |      |      | Mini-Drawer<br>Receptacle<br>Assembly Part No. | Required<br>Number of<br>Power Contact | Required<br>Number of<br>CT Connector |
|-----------------------------------|------------|------|------|------|------|------|------|------|------------------------------------------------|----------------------------------------|---------------------------------------|
|                                   | A          | B    | C    | D    | E    | F    | G    | H    |                                                |                                        |                                       |
| 12 (4-8)                          | 56.0       | 47.0 | 6.0  | 24.1 | 36.0 | 31.4 | 33.4 | 38.0 | 292182-8                                       | 4                                      | 4 Pos. x 2                            |
| 24 (4-20)                         | 68.0       | 59.0 | 18.0 | 36.1 | 48.0 | 43.4 | 45.4 | 50.0 | 2-292181-0**                                   | 4                                      | 10 Pos. x 2                           |
| 32 (4-28)                         | 76.0       | 67.0 | 26.0 | 44.1 | 56.0 | 51.4 | 53.4 | 58.0 | 2-292181-8                                     | 4                                      | 14 Pos. x 2                           |

\*12-Position connector is provided with sequential feature in one power circuit position. Other connector sizes have sequential feature in power circuits and signal circuits.

\*\*Optional part numbers offer sequential mating – see customer drawings for details.

**Note:** All part numbers are RoHS compliant.

## Hybrid Mini-Drawer Connectors (Continued)

### CT Receptacle Connectors to Mate with Signal Circuit Terminator with Insulation Displacement Contacts

#### Receptacle Assemblies (Wire Application Side)

##### Material and Finish

**Housing** — UL94V-0 rated, glass-filled P.B.T. see chart below for color.


**Contact** — Pre-tinned phosphor bronze

**Wire Size** — AWG #28-26  
(0.08-0.15 mm<sup>2</sup>)

**Insulation Dia.** — 0.85-1.05 mm

**Wire Size** — AWG #24  
(0.20-0.22 mm<sup>2</sup>)

**Insulation Dia** — 0.95-1.05 mm<sup>2</sup>  
(For AWG #24 wire, see notes under the table)



| No. of Positions | Dimensions |      |      | Part Number           |            |
|------------------|------------|------|------|-----------------------|------------|
|                  |            |      |      | Receptacle Assembly** |            |
|                  | A          | B    | C    | AWG #28-26*           | AWG #24*** |
| 2                | 2.0        | 4.8  | 6.0  | 173977-2              | 2-179694-2 |
| 3                | 4.0        | 6.8  | 8.0  | 173977-3              | 2-179694-3 |
| 4                | 6.0        | 8.8  | 10.0 | 173977-4              | 2-179694-4 |
| 5                | 8.0        | 10.8 | 12.0 | 173977-5              | 2-179694-5 |
| 6                | 10.0       | 12.8 | 14.0 | 173977-6              | 2-179694-6 |
| 7                | 12.0       | 14.8 | 16.0 | 173977-7              | 2-179694-7 |
| 8                | 14.0       | 16.8 | 18.0 | 173977-8              | 2-179694-8 |
| 9                | 16.0       | 18.8 | 20.0 | 173977-9              | 2-179694-9 |
| 10               | 18.0       | 20.8 | 22.0 | 1-173977-0            | 3-179694-0 |
| 11               | 20.0       | 22.8 | 24.0 | 1-173977-1            | 3-179694-1 |
| 12               | 22.0       | 24.8 | 26.0 | 1-173977-2            | 3-179694-2 |
| 13               | 24.0       | 26.8 | 28.0 | 1-173977-3            | 3-179694-3 |
| 14               | 26.0       | 28.8 | 30.0 | 1-173977-4            | 3-179694-4 |
| 15               | 28.0       | 30.8 | 32.0 | 1-173977-5            | 3-179694-5 |

\* The color of housing is natural. Other colors available include blue, yellow and black. For details contact our Sales Department

\*\* For wire to be used, contact our Sales Department as there are wires that have been tested by TE and can be recommended for your use.


\*\*\* The color of housing is gray.

**Note:** All part numbers are RoHS compliant.

## Hybrid Mini-Drawer Connectors (Continued)

### CT Receptacle Contacts to Mate with Signal Circuit Termination with Crimp Type Contacts

#### Receptacle Contact





#### Receptacle Housing Material


UL94-0 rated, 66 nylon, natural color (white)

| Wire Size<br>AWG (mm <sup>2</sup> ) | Insulation Dia.<br>(mm) | Material<br>and Finish                                | Part Number |             |                        |
|-------------------------------------|-------------------------|-------------------------------------------------------|-------------|-------------|------------------------|
|                                     |                         |                                                       | Strip Form  | Loose Piece | Hand Tool              |
| 30-26<br>(0.05-0.12)                | 0.65-1.35               | Phosphor bronze<br>(0.20 mm thickness),<br>tin plated | 179609-1    | —           | 234169-1<br>(411-5711) |
| 26-22<br>(0.12-0.35)                | 0.93-1.5                |                                                       | 179227-1    | 179518-1    | 91572-1<br>(408-8547)  |


**Note:** Loose piece contacts, being small in size, are supplied in the form of a comb with 10 pieces on 7.5 mm pitch. There is a slit at the root of each contact and it can be snapped off easily.



2 Position



3 Position



4 Position

4-15 Positions

| No. of<br>Positions | Dimensions |      |      | Part Number<br>Receptacle Assembly* |
|---------------------|------------|------|------|-------------------------------------|
|                     | A          | B    | C    |                                     |
| 2                   | 2.0        | 4.8  | 6.0  | 179228-2                            |
| 3                   | 4.0        | 6.8  | 8.0  | 179228-3                            |
| 4                   | 6.0        | 8.8  | 10.0 | 179228-4                            |
| 5                   | 8.0        | 10.8 | 12.0 | 179228-5                            |
| 6                   | 10.0       | 12.8 | 14.0 | 179228-6                            |
| 7                   | 12.0       | 14.8 | 16.0 | 179228-7                            |
| 8                   | 14.0       | 16.8 | 18.0 | 179228-8                            |
| 9                   | 16.0       | 18.8 | 20.0 | 179228-9                            |
| 10                  | 18.0       | 20.8 | 22.0 | 1-179228-0                          |
| 11                  | 20.0       | 22.8 | 24.0 | 1-179228-1                          |
| 12                  | 22.0       | 24.8 | 26.0 | 1-179228-2                          |
| 13                  | 24.0       | 26.8 | 28.0 | 1-179228-3                          |
| 14                  | 26.0       | 28.8 | 30.0 | 1-179228-4                          |
| 15                  | 28.0       | 30.8 | 32.0 | 1-179228-5                          |

\* The color of housing is natural. Other colors available include blue, yellow and black. For details contact our Sales Department

**Note:** All part numbers are RoHS compliant.

## ET Power Connector

### Product Facts

- Right-angle and vertical mounts available
- Low profile right-angle connector  $\leq 8$  mm above pcb
- 2.5 mm<sup>2</sup> (14 AWG) to 6 mm<sup>2</sup> (10 AWG) wire range
- Refer to current v temp rise graphs for current capability
- Coding contacts for sense function
- Positive metal latch retention
- Up to 30 Amps per contact. See temperature rise charts on page 103



### Description

- Cable to pcb
- Low profile Right Angle
- Vertical Mount
- High reliability interface
- Excellent price to performance ratio

Designed for low-profile power distribution units requiring small form factor connector with high current, the ET power connector is a low loss, highly reliable and cost effective solution for cable-to-pcb applications.

The connector is available in both a vertical mount and a right-angle mount, which stands at just 8 mm off of the board. A unique feature of the ET power series is integrated coding contacts which allow different electronic functions such as sense and enable to be

designed into the PDU electronics with activation on full insertion of the cable connector.

Crimp contacts from the industry proven "Standard Power Timer" range for use with 2.5 mm<sup>2</sup> (14 AWG), 4 mm<sup>2</sup> (12 AWG) and 6 mm<sup>2</sup> (10 AWG) wire.

The cable connector has a positive latching mechanism providing no accidental un-mating even with pull forces up to 100N.

### Material and Finish

**Housing ST Cable** — Black glass-filled thermoplastic, UL 94V-0 rated

**Latch** — Stainless Steel

**Housing ST & Right-angle PCB** — Black glass-filled thermoplastic, UL 94V-0 rated

**Power Contacts** — Copper alloy, 3.0  $\mu$ m Ag min.

**Contact Detection** — 0.8  $\mu$ m gold min. in contact place; 1.27  $\mu$ m nickel min. contact place

### Application

- Power Distribution
- Power Supplies
- Telecoms Base Stations
- Computer Servers and Storage Systems
- Industrial Electronic Equipment Cabinets

### Technical Documents

#### Product Specification

108-19346


#### Application Specification

114-19110

## ET Power Connector (Continued)

### Test Results


#### Temperature Rise vs. Current Results



### Contact Summary

Refer to Standard Timer catalog 889759 for detailed information or Product/ Application Specification.

| Wire Size Range mm <sup>2</sup> | Part Number |
|---------------------------------|-------------|
| 0.2 – 0.5                       | 927840-4    |
| 0.5 – 1.0                       | 927831-4    |
| >1.0 – 2.5                      | 927837-4    |
| >2.5 – 4.0                      | 927829-5    |
| >4.0 – 6.0                      | 963709-5    |



**Material Plating** — Silver

### Technical Documents

#### Product Specification

108-18025

#### Application Specification

114-18037

**Note:** All part numbers are RoHS compliant.


## ET Power Connector (Continued)

### ET Power Cable Connector


#### Material and Finish

**Housing** — Thermoplastic,  
UL 94V-0 rated


**Latch** — Stainless Steel




**Part Number 1982299-1**  
With Right Coding Key Only



**Part Number 1982299-2**  
With Left Coding Key Only



**Part Number 1982299-3**  
With Two Coding Keys




**Part Number 1982299-4**  
Without Coding Keys

### Right-Angle PCB Header

#### Material and Finish

**Housing** — High temperature liquid  
crystal polymer, UL 94V-0 rated

**Contacts** — Silver plated copper alloy



**Part Number 1982295-1**  
With Coding Contacts


**Part Number 1982295-2**  
Without Coding Contacts

### Vertical PCB Header

#### Material and Finish

**Housing** — High temperature liquid  
crystal polymer, UL 94V-0 rated

**Contacts** — Silver plated copper alloy



**Part Number 2042274-1**  
With Coding Contacts

**Part Number 2042274-2**  
Without Coding Contacts

**Note:** All part numbers are RoHS  
compliant.

## AMP-DUAC PL Connectors

### Product Facts

- Wire to board connection system
- Improved dual-action contact design — provides better contact lead-in and reduces contact mating force
- Sequenced contacts available for mate-first break-last operation
- 4-, 6- and 12-position right-angle headers and free hanging receptacles
- 4.2 mm x 5.5 mm centerline
- Receptacle contacts designed for 26-16 AWG stranded wire
- Recognized under the Component Program of Underwriters Laboratories Inc.,  File No. E28476
- Certified by Canadian Standards Association,  File No. LR7189

### Technical Documents

**Product Specification**  
108-1646

**Application Specification**  
114-6067-Crimping Contacts

**Qualification Test Report**  
501-394

### Performance Data

**Voltage Rating** — 600 VAC


**Current Rating** — 9 Amps maximum  
in 2-position application

**Low Level Resistance** —  
10 megohms max.

**Dielectric Withstanding Voltage** —  
1500 VAC/min.

**Insulation Resistance** —  
1000 Megohms minimum

**Operating Temperature** —  
-55°C to +105°C [-67°F to +221°F]



The latest addition to the 4.2 mm Wire-to-Board Power Connectors is the AMP-DUAC PL Connector. This product uses the industry proven AMP-DUAC contacts with the addition of several housing improvements to offer significant overall improvements in connector reliability. The product is available in both component form and as fully assembled custom cable assemblies.

The AMP-DUAC PL housings are designed to confirm that all electrical contacts are fully seated. The "PL" refers to "Positive

Locking" of the contacts. It is also referred to as terminal position assurance. Contacts are inserted into the receptacle housing and the contact lock is installed to lock all the contacts into position. If any one of the contacts is not fully inserted, the contact lock cannot be installed. This feature eliminates a common concern of operator fatigue and the resulting contact back-out, which occurs when a contact is not installed properly. An improved mounting flange has also been added for more secure printed circuit board mounting.

Finally, the housings have been re-designed to provide an improved latch, which offers a metal spring instead of the original plastic spring/latch. An extended latch arm is also available for hard to reach installations or where the connectors are stacked in close proximity.

All the housings are polarized to help prevent mis-mating.

### AMP-DUAC PL Connectors (Continued)

## AMP-DUAC PL PCB Headers





## Material

**Housings** — Nylon, UL 94V-0

Color, white

**Contacts** — Brass, tin-lead

**Finish** — 0.00038 [0.00030] gold in mating area, tin-lead in solder tail, all over 0.00127 [0.000050] nickel



**Recommended Mounting Hole Pattern  
For 1.78 Max. Thick PC Board  
Component Side Shown**

| No. of Positions | Mate-First Break-Last Position # | Part Number |
|------------------|----------------------------------|-------------|
| 4                | All Standard Length 3            | 5794172-2   |
|                  |                                  | 5794172-3   |
| 6                | All Standard Length 3            | 5794173-2   |
|                  |                                  | 5794173-3   |
| 12               | All Standard Length 4            | 5794176-2   |
|                  |                                  | 5794176-3   |

**Note:** All part numbers are RoHS compliant.

## AMP-DUAC PL Connectors (Continued)

### AMP-DUAC PL Receptacles




#### Material

**Housings** — Nylon, UL94V-0

Color, White

**Technical Documents** — page 105

**Contacts** — page 113



| No. of Positions | Dimension L | Part Numbers |                            |                |                |
|------------------|-------------|--------------|----------------------------|----------------|----------------|
|                  |             | Housing      | Housing with Positive Lock | Standard Latch | Extended Latch |
| 4                | 15.9        | 794152-1*    | 794318-1                   |                |                |
| 6                | 20.1        | 794153-1     | 794319-1                   | 794150         | 794149         |
| 12               | 28.6        | 794156-1     | 794322-1                   |                |                |

\*Latch items ordered separately

Optional keying plug — Part No. 794144-1

**Note:** Position Lock Required — use one per housing — Part No. 794145-3

**Note:** All part numbers are RoHS compliant.

## AMP-DUAC PL-II Connectors

### Product Facts

- Wire-to-board connection system combining power and signal contacts
  - 10A power contacts
  - 4A signal contacts
- High conductivity copper alloy power contacts yield 30% gain in current carrying capacity compared to alternative designs
- Dual action contact design — reduces mating forces by up to 50% compared to alternative designs
- 9 power and 20 signal contacts
- Positive Lock (PL) feature on both power and signal contacts ensures contacts remain in position in cable receptacle
- Pin and receptacle contacts offered in three sizes:
  - 16 AWG
  - 18 AWG
  - 20-22 AWG
- Wide 5.2 X 5.5 mm contact spacing allows for 300V applications.

- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476



The AMP-DUAC PL-II Connectors bring both shielding and a power / signal mix to the popular AMP-DUAC product family. In addition, the wider contact spacing and the use of high conductivity materials results in a higher current carrying capacity than the original 4.2 mm pitch AMP-DUAC product.

The deep back shell allows for gathering the larger wire and insulation diameters involved with combination power / signal and shielding all in the same cable. Traditional signal connectors do not accept the range of wire sizes covered by the AMP-DUAC PL-II product.

For applications involving higher voltage cabled power distribution, this product is the ideal solution. The AMP-DUAC PL-II connector uses the original industry proven dual-action contact design which provides a lower mating force and less plating wear than alternate contact designs. The signal contacts also feature a twin-cantilever beam that mates on the milled contact surface to provide low plating wear and high long-term reliability.

The cable mounted receptacle uses the popular "Positive Lock" devices proven throughout the automotive industry to ensure all the contacts are fully seated. The "positive locks" are also referred to as "terminal position assurance". If any one of the contacts is not properly/ completely installed into the housing, then the "Positive Lock" can not be installed. This feature reduces the common concern of operator fatigue and the resulting contact back-out which occurs when a contact is not properly seated.

The shielding system fully encapsulates the inner conductors and cable braids and provides a reliable conduction to the faceplate of the mating equipment.

Finally, the cable retention is accomplished through two rear-accessed over molded jackscrews for easy installation and removal.

### Technical Documents

**Product Specification**  
108-2218

**Application Specification**  
Contact TE

### Performance Data

**Voltage Rating** — 600 VAC

**Current Rating** —  
10 Amps max on a single contact  
6 Amps on each contact in 48 pos. connector

**Low Level Resistance** —  
10 milliohms max

**Insulation Resistance** —  
1000 Megohms minimum

**Operating Temperature** —  
-40°C to +105°C



### Materials

**Housing Material** — PBT, UL 94V-0


**Colors** —  
Plugs and Receptacles — Black  
Positive Locks — White

## AMP-DUAC PL-II Connectors (Continued)


### PCB Plug Part Number 6469602-3



**Free-Hanging Receptacle  
Shown with Positive Locks  
Part Number 1469606-1**



**Shield  
Part Number 1469609-2**



**Cable Clamp  
Part Number 1469610-1**


**Note:** Other cable components required.  
Cable receptacle components shown not  
sold separately. Receptacle only sold as  
part of a finished cable assembly.

**Note:** All part numbers are RoHS compliant.

## AMP-DUAC UPC Connectors

### Product Facts

- Wire-to-wire connection system
- High conductivity copper alloy contacts yield 30% gain in current carrying capacity compared to alternative designs
- Dual action contact design — reduces mating forces by up to 50% compared to alternative designs
- Sequenced contacts for make-first-break-last operation
- 48 and 66 position housings
- 4.4 mm X 5.3 mm contact grid
- Pin and Receptacle contacts offered in three sizes:
  - 16 AWG
  - 18 AWG
  - 20-22 AWG
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476



The latest addition to the AMP-DUAC product family is the AMP-DUAC UPC connector. The UPC connector offers much higher pin counts and a variety of product improvements to make the connector more reliable and easier to use. The UPC connector uses the original industry proven dual-action contact design along with very high conductivity copper alloys to improve the current carrying capacity.

The first noticeable difference of the UPC connector is the large pin count. With either 48 or 66 positions, the housing can serve as a common mating I/O point where multiple low current power connector cables are combined into one interface. Other connectors would yield an excessive mating force when mating this number of wires, however, the low mating force of the AMP-DUAC / UPC connector allows up to 66 wires to be mated with less than a 20 lb mating force.

The next key improvement is the use of molded-in guide pins. The guide pins make the mating process very easy and provide a visual polarization of the connector. The housings mate together easily.

The use of two locking latches provides a more secure connection and the screw-mounts for the panel mounted plug provide better retention than plastic latches.

Finally, the free-hanging receptacle uses the popular "Positive Lock" device to confirm all the contacts are fully seated. The "positive locks" are also referred to as "terminal position assurance". If any one of the contacts is not properly/ completely installed into the housing, then the "Positive Lock" can not be installed. This feature eliminates the common concern of operator fatigue and the resulting contact back-out which occurs when a contact is not properly seated.

### Technical Documents

#### Product Specification

108-2248

#### Application Specification

114-13195

### Performance Data

**Voltage Rating** — 600 VAC

**Current Rating** —

11 Amps max on a single contact  
4 Amps on each contact in 48 pos. connector

**Low Level Resistance** —  
10 milliohms max

**Insulation Resistance** —  
1.2 E16 ohms minimum

**Operating Temperature** —  
-40°C to +105°C


### Materials

**Housing Material** — PBT, UL 94V-0


**Colors** —

Plugs and Receptacles — Black  
Positive Locks — White

## AMP-DUAC UPC Connectors (Continued)



**Panel-Mount Plug**  
(Accepts contacts on page 112)



**Free-Hanging Receptacle**  
(Accepts contacts on page 113)


| Size<br>(No. Circuits) | Panel-Mount<br>Plug | Dimensions   |              |              | Free-Hanging<br>Receptacle | Positive<br>Lock* |
|------------------------|---------------------|--------------|--------------|--------------|----------------------------|-------------------|
|                        |                     | A            | B            | C            |                            |                   |
| 48                     | 1934142-1           | 1.61<br>41.0 | 1.85<br>47.0 | 2.22<br>56.4 | 1934144-1                  | 1469910-1         |
| 66                     | 1934143-1           | 2.13<br>54.2 | 2.37<br>60.2 | 2.74<br>69.6 | 1934145-1                  | 1934017-1         |

\*Two (2) required for each receptacle housing. Not used in plug housings.  
Additional configurations possible. For information, please contact your TE sales engineer.

**Note:** All part numbers are RoHS compliant.

## Contacts for AMP-DUAC PL, PL-II and UPC Connectors

**Materials** — High Conductivity  
Copper Alloy  
**Finish** — Pre-Tin or Gold Plated



### Contacts, Male

#### Technical Documents

##### Product Specification

108-2248 AMP-DUAC UPC

##### Application Specification

114-6067 AMP-DUAC PL

114-13195 AMP-DUAC UPC

### AMP-DUAC PL or UPC Contacts

| Wire Size<br>Range<br>AWG [mm <sup>2</sup> ] | Ins. Dia.<br>Range       | Plating | Part Number<br>(Continuous Strip) | Applicator |
|----------------------------------------------|--------------------------|---------|-----------------------------------|------------|
| 22-20<br>[0.3-0.5]                           | .590-.094<br>[1.50-2.40] | Gold    | 794576-4                          | 680308-3   |
| 18 or 18+22<br>[0.8-1.1]                     | .087-.154<br>[2.20-3.90] | Gold    | 1934185-4                         | 1852467-3  |
| 16 or 2 @ 18<br>[1.3-1.6]                    | .098-.173<br>[2.50-4.40] | Gold    | 1934184-4                         | 1852468-3  |


Application Equipment: Extraction Tool 1976132

\*Made from Phosphor-Bronze material (low conductivity)

**Note:** All part numbers are RoHS compliant.

## Contacts for AMP-DUAC PL, PL-II and UPC Connectors (Continued)

**Materials** — High Conductivity  
Copper Alloy  
**Finish** — Gold Plated



### Contacts, Female

#### Technical Documents

##### Product Specification

108-2248 AMP-DUAC UPC

##### Application Specification

114-6067 AMP-DUAC PL

114-13195 AMP-DUAC UPC

### AMP-DUAC PL or UPC Contacts

| Wire Size<br>Range<br>AWG [mm <sup>2</sup> ] | Ins. Dia.<br>Range       | Plating | Part Number<br>(Continuous Strip) | Applicator |
|----------------------------------------------|--------------------------|---------|-----------------------------------|------------|
| 22-20<br>[0.3-0.5]                           | .590-.094<br>[1.50-2.40] | Gold    | 1934193-4                         | 1852469-3  |
| 18 or 18+22<br>[0.8-1.1]                     | .087-.154<br>[2.20-3.90] | Gold    | 1934183-4                         | 1852467-3  |
| 16 or 2 @ 18<br>[1.3-1.6]                    | .098-.173<br>[2.50-4.40] | Gold    | 1934182-4                         | 1852468-3  |


Application Equipment: Extraction Tool 1976382

**Note:** All part numbers are RoHS compliant.

## Other Soft Shell Pin & Socket Connectors


### Micro MATE-N-LOK 3 mm Connector System

- Wire-to-wire and wire-to-board, pin and receptacle connectors
- 3.0 mm [.118] centerline spacing
- 2-12 positions – single row
- 2-24 positions – dual row
- Ratings: 5A, 250 VAC
- Accommodates 30-20 AWG wire
- Panel-mount or free-hanging versions
- Dual beam receptacle contact design for improved reliability
- PCB-mount pin header assemblies available in both vertical and right-angle styles; surface-mount or through hole versions
- Available in a low profile design (<4.7 mm)




### Grace Inertia Connector System

- Wire-to-wire and wire-to-board, blade and receptacle connectors
- Wire-to-wire
  - 2.5 mm, 3.5 mm and 6.2 mm centerline spacing
  - Select 2-12 position depending on centerline spacing
- Wire-to board
  - 2.0 mm, 3.3 mm, 6.5 mm, 7.92 mm, 9.0 mm and 12.4 mm centerline spacing
  - Select 2-20 position depending on centerline spacing
- Four kinds of keying per color-coded housings
- Inertia locking mechanism on the housing which simultaneously locks when mated to prevent mismatching
- Robust connections for use in high vibration or transportation applications



### Commercial Pin and Socket Connector System

- Panel-mount or free-hanging, wire-to-wire, pin and socket connectors
- 3.68 mm [.145"] and 5.03 mm [.198"] centerline spacing
- High density, 1-9 positions – 2, 3 & 4 in-line and 4, 6 & 9 matrix
- Standard density, 1-15 positions – 2-6 in-line and 4, 6, 9, 12 & 15 matrix
- Ratings: 7A (high density) or 13A, 250 VAC or VDC
- High density system accommodates 30-18 AWG wire
- Standard density system accommodates 24-14 AWG wire
- Dual contact locking lances provide optimum contact stability
- Low contact-mating force




For more Information Order Catalog 82181, "Soft Shell Pin and Socket Connectors"

## Other Soft Shell Pin & Socket Connectors (Continued)


### Power Double Lock Connector System

- Wire-to-wire and wire-to-board, blade and receptacle connectors
- 3.96 mm [.156] and 6.5 mm [.256] centerline spacing
- High density, 1-12 positions – 2, 3 & 4 in-line and 4, 6, 8, 9, 10 & 12 matrix
- Standard density, 2-12 positions – 2, 3 & 4 in-line and 4, 6, & 12 matrix
- Ratings: 14A, 300 VAC
- Accommodates 26-16 AWG wire
- Panel-mount or free-hanging versions
- Optional double lock plate on the wire side that confirms contact seating
- Lanceless contacts prevent entanglement of contacts with each other
- Housings are polarized with four types of special keying to prevent mismatching



### Mini-Universal MATE-N-LOK and Mini-Universal MATE-N-LOK II Connector System

- Wire-to-wire and wire-to-board, pin and socket connectors
- 4.14 mm [.163"] centerline
- 1-24 and 2-24 positions, respectively
- Ratings: 9.5A and 10.5A respectively  
600 VAC or VDC
- Accommodates 30-16 AWG wire
- Compact, durable housings
- Contacts protected in the housings
- Fully polarized to provide proper mating
- Seals available for splash protection  
(Mini-Universal MATE-N-LOK system only)



### VAL-U-LOK Connector System

- Wire-to-wire and wire-to-board, pin and receptacle connectors
- 4.2 mm [.165] centerline
- 2-24 position dual row and 3-5 single row configurations
- Ratings: 9A, 600 VAC
- Accommodates 26-18 AWG wire
- Easy-to-mate, positive locking housings
- Fully isolated terminals
- Panel-mount or free-hanging versions
- Black, red and blue in addition to the standard white
- PCB headers are available in vertical, right-angle, screw-mount, and blind-mate configurations
- Intermateable with similar connectors from other manufacturers




For more Information Order Catalog 82181, "Soft Shell Pin and Socket Connectors"

## Other Soft Shell Pin & Socket Connectors (Continued)


### Commercial MATE-N-LOK Connector System

- Wire-to-wire and wire-to-board, pin and socket connectors
- 5.08 mm [.200"] centerline
- Panel-mount or free-hanging versions
- 1-16 positions
- Ratings: 19A, 250 VAC or VDC
- Accommodates 30-14 AWG wire
- Fully polarized housings
- Contact stabilization and self-aligning features
- Hot side is egg-crated for safety
- Locking devices are integral part of design



### Universal MATE-N-LOK and Universal MATE-N-LOK II Connector System

- Wire-to-wire and wire-to-board, pin and socket connectors
- 6.35 mm [.250"] centerline
- 1-15 and 2-15 positions, respectively
- Panel-mount or free-hanging versions
- Ratings: 19A, 600 VAC or VDC
- Accommodates 30-10 AWG wire
- Contacts protected in the housings
- Special keying to prevent incorrect mating
- Additional offerings include:
  - UV resistant materials
  - High temperature materials
  - Glow wire approved products
  - Special high retention contacts
  - Seals available for splash protection (UMNL only)
  - Color housings available (UMNL only)




For more Information Order Catalog 82181, "Soft Shell Pin and Socket Connectors"

## AMPINNERGY Wire-To-Wire Connectors

### Product Facts

- Rated to 600 VAC (RMS)
- Flame retardant housings 94V-0
- Housings, adapters, and power terminals keyed for proper assembly
- Stackable housings provide easy wire routing and neat wire dressing
- Built-in interlocking features better resist shock and vibration
- Usable as in-line connector, or as panel and surface-mount connector
- Available in six different colors for circuit coding and identification
- Choice of two power terminals accommodates 10-12 AWG and 14-16-18 AWG conductors
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476 
- Certified by Canadian Standards Association, File No. LR7189 
- VDE Registered #5133



AMPINNERGY wire-to-wire (WTW) Connectors provide a reliable and efficient means of interconnecting conductors employed to carry up to 600 VAC in power circuits or networks.

The WTW connectors consist of mating hermaphroditic, flame retardant polycarbonate housings into which customer terminated power contacts are inserted. Stackable in four directions through the use of molded interlocking keyways, the connectors make wire routing and dressing orderly and easy to accomplish. More importantly, the built-in interlocking features on the connectors and the accessory mounting adapters provide better resistance to the effects of shock and vibration, keeping the interconnect more stable and secure.

The design features of the WTW connector make it easily applicable to free-hanging, surface mounted or panel mounted applications. By simply sliding the accessory mounting adapters into the molded keyways of the connector housing, a free-hanging connector can be trans-

formed into a surface-mount connector or a panel-mount connector. Customer supplied 8-32 screws and nuts may be used to secure the connectors configured with the mounting adapters to printed circuit boards or distribution panels. The same hardware may be used to secure the connectors to pre-cut openings in the panels.

Furthermore, WTW connector housings, mounting adapters and power terminals are all provided with alignment or keying features that make it difficult to improperly assemble and apply the connector. Alignment slots and tabs on the plastic connector housings provide for easy mating of the housings, even in the dark! Mounting adapters have a keyway on one side and a key on the other side providing for easy assembly to the connector by touch alone if necessary. And the power terminals have a side tab that helps prevent the incorrect insertion of the terminated conductor into the housing. Once inserted, the contacts firmly

latch within the connector housing.

The WTW connector system is available in six different and distinctive colors which makes circuit differentiation and identification possible. The crimped power terminals will accommodate either 10-12 AWG or 14-16-18 AWG stranded conductors. Depending upon the conductor size and the number of conductors in the connector configuration, the current rating ranges from 10 Amps to 55 Amps.

### Technical Documents

#### Product Specification

108-1373 AMPINNERGY WTW Connectors

#### Application Specification

114-6051

#### Instruction Sheets

408-3277 AMPINNERGY Wire-To-Wire Stackable Connectors

408-3198 Inspection of AMPINNERGY System Power Contacts

For more information, request Catalog 1308885.

Catalog 1773096  
Revised 4-12

[www.te.com](http://www.te.com)

Dimensions are shown for reference purposes only. Specifications subject to change.

Dimensions are in inches and millimeters unless otherwise specified.  
USA: +1 (800) 522-6752

Canada: +1 (905) 475-6222  
Mexico/C. Am.: +52 (0) 55-1106-0800  
Latin/S. Am.: +54 (0) 11-4733-2200  
Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666  
France: +33 (0) 1-3420-8686  
Netherlands: +31 (0) 73-6246-999  
China: +86 (0) 400-820-6015


## AMPINNERGY Wire-To-Wire Connectors (Continued)

### Housings

#### Material and Finish

**Housing** — Polycarbonate, 94V-0

For surface mounting and panel mounting information, see Instruction Sheet 408-3277, AMPINNERGY Wire-To-Wire Stackable Connectors.





Customer terminated power contacts are inserted into housings



Free-Hanging Interconnections

| Color | Housing Part Numbers |
|-------|----------------------|
| White | 556137-1             |
| Black | 556137-2             |
| Green | 556137-3             |
| Red   | 556137-4             |
| Blue  | 556137-6             |
| Gray  | 556137-8             |



Wire-To-Wire Connector Housing



### Mounting Adapters

**Part Number** 557313-1

#### Material and Finish

**Housing** — Polycarbonate, Black


Two mounting adapters can be used with one or more connector housings to provide thru-panel or horizontal surface mounting capability of the completed assembly.



### External Locking Latch Clip

**Part Number** 557640-1

AMPINNERGY wire-to-wire connector housings have an integral locking feature designed to keep housings mated in most applications. However, the external locking latch clip may be used as needed in applications where severe vibration or tension may pull mated housings apart.



AMPINNERGY Wire-To-Wire Clips  
Part Number 557640-1



AMPINNERGY Wire-To-Wire Clips (Installed)  
Part Number 557640-1

**Note:** All part numbers are RoHS compliant.

## AMPINNERGY Wire-To-Wire Connectors (Continued)

### Power Terminals

#### Material and Finish

**Contacts** — Copper alloy plated with .000100 [0.00254] minimum tin

The wire-to-wire connector power contacts are available in either strip form or in loose piece form.


Contacts in strip form are terminated on continuous feed type terminators and the loose piece contacts are terminated with the hand tool or pneumatic tool.

For wire preparation and crimped contact inspection information, refer to Instruction Sheet 408-3198, Inspection of AMPINNERGY System Power Contacts.

#### Loose Piece

**Part Number** 556136-2

**Part Number** 556135-2




| Contact Part Numbers   | Wire Size (AWG) | Hand Tool Part Number | Pneumatic Tool Part Numbers | Die Set Part Numbers |
|------------------------|-----------------|-----------------------|-----------------------------|----------------------|
| 556135-2 (loose piece) | 18-16           | 69710-1               | 189721-2*                   | 58493-1              |
|                        | 14              |                       |                             | 58492-1              |
| 556136-2 (loose piece) | 12              |                       |                             | 58490-1              |
|                        | 10              |                       |                             | 58491-1              |

\*Requires "C" head adapter part number 318161-1 and adapter holder part number 189928-1. See Catalog 124208 for more information.

**Note:** The same hand tool or pneumatic tool and die sets may be used to apply the wire-to-board connector terminals.

#### Strip Form



| Contact Part Numbers | Wire Size (AWG) | AMP-O-LECTRIC Model G Terminating Machine | Applicator Part Numbers |
|----------------------|-----------------|-------------------------------------------|-------------------------|
| 556135-1 (strip)     | 18-16-14        | 354500-1                                  | 567403-3                |
| 556136-1 (strip)     | 10-12           | 354500-1                                  | 567256-6                |
| 788109-1 (strip)     | 18-14           | 354500-1                                  | 680447-3                |
| 788110-1 (strip)     | 10-12           | 354500-1                                  | 680449-3                |

**Note:** All part numbers are RoHS compliant.

## AMPINNERGY Wire-To-Board Connectors

### Product Facts

- **Ratings: 600 VAC (RMS), current ratings range from 12-35 Amps**
- **Receptacles polarized to plug**
- **Receptacles and plugs available in contact configurations of 2 through 8 positions**
- **Vertical receptacle polarized to PCB**
- **Receptacle contacts have dual solder posts for efficient heat dissipation, low millivolt drop and mechanical strength**
- **Receptacles may be mounted on PCBs .062 to .125 inch thick**
- **Plugs have positive latching to receptacles**
- **Removable crimp contacts latch firmly in plug**
- **Plugs are one-piece design**
- **Two ranges of crimped contacts accommodate either 10-12 AWG or 14-16-18 AWG conductors**
- **Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476**
- **Certified by Canadian Standards Association, File No. LR7189-239**



### Technical Documents

#### Product Specification


108-1349 AMPINNERGY WTB Connectors

#### Application Specification

114-6044 AMPINNERGY WTB Connectors

#### Instruction Sheets

408-3236 Installation of AMPINNERGY WTB Connectors  
408-3198 Inspection of AMPINNERGY Contacts



### AMPINNERGY Wire-To-Board (WTB) Connectors

Connectors provide a convenient and efficient means of delivering up to 600 VAC to component printed circuit boards and other power distribution devices in computers and peripherals, telephone systems and appliances. The WTB connectors also have automotive and industrial applications.

#### Receptacles

The AMPINNERGY WTB connector receptacles can be installed on pc boards varying in thickness from .062 inch to .125 inch. A polarizing pin is provided on the vertical receptacle assembly to aid in proper positioning on the pc board. Both the vertical and right-angle assemblies are polarized for accurate mating to the plug assemblies. The receptacle

assemblies are available in contact configurations ranging from two to eight positions.

#### Plugs

The single piece plug housings are available in contact configurations to mate with the receptacles. The plug is equipped with positive latches to allow full and more secure mating to the respective receptacle.

A make-first/break-last feature is designed into position 1 of the plug assemblies to provide grounding protection.

#### Contacts

The crimp contacts will accommodate either 10-12 AWG or 14-16-18 AWG conductors. The contacts latch firmly within the plug housing.

## AMPINNERGY Wire-To-Board Connectors (Continued)

## Vertical PCB Receptacles



## Product Facts

- Withstands vapor phase, infrared and wave soldering processes
- .040 inch minimum standoff to PCB
- Polarized to PCB; to plug
- Contact centerline spacing: .440 inch
- Overall height on PCB: .600 inch
- Fits PCB thickness .062 through .125 inch
- Contacts have dual solder posts for efficient heat dissipation, low millivolt drop and mechanical strength
- Positive latching to mating plug

## Material and Finish

**Housing** — Polyphenylene Sulfide, Black, 94V-0

### Contacts — Tin Plated Copper Alloy



**PCB Thickness — .062-.125 inch**

| No. of Positions | Dimensions           |                       |                       | Receptacle Part Numbers |
|------------------|----------------------|-----------------------|-----------------------|-------------------------|
|                  | A                    | B                     | C                     |                         |
| 2                | <b>.93</b><br>23.50  | <b>1.56</b><br>39.62  | <b>1.84</b><br>46.61  | 556881-2                |
| 3                | <b>1.37</b><br>34.68 | <b>2.00</b><br>50.80  | <b>2.28</b><br>57.79  | 556881-3                |
| 4                | <b>1.81</b><br>45.85 | <b>2.44</b><br>61.98  | <b>2.72</b><br>68.97  | 556881-4                |
| 5                | <b>2.25</b><br>57.03 | <b>2.88</b><br>73.15  | <b>3.16</b><br>80.14  | 556881-5                |
| 6                | <b>2.69</b><br>68.20 | <b>3.32</b><br>84.33  | <b>3.60</b><br>91.32  | 556881-6                |
| 7                | <b>3.13</b><br>79.38 | <b>3.76</b><br>95.50  | <b>4.04</b><br>102.49 | 556881-7                |
| 8                | <b>3.57</b><br>90.56 | <b>4.20</b><br>106.68 | <b>4.48</b><br>113.67 | 556881-8                |

**PCB Thickness — .250 inch**

| No. of Positions | Receptacle Part Numbers |
|------------------|-------------------------|
| 4                | 558574-1                |
| 6                | 558084-1                |


**Note:** All part numbers are RoHS compliant.

## Product Facts

- Withstands vapor phase, infrared and wave soldering processes
- .040 inch minimum standoff to PCB
- Receptacles polarized to plug
- Contact centerline spacing: .440 inch
- Overall height on PCB: .600 inch
- Fits PCB thickness .062 through .125 inch
- Contacts have dual solder posts for efficient heat dissipation, low millivolt drop and mechanical strength
- Positive latching to mating plug

**Housing** — Polyphenylene Sulfide, Black, 94V-0

**Contacts** — Tin Plated Copper Alloy



**PCB Thickness — .062-.125 inch**

| No. of Positions | Dimensions    |                |                | Receptacle Part Numbers |
|------------------|---------------|----------------|----------------|-------------------------|
|                  | A             | B              | C              |                         |
| 2                | .93<br>23.50  | 1.56<br>39.62  | 1.84<br>46.61  | 556882-2                |
| 3                | 1.37<br>34.68 | 2.00<br>50.80  | 2.28<br>57.79  | 556882-3                |
| 4                | 1.81<br>45.85 | 2.44<br>61.98  | 2.72<br>68.97  | 556882-4                |
| 5                | 2.25<br>57.03 | 2.88<br>73.15  | 3.16<br>80.14  | 556882-5                |
| 6                | 2.69<br>68.20 | 3.32<br>84.33  | 3.60<br>91.32  | 556882-6                |
| 7                | 3.13<br>79.38 | 3.76<br>95.50  | 4.04<br>102.49 | 556882-7                |
| 8                | 3.57<br>90.56 | 4.20<br>106.68 | 4.48<br>113.67 | 556882-8                |

**Note:** All part numbers are RoHS compliant.

## AMPINNERGY Wire-To-Board Connectors (Continued)



### Plug Housings

#### Product Facts

- One-piece housing
- Polarized to mating receptacles
- Positive latching to mating receptacles
- Accepts crimp contacts  
Part Numbers 556880-2 and 556883-1
- Internal latching of crimp contact

#### Material

**Housing** — Polycarbonate,  
Black, 94V-0



| No. of Positions | Dimensions    |               | Plug Part Numbers |
|------------------|---------------|---------------|-------------------|
|                  | A             | B             |                   |
| 2                | .85<br>21.42  | 1.20<br>30.31 | 556879-2          |
| 3                | 1.29<br>32.59 | 1.64<br>41.48 | 556879-3          |
| 4                | 1.73<br>43.77 | 2.08<br>52.66 | 556879-4          |
| 5                | 2.17<br>54.94 | 2.52<br>63.83 | 556879-5          |
| 6                | 2.61<br>77.30 | 2.96<br>75.01 | 556879-6          |
| 7                | 3.05<br>77.30 | 3.40<br>86.19 | 556879-7          |
| 8                | 3.49<br>88.47 | 3.84<br>97.36 | 556879-8          |

**Note:** All part numbers are RoHS compliant.

## AMPINNERGY Wire-To-Board Connectors (Continued)


### Crimp Contacts

#### Product Facts

- Contacts are dual beam design

#### Material and Finish

**Contacts**—Tin Plated Copper Alloy



### Wire barrel accepts one 10 or 12 AWG stranded copper conductor

**Part Number** 556880-2 Strip

**Part Number** 556880-1 Loose Piece


#### Application Tooling

##### Applicator Part Number

567256-3 (for Lead Makers)

567256-4 (for AMP-O-LECTRIC Model K Machine)

567256-6 (for AMP-O-LECTRIC Model G Machine)



### Wire barrel accepts one 14, 16 or 18 AWG stranded copper conductor

**Part Number** 556883-1 Loose Piece

**Part Number** 556883-2 Strip


#### Application Tooling Part Number

69710-1 Hand Tool

58492-1 Die Set (14 AWG)

58493-1 Die Set (18-16 AWG)

91308-1 Extraction Tool



**Note:** All part numbers are RoHS compliant.

## Circular (CPC) Connectors for Commercial Signal and Power Applications

### Product Facts

- Lightweight, all-plastic and metal-shell connectors
- CPC connectors are UL 94V-0 rated and made of stabilized, heat resistant, self-extinguishing thermo-plastic material
- Metal-shell CPC connector housings made of UL 94V-0 rated thermoplastic
- Operating temperature range: -55°C to +125°C
- Available in panel- or chassis-mount and free-hanging configurations
- Quick connect/disconnect capability with thread assist, positive detent coupling
- Built-in pin and socket protection
- Polarized for proper mating of connector halves
- Special connector configurations offer special solder and posted contacts, special receptacles with or without threaded inserts
- Full complement of optional accessories
- Recognized under the Component Program of Underwriters Laboratories Inc.  for 250 VAC, rms or 250 VDC, Service†; Series 1 and Series 3 (600 V); Series 2, Series 4, Series 5 and Series 6 (250 V) File No. E28476

†Select connectors are recognized for 600 volts service.

- Certified by Canadian Standards Association, File No. LR 7189 
- Certain products meet VDE Standard 0627 



- Produced under a Quality Management System certified to ISO 9001

A copy of the certificate is available upon request.

### Connector series for different interconnection requirements:

- Series 3 — Low density, power applications with Type XII contacts capable of carrying up to 35 Amps of current

- Series 4 — Combination of standard and power density application with Type III+ and Type XII contacts
- Series 5 — Power density application with Size 8 screw machined and precision formed contacts
- Series 6 — Combination of standard and power density application with Type III+ and Size 8 contacts

### Type XII, Precision Formed, Crimp Contacts



Male

Female

### High Current Type XII Crimp Contacts




High Current Type XII Socket

High Current Type XII Pin

For more information, request Catalog 82021.

## Circular (CPC) Connectors for Commercial Signal and Power Applications (Continued)


### Connector Series and Types



#### Series 3 — Power Contacts

Series 3 connectors accept Type XII power contacts which can carry up to 25 Amps per contact. These contacts will accommodate a wire size range of 16 to


10 AWG [1.4 to 5 mm<sup>2</sup>]. Two connector sizes are available in both standard and reverse sex connector arrangements **3 and 7 positions**.



#### Series 4 — Combination Size 16 and Power Contacts

Series 4 connectors accept Size 16 Multimate and Type XII power contacts, combining the signal and coaxial circuit capabilities of Series 1 connectors with the

power circuit capabilities of Series 3 connectors. Available in two connector sizes offering power mixing combinations totaling **16 and 22 positions**.




#### Series 5 — Power Contacts .125 POWERBAND

Series 5 connectors combine the revolutionary performance of the new POWERBAND Contact, high current contact in configurations similar to the Series 3 connectors. POWERBAND contacts offer the electrical perform-

ance of the best Mil Spec Size 8 screw-machined contacts with the economy and productivity of strip-fed, precision formed contacts.

Series 5 connectors are environmentally sealable to meet IEC IP 65 and IP 67 specifications.

Rated at 600 VAC or VDC, 45 Amps maximum in a single contact, the connectors are available in free-hanging and panel-mount applications — **one connector configuration containing three .125 POWERBAND contacts**.



#### Series 6 — Combination, Size 16 and .125 POWERBAND Contacts

Series 6 combines the high current and environmental sealing capability of Series 5, POWERBAND contacts, and the reliability of signal carrying, low current Type III+ contacts. This

combination of power and signal contacts is offered in **one connector configuration containing two .125 POWERBAND contacts and eight Type III+ signal pin and socket contacts**.

For more information, request Catalog 82021.

## Circular (CPC) Connectors for Commercial Signal and Power Applications (Continued)


### Connector Series and Types (Continued)



#### Metal-Shell, Circular Plastic Connectors (Series 3 and 4)

Metal-Shell CPC connectors consist of a black thermo-plastic insert in a nickel-plated, zinc alloy shell. These connectors

are currently available in **shell sizes 14, 22 and 28, and in two basic configurations consisting of plugs and square flange receptacles.**



#### Miniature CPC Connectors

These compact connectors accept existing Mini-Universal MATE-N-LOK pin and socket contacts, 30-18 AWG [.05-.8 mm<sup>2</sup>].

Two shell sizes (8 or 11) are available, accommodating **from 1 to 4 and 5 to 9 positions.**

Featuring high contact density and IP67 sealing, these durable connectors are well suited for many wire-to-wire, wire-to-board, and wire-to-panel applications.

For more information,  
request Catalog 82021.

## High Current Products (LOUVERTAC Contacts)

### Product Facts

- Pins and sockets have low insertion force
- High current ratings with very low resistance
- All plated products are gold or silver plated
- LOUVERTAC bands have a temperature range from  $-196^{\circ}\text{C}$  to  $+200^{\circ}\text{C}$  available
- Formed bands are available for up to 1.250 [31.75] pin diameter


The transfer of high current with manageable insertion and withdrawal forces has always presented a challenge to the connector industry.

LOUVERTAC bands provide a unique means of transferring high amperage with a resultant space and weight

savings. TE offers a wide range of pin and socket sizes for your applications. Strip and formed LOUVERTAC bands are also offered for customer use in their own contact design. The wide variety of flat and formed male and female bands provide the ability to

design electrical connections more inexpensively and quickly. LOUVERTAC products are your high current applications solution.

The variety of pins and sockets available from TE provide a quick and simple solution to most high current applications.



## High Current Products (LOUVERTAC Contacts) (Continued)

### Thread-Mount Sockets

These sockets are designed for easy installation and removal. The large variety of sizes have ratings from 30 continuous Amps and can be mated with Thread-Mount Pins and Crimp Pins.

#### Material


**Body** — Brass

**LOUVERTAC Band** — Beryllium Copper

#### Finish

**Body** — Silver


**LOUVERTAC Band** — See Table



| Mating Pin Dia. | Part Number | Thread  | Contin. Current (Amp) | Voltage Drop (mV) | Dimensions  |              |              |              |              |              | LOUVERTAC Band Plating |
|-----------------|-------------|---------|-----------------------|-------------------|-------------|--------------|--------------|--------------|--------------|--------------|------------------------|
|                 |             |         |                       |                   | A Dia.      | B Dia.       | C            | D            | E Ref.       | F            |                        |
| 2 mm            | 192059-1    | M3x0.5  | 30                    | 12                | .080<br>2.0 | .220<br>5.6  | .670<br>17.0 | 1.42<br>36.1 | .630<br>16   | .790<br>20.1 | Silver                 |
| 4 mm            | 192129-1    | 10-32   | 60                    | 10                | .160<br>4.1 | .280<br>7.1  | .790<br>20.1 | 2.00<br>50.8 | 1.00<br>25.4 | 1.00<br>25.4 | Gold                   |
| 6 mm            | 192211-1    | 1/4-28  | 100                   | 11                | .240<br>6.1 | .410<br>10.4 | .800<br>20.3 | 2.09<br>53.1 | 1.00<br>25.4 | 1.09<br>27.7 | Gold                   |
| 8 mm            | 192271-1    | 5/16-24 | 185                   | 12                | .320<br>8.1 | .560<br>14.2 | 1.40<br>35.6 | 3.07<br>78   | 1.42<br>36.0 | 1.65<br>41.9 | Silver                 |

### Thread-Mount Pins

These pins are designed for thread-mount. The large variety of sizes have ratings from 30 continuous Amps and are designed to be mated with Thread-Mount Sockets, Threaded Sleeve Sockets and Crimp Sockets.



**Material** — Brass

**Finish** — Silver



| Pin Dia. | Part Number | Thread  | Contin. Current (Amp) | Dimensions  |             |              |              |              |
|----------|-------------|---------|-----------------------|-------------|-------------|--------------|--------------|--------------|
|          |             |         |                       | A Dia.      | B           | C            | D            | E Ref.       |
| 2 mm     | 192085-1    | M3x0.5  | 30                    | .080<br>2.0 | .16<br>4.1  | .65<br>16.5  | 1.40<br>35.6 | .63<br>15.0  |
| 4 mm     | 192161-1    | 10-32   | 60                    | .160<br>4.1 | .25<br>6.4  | .77<br>19.6  | 1.91<br>48.5 | .99<br>25.1  |
| 6 mm     | 192244-1    | 1/4-28  | 100                   | .240<br>6.1 | .31<br>7.9  | .77<br>19.6  | 2.03<br>51.6 | 1.11<br>25.2 |
| 8 mm     | 192293-1    | 5/16-24 | 185                   | .320<br>8.1 | .44<br>11.2 | 1.30<br>33.0 | 2.95<br>74.9 | 1.47<br>37.3 |

**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)

### Threaded Sleeve Sockets

The Threaded Sleeve Socket Assembly is designed for High Current in a restricted space. The Sleeve can be screwed directly into a threaded bus bar or it may be inserted into a drilled hole in the bus bar with tightened nuts on each side of the bus bar. A Crimp Pin or Thread-Mount Pin can be attached to a cable for the completed connector.



#### Material

**Body** — Brass


**LOUVERTAC Band** —  
Beryllium Copper

#### Finish

**Body** — Silver

**LOUVERTAC Band** —  
See Table

| Mating Pin Dia. | Part Number | Thread            | Contin. Current (Amp) | Voltage Drop (mV) | Dimensions   |              |             |             | LOUVERTAC Band Plating |
|-----------------|-------------|-------------------|-----------------------|-------------------|--------------|--------------|-------------|-------------|------------------------|
|                 |             |                   |                       |                   | A Dia.       | B            | C           | D           |                        |
| 2 mm            | 1-192447-0  | 5/16-32           | 30                    | 12                | .090<br>2.3  | .650<br>16.5 | .060<br>1.5 | .060<br>1.5 | Silver                 |
| 4 mm            | 192447-8    | 5/16-32           | 60                    | 10                | .160<br>4.1  | .770<br>19.6 | .060<br>1.5 | .060<br>1.5 | Gold                   |
| 6 mm            | 192447-2    | 1/2-20            | 100                   | 11                | .240<br>6.1  | .770<br>19.6 | .078<br>2.0 | .078<br>2.0 | Gold                   |
| 8 mm            | 1-192447-8  | 9/16-18           | 185                   | 12                | .320<br>8.1  | 1.35<br>34.3 | .100<br>2.5 | .100<br>2.5 | Silver                 |
| 12 mm           | 1-192447-2  | 3/4-16 UNF<br>-2A | 290                   | 13                | .479<br>12.2 | 1.34<br>34.0 | .130<br>3.3 | .130<br>3.3 | Silver                 |




**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)

### Crimp Pins

Crimp Pins feature a mechanism for locking the pin into a housing designed by the customer. The 2 mm and 4 mm pins are crimped with a Daniels Hand Crimp Tool. Pin sizes from 6 mm to 8 mm may be crimped with the indicated tooling and a DYNA-CRIMP 69120-1 electric-hydraulic power unit. The large variety of sizes have ratings from 24 continuous Amps and can be mated with Thread-Mount Socket Assemblies, Threaded Sleeve Socket Assemblies or Crimp Sockets.



### Material

**Body** — Copper Alloy

**Retention Spring** — Stainless Steel or Beryllium Copper

### Finish

**Body** — Silver

| Pin Dia. | Part Number | Contin. Current (Amp) | Voltage Drop (mV) | Dimensions   |              |               |              |              |              |             | Use with AWG | Tooling Part Numbers |            |                 |
|----------|-------------|-----------------------|-------------------|--------------|--------------|---------------|--------------|--------------|--------------|-------------|--------------|----------------------|------------|-----------------|
|          |             |                       |                   | A            | B Dia.       | C Dia.        | D            | E            | F            | G Dia.      |              | Crimp Die            | Crimp Head | Extraction Tool |
| 2 mm     | 193837-1    | 30                    | 12                | 1.40<br>35.6 | .225<br>5.72 | .100<br>2.54  | .640<br>16.3 | .211<br>5.36 | .050<br>1.27 | .080<br>2.0 | 12-14        | M310                 | TP1019     | 318813-1        |
| 4 mm     | 193837-2    | 44                    | 8                 | 1.53<br>38.9 | .300<br>7.6  | .145<br>3.7   | .750<br>19.1 | .211<br>5.36 | .050<br>1.27 | .160<br>4.0 | 10           | M310                 | TP1020     | 679916-1        |
|          | 193837-3    | 60                    | 8                 | 1.53<br>38.9 | .300<br>7.6  | .181<br>4.60  | .750<br>19.1 | .211<br>5.36 | .050<br>1.27 | .160<br>4.0 | 8            | M310                 | TP1020     | 679916-1        |
| 6 mm     | 193837-4    | 76                    | 9                 | 1.64<br>41.7 | .410<br>10.4 | .235<br>5.97  | .760<br>19.3 | .211<br>5.36 | .050<br>1.27 | .240<br>6.0 | 6            | 69133-1              | 69099      | 679917-1        |
|          | 193837-5    | 100                   | 9                 | 1.73<br>43.9 | .410<br>10.4 | .290<br>7.37  | .760<br>19.3 | .211<br>5.36 | .050<br>1.27 | .240<br>6.0 | 4            | 69134-2              | 69099      | 679917-1        |
| 8 mm     | 193837-6    | 135                   | 10                | 2.50<br>63.5 | .570<br>14.5 | .390<br>9.91  | 1.30<br>33.0 | .211<br>5.36 | .050<br>1.27 | .320<br>8.0 | 2            | 46765-3              | 69099      | 679918-1        |
|          | 193837-7    | 185                   | 12                | 2.63<br>66.8 | .570<br>14.5 | .487<br>12.37 | 1.30<br>33.0 | .211<br>5.36 | .050<br>1.27 | .320<br>8.0 | 1/0          | 46766-2              | 69099      | 679918-1        |


**Notes:** 1. Additional information on AMPPOWER terminal hydraulic crimping is available in Catalog 82025.  
2. Application Specification — 114-16022

**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)

### Crimp Sockets

Crimp Sockets feature a mechanism for locking the socket into a housing designed by the customer. A TE extraction tool is offered to remove the contact. The 2 mm and 4 mm sockets are crimped with a Daniels Hand Crimp Tool. Socket sizes from 6 mm to 8 mm may be crimped with the indicated tooling and a DYNA-CRIMP 69120-1 electric-hydraulic power unit. The large variety of sizes have ratings from 24 continuous Amps and can be mated with Thread-Mount Pins or Crimp Pins.



### Material

**Body** — Copper Alloy

**LOUVERTAC Band** — Beryllium Copper

**Retention Spring** — Stainless Steel or Beryllium Copper

### Finish

**Body** — Silver

**LOUVERTAC Band** — Silver

| Mating Pin Dia. | Part Number | Contin. Current (Amp) | Voltage Drop (mV) | Dimensions   |                |               |               |              |              | Use with AWG | Tooling Part Numbers |            |                 |
|-----------------|-------------|-----------------------|-------------------|--------------|----------------|---------------|---------------|--------------|--------------|--------------|----------------------|------------|-----------------|
|                 |             |                       |                   | A            | B Dia.         | C Dia.        | D             | E            | F            |              | Crimp Die            | Crimp Head | Extraction Tool |
| 2 mm            | 193673-1    | 24                    | 10                | 1.13<br>28.7 | .230<br>5.8    | .100<br>2.54  | .420<br>10.7  | .211<br>5.36 | .209<br>5.31 | 14           | M310                 | TP1021     | 318813-1        |
|                 | 193673-1    | 30                    | 12                | 1.13<br>28.7 | .230<br>5.8    | .100<br>2.54  | .420<br>10.7  | .211<br>5.36 | .209<br>5.31 | 12           | M310                 | TP1021     | 318813-1        |
| 4 mm            | 193673-2    | 44                    | 8                 | 1.31<br>33.3 | .300<br>7.6    | .145<br>3.68  | .400<br>10.2  | .211<br>5.36 | .209<br>5.31 | 10           | M310                 | TP1022     | 679916-1        |
|                 | 193673-3    | 60                    | 8                 | 1.31<br>33.3 | .300<br>7.6    | .181<br>4.60  | .410<br>10.4  | .211<br>5.36 | .209<br>5.31 | 8            | M310                 | TP1022     | 679916-1        |
| 6 mm            | 193673-4    | 76                    | 9                 | 1.42<br>36.1 | .410<br>10.4   | .235<br>5.97  | .460<br>11.7  | .211<br>5.36 | .209<br>5.31 | 6            | 69133-1              | 69099      | 679917-1        |
|                 | 193673-5    | 100                   | 9                 | 1.48<br>37.6 | .410<br>10.4   | .290<br>7.37  | .530<br>13.5  | .211<br>5.36 | .209<br>5.31 | 4            | 69134-2              | 69099      | 679917-1        |
| 8 mm            | 193673-6    | 135                   | 10                | 2.26<br>57.4 | .570<br>14.5   | .390<br>9.91  | .640<br>16.3  | .211<br>5.36 | .209<br>5.31 | 2            | 46765-3              | 69099      | 679918-1        |
|                 | 193673-7    | 185                   | 12                | 2.45<br>62.2 | .570<br>14.5   | .487<br>12.37 | —             | .211<br>5.36 | .209<br>5.31 | 1/0          | 46766-2              | 69099      | 679918-1        |
| 12 mm           | 193673-8*   | 290                   | 13                | 2.51<br>63.7 | .795<br>20.19  | .541<br>13.74 | .930<br>23.62 | —            | —            | 2/0          | 46767-2              | 69099      | —               |
| 20 mm           | 1-193673-2* | 480                   | 11                | 3.17<br>80.5 | 1.072<br>27.23 | .721<br>18.31 | 1.24<br>31.50 | —            | —            | 250 MCM      | 46751-2              | 69099      | —               |

\* Socket contact uses retention ring (not supplied) for locking contact in housing. See Application Specification 114-16022 for details.

**Notes:** 1. Additional information on AMPPOWER terminal hydraulic crimping is available in Catalog 82025.  
2. Application Specification — 114-16022

**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)

### Thread-Mount Fork

The Thread-Mount Fork was developed to mount onto a plate or bus bar designed and fabricated by the customer. The Fork is rated at 84 Amps (Upper Tolerance Limit) and accepts a .087 thick blade or circuit board. The anti-rotation pin is in place to help prevent the Fork from rotating while tightening the screw.

#### Material

**Fork** — Zinc Al Alloy

**LOUVERTAC Bands** — Copper Alloy


**Screw** — Steel

#### Finish

**Fork** — Silver



**LOUVERTAC Bands** — Silver

**Screw** — Zinc



Part Number 194257-1

### Right-Angle Thread-Mount Fork



Part Number 194305-1

#### Material

**Fork** — Zinc Al Alloy

**LOUVERTAC Bands** — Copper Alloy

**Spring Pin** — Stainless Steel

#### Finish

**Fork** — Silver

**LOUVERTAC Bands** — Silver

**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)

### LOUVERTAC Strip, Torsional Louver Type


The Torsional Louver Type Band was designed as an electrical interface that allows the transfer of high current and a more generous tolerance between mating surfaces. A strip can be sized with scissors in an on-site installation. They are available for use in flat and circular applications. A male band is used on the outside diameter of a pin. The female band is used on the inside diameter of a socket.

**Material** — Beryllium Copper

**Finish** — See Tables

### LAO .092 [2.27] Louver Height


Tooth Angle — 15°  
Minimum Diameter — 1.75 inches



| Part Number | Application    | Material Thickness | Suggested Current Limit per inch | Finish |
|-------------|----------------|--------------------|----------------------------------|--------|
| 192000-2    | Flat or Female | .006<br>.15        | 150                              | Silver |
| 192000-9    | Flat or Female | .010<br>.25        | 250                              | Silver |
| 192001-4    | Flat or Male   | .006<br>.15        | 150                              | Silver |

### LAOG Louver Height — See Table


Tooth Angle — 45°  
Minimum Diameter — 1.75 inches



| Part Number | Application    | Material Thickness | Suggested Current Limit per inch | Louver Height | Finish   |
|-------------|----------------|--------------------|----------------------------------|---------------|----------|
| 192002-1    | Flat or Female | .006<br>.15        | 300                              | .105<br>2.67  | Unplated |
| 192002-2    | Flat or Female | .006<br>.15        | 300                              | .105<br>2.67  | Silver   |
| 192002-3    | Flat or Female | .010<br>.25        | 500                              | .110<br>2.79  | Unplated |

### LAIA .050 [1.27] Louver Height

Tooth Angle — See Table  
Minimum Diameter — 1½ inches



| Part Number | Application    | Material Thickness | Suggested Current Limit per inch | Tooth Angle | Finish |
|-------------|----------------|--------------------|----------------------------------|-------------|--------|
| 192004-4    | Flat or Female | .004<br>.10        | 150                              | 15°         | Silver |
| 192004-6    | Flat or Female | .004<br>.10        | 150                              | 45°         | Silver |
| 192004-8    | Flat or Female | .006<br>.15        | 250                              | 15°         | Silver |
| 1-192004-1  | Flat or Female | .006<br>.15        | 250                              | 15°         | Gold   |
| 1-192004-4  | Flat or Female | .006<br>.15        | 250                              | 45°         | Silver |
| 192007-7    | Flat or Male   | .006<br>.15        | 250                              | 15°         | Silver |
| 192008-1    | Flat or Male   | .004<br>.10        | 150                              | 45°         | Silver |

**Notes:** 1. Product will be sold by the foot except where length is specified.  
2. Suggested current limits are application dependent.  
3. Additional sizes are available upon request.

**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)



### LOUVERTAC Strip, Bridge Louver Type

The Bridge Louver Type Band was designed to transfer high currents in very small spaces. A strip can be sized with scissors in an on-site installation. They are available for use in flat and circular applications. A male band is used on the outside diameter of a pin. The female band is used on the inside diameter of a socket.

**Material**—Beryllium Copper

#### LAIII .034 [.86] Louver Height



Minimum Diameter — 1 inch  
Suggested Current Limit  
Per Inch — 150 Amps  
Material Thickness — .006 [.15]



| Part Number | Application | Finish |
|-------------|-------------|--------|
| 192038-6    | Female      | Silver |
| 192039-5    | Male        | Silver |

#### LAIV .026 [.66] Louver Height



Minimum Diameter — ¾ inch  
Suggested Current Limit  
Per Inch — 150 Amps  
Material Thickness — See Table



| Part Number | Application | Finish | Material Thickness |
|-------------|-------------|--------|--------------------|
| 1-192041-2  | Female      | Silver | .006<br>.15        |
| 192042-5    | Male        | Silver | .006<br>.15        |
| 192048-2    | Male        | Gold   | .004<br>.10        |

#### LAV .022 [.56] Louver Height

Minimum Diameter — ¾ inch  
Suggested Current Limit  
Per Inch — 120 Amps  
Material Thickness — See Table



| Part Number | Application | Finish | Material Thickness |
|-------------|-------------|--------|--------------------|
| 1-192044-9  | Female      | Silver | .005<br>.13        |
| 192045-5    | Male        | Silver | .005<br>.13        |
| 192045-2    | Male        | Gold   | .004<br>.10        |
| 1-192045-2  | Male        | Gold   | .004<br>.10        |

**Notes:** 1. Product will be sold by the foot except where length is specified.  
2. Suggested current limits are application dependent.  
3. Additional sizes are available upon request.

**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)

### Preformed Female LOUVERTAC Bands

#### Female Torsional Formed Type

#### LA1A/LA1B

**.050 [1.27] Louver Height**

**Material**—Beryllium Copper


**Finish**—See Table

**Tooth Angle**—See Table

LOUVERTAC Bands can be manufactured as preformed diameters. This will allow the insertion of the band into a socket.

The diameter indicated is the mating pin diameter that will be inserted into the socket assembly.

Consult Product Engineering for mounting details.



| Part Number | Mating Pin Dia. | Material Thickness | Suggested Current Limit (A) | Finish | Tooth Angle | Band Type |
|-------------|-----------------|--------------------|-----------------------------|--------|-------------|-----------|
| 4-192013-3  | .312 [7.92]     | .004 [.10]         | 150                         | Silver | 15°         | LA1A      |
| 4-192013-5  | .312 [7.92]     | .006 [.15]         | 250                         | Silver | 15°         | LA1A      |
| 5-192013-1  | .355 [9.01]     | .006 [.15]         | 275                         | Gold   | 15°         | LA1A      |
| 5-192013-4  | .375 [9.53]     | .006 [.15]         | 300                         | Silver | 15°         | LA1A      |
| 5-192013-5  | .394 [10.00]    | .006 [.15]         | 325                         | Silver | 15°         | LA1A      |
| 5-192013-8  | .434 [11.02]    | .006 [.15]         | 350                         | Gold   | 15°         | LA1A      |
| 5-192013-9  | .437 [11.10]    | .006 [.15]         | 350                         | Silver | 15°         | LA1A      |
| 6-192013-7  | .472 [11.99]    | .006 [.15]         | 375                         | Silver | 15°         | LA1A      |
| 6-192013-9  | .472 [11.99]    | .008 [.20]         | 375                         | Silver | 15°         | LA1A      |
| 7-192013-1  | .500 [12.70]    | .006 [.15]         | 400                         | Silver | 15°         | LA1A      |
| 7-192013-6  | .551 [14.00]    | .006 [.15]         | 450                         | Silver | 15°         | LA1A      |
| 8-192013-2  | .625 [15.88]    | .006 [.15]         | 500                         | Silver | 15°         | LA1A      |
| 8-192013-6  | .625 [15.88]    | .008 [.20]         | 475                         | Silver | 15°         | LA1A      |
| 8-192013-9  | .685 [17.40]    | .006 [.15]         | 550                         | Silver | 15°         | LA1A      |
| 9-192013-6  | .750 [19.05]    | .006 [.15]         | 600                         | Silver | 15°         | LA1A      |
| 192033-3    | .750 [19.05]    | .008 [.20]         | 600                         | Silver | 15°         | LA1A      |
| 1-192033-9  | .875 [22.22]    | .006 [.15]         | 675                         | Gold   | 15°         | LA1A      |
| 2-192033-0  | .875 [22.22]    | .006 [.15]         | 700                         | Silver | 15°         | LA1A      |
| 2-192033-6  | 1.000 [25.40]   | .006 [.15]         | 775                         | Silver | 15°         | LA1A      |
| 3-192033-4  | 1.250 [31.75]   | .006 [.15]         | 975                         | Silver | 15°         | LA1A      |
| 5-192033-2  | 1.000 [25.40]   | .008 [.20]         | 800                         | Silver | 15°         | LA1A      |
| 3-192013-8  | 1.187 [30.10]   | .006 [.15]         | 950                         | Silver | 45°         | LA1B      |
| 5-192033-0  | .812 [20.62]    | .008 [.20]         | 625                         | Silver | 45°         | LA1B      |

**Notes:** 1. Suggested current limits are application dependent.  
2. Additional sizes are available upon request.

**Note:** All part numbers are RoHS compliant.

## High Current Products (LOUVERTAC Contacts) (Continued)


### Preformed Female LOUVERTAC Bands

(Continued)

### Female Bridge Formed Type LAIII through LAVI

Material — Beryllium Copper

Finish — See Table



| Part Number | Mating Pin Dia. | Length     | Material Thickness | Suggested Current Limit (A) | Finish   | Band Type |
|-------------|-----------------|------------|--------------------|-----------------------------|----------|-----------|
| 1-192038-9  | .125 [3.18]     | .47 [11.9] | .004 [.10]         | 40                          | Nickel   | LAIII     |
| 2-192038-8  | .197 [5.00]     | .47 [11.9] | .006 [.15]         | 90                          | Gold     | LAIII     |
| 3-192038-7  | .236 [6.00]     | .47 [11.9] | .006 [.15]         | 100                         | Gold     | LAIII     |
| 4-192038-0  | .236 [6.00]     | .47 [11.9] | .008 [.20]         | 120                         | Gold     | LAIII     |
| 4-192038-1  | .236 [6.00]     | .47 [11.9] | .008 [.20]         | 120                         | Gold     | LAIII     |
| 4-192038-8  | .250 [6.35]     | .47 [11.9] | .006 [.15]         | 110                         | Silver   | LAIII     |
| 4-192038-9  | .250 [6.35]     | .47 [11.9] | .006 [.15]         | 110                         | Gold     | LAIII     |
| 5-192038-4  | .250 [6.35]     | .47 [11.9] | .008 [.20]         | 125                         | Gold     | LAIII     |
| 6-192038-0  | .280 [7.11]     | .47 [11.9] | .008 [.20]         | 165                         | Silver   | LAIII     |
| 6-192038-1  | .280 [7.11]     | .47 [11.9] | .008 [.20]         | 125                         | Gold     | LAIII     |
| 6-192038-2  | .250 [6.35]     | .47 [11.9] | .006 [.15]         | 125                         | Unplated | LAIII     |
| 6-192038-5  | .315 [8.00]     | .47 [11.9] | .008 [.20]         | 185                         | Silver   | LAIII     |
| 6-192038-6  | .315 [8.00]     | .47 [11.9] | .008 [.20]         | 185                         | Gold     | LAIII     |
| 7-192038-7  | .394 [10.00]    | .47 [11.9] | .008 [.20]         | 250                         | Silver   | LAIII     |
| 8-192038-1  | .437 [11.10]    | .47 [11.9] | .008 [.20]         | 270                         | Silver   | LAIII     |
| 8-192038-6  | .472 [11.99]    | .47 [11.9] | .008 [.20]         | 300                         | Silver   | LAIII     |
| 9-192038-4  | .500 [12.70]    | .47 [11.9] | .008 [.20]         | 300                         | Tin      | LAIII     |
| 192040-8    | .375 [9.53]     | .47 [11.9] | .008 [.20]         | 200                         | Gold     | LAIII     |
| 2-192040-7  | .250 [6.35]     | .47 [11.9] | .006 [.15]         | 110                         | Gold     | LAIII     |
| 2-192041-9  | .025 [0.64]     | .32 [8.13] | .005 [.13]         | 15                          | Gold     | LAIV      |
| 4-192041-0  | .062 [1.57]     | .32 [8.13] | .006 [.15]         | 25                          | Silver   | LAIV      |
| 4-192041-1  | .062 [1.57]     | .32 [8.13] | .006 [.15]         | 25                          | Gold     | LAIV      |
| 4-192041-4  | .080 [2.03]     | .32 [8.13] | .006 [.15]         | 35                          | Gold     | LAIV      |
| 5-192041-0  | .093 [2.36]     | .32 [8.13] | .005 [.13]         | 40                          | Gold     | LAIV      |
| 5-192041-9  | .100 [2.54]     | .32 [8.13] | .006 [.15]         | 50                          | Gold     | LAIV      |
| 6-192041-9  | .125 [3.18]     | .32 [8.13] | .006 [.15]         | 60                          | Gold     | LAIV      |
| 7-192041-4  | .157 [4.00]     | .32 [8.13] | .006 [.15]         | 65                          | Gold     | LAIV      |
| 7-192041-7  | .157 [4.00]     | .32 [8.13] | .006 [.15]         | 65                          | Silver   | LAIV      |
| 7-192041-8  | .157 [4.00]     | .32 [8.13] | .006 [.15]         | 65                          | Gold     | LAIV      |
| 8-192041-4  | .157 [4.00]     | .32 [8.13] | .008 [.20]         | 75                          | Gold     | LAIV      |
| 8-192041-9  | .173 [4.39]     | .32 [8.13] | .006 [.15]         | 70                          | Gold     | LAIV      |
| 192043-6    | .218 [5.54]     | .32 [8.13] | .006 [.15]         | 95                          | Silver   | LAIV      |
| 1-192043-5  | .254 [6.45]     | .32 [8.13] | .006 [.15]         | 110                         | Silver   | LAIV      |
| 1-192043-6  | .250 [6.35]     | .32 [8.13] | .006 [.15]         | 120                         | Gold     | LAIV      |
| 2-192043-0  | .280 [7.11]     | .32 [8.13] | .006 [.15]         | 130                         | Gold     | LAIV      |
| 2-192043-7  | .315 [8.00]     | .32 [8.13] | .006 [.15]         | 165                         | Silver   | LAIV      |
| 4-192043-5  | .375 [9.53]     | .32 [8.13] | .006 [.15]         | 175                         | Gold     | LAIV      |
| 5-192043-0  | .375 [9.50]     | .32 [8.13] | .007 [.18]         | 175                         | Tin      | LAIV      |
| 6-192043-7  | .602 [15.30]    | .32 [8.13] | .006 [.15]         | 285                         | Gold     | LAIV      |
| 7-192043-2  | .125 [3.18]     | .32 [8.13] | .006 [.15]         | 60                          | Silver   | LAIV      |
| 9-192043-3  | .157 [4.00]     | .32 [8.13] | .006 [.15]         | 65                          | Silver   | LAIV      |
| 9-192043-6  | .725 [18.40]    | .32 [8.13] | .006 [.15]         | 350                         | Silver   | LAIV      |
| 4-192044-1  | .030 [0.76]     | .20 [5.10] | .005 [.13]         | 13                          | Gold     | LAV       |
| 4-192044-2  | .030 [0.76]     | .20 [5.10] | .005 [.13]         | 11                          | Unplated | LAV       |
| 4-192044-4  | .055 [1.40]     | .20 [5.10] | .005 [.13]         | 20                          | Gold     | LAV       |
| 4-192044-7  | .060 [1.54]     | .20 [5.10] | .004 [.10]         | 22                          | Gold     | LAV       |
| 5-192044-6  | .062 [1.57]     | .20 [5.10] | .005 [.13]         | 25                          | Gold     | LAV       |
| 5-192044-8  | .065 [1.65]     | .20 [5.10] | .005 [.13]         | 23                          | Unplated | LAV       |
| 6-192044-0  | .080 [2.03]     | .20 [5.10] | .004 [.10]         | 30                          | Silver   | LAV       |
| 6-192044-4  | .080 [2.03]     | .20 [5.10] | .005 [.13]         | 30                          | Gold     | LAV       |

**Note:** All part numbers are RoHS compliant.

**Notes:** 1. Suggested current limits are application dependent.  
2. Additional sizes are available upon request.

## High Current Products (LOUVERTAC Contacts) (Continued)


### Preformed Female LOUVERTAC Bands

(Continued)

### Female Bridge Formed Type LAIII through LAVI

(Continued)

**Material** — Beryllium Copper

**Finish** — See Table


| Part Number | Mating Pin Dia. | Length     | Material Thickness | Suggested Current Limit (A) | Finish   | Band Type |
|-------------|-----------------|------------|--------------------|-----------------------------|----------|-----------|
| 6-192044-6  | .080 [2.03]     | .20 [5.10] | .008 [.20]         | 30                          | Gold     | LAV       |
| 7-192044-1  | .093 [2.36]     | .20 [5.10] | .005 [.13]         | 35                          | Gold     | LAV       |
| 8-192044-1  | .125 [3.18]     | .20 [5.10] | .004 [.10]         | 45                          | Gold     | LAV       |
| 8-192044-3  | .125 [3.18]     | .20 [5.10] | .005 [.13]         | 45                          | Silver   | LAV       |
| 8-192044-4  | .125 [3.18]     | .20 [5.10] | .005 [.13]         | 45                          | Gold     | LAV       |
| 8-192044-7  | .125 [3.18]     | .20 [5.10] | .005 [.13]         | 45                          | Unplated | LAV       |
| 192046-6    | .172 [4.40]     | .20 [5.10] | .006 [.15]         | 65                          | Gold     | LAV       |
| 1-192046-6  | .225 [5.70]     | .20 [5.10] | .006 [.15]         | 85                          | Gold     | LAV       |
| 1-192046-9  | .250 [6.35]     | .20 [5.10] | .006 [.15]         | 110                         | Gold     | LAV       |
| 2-192046-0  | .250 [6.30]     | .20 [5.10] | .006 [.15]         | 95                          | Tin      | LAV       |
| 3-192046-0  | .400 [10.2]     | .20 [5.10] | .005 [.13]         | 150                         | Gold     | LAV       |
| 5-192046-0  | .750 [19.0]     | .20 [5.10] | .005 [.13]         | 285                         | Gold     | LAV       |
| 5-192046-9  | .134 [3.40]     | .20 [5.10] | .006 [.15]         | 50                          | Gold     | LAV       |
| 1-192047-4  | .040 [1.00]     | .10 [2.54] | .004 [.10]         | 15                          | Gold     | LAVI      |
| 1-192047-9  | .062 [1.60]     | .10 [2.54] | .004 [.10]         | 22                          | Gold     | LAVI      |
| 3-192047-7  | .125 [3.20]     | .10 [2.54] | .004 [.10]         | 45                          | Gold     | LAVI      |
| 5-192047-1  | .256 [6.50]     | .10 [2.54] | .004 [.10]         | 95                          | Gold     | LAVI      |
| 5-192047-3  | .272 [6.90]     | .10 [2.54] | .004 [.10]         | 65                          | Gold     | LAVI      |
| 7-192047-5  | .256 [6.50]     | .10 [2.54] | .004 [.10]         | 95                          | Unplated | LAVI      |

**Note:** All part numbers are RoHS compliant.

**Notes:** 1. Suggested current limits are application dependent.  
2. Additional sizes are available upon request.

## High Current Products (LOUVERTAC Contacts) (Continued)

### Preformed Male LOUVERTAC Bands

#### Male Torsional Formed Type


##### LA1AS/LA1BS

**Material**—Beryllium Copper

**Finish**—See Table

**Tooth Angle**—See Table

LOUVERTAC Bands can be formed into a "male" shape for use on a pin. Selection begins with the amperage requirement and then the mating hole diameter. Consult Product Engineering for mounting details.




| Part Number | Mating Hole Dia. | Material Thickness | Suggested Current Limit (A) | Finish | Tooth Angle | Band Type |
|-------------|------------------|--------------------|-----------------------------|--------|-------------|-----------|
| 192007-9    | .312 [7.92]      | .006 [.15]         | 200                         | Silver | 15°         | LA1AS     |
| 1-192007-9  | .620 [15.7]      | .006 [.15]         | 425                         | Silver | 15°         | LA1AS     |
| 2-192007-5  | .750 [19.0]      | .008 [.20]         | 550                         | Silver | 15°         | LA1AS     |
| 3-192007-1  | 1.000 [25.4]     | .006 [.15]         | 750                         | Silver | 15°         | LA1AS     |
| 192008-6    | .500 [12.7]      | .006 [.15]         | 350                         | Silver | 45°         | LA1BS     |
| 1-192008-3  | .750 [19.0]      | .008 [.20]         | 550                         | Silver | 45°         | LA1BS     |
| 1-192008-5  | .781 [19.8]      | .006 [.15]         | 575                         | Silver | 45°         | LA1BS     |
| 2-192008-1  | .875 [22.22]     | .008 [.20]         | 650                         | Silver | 45°         | LA1BS     |
| 3-192008-4  | 1.197 [30.4]     | .008 [.20]         | 900                         | Silver | 45°         | LA1BS     |
| 4-192008-2  | 1.450 [36.8]     | .006 [.15]         | 1100                        | Silver | 45°         | LA1BS     |

### Male Bridge Formed Type LAIIS through LAVIS

**Material**—Beryllium Copper

**Finish**—See Table



| Part Number | Mating Hole Dia. | Length      | Material Thickness | Suggested Current Limit (A) | Finish   | Band Type |
|-------------|------------------|-------------|--------------------|-----------------------------|----------|-----------|
| 1-192039-7  | .157 [4.0]       | .470 [11.9] | .008 [.20]         | 75                          | Gold     | LAIIS     |
| 2-192039-1  | .250 [6.35]      | .470 [11.9] | .008 [.20]         | 130                         | Silver   | LAIIS     |
| 2-192039-3  | .248 [6.3]       | .470 [11.9] | .008 [.20]         | 130                         | Silver   | LAIIS     |
| 2-192039-7  | .311 [7.9]       | .470 [11.9] | .008 [.20]         | 175                         | Unplated | LAIIS     |
| 2-192039-9  | .311 [7.9]       | .470 [11.9] | .008 [.20]         | 175                         | Silver   | LAIIS     |
| 3-192039-0  | .311 [7.9]       | .470 [11.9] | .008 [.20]         | 175                         | Gold     | LAIIS     |
| 5-192039-3  | .236 [6.0]       | .470 [11.9] | .008 [.20]         | 120                         | Nickel   | LAIIS     |
| 5-192039-4  | .157 [4.0]       | .470 [11.9] | .008 [.20]         | 75                          | Nickel   | LAIIS     |
| 1-192042-5  | .080 [2.0]       | .320 [8.13] | .005 [.12]         | 30                          | Nickel   | LAIVS     |
| 2-192042-5  | .157 [4.0]       | .320 [8.13] | .006 [.15]         | 65                          | Unplated | LAIVS     |
| 2-192042-8  | .157 [3.99]      | .320 [8.13] | .006 [.15]         | 60                          | Gold     | LAIVS     |
| 4-192042-8  | .500 [1.27]      | .320 [8.13] | .005 [.12]         | 235                         | Unplated | LAIVS     |
| 6-192042-6  | .368 [9.38]      | .320 [8.13] | .004 [.10]         | 170                         | Unplated | LAIVS     |
| 6-192042-7  | .375 [9.53]      | .320 [8.13] | .006 [.15]         | 175                         | Tin      | LAIVS     |
| 6-192042-8  | .375 [9.53]      | .320 [8.13] | .006 [.15]         | 175                         | Gold     | LAIVS     |
| 2-192045-3  | .250 [6.35]      | .200 [5.10] | .006 [.15]         | 95                          | Gold     | LAIVS     |
| 192048-6    | .051 [1.3]       | .100 [2.54] | .004 [.10]         | 17                          | Gold     | LAVIS     |
| 1-192048-1  | .127 [3.23]      | .100 [2.54] | .004 [.10]         | 22                          | Gold     | LAVIS     |
| 2-192048-4  | .156 [3.96]      | .100 [2.54] | .004 [.10]         | 65                          | Gold     | LAVIS     |

**Note:** All part numbers are RoHS compliant.

**Notes:** 1. Suggested current limits are application dependent.  
2. Additional sizes are available upon request.

## AMP Power Series Connectors

### Product Facts

- Single-pole and 2-pole (battery) quick connect/disconnect connectors
- Eight Series, based on approximate current-carrying capability:
  - Series 15/30/45 (Single-Pole)
  - Series 50 (2-Pole Battery)
  - Series 50 Finger Probe Resistant (FPR)
  - Series 75 (Single-Pole)
  - Series 120 (Single- and 2-Pole)
  - Series 175 (2-Pole Battery)
  - Series 180 (Single-Pole)
  - Series 350 (2-Pole Battery)
- Voltage rating: 600 V AC/DC
- Color-coded housings, UL 94V-0
- Hermaphroditic (genderless) housings reduce inventory
- Modular, single-pole housings are stackable in four directions
- Polarity (+ and -) molded into 2-pole housings promotes proper wiring
- Mechanical keys help prevent two different color-coded housings from mating
- Stainless steel retaining springs secure contacts in housings
- Stamped and formed, open barrel contacts (6-20 AWG) on reels for automatic and semiautomatic machine termination
- Loose piece, cold-headed contacts (6 AWG – 300 MCM) for manual and hydraulic hand tools; reducing bushings accommodate smaller wire sizes
- Compatible with industry standard crimp tooling from Pico Corporation (<http://www.picotools.com>)
- Connectors intermateable with similar connectors from other manufacturers



- **Series 15/30/45, single-pole connectors designed to meet Amateur Radio Emergency Service (ARES)/Radio Amateur Civil Emergency Service (RACES) Standard Power Connector requirements**
- **Accessories available for mounting, vibration protection, and strain relief**
- **Component Recognized by Underwriters Laboratories Inc. to US and Canadian Standards, File No. E28476**



AMP power series connectors provide a durable, quick connect/disconnect means to transmit "power" levels of current and voltage (15-275 A, 600 V AC/DC).

This product family is primarily comprised of single-pole and 2-pole (battery) connector housings, crimp snap-in contacts, and accessories. Housings are offered in various colors. Two-pole housings have different polarization configurations; with the exception of black housings, each color identifies a different keying configuration. In general, only like color housings will mate. Contacts are either cold-headed or stamped and formed, depending upon the connector series.

AMP power series connectors are divided into eight series, based on approximate current-carrying capability.

### Applications

AC/DC power supplies and charging systems, rechargeable batteries, material handling equipment (e.g. forklift trucks), electric vehicles (e.g., golf carts, sweepers, wheelchairs), office furniture/panels, amateur emergency radios, and industrial equipment.

## AMP Power Series Connectors (Continued)



### AMP Power Series 15/30/45

Single-pole connector housings are stackable side-to-side and top-to-bottom. For example, Series 30 red and black housings joined side-to-side, are commonly used as standard power connectors for handheld, mobile, or base amateur radio equipment.

Modular housings can also be grouped into plug frames with or without latches, which mate with receptacle housings. Typically, these are used as quick disconnects for electrical power distribution in office furniture and panels.



### AMP Power Series 50

Two-pole (battery) housings are available in bulk quantities or in kit form (i.e., 1 housing and 2 contacts). These high durability connectors are designed for repeated mating and unmating.



### AMP Power Series 50 Finger Probe Resistant (FPR)


This new, 2-pole, FPR version helps prevent finger access, which allows it to be more safely used at elevated voltages and in user access areas.



### AMP Power Series 75

Single-pole, stackable housings, in locking and non-locking versions, are available in a variety of colors. Housings accept stamped and formed or cold-headed contacts. Bulk quantities and connector kits (1 housing and

1 contact) can be ordered. Accessories include: mounting wings for through-panel or surface mounting and mounting clamp sets for ganging housings.



### AMP Power Series 120

This Series includes both single- and 2-pole (battery) versions. Single-pole housings with molded-in dovetails allow stacking. Housing retaining pins provide more vibration protection. Two-pole housing have slots designed to accept mounting clamp sets for easier panel mounting.



### AMP Power Series 175

Two-pole (battery) housings accept cold-headed contacts (4-1/0 AWG). Basically, these connectors offer the same features as the two-pole Series 50 connectors.



### AMP Power Series 180

These stackable, single-pole connectors accept cold-headed contacts (4-1/0 AWG). Most features are similar to the smaller, single-pole, Series 120 connectors.



### AMP Power Series 350

Rugged, 2-pole housings accept only loose piece, cold-headed contacts (1/0-300 MCM). Rated at 275 A, these connectors have been tested up to 275 A, with 4/0 AWG wire.

## Selection Guide

| Series | Housing Type | Stackable Housing | Current Max. (A) | Voltage, Max. (V, AC or DC) | Cold-headed Contact (AWG)   | Stamped & Formed Contact (AWG) | Housing Colors                                      | Approvals          |
|--------|--------------|-------------------|------------------|-----------------------------|-----------------------------|--------------------------------|-----------------------------------------------------|--------------------|
| 15     | Single-Pole  | Yes               | 15               | 600                         | —                           | 16-20                          | Blue, Black, White, Red Green, Yellow, Orange, Gray | UL File No. E28476 |
| 30     | Single-Pole  | Yes               | 30               | 600                         | —                           | 12-16                          | Blue, Black, White, Red Green, Yellow, Orange, Gray | UL File No. E28476 |
| 45     | Single-Pole  | Yes               | 40*              | 600                         | —                           | 10-14                          | Blue, Black, White, Red Green, Yellow, Orange, Gray | UL File No. E28476 |
| 50     | 2-Pole       | No                | 50               | 600                         | 6, 8, 10-12                 | 6-10,10-12                     | Red, Gray, Blue, Black, Yellow                      | UL File No. E28476 |
| 75     | Single-Pole  | Yes               | 75               | 600                         | 6, 8,10-12                  | 6-10,10-12                     | Blue, Black, White, Green, Red (Single-Pole)        | UL File No. E28476 |
| 120    | Single-Pole  | Yes               | 120              | 600                         | 2, 4, 6                     | —                              | Blue, Black, White, Green, Red (Single-Pole)        | UL File No. E28476 |
| 120    | 2-Pole       | No                | 120              | 600                         | 2, 4, 6                     | —                              | Blue, Gray (2-Pole)                                 | UL File No. E28476 |
| 175    | 2-Pole       | No                | 175              | 600                         | 1/0, 1, 2, 4                | —                              | Blue, Gray, Orange, Yellow, Red                     | UL File No. E28476 |
| 180    | Single-Pole  | Yes               | 180              | 600                         | 1/0, 1, 2, 4                | —                              | Blue, Black, White, Green, Red                      | UL File No. E28476 |
| 350    | 2-Pole       | No                | 275**            | 600                         | 1/0, 2/0, 3/0, 4/0, 300 MCM | —                              | Blue, Green, Red, Yellow, Orange, Gray              | UL File No. E28476 |

\*Performance equivalent to competition \*\*Tested to 275 Amps with 4/0 AWG wire

## AMP Power Series 15/30/45 Connectors (Single-Pole)

### Product Facts

- Color-coded UL 94V-0 housings: blue, black, white, green, red, yellow, orange and gray
- Genderless housings reduce inventory
- 3 contact offerings available: Series 15, 30 and 45
- Built-in interlocking features (dovetails) allow stacking
- Series 15/30/45, single-pole connectors designed to meet Amateur Radio Emergency Service (ARES)/Radio Amateur Civil Emergency Service (RACES) Standard Power Connector requirements
- Plug frames (with or without latches) and receptacle housings accept stacked single-pole housings (2 to 8 poles)
- File No. E28476 US

### Material and Finish

**Housing**—Polycarbonate, UL 94V-0

**Retaining Spring**—Stainless Steel

**Contacts**—Copper with silver or tin plating

**Mounting Wings & Spacers**—Polycarbonate, UL 94V-0

**Retaining Pins**—Stainless steel

### Electrical Characteristics

**Current Carrying Capability**—

40 A w/10 AWG wire (Series 45)

30 A w/12 AWG wire (Series 30)

20 A w/16 AWG wire (Series 15)

**Operating Voltage**—600 V, AC or DC

**Dielectric Withstanding Voltage**—2200 VDC

**Average Initial Contact**

**Resistance**—525 micro-ohms

### Mechanical Characteristics

**Contact Retention**—25 lbs. [111.2 N]

**Average Mating/Unmating Force**—4.7 [20.9 N]


**Max. Wire Insulation Diameter**—175 [18.16]

**Wire Size Range**—10-20 AWG [5-0.5 mm<sup>2</sup>]


### Related Product Data

**Accessories**—page 151


### Single-Pole Housing



### Stamped and Formed Contact (Strip)



### Closed Barrel Contact (Loose Piece)



### AMP Power Series 15

| Housing <sup>1</sup> |             | Contact Part Number             |                         |
|----------------------|-------------|---------------------------------|-------------------------|
| Color                | Part Number | Strip Form (16, 18, 20 AWG)     | Loose Piece (16-20 AWG) |
| Blue                 | 1445957-1   |                                 |                         |
| Black                | 1445957-2   |                                 |                         |
| White                | 1445957-3   |                                 |                         |
| Green                | 1445957-4   | 1604113-1 (silver) <sup>2</sup> | 1744042-1               |
| Red                  | 1445957-5   | 1604113-2 (tin) <sup>2</sup>    |                         |
| Yellow               | 1445957-6   |                                 |                         |
| Orange               | 1445957-7   |                                 |                         |
| Gray                 | 1445957-8   |                                 |                         |

### AMP Power Series 30

| Housing <sup>1</sup> |             | Contact Part Number             |                                   |
|----------------------|-------------|---------------------------------|-----------------------------------|
| Color                | Part Number | Strip Form (12, 14, 16 AWG)     | Loose Piece (12-16 AWG)           |
| Blue                 | 1445957-1   |                                 |                                   |
| Black                | 1445957-2   |                                 |                                   |
| White                | 1445957-3   |                                 |                                   |
| Green                | 1445957-4   | 1604112-1 (silver) <sup>3</sup> | 1744041-1 Dimensions shown above. |
| Red                  | 1445957-5   | 1604112-2 (tin) <sup>3</sup>    |                                   |
| Yellow               | 1445957-6   |                                 |                                   |
| Orange               | 1445957-7   |                                 |                                   |
| Gray                 | 1445957-8   |                                 |                                   |

### AMP Power Series 45

| Housing <sup>1</sup> |             | Contact Part Number             |  |
|----------------------|-------------|---------------------------------|--|
| Color                | Part Number | Strip Form (10, 12, 14 AWG)     |  |
| Blue                 | 1445957-1   |                                 |  |
| Black                | 1445957-2   |                                 |  |
| White                | 1445957-3   |                                 |  |
| Green                | 1445957-4   | 1445962-1 (silver) <sup>4</sup> |  |
| Red                  | 1445957-5   | 1445962-2 (tin) <sup>4</sup>    |  |
| Yellow               | 1445957-6   |                                 |  |
| Orange               | 1445957-7   |                                 |  |
| Gray                 | 1445957-8   |                                 |  |

<sup>1</sup> Housings are bulk packaged.

<sup>2</sup> Use Applicator Part No. 1385450-3

<sup>3</sup> Use Applicator Part No. 1385468-3

<sup>4</sup> Use Applicator Part No. 1385469-3

**Note:** TE does NOT recommend intermating connectors with different contact platings.

**Note:** All part numbers are RoHS compliant.

## AMP Power Series 50 Connectors (2-Pole Battery)

### Product Facts

- Color-coded UL 94V-0 housings: gray, red, blue, yellow and black; other colors available upon request  
Note: Black color housing has the same mechanical key as the gray housing
- Mechanical keys help prevent two different voltage color-coded housings from mating
- Polarity (+ and -) molded into housings
- Genderless housings reduce inventory
- Cold-headed contact wire range: 6, 8, 10-12 AWG (Taped version of the cold-headed contacts available.)
- File No. E28476 c US

### Material and Finish

**Housing**—Polycarbonate, UL 94V-0  
**Retaining Spring**—Stainless Steel  
**Contacts**—Copper with silver plating  
**Reducing Bushings**—Copper with silver plating

### Electrical Characteristics

**Current Carrying Capability**—50 Amps per circuit w/6 AWG wire  
**Max. Operating Voltage**—600 V, AC or DC  
**Dielectric Withstanding Voltage**—2200 VDC  
**Average Initial Contact Resistance**—200 micro-ohms


### Mechanical Characteristics

**Contact Retention**—50 lbs. [222.4 N]  
**Average Mating/Unmating Force**—15 lbs. [66.7 N]  
**Max. Wire Insulation Diameter**—.44 [11.18]  
**Wire Size Range**—6-12 AWG (also 6-16 AWG w/Reducing Bushings)


### Related Product Data

**Accessories**—page 151

### 2-Pole Housing




### Cold-headed Contact



\*Inside Diameter  
6 AWG .222 [5.64]  
8 AWG .187 [4.75]  
10-12 AWG .150 [3.81]

### Stamped and Formed Contact (on Reel)



### AMP Power Series 50 (2-Pole)

| Housing <sup>2,3</sup>                            |             | Contact <sup>2</sup> |                        | Connector Kit            |
|---------------------------------------------------|-------------|----------------------|------------------------|--------------------------|
| Color                                             | Part Number | Wire Size            | Part Number            | Part Number <sup>1</sup> |
| Red                                               | 647845-3    | 6 AWG                | 647877-1               | 647892-3                 |
|                                                   |             | 10-12 AWG            | 647879-1               | 647893-3                 |
| Gray                                              | 647845-4    | 6 AWG                | 647877-1               | 647892-4                 |
|                                                   |             | 10-12 AWG            | 647879-1               | 647893-4                 |
| Blue                                              | 647845-5    | 6 AWG                | 647877-1               | 647892-5                 |
|                                                   |             | 10-12 AWG            | 647879-1               | 647893-5                 |
| Black <sup>4</sup>                                | 647845-7    | 6 AWG                | 647877-1               | 647892-7                 |
|                                                   |             | 10-12 AWG            | 647879-1               | 647893-7                 |
| Yellow                                            | 647845-8    | 6 AWG                | 647877-1               | 647892-8                 |
|                                                   |             | 10-12 AWG            | 647879-1               | 647893-8                 |
| Cold-headed Contact                               |             | 8 AWG                | 647878-1               | —                        |
| <sup>5</sup> Stamped and Formed contacts, on Reel |             | 6-10 AWG             | 1604433-1 <sup>7</sup> |                          |
| <sup>6</sup> Stamped and Formed contacts, on Reel |             | 10-12 AWG            | 1604433-2 <sup>7</sup> |                          |

<sup>1</sup> 1 Housing and 2 contacts.

<sup>2</sup> Housings and contacts are bulk packaged.

<sup>3</sup> Mechanical keys molded in housings generally will engage only with housings of same color.

<sup>4</sup> Black color housing has the same mechanical key as the gray housing.

<sup>5</sup> Use Heavy Duty Mini-Applicator (HDM) for 6 to 8 AWG - Part Number 1385663-2 (Use with AMP-O-LECTRIC Model K Terminator)

<sup>6</sup> Use Heavy Duty Mini-Applicator (HDM) for 10 to 12 AWG - Part Number 1385664-2 (Use with AMP-O-LECTRIC Model K Terminator)

<sup>7</sup> Use Power Lock Machine Part Number 68296-1

### Voltage Key Color Chart

| Housing Color | Voltage |
|---------------|---------|
| Yellow        | 12V     |
| Red           | 24V     |
| Gray          | 36V     |
| Blue          | 48V     |
| Black         | 80V     |

Color code given for various voltages is only a suggestion, other codes and keys available upon request.


**Note:** All part numbers are RoHS compliant.

## AMP Power Series 50 FPR (Finger Probe Resistant) Connectors


### Product Facts

- Complies with UL 60950 finger probe requirements
- Utilizes AMP Power Series 50 contacts
- Brown and white housing colors available (other colors possible)
- Two keying configurations available (up to 6 keying configurations possible)
- File No. E28476 


### 2-Pole Housing



### Cold-headed Contact



### Stamped and Formed Contact (on Reel)



### Material and Finish

**Housing**—Polycarbonate, UL 94V-0

**Retaining Spring**—Stainless Steel

**Contacts**—Copper

**Reducing Bushings**—Copper with silver plating

### Electrical Characteristics

**Current Capability**—50 A max.

**Voltage Rating**—600 V, AC or DC

**Dielectric Withstanding Voltage**—2200 VDC

### Mechanical Characteristics

Meets UL finger probe as outlined in UL 60950

**Contact Retention**—50 lbs. [222.4 N]

**Wire Size**—6-12 AWG [15-3 mm<sup>2</sup>]

**Max. Wire Insulation Diameter**—.44 [11.18]

### Related Product Data

**Accessories**—page 151

### Applications

- Uninterruptible Power Supplies
- Power Supplies
- Battery Banks

### AMP Power Series 50 FPR (2-Pole)

| Housing <sup>1,2</sup> |             | Wire Size | Contact Part Number <sup>1</sup> |          |                                           |                        |
|------------------------|-------------|-----------|----------------------------------|----------|-------------------------------------------|------------------------|
| Color                  | Part Number |           | Cold-headed <sup>5</sup>         |          | Stamped and Formed/Strip <sup>3,4,6</sup> |                        |
|                        |             |           | Loose Piece                      | On Tape  | On Reel                                   |                        |
| Brown                  | 1604342-1   | 6 AWG     | 647877-1                         | 647754-1 | 6-10 AWG                                  | 1604433-1 <sup>6</sup> |
| White                  | 1604342-2   | 8 AWG     | 647878-1                         | 647755-1 |                                           |                        |
|                        |             | 10-12 AWG | 647879-1                         | 647756-1 | 10-12 AWG                                 | 1604433-2 <sup>6</sup> |

<sup>1</sup> Housings and contacts are bulk packaged.

<sup>2</sup> Mechanical keys molded in housings will engage only with housings of same color.

<sup>3</sup> Use Heavy Duty Mini-Applicator (HDM) for 6 to 8 AWG - Part Number 1385663-2 (Use with AMP-O-LECTRIC Model K Terminator)

<sup>4</sup> Use Heavy Duty Mini-Applicator (HDM) for 10 to 12 AWG - Part Number 1385664-2 (Use with AMP-O-LECTRIC Model K Terminator)

<sup>5</sup> Hand Tool for Cold-headed Contact - Part Number 1526955-1

Taped version can be terminated using the AMP-TAPETRONIC Machine

<sup>6</sup> Use Power Lock Machine Part Number 68296-1

**Note:** All part numbers are RoHS compliant.

## AMP Power Series 75 Connectors (Single-Pole)

### Product Facts

- Color-coded UL 94V-0 housings: blue, black, white, green and red
- Genderless housings reduce inventory
- Cold-headed contact wire range: 6, 8, 10-12 AWG
- Stamped and formed contacts available:  
6-8 AWG Part Number 1604433-1 (strip);  
10-12 AWG Part Number 1604433-2 (strip)
- File No. E28476 

### Material and Finish

**Housing**—Polycarbonate, UL 94V-0  
**Retaining Spring**—Stainless Steel  
**Contacts**—Copper with silver plating  
**Reducing Bushings**—Copper with silver plating  
**Mounting Wings**—Polycarbonate, UL 94V-0  
**Retaining Pins**—Stainless steel

### Electrical Characteristics

**Current Carrying Capability (with 6 AWG)**—Configuration:

Single-Pole 75 A

1x2 Stacked 62 A

2x2 Stacked 60 A

1x3 Stacked 58 A

2x3 Stacked 52 A

**Operating Voltage**—600 V, AC or DC

**Dielectric Withstanding Voltage**—2200 VDC

**Average Initial Contact**

**Resistance**—200 micro-ohms

### Mechanical Characteristics

**Contact Retention**—50 lbs. [222.4 N]

**Average Mating/Unmating Force**—15 lbs. [66.7 N]

**Max. Wire Insulation Diameter**—.44 [11.18]


**Wire Size Range**—6-12 AWG [15-3 mm<sup>2</sup>]

### Related Product Data


**Accessories**—page 151

**Application Tooling**—page 153


#### Housing without Locking Feature




#### Cold-headed Contact



#### Housing with Locking Feature



#### Stamped and Formed Contact (on Reel)



### AMP Power Series 75 (Single-Pole)

| Housing <sup>2</sup> |             | Cold-headed Contact <sup>2</sup> |             | Connector Kit<br>Part Number <sup>1</sup> |
|----------------------|-------------|----------------------------------|-------------|-------------------------------------------|
| Color                | Part Number | Wire Size                        | Part Number |                                           |
| Non-Locking Version  |             |                                  |             |                                           |
| Blue                 | 1445715-1   | 6 AWG                            | 647877-1    | 1445716-1                                 |
| Black                | 1445715-2   | 6 AWG                            | 647877-1    | 1445716-2                                 |
| White                | 1445715-3   | 6 AWG                            | 647877-1    | 1445716-3                                 |
| Green                | 1445715-4   | 6 AWG                            | 647877-1    | 1445716-4                                 |
| Red                  | 1445715-5   | 6 AWG                            | 647877-1    | 1445716-5                                 |
| Locking Version      |             |                                  |             |                                           |
| Blue                 | 1445715-6   | 6 AWG                            | 647877-1    | 1445716-6                                 |
| Black                | 1445715-7   | 6 AWG                            | 647877-1    | 1445716-7                                 |
| White                | 1445715-8   | 6 AWG                            | 647877-1    | 1445716-8                                 |
| Green                | 1445715-9   | 6 AWG                            | 647877-1    | 1445716-9                                 |
| Red                  | 1-1445715-0 | 6 AWG                            | 647877-1    | 1-1445716-0                               |

\*Samples available on loose housing and contacts only.

### Contacts

| Description                            | Wire Size | Part Number | Die Set Part Number <sup>3</sup> | Applicator Part No. for AMP-O-ELECTRIC Model K Terminator |
|----------------------------------------|-----------|-------------|----------------------------------|-----------------------------------------------------------|
| Cold-headed (Loose Piece) <sup>4</sup> | 6 AWG     | 647877-1    | —                                | —                                                         |
|                                        | 8 AWG     | 647878-1    | —                                | —                                                         |
|                                        | 10-12 AWG | 647879-1    | —                                | —                                                         |
| Cold-headed (Tape) <sup>3, 4</sup>     | 6 AWG     | 647754-1    | 68344-1                          | —                                                         |
|                                        | 8 AWG     | 647755-1    | 68344-1                          | —                                                         |
|                                        | 10-12 AWG | 647756-1    | 68313-1                          | —                                                         |
| Stamped and Formed (Strip)             | 6-8 AWG   | 1604433-1   | —                                | 1385664-2                                                 |
|                                        | 10-12 AWG | 1604433-2   | —                                | 1385663-2                                                 |

<sup>1</sup> 1 housing and 1 contact

<sup>2</sup> Housings and contacts are bulk packaged.

<sup>3</sup> Taped version can be terminated using the AMP-TAPETRONIC machine Part Number 68250-1.

<sup>4</sup> Use hand tool Part Number 1526955-1 for Cold-headed contacts

**Note:** All part numbers are RoHS compliant.

## AMP Power Series 120 Connectors (Single-Pole)



### Product Facts

- Color-coded modular housings: blue, black, white, green and red
- Genderless housings reduce inventory
- Cold-headed contact wire range: 2, 4, and 6 AWG
- Built-in interlocking features (dovetails) allow stacking and wire routing
- Self-wiping contacts increase product life and improve conductivity
- Integral stainless steel locking spring in housing for contact retention
- Rugged design
- File No. E28476 c 

### Material and Finish

**Housing**—Polycarbonate, UL 94V-0  
**Retaining Spring**—Stainless Steel  
**Contacts**—Copper with silver plating  
**Reducing Bushings**—Copper with silver plating  
**Mounting Clamp Sets**—Aluminum

### Electrical Characteristics

#### Current Carrying Capability—

Single-Pole—120 A  
 2x1 Stacked Array—115 A  
 2x2 Stacked Array—115 A

**Voltage Rating**—600 V  
 (both AC and DC)

**Dielectric Withstanding Voltage**—  
 2200 VDC

**Average Initial Contact Resistance**—136 micro-ohms

### Mechanical Characteristics

**Contact Retention**—100 lbs.  
 [444.8 N]


**Average Mating/Unmating Force**—8 lbs. [35.6 N]

**Temperature Rating**—-4°F to  
 221°F [-20°C to 105°C]



**Max. Wire Insulation Diameter**—  
 .6 [15.24]

**Wire Size Range**—2-6 AWG

### Single-Pole Housing



### Cold-headed Contact



\*Inside Diameter 6 AWG .222 [5.64];  
 4 AWG .295 [7.5];  
 2 AWG .344 [8.74]

### AMP Power Series 120 (Single-Pole)

| Housing |             | Contact   |             | Connector Kit Part Number <sup>1</sup> |
|---------|-------------|-----------|-------------|----------------------------------------|
| Color   | Part Number | Wire Size | Part Number |                                        |
| Blue    | 1604001-1   | 2 AWG     | 1445995-1   | 1604002-1                              |
| Black   | 1604001-2   | 2 AWG     | 1445995-1   | 1604002-2                              |
| White   | 1604001-3   | 2 AWG     | 1445995-1   | 1604002-3                              |
| Green   | 1604001-4   | 2 AWG     | 1445995-1   | 1604002-4                              |
| Red     | 1604001-5   | 2 AWG     | 1445995-1   | 1604002-5                              |
| —       | —           | 4 AWG     | 1445996-1   | —                                      |
| —       | —           | 6 AWG     | 1445997-1   | —                                      |

<sup>1</sup> 1 Housing and 1 contact.

### Related Product Data

**Accessories**—page 152

**Application Tooling**—page 153

**Technical Documents**—page 154

**Note:** All part numbers are RoHS compliant.

## AMP Power Series 120 Connectors (2-Pole Battery)



### Product Facts

- Color-coded UL 94V-0 housings: gray and blue
- Keying feature helps prevent two different voltage color-coded housings from mating
- Genderless housings reduce inventory
- Contact wire range: 2, 4, 6 AWG
- Molded-in panel-mount grooves
- Integral stainless steel locking spring in housing for contact retention
- Rugged design
- File No. E28476 

### Material and Finish

**Housing**—Polycarbonate, UL 94V-0  
**Retaining Spring**—Stainless Steel  
**Contacts**—Copper with silver plating  
**Reducing Bushings**—Copper with silver plating

### Electrical Characteristics

**Current Carrying Capability**—115 A with 2 AWG  
**Voltage Rating**—600 V (both AC and DC)  
**Dielectric Withstanding Voltage**—2200 VDC  
**Avg. Initial Contact Resistance**—136 micro-ohms


### Mechanical Characteristics

**Contact Retention**—100 lbs. [444.8 N]  
**Average Mating/Unmating Force**—18 lbs. [80.1 N]  
**Temperature Rating**—-4°F to 221°F [-20°C to 105°C]  
**Max. Wire Insulation Diameter**—.6 [15.24]  
**Wire Size Range**—2-6 AWG


### Related Product Data

**Accessories**—page 152  
**Application Tooling**—page 153  
**Technical Documents**—page 154

### 2-Pole Housing



### Cold-headed Contact



### AMP Power Series 120 (2-Pole)

| Housing <sup>2,3</sup> |             | Contact <sup>2</sup> |             | Connector Kit Part Number <sup>1</sup> |
|------------------------|-------------|----------------------|-------------|----------------------------------------|
| Color                  | Part Number | Wire Size            | Part Number |                                        |
| Gray                   | 1445994-1   | 2 AWG                | 1445995-1   | 1445998-1                              |
| Blue                   | 1445994-2   | 2 AWG                | 1445995-1   | 1445998-2                              |
| Gray                   | 1445994-1   | 4 AWG                | 1445996-1   | 1445999-1                              |
| Blue                   | 1445994-2   | 4 AWG                | 1445996-1   | 1445999-2                              |
| Gray                   | 1445994-1   | 6 AWG                | 1445997-1   | 1446000-1                              |
| Blue                   | 1445994-2   | 6 AWG                | 1445997-1   | 1446000-2                              |

<sup>1</sup> 1 Housing and 2 contacts.

<sup>2</sup> Housings and contacts are bulk packaged.

<sup>3</sup> Mechanical keys molded in connectors will engage only with connectors of same color.

### Voltage Key Color Chart

| Housing Color <sup>2,3</sup> | Voltage |
|------------------------------|---------|
| Gray                         | 36 V    |
| Blue                         | 48 V    |

Color code given for various voltages is only a suggestion, other codes and keys available upon request.


**Note:** All part numbers are RoHS compliant.

## AMP Power Series 175 Connectors (2-Pole Battery)


### Product Facts

- Color-coded UL 94V-0 housings: yellow, orange, red, gray, blue, and black
- Keying feature helps prevent two different voltage color-coded housings from mating
- Genderless housings reduce inventory
- Contact wire range: 1/0, 1, 2, 4 AWG
- Integral stainless steel locking spring in housing for contact retention
- Reducing bushings down to 10 gauge
- File No. E28476 c us

### 2-Pole Housing



### Cold-headed Contact



Inside Diameter .516 ± .005 [13.1 ± 0.13] for 1/0 AWG  
.512 ± .005 [13.0 ± 0.13] for 1 AWG,  
2 AWG, and 4 AWG

### Material and Finish

**Housing**—Polycarbonate, UL 94V-0

**Retaining Spring**—Stainless Steel

**Contacts**—Copper with silver plating

**Reducing Bushings**—Copper with silver plating

### Electrical Characteristics

**Current Carrying Capability**—  
175 Amp @ 80.42°F [26.9°C] T-Rise  
with 1/0 AWG wire

**Voltage Rating**—600 V (both AC and DC)

**Dielectric Withstanding Voltage**—  
2200 VDC

**Avg. Initial Contact Resistance**—  
100 micro-ohms

### Mechanical Characteristics

**Average Mating/Unmating**

**Force**—25 lbs. [111.21 N]

**Max. Wire Insulation Diameter**—  
.750 [19.05]

**Wire Size Range**—1/0, 1, 2, 4 AWG  
[53, 40, 35, 21 mm<sup>2</sup>]

**Contact Retention**—300 lbs.  
[1,334.47 N]

**Temperature Rating**—-4°F to  
221°F [-20°C to 105°C]

### Related Product Data

**Accessories**—page 152

**Application Tooling**—page 153

**Technical Documents**—page 154

### AMP Power Series 175 (2-Pole)

| Housing            |             | Connector Kit Part Numbers <sup>1,2</sup> |           |           |           |
|--------------------|-------------|-------------------------------------------|-----------|-----------|-----------|
| Color              | Part Number | 4 AWG                                     | 2 AWG     | 1 AWG     | 1/0 AWG   |
| Yellow             | 1604037-1   | 1604044-1                                 | 1604043-1 | 1604045-1 | 1604042-1 |
| Orange             | 1604037-2   | 1604044-2                                 | 1604043-2 | 1604045-2 | 1604042-2 |
| Red                | 1604037-3   | 1604044-3                                 | 1604043-3 | 1604045-3 | 1604042-3 |
| Gray               | 1604037-4   | 1604044-4                                 | 1604043-4 | 1604045-4 | 1604042-4 |
| Blue               | 1604037-5   | 1604044-5                                 | 1604043-5 | 1604045-5 | 1604042-5 |
| Black <sup>3</sup> | 1604037-6   | 1604044-6                                 | 1604043-6 | 1604045-6 | 1604042-6 |

<sup>1</sup> 1 Housing and 2 contacts.

<sup>2</sup> Housings and contacts are bulk packaged.

<sup>3</sup> Black housing mates with any other housing.

### Contacts (Cold-headed)

| Wire Size | Part Number |
|-----------|-------------|
| 4 AWG     | 1604040-1   |
| 2 AWG     | 1604039-1   |
| 1 AWG     | 1604041-1   |
| 1/0 AWG   | 1604038-1   |

### Voltage Key Color Chart

| Housing Color | Voltage |
|---------------|---------|
| Yellow        | 12 V    |
| Orange        | 18 V    |
| Red           | 24 V    |
| Gray          | 36 V    |
| Blue          | 48 V    |
| Black         | 80 V    |

Color code given for various voltages is only a suggestion, other codes and keys available upon request.


**Note:** All part numbers are RoHS compliant.

## AMP Power Series 180 Connectors (Single-Pole)


### Product Facts

- Color-coded modular housings: blue, black, white, red and green
- Genderless housings reduce inventory
- Contact wire range: 1/0, 1, 2, 4 AWG
- Integral stainless steel locking spring in housing for contact retention
- Built-in interlocking features (dovetails) allow stacking and wire routing
- Reducing bushings down to 10 gauge
- File No. E28476 c  us

### Single-Pole Housing



### Cold-headed Contact



### Material and Finish

**Housing**—Polycarbonate, UL 94V-0

**Retaining Spring**—Stainless Steel

**Contacts**—Copper with silver plating

**Mounting Clamp Sets**—Aluminum

**Reducing Bushings**—Copper with silver plating

### Electrical Characteristics

#### Current Carrying Capability—

(1/0 AWG Wire)

1 x 1 — 180 A, 84.9°F [29.4°C] T-Rise

2 x 1 — 165 A, 78.3°F [25.7°C] T-Rise

2 x 2 — 150 A, 76.6°F [24.8°C] T-Rise

**Voltage Rating**—600 V (both AC and DC)

**Dielectric Withstanding Voltage**—2200 VDC

**Avg. Initial Contact Resistance**—100 micro-ohms

### Mechanical Characteristics

#### Average Mating/Unmating

**Force**—20 lb. [89 N]

**Max. Wire Insulation Diameter**—.900 [22.86]

**Wire Size Range**—1/0, 1, 2, 4 AWG [53, 40, 35, 21 mm<sup>2</sup>]

**Contact Retention**—170 lb. [756 N]

**Temperature Rating**—-4°F to 221°F [-20°C to 105°C]

### Related Product Data

**Accessories**—page 152

**Application Tooling**—page 153

**Technical Documents**—page 154

### AMP Power Series 180 (Single-Pole)

| Housing |             | Connector Kit Part Numbers <sup>1,2</sup> |           |           |           |
|---------|-------------|-------------------------------------------|-----------|-----------|-----------|
| Color   | Part Number | 4 AWG                                     | 2 AWG     | 1 AWG     | 1/0 AWG   |
| Blue    | 1604062-1   | 1604395-1                                 | 1604396-1 | 1604397-1 | 1604398-1 |
| Black   | 1604062-2   | 1604395-2                                 | 1604396-2 | 1604397-2 | 1604398-2 |
| White   | 1604062-3   | 1604395-3                                 | 1604396-3 | 1604397-3 | 1604398-3 |
| Red     | 1604062-4   | 1604395-4                                 | 1604396-4 | 1604397-4 | 1604398-4 |
| Green   | 1604062-5   | 1604395-5                                 | 1604396-5 | 1604397-5 | 1604398-5 |

<sup>1</sup> 1 Housing and 1 contact.

<sup>2</sup> Housings and contacts are bulk packaged.

### Contacts (Cold-headed)

| Wire Size | Part Number |
|-----------|-------------|
| 4 AWG     | 1604040-1   |
| 2 AWG     | 1604039-1   |
| 1 AWG     | 1604041-1   |
| 1/0 AWG   | 1604038-1   |


**Note:** All part numbers are RoHS compliant.

## AMP Power Series 350 Connectors (2-Pole Battery)


### Product Facts

- Color-coded UL 94V-0 housings: yellow, orange, red, gray, blue, and green
- Keying feature helps prevent two different voltage color-coded housings from mating
- Genderless housings reduce inventory
- Contact wire range: 1/0, 2/0, 3/0, 4/0, 300 MCM
- Replaceable contacts
- Integral stainless steel locking spring in housing for contact retention
- File No. E28476

### 2-Pole Housing



### Cold-headed Contact



### Material and Finish

**Housing**—Polycarbonate, UL 94V-0

**Retaining Spring**—Stainless Steel

**Contacts**—Copper with silver plating

**Reducing Bushings**—Copper with silver plating

### Electrical Characteristics

**Current Carrying Capability**—275 Amp @ 83.3°F [28.5°C] T-Rise with 4/0 AWG wire

**Voltage Rating**—600 V, AC or DC

**Dielectric Withstanding Voltage**—2200 VDC

**Average Initial Contact**

**Resistance**—50 micro-ohms

### Mechanical Characteristics

**Contact Retention**—500 lbs. [2224.1 N]

**Average Mating/Unmating Force**—30 lbs. [133.5 N]

**Max. Wire Insulation Diameter**—1.10 [27.94]

**Temperature Rating**—-4°F to 221°F [-20°C to 105°C]

**Wire Size Range**—1/0, 2/0, 3/0, 4/0, 300 MCM [53, 67, 85, 107, 152 mm²]

### Related Product Data

**Accessories**—page 152

**Application Tooling**—page 153

**Technical Documents**—page 154

**Reducing Bushing**—(1/0 to 2/0 AWG)  
**Part No.** 1604121-6

**Cable Clamp**—**Part No.** 647688-1

### AMP Power Series 350 (2-Pole)

| Housing |             | Connector Kit Part Numbers <sup>1,2</sup> |           |           |           |           |
|---------|-------------|-------------------------------------------|-----------|-----------|-----------|-----------|
| Color   | Part Number | 1/0 AWG                                   | 2/0 AWG   | 3/0 AWG   | 4/0 AWG   | 300 MCM   |
| Yellow  | 1604050-1   | 1604060-1                                 | 1604059-1 | 1604058-1 | 1604057-1 | 1604056-1 |
| Orange  | 1604050-2   | 1604060-2                                 | 1604059-2 | 1604058-2 | 1604057-2 | 1604056-2 |
| Red     | 1604050-3   | 1604060-3                                 | 1604059-3 | 1604058-3 | 1604057-3 | 1604056-3 |
| Gray    | 1604050-4   | 1604060-4                                 | 1604059-4 | 1604058-4 | 1604057-4 | 1604056-4 |
| Blue    | 1604050-5   | 1604060-5                                 | 1604059-5 | 1604058-5 | 1604057-5 | 1604056-5 |
| Green   | 1604050-6   | 1604060-6                                 | 1604059-6 | 1604058-6 | 1604057-6 | 1604056-6 |

<sup>1</sup> 1 Housing and 2 contacts.

<sup>2</sup> Housings and contacts are bulk packaged.

### Contacts (Cold-headed)

| Wire Size | Part Number |
|-----------|-------------|
| 1/0 AWG   | 1604055-1   |
| 2/0 AWG   | 1604054-1   |
| 3/0 AWG   | 1604053-1   |
| 4/0 AWG   | 1604052-1   |
| 300 MCM   | 1604051-1   |

### Voltage Key Color Chart


| Housing Color | Voltage |
|---------------|---------|
| Yellow        | 12V     |
| Orange        | 18V     |
| Red           | 24V     |
| Gray          | 36V     |
| Blue          | 48V     |
| Green         | 72V     |

Color code given for various voltages is only a suggestion, other codes and keys available upon request.

**Note:** All part numbers are RoHS compliant.

## AMP Power Series Accessories

### AMP Power Series 15/30/45 Mounting Wings




### AMP Power Series 15/30/45 Accessories

| Part Number                                       | Description          |
|---------------------------------------------------|----------------------|
| <b>Mounting Wings</b>                             |                      |
| 1445960-1                                         | Red, UL 94V-0        |
| <b>Spacers</b>                                    |                      |
| 1445959-1                                         | Red, UL 94V-0, Short |
| 1445959-2                                         | Red, UL 94V-0, Long  |
| <b>Retaining Pins for use with 15 A/30 A/45 A</b> |                      |
| 1445886-4                                         | .25 [6.35] length    |
| 1445886-5                                         | .44 [11.18] length   |

| Part Number                                                    | Description |
|----------------------------------------------------------------|-------------|
| <b>Hardware Kits</b><br>(Cable clamp, screws & retaining pins) |             |
| 647747-3                                                       | 4 pole      |
| 647747-2                                                       | 6 pole      |
| 647747-1                                                       | 8 pole      |

### AMP Power Series 15/30/45 Hardware Kits



### AMP Power Series 50 Accessories

| Part Number | Description                       |
|-------------|-----------------------------------|
| 1744077-1   | Dust Cover, Black                 |
| 1445762-1   | Reducing Bushing — 6 to 8 AWG     |
| 647840-1    | Reducing Bushing — 6 to 10-12 AWG |
| 1445763-1   | Reducing Bushing — 6 to 14-16 AWG |

Please contact Product Engineering or Product Management for availability.  
(permits use of smaller wires with 6 AWG contact Part Number 647877-1)

### AMP Power Series 75 Accessories


| Part Number                                         | Description                         |
|-----------------------------------------------------|-------------------------------------|
| <b>Mounting Wings</b>                               |                                     |
| 1445729-1                                           | Blue, oval mounting hole            |
| 1445729-2                                           | Blue, round mounting hole           |
| <b>Retaining Pins for use with 75 A/120 A/180 A</b> |                                     |
| 1445886-1                                           | 75 A/120 A/180 A hsgs, 1 high block |
| 1445886-2                                           | 75 A/120 A/180 A hsgs, 2 high block |
| <b>Reducing Bushings for Series 50 A and 75 A</b>   |                                     |
| 1445762-1                                           | 6 to 8 AWG                          |
| 647840-1                                            | 6 to 10-12 AWG                      |
| 1445763-1                                           | 6 to 14-16 AWG                      |

Mounting clamp set part numbers available.

**Note:** All part numbers are RoHS compliant.

## AMP Power Series Accessories (Continued)


### AMP Power Series 120 Panel Mounting Clamp



### AMP Power Series 120 Accessories

| Part Number                                      | Type          | Description                |
|--------------------------------------------------|---------------|----------------------------|
| <b>Retaining Pins for use with 75A/120A/180A</b> |               |                            |
| 1445886-1                                        | Single-Pole   | 1 high block               |
| 1445886-2                                        | Single-Pole   | 2 high block               |
| <b>Reducing Bushings</b>                         |               |                            |
| 1604072-3                                        | Single/2-Pole | 2 to 4 AWG                 |
| 1604072-2                                        | Single/2-Pole | 2 to 6 AWG                 |
| 1604072-1                                        | Single/2-Pole | 2 to 8 AWG                 |
| <b>Mounting Clamp Sets</b>                       |               |                            |
| 647721-1                                         | Single-Pole   | 2- & 4- pole configuration |
| 647722-1                                         | Single-Pole   | 3-pole configuration       |
| <b>Panel Mounting Clamp</b>                      |               |                            |
| 1744090-1                                        | 2-Pole        | —                          |


### AMP Power Series 175 & 350 Handle Kit



### AMP Power Series 175, 180 & 350 Accessories

| Part Number              | Type       | Description    |
|--------------------------|------------|----------------|
| <b>Reducing Bushings</b> |            |                |
| 1604121-1                | 175/180    | 10 to 1/0 AWG  |
| 1604121-2                | 175/180    | 6 to 1/0 AWG   |
| 1604121-5                | 175/180    | 4 to 1/0 AWG   |
| 1604121-4                | 175/180    | 2 to 1/0 AWG   |
| 1604121-3                | 175/180    | 1 to 1/0 AWG   |
| 1604121-6                | 350        | 1/0 to 2/0 AWG |
| <b>Handle Kit</b>        |            |                |
| 647737-1                 | 175 2-Pole | Red            |
| 647737-2                 | 175 2-Pole | Gray           |
| 1-647737-1               | 350 2-Pole | Red            |
| 1-647737-2               | 350 2-Pole | Gray           |

### AMP Power Series 175 Dust Cover Assembly



### AMP Power Series 175 & 180 Accessories

| Part Number         | Type | Description                 |
|---------------------|------|-----------------------------|
| <b>Cable Clamps</b> |      |                             |
| 647720-1            | 180  | 2 pole version              |
| 647719-1            | 180  | 3 pole version              |
| <b>Dust Cover</b>   |      |                             |
| 647691-1            | 175  | Dust Cover Assembly (Shown) |
| 647692-1            | 175  | Dust Cover Housing          |

**Note:** All part numbers are RoHS compliant.

## AMP Power Series Tooling

### Power Applicator Part Number 68296-1 (Customer Manual 409-2661)



The semiautomatic power applicator is designed to produce a carefully controlled uniform pressure crimp while providing a high rate of production. The applicator features matching dies that fully bottom at the completion of the crimp to provide proper crimp height. The one die set is fully adjustable to provide the full range of crimp heights for all wire sizes.

### 500 MCM Heavy Duty Cable Cutter Part No. 605742-1 (408-4557)



- Designed to cut aluminum or copper cable up to 500 MCM.
- Light weight tubular steel handles with hand grips
- 21" overall length

### Cable Insulation Stripper/Slitter Part No. 606700-1 (408-9688)



- Used on single or multiple conductor cable up to 1.75" in diameter

### Contact Extraction Tool Part No. 68265-1 or standard insulated screwdriver



### Hand Tools for Cold-Headed Contacts and Heavy-Duty Lug Terminals (Single-Indent Crimp)



| For AMP Power Series<br>50 and 75 Contacts |               |          | TE<br>Crimp Tool Part No. 1526955-1<br>Includes Adapter |         | OR | American Electrical Terminal (AET)<br>Crimp Tool Part No. T-406<br>Includes Adapter |         | Also For Heavy-Duty<br>Lug Terminals |               |
|--------------------------------------------|---------------|----------|---------------------------------------------------------|---------|----|-------------------------------------------------------------------------------------|---------|--------------------------------------|---------------|
| Wire Size<br>(AWG)                         | Strip Length  | Part No. | Part Number                                             | Marking |    | Part Number                                                                         | Marking | Wire Size<br>(AWG)                   | Strip Length  |
| 6                                          | .475-.525     | 647877-1 | 1527508-1                                               | A       |    | 5992                                                                                | A       | 6                                    | 7/16 [11.11]  |
| 8                                          | [12.06-13.33] | 647878-1 |                                                         |         |    |                                                                                     |         | 4                                    | 1/2 [12.70]   |
| 10-12                                      |               | 647879-1 |                                                         |         |    |                                                                                     |         | 1/0                                  | 11/16 [17.46] |
|                                            |               |          | 1527507-1                                               | B       |    | 5991                                                                                | B       | 2/0                                  | 11/16 [17.46] |
|                                            |               |          | 1527505-1                                               | C       |    | 5989                                                                                | C       | 2                                    | 9/16 [14.29]  |
|                                            |               |          | No Adapter                                              | —       |    | No Adapter                                                                          | —       | 1                                    | 5/8 [15.87]   |
|                                            |               |          |                                                         |         |    |                                                                                     |         | 3/0                                  | 3/4 [19.05]   |
|                                            |               |          |                                                         |         |    |                                                                                     |         | 4/0                                  | 13/16 [20.64] |

### Pneumatic Tools for Cold-Headed Contacts (Dual-Indent Crimp) and Heavy-Duty Lug Terminals



| AMP Power Series Contacts |                 |           | PICO* Pneumatic Tools** |           |             |           |           |              |
|---------------------------|-----------------|-----------|-------------------------|-----------|-------------|-----------|-----------|--------------|
| Series                    | Wire Size (AWG) | Part No.  | 400 Series Power Unit   |           | Die         | Locator   |           | Closure Dim. |
|                           |                 |           | Preferred               | Alternate |             | Preferred | Alternate |              |
| 50/50 FPR/75              | 6               | 647877-1  |                         |           | 414DA-4583  |           |           | .152 [3.86]  |
|                           | 8               | 647878-1  | 400-BEC                 | 400-BHD   | 414DA-4583  | 4582-1    | 9616-1    | .152 [3.86]  |
|                           | 10-12           | 647879-1  |                         |           | 414DA-4582  |           |           | .134 [3.40]  |
| 120                       | 2               | 1445995-1 |                         |           |             |           |           |              |
|                           | 4               | 1445996-1 | 400-BEC                 | 400-BHD   | 414DA-4580  | 4580-1    | None      | .200 [5.08]  |
|                           | 6               | 1445997-1 |                         |           |             |           |           |              |
| 500 Series Power Unit     |                 |           |                         |           |             |           |           |              |
| 50/50 FPR/75              | 6               | 647877-1  |                         |           | 514DA-7033  |           |           | .152 [3.86]  |
|                           | 8               | 647878-1  | 500-DEC                 | 500-D     | 514DA-7033  | 7033-1    | 7034-1    | .152 [3.86]  |
|                           | 10-12           | 647879-1  |                         |           | 514DA-7034  |           |           | .134 [3.40]  |
| 120                       | 2               | 1445995-1 |                         |           |             |           |           |              |
|                           | 4               | 1445996-1 | 500-DEC                 | 500-D     | 514DA-7035  | 7035-1    | None      | .200 [5.08]  |
|                           | 6               | 1445997-1 |                         |           |             |           |           |              |
| 175/180                   | 1/0             | 1604038-1 |                         |           |             |           |           |              |
|                           | 2               | 1604039-1 | 500-DEC                 | 500-D     | 514DA-10023 | 10034-1   | None      | .225 [5.72]  |
|                           | 4               | 1604040-1 |                         |           |             |           |           |              |
| 350                       | 1               | 1604041-1 |                         |           |             |           |           |              |
|                           | 300 MCM         | 1604051-1 |                         |           | 514DA-10027 | 10023-2   |           | .475 [12.07] |
|                           | 4/0             | 1604052-1 |                         |           | 514DA-10026 | 10023-2   |           | .400 [10.16] |
|                           | 3/0             | 1604053-1 | 500-DEC                 | 500-D     | 514DA-10025 | 10023-2   | None      | .360 [9.14]  |
|                           | 2/0             | 1604054-1 |                         |           | 514DA-10024 | 10023-1   |           | .325 [8.26]  |
|                           | 1/0             | 1604055-1 |                         |           | 514DA-10023 | 10023-1   |           | .225 [5.72]  |

\* Pico Corporation, 444 Constitution Ave., Camarillo, CA 93012-8505; Tel: (805) 388-5510

\*\* Pneumatic Tool consists of a power unit, die, and locator; it can be used as a portable hand tool, bench-mounted hand tool, or foot-controlled unit.

**Note:** All part numbers are RoHS compliant.

## AMP Power Series Connectors (Continued)

### Technical Documents

Various technical documents are available for your use:

**Product Specifications** describe technical performance characteristics and verification tests. They are intended for the Design, Component and Quality Engineer.

|                 |                                 |
|-----------------|---------------------------------|
| <b>108-1349</b> | AMPINNERGY WTB Connectors       |
| <b>108-1373</b> | AMPINNERGY WTW Connectors       |
| <b>108-2104</b> | AMP Power Series 50 Connectors  |
| <b>108-2149</b> | AMP Power Series 15 Connectors  |
| <b>108-2150</b> | AMP Power Series 30 Connectors  |
| <b>108-2151</b> | AMP Power Series 45 Connectors  |
| <b>108-2152</b> | AMP Power Series 75 Connectors  |
| <b>108-2153</b> | AMP Power Series 120 Connectors |
| <b>108-2154</b> | AMP Power Series 175 Connectors |
| <b>108-2155</b> | AMP Power Series 180 Connectors |
| <b>108-2156</b> | AMP Power Series 350 Connectors |

**Application Specifications** describe requirements for using the product in its intended application and/or crimping information. They are intended for the Packaging and Design Engineer and the Machine Setup Person.

|                  |                                                                               |
|------------------|-------------------------------------------------------------------------------|
| <b>114-6044</b>  | AMPINNERGY WTB Connectors                                                     |
| <b>114-6051</b>  | AMPINNERGY WTW Connectors                                                     |
| <b>114-13071</b> | AMP Power Series 50 (Double-Pole) and 75 (Single Pole) Connector Assemblies   |
| <b>114-13107</b> | AMP Power Series 120 (Single- and Double-Pole) Connector Assemblies           |
| <b>114-13118</b> | AMP Power Series 175 (Double-Pole) and 180 (Single-Pole) Connector Assemblies |
| <b>114-13119</b> | AMP Power Series 350 (Double-Pole) Connector Assemblies                       |
| <b>114-13127</b> | AMP Power Series 15, 30 and 45 (Single-Pole) Connector Assemblies             |

**Instruction Sheets** provide instructions for assembling or applying the product. They are intended for the Manufacturing Assembler or Operator.

|                 |                                                                         |
|-----------------|-------------------------------------------------------------------------|
| <b>408-3198</b> | Inspection of AMPINNERGY System Power Contacts                          |
| <b>408-3236</b> | Installation of AMPINNERGY WTB Connectors                               |
| <b>408-3277</b> | AMPINNERGY Wire-To-Wire Stackable Connectors                            |
| <b>408-8636</b> | AMP Power Series 50 Connector Assemblies                                |
| <b>408-8868</b> | AMP Power Series 175 and 350 Connector Assemblies with Cable Clamp Kits |
| <b>408-4557</b> | Heavy Duty Cable Cutter Hand Tool 605743-1                              |
| <b>408-4559</b> | Heavy Duty Cable Cutter Hand Tool 605744-1                              |
| <b>408-4561</b> | Heavy Duty Cable Cutter Hand Tool 6057469-1                             |
| <b>408-8540</b> | Crimp Tool 1526955-1                                                    |
| <b>408-9688</b> | Cable Stripper/Slitter Tool 606700-1                                    |
| <b>408-9816</b> | Handling of Reeled Products                                             |

### Test Summary

|                 |                                                |
|-----------------|------------------------------------------------|
| <b>502-1136</b> | 50/75 Product Evaluation                       |
| <b>502-1160</b> | 15/30/45 Product Evaluation                    |
| <b>502-1166</b> | 120 Product Evaluation                         |
| <b>502-1167</b> | 120 Competitive Evaluation                     |
| <b>502-1172</b> | AMP Power Series 175/180 Product Evaluation    |
| <b>502-1173</b> | AMP Power Series 350 Product Evaluation        |
| <b>502-1189</b> | 15/30/45 Intermate                             |
| <b>502-1206</b> | 15/30/45 Stamped and Formed Contact Evaluation |

### Customer Manual

|                 |                                                     |
|-----------------|-----------------------------------------------------|
| <b>409-5128</b> | AMP-O-LECTRIC Model K Terminator Machine 1-471273-2 |
|-----------------|-----------------------------------------------------|

**Note:** All part numbers are RoHS compliant.

## Domino Series Connectors

### Hot-Plug High Current Modular Power Connectors

#### Key Features

- Modular construction
- Blind-mating
- High current CROWN BAND contacts
- Logic/Signal
- Locking system
- Uses ELCON drawer contacts

#### Typical Applications

- Power Supplies
- Telecommunications
- Automatic Test Equipment
- Computer Hardware
- Process Control
- Uninterruptible Power Systems
- All Domino products in this section are RoHS compliant



The ELCON Domino connector system is a modular high-current connector system consisting of interchangeable modules which can provide AC, DC, logic and signal, float mounting, and pin sequencing. All Domino modules incorporate CROWN BAND technologies, tried and tested under the most arduous conditions. The high current capabilities virtually eliminate the need for bussing or splitting current, with resulting space savings and economies.

The Domino connector system allows the user to configure a connector specific to an application, from off-the-shelf components. It can be purchased as separate modules and assembled by the user, but is more

generally ordered as a connector assembly using an assembly part number which TE assigns to a specific configuration. Consult TE for assistance in laying out a new connector. If required, Domino connector assembly is simple: once the locking rails are cut to size, the only tool required is a Phillips screwdriver for tightening the end-caps.

Most Domino contacts are the same as used in ELCON drawer connectors. Modules A through E and R are sold as housings with retention clips; the contacts are ordered separately. See page 80 for available contact options and plating information, page 67 for tooling. Modules K, L, and M are sold pre-loaded with contacts. Domino assemblies are shipped complete with contacts.

The Domino system is ideal for use with hot-pluggable power supplies of the type employed for load-sharing and/or redundant power for computer systems. Current interruption capability is standard in the L module and an available option in the A module.


The CROWN BAND contact is a small louvered cylindrical receptacle of beryllium copper. Manufactured on progressive dies to allow consistent, even insertion and withdrawal forces, its design helps ensure maximum surface contact area for minimum voltage drop and minimum heat generation. CROWN BAND contacts also provide excellent shock and vibration resistance.

## Domino Series Connectors (Continued)


### A Modules — 3 x #12 Power Contacts, Hot-Plug option available

**Note:** Supplied without contacts. Crimp insertable/removable, PCB insertable/non-removable

Specifications: Contact rating 35 Amps UL, 20 Amps CSA, 250V; Hot-plug 35 Amps UL, 30 Amps CSA, 120 V ac, 50 cycles; Fully loaded module nominal forces: insertion 9.2 lbs, extraction 5.5 lbs (Hot-plug insertion 11.5 lbs, extraction 6.4 lbs)



**Pin Housing**  
(without contacts)  
Part Number 1648461-1




**Socket Housing**  
(without contacts)  
Part Number 1648466-1


### B Modules — 2 x #8 Power Contacts

**Note:** Supplied without contacts. Crimp insertable/removable, PCB insertable/non-removable

Specifications: Contact rating 75 Amps UL, 40 Amps CSA, 250V; Fully loaded module nominal forces: insertion 6.7 lbs, extraction 3.9 lbs



**Pin Housing**  
(without contacts)  
Part Number 1648462-1




**Socket Housing**  
(without contacts)  
Part Number 1648467-1


### C Modules — 20 x #20 Signal Contacts

**Note:** Supplied without contacts. Crimp insertable/removable, PCB insertable/non-removable

Specifications: Contact rating 5 Amps UL, 4 Amps CSA, 125V; Fully loaded module nominal forces: insertion 2.4 lbs, extraction 2.6 lbs



**Pin Housing**  
(without contacts)  
Part Number 1648463-1




**Socket Housing**  
(without contacts)  
Part Number 1648468-1


### D Module — 5 x #16 Power Contacts

**Note:** Supplied without contacts. Crimp insertable/removable, PCB insertable/non-removable

Specifications: Contact rating 15 Amps UL, 10 Amps CSA, 125V; Fully loaded module nominal forces: insertion 18.6 lbs, extraction 13.0 lbs



**Pin Housing**  
(without contacts)  
Part Number 1648464-1



**Socket Housing**  
(without contacts)  
Part Number 1648469-1


**Note:** All part numbers are RoHS compliant.

## Domino Series Connectors (Continued)


### E Modules — 14 x #16 Power Contacts

**Note:** Supplied without contacts. Crimp insertable/removable, PCB insertable/non-removable

Specifications: Contact rating 15 Amps UL, 10 Amps CSA, 125V; Fully loaded module nominal forces: insertion 43.1 lbs, extraction 33.7 lbs



Pin Housing  
(without contacts)  
Part Number 1648465-1




Socket Housing  
(without contacts)  
Part Number 1648470-1


### G Modules - Non-electrical Guide Module

**Note:** May be turned through 180 in the horizontal plane

Specifications: Guide pin type 303 Stainless Steel, passivated



Guide Pin  
Part Number 1648505-1




Guide Socket  
Part Number 1648473-1


### J Modules — Jackscrew Locking Module

**Note:** Select socket side to match desired orientation of T-handle in locked position

Specifications: Corrosion resistant Steel



Pin Side  
4.20" T-Handle Part  
Number 1648482-1



Parallel Socket Side  
Part Number 6650679-1

Perpendicular Socket Side  
Part Number 6650680-1


**Note:** All part numbers are RoHS compliant.

## Domino Series Connectors (Continued)


### K Modules — Electrically Active Ground/Guide Module

**Note:** May be turned through 180 in the horizontal plane. Use Crimp Tool PN 1766453-1

Specifications: Contact rating 40 Amps UL, 15 Amps CSA, 250V; Fully loaded module nominal forces: insertion 3.0 lbs, extraction 1.3 lbs




Guide Pin  
# 10 AWG Crimp  
Part Number 6648508-1




Guide Socket  
# 10 AWG Crimp  
Part Number 6648476-1

### M Modules — Pre-installed Dual In-Line Crown Pin & Socket

Specifications: Contact rating 125 Amps UL/CSA, 250V; Fully loaded module nominal forces: insertion 14.9 lbs, extraction 9.8 lbs



Pin Module  
Ext. Threaded  
Part Number 6648499-1




Socket Module  
Ext. Threaded  
Part Number 6648454-1

Recommended torque value 40 lb.in (4.52 N.m)


### R Modules — 2 x 1/4" Power Contacts

**Note:** Supplied without contacts; available contacts: Crimp insertable/removable, Ext. Threaded insertable/non-removable, consult TE for contact part numbers and available Double Crown option.

Specifications: Contact rating 150 Amps UL, 110 Amps CSA, 250V; Fully loaded module nominal forces: insertion 9.4 lbs, extraction 6.0 lbs



Pin Module  
(without contacts)  
Part Number 6648515-1



Socket Module  
(without contacts)  
Part Number 6648457-1


### Spacer Module — Non-electrical

**Note:** any module may be ordered without contacts for use as spacers; consult sales engineer for options and part numbers.


**Note:** All part numbers are RoHS compliant.

## Domino Series Connectors (Continued)

### Domino Assembly Mounting Accessories



Screw Part Number 1766829-1, Steel




Locking Rail Part Number 1648990-1,  
Aluminum alloy, gold anodized finish, 36" length.  
Requires cutting to size.


Locking Rail (at 1' interval)  
Part Number 1650469-1

### End Caps — Zinc die cast, CRS hardware, trivalent chromate finish


End caps secure the modules when screwed into the locking rails providing rigid assembly and a means of mounting assembly to frames, bulkheads, etc. Float-mount styles correct for misalignment during mating. Any end cap may be used to mount either pin or socket sides.




Fix-Mount, Guide Pin  
Part Number 6648259-1  
A = 1.22 (30.98), B = .275 (6.98)



Fix-Mount, Guide Socket  
Part Number 6648263-1  
A = .175 (4.44)



Float-Mount, Guide Pin  
Part Number 6648251-1  
Standard  
A = 1.22 (30.98), B = .275 (6.98)  
Part Number 6648253-1  
L-Module  
A = 1.62 (41.14), B = .125 (3.17)



Float-Mount, Guide Socket  
Part Number 6648252-1  
Standard  
A = .175 (4.44)  
Part Number 6648254-1  
L-Module  
A = .325 (8.25)

**Note:** All part numbers are RoHS compliant.

## Domino Series Connectors (Continued)


### Domino Module Assembly Process



1. Align modules in desired order.



2. Measure length of assembly, and add .100" (2.54 mm) to determine overall rail length. Cut rails to length.



3. Slide locking rails into position on both sides of module assembly via the molded rail tracks.



4. Position end caps over locking rail ends and secure using Phillips head screws.

## Domino Connector Layout Form

### Instructions

1. Indicate the connector layout by filling in the Module letter for each module required in the boxes below, one per box. Use one form per mated pair.
2. Contacts are required for most modules, and are sold separately. Please see the High Current Drawer Section Contacts for specific part numbers.
3. The left to right order of the modules should match the **mating face views** of the connector.
4. Sign, date and send the completed form to your local TE Sales Engineer.

**Upon receipt of this form, TE will generate a Customer Drawing for you to check and approve prior to connector production.**

### Pin Side:

|  |  |  |  |  |  |  |  |  |  |
|--|--|--|--|--|--|--|--|--|--|
|  |  |  |  |  |  |  |  |  |  |
|--|--|--|--|--|--|--|--|--|--|

### Socket Side:

|  |  |  |  |  |  |  |  |  |  |
|--|--|--|--|--|--|--|--|--|--|
|  |  |  |  |  |  |  |  |  |  |
|--|--|--|--|--|--|--|--|--|--|

**A Modules**  
3 x #12  
Power Contacts  
Hot Plug

**B Modules**  
2 x #8  
Power Contacts

**C Modules**  
20 x #20  
Signal Contacts

**D Modules**  
5 x #16  
Power Contacts

**E Modules**  
14 x #16  
Power Contacts

**G Modules**  
Non-Electrical  
Guide Modules

**J Modules**  
Jackscrew  
Locking Module


**K Modules**  
Electrically Active Guide/  
Ground Module

**M Modules**  
Pre-Installed Dual  
In-Line Crown Pin & Socket


**R Modules**  
2 x #14  
Power Contacts

**Domino Mounting Accessories**

Locking Rail  
Aluminum Alloy, 36" length (must cut to size)  
Part Number 1648990-1  
Locking Rail, 1' Interval  
Part Number 1650469-1



**Fix-Mount End Cap**  
with Guide Pin



**Float-Mount End Cap**  
with Guide Pin

### Contacts

Please reference Power Connectors & Interconnection Systems Catalog 1773096 for contact part numbers.

| Part Number | Quantity |
|-------------|----------|
|             |          |
|             |          |
|             |          |

| Part Number | Quantity |
|-------------|----------|
|             |          |
|             |          |
|             |          |

**Note:** All part numbers are RoHS compliant.

## HTS Power Connectors

### Product Facts

- Heavy-duty, rectangular, multiple-position, pin and socket connectors
- Current rating: 10-500 A
- Voltage rating: 1-1.4 kV
- Number of contact positions: 1 through 216
- Connectors are designated by four components: base and hood, and male and female inserts
- Contact inserts provide for three types of wire termination: screw (no crimp tool required), crimp (higher pin count), and cage clamp (fastest)
- HE Series inserts (screw terminated) are the most popular
- Bases provide environmental (IP 55, 65 and 68) and electrical protection (NEMA 4 and 4X)
- Bases share an industry standard panel cutout and mounting hole pattern
- Hoods offer top, side, or angled cable entry. Hoods are tapped to accommodate metric or PG fittings
- Automated tooling matched to contact
- DIN/VDE, UL, CSA and SEV approved



HTS power connectors are heavy-duty, rectangular, multiple-position, pin and socket connectors. They are commonly referred to as "rectangular" or "European metal shell" connectors.

HTS connectors are designated by four components: base and hood, and male and female inserts. The designation is driven by electrical specifications; pin count and current rating define the inserts needed. From 1 to 216 contact positions are available. Current ratings range from 10-500 A.

The appropriate housing size (1-12) to accommodate selected inserts is then defined. Housing selection criteria include: base mounting style, latch type, hood cable entry location, and hood gland size. The most popular housing sizes are: Shell Size 1 (3 or 4 positions), Shell Size 3 (6 positions), Shell Size 6 (16 positions), Shell Size 8 (24 positions), and Shell Size 5 (25 positions).

HTS connectors have many applications: industrial machinery (automotive, plastics, semiconductors, material handling, packaging and printing), and railroad and mass transit (A/C and brake subsystems, power transformers, door systems, switches and signals, and drive motor enclosures).

For more information on the entire line of HTS heavy-duty connectors, see Catalog 889745-2.

## HTS Power Connectors (Continued)


### Contact Inserts

#### Series HVS

- High Variable System
- Zinc Frames Size 3 to 8 (acc. to Housing)
- For up to 6 Single Modules

#### Material

- PBT
- Flammability Rating: acc. UL 94 V-0



To offer a maximum of flexibility and reliability with a minimum of installation or maintenance effort TE developed the HVS product range (high variable system).

This system enables customers to build their own application specific connection and due to the combination variety of the different modules customers benefit in terms of reduced costs (cost efficiency) and less mounting space.


The HVS range comprises more than 25 different modules and the particular zinc frames which can then be mounted into all standard hoods and housings from TE. There is no tooling needed to put the modules in and out of the frame due to lever snap-in technology.

Up to 6 single modules can be used in a size 8 frame whereby the customer can individually define the combination of modules.

Signal, high current and high voltage, high density, Fire Wire, RJ45, USB, Coax, twisted pair, high speed and also pressure air are only some of the different connector modules. According to the insert contacts can be used individually.

In combination with the TE's hoods and housings IP ratings of IP 65 or even IP 68 can be realized. Customers also benefit from EMI- and corrosion-protection dependent on housing.

A large variety of customer specific applications complete the product range.



For more information on the entire line of HTS heavy-duty connectors, see Catalog 889745-2.

## RAPID LOCK Quick Connect/Disconnect Bus Bar Connectors

### Product Facts

- Replaces power lugs
- Locking feature “snaps” each contact to mating pin
- Up to 250 Amps per contact
- CROWN BAND connector technology provides low contact resistance

### Typical Applications

- Power Distribution Systems
- Recognized under the Component Program of Underwriters Laboratories, File No. E28476



The RAPID LOCK connector is a single-pole, quick connect/disconnect replacement for lug connections, used in bus bar and backplane power distribution applications. RAPID LOCK connectors allow a reliable and safe connection, as well as better serviceability, than bolt-fitted lugs. The cable mounted sockets have a right-angle configuration, and feature an insulator cap that provides the retention mechanism on the pin. The pin contacts can be attached to a bus bar by screw or swage, and to a backplane by press fit and backup screw.

### Secure Power Distribution

By replacing power lugs fitted using nuts and bolts, the RAPID LOCK connector offers an extremely secure interconnect mechanism that totally frees the power distribution system from the risk of loose connections, which can cause arcing.

### Safety Locking Feature

A locking feature is provided on the pins for protection against accidental unlatching of the cable. Although connection of the cable is easily performed by hand, disconnection requires a simple tool to provide the leverage needed to overcome the locking feature.

### Improved Ease of Service

Service in the field becomes very easy with RAPID LOCK connectors because there are no nuts and washers to lose in the equipment. The RAPID LOCK connector is available with red or black color insulators.

### CROWN BAND Technology

The RAPID LOCK connector enjoys all the benefits of the ELCON CROWN BAND technology, providing a stable connection with excellent mechanical and electrical performance with ratings up to 300 Amps depending on wire gauge and application.

**Note:** All RAPID LOCK Products in this section are RoHS compliant.

**Note:** All part numbers are RoHS compliant.

## RAPID LOCK Connectors Ordering Information

## RAPID LOCK Quick Connect/Disconnect Bus Bar Connectors (Continued)

| Size  | Crimp Size | Part Numbers |           |           |           |           |
|-------|------------|--------------|-----------|-----------|-----------|-----------|
|       |            | Socket       |           |           | Pin       |           |
|       |            | Black        | Red       | Blue      | Swage     | Screw     |
| #8    | AWG #8     | 6648228-1    | 6648228-2 | N/A       | 6648221-1 | —         |
|       | AWG #12    | 6648237-1    | 6648237-2 | N/A       | 6648221-1 | N/A       |
|       | AWG #6     | 1766484-1    | 1766484-2 | N/A       | 6648221-1 | —         |
| #4    | AWG #8     | 6648235-1    | 6648235-2 | N/A       | 6648222-1 | —         |
|       | AWG #4     | 6648236-1    | 6648236-2 | N/A       | 6648222-1 | 6648224-1 |
|       | AWG #6     | 6648239-1    | 6648239-2 | N/A       | 6648222-1 | —         |
| #2    | AWG #0     | 6648234-1    | 6648234-2 | N/A       | 6648223-1 | 6648226-1 |
|       | AWG #2     | 6648238-1    | 6648238-2 | N/A       | 6648223-1 | 6648226-1 |
| 12 mm | 95 Sq. mm  | N/A          | 1857547-1 | 1857547-2 | 1857523-3 | N/A       |

| Size  | Insulation Boot |           |           |           |
|-------|-----------------|-----------|-----------|-----------|
|       | Black           | Red       | Grey      | Blue      |
| #4/#8 | 1651003-1       | 1651003-2 | 1651003-3 | 1651003-4 |
| #2    | 1766600-1       | 1766600-2 | 1766600-3 | 1766600-4 |


## Product Specifications

| Materials                    |                                                                                                                                                          |
|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Insulator                    | Thermoplastic, UL 94V-0 flammability rated                                                                                                               |
| Socket Contact Body          | Copper alloy, plated Silver over nickel                                                                                                                  |
| CROWN BAND                   | Beryllium Copper, plated Gold (30 micro inches minimum) over nickel                                                                                      |
| Pin Contact                  | Copper alloy, plated Silver over nickel                                                                                                                  |
| Electrical                   |                                                                                                                                                          |
| Current Rating @ 30°C T-rise | Size 8 — 50 Amps on 8 AWG wire<br>Size 4 — 115 Amps on 4 AWG wire<br>Size 2 — 145 Amps on 2 AWG wire<br>Size 12 mm — 250 Amps on 95 mm <sup>2</sup> wire |
| Contact Resistance           | Size 8 — 0.5mΩ<br>Size 4 — 0.15 mΩ<br>Size 2 — 0.12 mΩ                                                                                                   |
| Voltage Drop                 | See graphs                                                                                                                                               |
| Mechanical                   |                                                                                                                                                          |
| Removal Tool                 | Part Number 1857376-1                                                                                                                                    |


**Note:** For more information about tooling, call Tooling Sales at 888-777-5917, (717)-810-2080 or e-mail toolingsales@te.com.

## Test Data

Shown below is current versus temperature rise of the five different available socket sizes.



Shown below is current versus voltage drop performance of the five different available socket sizes.




**Note:** All part numbers are RoHS compliant.

## RAPID LOCK Quick Connect Sockets and Pins

### Cable Mounted Sockets

RAPID LOCK sockets are crimped to AWG #4, #6 or #8 size cable depending on the application requirements. Envelope dimensions are common except for the crimp barrel diameter.



| Part Number | Size    | Dimensions |       |       | Cable AWG |
|-------------|---------|------------|-------|-------|-----------|
|             |         | C          | D     | E     |           |
| 6648228-X   | #8      |            |       |       | 8         |
| 6648237-X   |         | 1.080      | .500  | .500  | 12        |
| 1766484-X   |         | 27.43      | 12.70 | 12.70 | 6         |
| 6648235-X   | #4      |            |       |       | 8         |
| 6648236-X   |         | 1.08       | .500  | .500  | 4         |
| 6648239-X   |         | 27.43      | 12.70 | 12.70 | 6         |
| 6648234-X   | #2      |            |       |       | 0         |
| 6648238-X   |         | 1.280      | .490  | .640  | 2         |
| 1857178-X   |         | 32.51      | 12.45 | 16.26 | 1/0       |
| 1857547-X   | 12.0 mm | 1.920      | .930  | .930  | 3/0       |
|             |         | 48.70      | 23.70 | 23.70 |           |

**Note:** X refers to available color variants.

### Pin Contacts


RAPID LOCK pin contacts are offered in either swage or screw & washer mounting options for .125" (3.18 mm) or 3 mm (.118") thick PCB or bus bars. Consult TE Customer Service for other bus bar and backplane thicknesses and designs.

### Press Fit Pin Contacts

| Attach Type      | Pin Size | Mounts to         |
|------------------|----------|-------------------|
| Screw and Washer | #4       | Bus bar/Backplane |
|                  |          | Bus bar           |
| Swage            | #4       | Bus bar           |

**Note:** All part numbers include attachment hardware (screw, washer, etc.)


### Swage-Mount Pin



| Part Number | Size    | Dimensions |       |
|-------------|---------|------------|-------|
|             |         | A          | B     |
| 6648221-1   | #8      | .142       | .550  |
|             |         | 3.81       | 13.97 |
| 6648222-1   | #4      | .250       | .550  |
|             |         | 6.35       | 13.97 |
| 6648223-1   | #2      | .375       | .550  |
|             |         | 9.53       | 13.97 |
| 1857523-3*  | 12.0 mm | .470       | .850  |
|             |         | 12.00      | 21.70 |

\*Requires washer Part Number 1857513-2

### Screw-Mount Pin



| Part Number | Size | Dimensions |       |
|-------------|------|------------|-------|
|             |      | A          | B     |
| 6648224-1   | #4   | .250       | .550  |
|             |      | 6.35       | 13.97 |
| 6648226-1   | #2   | .375       | .550  |
|             |      | 9.53       | 13.97 |

**Note:** All part numbers are RoHS compliant.

## Custom RAPID LOCK Connector Products

In addition to the flexibility offered with standard RAPID LOCK connector products, the basic technology and standard components may also be packaged to suit specific customer needs. Some examples of custom packages are given below.

### Snap-Lock Sockets

Discrete pins are generally offered with or without a locking feature. A locking feature for a discrete socket is provided by a special two piece molding (94 V-0). This enables the socket to snap over a locking pin, and provides a 5 lb withdrawal force. The molding will also lock into a panel or holder of .125 (3.18) thickness.



| Part Numbers | Wire Size | Color |
|--------------|-----------|-------|
| 1643279-1    |           | Black |
| 1643279-2    | 8 AWG     | Red   |
| 1643279-3    |           | Blue  |
| 1651766-1    | 4 AWG     | Black |

### Press-Fit Discrete Contacts

Pins and sockets of the type shown are designed for press-fit to board or bus bar, and allow plug-in removal of a variety of board-mount components, discrete contacts, and flat-pack power supplies. Each socket contains a CROWN BAND contact, providing high current capacity and minimum loss, and accommodating misalignment.




**Note:** All part numbers are RoHS compliant.

## AMP Power Taps

### Product Facts

- **ACTION PIN** contacts eliminate soldering
- Provides high current, separable connection to pc board traces
- Wire-to-board connection using common terminals
- All metal-to-metal assembly for long-term integrity
- Standard DIP outlines (7.62 x 2.54 [.300 x .100]), 10 positions, and 6.35 x 3.18 [.250 x .125], 6 and 10 positions, plus high current versions on 10.16 x 5.08 [.400 x .200] footprint in 4 and 6 positions, 7.62 x 2.54 [.300 x .100] in 8 positions, and both 2 and 3 position in-line 2.54 [.100] tab taps
- Low resistance interface
- Internally threaded tap to secure screw to terminal
- Anti-rotational embossments hold wire and terminal in place
- Standard power taps rated at 2.5 Amps per pin — 6 position 15 Amps, 10 position 25 Amps current carrying capability
- High current power taps rated at up to 5 Amps per pin — 2 position 10 Amps, 3 position 15 Amps, 4 and 6 position 20 Amps and 8 position 40 Amps
- 30 Amp inverse sex power tap



AMP power taps are designed for the growing need for power to printed circuit board applications required in today's electronic industry. The taps provide a high current, separable connection to a pc board. Pin configuration is of the standard DIP outline with 7.62 x 2.54 [.300 x .100] or 6.35 x 3.18 [.250 x .125] for the standard versions, plus 10.16 x 5.08 [.400 x .200], 7.62 x 2.54 [.300 x .100] and in-line spacing for the high current versions.

ACTION PIN contacts provide a low resistance interface with tin-plated through holes in the pc board, thereby eliminating the need for soldering.

The variety of available power taps allow for various installation schemes. The uninsulated tap and low profile tap can be used in bus bar pattern. The high profile and low profile taps offer insulation protection from other components. The high current versions provide a greater power

density option with current ratings from 10 Amps on the 2 position in-line 6.35 [.250] tab tap up to 40 Amps on the 8 position dual 6.35 [.250] tab tap.

All AMP power tap configurations are easily inserted into the pc board with a simple TE or customer supplied tool.

## AMP Power Taps (Continued)

### Material and Finish

**Connector Body and Lid** — Nylon, 105°C 94V-0 rated

**Contact** — Copper alloy, bright tin-lead or tin plated

**Screw** — Plated steel

### Electrical and Mechanical Characteristics

**Resistance** — 2 milliohms, max. (stud hole to ACTION PIN contact)

**Insertion Force** — 40 lbs. [177.9N], max. per pin

**Retention Force** — 7 lbs. [31.1N], min. per pin

### Technical Documents

#### Product Specification


108-11030 Tap, Power Distribution

#### Application Specification

114-11000 Tap, Power Distribution

#### Handbook

5697 Guide to Application of ACTION PIN Connectors



| Tap Version  | PCB Thickness          | Description                                             | Screw Hole Size | Part Number |           |
|--------------|------------------------|---------------------------------------------------------|-----------------|-------------|-----------|
|              |                        |                                                         |                 | Tin Lead    | Tin       |
| High Profile | 1.57–3.18<br>.062–.125 | Housing and Contact Assembled With Screw <sup>1,2</sup> | 6-32            | 55557-4●    | 5055557-4 |
| Low Profile  | 1.57–3.18<br>.062–.125 | Housing and Contact Assembled With Screw <sup>2</sup>   | 6-32            | 55556-4●    | 5055556-4 |
| Low Profile  | 1.57–3.18<br>.062–.125 | Housing and Contact Assembled With Screw <sup>2,3</sup> | 6-32            | 55673-2●    | 5055673-2 |
| Low Profile  | 1.57–3.18<br>.062–.125 | Housing and Contact Assembled Without Screw             | M4              | 55556-9●    | 5055556-9 |

<sup>1</sup>Cover not Assembled

<sup>2</sup>Screw not Assembled

<sup>3</sup>No Anti-rotational Embossments

**Note:** Part Numbers are RoHS compliant except: ● Indicates "5 of 6 compliant" (lead in solderable interface only).

## AMP Power Taps (Continued)

### Material and Finish

**Contact**—Copper alloy, post plated bright tin-lead or tin plated


**Screw**—Stainless steel, passivated

### Electrical and Mechanical Characteristics

**Resistance** — 2 milliohms, max. (stud hole to ACTION PIN contact)

**Insertion Force** — 40 lbs. [177.9N] max. per pin

**Retention Force** — 7 lbs. [31.1N] min. per pin



| Size                                             | PCB Thickness                 | Dimensions           |                     |                     |                     | Description   | Screw Size | Part Number |             |
|--------------------------------------------------|-------------------------------|----------------------|---------------------|---------------------|---------------------|---------------|------------|-------------|-------------|
|                                                  |                               | A                    | B                   | C                   | D                   |               |            | Tin Lead    | Tin         |
| <b>7.62 x 2.54</b><br>.300 x .100<br>10 Position | <b>1.57-3.18</b><br>.062-.125 | <b>11.18</b><br>.440 | <b>8.26</b><br>.325 | <b>2.54</b><br>.100 | <b>7.62</b><br>.300 | Without Screw | 6-32       | 55558-3●    | 5055558-3   |
|                                                  |                               |                      |                     |                     |                     | With Screw    | 6-32       | 55558-4●    | 5055558-4   |
| <b>6.35 x 3.18</b><br>.250 x .125<br>6 Position  | <b>1.57-3.18</b><br>.062-.125 | <b>8.13</b><br>.320  | <b>6.99</b><br>.275 | <b>3.18</b><br>.125 | <b>6.35</b><br>.250 | Without Screw | 6-32       | 55323-5●    | 5055323-5   |
|                                                  |                               |                      |                     |                     |                     | With Screw    | 6-32       | 55323-9●    | 5055323-9   |
| <b>6.35 x 3.18</b><br>.250 x .125<br>10 Position | <b>1.57-3.18</b><br>.062-.125 | <b>14.48</b><br>.570 | <b>6.99</b><br>.275 | <b>3.18</b><br>.125 | <b>6.35</b><br>.250 | Without Screw | 6-32       | 55323-6●    | 5055323-6   |
|                                                  |                               |                      |                     |                     |                     | With Screw    | 6-32       | 1-55323-0●  | 1-5055323-0 |

### High Current\* Power Taps

\*Up to 20 Amps

### Material and Finish

**Contact** — Phosphor bronze, tin-lead or tin plated

**Screw** — Stainless steel, passivated


**Washer** — Stainless steel

### Electrical and Mechanical Characteristics

**Current Rating** — 20 Amps max.

**Insertion Force** — 40 lbs. [180N] max. per pin

**Retention Force** — 7 lbs. [30N] min. per pin



| Size       | PCB Thickness                 | Dimensions          |                      |                     |                      | Description        | Part Number            |           |
|------------|-------------------------------|---------------------|----------------------|---------------------|----------------------|--------------------|------------------------|-----------|
|            |                               | A                   | B                    | C                   | D                    |                    | Tin Lead               | Tin       |
| 4 Position | <b>1.57-3.18</b><br>.062-.125 | <b>9.09</b><br>.358 | <b>10.95</b><br>.431 | <b>5.08</b><br>.200 | <b>10.16</b><br>.400 | With Screw, Washer | 213815-1●              | 5213815-1 |
|            |                               |                     |                      |                     |                      | Without Screw      | 216906-1● <sup>1</sup> | —         |
| 6 Position | <b>1.57-3.18</b><br>.062-.125 | <b>9.09</b><br>.358 | <b>10.95</b><br>.431 | <b>2.54</b><br>.100 | <b>10.16</b><br>.400 | With Screw, Washer | 213816-1●              | 5213816-1 |
|            |                               |                     |                      |                     |                      | Without Screw      | 216907-1● <sup>1</sup> | —         |

<sup>1</sup>No Anti-rotation Embossments featured on High Current Taps. Therefore, if application requires product supplied without washer and screw, use of lock-washers with a high surface contact area are strongly recommended.

### For High Current and FASTON Taps


Use with Hand Press **677430-1**

### Recommended PC Board Layout

**Drilled Hole Diameter**—  
1.60±0.03 [.063±.001]

**Cu Thickness**—  
0.03-0.08 [.001-.003]

**SnPb Thickness**—  
0.004 min. [.0002 min.]



**Finished Hole**—  
1.36-1.54 [.054-.061]

**After Reflow**—  
1.36-1.54 [.054-.061]

| Type       | A                    | B                   | C                   |
|------------|----------------------|---------------------|---------------------|
| 4 Position | <b>10.16</b><br>.400 | <b>5.08</b><br>.200 | <b>5.08</b><br>.200 |
| 6 Position | <b>10.16</b><br>.400 | <b>2.54</b><br>.100 | <b>5.08</b><br>.200 |
| I          | —                    | <b>5.08</b><br>.200 | <b>5.08</b><br>.200 |
| II         | —                    | <b>2.54</b><br>.100 | <b>5.08</b><br>.200 |
| III        | <b>10.16</b><br>.400 | <b>5.08</b><br>.200 | <b>5.08</b><br>.200 |
| IV         | <b>7.62</b><br>.300  | <b>2.54</b><br>.100 | <b>7.62</b><br>.300 |

**Note:** Part Numbers are RoHS compliant except: ● Indicates "5 of 6 compliant" (lead in solderable interface only).

## AMP Power Taps (Continued)

\*Up to 5 Amps per pin

### Mating Connectors FASTON Receptacles

#### Material and Finish

**Contact** — Phosphor bronze, post plated tin-lead or tin plated

**Screw** — Stainless steel, passivated


**Washer** — Stainless steel

#### Electrical and Mechanical Characteristics

**Current Rating** — 5 Amps max. per pin

**Insertion Force** — 40 lbs. [180N] max. per pin

For Recommended PC Board Layout, see page 170.



| Style | PCB Thickness              | Dimensions    |               |               |               | Description                      | Part Number           | Receptacle Mating |
|-------|----------------------------|---------------|---------------|---------------|---------------|----------------------------------|-----------------------|-------------------|
|       |                            | A             | B             | C             | D             |                                  |                       |                   |
| I     | 1.39 x 1.54<br>.055 x .061 | 13.50<br>.531 | 10.75<br>.423 | 18.50<br>.728 | 2.54<br>.100  | 2.8 x 0.80<br>.110 x .031 Tab    | 338429-2              | Positive Lock     |
| II    | 1.57 x 3.18<br>.062 x .125 | 5.08<br>.200  | 13.49<br>.531 | —             | —             | 6.35 x 0.81<br>.250 x .032 Tab   | 216926-1              | Positive Lock     |
| III   | 1.57 x 3.18<br>.062 x .125 | 2.54<br>.100  | 13.49<br>.531 | —             | —             | 6.35 x 0.81<br>.250 x .032 Tab   | 216843-1              | Positive Lock     |
| IV    | 1.57 x 3.18<br>.062 x .125 | 10.16<br>.400 | 5.08<br>.200  | 13.49<br>.531 | 10.95<br>.431 | 1-6.35 x 0.81<br>.250 x .032 Tab | 216905-1 <sup>1</sup> | Positive Lock     |
|       |                            |               |               |               |               | 2-2.79 x 0.81<br>.110 x .032 Tab |                       |                   |
| V     | 3.18<br>.125               | 7.62<br>.300  | 2.54<br>.100  | 12.32<br>.485 | 12.70<br>.500 | With Dimple                      | 167892-3 <sup>2</sup> | FASTON Rcpt.      |
|       |                            |               |               |               |               | With Hole                        | 167892-6 <sup>2</sup> | Positive Lock     |

<sup>1</sup>No Anti-rotation Embossments featured on High Current Taps. Therefore, if application requires product supplied without washer and screw, use of lock-washers with a high surface contact area are strongly recommended.

<sup>2</sup>Phosphor Bronze, post plated matte tin

**Note:** All part numbers are RoHS compliant.

## AMP Power Taps (Continued)

### Application Tooling/ PCB Layout

#### For Standard Threaded Taps Only

#### Recommended PC Board Layout

**Drilled Hole Diameter—**  
.0453±.001 [1.15±0.03]

**After Plating**

.037-.043 [0.94-1.09]



**After Reflow—**

.036-.043 [0.91-1.09]

#### Installation and Extraction Tooling

**Impact Insertion Tool Number**  
313102-1

(Insertion Tip No. 58133-1 required)



| Size                                      | Dimensions   |              |               |
|-------------------------------------------|--------------|--------------|---------------|
|                                           | A            | B            | C             |
| .300 x .100<br>7.62 x 2.54<br>10 Position | .300<br>7.62 | .100<br>2.54 | .400<br>10.16 |
| .250 x .125<br>6.35 x 3.18<br>6 Position  | .250<br>6.35 | .125<br>3.18 | .250<br>6.35  |
| .250 x .125<br>6.35 x 3.18<br>10 Position | .250<br>6.35 | .125<br>3.18 | .500<br>12.7  |



**Extraction Tool**  
Part Number 68380-1

#### For High Current and FASTON Taps

Use with Hand Press 677430-1

#### Recommended PC Board Layout

**Drilled Hole Diameter—**  
.063±.001 [1.60±0.03]

**Cu Thickness—**

.001-.003 [0.03-0.08]

**SnPb Thickness—**


.0002 min.[0.004 min.]

**Finished Hole—**

.055-.061 [1.39-1.54]

**After Reflow—**

.054-.061 [1.36-1.54]



| Type       | A             | B            | C            |
|------------|---------------|--------------|--------------|
| 4 Position | .400<br>10.16 | .200<br>5.08 | .200<br>5.08 |
| 6 Position | .400<br>10.16 | .100<br>2.54 | .200<br>5.08 |
| I          | —             | .200<br>5.08 | .200<br>5.08 |
| II         | —             | .100<br>2.54 | .200<br>5.08 |
| III        | .400<br>10.16 | .200<br>5.08 | .200<br>5.08 |
| IV         | .300<br>7.62  | .100<br>2.54 | .300<br>7.62 |

#### Installation Tooling


| Type                         | Part Number           | Upper Tool | Lower Tool              |
|------------------------------|-----------------------|------------|-------------------------|
| High Current 4 & 6 Positions | 216906-1<br>216907-1  | 432848-1   | 433600-2 or<br>432130-2 |
| High Current Style I, II     | 216926-1<br>216843-1  | 432845-1   | 433600-2 or<br>432130-2 |
| High Current Style III       | 216905-1              | 432847-1   | 433600-2 or<br>432130-2 |
| High Current Style IV        | 5167892-3<br>167892-6 | 432849-1   | 433600-2 or<br>432130-2 |

**Note:** All part numbers are RoHS compliant.

## Introduction to High Current Card Edge Connectors

### Product Facts

- Contacts on .100 [2.54] Centerlines
- Selective gold plating of contacts for high performance at low cost
- Flow solder applications
- Glass-filled polyester housing is 94V-0 rated
- Available in vertical, right-angle or straddle PCB-mount
- Solder tails for wave solder applications
- Compliant press-fit PCB tails for solder-less applications
- 50% to 100% greater current carrying capacity than traditional card edge connectors
- Accepts double sided PC boards, .054-.070 [1.27-1.78] thick
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476
- Certified by Canadian Standards Association, File No. LR 7189



### Introduction

The High Current Edge family of connectors provides high reliability and economy in packages compatible with industry standards. While many new card edge connectors for signal applications have moved toward higher density configurations (0.050" and 1 mm centerlines), TE has redesigned the 0.100" standard edge product family to carry more current, for low power distribution.

This product family includes the following:

- CROWN EDGE Products
- Standard Edge Connector — 2nd generation
- SEC-II Power Products


The connectors serve low durability cycle applications which do not have the available room for a traditional 2-piece power distribution connector. In other applications, a low-profile connector is needed to allow for better airflow / less airflow restriction. This grouping of power card edge connectors is focused on providing high current density with the favored multi-point contact design which reduces contact interface resistance.

The connectors were used originally in the ISA Standard for computer expansion cards. Today these connectors are being

used in applications such as; DC-to-DC converters, low-wattage power supplies, industrial grade card extenders and general low cost I/O applications requiring durable/rugged card edge contacts. The improvements made still allows use in the original applications and they provide a lower resistance connection due to the high conductivity contacts plated with a minimum 30 micro inches gold.


The options include vertical or right-angle PCB mounting as well as straddle-mount configurations for co-planar PCB applications.

## Introduction to High Current Card Edge Connectors (Continued)




### CROWN EDGE Connector

- Design based on CROWN BAND technology
- 35A per power contact
- True hot-plug power modules
- Flexible modular design
- Mates with .062 [1.6] thick card edge or bus bar tab



### SEC-II Power Connector

- High current density than high current SEC II
- Uses new MULTI-BEAM style power contact
- Vertical, straddle or right-angle PCB mounting
- 22A (straddle) or 28A (vertical) power contact +3A signal contact



### SEC-II Connectors

- Provides high reliability in packages compatible with industry standards for double-sided printed circuit boards
- Uses signal style contact
- High IACS copper alloy contacts available to improve current carrying capability
- Accepts double-sided boards .054 [1.27]-.070 [1.78] thick
- Maximum number of dual positions
  - .100 [2.54] Centerlines — 70 positions
  - .125 [3.18] Centerlines — 50 positions
  - .150 [3.81] Centerlines — 31 positions


## CROWN EDGE Card Edge-style High Current Connectors

### Product Facts

- Low cost power solution
- Power, signal and mixed modules
- 35A per power contact
- Mates with .062 (1.6 mm) thick card edge or bus bar tab
- Press-fit or solder tail terminations
- True hot-plug power modules
- Meets regulatory safety requirements
- All CROWN EDGE products in this section are RoHS compliant.

### Typical Applications

- Board-to-board power connections
- DC-DC converters
- Uninterruptible Power Supply (UPS)
- Power supplies



CROWN EDGE connectors are a board-to-board power interconnect solution that uses ELCON high performance CROWN BAND contact technology configured to mate directly with a printed circuit board edge or — for higher currents — with a solid bus bar. Power and signal can be combined and mounted end-to-end to meet the requirements of the applications.

### Product Highlights

#### High-current Card Edge Interface

CROWN EDGE connectors use TE proven ELCON CROWN BAND contacts that provide multiple points of contact for high current, and low voltage drop and minimal heat generation. The desired current rating for most applications can be achieved by bussing multiple contacts or even modules. For even higher currents, CROWN EDGE connectors can be mounted onto a bus bar, and mate directly with a bus bar tab. Optimum interface to the mounting PC board is achieved through five termination tails.

### Flexible Modular Design

To make easy work of power distribution design, CROWN EDGE connectors are available in modules of 2 and 3 contact segments with power or signal contacts or a combination of both in a single module. Modules can be placed end-to-end for assemblies up to 8" (203.20 mm) long. Custom molded configurations are possible on high-volume projects. Consult TE or your local TE sales representative for details.

### Versatile Power Arrangements

Opposing contacts are isolated, so power connections at different voltage levels can be on one side of the board, with ground or power return on the other side.

### True Hot-Plug Support

CROWN EDGE power modules that support current interruption under load as defined by safety regulatory agencies are also available for mating to a metal blade or bus bar tab. These true hot-plug modules allow current interruption under load by incorporating a contact design that restricts the effects of arcing to areas that do not compromise the integrity of the connection.

## CROWN EDGE Card Edge-style High Current Connectors (Continued)


### Product Specifications

| Materials & Finishes  |                            |                    |                                                                                                                        |
|-----------------------|----------------------------|--------------------|------------------------------------------------------------------------------------------------------------------------|
| Insulators            |                            |                    | PPA, UL 94-V-0 flammability rated, color black                                                                         |
| Contacts              | Non-hot-plug power contact |                    | Copper alloy, selectively plated with gold (30 micro inches minimum) and tin on terminations, all over nickel          |
|                       | Hot-plug power contact     | Contact holder     | Phosphor bronze alloy, selectively plated with tin on terminations, over nickel                                        |
|                       |                            | CROWN BAND element | Beryllium copper alloy, selectively plated with gold (30 micro inches minimum), over nickel                            |
|                       | Signal contacts            |                    | Phosphor bronze alloy, selectively plated with gold (30 micro inches minimum) and tin on terminations, all over nickel |
| Electrical            |                            |                    |                                                                                                                        |
| Current ratings       | Power contact              |                    | 35A (see graph below)                                                                                                  |
|                       | Signal contact             |                    | 3A max.                                                                                                                |
| Insulation resistance |                            |                    | 5,000M $\Omega$ minimum at 500 VDC for 2 minutes, power MIL-STD 1344, Method 3003                                      |
| Dielectric strength   |                            |                    | 1,500VDC for 1 minute, per MIL-STD 1344, Method 3001                                                                   |
| Mechanical            |                            |                    |                                                                                                                        |
| Mating PCB thickness  |                            |                    | .062" 91.6 mm $\pm$ .006" (0.15 mm)                                                                                    |
| Insertion Forces      | 2 segment power module     |                    | 5.0 lbf typical using .062" (1.6 mm) thick mating board with 5 oz. of copper                                           |
|                       | 3 segment power module     |                    | 6.0 lbf typical using .062" (1.6 mm) thick mating board with 5 oz. of copper                                           |
| Extraction Forces     | 2 segment power module     |                    | 3.0 lbf typical using .062" (1.6 mm) thick mating board with 5 oz. of copper                                           |
|                       | 3 segment power module     |                    | 5.0 lbf typical using .062" (1.6 mm) thick mating board with 5 oz. of copper                                           |
| Tooling               |                            |                    | Press fixture is recommended for compliant press-fit assemblies<br>Consult TE customer service for details             |

### Current Ratings

The chart below demonstrates the performance of the CROWN EDGE power contact by showing the temperature rise at different current levels applied to two power contacts connected in series.

Current rating for any given application will depend, among other things, on the module combination, PCB copper trace volume, and internal equipment temperature/air flow. Mounting and mating to a bus bar will increase current ratings.



### Safety Regulatory Compliance

CROWN EDGE connectors have been evaluated by Underwriters Laboratories and have been found to comply with the requirements of U.S. standard UL1997 and Canadian standard C22.2 No. 182.3-M1987.



### Compliance with Current Interruption Requirements



Hot-plug CROWN EDGE modules are available for applications that require current interruption as defined by safety regulatory agencies. These power-only modules have been evaluated and recognized by Underwriters Laboratories for current interruption up to 50 cycles as per the UL1977 standard. See hot-plug requirements on page 180.

## CROWN EDGE Card Edge-style High Current Connectors (Continued)

## 4-Position Power Module

## Part Numbers



|           |                                  |                                                                                                     |
|-----------|----------------------------------|-----------------------------------------------------------------------------------------------------|
| 6651170-1 | Long solder tail, non-hot-plug*  | * Also available for .093" (2.4 mm) thick mating board.<br>Contact TE Customer Service for details. |
| 6651170-2 | Press-fit tail, non-hot-plug*    |                                                                                                     |
| 6651170-3 | Short solder tail, non-hot-plug* |                                                                                                     |
| 6651331-1 | Press-fit tail, hot-plug         |                                                                                                     |
| 6650380-1 | Short solder tail, hot-plug      |                                                                                                     |
| 6650380-2 | Long solder tail, hot-plug       |                                                                                                     |



## 6-Position Power Module

## Part Numbers



|           |                                 |
|-----------|---------------------------------|
| 6650383-1 | Press-fit tail, non-hot-plug    |
| 6650383-2 | Long solder tail, non-hot-plug  |
| 6650383-3 | Short solder tail, non-hot-plug |
| 6650384-1 | Short solder tail, hot-plug     |
| 6650384-2 | Press-fit tail, hot-plug        |
| 6650384-3 | Long solder tail, hot-plug      |



### 30-Position Signal Module

## Part Number

1926088-1 Press-fit tail, non-hot-plug




**Note:** All part numbers are RoHS compliant.

## CROWN EDGE Card Edge-style High Current Connectors (Continued)

### 16-Position Signal Module

#### Part Numbers

6650534-1 Press-fit tail




### 24-Position Signal Module

#### Part Numbers

6650494-1 Press-fit tail

6651193-1 Long solder tail

6651214-1 Short solder tail




**Note:** All part numbers are RoHS compliant.

## CROWN EDGE Card Edge-style High Current Connectors (Continued)

### 2 Power + 8 Signal Modules

#### Part Numbers


- 6643460-1 Short solder tail  
6643460-2 Long solder tail  
6643460-3 Press-fit tail



### 4 Power + 8 Signal Modules

#### Part Numbers

- 6651290-1 Press-fit tail  
6651290-2 Long solder tail  
6651290-3 Short solder tail



**Note:** All part numbers are RoHS compliant.

## CROWN EDGE Card Edge-style High Current Connectors (Continued)

## Design Notes

## Mating PCB Requirements


Mating PCB edge fingers should be gold plated, have .050" (1.3 mm) side margins, and be of suitable copper weight for power applications. Mating board thickness is .062 [1.60].

## Sequenced Mating

Sequenced mating can be achieved by designing one or more setback traces on the mating card edge, or by notching the edge of the card.


## End-to-end Mounting

CROWN EDGE modules can be placed end-to-end for connector assemblies up to 8" (203.20 mm) long.




### Mating PC Card Edge Samples

The drawings below show two PC card edge samples with signal and power lines designed to mate with 2 and 3-segment CROWN EDGE modules.





**2 x 2 Segment Modules Provide Two Sequenced Power Traces and 30 Signal Traces**



### 2 x 3 Segment Modules Provide Ground Plane and 12 Signal Lines

## Hot-Plug Requirements

Hot-plug application of this product requires the use of the CROWN EDGE true hot-plug modules (see part numbers on pages 177-179) mated with a customer-supplied metal blade or bus bar. Dimensions of a sample mating blade for use with CROWN EDGE hot-plug modules is shown below.




## CROWN EDGE Card Edge-style High Current Connectors (Continued)

### Connector Mounting

#### Solder Tails

Solder termination is available in two lengths. See table below for board thicknesses and recommended tail lengths.




Solder Tail Detail

#### Tail Length vs. Board Thickness

| Board Thickness          | Dimension "A"                                               |
|--------------------------|-------------------------------------------------------------|
| .062" (1.6 mm)           | .100" - .140" (2.55 - 3.57 mm)<br>[.115" (2.92 mm) nominal] |
| .092"/.125" (2.3/3.0 mm) | .160" - .200" (4.06 - 5.08 mm)<br>[1.77" (4.5 mm) nominal]  |

#### Press-fit Tails

CROWN EDGE connectors use truly compliant eye of the needle press-fit tails designed for boards 0.093" thick and above.



Press-fit Tail Detail

#### Tooling for Compliant Press-fit Assemblies

Pressing fixtures are recommended for compliant press-fit assemblies. Contact TE for a detailed tool drawing.

#### Suggested Printed Circuit Hole for Power and 2.5 mm Signal




Finished Hole:  $\varnothing .040 \pm .003$  [ $\varnothing 1.02 \pm .08$ ]  
 Drilled Hole:  $\varnothing .0453 \pm .005$  [ $\varnothing 1.151 \pm .013$ ]  
 Copper Plate: .0010 [.025] min. (per surface)  
 Tin Plate: .0003 [.008] min. (per surface)

#### Suggested Printed Circuit Hole for 1.5 mm Signal

Finished Hole:  $\varnothing .022 \pm .002$  [ $\varnothing 0.56 \pm 0.05$ ]  
 Drilled Hole:  $\varnothing .026 \pm .002$  [ $\varnothing 0.65 \pm 0.02$ ]  
 Copper Plate: .0010 [.025] min. (per surface)  
 Tin Plate: .0003 [.008] min. (per surface)

#### Spacing Between Modules in End-to-end Mounting

This spacing between plated thru-holes for end-to-end mounting varies depending on the chosen module combination. Spacing for the three possible combinations is shown below.



### Custom Solutions

#### Non-standard Modules

In case the standard CROWN EDGE modules do not meet your design requirements, TE has the capability to mold any combination of power and signal contact layouts in 2 and 3 segment modules.



#### Application-specific Custom Designs

TE has a long history of designing and building application specific custom connectors, and CROWN EDGE connectors are no exception. A one-piece CROWN EDGE insulator, instead of a combination of several modules, provides a more robust interconnection design, as well as cost savings in high volume projects. Consult TE Customer Service for details.



## SEC-II Power Products

### Product Facts

- Combines industry standard 0.100" pitch card edge format in a high power density design
- Industry-proven multi-beam power contact design
- High conductivity contact materials
- High temperature housing materials
- UL 94V-0
- Selective gold plating for high performance with low cost
- .000030 [0.00076] gold in contact area. Tin/lead on posts with entire contact nickel underplated
- Power Contact Current Ratings:
  - 38 amps — Single Contact
  - 22 amps — on each of 4 adjacent pairs (8 power contacts)
- Signal Contact Ratings:
  - 6 amps — Single Contact
  - 4 amps — on each of 6 adjacent contacts



The trends in electronic power supplies require high current density and lower cost. In addition, smaller sized connectors are needed to provide less airflow restriction for cooling the power supplies. The SEC-II power connectors offer an ideal combination of low-current and high-current connections in a single, durable design.

SEC-II power connectors are built on an expandable tooling platform which

allows for a variety of combinations of power and signal contacts, all combined in a single molded housing. The vertical press-fit versions are ideal for high density stacking of cards into a backplane or for low air restriction of blade-style power supply designs. The straddle mount style offers a true co-planar interconnection with a total height of less than 4 mm from the top surface of the PCB.

SEC-II power connectors are currently in use in high-end computer and data storage equipment. Extensive testing in exposure to high vibration and shock has proven these connectors equally suited for industrial applications as well, where low contact resistance and high current density is required.

### Product Specification

108-2202

### Qualification Test Report


501-608




Vertical



Co-Planar




Right-Angle



8P

Power Only



6P + 16S


Power and Signal

**Note:** See page 183 for part numbers and details.


## SEC-II Power Products (Continued)

### Co-Planar Application

Straddle-Mount to .062 [1.6]  
PCB



| No. of Power Contacts | No. of Signal Contacts | Dimensions     |                | With or Without Mounting Ears | Part Number |
|-----------------------|------------------------|----------------|----------------|-------------------------------|-------------|
|                       |                        | "A" Length     | "B" Card Slot  |                               |             |
| 4                     | 16                     | 1.66<br>42.16  | 1.500<br>38.10 | Without                       | 2007088-2   |
| 6                     | 16                     | 1.960<br>49.78 | 1.800<br>45.72 | Without                       | 2007088-1   |
| 6                     | 20                     | 2.745<br>69.72 | 2.000<br>50.80 | With                          | 1761500-1   |
| 8                     | 16                     | 2.260<br>57.40 | 2.100<br>53.40 | Without                       | 2007088-3   |
| 8                     | 22                     | 3.145<br>79.88 | 2.400<br>60.96 | With                          | 1761879-1   |



| No. of Power Contacts | No. of Signal Contacts | Dimensions     |                | Part Number |
|-----------------------|------------------------|----------------|----------------|-------------|
|                       |                        | "A" Length     | "B" Card Slot  |             |
| 6                     | 16                     | 1.960<br>49.78 | 1.880<br>47.75 | 2057372-1   |



**Note:** All part numbers are RoHS compliant.

## SEC-II Power Products (Continued)

### Vertical PCB-Mount

#### Seating tool required

\*See customer drawing for details



| Dimensions                    |                  |   |                  |                  |    |                  |                  | No. of Power Contacts | No. of Signal Contacts | Omitted PIN | Molded Key Location | Part Number |
|-------------------------------|------------------|---|------------------|------------------|----|------------------|------------------|-----------------------|------------------------|-------------|---------------------|-------------|
| A                             | B                | C | D                | E                | F  | G                | H                |                       |                        |             |                     |             |
| Power and Signal, Solder Tail |                  |   |                  |                  |    |                  |                  |                       |                        |             |                     |             |
| 92.93<br>[3.660]              | 88.90<br>[3.500] | 7 | 53.34<br>[2.100] | 81.28<br>[3.200] | 23 | 58.42<br>[2.300] | 90.18<br>[3.550] | 16                    | 20                     | None        | None                | 1761426-1   |
| 70.1<br>[2.760]               | 66.07<br>[2.600] | 4 | 30.48<br>[1.200] | 58.42<br>[2.300] | 14 | 35.56<br>[1.400] | 67.31<br>[2.650] | 10                    | 20                     | None        | None                | 1761426-2   |
| 54.86<br>[2.160]              | 50.80<br>[2.000] | 2 | 15.24<br>[0.600] | 43.18<br>[1.700] | 8  | 20.32<br>[0.800] | 52.07<br>[2.050] | 6                     | 20                     | None        | None                | 1761426-3   |
| Power and Signal, Press-Fit   |                  |   |                  |                  |    |                  |                  |                       |                        |             |                     |             |
| 54.61<br>[2.150]              | 50.80<br>[2.000] | 3 | 22.86<br>[0.900] | 40.64<br>[1.600] | 17 | 43.16<br>[1.700] | 49.53<br>[1.950] | 8                     | 12                     | None        | None                | 1761786-1   |
| Power only, Press-Fit         |                  |   |                  |                  |    |                  |                  |                       |                        |             |                     |             |
| 24.13<br>[0.950]              | 20.32<br>[0.800] | 1 | 3.81<br>[0.150]  | 12.70<br>[0.500] | 5  | N/A              | 18.79<br>[0.740] | 4                     | 0                      | None        | None                | 1888946-1   |
| 31.75<br>[1.250]              | 27.94<br>[1.100] | 2 | 7.62<br>[0.300]  | 20.32<br>[0.800] | 8  | N/A              | 26.42<br>[1.040] | 6                     | 0                      | None        | None                | 1888946-2   |
| 39.37<br>[1.550]              | 35.56<br>[1.400] | 3 | 11.43<br>[0.450] | 27.94<br>[1.100] | 11 | N/A              | 34.03<br>[1.340] | 8                     | 0                      | None        | None                | 1888946-3   |

**Note:** All part numbers are RoHS compliant.

## Standard Edge II Card Edge Connectors

### Product Facts

- Maximum number of dual positions  
.100 [2.54] Centerlines-70,  
.125 [3.18] Centerlines-50,  
.150 [3.81] Centerlines-31
- Selective gold plating of contacts for high performance at low cost
- .025 [0.64] square solid posts meet standard wrap-type specifications
- For flow solder applications
- Glass-filled polyester housing is 94V-0 rated
- Accepts double sided PC boards, .054-.070 [1.27-1.78] thick
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476 
- Certified by Canadian Standards Association, File No. LR 7189 

### Performance Specifications

**Contact Rating\*** — 3 Amps continuous (UL and CSA)

**Contact Resistance** — 10 milliohms max.

**Operating Temperature** — -55°C to +85°C

**Voltage Rating (Sea Level)** —  
.100 [2.54] centerline — 1000 VAC (test)  
.125 [3.18] centerline — 1500 VAC (test)  
.150 [3.81] centerline — 1500 VAC (test)

**Insulation Resistance** —  
5000 megohms min., after exposure to humidity

**Vibration Tolerance** — 10 to 500 Hz

**Contact Engagement Force** —  
12 oz [3.3 N] average per pair with .062 [1.57] PC board

**Contact Separation Force** —  
2 oz [0.6 N] average per pair with .062 [1.57] PC board

**Humidity Tolerance** — 90%-95% for 96 hours

\*Consult TE engineering when paralleling contacts for power applications.



TE Standard Edge II Connectors provide high reliability and economy in packages compatible with industry standards for double sided printed circuit boards.

TE offers Standard Edge II Connectors with or without mounting ears, for rack mounting and soldering. Contacts are arranged on .100 [2.54] centers, .125 [3.18] centers, .150 [3.81] centers, .200 [5.08] row-to-row; and .250 [6.35] row-to-row.

Right-angle connectors are also available with contacts arranged on .100 [2.54] centers, .150 [3.81] row-to-row or .200 [5.08] row-to-row.

Card extenders with contacts on .100 [2.54] and .125 [3.18] centers also are available.

Precision formed phosphor bronze contacts are selectively gold plated. Phosphor bronze has excellent strength characteristics which help the connector absorb load deflection movement of a PC board while maintaining sufficient contact force for good electrical connection. Bifurcated cantilever beam contacts provide redundant contact.

## Standard Edge II Card Edge Connectors (Continued)


### .100 [2.54] Centerline, Vertical Solder Posts, Without Mounting Ears

#### Material and Finish

**Housing** — Black glass-filled polyester, 94V-0 rated

**Contacts** — Phosphor bronze, duplex plated as follows:

**Plating** — .000030 [0.00076] gold in contact area, tin on posts, with entire contact nickel underplated



#### Technical Documents

##### Product Specification

108-9039


##### Qualification Test Report

501-227

### Intercontact Keying Plug

#### Material

Natural color polyester



**Part Number 650025-2**  
(.100 [2.54] Centerline)

| No. of Dual Positions | Dimensions      |                 |                 |                 | Post Length*                   | Part Numbers***<br>Solder Tail |
|-----------------------|-----------------|-----------------|-----------------|-----------------|--------------------------------|--------------------------------|
|                       | A               | B               | C**             | D               |                                |                                |
| 6                     | .860<br>21.84   | .750<br>19.05   | .700<br>17.78   | .500<br>12.70   | .125<br>3.18                   | 7-5530843-5                    |
| 10                    | 1.260<br>32.00  | 1.150<br>29.21  | 1.100<br>27.94  | .900<br>22.86   | .125<br>3.18                   | 5-5530843-0                    |
| 12                    | 1.460<br>37.08  | 1.350<br>34.29  | 1.300<br>33.02  | 1.100<br>27.94  | .125<br>3.18                   | 8-5530843-3                    |
| 15                    | 1.760<br>44.70  | 1.650<br>41.91  | 1.600<br>40.64  | 1.400<br>35.56  | .125<br>3.18                   | 5530843-2                      |
| 17                    | 1.960<br>49.78  | 1.850<br>46.99  | 1.800<br>45.72  | 1.600<br>40.64  | .125<br>3.18                   | 5-5530843-3                    |
| 18                    | 2.060<br>52.32  | 1.950<br>49.53  | 1.900<br>48.26  | 1.700<br>43.18  | .125<br>3.18                   | 5530843-3                      |
| 20                    | 2.260<br>57.40  | 2.150<br>54.61  | 2.100<br>53.34  | 1.900<br>48.26  | .125<br>3.18                   | 5-5530843-4                    |
| 22                    | 2.640<br>62.48  | 2.350<br>59.69  | 2.300<br>58.42  | 2.100<br>53.34  | .125<br>3.18                   | 5530843-4                      |
| 25                    | 2.760<br>70.10  | 2.650<br>67.31  | 2.600<br>66.04  | 2.400<br>60.96  | .125<br>3.18                   | 5530843-5                      |
| 28                    | 3.060<br>77.72  | 2.950<br>74.93  | 2.900<br>73.66  | 2.700<br>68.58  | .125<br>3.18                   | 5530843-6                      |
| 30                    | 3.260<br>82.80  | 3.150<br>80.01  | 3.100<br>78.74  | 2.900<br>73.66  | .125 and .187<br>3.18 and 4.75 | 5530843-7                      |
| 31                    | 3.360<br>85.34  | 3.250<br>82.55  | 3.200<br>81.28  | 3.000<br>76.20  | .125<br>3.18                   | 6-5530843-5                    |
| 35                    | 3.760<br>95.50  | 3.650<br>92.71  | 3.600<br>91.44  | 3.400<br>86.36  | .125<br>3.18                   | 2-5530843-3                    |
| 36                    | 3.860<br>98.04  | 3.750<br>95.25  | 3.700<br>93.98  | 3.500<br>88.90  | .125<br>3.18                   | 5530843-8                      |
| 40                    | 4.260<br>108.20 | 4.150<br>105.41 | 4.100<br>104.14 | 3.900<br>99.06  | .187<br>3.18                   | 2-5530843-0                    |
| 50                    | 5.260<br>133.60 | 5.150<br>130.81 | 5.100<br>129.54 | 4.900<br>124.46 | .187<br>3.18                   | 2-5530843-2                    |

\*Contact TE for alternate post length.

\*\*C dimension is card slot length.

\*\*\*Press-fit parts can be made available, consult TE.

**Notes:** 1. Other connector sizes can be made available, consult TE.

2. High temperature IR reflow compatible connectors can be made available, consult TE.

**Note:** All part numbers are RoHS compliant.

## Standard Edge II Card Edge Connectors (Continued)

### .100 [2.54] Right-Angle Solder Posts, with Low and No Mounting Ears

#### Material and Finish

**Housing** — Black glass-filled polyester, 94V-0 rated

**Contacts** — Phosphor bronze, duplex plated as follows:

**Plating A** — .000030 [0.00076] gold in contact area, tin on posts, with entire contact nickel underplated

**Plating B** — .000015 [0.00038] gold in contact area, tin on posts, with entire contact nickel underplated

#### Related Product Data

**Performance Specifications** — page 185


#### Technical Documents

**Product Specification**  
108-9039


### Intercontact Keying Plug

#### Material

Natural color polyester



**Part Number 650025-2**  
(.100 [2.54] Centerline)



### Low Mounting Ears

| No. of Dual Positions | Dimensions     |                |                |                |                |                |                | Post Length <sup>2</sup> | Part Numbers (Plating A) |
|-----------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|--------------------------|--------------------------|
|                       | A              | B              | C*             | D              | E              | F              | G <sup>1</sup> |                          |                          |
| 12                    | 1.460<br>37.08 | 1.350<br>34.29 | 1.300<br>33.02 | 1.100<br>27.94 | 2.045<br>51.94 | 1.775<br>45.08 | .100x<br>.150  | .090                     | 5145089-1 <sup>3</sup>   |
| 18                    | 2.060<br>52.32 | 1.950<br>49.53 | 1.900<br>48.26 | 1.700<br>43.18 | 2.645<br>67.18 | 2.375<br>60.32 | .100x<br>.150  | .090                     | 5645384-1                |
| 20                    | 2.260<br>57.40 | 2.150<br>54.61 | 2.100<br>53.34 | 1.900<br>48.26 | 2.845<br>72.30 | 2.575<br>65.40 | .100x<br>.150  | .090                     | 5645384-3                |

\*C dimension is card slot length.

<sup>1</sup> Metric equivalent for .100 x .150 and .100 x .200 are [2.54 x 3.81] and [2.54 x 5.08].

<sup>2</sup> Metric equivalent for post length is .090 = [2.27].

<sup>3</sup> Connector with Board Locks.

**Note:** Other connector sizes can be made available, consult TE.

### No Mounting Ears

| No. of Dual Positions | Dimensions     |                |                |                |                | Post Length <sup>2</sup> | Part Numbers |           |
|-----------------------|----------------|----------------|----------------|----------------|----------------|--------------------------|--------------|-----------|
|                       | A              | B              | C*             | D              | G <sup>1</sup> |                          | Plating A    | Plating B |
| 10                    | 1.260<br>32.00 | 1.150<br>29.21 | 1.100<br>27.94 | 0.900<br>22.96 | .100x<br>.150  | .090                     | 5650118-2    | —         |
| 15                    | 1.760<br>44.70 | 1.650<br>41.91 | 1.600<br>40.64 | 1.400<br>35.56 | .100x<br>.150  | .090                     | 5650118-1    | —         |
| 19                    | 2.160<br>54.86 | 2.750<br>69.85 | 2.700<br>68.58 | 1.800<br>45.72 | .100x<br>.150  | .090                     | —            | 5532600-6 |
| 25                    | 2.760<br>70.10 | 2.350<br>67.61 | 2.600<br>66.04 | 2.400<br>60.96 | .100x<br>.150  | .090                     | —            | 5532600-2 |
| 31                    | 3.360<br>85.34 | 3.250<br>82.55 | 3.200<br>81.28 | 3.000<br>76.20 | .100x<br>.150  | .090                     | —            | 5532600-4 |
| 32                    | 3.460<br>87.88 | 3.350<br>85.09 | 3.300<br>83.82 | 3.100<br>78.74 | .100x<br>.150  | .090                     | —            | 5532600-5 |

\*C dimension is card slot length.

<sup>1</sup> Metric equivalent for .100 x .150 and .100 x .200 are [2.54 x 3.81] and [2.54 x 5.08].

<sup>2</sup> Metric equivalent for post length is .090 = [2.27].

**Notes:** 1. Other connector sizes can be made available, consult TE.

2. High temperature IR reflow compatible connectors can be made available, consult TE.

**Note:** All part numbers are RoHS compliant.

## Voltage Regulation Module (VRM) Connectors

### Product Facts

- Available in latch versions for VRMs up to 3 oz.
- Available with metal clip for VRMs over 3 oz.
- VRM connectors to support a wide variety of power supply standards
- Solder tail, press-fit and right-angle versions to support specific customer needs
- Up to 5.5 Amps per contact in typical VRM applications
- New materials are 94 V-0 rated with max. operating temperature of 125°C — VRM 10.x Series
- Keying prevents plugging the wrong VRM into the connector

### Materials

**Housing** — PBT thermoplastic

**Contact** — High conductivity copper alloy

### Technical Documents

#### Product Specification

108-9039-1 & -2

#### Qualification Test Report

501-227-1 & -2



The new Voltage Regulation Module (VRM) family of connectors is designed to meet the needs of many existing and new power supply standards being developed.

They are dual row card edge style connectors that are well known in the computer market. Currently the connectors are designed to carry up to 150 amps of DC power — that's 300 amps total running through the connector. The connector is PCB mounted and there are versions available in press-fit or right-angle. The connectors have card retention either in the form of a latch

or a metal retention clip which is added after the VRM is in place.

### Industry Applications

The VRM connector is controlled by various power supply standards. Current ones are EPS-1U, AD2D-VID, AD2D, VRM 8.5, VRM 9.0, VRM 9.1, VRM 10.0 and VRM 10.1. Many applications with a need to transmit high power from board to board can benefit from this connector and additional customer specific applications are developing.

### VRM Selection Chart

|               | Part Numbers |           |           |                 |           |           |           |
|---------------|--------------|-----------|-----------|-----------------|-----------|-----------|-----------|
|               | VRM 9.1      | VRM 10.0  | VRM 10.1  | VRM 10.2 - 11.X | VRM 12.X  | VR 372    | TW        |
| Solder        | 6489165-1    | 6489930-2 | 6489930-2 | 1651826-1       | —         | —         | —         |
| Press-Fit     | 6489651-1    | —         | —         | 1766436-1       | —         | —         | —         |
| Surface-Mount | —            | —         | —         | 1766336-1       | 1766735-2 | 1761347-2 | 1761122-1 |

**Note:** All part numbers are RoHS compliant.

## Voltage Regulation Module (VRM) Connectors (Continued)



### VR 372 Power POD Connector for Intel MONTECITO VRMs

- Industry favored design for MONTECITO VR372 voltage regulator modules
- 130 Amps DC Output Power (260A Total)
- 350 compressive contacts carry a total of 200 Amps — resulting in less than 0.75 Amps per contact
- 22 additional signal contacts
- Rated to carry 120 Amps DC output power
- Maximum continuous operating temperature 125° C



### Mini CROWN EDGE Connectors for 1U/2U Pluggable VRMs

- Lowest profile available on the market (7 mm tall)
- High-performance CROWN BAND contacts that deliver 25A each
- High-density power designed for VRM 10.2 and beyond
- Multiple power and signal contacts allow flexible power PCB trace layouts
- SMT, pc tail and press-fit terminations
- Mating blade for board-stacking interconnection also available




### SEC-II with Latch for VRMs

- High Conductivity Contacts & High Strength Plastic Latches
- Vertical or Right-Angle
- Solder or Press-Fit (vertical only)
- Meets Intel VRM 8.5, 9.0, 9.1, 10.0 and 10.1 Standards
- 4.3 Amps/contact


MONTECITO is a trademark of Intel Corporation.

Other VRM Connectors such as “TW Power” and others are available.  
Please contact your local TE Sales Engineer for more information.


## VR 372 Power POD Connector — for Intel MONTECITO VRMs



MONTECITO Voltage Regulator Module



Socket Assembly with Cover  
Reference Dimensions



Socket Assembly with Cover

### Material

**Housing** — Liquid Crystal Polymer (LCP), 94V-0

### Colors

Plugs and Receptacles — Black  
Positive Locks — White


### Technical Documents

#### Product Specification

108-2170

#### Application Specification

114-13117



Socket Assembly with Alignment Plugs  
Alignment Plug Snap-On: Part Number 1761259-1

MONTECITO is a trademark of Intel Corporation.

**Note:** All part numbers are RoHS compliant.

## Mini CROWN EDGE Connector Configurations

### General Dimensions


Mini CROWN EDGE connectors are available in several form factors designed to meet diverse application requirements. For other available Mini CROWN EDGE Connector configurations, please check our website at <http://www.te.com> or consult TE.

#### Configuration: P2/S18/P10

Meets Intel VRM 10.2 specifications  
Power contacts x 12  
Signal contacts x 18  
Mating board thickness — 0.062"

#### Reference Part Numbers:

Solder tail, 4.5 mm (0.18")  
Part Number 1651826-1  
Solder tail, 3.0 mm (0.12")  
Part Number 1651929-1  
Surface-Mount  
Part Number 1766336-1  
Compliant Press-fit 3.8 mm (0.15")  
Part Number 1766436-1




#### Configuration: P2/S20/P16

Meets AMD K8 specifications  
Power contacts x 18  
Signal contacts x 20  
Mating board thickness — 0.093"

#### Reference Part Numbers:

Solder tail, 4.5 mm (0.18")  
Part Number 1766442-1  
Solder tail, 3.0 mm (0.12")  
Part Number 1651864-1  
Compliant Press-fit 3.8 mm (0.15")  
Part Number 1766443-1



**Note:** All part numbers are RoHS compliant.

## Mini CROWN EDGE Connector Configurations (Continued)

### Configuration: S14/P14/S16

Meets AMD K9 specifications

Power contacts x 14


Signal contacts x 30

Mating board thickness — 0.093"

### Reference Part Numbers:

Solder tail, 4.5 mm (0.18")

Part Number 1766308-1




| Configuration | Part Number | Overall Length     | Mating Board Thickness | Tail Length    | Type                |
|---------------|-------------|--------------------|------------------------|----------------|---------------------|
| P2/S24/P4     | 1926155-2   | 63.74 mm [2.509"]  | 1.57 mm [0.06"]        | N/A            | Surface-Mount       |
| P2/S24/P8     | 1926024-2   | 83.14 mm [3.273"]  | 1.57 mm [0.06"]        | N/A            | Surface-Mount       |
| P2/S18/P10    | 1651826-1   | 102.50 mm [4.040"] | 1.57 mm [0.06"]        | 4.5 mm [0.18"] | Solder Tail         |
|               | 1651929-1   |                    |                        | 3.0 mm [0.12"] | Solder Tail         |
|               | 1766336-1   |                    |                        | N/A            | Surface-Mount       |
|               | 1766436-1   |                    |                        | 3.8 mm [0.15"] | Compliant Press-Fit |
| P2/S24/P12    | 1766735-2   | 102.54 mm [4.037"] | 1.57 mm [0.06"]        | N/A            | Surface-Mount       |
| S14/P14/S16   | 1766308-1   | 129.60 mm [5.102"] | 2.36 mm [0.09"]        | 4.5 mm [0.18"] | Solder Tail         |
|               | 1766442-1   |                    |                        | 4.5 mm [0.18"] | Solder Tail         |
| P2/S20/P16    | 1651864-1   | 135.80 mm [5.346"] | 2.36 mm [0.09"]        | 3.0 mm [0.12"] | Solder Tail         |
|               | 1766443-1   |                    |                        | 3.8 mm [0.15"] | Surface-Mount       |

Application without latches and custom layouts are available. Please contact TE Customer Service or your local sales engineer.

### OTHER Applications

A mating blade that allows certain Mini CROWN EDGE Connector configurations to be used as a stacked board power interconnection device is also available.




Shown: P6

Socket Part Number 1766685-1 (Solder Tail)  
6651712-1 (SMT)

Blade Part Number 6651711-1 (Solder Tail)  
1926785-1 (SMT)

### Sample of Stacked Board Application

In this application, a Mini CROWN EDGE connector is used in close proximity to the MPU for delivery of high-current from a power board stacked over the processor board.




### Custom Layouts:

Shown above are some of the currently tooled Mini CROWN EDGE connector layouts. If none of them meets your application requirements, TE can design a custom layout based on your specifications.

**Note:** All part numbers are RoHS compliant.

## SEC-II Connectors with Latches for VRMs



### Material



**Housing** — Black glass-filled polyester

**Latch** — Black glass-filled polyester

**Contact** — Phosphor bronze, plated  
.000030 [0.00076] min. gold plating in  
contact area, .000100 [0.00254] min. tin  
on solder posts, all over .000050  
[0.00127] min. nickel

| Dimensions            |                        |                       |                        |                        | No. of<br>Dual<br>Positions | Mount<br>Type | Board<br>Retention<br>Feature | Molded<br>Key<br>Locations | Part<br>Number |
|-----------------------|------------------------|-----------------------|------------------------|------------------------|-----------------------------|---------------|-------------------------------|----------------------------|----------------|
| A                     | B                      | C                     | D                      | E                      |                             |               |                               |                            |                |
| <b>2.000</b><br>60.96 | <b>2.944</b><br>74.78  | <b>2.649</b><br>67.28 | <b>3.223</b><br>81.86  | <b>3.849</b><br>97.76  | 25                          | Press-Fit     | No                            | 17 & 18                    | 6489649-1      |
| <b>3.249</b><br>82.52 | <b>3.544</b><br>90.02  | <b>3.249</b><br>82.52 | <b>3.823</b><br>97.10  | <b>4.449</b><br>113.00 | 31                          | Solder        | Yes                           | 12 & 13                    | 6489165-6      |
| <b>3.400</b><br>86.36 | <b>3.944</b><br>100.18 | <b>3.649</b><br>92.68 | <b>4.130</b><br>104.90 | <b>4.850</b><br>123.17 | 35                          | Solder        | No                            | 23 & 24                    | 5145459-5      |

**Note:** See customer drawing for board retention locations.



**Note:** All part numbers are RoHS compliant.

## CROWN CLIP Series Sockets

### Product Facts

- Compact design
- High performance CROWN BAND contacts
- Currents to 350 Amps<sup>1</sup>
- Mates with solid or laminated blades
- Supports true hot-plug (current interruption)<sup>2</sup>
- Float-mount option reduces mating forces
- Meets UL (USR & CNR), and CSA safety requirements
- All CROWN CLIP products in this section are RoHS compliant


### Typical Applications

- Bus Bar based power distribution
- Power racks
- Rack mounted switching power supplies

#### Notes:

1 Dual CROWN CLIP socket using nickel plated mating tab, equivalent rating for other CROWN CLIP socket designs is 300A

2 Current interruption requires a gold plated, solid mating tab, and is not currently supported using a laminated mating tab



CROWN CLIP sockets are compact, high-current socket connectors for high current bus bar power distribution. Using ELCON high performance CROWN BAND technology, CROWN CLIP Sockets are available in single pole format to mate with a solid blade, handling up to 350 Amps, or in dual pole format to mate with laminated bus bar tabs for feed and return currents.

### Product Highlights

#### Hot-Plug Design

CROWN CLIP sockets also comply with safety regulatory requirements for current interruption under load. Compliance is achieved by a contact design that restricts the effects of arcing to areas that do not compromise the integrity of the connection. Hot-plugging requires a gold plated mating blade.

### Safety Agency Compliance


CROWN CLIP sockets comply with the UL1977 standard and CSA standard C22.2 No. 182.3-M1987. TE will work with customers to obtain application specific regulatory certifications if needed.



### Sample Application

CROWN CLIP sockets allow hot-plugging of rack-mounted switching power supplies.

Photo reproduced courtesy of Unipower Corporation.



### Mating Blades

Recommendations for customer supplied mating blades are:

**Insertion Length** — .650 [16.50] minimum, 1.00 [25.40] maximum

**Thickness** — .125 [3.18] or .118 [3.00]

**Material** — Copper, gold or nickel plated, with chamfered or rounded mating edge



## CROWN CLIP Series Sockets (Continued)

### Original CROWN CLIP Sockets

Part Number 1643906-1

#### Product Specifications

##### Materials

**Insulator** — Polyester, UL 94V-0

##### CROWN BAND Contacts

Beryllium copper alloy, selectively plated with gold (30 micro inches minimum), over nickel

**Crown Holder** — Copper alloy

##### Electrical

##### Current Rating, Steady State

Nickel plated solid tab: 300 Amp maximum; 200 Amp at 30°C maximum temperature rise

##### Current Rating, Hot-Plug

Gold plated solid tab: 200 Amp maximum, 42V; 100 Amp maximum, 48V

##### Mechanical

**Insertion Force** — 10.0 lbs (4.54 Kg) maximum


**Extraction Force** — 5.0 lbs (2.72 Kg) minimum

Single pole, float-mount socket design delivers 300 Amp current capability plus current interruption.

Float-mount design provides alignment for blind-mating of rack-mounted power supply units. Parallel cantilever design contacts include


ELCON CROWN BAND contact elements to ensure low voltage drop and heat generation, plus consistent insertion and extraction forces. Current interruption ratings are 100A at 48V and 200A at 42V, both using a gold plated, solid tab.

Customer Drawing available upon request.



### CROWN CLIP Sockets Electrical Performance

The graph at right shows the electrical performance of CROWN CLIP sockets in terms of temperature rise and voltage drop at currents from 150 Amps to 350 Amps. The set up used for the test had six CROWN CLIP socket samples mounted on a .25" x 1.75" x 6.0" bus bar, mating with 1.0" long by .125" thick nickel plated blades connected in series using 1/0 AWG wire.



**Note:** All part numbers are RoHS compliant.

## CROWN CLIP Series Sockets (Continued)

### CROWN CLIP II Sockets Part Number 1643903-1

#### Product Specifications

##### Materials

**Insulator** — Polyester, UL 94V-0

**Contact** — Copper alloy, selectively plated with gold (30 micro inches minimum), over nickel

##### Electrical

##### Current Rating, Steady State —

Nickel plated solid tab: 300 Amp maximum; 230 Amp at 30°C maximum temperature rise

**Current Rating, Hot-Plug** — Gold plated solid tab: 200 Amp maximum, 42V; 100 Amp maximum, 48V

##### Mechanical

**Insertion Force** — 20.0 lbs (9.08 Kg) typical

**Extraction Force** — 10.0 lbs (4.54 Kg) typical


Dual pole, float-mount socket design delivers 300 Amp current capability plus current interruption.

Float-mount design provides alignment for blind-mating of rack-mounted power supply units. The dual pole contact design allows mating to a

two pole laminated bus bar or double sided PCB tab, adding design flexibility by providing feed and return using a single socket.



Current interruption ratings are 100 A at 48 V and 200 A at 42 V, both using a gold plated, solid tab.

Customer Drawing available upon request.



### CROWN CLIP Sockets II Connector Electrical Performance

The graphs below show the electrical performance of CROWN CLIP II sockets in terms of temperature rise and voltage drop at currents from 150 Amps to 350 Amps. The set up used for the test had samples of six CROWN CLIP sockets mounted on a .25" x 1.75" x 6.0" bus bar, mating with 1.0" long by .125" thick nickel plated blades connected in series using 1/0 AWG wire.



**Note:** All part numbers are RoHS compliant.

## CROWN CLIP Series Sockets (Continued)

### Dual CROWN CLIP Sockets Part Number 1926671-1

#### Product Specifications

##### Materials

**Insulator** — Polyester, UL 94V-0

**CROWN BAND** — Beryllium copper alloy, selectively plated with gold (30 micro inches minimum), over nickel

**Crown Holder** — Copper alloy

##### Electrical

##### Current Rating, Steady State —

Nickel plated solid tab: 350 Amp maximum; 225 Amp at 30°C maximum temperature rise

##### Current Rating, Steady State —

Laminated bus bar tab: 130 Amp per side (260 A total) maximum; 75 Amp per side (150 A total) at 30°C maximum temperature rise

**Current Rating, Hot-Plug** — Gold plated solid tab: 200 Amp maximum, 5V; 100 Amp maximum, 60V

##### Mechanical

**Insertion Force** — 20.0 lbs (9.08 Kg) typical

**Extraction Force** — 13.0 lbs (5.9 Kg) typical



Dual pole, feed-through socket design delivers 350 Amp current capability plus current interruption. The dual pole contact design allows mating to a two pole laminated bus bar or double sided PCB tab, adding design flexibility by providing feed and return using a single socket. The feed-through design aspect allows insertion of mating

blade from both top and bottom of socket. The contacts include ELCON CROWN BAND contact elements to help provide low voltage drop and heat generation, plus consistent insertion and extraction forces. Current interruption ratings are 100A at 60V and 200A at 5V, both using a gold plated, solid tab.



Feed-Thru View

Customer Drawing available upon request.



Part Number 1926671-1  
4-hole CROWN CLIP  
300A

### Sample Application

ELCON Dual CROWN CLIP connectors mounted on a laminated power distribution bus bar in a large server.

**Note:** All part numbers are RoHS compliant.



Photos reproduced courtesy of Eldre Corporation

## CROWN CLIP Series Sockets (Continued)

### CROWN CLIP Junior Direct Power Connection for Bus Bars

#### Product Facts

- Current: 150 A
- Mating Force: 40 N max.
- Mating Bus Bar Thickness:  $3.0 \pm 0.1$  mm
- Bus Bar misalignment:  $\pm 1.0$  mm
- Hot Pluggable
- Contact Resistance: 0.2 milliohms
- Blind Mateable
- Anti Over Stress Feature
- Reduced Installation Costs
- Screw Fix or PC Tail Option


#### Technical Documents

##### Product Specification

108-19360

##### Application Specification

114-19128



#### Applications


- Core Network Energy Systems
- Cellular Base Stations
- PSU Power Distribution
- Servers, Storage & Network Routers
- Industrial

The CROWN CLIP Junior connector provides a space efficient connector in solder or screw-mount configurations ideal for power supply/distribution applications. Satisfying the demand for low insertion/extraction forces, it is hot plug capable for controlled and reliable separation of high power.

The connector mates to a 3.0 mm thick plated bus bar that provides a separable interface to ease assembly, inspection and trouble shooting. The selective

plated, high conductivity copper contacts offer low resistance, low millivolt drop for efficient power distribution. In blind mate applications this connector can handle adverse tolerances through the unique anti-stress feature allowing reliable mating to mis-aligned bus bars.

The CROWN CLIP Junior connector can be soldered direct to a PCB or screwed to a bus bar for a 150 A current capacity.



## CROWN CLIP Series Sockets (Continued)

### CROWN CLIP Junior Direct Power Connection for Bus Bars (Continued)

#### Part Number 1982995-1 Screw-Mount

##### Material and Finish

##### Bus Bar

**Conductor** — Copper, plated nickel or suitable alternative



**Temperature** — -40°C to +125°C

##### Connector

**Conductor** — High conductivity copper alloy, plated nickel or suitable alternative

**Insulator** — Thermoplastic, glass reinforced

**Temperature** — -40°C to +125°C



Part Number 1982995-1

#### Part Number 1982530-1 Solder Tail

##### Material and Finish

##### Bus Bar

**Conductor** — Copper, plated nickel or suitable alternative



**Temperature** — -40°C to +125°C

##### Connector

**Conductor** — High conductivity copper alloy, plated nickel or suitable alternative

**Insulator** — Thermoplastic, glass reinforced

**Temperature** — -40°C to +125°C




Part Number 1982530-1

**Note:** All part numbers are RoHS compliant.

## Pluggable Bus Bar Connectors

### Product Facts

- Separable bus bar connector
- 062 series for .062" [1.57] thick, 1/2" [12.7] minimum width bus bar
- 125 series for .125" [3.18] thick, 1" [25.4] minimum width bus bar
- Mounts direct to bus bar or terminated wire
- Low resistance, low millivolt drop
- High current rating: up to 500 amps for 125 series and 250 amps for 062 series
- Blind mateable (misalignment up to  $\pm .060$ " [1.52 mm] for both series)
- Anti-overstress feature
- Component Recognition Underwriter's Laboratories File No. E113407 



### Technical Documents

#### Applications Specifications

Provide instructions for assembling or applying product

114-2130 062 Series  
114-2111 125 Series

#### Product Specifications

108-1380 062 Series  
108-1101 125 Series

The TE pluggable bus bar connectors are suitable for computer, industrial control and modular power supply applications that demand low millivolt drop and reliable separation. This unique connector design replaces the nuts and bolts previously used to transfer power from the source to the bus bar and simplifies power distribution.


The pluggable bus bar connectors mate with .125" [3.18] or .062" [1.57] thick plated bus bars providing a separable connection that eases assembly, inspection and trouble shooting. The silver-plated, high conductivity copper alloy contacts offer a low resistance contact resulting in low millivolt drop providing efficient power distribution.

These blind mateable connectors feature a generous lead-in on the integral stainless steel guide plate. This permits mating if the bus bar is slightly misaligned and provides anti-overstress protection for the contact.


Pluggable bus bar connectors can be mounted directly to a bus bar or fed by a power supply cable as outlined in the Application Specifications.

## Pluggable Bus Bar Connectors (Continued)


### 125 Series



Style F



Style F2




Style F3

### Selection Data


| Series                                          | Style | Dimensions     |                |                | Part Number |
|-------------------------------------------------|-------|----------------|----------------|----------------|-------------|
|                                                 |       | "A" (Width)    | "B" (Height)   | "C" (Length)   |             |
| 125 Series<br>Fits Bus Bar<br>.125 [3.18] Thick | F *   | 2.290<br>58.17 | 1.141<br>28.99 | 3.200<br>81.28 | 104502-1    |
|                                                 | F2    | .850<br>21.59  | 1.122<br>28.5  | 3.294<br>83.67 | 104501-1    |
|                                                 | F3    | 1.250<br>31.75 | 1.141<br>28.99 | 1.993<br>50.61 | 213647-1    |

\* Bus Bar or Cable Power Feed

### 062 Series



Style F



Style F2

### Selection Data

| Series                                          | Style | Dimensions     |               |                | Part Number |
|-------------------------------------------------|-------|----------------|---------------|----------------|-------------|
|                                                 |       | "A" (Width)    | "B" (Height)  | "C" (Length)   |             |
| 062 Series<br>Fits Bus Bar<br>.062 [1.57] Thick | F     | 1.360<br>34.54 | .705<br>17.91 | 1.342<br>34.09 | 104729-1    |
|                                                 | F2    | .356<br>9.04   | .705<br>17.91 | 1.342<br>34.09 | 104742-2    |

**Note:** All part numbers are RoHS compliant.

## Pluggable Bus Bar Connectors (Continued)

### Materials

**Contact** — Copper alloy, plated Silver over nickel

**Guide Plate** — Stainless steel

### Specifications

#### Rated Current —

125 Series — Up to 500 amps at 30°C maximum t-rise \*

062 Series — Up to 250 amps at 30°C maximum t-rise \*

\*actual current rating is dependent on bus bar/wire and ambient conditions (see charts).

#### Contact Resistance —

125 Series — 10 milliohms maximum

062 Series — 50 milliohms maximum

#### Mating Force —

125 Series — 30 lb. [133.4 N] maximum

062 Series — 6 lb. [26.7 N] maximum

#### Unmating Force —


125 and 062 Series — 1 lb. [4.4 N] minimum

#### Durability —

125 Series — 100 cycle minimum

062 Series — 50 cycle minimum


### 125 Series



### Current Carrying Capability

| Test Configuration                                                      | Multiplication Factor |
|-------------------------------------------------------------------------|-----------------------|
| Contact on 4x12 [101.6 x 304.8] bar mated with 4x12 [101.6 x 304.8] bar | 1.00                  |
| Contact on 1x12 [25.4 x 304.8] bar mated with 1x23 [25.4 x 584.2] bar   | 0.40                  |
| Contact on AWG #00 mated with 1x12 [25.4 x 304.8] bar                   | 0.38                  |
| Contact on AWG #2 mated with 1x12 [25.4 x 304.8] bar                    | 0.32                  |

### 062 Series



### Current Carrying Capability

| Test Configuration                                                           | Multiplication Factor |
|------------------------------------------------------------------------------|-----------------------|
| Contact on 1.5 x 6 [38.1 x 304.8] Bar mated with 1.5 x 12 [38.1 x 304.8] Bar | 1.00                  |
| Contact on 1.0 x 6 [25.4 x 304.8] Bar mated with 1.0 x 12 [25.4 x 304.8] Bar | 0.81                  |
| Contact on 0.5 x 6 [12.7 x 304.8] Bar mated with 0.5 x 12 [12.7 x 304.8] Bar | 0.58                  |

## CROWN LINE Power Distribution System

### Product Facts

- Currents up to 250 A
- Up to 2 Meters in Length
- Pluggable Breakers
- VDE Finger proof
- Flammability UL 94 V-0
- Easily Configurable
- Adaptable
- Space Efficient
- Reduced Cable
- Reduced Installation Costs
- Polarized Connector Fitting
- Left and Right Handed

### Applications

- Power Distribution
- Core Network Equipment
- Cellular Base Stations
- Servers, Storage & Network Routers
- Industrial

### Technical Documents

#### Product Specification

108-19299

#### Application Specification

114-19108



The CROWN LINE system is designed for cost effective power distribution in equipment cabinets, telecoms base stations, computer servers, storage systems and industrial applications.

The unique finger proof design is designed to reduce assembly time, give repeatable low impedance electrical performance and reduce wiring errors with pre-determined input/output connections. System thermal characteristics are improved with the use of flat copper conductors allowing better airflow and


reducing current skin effects compared to conventional use of large AWG cables.

The CROWN LINE system consists of an extruded profile holding two solid copper conductors. Power is supplied to conductors from a regulated power source using flexible power cables and color coded RAPID LOCK right-angle sockets. The option to vary conductor thickness provides a flexible and adaptable design up to 2 meters in length with the ability to preform conductors to fit into awkward spaces.

Power input and output connectors use proven CROWN BAND and CROWN CLIP contact systems for reliable, low loss connections.

A connector with or without a circuit breaker, can be mated direct to the CROWN LINE System at any location along its length. The circuit breaker connector (CBC) accepts industry standard circuit breakers with tab terminals. A positive lock cable assembly connects from the CBC to deliver power where needed.

## CROWN LINE Power Distribution System (Continued)




**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System

### Product Facts

- Termination of flat cable requires no stripping, does not reduce cable cross section and provides a reliable, low resistance, gas tight interface
- Separable interfaces have positive locking, polarization and contact shrouding
- Right-angle and vertical headers on 2.54 [.100] centers, accommodate standard 1.02 [.040] PCB hole diameters
- Four cable self-aligning connector can pickup 2.03 [.080] misalignment off a common axis and measures 80 amps per cable (at 30°C temperature rise) depending upon the application
- Unique tap permits branching of trunk lines to serve multiple distribution points
- Assemblies are measured at 80–110 amps (with 30°C temperature rise) depending upon mounting interface
- Recognized under the Component Program of Underwriters Laboratories Inc.,  File No. E28476, No. E13288, and No. E53799
- Certified by Canadian Standards Association, File No. LR7189A-149 



Today's intelligent systems require more sophisticated power distribution solutions than ever before. Even the conductor geometry can make a significant impact on systems performance. Flat conductors offer desirable packaging advantages:

- Improved heat dissipation resulting in higher current capacity or reduced operating temperature.
- Low inductance, high capacitance power distribution.
- Reduced noise.
- Packaging flexibility.

The AMPOWER Wave Crimp System is the first power distribution system to offer a cost effective, totally mechanical termination method for insulated flat copper cable.

Assemblies provide:  
A fully shrouded and polarized separable interface with right-angle and vertical board-mount headers.

The first flat cable tap that allows branching from primary trunk lines, side tapping and discrete wire tapping.

Blindmate drawer connectors feature sequential mating and signal contacts.

AMPOWER flat cable assemblies provide a unique and effective means of distributing power from source to load in today's high speed, high density systems.

### Performance Data

**Voltage Rating** — 250 V AC RMS/DC.  
Single conductor cable assemblies are available with a 600 V AC RMS/DC rating.

**Dielectric Withstanding Voltage** —  
Power Contact: 1500 VAC  
Signal Contact: 1200 VAC

**Insulation Resistance** —  
5000 megohms initial  
1000 megohms final

**Temperature Range** —  
–55°C to +105°C

**Current Rating** — Refer to Product and/or Application Specifications.

### Typical Applications

- Mass Storage
- Switches
- Various Power Distribution Applications

### Technical Documents

#### Product Specifications


|          |                                     |
|----------|-------------------------------------|
| 108-1308 | Separable Interface                 |
| 108-1313 | Terminal Block & Stud Interface     |
| 108-1315 | Cable Tap Interface                 |
| 108-1319 | Drawer Connector                    |
| 108-1387 | FASTON Wire Tap                     |
| 108-1391 | Side Tap                            |
| 108-1323 | Cable Specification                 |
| 108-1410 | ACTION PIN Header                   |
| 108-1436 | Cable-to-Cable Drawer Connector     |
| 108-1479 | ACTION PIN Self-Aligning Connector  |
| 108-1403 | Self-Aligning Header and Receptacle |
| 108-1408 | Wave Crimp System (Cable-to-Cable)  |

**Application Specification**  
114-49005

## AMPOWER Wave Crimp System (Continued)

### Applications

The variety of AMPOWER wave crimp system interfaces available from TE make flat copper cable a versatile and innovative systems solution to power distribution.



## AMPOWER Wave Crimp System (Continued)

### Copper Cable Options

Copper cable used in AMPOWER wave crimp system assemblies are available in a variety of thicknesses and widths. The most common cable sizes are shown here.

| Conductor Thickness | Resistance |       |
|---------------------|------------|-------|
|                     | Single     | Dual  |
| 0.25<br>.010        | .912       | 2.030 |
| 0.51<br>.020        | .456       | .996  |

**Note:** The D.C. resistance of a 304.80 [12.00] length of conductor, when measured at 25°C and 10 amps, shall be < this figure (in milliohms).

|  |                  | Circular MILS | Approx AWG | Amps  |
|--|------------------|---------------|------------|-------|
|  |                  | Per Conductor |            |       |
|  | Single Conductor | 12,566        | 9          | 80    |
|  |                  |               |            |       |
|  | Dual Conductor   | 5,729         | 13         | 40/40 |
|  |                  |               |            |       |
|  | Single Conductor | 25,133        | 6          | 110   |
|  |                  |               |            |       |
|  | Dual Conductor   | 11,459        | 10         | 55/55 |
|  |                  |               |            |       |

## AMPOWER Wave Crimp System (Continued)

### Terminal Block and Stud Interface


#### Material and Finish

**Housing** — UL 94V-0 rated thermoplastic, black


**Contacts** — Copper alloy silver on termination and mating interface.

All over nickel base plate.

### Terminal Block Interface (14.27 [.562] Centerline)




### Terminal Block Interface (17.48 [.688] Centerline)



| Centerline Spacing | Part Numbers         |                     |
|--------------------|----------------------|---------------------|
|                    | Termination Assembly | Cover               |
| 14.24<br>.562      | —                    | 765228-1 Full Width |
| —                  | —                    | 765229-1 Half Width |
| 17.48<br>.688      | 765225-1             | 765228-1 Full Width |
| —                  | 765225-1             | 765229-1 Half Width |

### Stud Interface




| Stud Size | Hole Size "A" | Part Numbers |
|-----------|---------------|--------------|
|           |               | Cover (x2)   |
| 1/4"      | 6.76<br>.266  | 765228-1     |
| 5/16"     | 8.33<br>.328  | 765228-1     |

**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System (Continued)

### Cable-to-Cable Blindmate Receptacle Housing

#### Part Number 766569-1



\*Panel-mount (765530-1) or squeeze-to-release (765529-1) strain relief can be used on either 766569-1 or 765528-1 housing. At least one housing must have the squeeze-to-release strain relief; the panel-mount strain relief is optional on the mating housing.

### Separable Interface


#### Material and Finish

**Housing** — UL94V-0 rated thermoplastic, black


**Contact** — Copper alloy silver on termination and mating interface.

Tin-lead on header solder and ACTION PIN contact Tails. All over nickel base plate.



#### Plug Part Number 765191-1



**Mates with Part Numbers 765478, 765204, 765206**



#### Cable-to-Cable Receptacle Part Number 765478-1



**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System (Continued)

### Separable Interface — Headers

#### Material and Finish


**Housing** — UL94V-0 rated thermoplastic, black

**Contact** — Copper alloy silver on termination and mating interface.

Tin-lead on header solder and ACTION PIN contact Tails.

All over nickel base plate.



### Vertical Header



| "X"          | Tail Type       | Housing                 | Part Numbers          |
|--------------|-----------------|-------------------------|-----------------------|
| 3.15<br>.124 | Solder Tail     | Standard Temp,<br>Black | 765206-1              |
| 5.72<br>.225 | Solder Tail     | Standard Temp,<br>Black | 765206-4              |
| 4.19<br>.165 | Solder Tail     | High Temp,<br>Natural   | 765206-6              |
| 3.66<br>.144 | ACTION PIN Tail | Standard Temp,<br>Black | 765271-1 <sup>1</sup> |

<sup>1</sup>Uses insertion tool Part Number 765312-1

### Horizontal Header



Mates with Part Number 766569-1

| "X"          | Tail Type   | Housing                 | Part Numbers |
|--------------|-------------|-------------------------|--------------|
| 4.19<br>.165 | Solder Tail | Standard Temp,<br>Black | 765204-2     |
| 3.15<br>.124 | Solder Tail | High Temp,<br>Natural   | 765204-5     |
| 4.19<br>.165 | Solder Tail | High Temp,<br>Natural   | 765204-6     |

**Note:** Recommended mounting hardware, 2 #4-40 screws and nuts, or 2 eyelets TE Part Number 748572-2.

**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System (Continued)

### Half Width Plug Header

#### Material and Finish


**Housing**—UL94V-0 rated thermoplastic, black

**Contact**—Copper alloy silver on termination and mating interface.


Tin-lead on header solder and ACTION PIN contact Tails.

All over nickel base plate.


### Plug



### Horizontal Header



### Vertical Header



| Header Pin Pitch<br>"A" | "X"          | Header Assembly Part Numbers |            |          |
|-------------------------|--------------|------------------------------|------------|----------|
|                         |              | Tail Type                    | Horizontal | Vertical |
| 2.54<br>.100            | 3.15<br>.124 | Solder Tail                  | 765450-1   | 765449-1 |
|                         | 4.19<br>.165 | Solder Tail                  | 765450-2   | 765449-2 |
|                         | 5.72<br>.225 | Solder Tail                  | 765450-4   | 765449-4 |
|                         | 3.66<br>.144 | ACTION PIN Tail              | —          | 765451-1 |

<sup>1</sup>High temperature material.

**Notes:** Recommended mounting hardware, 2 #4-40, screws and nuts or, 2 eyelets TE Part Number 748572-2, customer supplied.

Allow 5.65 [.262] for mating cable to PCB.

**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System (Continued)

### Mid-Cable Terminations



#### Material and Finish

**Housing**—UL94V-0 rated thermoplastic, black



**Contact**—Silver plated copper alloy

All over nickel base plate.

#### Tap





#### .250 FASTON Tab Tap





1. FASTON Receptacles not included. Use Ultra-Pod fully insulated FASTON receptacles with 18 AWG to 12 AWG wire.

#### Side-Tap



#### Right-Angle Side-Tap



| Termination Type | Part Numbers         |               |              |
|------------------|----------------------|---------------|--------------|
|                  | Termination Assembly | Housing Cover | Housing Base |
| Flat Cable       | 765277-1             | 765278-1      | —            |
| .250 FASTON Tab  | 765276-1             | 765295-1      | 765296-1     |
| ¼" Stud          | —                    | 765278-1      | —            |
| ¼" Stud          | 765311-1             | 765278-1      | —            |

**Note:** Connectors on this page are capable of terminating up to two 0.51 [.020] thick cables.

**Note:** All part numbers are RoHS compliant.


## AMPOWER Wave Crimp System (Continued)

### Self-Aligning Headers


#### Material and Finish

**Housing** — UL94V-0 rated thermoplastic, black


**Contact** — Copper alloy silver on mating interface  
Tin-lead on solder tails.  
ALL over nickel base plate.  
Signal contact gold plate.



Typical For All Right-Angle Headers





Typical For All Vertical Headers





Typical For All Vertical Headers

### 2 Cable Header




Part Number 765608-1

### 4 Cable Header




Part Number 766510-1

### 4 Cable Header w/8 Signal Lines<sup>3, 4</sup>



### 4 Cable Header w/21 Signal Lines<sup>3, 4</sup>



| "X"          | Tail Type       | Part Numbers   |                |                                            |                                             |
|--------------|-----------------|----------------|----------------|--------------------------------------------|---------------------------------------------|
|              |                 | 2 Cable Header | 4 Cable Header | 4 Cable Header 8 Signal Lines <sup>3</sup> | 4 Cable Header 21 Signal Lines <sup>3</sup> |
| 3.10<br>.122 | Solder Tail     | 765527-1       | 765208-1       | 765249-1                                   | 765265-1                                    |
| 3.96<br>.156 | Solder Tail     | 765527-2       | 765208-2       | 765249-2                                   | 765265-2                                    |
| 3.66<br>.144 | ACTION PIN Tail | 765527-5       | 765208-5       | 765249-5                                   | 765265-5                                    |

<sup>1</sup>Mounting holes offset from centerline of part .76 [.030].

<sup>2</sup>High temperature material.

<sup>3</sup>Mates with MINI-TANDEM contact, TE Part Number 530553-x. Reference Catalog 82055.

<sup>4</sup>Signal pins not shown for clarity.

**Notes:** Tail length "x" is 4.20 (.165) for all right-angle headers.

Recommended mounting hardware, 2 #4-40, screws and nuts or, 2 eyelets TE Part Number 748572-2, customer supplied.

**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System (Continued)

### Self-Aligning Receptacles (Float-Mount)

#### Material and Finish



**Housing**—UL94V-0 rated thermoplastic, black

**Contact**—Copper alloy silver on termination and mating interface.


All over nickel base plate.

Signal contact see page 213.



### 2 Cable Receptacle





Typical For All Self-Aligning Receptacles





### 4 Cable Receptacle



### 4 Cable Receptacle w/8 Signal Lines



### 4 Cable Receptacle w/21 Signal Lines



|                 | Part Numbers             |                          |                          |                           |
|-----------------|--------------------------|--------------------------|--------------------------|---------------------------|
|                 | 2 Cable w/o Signal Lines | 4 Cable w/o Signal Lines | 4 Cable w/8 Signal Lines | 4 Cable w/21 Signal Lines |
| Housing         | 765528-1                 | 765247-1                 | 765224-1                 | 765261-1                  |
| Strain Relief   | 765530-1                 | 765250-1                 | 765238-1                 | 765238-1                  |
| Ground Contacts | 765209-1                 | 765209-1                 | 765209-1                 | 765209-1                  |
| Power Contacts  | 765209-2                 | 765209-2                 | 765209-2                 | 765209-2                  |

<sup>1</sup>Service loop suggested, allows for connector float.

<sup>2</sup>Recommended mounting hardware, TE Part Number 208211-4, 2 required per kit and 2 #6-32 nuts (customer supplied).

<sup>3</sup>Polarizing ribs, 2 places.

**Note:** Custom signal module assemblies available with power assemblies.

**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System (Continued)

### Self-Aligning Receptacles (Latching)

#### Material and Finish



**Housing**—UL94V-0 rated thermoplastic, black

**Contact**—Copper alloy silver on termination and mating interface.


All over nickel base plate.

Signal contact see page 213.



### 2 Cable Receptacle





Typical For All Self-Aligning Receptacles





### 4 Cable Receptacle



### 4 Cable Receptacle w/8 Signal Lines



### 4 Cable Receptacle w/21 Signal Lines



|                 | Part Numbers |          |                          |                           |
|-----------------|--------------|----------|--------------------------|---------------------------|
|                 | 2 Cable      | 4 Cable  | 4 Cable w/8 Signal Lines | 4 Cable w/21 Signal Lines |
| Housing         | 765528-1     | 765247-1 | 765224-1                 | 765261-1                  |
| Strain Relief   | 765529-1     | 765248-1 | 765251-1                 | 765251-1                  |
| Ground Contacts | 765209-1     | 765209-1 | 765209-1                 | 765209-1                  |
| Power Contacts  | 765209-2     | 765209-2 | 765209-2                 | 765209-2                  |

<sup>1</sup>Service loop suggested, allows for connector disconnection.

<sup>2</sup>Polarizing ribs, 2 places.

**Note:** Custom signal module assemblies available with power assemblies.

**Note:** All part numbers are RoHS compliant.

## AMPOWER Wave Crimp System (Continued)

### Cable-to-Cable Plug Connector w/8 Signal Lines

#### Material and Finish


**Housing** — UL94V-0 rated thermoplastic, black

**Contact** — Copper alloy silver plated

All over nickel base plate.

**Mates with** —

Self-Aligning receptacle, with 8 signal lines.



| Part Numbers<br>4 Cable w/8 Signal Lines |          |
|------------------------------------------|----------|
| Housing                                  | 765241-1 |
| Strain Relief                            | 765242-1 |

<sup>1</sup>Service loop suggested, when float-mount strain relief used (not shown).


<sup>2</sup>Polarizing slots, 2 places.

**Note:** Custom signal module assemblies available with power assemblies.

### Self-Aligning Right-Angle Connector w/48 Signal Lines


#### Product Facts

- Right-angle header for .06"-.12" PWB thickness
- 8 DC contacts
- 48 signal contacts
- 3 possible levels of sequencing
- Blindmate with .19" total mismatch alignment
- Polarization
- Mechanical PWB fasteners
- Drop-in-place custom assemblies



Floating Receptacle

Plug Header



#### Material and Finish

**Housing** — UL94V-0 rated thermoplastic, black

**Contact** — Copper alloy silver on mating interface


Tin-lead on header solder tails.

All over nickel base plate.

Signal contact gold plate.

<sup>1</sup>Polarizing rib, 2 places.

<sup>2</sup>Polarizing slot, 2 places.




**Note:** All part numbers are RoHS compliant.

## ISOLAMES Flexible Bus Bar

### Products Facts

- Wide range of cross section  
21 to 1,200 mm<sup>2</sup>
- Various laminated copper  
layer widths enable  
connection on all main  
apparatus and copper  
busbars
- High dielectric strength
- Flame retardant insulating  
material
- Limited temperature rises  
compared to cables or  
non-insulated copper bars
- High flexibility enables  
bending by hand
- Space saving: ISOLAMES  
bus bar bend radius is  
smaller than equivalent  
copper cable one
- Standard delivery length:  
2.00 m
- Also available on request:
  - Tin plated copper strips
  - Halogen-free insulation  
material
  - Longer bars  
(up to 4.00m)
- Approvals:  
LLOYD N° 93/30023  
CSA N° 099903  
UL105°C N° E113407



Bulk Cable

### Applications

- Low voltage power  
distribution: connections of  
switchboards, panel boards,  
transformers, busbars

ISOLAMES bus bar flexible insulated bars are made of high flexibility laminated copper layers, coated with black colored, self-extinguishable insulating PVC compound.




For more information,  
request Catalog 1242405

---

**Engineering Notes**

---



## Convenience Outlets

### Product Facts

- Panel-mount connector snaps in without the use of tools and holds securely without retention hardware
- Terminates solid copper wire using striplless insulation displacement terminals
- Terminates wire end or allows wire to feed thru
- Alternate connection uses FASTON 205 Series tabs (see Catalog 82004)
- Panel-mount connectors available in two sizes:  
14-12 AWG [2-3 mm<sup>2</sup>]  
18-16 AWG [0.8-1.4 mm<sup>2</sup>]
- Rated under the Component Recognition Program of Underwriters Laboratories Inc., File No. E146448, except for 213727-1




- Designed to UL Performance Std. 498
- Certified by Canadian Standards Association, File No. LR-7189A  
15 A, 12-14 AWG [3-2 mm<sup>2</sup>]  
13 A, 16 AWG [1.4 mm<sup>2</sup>]  
10 A, 18 AWG [0.8 mm<sup>2</sup>]



File No. LR-7189A  
(213727-1 only)



NRTL/C



The convenience outlets offer a fast and easy way to add an AC power outlet to a variety of electrical and/or electronic equipment. The connectors are available to snap-in to panels or to be mounted on a printed circuit board. The end applications vary from use in applications such as

multiple outlet strips and uninterruptible power supplies to industrial applications where a convenient AC power outlet is needed to be installed to the equipment in order to power external devices.

The panel-mount connectors use insulation displacement

technology to terminate the contacts to solid wires (from 18 AWG to 12 AWG). The printed circuit mounted connectors include both outlet jacks which are touch-safe and input jacks, which accept custom molded power cord receptacles.

AC Inputs

### Technical Documents

#### Instruction Sheets

408-6669 — 14-12 AWG [2-3 mm<sup>2</sup>]

IDC version

408-6698 — 18-16 AWG [0.8-1.4 mm<sup>2</sup>]

IDC version

For more information, request Catalog 82067.

Catalog 1773096  
Revised 4-12

www.te.com

Dimensions are shown for reference purposes only. Specifications subject to change.

Dimensions are in inches and millimeters unless otherwise specified.  
USA: +1 (800) 522-6752

Canada: +1 (905) 475-6222  
Mexico/C. Am.: +52 (0) 55-1106-0800  
Latin/S. Am.: +54 (0) 11-4733-2200  
Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666  
France: +33 (0) 1-3420-8686  
Netherlands: +31 (0) 73-6246-999  
China: +86 (0) 400-820-6015

## Convenience Outlets — Panel-Mount

### Current Rating —

14-12 AWG — 15A  
16 AWG — 13A  
18 AWG — 10A

### Material

**Housing** — thermoplastic

**Contact** — Copper alloy

### 205 Series FASTON Tab Part Number 62531-1\*


### Specifications

**Wire Range** — 18-14 AWG  
[0.8-2 mm<sup>2</sup>]



**Insulation Diameter** —  
.120-.150 [3.05-3.81]

**Material and Finish** —  
Brass, tin plated


| No. of<br>Contacts | Part Numbers                        |                                        | Panel<br>Plug | Housing<br>Color |
|--------------------|-------------------------------------|----------------------------------------|---------------|------------------|
|                    | 14-12 AWG<br>[2-3 mm <sup>2</sup> ] | 18-16 AWG<br>0.8-1.4 mm <sup>2</sup> ] |               |                  |
| 2 Plus<br>Ground   | 208979-2                            | 208697-2                               | —             | Black            |
|                    | 208979-4                            | 208697-4                               | —             | Almond           |
|                    | 1-208979-0                          | —                                      | —             | Platinum         |
|                    | 1-208979-1                          | —                                      | —             | Gray             |
|                    | 1-208979-2                          | —                                      | —             | Orange           |
|                    | 1-208979-4                          | —                                      | —             | Putty White      |
| 2 (No Ground)      | 213878-1                            | —                                      | —             | Black            |
| 0 (Blank)          | —                                   | —                                      | 796285-1      | Black            |



Part Number 213878-1



\*Reverse reeled for use in  
Model "K" Terminating Machine  
Part Number 585435-5 using  
Heavy Duty Miniature (HDM)  
Applicator Part Number 567069-2  
or in Leadmakers using HDM  
Applicator Part Number 567069-1



**Recommended Panel Cutout**  
Panel Thickness — 0.76-1.78 [0.030-.070]


### 205 Series FASTON Tab Part Number 62531-1\*\*

### Specifications

**Wire Range** — 18-14 AWG  
[0.8-2 mm<sup>2</sup>]

**Insulation Diameter** —  
.120-.150 [3.05-3.81]

**Material and Finish** —  
Brass, tin plated



\*\*Reeled for use in Model "G" and  
Model "K" Terminating Machine  
using Heavy Duty Miniature  
Applicator Part Number 567069-1

**Note:** All part numbers are RoHS compliant.

## Convenience Outlets — PCB-Mount


### 15 Amps

#### Material and Finish

**Housing** — Nylon

**Contacts** — Brass plated .000100 [0.00254] min. tin-lead for a minimum length of .195 [4.95] on end opposite mating face, over .000050 [0.00127] min. nickel on entire contact

| Part Numbers | Housing Color |
|--------------|---------------|
| 213598-1     | Gray          |
| 213598-2     | Black         |



Recommended Panel Cutout

Recommended Hole Pattern


### 20 Amps

#### Part Number 213727-1

#### Material and Finish

**Housing** — Nylon, Gray

**Contacts** — Brass plated .000100 [0.00254] min. tin-lead for a minimum length of .195 [4.95] on end opposite mating face, over .000050 [0.00127] min. nickel on entire contact



Recommended Panel Cutout

Recommended Hole Pattern

**Note:** All part numbers are RoHS compliant.


## Convenience Outlets

### Product Facts


- PCB Mountable
- 15A Output (outlet) Jacks
- 7A Input Jacks
- Connectors feature PCB retention features
- Horizontal or Vertical Mount
- Combination Jacks ideal for compact inverters — saves space vs. separate input/output connectors

For specific part numbers, contact TE


### AC Output Jack Panel-Mount with Solder Tabs Part Number 1775640-1




### AC Output Jack PCB-Mount Part Number 1775643-1



### AC Input Jack PCB-Mount Part Number 1775641-1



### Combination Input/Output Jack PCB-Mount Part Number 1775642-1 (UL94 V-1) Part Number 1-1775642-1 (UL94 V-0)



**Note:** All part numbers are RoHS compliant.

## CORCOM EMI/RFI Filter Products

### Product Facts

- Broad range of single and three phase power line filters, IEC power inlet filters and power entry modules
- Wide range of current ratings
  - Power line filters (up to 400 amps)
  - IEC power inlet filters (up to 20 amps)
  - Power entry modules (up to 15 amps)
- Various termination options including:
  - Standard receptacle (IEC)
  - Quick connect
  - Stud termination
  - DIN type terminal block
- Safety agency approvals
- Complimentary screen room testing
- Consultation services
- Custom solutions available
- Technical support line to answer customer inquiries
  - CORCOMTechHelp@te.com
  - 847-573-6597



As electronic equipment becomes more complex, the need for proper filtering increases. TE offers a complete line of CORCOM filter products for controlling EMI/RFI in practically any application. CORCOM brand products are recognized globally as effective solutions for bringing electrical/electronic products into compliance with safety agency standards for EMI emissions and protecting equipment from the effects of incoming electronic noise.

Power line filters, IEC power inlet filters and power entry modules are available in a wide range of current ratings, termination styles and filtering performance. In addition to the extensive selection of catalog products, custom solutions are also available. All products are RoHS compliant and have safety agency approvals. For more detailed information on CORCOM brand products, visit our CORCOM website at [www.corcom.com](http://www.corcom.com).

For more information, request Catalog 1654001.

Catalog 1773096  
Revised 4-12

[www.te.com](http://www.te.com)

Dimensions are shown for reference purposes only. Specifications subject to change.

Dimensions are in inches and millimeters unless otherwise specified.  
USA: +1 (800) 522-6752

Canada: +1 (905) 475-6222  
Mexico/C. Am.: +52 (0) 55-1106-0800  
Latin/S. Am.: +54 (0) 11-4733-2200  
Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666  
France: +33 (0) 1-3420-8686  
Netherlands: +31 (0) 73-6246-999  
China: +86 (0) 400-820-6015

## CORCOM DB Products

### Product Facts

- Compact connector for high-current DC applications
- Reliable performance in a compact assembly
- 60A DC current rating
- Polarized mating scheme
- Easy customer termination of power source
- Plug and receptacle available preterminated with standard wire lengths

### Standard and Specs

#### RFI Filter

- UL1283 Recognized
- CSA Certified C22.2 No.8/TUV Certified EN60950-1 (Filter)

#### Connector System

- UL1977 Recognized/CSA 182.3 Certified (through UL)
- TUV Certified EN61984

### Application Tooling

#### (Unterminated Contacts Only)

- Insertion/Extraction tool recommended:  
Part Number 1643922-1 (for DBR/DBP only)
- No hand tool available. Must crimp per TE's application spec 114-13206
- Crimp tool: M22520/23-01
- Indenter head: M22520/23-04
- Locator: M22520/23-11

### Accessories

- Connector system locking kit available. (Contact TE)



### Applications

- Telecom equipment
- Automotive equipment
- Data communications
- Power distribution panels

TE has expanded the CORCOM product line with a new power inlet filter. Available in four levels of filtering and an unfiltered version, these inlets are designed to accept up to 60 amps of current at 150 volts DC (UL/CSA) and 120 volts DC (TUV) in the filtered versions and 300 volts AC or DC in the unfiltered version. Filtered versions include the basic clean-up DBJ style through the higher performing DB style and DBX style


which provides up to 68dB insertion loss within the 150kHz to 30Mhz frequency range. The DBF style uses feedthrough capacitors for improved high-frequency performance. Power input terminals are TE's #4 AWG ELCON "drawer style" contacts. The filters' load sides come prewired with #6 AWG hi-flex stranded wire. The unfiltered plugs and receptacles are available with pre-terminated, hi-flex wire of various lengths.

**Note:** Tool required to disengage mated connector pair when using locking kit.


**WARNING:** This is not approved for hot swap or current interruption in DC applications. Doing so will result in irreparable damage to contact.

**Note:** All part numbers are RoHS compliant.


## CORCOM DB Products (Continued)




Part Number 60DBJ8




Part Number 60DB8 and 60DBF8




Part Number 60DBX8



Part Number 60DBRL



Part Number 60DBRL and 60DBJ8  
Panel Cutout



Part Number 60DBPL

### Product Offering

- Part Number 60DBR** — Connector housing, receptacle with retention clips
- Part Number 60DBP** — Connector housing, plug with retention clips
- Part Number 60DBPL1** — Mating connector plug terminated with 1 foot cable
- Part Number 60DBPL3** — Mating connector plug terminated with 3 foot cable
- Part Number 60DBPL9** — Mating connector plug terminated with 9 foot cable
- Part Number 60DBRL1** — Receptacle terminated with 1 foot cable
- Part Number 60DBRL3** — Receptacle terminated with 3 foot cable
- Part Number 60DBJ8** — Filter assembly with 6 inch wire leads
- Part Number 60DB8** — Filter assembly with conventional wire leaded capacitors
- Part Number 60DBF8** — Filter assembly with feedthrough capacitors
- Part Number 60DBX8** — High performance filter assembly

**WARNING:** This is not approved for hot swap or current interruption in DC applications. Doing so will result in irreparable damage to contact.

**Note:** All part numbers are RoHS compliant.

### Case Dimensions

| Part Number | Dimensions |        |                |                |                |                |
|-------------|------------|--------|----------------|----------------|----------------|----------------|
|             | A Max.     | B Max. | C ±.025 ±0.635 | D ±.025 ±0.635 | E ±.025 ±0.635 | F ±.025 ±0.635 |
| 60DBJ8      | 3.2        | 1.36   | 1.181          | 1.654          | 2.087          | 1.280          |
| 60DB8       | 81.28      | 34.54  | 29.997         | 42.012         | 53.01          | 32.51          |
| 60DBF8      | 4.06       | 3.20   | 1.45           | 2.50           | .875           | 2.077          |
| 60DBX       | 103.12     | 81.28  | 36.83          | 63.50          | 22.23          | 52.76          |
| 60DBJ8      | 6.06       | 3.50   | 1.45           | 2.876          | .875           | 2.265          |
| 60DBX       | 153.92     | 88.90  | 36.83          | 73.05          | 22.23          | 57.53          |
| 60DBRL      | 1.22*      | 1.181* | 2.087          | 1.654          | 1.023          | .591           |
| 60DBRL      | 30.98      | 29.99* | 53.009         | 42.011         | 25.984         | 15.01          |
| 60DBPL      | 1.695*     | .93*   | 2.08           | 1.654          | 1.195          | .465           |
| 60DBPL      | 43.05      | 23.62* | 52.832         | 42.011         | 30.353         | 11.81          |

\* ±.025 [±0.635]

## CORCOM DB Products (Continued)

### Electrical Schematics


#### Line-to-ground in 50 ohm circuit (Frequency MHz)

| Part Number | 0.01 | 0.015 | 0.5 | 1 | 5  | 10 | 20 | 30 | 50 | 100 |
|-------------|------|-------|-----|---|----|----|----|----|----|-----|
| 60DBJ8      | —    | —     | —   | 1 | 13 | 21 | 30 | 40 | 30 | 20  |


| Part Number | 0.05 | 0.1 | 0.15 | 0.5 | 1  | 3  | 5  | 10 | 20 | 30 |
|-------------|------|-----|------|-----|----|----|----|----|----|----|
| 60DB8       | 2    | 7   | 10   | 23  | 30 | 48 | 38 | 28 | 20 | 16 |
| 60DBF8      | 15   | 22  | 25   | 35  | 42 | 50 | 58 | 54 | 38 | 36 |
| 60DBX8      | —    | 10  | 16   | 40  | 48 | 54 | 60 | 51 | 40 | 36 |

#### Line-to-line in 50 ohm circuit (Frequency MHz)


| Part Number | 0.05 | 0.1 | 0.15 | 0.5 | 1  | 3  | 5  | 10 | 20 | 30 |
|-------------|------|-----|------|-----|----|----|----|----|----|----|
| 60DBJ8      | —    | 5   | 8    | 19  | 26 | 36 | 34 | 26 | 20 | 16 |
| 60DB8       | 20   | 26  | 29   | 43  | 53 | 30 | 30 | 24 | 20 | 18 |
| 60DBF8      | 9    | 15  | 18   | 30  | 34 | 40 | 44 | 44 | 48 | 52 |
| 60DBX8      | 31   | 30  | 30   | 70  | 70 | 54 | 50 | 60 | 54 | 50 |




Part Number 60DBJ8



Part Number 60DBX8



Part Number 60DB8



Part Number 60DBF8

AC Inputs

**WARNING:** This is not approved for hot swap or current interruption in DC applications. Doing so will result in irreparable damage to contact.

**Note:** All part numbers are RoHS compliant.

## Battery Interconnects

### Product Facts

- Total interface solution
- Current capacity — 7 Amps/ single contact at 30°C T-Rise
- Choice of right-angle or vertical mount headers with left, right or keyless polarization
- 5.0 mm pitch headers available for 7.2, 10.8, and 12.0 volt rechargeable batteries
- Receptacle connectors available with solder tails or weld tabs
- Consumer friendly mating/unmating of battery
- Produced under a Quality Management System certified to ISO 9001
- Blade Contacts for high durability
- Used Industry-wide for rechargeable battery I/O — in laptop computers
- Offered in a variety of key arrangements — for different voltage batteries
- 2.0 mm, 2.5 mm, 3.0 mm and 5.0 mm contact pitch batteries available
- MDI systems designed to mate at any angle
- Up to 7 Amps per contact
- Up to 2500 cycle durability
- Two pc tails per blade — for better current distribution

Since the introduction of the standard-size NiMH rechargeable battery to the computer and communications industries, TE has played a major role in the development and manufacture of reliable, high performance battery interconnect systems.

As the needs and applications of original equipment manufacturers have evolved, so have TE's battery interconnect systems. Today, we offer several types of connectors including:

- **Standard 5-position, 5.0 mm centerline assemblies**
- **Space efficient battery packs available at 2.0 mm, 2.5 mm, and 3.0 mm centerlines**

### ■ Multi-Directional Interconnection (MDI) systems


#### ■ Coin cell battery holders

All battery interconnect assembly housings are made of high temperature, UL 94V-0 rated thermoplastic. Single contacts are rated at 7 Amps with a 30° T-Rise, and have an operating temperature rating of -30° to +70°C. These assemblies can be customized for various applications and are available with many keying and mounting options.

TE answers the need in the portable equipment market for a high density, robust, and versatile interconnection system with the Multi-

Directional Interconnection (MDI) System. This durable system, designed to permit mating/unmating at any angle between 0° and 90°, features AMP-DURAGOLD plated contacts for up to 2500 cycles.

Our coin-cell battery holders are ideal for a variety of electronic equipment needing a compact low wattage (typically less than 2 Watts) battery source. These holders are available in both horizontal and vertical mount. Surface-mount and re-flow compatible options are also ready to meet the newer PCB assembly requirements.





## 2.0 mm Pitch Battery Assemblies

### 2.0 mm Pitch Plug Assemblies


#### Material and Finish

**Housing** — Black thermoplastic resin, UL 94V-0 rated


**Contacts** — High conductivity copper alloy, gold plating



Retention Leg  
(Part Number 1827654-1 Feature)



2 mm Plug Assembly with Nut Plates





2 mm Plug Assembly with Nut Plate (One Side)

### 2.0 mm Pitch Receptacle Assemblies


#### Material and Finish

**Housing** — Black thermoplastic resin, UL 94V-0 rated

**Contacts** — High conductivity copper alloy, gold plating



2.0 mm Receptacle Assembly,  
Surface-Mount



2.0 mm Receptacle Assembly,  
Through Hole Mount

**Note:** All part numbers are RoHS compliant. Tin-lead versions are available upon request.

## 2.0 mm Pitch Multi-Directional Interconnection (MDI) Systems


### 6-Position Multi-Directional Headers

#### Material and Finish


**Housing** — Black liquid crystal polymer, UL 94V-0 rated

**Contacts** — Brass, plated .000030 [0.00076] min. gold on mating area, .00015 [0.0038] min. tin on solder tail, all over .000050 [0.00127] min. nickel


| Mount Type      | Boardlocks | Part Number | Special Features   |
|-----------------|------------|-------------|--------------------|
| Through Hole    | With       | 5146877-1   | Sequenced contacts |
| Retention Tails | Without    | 5787252-1   |                    |
| Straight Solder |            | 5787531-1   | Sequenced contacts |




Part Number 5787531-1  
Straight Solder Tails



Part Number 5787252-1  
Below-the-Board Retention Tails



Part Number 5146877-1




### 6-Position Multi-Directional Receptacles

#### Material and Finish


**Housing** — Black liquid crystal polymer, UL 94V-0 rated

**Contacts** — Phosphor bronze, plated .000030 [0.00076] min. gold on mating area, .00015 [0.0038] min. tin on solder tail, all over .000050 [0.00127] min. nickel


| Mount Type    | Boardlocks | Part Number |
|---------------|------------|-------------|
| Surface-Mount | With       | 5787090-1   |
| Through Hole  | Without    | 5787253-1   |
|               |            | 5787526-1   |




Part Number 5787253-1  
Through Hole Mount



Part Number 5787526-1  
Through Hole Mount



Part Number 5787090-1  
Surface-Mount with Boardlocks



**Note:** All part numbers are RoHS compliant.

## 2.5 mm Pitch Battery Assemblies


### 2.5 mm Pitch Plug Assemblies

#### Material and Finish


**Housing** — Black thermoplastic resin, UL 94V-0 rated

**Contacts** — High conductivity copper alloy, gold plating

| No. of Positions | Mount Type   | Mount Angle          | Part Number | Special Features      |
|------------------|--------------|----------------------|-------------|-----------------------|
| 4                | Through Hole | Right-Angle Offset   | 6123987-1   | M2 Nut Plate          |
|                  | Through Hole | Right-Angle Offset   | 6123978-1   |                       |
| 5                | Through Hole | Right-Angle On Board | 6376042-2   | M2 Nut Plate          |
|                  | Through Hole | Right-Angle On Board | 9-1612503-1 |                       |
|                  | Through Hole | Right-Angle Offset   | 6318792-1   |                       |
|                  | Through Hole | Vertical             | 6473451-1   |                       |
| 6                | Through Hole | Right-Angle Offset   | 6318977-3   | M2 Nut Plate          |
| 7                | Through Hole | Right-Angle On Board | 6318573-4   |                       |
|                  | Through Hole | Right-Angle On Board | 1747602-1   | M2 Nut Plate          |
| 8                | Through Hole | Right-Angle On Board | 1717445-2   |                       |
| 10               | Through Hole | Right-Angle On Board | 6123738-7   |                       |
|                  | Through Hole | Right-Angle On Board | 1123822-7   | M2 Nut Plate          |
|                  | Through Hole | Right-Angle On Board | 1123684-7   | One Side M2 Nut Plate |
|                  | Through Hole | Right-Angle Offset   | 6473539-7   | M2 Nut Plate          |



Part Number 6376042-2  
Right-Angle On Board Assembly  
with Nut Plate



Part Number 6123978-1  
Right-Angle Offset Assembly


### 2.5 mm Pitch Receptacle Assemblies

#### Material and Finish


**Housing** — Black thermoplastic resin, UL 94V-0 rated

**Contacts** — High conductivity copper alloy, gold plating

| No. of Positions | Mount Type    | Mount Angle | Part Number |
|------------------|---------------|-------------|-------------|
| 4                | Through Hole  | Right-Angle | 6123981-1   |
| 5                | Through Hole  | Right-Angle | 6318430-2   |
|                  | Surface-Mount | Right-Angle | 1612504-1   |
| 6                | Surface-Mount | Vertical    | 1123688-3   |
| 7                | Surface-Mount | Vertical    | 1318574-4   |
| 8                | Through Hole  | Vertical    | 1717478-1   |
|                  | Through Hole  | Right-Angle | 1717620-1   |
| 10               | Surface-Mount | Vertical    | 1123688-7   |
|                  | Through Hole  | Vertical    | 1674231-1   |



Part Number 6318430-2  
Right-Angle Through Hole Mount




Part Number 1318574-4  
Vertical Surface-Mount

**Note:** All part numbers are RoHS compliant.

## 5.0 mm Pitch Battery Plug Assemblies

### 5.0 mm Pitch Right-Hand Key Plug Assemblies




#### Material and Finish

**Housing** — Polyphthalamide, UL 94V-0 rated, black


**Contacts** — Brass, plated .000100 [0.00254] min. tin on solder tail over .000075 [0.00190] min. nickel overall

| Voltage | Mount Type       | Mount Angle | Part Number |
|---------|------------------|-------------|-------------|
| 12.0    | Retentive Solder | Right-Angle | 5787424-1   |
|         | Straight Solder  | Right-Angle | 5787422-1   |
|         | Straight Solder  | Vertical    | 5787430-1   |
| 10.8    | Retentive Solder | Vertical    | 5787421-1   |
|         | Straight Solder  | Vertical    | 5787419-1   |
| 7.2     | Retentive Solder | Right-Angle | 5787141-1   |
|         | Straight Solder  | Vertical    | 5787334-1   |
|         | Straight Solder  | Right-Angle | 5787142-1   |





Part Number 5787421-1

Vertical Assembly with Retentive Tails




Part Number 5787142-1

Right-Angle Assembly with Straight Tails



### 5.0 mm Pitch Left-Hand Key Plug Assemblies




#### Material and Finish

**Housing** — Polyphthalamide, UL 94V-0 rated, black


**Contacts** — Brass, plated .000100 [0.00254] min. tin on solder tail over .000075 [0.00190] min. nickel overall

| Voltage | Mount Type       | Mount Angle | Part Number | Special Features |
|---------|------------------|-------------|-------------|------------------|
| 12.0    | Straight Solder  | Right-Angle | 5787428-1   | Mounting Holes   |
| 10.8    | Retentive Solder | Right-Angle | 5787418-1   |                  |
|         | Straight Solder  | Right-Angle | 5787246-1   |                  |




Part Number 5787428-1

Right-Angle Assembly with Mounting Holes



### 5.0 mm Pitch Keyless Plug Assemblies




#### Material and Finish


**Housing** — Polyphthalamide, UL 94V-0 rated, black

**Contacts** — Brass, plated .000100 [0.00254] min. tin on solder tail over .000075 [0.00190] min. nickel overall

| Voltage | Mount Type       | Mount Angle | Part Number | Special Features   |
|---------|------------------|-------------|-------------|--------------------|
| N/A     | Straight Solder  | Right-Angle | 5787441-1   |                    |
|         | Retentive Solder | Right-Angle | 5787443-1   |                    |
|         | Straight Solder  | Right-Angle | 5796078-1   | Sequenced Contacts |
|         | Retentive Solder | Vertical    | 5787446-1   |                    |
|         | Straight Solder  | Vertical    | 5787444-1   |                    |



Part Number 5796078-1  
Right-Angle Assembly with  
Straight Tails & Sequenced Contacts



Note: All part numbers are RoHS compliant.

## 5.0 mm Pitch Battery Receptacle Assemblies

### 5.0 mm Pitch Right-Hand Key Receptacle Assemblies


#### Material and Finish

**Housing** — Black polycarbonate, UL 94V-0 rated

**Contacts** — Copper alloy, plated .000075 [0.00190] min. nickel

| Voltage | Mount Type    | Part Number |
|---------|---------------|-------------|
| 12.0    | Surface-Mount | 787439-1    |
|         | Weld Tabs     | 787615-1    |
| 10.8    | Weld Tabs     | 787614-1    |

**Note:** All receptacles include a dovetail locator.



**Part Number 787439-1**  
Surface-Mount Receptacle

### 5.0 mm Pitch Left-Hand Key Receptacle Assemblies


#### Material and Finish

**Housing** — Black polycarbonate, UL 94V-0 rated

**Contacts** — Copper alloy, plated .000075 [0.00190] min. nickel

| Voltage | Mount Type    | Part Number |
|---------|---------------|-------------|
| 7.2     | Solder Tail   | 5787590-1   |
|         | Surface-Mount | 787328-1    |
|         | Weld Tab      | 787613-1    |

**Note:** All receptacles include a dovetail locator.



**Part Number 787613-1**  
Weld Tab Receptacle

### 5.0 mm Pitch Keyless Receptacle Assemblies


#### Material and Finish

**Housing** — Black polycarbonate, UL 94V-0 rated

**Contacts** — Copper alloy, plated .000075 [0.00190] min. nickel

| Voltage | Mount Type    | Part Number |
|---------|---------------|-------------|
| N/A     | Solder Tail   | 5787802-1   |
|         | Surface-Mount | 146845-1    |

**Note:** All receptacles include a dovetail locator.



**Part Number 5787802-1**  
Solder Tail Receptacle


**Note:** All part numbers are RoHS compliant.

## Coin Cell Battery Holders


### Horizontal Mount Battery Holders

#### Material and Finish


**Housing** — Black thermoplastic resin, UL 94V-0 rated



| Mount Type    | Part Number | Special Features                  |
|---------------|-------------|-----------------------------------|
| Surface-Mount | 796136-1    |                                   |
| Through Hole  | 1734178-1   | Flexible housing for easy removal |
|               | 120591-1    |                                   |



Part Number 120591-1  
Through Hole Mount




Part Number 796136-1  
Surface-Mount


### Vertical Mount Battery Holders

#### Material and Finish


**Housing** — Black thermoplastic resin, UL 94V-0 rated



| Mount Type   | Part Number | Special Features |
|--------------|-------------|------------------|
| Through Hole | 6339488-1   |                  |
|              | 1775485-1   | Low Profile      |



Part Number 6339488-1




Part Number 1775485-1  
Low Profile

**Note:** All part numbers are RoHS compliant.

## DC Power Jacks

### Product Facts


- Low Profile Design
- Accepts industry standard DC power plugs
- Available with:
  - Solder tabs
  - Through-hole solder tails
  - SMT leads
- Available to accept these plug sizes:
  - 0.65 mm
  - 1.0 mm
  - 1.3 mm
  - 1.47 mm
  - 1.87 mm
  - 2.0 mm
  - 2.35 mm
  - 2.5 mm
- Ideal for portable electric devices



### Surface-Mount Power Jacks

Pin Diameters — 0.65 mm and 1.3 mm


Part Number 1775638-1



Bottom View

|                        |         |
|------------------------|---------|
| CENTER PIN DIAMETER ØA | 1.3 DIA |
| SCHEMATIC              |         |

Part Number 1775639-1




Bottom View

|                        |          |
|------------------------|----------|
| CENTER PIN DIAMETER ØA | 0.65 DIA |
| SCHEMATIC              |          |

### Vertical DC Jack

Part Number 1470390-1




**Note:** All part numbers are RoHS compliant.

## DC Power Jacks (Continued)

### Right-Angle DC Jacks Miniature Jacks

For specific part numbers,  
contact TE

| Center Dia. | Tail Length | Part Number |
|-------------|-------------|-------------|
| 1.30        | 3.00        | 1775529-1   |
|             | 1.50        | 1775529-2   |
| 1.00        | 3.00        | 1-1775529-1 |
|             | 1.50        | 1-1775529-2 |




Bottom View



| CENTER PIN DIAMETER (A) | 1.3 DIA | 1.0 DIA | 1.3 DIA |
|-------------------------|---------|---------|---------|
| B LENGTH                | 3.0mm   | 1.5mm   | 3.0mm   |
| SCHEMATIC               |         |         |         |

### Shielded Jack


| Dia. A | N.W. (q) | Part Number |
|--------|----------|-------------|
| 2.0    | 1.8      | 1734894-1   |
| 2.5    | 2.0      | 1734894-2   |



PCB Layout  
(Tolerance  $\pm 0.05$ )

### Standard Jacks

| Center Diameter | Part Number |
|-----------------|-------------|
| 2.00            | 1775069-1   |
| 2.35            | 1775069-2   |
| 2.50            | 1775069-3   |



Bottom View




| CENTER PIN DIAMETER (A) | 1.35 DIA | 1.47 DIA | 1.7 DIA | 1.87 DIA | 2.0 DIA | 2.2 DIA | 2.35 DIA | 2.5 DIA |
|-------------------------|----------|----------|---------|----------|---------|---------|----------|---------|
| SCHEMATIC               |          |          |         |          |         |         |          |         |

### Standard Jack — Recessed Flange

For specific part numbers,  
contact TE

| Center Diameter | Part Number |
|-----------------|-------------|
| 1.47            | 1775637-1   |
| 1.87            | 1775637-2   |
| 2.00            | 1775637-3   |
| 2.35            | 1775637-4   |
| 2.45            | 1775637-5   |



Bottom View

**Note:** All part numbers are RoHS compliant.

## Custom Cable Assemblies



TE specializes in custom power cable assemblies for most applications. TE provides solutions using a wide array of connector styles and cable types, regardless of manufacturer.

TE currently supplies the major Original Equipment Manufacturers (OEM's),

within the market, with simple double-ended MATE-N-LOK assemblies, complex power harnesses, and even rugged mechanical line cords, to name a few.

If power distribution through cabling is what you need, TE engineering capabilities,

combined with global manufacturing and logistics are just the right combination to help you succeed. It is time you 'hooked up' with the leader in the power area, TE.

## Application Tooling



TE has long been recognized as a leader in providing the tools for wire harness and printed circuit manufacturing. Our products are designed to meet and anticipate our customers' ever-changing requirements and built to the highest quality standards, for longest, most productive performance lifetimes.

With a full range of tooling from hand tools to high volume, fully automated systems, TE is able to meet manufacturing demands worldwide. It's an ability that comes from our experience with manufacturers large and small, giving us a unique view of the trends and challenges in wire harness and PCB manufacturing. It all derives from our commitment to your manufacturing challenges, giving you the advantage in your marketplace.

**For technical support: Contact Tooling Assistance Center (TAC)  
at 800-722-1111 for applicator part numbers.**

**For sales support: Call 888-777-5917 or email:  
toolingsales@te.com**

## Application Tooling — Hand Tools

### CERTI-CRIMP Hand Tools

- Designed and manufactured to exacting specifications using the highest quality materials
- Ratchet control provides complete crimping cycle
- For most military, UL and CSA applications
- Calibrated; recalibration recommended every 6 months or 5,000 cycles
- Many SAHT and DAHT crimping heads, and many die sets, can be adapted for use with the Standard Die Envelope (SDE) System



### Standard Die Envelope (SDE) System

The SDE System is a new approach to crimp die interchangeability. This flexibility in die options provides the capability to crimp a large variety of product types and wire sizes while using multiple application platforms from manual hand tools and electrical bench terminators to a portable battery-powered unit.



### PRO-CRIMPER III Hand Tool

- Exceptional quality and performance at an affordable price
- Compatible with all SDE dies, with enhanced ergonomics, providing a thinner, more comfortable handle profile
- Precision stamping techniques permit close tolerance controls on critical parts



### Battery Crimp Tool Kit, Part Number 1725837-1

- Compatible with all SDE dies
- Terminates wire range of 6-.03 mm<sup>2</sup> (10-22 AWG)
- Portable, 1.57kg (3.46lb) w/battery
- Kit includes tool, 2 batteries & charger (approx. 100 crimps per charge)



### SDE Electric Terminator, Part Number 1490076-2

- Compatible with all SDE dies
- Terminates wire range of 6-10 AWG
- Small footprint — 15.5 x 10 x 8" (390 x 260 x 220 mm); 29 lb (13kg)
- Foot actuated; Jog cycle; includes crimp adjustment



### 6-26 Pneumatic Tool System

- Pneumatic powered; providing the ultimate in wire range flexibility
- Includes a jaw adapter compatible with SDE dies
- Available in hand or foot actuated versions, with ratchet control
- Also available in a number of integral die options that terminate up to #6 SOLISTRAND terminals



For technical support: Contact the Tooling Assistance Center (TAC) at 800-722-1111 for applicator part numbers.

For sales support: Call 888-777-5917 or email: [toolsales@te.com](mailto:toolsales@te.com)

Note: Part Numbers are RoHS compliant.

## Application Tooling — Semi-Automatic Machines

### AMP 3K/40 and 5K/40 Terminators

- 3,000 lb [1361 kg] max. crimp force (AMP-3K/40);  
5,000 lb [2268 kg] max. crimp force (AMP-5K/40)
- Tool-less removal of applicators and guards for quick and simple maintenance and product change over
- Jog capability
- Quiet and fast operation — 80/76 dBA and cycle time less than 0.400 seconds
- Accepts Heavy Duty Mini (HDM) style applicators
- Optional equipment includes tool-less precision crimp height adjust, batch counter, CQM capability and work light
- Universal electrical input — 100-240 VAC, 50/60 Hz



### Heavy-Duty Mini (HDM) Applicator

This is the standard TE applicator, accommodating most requirements for crimping TE and other terminals.


- Produces consistent, high quality terminations
- Fits TE terminator-style presses
- Hardware adjustment — English units
- Stroke 1.18 in. [30 mm] or 1.57 in. [40 mm]
- Fine adjust, pneumatic feed available
- Over 5,000 different designs to accommodate full range of over 13,000 terminals
- Custom designs available for nearly any terminal



### BMEP 3T / 5T Servo Electric Press

Benchtop electric press for the application of compliant pin products

- Servo electric press
- PCB capacity of 18" x 24" [460 mm x 610 mm]
- Press force capacity of 3 or 5 tons [27 or 44 kN]
- Ability to monitor and control force, distance and speed for every press cycle
- Full SPC data of every component pressed for quality assurance and traceability
- Database driven software for simple programming and automatic setup
- Small foot-print for low to medium volume product levels






For technical support: Contact the Tooling Assistance Center (TAC)  
at 800-722-1111 for applicator part numbers.

For sales support: Call 888-777-5917 or email:  
toolsales@te.com

Note: Part Numbers are RoHS compliant.

## Wire Calculations and Instructions

### How to Compute Circular Mil Area of Various Wire Shapes

|                                                                                                                                        | U.S. Customary Dimensions                                                                                                                                                                                                                                    | Metric Dimensions                                                                                                                                                                                                                                                             |
|----------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Stranded Wire AWG</b><br> <p>Number of Strands</p> | <p>Use Chart 1. Read circular mil area directly from table.</p> <p><b>Alternate Method</b><br/>Multiply the diameter of one strand (in mils) by itself, and then multiply the result by the total number of strands.<br/><math>CMA = D^2 \times N</math></p> | <p>Use Chart 1. Read circular mil area directly from table.</p> <p><b>Alternate Method</b><br/>Multiply the diameter of one strand in millimeters by itself, and then by the number of strands, and then by 1500.003.<br/><math>CMA = D^2 \times N \times 1550.003</math></p> |
| <b>Round Solid Wire AWG</b><br>                       | <p>Use chart 1 or 2. Read circular mil area directly from table.</p> <p><b>Alternate Method</b><br/>Multiply the diameter in mils by itself.<br/><math>CMA = D^2</math></p>                                                                                  | <p>Use chart 1 or 2. Read circular mil area directly from table.</p> <p><b>Alternate Method</b><br/>Multiply the diameter in millimeters by itself by 1550.003.<br/><math>CMA = D^2 \times 1550.003</math></p>                                                                |
| <b>Square or Rectangular Wire</b><br>                 | <p>Multiply the width of the wire cross section in mils by the thickness of the wire cross section in mils by 1.2732 and subtract the radius factor included below.<br/><math>CMA = W \times T \times 1.2732 - \text{radius factor}</math></p>               | <p>Multiply the width of the wire cross section in millimeters by the thickness in millimeters by 1973.525 and subtract the radius factor included below.<br/><math>CMA = W \times T \times 1973.525 - \text{radius factor}</math></p>                                        |

#### Conversion Table

| To Convert From | To              | Multiply By  |
|-----------------|-----------------|--------------|
| CMA             | mm <sup>2</sup> | 0.0005067075 |
| CMA             | in <sup>2</sup> | 0.0000007854 |
| mm <sup>2</sup> | in <sup>2</sup> | 0.0015500030 |
| mm <sup>2</sup> | CMA             | 1973.525     |

#### Radius Factor, U.S. Customary

| Radius (in.) | Radius Factor To Subtract (CMA) |
|--------------|---------------------------------|
| .010         | 110                             |
| .012         | 158                             |
| .016         | 280                             |
| .020         | 438                             |
| .026         | 740                             |
| .032         | 1121                            |
| .040         | 1752                            |
| .063         | 4346                            |
| .940         | 9675                            |

#### Radius Factor, Metric

| Radius (mm) | Radius Factor To Subtract (CMA) |
|-------------|---------------------------------|
| 0.25        | 106                             |
| 0.30        | 153                             |
| 0.35        | 208                             |
| 0.40        | 272                             |
| 0.50        | 424                             |
| 0.60        | 611                             |
| 0.80        | 1086                            |
| 1.20        | 2444                            |
| 0.94        | 9675                            |

## How to Compute Circular Mil Area of Various Wire Shapes (Continued)

### Circular Mil Area (CMA) / Nominal Wire Sizes

| CMA    | Normal Wire Size |                 | No. | Strands  |       | Approximate Conductor Diameter |        |
|--------|------------------|-----------------|-----|----------|-------|--------------------------------|--------|
|        | AWG              | mm <sup>2</sup> |     | Diameter |       | Inch                           | mm     |
|        |                  |                 |     | Inch     | mm    |                                |        |
| 4.0    | 44               | 0.002           | 1   | .00195   | 0.050 | .002                           | 0.051  |
| 16.0   | 38               | 0.008           | 1   | .0040    | 0.102 | .004                           | 0.102  |
| 64.0   | 32               | 0.032           | 1   | .0080    | 0.203 | .008                           | 0.203  |
| 175.0  | 28               | 0.089           | 7   | .0050    | 0.127 | .015                           | 0.381  |
| 388    | 24               | 0.197           | 1   | .0197    | 0.500 | .020                           | 0.508  |
| 397    | 24               | 0.201           | 10  | .0063    | 0.160 | .023                           | 0.584  |
| 400    | 24               | 0.203           | 16  | .0050    | 0.127 | .023                           | 0.584  |
| 400    | 24               | 0.203           | 4   | .0100    | 0.254 | .023                           | 0.584  |
| 403    | 24               | 0.204           | 8   | .0071    | 0.180 | .023                           | 0.584  |
| 634    | 22               | 0.321           | 8   | .0089    | 0.226 | .029                           | 0.737  |
| 635    | 22               | 0.322           | 16  | .0063    | 0.160 | .029                           | 0.737  |
| 640    | 22               | 0.324           | 10  | .0080    | 0.203 | .029                           | 0.737  |
| 640    | 22               | 0.324           | 1   | .0253    | 0.643 | .025                           | 0.635  |
| 992    | 20               | 0.503           | 1   | .0315    | 0.800 | .032                           | 0.813  |
| 1000   | 20               | 0.507           | 10  | .0100    | 0.254 | .038                           | 0.965  |
| 1008   | 20               | 0.511           | 20  | .0071    | 0.180 | .039                           | 0.991  |
| 1024   | 20               | 0.519           | 16  | .0080    | 0.203 | .039                           | 0.991  |
| 1600   | 18               | 0.811           | 16  | .0100    | 0.254 | .049                           | 1.245  |
| 1608   | 18               | 0.815           | 19  | .0092    | 0.234 | .049                           | 1.245  |
| 1617   | 18               | 0.819           | 7   | .0152    | 0.386 | .042                           | 1.067  |
| 1624   | 18               | 0.823           | 1   | .0403    | 1.024 | .040                           | 1.016  |
| 2521   | 16               | 1.277           | 50  | .0071    | 0.180 | .059                           | 1.499  |
| 2540   | 16               | 1.287           | 16  | .0126    | 0.320 | .059                           | 1.499  |
| 2581   | 16               | 1.308           | 1   | .0508    | 1.290 | .051                           | 1.295  |
| 2800   | 16               | 1.419           | 7   | .0200    | 0.508 | .061                           | 1.549  |
| 3831   | 14               | 1.941           | 19  | .0142    | 0.361 | .076                           | 1.930  |
| 4099   | 14               | 2.077           | 7   | .0242    | 0.615 | .076                           | 1.930  |
| 4109   | 14               | 2.082           | 1   | .0641    | 1.628 | .064                           | 1.626  |
| 6503   | 12               | 3.295           | 19  | .0185    | 0.470 | .092                           | 2.337  |
| 6512   | 12               | 3.300           | 7   | .0305    | 0.775 | .086                           | 2.184  |
| 6529   | 12               | 3.308           | 1   | .0808    | 2.052 | .081                           | 2.057  |
| 9072   | 10               | 4.597           | 7   | .0360    | 0.914 | .096                           | 2.438  |
| 10080  | 10               | 5.108           | 1   | .1004    | 2.550 | .100                           | 2.540  |
| 10404  | 10               | 5.272           | 19  | .0234    | 0.594 | .117                           | 2.972  |
| 16512  | 8                | 8               | 1   | .1285    | 3.260 | .129                           | 3.260  |
| 16533  | 8                | 8               | 7   | .0486    | 1.230 | .146                           | 3.710  |
| 16535  | 8                | 8               | 19  | .0295    | 0.750 | .148                           | 3.760  |
| 262218 | 6                | 13              | 7   | .0612    | 1.550 | .184                           | 4.670  |
| 26244  | 6                | 13              | 1   | .1620    | 4.110 | .162                           | 4.110  |
| 26292  | 6                | 15              | 19  | .0372    | 0.940 | .202                           | 5.130  |
| 41616  | 4                | 21              | 1   | .2040    | 5.182 | .204                           | 5.180  |
| 41718  | 4                | 21              | 7   | .0772    | 1.961 | .232                           | 5.890  |
| 41792  | 4                | 21              | 19  | .0469    | 1.191 | .226                           | 5.740  |
| 95509  | 0                | 50              | 19  | .0709    | 1.800 | .354                           | 9.000  |
| 97610  | 0                | 50              | 396 | .0157    | 0.400 | .406                           | 10.300 |
| 98409  | 0                | 50              | 702 | .0118    | 0.300 | .370                           | 9.400  |

## Part Number Index

**Note:** This index lists all cataloged parts by base no. only. Complete part nos. (with prefixes and/or suffixes) are shown on the page(s) indicated.

| Part No. | Page     |
|----------|----------|
| 55323    | 170      |
| 55556    | 169      |
| 55557    | 169      |
| 55558    | 170      |
| 55673    | 169      |
| 58490    | 119      |
| 58491    | 119      |
| 58492    | 119      |
| 58493    | 119      |
| 60151    | 91       |
| 62531    | 220      |
| 66084    | 91       |
| 68344    | 145      |
| 104501   | 201      |
| 104502   | 201      |
| 104729   | 201      |
| 104742   | 201      |
| 120591   | 233      |
| 120943   | 55       |
| 120943   | 55       |
| 120953   | 39, 55   |
| 120954   | 53       |
| 120954   | 53       |
| 120955   | 53       |
| 120956   | 53       |
| 120957   | 53       |
| 120958   | 53       |
| 146845   | 232      |
| 167892   | 171, 172 |
| 170221   | 87       |
| 170222   | 87       |
| 170286   | 87       |
| 170289   | 87       |
| 170311   | 87, 95   |
| 170312   | 95       |
| 170313   | 87, 95   |
| 170314   | 95       |
| 170484   | 87, 95   |
| 170485   | 87, 95   |
| 172059   | 94       |
| 172061   | 94       |
| 172063   | 94       |
| 172624   | 94       |
| 172653   | 93       |
| 173032   | 94       |
| 173977   | 100      |
| 179227   | 101      |
| 179228   | 101      |
| 179316   | 98       |
| 179317   | 98       |
| 179321   | 98       |
| 179322   | 98       |
| 179518   | 101      |
| 179609   | 101      |
| 179694   | 100      |
| 192000   | 134      |
| 192001   | 134      |
| 192002   | 134      |

| Part No. | Page          |
|----------|---------------|
| 192004   | 134           |
| 192007   | 134, 139      |
| 192008   | 134, 139      |
| 192013   | 136           |
| 192033   | 136           |
| 192038   | 135, 137      |
| 192039   | 135, 139      |
| 192040   | 137           |
| 192041   | 135, 137      |
| 192042   | 135, 139      |
| 192043   | 137           |
| 192044   | 135, 137, 138 |
| 192045   | 135, 139      |
| 192046   | 138           |
| 192047   | 138           |
| 192048   | 135, 139      |
| 192059   | 129           |
| 192061   | 129           |
| 192085   | 129           |
| 192129   | 129           |
| 192211   | 129           |
| 192244   | 129           |
| 192271   | 129           |
| 192293   | 129           |
| 192447   | 130           |
| 193673   | 132           |
| 193837   | 131           |
| 194257   | 133           |
| 194305   | 133           |
| 208211   | 214           |
| 208697   | 220           |
| 208979   | 220           |
| 213598   | 221           |
| 213647   | 201           |
| 213727   | 221           |
| 213815   | 170           |
| 213816   | 170           |
| 213878   | 220           |
| 216843   | 171, 172      |
| 216905   | 171, 172      |
| 216906   | 170, 172      |
| 216907   | 170, 172      |
| 216926   | 171, 172      |
| 223041   | 56            |
| 223956   | 58            |
| 223969   | 58            |
| 223982   | 58            |
| 292180   | 97            |
| 292181   | 99            |
| 292182   | 99            |
| 292183   | 97            |
| 292184   | 97            |
| 292185   | 98            |
| 292186   | 97            |
| 292187   | 97            |
| 292189   | 97            |
| 292190   | 97            |
| 292192   | 97            |
| 292491   | 18            |
| 292495   | 18            |
| 292499   | 21            |
| 338429   | 171           |

| Part No. | Page          |
|----------|---------------|
| 343347   | 90            |
| 343348   | 90            |
| 343371   | 89, 90, 91    |
| 343404   | 88            |
| 343886   | 89            |
| 343887   | 89            |
| 530553   | 213           |
| 556135   | 119           |
| 556136   | 119           |
| 556137   | 118           |
| 556879   | 123           |
| 556880   | 123, 124      |
| 556881   | 121           |
| 556882   | 122           |
| 556883   | 123, 124      |
| 557313   | 118           |
| 557640   | 118           |
| 558084   | 121           |
| 558574   | 121           |
| 567256   | 119           |
| 567403   | 119           |
| 583204   | 89, 90, 91    |
| 583294   | 89, 90        |
| 583361   | 91            |
| 583555   | 91            |
| 583989   | 91            |
| 583990   | 89, 91        |
| 583991   | 91            |
| 647691   | 152           |
| 647692   | 152           |
| 647719   | 152           |
| 647720   | 152           |
| 647721   | 152           |
| 647722   | 152           |
| 647737   | 152           |
| 647747   | 151           |
| 647754   | 144, 145      |
| 647755   | 144, 145      |
| 647756   | 144, 145      |
| 647840   | 151           |
| 647845   | 143           |
| 647877   | 143, 144, 145 |
| 647878   | 143, 144, 145 |
| 647879   | 143, 144, 145 |
| 647892   | 143           |
| 647893   | 143           |
| 650025   | 186, 187      |
| 680308   | 112           |
| 680447   | 119           |
| 680449   | 119           |
| 748572   | 210, 213      |
| 765191   | 209           |
| 765204   | 210           |
| 765206   | 210           |
| 765208   | 213           |
| 765209   | 214, 215      |
| 765224   | 214, 215      |
| 765225   | 208           |
| 765228   | 208           |
| 765229   | 208           |
| 765238   | 214           |
| 765241   | 216           |

| Part No. | Page          |
|----------|---------------|
| 765242   | 216           |
| 765247   | 214, 215      |
| 765248   | 215           |
| 765249   | 213           |
| 765250   | 214           |
| 765251   | 215           |
| 765261   | 214, 215      |
| 765265   | 213           |
| 765271   | 210           |
| 765276   | 212           |
| 765277   | 212           |
| 765278   | 212           |
| 765295   | 212           |
| 765296   | 212           |
| 765311   | 212           |
| 765449   | 211           |
| 765450   | 211           |
| 765451   | 211           |
| 765478   | 209           |
| 765527   | 213           |
| 765527   | 213           |
| 765528   | 209, 214, 215 |
| 765529   | 209, 215      |
| 765530   | 209, 214      |
| 765608   | 213           |
| 766090   | 216           |
| 766510   | 213           |
| 766569   | 209           |
| 787328   | 232           |
| 787439   | 232           |
| 787613   | 232           |
| 787614   | 232           |
| 787615   | 232           |
| 788109   | 119           |
| 788110   | 119           |
| 794144   | 107           |
| 794145   | 107           |
| 794149   | 107           |
| 794150   | 107           |
| 794152   | 107           |
| 794153   | 107           |
| 794156   | 107           |
| 794318   | 107           |
| 794319   | 107           |
| 794322   | 107           |
| 794576   | 112           |
| 796136   | 233           |
| 796285   | 220           |
| 927829   | 103           |
| 927831   | 103           |
| 927837   | 103           |
| 927840   | 103           |
| 963709   | 103           |
| 1123684  | 230           |
| 1123688  | 230           |
| 1123822  | 230           |
| 1318574  | 230           |
| 1385663  | 145           |
| 1385664  | 145           |
| 1410270  | 52            |
| 1410271  | 52            |
| 1410278  | 52            |

## Part Number Index (Continued)

| Part No. | Page     | Part No. | Page          | Part No. | Page          | Part No. | Page          |
|----------|----------|----------|---------------|----------|---------------|----------|---------------|
| 1410279  | 52       | 1604001  | 146           | 1648162  | 70            | 1651929  | 191, 192      |
| 1410297  | 59       | 1604002  | 146           | 1648163  | 70            | 1674231  | 230           |
| 1410465  | 59       | 1604037  | 148           | 1648168  | 70            | 1717445  | 230           |
| 1410546  | 59       | 1604038  | 148, 149      | 1648183  | 73            | 1717458  | 228           |
| 1410548  | 59       | 1604039  | 148, 149      | 1648186  | 73            | 1717478  | 230           |
| 1410710  | 59       | 1604040  | 148, 149      | 1648203  | 69            | 1717620  | 230           |
| 1410714  | 59       | 1604041  | 148, 149      | 1648204  | 69            | 1734178  | 233           |
| 1410773  | 59       | 1604042  | 148           | 1648205  | 69            | 1734894  | 235           |
| 1410956  | 59       | 1604043  | 148           | 1648206  | 69            | 1744041  | 142           |
| 1410962  | 59       | 1604044  | 148           | 1648207  | 69            | 1744042  | 142           |
| 1410963  | 59       | 1604045  | 148           | 1648208  | 69            | 1744077  | 151           |
| 1445715  | 145      | 1604050  | 150           | 1648211  | 78            | 1744090  | 152           |
| 1445716  | 145      | 1604051  | 150           | 1648212  | 78            | 1747602  | 230           |
| 1445729  | 151      | 1604052  | 150           | 1648325  | 81            | 1747785  | 228           |
| 1445762  | 151      | 1604053  | 150           | 1648382  | 81            | 1747786  | 228           |
| 1445763  | 151      | 1604054  | 150           | 1648384  | 81            | 1761122  | 188           |
| 1445886  | 151, 152 | 1604055  | 150           | 1648387  | 81            | 1761259  | 190           |
| 1445957  | 142      | 1604056  | 150           | 1648461  | 156           | 1761347  | 188           |
| 1445959  | 151      | 1604057  | 150           | 1648462  | 156           | 1761419  | 21            |
| 1445960  | 151      | 1604058  | 150           | 1648463  | 156           | 1761421  | 27            |
| 1445962  | 142      | 1604059  | 150           | 1648464  | 156           | 1761426  | 184           |
| 1445994  | 147      | 1604060  | 150           | 1648465  | 157           | 1761500  | 183           |
| 1445995  | 146, 147 | 1604062  | 149           | 1648466  | 156           | 1761786  | 184           |
| 1445996  | 146, 147 | 1604072  | 152           | 1648467  | 156           | 1761819  | 21            |
| 1445997  | 146, 147 | 1604112  | 142           | 1648468  | 156           | 1761879  | 183           |
| 1445998  | 147      | 1604113  | 142           | 1648469  | 156           | 1766056  | 32            |
| 1445999  | 147      | 1604121  | 152           | 1648470  | 157           | 1766057  | 32            |
| 1446000  | 147      | 1604342  | 144           | 1648473  | 157           | 1766157  | 47            |
| 1469265  | 58       | 1604395  | 149           | 1648482  | 157           | 1766160  | 47            |
| 1469269  | 58       | 1604396  | 149           | 1648505  | 157           | 1766161  | 47            |
| 1469372  | 58       | 1604397  | 149           | 1648548  | 74            | 1766163  | 47            |
| 1469373  | 58       | 1604398  | 149           | 1648549  | 74            | 1766192  | 80            |
| 1469374  | 58       | 1604433  | 143, 144, 145 | 1648552  | 73            | 1766193  | 80            |
| 1469387  | 58       | 1612503  | 230           | 1648568  | 77            | 1766194  | 80            |
| 1469388  | 58       | 1612504  | 230           | 1648574  | 74            | 1766195  | 80            |
| 1469491  | 59       | 1612898  | 228           | 1648575  | 74            | 1766196  | 80            |
| 1469492  | 59       | 1612901  | 228           | 1648578  | 73            | 1766197  | 80            |
| 1469606  | 109      | 1612962  | 228           | 1648596  | 77            | 1766198  | 80            |
| 1469609  | 109      | 1612963  | 228           | 1650060  | 80            | 1766199  | 80            |
| 1469610  | 109      | 1612964  | 228           | 1650065  | 80            | 1766222  | 80            |
| 1469910  | 111      | 1643279  | 167           | 1650073  | 80            | 1766223  | 80            |
| 1469920  | 37       | 1643903  | 196           | 1650074  | 80            | 1766230  | 81            |
| 1469921  | 37       | 1643906  | 195           | 1650106  | 65            | 1766231  | 81            |
| 1469922  | 37       | 1645498  | 54            | 1650153  | 80            | 1766232  | 80            |
| 1470390  | 234      | 1645499  | 54            | 1650155  | 80            | 1766245  | 80            |
| 1489127  | 84       | 1645545  | 58            | 1650156  | 80            | 1766249  | 80            |
| 1489128  | 84       | 1648110  | 69            | 1650158  | 80            | 1766250  | 80            |
| 1489701  | 84       | 1648111  | 69            | 1650161  | 80            | 1766262  | 80            |
| 1489715  | 84       | 1648112  | 69            | 1650162  | 80            | 1766263  | 80            |
| 1600236  | 27       | 1648115  | 69            | 1650226  | 80            | 1766268  | 81            |
| 1600238  | 27       | 1648116  | 69            | 1650283  | 80            | 1766269  | 81            |
| 1600606  | 21       | 1648117  | 69            | 1650399  | 65            | 1766270  | 81            |
| 1600636  | 21       | 1648127  | 77            | 1650401  | 65            | 1766274  | 81            |
| 1600788  | 22       | 1648128  | 77            | 1650402  | 65            | 1766275  | 81            |
| 1600798  | 22       | 1648132  | 72            | 1650469  | 159           | 1766276  | 81            |
| 1600814  | 27       | 1648133  | 72            | 1650589  | 65            | 1766283  | 80            |
| 1600820  | 27       | 1648134  | 72            | 1651003  | 165           | 1766308  | 192           |
| 1600902  | 24, 109  | 1648135  | 72            | 1651202  | 79            | 1766336  | 188, 191, 192 |
| 1600903  | 23       | 1648151  | 71            | 1651203  | 79            | 1766436  | 188, 191, 192 |
| 1600914  | 21, 24   | 1648152  | 71            | 1651766  | 167           | 1766442  | 191, 192      |
| 1600960  | 23       | 1648156  | 71            | 1651826  | 188, 191, 192 | 1766443  | 191, 192      |
| 1600961  | 23       | 1648157  | 71            | 1651864  | 191, 192      | 1766447  | 76            |

## Part Number Index (Continued)

| Part No. | Page          | Part No. | Page   | Part No. | Page   | Part No. | Page       |
|----------|---------------|----------|--------|----------|--------|----------|------------|
| 1766448  | 76            | 1926273  | 39     | 5536565  | 56     | 6450130  | 13, 18, 21 |
| 1766484  | 165, 166      | 1926671  | 197    | 5536600  | 56     | 6450131  | 13         |
| 1766500  | 61            | 1926720  | 35     | 5536603  | 56     | 6450132  | 13, 18     |
| 1766501  | 61            | 1926721  | 35     | 5536607  | 57     | 6450140  | 12         |
| 1766502  | 61            | 1926732  | 35     | 5536613  | 57     | 6450142  | 12         |
| 1766503  | 61            | 1926733  | 35     | 5536614  | 57     | 6450150  | 12         |
| 1766600  | 165           | 1926785  | 192    | 5536620  | 56     | 6450151  | 12         |
| 1766663  | 48            | 1934017  | 111    | 5536623  | 56     | 6450152  | 12         |
| 1766685  | 192           | 1934142  | 111    | 5536625  | 56     | 6450160  | 12, 27     |
| 1766735  | 188, 192      | 1934143  | 111    | 5536628  | 56     | 6450161  | 12         |
| 1766811  | 81            | 1934144  | 111    | 5536642  | 56     | 6450163  | 12         |
| 1766812  | 80            | 1934145  | 111    | 5536642  | 56     | 6450170  | 12, 27     |
| 1766815  | 47            | 1934182  | 113    | 5536649  | 57     | 6450172  | 12         |
| 1766816  | 47            | 1934183  | 113    | 5645384  | 187    | 6450173  | 12, 27     |
| 1766817  | 47            | 1934184  | 112    | 5646954  | 53     | 6450178  | 18         |
| 1766818  | 80            | 1934185  | 112    | 5646955  | 53     | 6450230  | 13         |
| 1766819  | 81            | 1934193  | 113    | 5646956  | 53     | 6450231  | 13         |
| 1766821  | 80            | 1934988  | 58     | 5646957  | 53     | 6450330  | 13, 18, 21 |
| 1766829  | 159           | 1982257  | 54     | 5646958  | 53     | 6450503  | 13         |
| 1775069  | 235           | 1982260  | 54     | 5650118  | 187    | 6450523  | 13         |
| 1775485  | 233           | 1982295  | 104    | 5650118  | 187    | 6450540  | 12, 27     |
| 1775529  | 235           | 1982299  | 104    | 5787090  | 229    | 6450541  | 12         |
| 1775637  | 235           | 1982530  | 199    | 5787141  | 231    | 6450543  | 12, 27     |
| 1775638  | 234           | 1982995  | 199    | 5787142  | 231    | 6450550  | 12, 27     |
| 1775639  | 234           | 2007088  | 183    | 5787246  | 231    | 6450551  | 12         |
| 1775640  | 222           | 2042274  | 104    | 5787252  | 229    | 6450553  | 12         |
| 1775641  | 222           | 2057372  | 183    | 5787253  | 229    | 6450558  | 18         |
| 1775642  | 222           | 2085181  | 48     | 5787334  | 231    | 6450560  | 12         |
| 1775643  | 222           | 5055323  | 170    | 5787418  | 231    | 6450570  | 12         |
| 1820539  | 204           | 5055556  | 169    | 5787419  | 231    | 6450578  | 18         |
| 1827501  | 228           | 5055557  | 169    | 5787421  | 231    | 6450622  | 18         |
| 1827654  | 228           | 5055558  | 170    | 5787422  | 231    | 6450668  | 18         |
| 1827684  | 228           | 5055673  | 169    | 5787424  | 231    | 6450740  | 27         |
| 1827685  | 228           | 5120913  | 58     | 5787428  | 231    | 6450810  | 16         |
| 1852467  | 112, 113      | 5145089  | 187    | 5787430  | 231    | 6450820  | 16         |
| 1852468  | 112, 113      | 5145459  | 193    | 5787441  | 231    | 6450830  | 16         |
| 1852469  | 113           | 5146877  | 229    | 5787443  | 231    | 6450831  | 16         |
| 1857147  | 204           | 5167892  | 172    | 5787444  | 231    | 6450840  | 16         |
| 1857178  | 166           | 5172068  | 94     | 5787446  | 231    | 6450850  | 16         |
| 1857523  | 165, 166      | 5172069  | 94     | 5787526  | 229    | 6450860  | 16         |
| 1857547  | 165, 166, 204 | 5172070  | 94     | 5787531  | 229    | 6450870  | 16         |
| 1857561  | 204           | 5172625  | 94     | 5787590  | 232    | 6450871  | 16         |
| 1857988  | 58            | 5173033  | 94     | 5787802  | 232    | 6450880  | 16         |
| 1888132  | 18            | 5176916  | 86     | 5794172  | 106    | 6469602  | 109        |
| 1888179  | 18            | 5213815  | 170    | 5794173  | 106    | 6473451  | 230        |
| 1888803  | 61            | 5213816  | 170    | 5794176  | 106    | 6473539  | 230        |
| 1888804  | 61            | 5221980  | 18     | 5796078  | 231    | 6489165  | 188, 193   |
| 1888946  | 184           | 5221981  | 18     | 6123738  | 230    | 6489649  | 193        |
| 1903977  | 53            | 5223092  | 57     | 6123978  | 230    | 6489651  | 188        |
| 1903978  | 55            | 5223093  | 57     | 6123981  | 230    | 6489930  | 188        |
| 1926024  | 192           | 5223955  | 39, 55 | 6123987  | 230    | 6600303  | 13, 21     |
| 1926088  | 177           | 5223957  | 58     | 6318430  | 230    | 6600310  | 18         |
| 1926155  | 192           | 5223961  | 53     | 6318573  | 230    | 6600323  | 13         |
| 1926223  | 39            | 5223963  | 53     | 6318792  | 230    | 6600330  | 13, 21     |
| 1926224  | 39            | 5223979  | 58     | 6318977  | 230    | 6600333  | 13, 21     |
| 1926225  | 39            | 5223985  | 58     | 6339488  | 233    | 6600380  | 22         |
| 1926226  | 39            | 5223986  | 58     | 6376042  | 230    | 6600383  | 22         |
| 1926227  | 39            | 5223995  | 55     | 6450120  | 13, 21 | 6600390  | 22         |
| 1926228  | 39            | 5530843  | 186    | 6450121  | 13     | 6600393  | 22         |
| 1926229  | 39            | 5531216  | 24     | 6450123  | 13, 21 | 6643219  | 46         |
| 1926271  | 39            | 5531224  | 24     | 6450128  | 22     | 6643220  | 49         |
| 1926272  | 39            | 5532600  | 187    | 6450129  | 22     | 6643222  | 49         |


## Part Number Index (Continued)

| Part No. | Page | Part No. | Page     | Part No. | Page | Part No. | Page |
|----------|------|----------|----------|----------|------|----------|------|
| 6643223  | 49   | 6643449  | 46       | 6648418  | 82   | 6651668  | 32   |
| 6643227  | 49   | 6643450  | 46       | 6648419  | 82   | 6651669  | 32   |
| 6643228  | 49   | 6643451  | 46       | 6648420  | 82   | 6651670  | 32   |
| 6643229  | 49   | 6643460  | 179      | 6648428  | 82   | 6651671  | 32   |
| 6643232  | 46   | 6646465  | 43       | 6648429  | 82   | 6651672  | 32   |
| 6643248  | 47   | 6646597  | 43       | 6648430  | 82   | 6651673  | 32   |
| 6643252  | 47   | 6646722  | 43       | 6648431  | 82   | 6651711  | 192  |
| 6643253  | 47   | 6648167  | 70       | 6648434  | 82   | 6651712  | 192  |
| 6643264  | 46   | 6648221  | 165, 166 | 6648435  | 82   | 6651742  | 32   |
| 6643266  | 46   | 6648222  | 165, 166 | 6648454  | 158  | 6651743  | 32   |
| 6643269  | 46   | 6648223  | 165, 166 | 6648457  | 158  | 6651810  | 78   |
| 6643271  | 46   | 6648224  | 165, 166 | 6648476  | 158  | 6766014  | 76   |
| 6643272  | 46   | 6648226  | 165, 166 | 6648499  | 158  | 6766015  | 76   |
| 6643273  | 46   | 6648228  | 165, 166 | 6648508  | 158  | 6766439  | 46   |
| 6643274  | 46   | 6648234  | 165, 166 | 6648515  | 158  | 6766440  | 46   |
| 6643275  | 46   | 6648235  | 165, 166 | 6650380  | 177  | 6766441  | 46   |
| 6643276  | 46   | 6648236  | 165, 166 | 6650383  | 177  | 6766615  | 78   |
| 6643281  | 46   | 6648237  | 165, 166 | 6650384  | 177  | 60DB8    | 225  |
| 6643283  | 46   | 6648238  | 165, 166 | 6650494  | 178  | 60DB8    | 226  |
| 6643431  | 46   | 6648239  | 165, 166 | 6650534  | 178  | 60DBF8   | 225  |
| 6643432  | 46   | 6648251  | 159      | 6650679  | 157  | 60DBF8   | 226  |
| 6643433  | 46   | 6648252  | 159      | 6650680  | 157  | 60DBJ8   | 225  |
| 6643434  | 46   | 6648253  | 159      | 6650785  | 46   | 60DBJ8   | 226  |
| 6643435  | 46   | 6648254  | 159      | 6651170  | 177  | 60DBP    | 225  |
| 6643436  | 46   | 6648259  | 159      | 6651193  | 178  | 60DBPL   | 225  |
| 6643437  | 46   | 6648263  | 159      | 6651204  | 79   | 60DBPL1  | 225  |
| 6643438  | 46   | 6648317  | 47, 82   | 6651205  | 79   | 60DBPL3  | 225  |
| 6643439  | 46   | 6648318  | 81       | 6651214  | 178  | 60DBPL9  | 225  |
| 6643440  | 46   | 6648319  | 81       | 6651290  | 179  | 60DBR    | 225  |
| 6643441  | 46   | 6648335  | 82       | 6651331  | 177  | 60DBRL   | 225  |
| 6643442  | 46   | 6648374  | 81       | 6651380  | 32   | 60DBRL1  | 225  |
| 6643443  | 46   | 6648383  | 81       | 6651381  | 32   | 60DBRL3  | 225  |
| 6643444  | 46   | 6648400  | 82       | 6651457  | 75   | 60DBX    | 225  |
| 6643445  | 46   | 6648405  | 82       | 6651458  | 75   | 60DBX8   | 225  |
| 6643446  | 46   | 6648416  | 82       | 6651493  | 75   | 60DBX8   | 226  |
| 6643447  | 46   | 6648417  | 82       | 6651494  | 75   |          |      |

---

**Engineering Notes**

---



---

**Engineering Notes**

---



**te.com**

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

1773096 LUG PDF 04/2012

TE Connectivity and the TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

