

Digital Output Pressure Sensor

MMR940 Datasheet

DESCRIPTION



The MMR940 digitally outputs pressure value which was corrected. Customers need no correction because it corrects and outputs the differences of sensors and temperature characteristics. It does not require complicated sensor drive or control circuit, and devices with high performance can be made only with this module and an external microcontroller which will be the host.

FEATURES

- Dual nozzle package: 29(W) × 18(D) × 14.25(H)mm
- Operating pressure range
C02 rank: -20~20cmH₂O(-1.961~1.961kPa)
C04 rank: -40~40cmH₂O(-3.922~3.922kPa)
C07 rank: -70~70cmH₂O(-6.865~6.865kPa)
C10 rank: -100~100cmH₂O(-9.807~9.807kPa)
- Effective resolution: 0.002cmH₂O RMS (0.196Pa RMS) (at MODE4)
- Pressure measurement error
C02 rank: ±3.0 (TBD) [%FS]
C04 rank: ±1.5 [%FS]
C07 rank: ±1.3 (TBD) [%FS]
C10 rank: ±1.2 (TBD) [%FS]
- It corrects the differences of sensors and temperature characteristics when shipped from our factory.
- It digitally outputs pressure value corrected in the module. (I2C)
I2C slave address (7 bits) is 0x67
- Noise reduction is possible by a built-in Low Pass Filter.
- This product complies with RoHS.
- This product contains halogen.

rank	Pressure Unit Conversion Table							
	cmH ₂ O	mbar	bar	psi	inchH ₂ O	i.w.c	Pa	kPa
C02	±20	±19.61	±0.01961	±0.2845	±7.9402	±7.9402	±1961	±1.961
C04	±40	±39.23	±0.03923	±0.5689	±15.8804	±15.8804	±3922	±3.922
C07	±70	±68.65	±0.06865	±0.9956	±27.7907	±27.7907	±6865	±6.865
C10	±100	±98.07	±0.09807	±1.4223	±39.7010	±39.7010	±9807	±9.807

Index

DESCRIPTION	1
FEATURES.....	1
BLOCK DIAGRAM.....	4
PIN CONFIGURATION	5
TERMINAL EXPLANATIONS	6
ABSOLUTE MAXIMUM RATINGS	7
RECOMMENDED OPERATING CONDITIONS.....	8
ELECTRICAL CHARACTERISTICS	9
Analog characteristics.....	9
Digital I/O.....	9
C02 rank Pressure sensor characteristics	10
C04 rank Pressure sensor characteristics	11
C07 rank Pressure sensor characteristics	12
C10 rank Pressure sensor characteristics	13
Temperature sensor characteristics	14
Definition of characteristics	14
FUNCTION EXPLANATION.....	16
Function Outline.....	16
State transition table	17
Command code.....	18
Flow chart of pressure/temperature measurement	21
Product code obtain flow chart.....	22
Timing Chart.....	23
Low Pass Filter	24
SERIAL COMMUNICATION INTERFACE	25
Baud rate	25
I2C AC Characteristics	26
I2C format.....	27
TYPICAL APPLICATION CIRCUIT	29
TYPICAL PERFORMANCE CHARACTERISTICS	30
Analog characteristics.....	30
C02 rank Pressure sensor characteristics	33
C04 rank Pressure sensor characteristics	33
C07 rank Pressure sensor characteristics	35
C10 rank Pressure sensor characteristics	35
PACKAGE STRUCTURE	36
DIMENSIONS	37
MARKING CONTENTS	38
PRODUCT NAME.....	39
PRODUCT LINEUP	39
PRESSURE SENSOR LINEUP	40
NOTES.....	41
ATTENTION	42
ADDDITIONAL NOTES.....	42
PACKING SPECIFICATIONS (TRAY).....	43
CONDITION FOR PACKAGE MOUNTING	48
Design example of mount pad.....	48
Pb-Free recommended profile condition	49

Storage method50

BLOCK DIAGRAM




Fig. 1 Block diagram

PIN CONFIGURATION




Fig. 2 Pin configuration (Top view)

note¹ B: Pressure port to Bottom of MEMS sensor die
T: Pressure port to Top of MEMS sensor die




Fig. 3 Pin configuration (Bottom view)

TERMINAL EXPLANATIONS

Table 1 Pin table

No.	Pin Name	Type	Function
1	SCL	I/O	Serial clock for I2C communication (SCL)
2	VDD	I	Power-supply
3	GND	-	GND
4	SDA	I/O	Serial Data (Input and output) for I2C communication (SDA)
-	T	-	Pressure port to Top of MEMS sensor die (T) Output value decreases when Pressure port (T) is pressurized.
-	B	-	Pressure port to Bottom of MEMS sensor die (B) Output value increases when Pressure port (B) is pressurized.

ABSOLUTE MAXIMUM RATINGS

(unless otherwise specified, Ta=25°C)

Item	Symbol	Min.	Max.	Unit
Storage temperature range	T _{STG}	-40	85	°C
Analog supply voltage	VDD _{MAX}	-0.3	4.0	V
Digital input voltage	VDIN _{MAX}	-0.3	VDD + 0.3	V
Overpressure (note ²)	P _{MAX}	-200 (-19.6)	200 (19.6)	cmH ₂ O (kPa)
Burst pressure (note ³)	P _{Burst}	-500 (-49)	500 (49)	cmH ₂ O (kPa)
Common mode burst pressure (note ⁴)	P _{CMBurst}	-	5000 (490)	cmH ₂ O (kPa)
Pressure medium (note ⁵)	-	Non-corrosive Gas (non-condensing)		-

note²: Overpressure is defined as the maximum differential pressure that can be repeatedly applied between both pressure ports of the product. The product will remain within specifications if the pressure returns to the operating pressure range. (Tested to 1 million cycles)

note³: Burst pressure is defined as the differential pressure between both pressure ports of the product that, if exceeded even once, will cause permanent damage and leakage to the product.

note⁴: Common mode burst pressure is defined as the pressure applied simultaneously to both pressure ports, which, if exceeded even once, will cause permanent damage and leakage to the product.

note⁵: Storage and operation in an environment of dry and non-corrosive gases.

RECOMMENDED OPERATING CONDITIONS

(unless otherwise specified, Ta=25°C)

Item		Symbol	Min.	Typ.	Max.	Unit
Operating temperature range		T _{OPR}	-40	-	85	°C
Supply voltage		VDD _{OPR}	3.0	3.3	3.6	V
Operating pressure range	C02 rank	P _{OPR}	-20 (-1.961)	-	20 (1.961)	cmH2O (kPa)
	C04 rank		-40 (-3.922)	-	40 (3.922)	
	C07 rank		-70 (-6.865)	-	70 (6.865)	
	C10 rank		-100 (-9.807)	-	100 (9.807)	
Full Scale	C02 rank	FS	-	20 (1.961)	-	cmH2O (kPa)
	C04 rank		-	40 (3.922)	-	
	C07 rank		-	70 (6.865)	-	
	C10 rank		-	100 (9.807)	-	

ELECTRICAL CHARACTERISTICS

Analog characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit.
VDD Current consumption	I _{VDDact}	Pressure measure active	640	800	960	μA
	I _{VDDsd}	Shutdown	-	0.1	1.0	
Conversion time (note ⁶)	t _{con1}	MODE1	0.385	0.395	0.405	msec
	t _{con2}	MODE2	0.770	0.790	0.810	
	t _{con3}	MODE3	1.54	1.58	1.62	
	t _{con4}	MODE4	3.08	3.16	3.24	

note⁶: The conversion time is longer when the temperature is measured once every 256 times and the characteristic correction is updated.

Digital I/O

(unless otherwise specified, Ta=25°C, VDD=3.0~3.6V)

Item	Symbol	Conditions	Min.	Typ.	Max.	Unit
High level input voltage	V _{IH}	-	0.8 × VDD	-	VDD +0.3	V
Low level input voltage	V _{IL}	-	-0.3	-	0.2 × VDD	V
Output voltage Low level	V _{OL}	I _{OL} =3mA	-	-	0.4	V

C02 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
Operating pressure range	P _{OPR}	-	-20	-	20	cmH ₂ O
Full Scale	FS	-	-	20	-	cmH ₂ O
Pressure resolution	P _{Res}	-	-	0.00001	-	cmH ₂ O
Pressure effective resolution	P _{Eres1}	MODE1 (tcon1 = Typ 0.395ms)	-	0.019	0.076	cmH ₂ O RMS
	P _{Eres2}	MODE2 (tcon2 = Typ 0.790ms)	-	0.009	0.036	
	P _{Eres3}	MODE3 (tcon3 = Typ 1.58ms)	-	0.004	0.016	
	P _{Eres4}	MODE4 (tcon4 = Typ 3.16ms)	-	0.002	0.008	
Pressure measurement error	P _{Err}	-20 ~ 20cmH ₂ O Ta = 0°C~50°C	-3.0(TBD)	-	3.0(TBD)	%FS (note ⁷)
		-20 ~ 20cmH ₂ O Ta = -20°C~85°C	-7.0(TBD)	-	7.0(TBD)	
Pressure span accuracy	P _{Sacc}	-20 ~ 20cmH ₂ O Ta = 0°C~50°C	-1.30	-	1.30	%FS (note ⁷)
		-20 ~ 20cmH ₂ O Ta = -20°C~85°C	-4.00	-	4.00	
Pressure span accuracy Long term drift	P _{Slt}	-20 ~ 20cmH ₂ O Ta = 0°C~50°C Test condition = 0~50°C 1000h	-	-	±0.7	%FS (note ⁷)
Pressure linearity	P _L	-20 ~ 20cmH ₂ O Ta = 0°C~50°C	-0.44	-	0.44	%FS (note ⁷)
		-20 ~ 20cmH ₂ O Ta = -20°C~85°C	-1.20	-	1.20	

note⁷: Ratio to Full Scale (20cmH₂O).

C04 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
Operating pressure range	P _{OPR}	-	-40	-	40	cmH ₂ O
Full Scale	FS	-	-	40	-	cmH ₂ O
Pressure resolution	P _{Res}	-	-	0.00001	-	cmH ₂ O
Pressure effective resolution	P _{Eres1}	MODE1 (tcon1 = Typ 0.395ms)	-	0.019	0.076	cmH ₂ O RMS
	P _{Eres2}	MODE2 (tcon2 = Typ 0.790ms)	-	0.009	0.036	
	P _{Eres3}	MODE3 (tcon3 = Typ 1.58ms)	-	0.004	0.016	
	P _{Eres4}	MODE4 (tcon4 = Typ 3.16ms)	-	0.002	0.008	
Pressure measurement error	P _{Err}	-40 ~ 40cmH ₂ O Ta = 0°C~50°C	-1.5	-	1.5	%FS (note ⁸)
		-40 ~ 40cmH ₂ O Ta = -20°C~85°C	-3.5		3.5	
Pressure span accuracy	P _{Sacc}	-40 ~ 40cmH ₂ O Ta = 0°C~50°C	-0.65	-	0.65	%FS (note ⁸)
		-40 ~ 40cmH ₂ O Ta = -20°C~85°C	-2.00		2.00	
Pressure span accuracy Long term drift	P _{Slt}	-40 ~ 40cmH ₂ O Ta = 0°C~50°C Test condition = 0~50°C 1000h	-	-	±0.35	%FS (note ⁸)
Pressure linearity	P _L	-40 ~ 40cmH ₂ O Ta = 0°C~50°C	-0.22	-	0.22	%FS (note ⁸)
		-40 ~ 40cmH ₂ O Ta = -20°C~85°C	-0.60		0.60	

note⁸: Ratio to Full Scale (40cmH₂O).

C07 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
Operating pressure range	P _{OPR}	-	-70	-	70	cmH ₂ O
Full Scale	FS	-	-	70	-	cmH ₂ O
Pressure resolution	P _{Res}	-	-	0.00002	-	cmH ₂ O
Pressure effective resolution	P _{Eres1}	MODE1 (tcon1 = Typ 0.395ms)	-	0.019	0.076	cmH ₂ O RMS
	P _{Eres2}	MODE2 (tcon2 = Typ 0.790ms)	-	0.009	0.036	
	P _{Eres3}	MODE3 (tcon3 = Typ 1.58ms)	-	0.004	0.016	
	P _{Eres4}	MODE4 (tcon4 = Typ 3.16ms)	-	0.002	0.008	
Pressure measurement error	P _{Err}	-70 ~ 70cmH ₂ O Ta = 0°C~50°C	-1.3(TBD)	-	1.3(TBD)	%FS (note ⁹)
		-70 ~ 70cmH ₂ O Ta = -20°C~85°C	-3.3(TBD)	-	3.3(TBD)	
Pressure span accuracy	P _{Sacc}	-70 ~ 70cmH ₂ O Ta = 0°C~50°C	-0.65	-	0.65	%FS (note ⁹)
		-70 ~ 70cmH ₂ O Ta = -20°C~85°C	-2.00	-	2.00	
Pressure span accuracy Long term drift	P _{Slt}	-70 ~ 70cmH ₂ O Ta = 0°C~50°C Test condition = 0~50°C 1000h	-	-	±0.35	%FS (note ⁹)
Pressure linearity	P _L	-70 ~ 70cmH ₂ O Ta = 0°C~50°C	-0.4	-	0.4	%FS (note ⁹)
		-70 ~ 70cmH ₂ O Ta = -20°C~85°C	-0.60	-	0.60	

note⁹: Ratio to Full Scale (70cmH₂O).

C10 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
Operating pressure range	P _{OPR}	-	-100	-	100	cmH ₂ O
Full Scale	FS	-	-	100	-	cmH ₂ O
Pressure resolution	P _{Res}	-	-	0.00002	-	cmH ₂ O
Pressure effective resolution	P _{Eres1}	MODE1 (tcon1 = Typ 0.395ms)	-	0.019	0.076	cmH ₂ O RMS
	P _{Eres2}	MODE2 (tcon2 = Typ 0.790ms)	-	0.009	0.036	
	P _{Eres3}	MODE3 (tcon3 = Typ 1.58ms)	-	0.004	0.016	
	P _{Eres4}	MODE4 (tcon4 = Typ 3.16ms)	-	0.002	0.008	
Pressure measurement error	P _{Err}	-100 ~ 100cmH ₂ O Ta = 0°C~50°C	-1.2(TBD)	-	1.2(TBD)	%FS (note ¹⁰)
		-100 ~ 100cmH ₂ O Ta = -20°C~85°C	-3.2(TBD)	-	3.2(TBD)	
Pressure span accuracy	P _{Sacc}	-100 ~ 100cmH ₂ O Ta = 0°C~50°C	-0.65	-	0.65	%FS (note ¹⁰)
		-100 ~ 100cmH ₂ O Ta = -20°C~85°C	-2.00	-	2.00	
Pressure span accuracy Long term drift	P _{Slt}	-100 ~ 100cmH ₂ O Ta = 0°C~50°C Test condition = 0~50°C 1000h	-	-	±0.35	%FS (note ¹⁰)
Pressure linearity	P _L	-100 ~ 100cmH ₂ O Ta = 0°C~50°C	-0.4	-	0.4	%FS (note ¹⁰)
		-100 ~ 100cmH ₂ O Ta = -20°C~85°C	-0.60	-	0.60	

note¹⁰: Ratio to Full Scale (100cmH₂O).

Temperature sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)

Item	Symbol	Conditions	Min.	Typ.	Max.	Unit
Temperature measurement error	T _{acc}	0°C~ 50°C Initial temperature ADC value (Timing Chart Temperature n=1st)	-2.0	-	2.0	°C

Definition of characteristics

Pressure measurement value P_{result}

It is the device output value obtained by Read Pressure Result Command.

Pressure resolution P_{Res}

This Value is equivalent to 1LSB of output digital value.

Pressure effective resolution P_{Eres}

Measure 16 points after the pressure output is stable, and it is the standard deviation of the 16 points.

Pressure measurement error P_{Err}

It is the deviation amount of the Pressure measurement value from the ideal line. (Refer to Fig. 4)
Fig. 5 shows source of error included in the pressure measurement error.

Pressure linearity P_L

It is the amount of deviation from the Ref. line connecting measurement value -FS cmH2O with FS cmH2O. (Refer to Fig. 4)




Fig. 4 Definition of Characteristics

Pressure span accuracy P_{Sacc}

It is the accuracy removing the error caused by the offset from the pressure measurement error. (Refer to Fig. 5)




Fig. 5 Source of Error

Pressure span accuracy Long term drift P_{Sltld}

The amount of fluctuation in Pressure span accuracy over a long term.

FUNCTION EXPLANATION

Function Outline

The MMR940 is consists of piezoresistive pressure sensor and an analog front end IC.

It converts analog output voltage from piezoresistive pressure sensor to digital value of 24 bits, and corrects and outputs variations of sensor characteristics due to variations of temperature and process.

Conversion time and Pressure effective resolution are selectable with the mode of different four. Conversion time and Pressure effective resolution are in the relationship of trade-off.

Noise reduction is possible by a built-in Low Pass Filter. Cutoff frequency of Low Pass Filter can be changed.

State transition table




Fig. 6 State transition diagram

Table 2 State transition table

State Command	Shutdown	Active	Idle
Reset	Power on Reset & Initial Boot =>Shutdown	Power on Reset & Initial Boot =>Shutdown	Power on Reset & Initial Boot =>Shutdown
Active	Reset & Boot Load =>Active state(AD conversion)	Ignore(note ¹¹) =>Keep state	=>Active state (AD conversion)
Result	Ignore(note ¹¹) =>Keep state	Output result =>Keep state	Do not issue(note ¹²) =>Keep state
Idle	Reset & Boot Load =>Idle state	Do not issue(note ¹³) =>Idle state	=>Keep state
MACRAM Write	Ignore(note ¹¹) =>Keep state	Do not issue(note ¹³) =>Keep state	Change cutoff frequency =>Keep state
Status	Output code =>Keep state	Output code =>Keep state	Output code =>Keep state

note¹¹: NACK is returned to the command.
note¹²: The correct result isn't output. Additionally, ACK is returned to the command.
note¹³: Although command is acceptable, it goes unintended behavior since sequence is running.

Command code

Table 3 Command code list

Command Name		Command Code									Applicable format
		HEX.	BIN.								
			C7	C6	C5	C4	C3	C2	C1	C0	
Reset		0x72	0	1	1	1	0	0	1	0	I2C Write format
		Reset and Return to Shutdown state. It becomes busy for the maximum 10msec.									
Idle		0x94	1	0	0	1	0	1	0	0	I2C Write format
		Start up the internal circuit and put it in the idle state.									
Active	Measure at MODE 1	0xA0	1	0	1	0	0	0	0	0	I2C Write format
	Measure at MODE 2	0xA2	1	0	1	0	0	0	1	0	
	Measure at MODE 3	0xA4	1	0	1	0	0	1	0	0	
	Measure at MODE 4	0xA6	1	0	1	0	0	1	1	0	
		Start AD conversion.									

Table 4 Command code list (continued)

Command Name		Command Code									Applicable format																																																												
		HEX.	BIN.																																																																				
			C7	C6	C5	C4	C3	C2	C1	C0																																																													
	Normal	0xC0	1	1	0	0	0	0	0	0	I2C Combined format																																																												
	With Low Pass Filter	0xC4	1	1	0	0	0	1	0	0																																																													
Read Pressure Result		Read compensated pressure result. It outputs the result of pressure measurement at 24bits, MSB first. A negative number is expressed by 2's complement. About output range, in case of positive output : 000000 h ~ 7FFFFFFF h (in decimal number : 0 ~ 8388607), in case of negative output : FFFFFFFF h ~ 800000 h (in decimal number : -1 ~ -8388608) However, the result of measurement when being used beyond a recommended operating condition can't be guaranteed. C02 rank, C04 rank Pressure value = DEC. / 10^5 Output example: <table><tr><th>HEX.</th><th>DEC.</th><th>Pressure</th></tr><tr><td>800000 h</td><td>-8388608</td><td>-83.88608 cmH2O</td></tr><tr><td>C2F700 h</td><td>-4000000</td><td>-40.00000 cmH2O</td></tr><tr><td>E17B80 h</td><td>-2000000</td><td>-20.00000 cmH2O</td></tr><tr><td>FFFFFF h</td><td>-1</td><td>-0.00001 cmH2O</td></tr><tr><td>000000 h</td><td>0</td><td>0.00000 cmH2O</td></tr><tr><td>000001 h</td><td>1</td><td>0.00001 cmH2O</td></tr><tr><td>1E8480 h</td><td>2000000</td><td>20.00000 cmH2O</td></tr><tr><td>3D0900 h</td><td>4000000</td><td>40.00000 cmH2O</td></tr><tr><td>7FFFFFFF h</td><td>8388607</td><td>83.88607 cmH2O</td></tr></table> C07 rank, C10 rank Pressure value = DEC. x 2 / 10^5 Output example: <table><tr><th>HEX.</th><th>DEC.</th><th>Pressure</th></tr><tr><td>800000 h</td><td>-8388608</td><td>-167.77216 cmH2O</td></tr><tr><td>B3B4C0 h</td><td>-5000000</td><td>-100.00000 cmH2O</td></tr><tr><td>CA9820 h</td><td>-3500000</td><td>-70.00000 cmH2O</td></tr><tr><td>FFFFFF h</td><td>-1</td><td>-0.00002 cmH2O</td></tr><tr><td>000000 h</td><td>0</td><td>0.00000 cmH2O</td></tr><tr><td>000001 h</td><td>1</td><td>0.00002 cmH2O</td></tr><tr><td>3567E0 h</td><td>3500000</td><td>70.00000 cmH2O</td></tr><tr><td>4C4B40 h</td><td>5000000</td><td>100.00000 cmH2O</td></tr><tr><td>7FFFFFFF h</td><td>8388607</td><td>167.77214 cmH2O</td></tr></table>										HEX.	DEC.	Pressure	800000 h	-8388608	-83.88608 cmH2O	C2F700 h	-4000000	-40.00000 cmH2O	E17B80 h	-2000000	-20.00000 cmH2O	FFFFFF h	-1	-0.00001 cmH2O	000000 h	0	0.00000 cmH2O	000001 h	1	0.00001 cmH2O	1E8480 h	2000000	20.00000 cmH2O	3D0900 h	4000000	40.00000 cmH2O	7FFFFFFF h	8388607	83.88607 cmH2O	HEX.	DEC.	Pressure	800000 h	-8388608	-167.77216 cmH2O	B3B4C0 h	-5000000	-100.00000 cmH2O	CA9820 h	-3500000	-70.00000 cmH2O	FFFFFF h	-1	-0.00002 cmH2O	000000 h	0	0.00000 cmH2O	000001 h	1	0.00002 cmH2O	3567E0 h	3500000	70.00000 cmH2O	4C4B40 h	5000000	100.00000 cmH2O	7FFFFFFF h	8388607	167.77214 cmH2O
		HEX.	DEC.	Pressure																																																																			
		800000 h	-8388608	-83.88608 cmH2O																																																																			
		C2F700 h	-4000000	-40.00000 cmH2O																																																																			
		E17B80 h	-2000000	-20.00000 cmH2O																																																																			
		FFFFFF h	-1	-0.00001 cmH2O																																																																			
		000000 h	0	0.00000 cmH2O																																																																			
		000001 h	1	0.00001 cmH2O																																																																			
		1E8480 h	2000000	20.00000 cmH2O																																																																			
		3D0900 h	4000000	40.00000 cmH2O																																																																			
		7FFFFFFF h	8388607	83.88607 cmH2O																																																																			
		HEX.	DEC.	Pressure																																																																			
		800000 h	-8388608	-167.77216 cmH2O																																																																			
		B3B4C0 h	-5000000	-100.00000 cmH2O																																																																			
		CA9820 h	-3500000	-70.00000 cmH2O																																																																			
		FFFFFF h	-1	-0.00002 cmH2O																																																																			
		000000 h	0	0.00000 cmH2O																																																																			
		000001 h	1	0.00002 cmH2O																																																																			
		3567E0 h	3500000	70.00000 cmH2O																																																																			
		4C4B40 h	5000000	100.00000 cmH2O																																																																			
7FFFFFFF h	8388607	167.77214 cmH2O																																																																					

Table 5 Command code list (continued)

Command Name	Command Code									Applicable format												
	HEX.	BIN.																				
		C7	C6	C5	C4	C3	C2	C1	C0													
Read Temperature Result	0xC2	1	1	0	0	0	0	1	0	I2C Combined format												
	Read compensated temperature result. It outputs the result of pressure measurement at 24bits, MSB first. A negative number is expressed by 2's complement. About output range, in case of positive output : 000000 h ~ 7FFFFF h (in decimal number : 0 ~ 8388607), in case of negative output : FFFFFFFF h ~ 800000 h (in decimal number : -1 ~ -8388608) However, the result of measurement when being used beyond a recommended operating condition can't be guaranteed. Temperature value = DEC. / 2^7 Output example:																					
	<table><tr><td>HEX.</td><td>DEC.</td><td>Temperature</td></tr><tr><td>000000 h</td><td>0</td><td>0.000 °C</td></tr><tr><td>000C80 h</td><td>3200</td><td>25.000 °C</td></tr><tr><td>001900 h</td><td>6400</td><td>50.000 °C</td></tr></table>										HEX.	DEC.	Temperature	000000 h	0	0.000 °C	000C80 h	3200	25.000 °C	001900 h	6400	50.000 °C
	HEX.	DEC.	Temperature																			
	000000 h	0	0.000 °C																			
000C80 h	3200	25.000 °C																				
001900 h	6400	50.000 °C																				
Status	0x80	1	0	0	0	0	0	0	0	I2C Combined format												
	Output 8bits data depending on the IC conditions																					
	D7	D6	D5	D4	D3	D2	D1	D0	State													
	0	0	0	0	0	0	0	0	Shutdown													
	1	1	1	0	0	1	0	1	Idle													
	1	1	1	0	1	1	0	1	Active													
MACRAM Write	0xE4	1	1	1	0	0	1	0	0	I2C MACRAM Write format (special format)												
	It is used for writing filter coefficient. For the filter coefficient, refer to LowPassFilter .																					
Register Write	0xE0	1	1	1	0	0	0	0	0	I2C Register Write format												
	Write data to the register.																					
NVM Read	0xD6	1	1	0	1	0	1	1	0	I2C NVM Read format												
	Read data from NVM.																					

Flow chart of pressure/temperature measurement




Fig. 7 Flow chart of pressure/temperature measurement

note¹⁴: Temperature is measured once every 256 times and the pressure characteristic correction is updated. Conversion time will be longer at this timing.

Product code obtain flow chart

Product code has been recorded in internal memory (NVM (Non-volatile memory)) of the MMR940. Product code can be obtained by the process of Fig. 8.




Fig. 8 Flow chart of product code gets

Table 6 Description of the product code

Rank	Product code
C02	0xC2
C04	0xC4
C07	0xC7
C10	0xCA

Timing Chart




Fig. 9 Timing Chart

Low Pass Filter

Noise reduction is possible by a built-in Low Pass Filter. Pressure value with Low Pass Filter applied can be got using command code 0xC4. Cutoff frequency f_c can be changed by filter coefficient 4Bytes calculated by the equation (1). Filter coefficient is written to the IC using the MACRAM Write command in the idle state. Filter coefficient is cleared to the default value in the shutdown state.




Fig. 10 Low Pass Filter Configuration

Table 7 example of character with Low Pass Filter

Cutoff frequency		No filter	fc=100Hz	fc=10Hz
Pressure effective resolution example [cmH2O RMS]	MODE1	0.019	0.012	0.0068
	MODE2	0.008	0.0064	0.0034
	MODE3	0.0044	0.0036	0.0022
	MODE4	0.0025	0.0023	0.0013

Filter coefficient equation

Filter coefficient(4Bytes) = $2^{27} \times \exp(-2\pi \times f_c \times t_{con})$(Eq1)




Fig. 11 Filter coefficient example

SERIAL COMMUNICATION INTERFACE

It supports I2C (max.3.4Mbps) as an interface for serial communication.

Baud rate

※ This item is not inspected at the time of shipment.
(unless otherwise specified, Ta=25°C, VDD=3.0~3.6V)

Item	Symbol	Conditions	Min.	Typ.	Max.	Unit
I2C communication speed	BR _{I2C1}	Cb≤100pF	-	-	3.4	Mbps
	BR _{I2C3}	Cb≤400pF	-	-	1.7	

I2C AC Characteristics

※ This item is not inspected at the time of shipment




Fig. 12 I2C AC timing chart

Table 8 I2C AC Characteristics

Items	Symbol	Hsmode				Unit
		Cb=100pF		Cb=400pF		
		min.	max.	min.	max.	
SCL frequency	f _{SCL}	0	3.4	0	1.7	MHz
Start condition setup time	t _{SU;STA}	160	-	160	-	ns
Start condition hold time	t _{HD;STA}	160	-	160	-	ns
Stop condition setup time	t _{SU;STO}	160	-	160	-	ns
Data setup time	t _{SU;DAT}	20	-	20	-	ns
Data hold time (note ¹⁵)	t _{HD;DAT}	20	70	20	150	ns
SCL rise time	t _{rCL}	10	40	20	80	ns
Rise time of SCL after ACK (When clock stretch is released.)	t _{rCL1}	10	80	20	160	ns
SCL fall time	t _{fCL}	10	-	20	80	ns
SDA rise time	t _{rDA}	10	80	20	160	ns
SDA fall time	t _{fDA}	10	80	20	160	ns

note¹⁵: This product does not have the function to retain data in SDA.

Please ensure the hold of SDA with 20nsec for the area where SCL falling edge is not defined.

I2C format


It conforms to I2C protocol except some special formats. I2C address is the total of 8 bits. The first 7 bits are slave address and the rest of 1 bit is R/W bit. Slave address of MMR940 (7 bits) is 0x67. I2C address (8 bits) will be 0xCE (Write) and 0xCF (Read) by combining with R/W bit.

Table 9 I2C address

	I2C Address (8 bit)							R/W bit
	Slave address (7 bit)							
HEX.	A6	A5	A4	A3	A2	A1	A0	
0xCE	1	1	0	0	1	1	1	0
0xCF	1	1	0	0	1	1	1	1

I2C Write format

Please send I2C address of 8 bits (0xCE) by Write Mode. Then please send command code.



Combined format

Please send I2C address (0xCE) and the command code by Write Mode. Then please send I2C address (0xCF) by Read Mode. It outputs the data MSB first




Fig. 14 I2C Combined format

I2C MAC Write format (special format)

It is a format unique to this product that does not partially conform to I2C protocol. Please send I2C address (0xCE), the command (0xE4), and memory address (0x6F) by Write Mode. Then send the data of 4Bytes Filter coefficient. At this time, please be careful that NACK is returned after transmitting LSB. After receiving data, it becomes busy for the maximum 15msec in order to data- writing. During this time, SCL is put in clock stretch. When data- writing is completed, SCL is released.




Fig. 15 I2C MACRAM Write format

I2C Register Write format

Please send I2C address 0xCE), the command (0xE0), and memory address (0x3C or 0x3D) by Write Mode. Then send the data of 1Byte (0x80 or 0x02).




Fig. 16 I2C Register Write format

I2C NVM Read format

Please send I2C address (0xCE) command code (0xD6), and memory address (0x30) by Write Mode. After receiving memory address, it becomes busy during preparing to send data. During this time, SCL is in a clock stretch. SCL is released when data-preparation is completed. Then please send I2C address (0xCF) by Read Mode. When the address is received, 1byte data is output.




Fig. 17 I2C NVM Read format

TYPICAL APPLICATION CIRCUIT




Fig. 18 Typical Electrical Connection

note¹⁶: The longer the bus line on the board, the larger the parasitic capacitance and communication waveform rounding becomes.

In this case, reduce the pull-up resistor to improve the communication waveform. (Min 1.2k ohm)

※It should be designed in accordance with "NXP's UM10204: I2C-bus specification and user manual".

note¹⁷: Place the bypass capacitor for the power supply as close to the IC as possible.

TYPICAL PERFORMANCE CHARACTERISTICS

Analog characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)




Fig. 19.1 VDD current consumption I_{VDDact} at pressure measure active temperature characteristic




Fig. 19.2 VDD current consumption I_{VDDact} at pressure measure active supply voltage characteristic




Fig. 19.3 VDD current consumption I_{VDDsd} at shutdown temperature characteristic




Fig. 19.4 VDD current consumption I_{VDDsd} at shutdown supply voltage characteristic

(unless otherwise specified, Ta=25°C, VDD=3.3V)




Fig. 19.5 Conversion time at MODE 1 temperature characteristic




Fig. 19.6 Conversion time at MODE 1 supply voltage characteristic




Fig. 19.7 Conversion time at MODE 2 temperature characteristic




Fig. 19.8 Conversion time at MODE 2 supply voltage characteristic

(unless otherwise specified, Ta=25°C, VDD=3.3V)




Fig. 19.9 Conversion time at MODE 3 temperature characteristic




Fig. 19.10 Conversion time at MODE 3 supply voltage characteristic




Fig. 19.11 Conversion time at MODE 4 temperature characteristic




Fig. 19.12 Conversion time at MODE 4 supply voltage characteristic

C02 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)
TBD

C04 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)




Fig. 20.1 Pressure measurement value P_{Result} temperature characteristic




Fig. 20.2 Pressure measurement value P_{Result} supply voltage characteristic




Fig. 20.3 Pressure measurement error P_{Err} temperature characteristic 0~50deg.C




Fig. 20.4 Pressure measurement error P_{Err} temperature characteristic -40~85deg.C

(unless otherwise specified, Ta=25°C, VDD=3.3V)




Fig. 20.5 Pressure measurement error P_{Err} supply voltage characteristic




Fig. 20.6 Pressure Span accuracy P_{Sacc} temperature characteristic




Fig. 20.7 Pressure Span accuracy P_{Sacc} supply voltage characteristic


C07 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)
TBD

C10 rank Pressure sensor characteristics

(unless otherwise specified, Ta=25°C, VDD=3.3V)
TBD

PACKAGE STRUCTURE




Part Name	Material	Wetted Material		Remarks
		B Side	T Side	
IC chip 1	Silicon (Si)	✓	✓	
	Aluminium (Al), Tungsten (W)		✓	
IC chip 2	Si, Al, W, Copper (Cu), Tantalum (Ta)		✓	
Printed wiring board 1	Epoxy resin, Glass fiber, Acrylic resin, Gold (Au)		✓	
	Cu, Nickel (Ni)			
Printed wiring board 2	Epoxy resin, Glass fiber, Acrylic resin	✓	✓	
	Au, Cu, Ni		✓	
Cover 1	PBT, Glass fiber	✓	✓	
Cover 2	PPS, Glass fiber, Carbon black	✓	✓	
Au wire	Au		✓	
Lead	Tin (Sn)		✓	
	Cu, Ni, LCP			
Silicone paste	Silicone, SiO2	✓	✓	
DAF Tape	Epoxy resin		✓	
Epoxy paste	Epoxy resin, SiO2, Carbon Black	✓	✓	
Ag paste	Silver (Ag), Epoxy resin		✓	
Solder	Sn, Ag, Cu		✓	

DIMENSIONS

PACKAGE : MEMS-4A


UNIT	mm
------	----



Terminal list

PIN No.	Name
1	SCL
2	VDD
3	GND
4	SDA


MARKING CONTENTS



①～③	Model name		Rank	
	MMR940C04A		C04	
④	Production year			
⑤	Production month			
	month	marking	month	marking
	JAN	1	JUL	7
	FEB	2	AUG	8
	MAR	3	SEP	9
	APR	4	1OCT	J
	MAY	5	NOV	K
	JUN	6	DEC	L
⑥	Production day			
	day	marking	day	marking
	1	1	16	G
	2	2	17	H
	3	3	18	J
	4	4	19	K
	5	5	20	L
	6	6	21	M
	7	7	22	N
	8	8	23	P
	9	9	24	R
	10	A	25	S
	11	B	26	T
	12	C	27	U
	13	D	28	V
	14	E	29	W
	15	F	30	X
			31	Y

※Other…I,O,Q

PRODUCT NAME



PRODUCT LINEUP

Product Name	Rank	Pressure Range	Packing	Status
MMR940C02A	C02	-20~20cmH2O(-1.961~1.961kPa)	Tray	Planning
MMR940C04A	C04	-40~40cmH2O(-3.922~3.922kPa)	Tray	Developing
MMR940C07A	C07	-70~70cmH2O(-6.865~6.865kPa)	Tray	Planning
MMR940C10A	C10	-100~100cmH2O(-9.807~9.807kPa)	Tray	Planning

PRESSURE SENSOR LINEUP

Function	Product Name	Size [mm] (L x W x H)	Pressure Range [Pa]	Full Scale [Pa]	Pressure Measurement error [%FS]	Span Accuracy [%FS]	Effective Resolution [PaRMS]	Packing	Halogen	Status
Gage Pressure Sensor	MMR920C02A	7 x 7 x 7.2	-1,961 ~ 1,961	1,961	2.0	1.30	0.2	Tray	Contain	Developing
	MMR920C02ARE	7 x 7 x 7.2	-1,961 ~ 1,961	1,961	2.0	1.30	0.2	Taping (R)	Contain	Developing
	MMR920C04A	7 x 7 x 7.2	-3,922 ~ 3,922	3,922	1.0	0.65	0.2	Tray	Contain	MP
	MMR920C04ARE	7 x 7 x 7.2	-3,922 ~ 3,922	3,922	1.0	0.65	0.2	Taping (R)	Contain	MP
	MMR920C07A	7 x 7 x 7.2	-6,865 ~ 6,865	6,865	1.0	0.65	0.2	Tray	Contain	Developing
	MMR920C07ARE	7 x 7 x 7.2	-6,865 ~ 6,865	6,865	1.0	0.65	0.2	Taping (R)	Contain	Developing
	MMR920C10A	7 x 7 x 7.2	-9,807 ~ 9,807	9,807	1.0	0.65	0.2	Tray	Contain	MP
	MMR920C10ARE	7 x 7 x 7.2	-9,807 ~ 9,807	9,807	1.0	0.65	0.2	Taping (R)	Contain	MP
	MMR906XAN	6 x 5 x 7.2	-1,000 ~ 40,000	40,000	-	0.66	1.0	Tray	Free	MP
	MMR906XARE	6 x 5 x 7.2	-1,000 ~ 40,000	40,000	-	0.66	1.0	Taping (R)	Free	MP
	MMR902A34A	7 x 7 x 7.2	-1,000 ~ 40,000	40,000	2.3	0.66	0.7	Tray	Free	MP
	MMR902A34ABE	7 x 7 x 7.2	-1,000 ~ 40,000	40,000	2.3	0.66	0.7	Taping (B)	Free	MP
	MMR902A34ARE	7 x 7 x 7.2	-1,000 ~ 40,000	40,000	2.3	0.66	0.7	Taping (R)	Free	MP
Differential Pressure Sensor	MMR940C02A	29 x 18 x 14.25	-1,961 ~ 1,961	1,961	(2.0)	1.30	0.2	Tray	Contain	Planning
	MMR940C04A	29 x 18 x 14.25	-3,922 ~ 3,922	3,922	(1.0)	0.65	0.2	Tray	Contain	Developing
	MMR940C07A	29 x 18 x 14.25	-6,865 ~ 6,865	6,865	(1.0)	0.65	0.2	Tray	Contain	Planning
	MMR940C10A	29 x 18 x 14.25	-9,807 ~ 9,807	9,807	(1.0)	0.65	0.2	Tray	Contain	Planning

NOTES

Safety Precautions

- Though Mitsumi Electric Co., Ltd. (hereinafter referred to as "Mitsumi") works continually to improve our product's quality and reliability, semiconductor products may generally malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of this product could cause loss of human life, bodily injury, or damage to property, including data loss or corruption. Before customers use this product, create designs including this product, or incorporate this product into their own applications, customers must also refer to and comply with (a) the latest versions or all of our relevant information, including without limitation, product specifications, data sheets and application notes for this product and (b) the user's manual, handling instructions or all relevant information for any products which is to be used, or combined with this products. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. Mitsumi assumes no liability for customers' product design or applications.
- This product is intended for applying to computers, OA units, communication units, instrumentation units, machine tools, industrial robots, AV units, household electrical appliances, and other general electronic units.
- This product is not designed as a component of equipment or devices that require a high degree of reliability, may affect the life or body, or could damage the property (space systems, submarine repeaters, nuclear power controllers, infrastructure controllers, medical equipment, military devices, units related to the control and safety of transport equipment (automobiles, trains, aircraft, etc.), traffic signaling equipment, disaster / crime prevention units, or the like). In the case where this product is used in these applications, Mitsumi does not bear any responsibility. If the product is used as a component of the above equipment or devices, Mitsumi shall not be liable for any damage caused thereby. It is the customer's responsibility to carry out the necessary safety design for the customer's hardware, software and systems.
- Before using this product, even when it is not used for the applications written previous paragraph, notify and present us beforehand if special care and attention are needed for its application, intended purpose, environment of usage, risk, and the design or inspection specification corresponding to them.
- If any damage to our customer is objectively identified to be caused by the defect of this product, Mitsumi is responsible for it. In this case, Mitsumi is liable for the cost limited to the delivery price of this product.

Application considerations during actual circuit design

- The outline of parameters described herein has been chosen as an explanation of the standard parameters and performance of the product. When you actually plan to use the product, please ensure that the outside conditions are reflected in the actual circuit and assembling designs.
- Before using this product, please evaluate and confirm the actual application with this product mounted and embedded.
- To investigate the influence by applied transient load or external noise, It is necessary to evaluate and confirm them with mounting this product to the actual application.
- Any usage above the maximum rating may destroy this product or shorten the lifetime. Be sure to use this product under the maximum rating.
- If you continue to use this product highly-loaded (applying high temperature, large current or high voltage; or variation of temperature) even under the absolute maximum rating and even in the operating range, the reliability of this product may decrease significantly. Please design appropriate reliability in consideration of power dissipation and voltage corresponding to the temperature and designed lifetime after confirming our individual reliability documents (such as reliability test report or estimated failure rate). It is recommended that, before using this product, you appropriately derate the maximum power dissipation (typically, 80% or less of the maximum value) considering parameters including ambient temperature, input voltage, and output current.

Precautions for Foreign Exchange and Foreign Trade Control Act

- If you export or take products and technologies in this document which are subject to security trade control based on the Foreign Exchange and Foreign Trade Act to overseas from Japan, permission of the Japanese government is required.

Prohibitions for Industrial Property Rights

- Since this document contains the contents related to our copyright and know-how, you are requested not to use this document for any purpose other than the application of this product.
- If a use of this product causes a dispute related to the industrial property rights of a third party, Mitsumi has no liability for any disputes except those which arise directly from the manufacturing and manufacturing method of our products.

Precautions for Product Liability Act

- Mitsumi does not bear any responsibility for any consequence resulting from any wrong or improper use of this product and other factors.

Others

- Any part of the contents contained herein must not be reprinted or reproduced without our prior permission.
- In case of any question arises out of the description in this specification, it shall be settled by the consultation between both parties promptly.

ATTENTION

- This product is designed and manufactured with the intention of normal use in general electronics. No special circumstance as described below is considered for the use of it when it is designed. With this reason, any use and storage under the circumstances below may affect the performance of this product. Prior confirmation of performance and reliability is requested to customers.
 - Environment with strong static electricity or electromagnetic wave
 - Environment with high temperature or high humidity where dew condensation may occur
- This product is not designed to withstand radioactivity, and must avoid using in a radioactive environment.

ADDDITIONAL NOTES

- The pressure medium which can use directly is only air. Please do not use other media, especially corrosive gases (organic solvent gas, sulfurous acid gas, hydrogen sulfide gas, etc.) and media which include moisture and foreign substance, since they could cause damages or malfunctions.
- Please handle it noting the foreign body mixing with the pressure opening and atmospheric pressure opening after opening packing.
- When cut folding the PCB after mounting this product, take measures to prevent stress to the package. Also, when you insert the tube in this product, please note that plugging it vertically. Load in the lateral direction of the cover of the nozzle is up to 1kg or less. (Load condition: position of height 4mm from the marking surface.) Excessive load could cause damages of cover, or air leak by peeling from the interface of the cover and the substrate, or malfunctions.
- The light that enters from the pressure entrance reaches the semiconductor chip. Please avoid use in the environment that light enters into the pressure entrance directly, because the semiconductor chip might malfunction because of light.

PACKING SPECIFICATIONS (TRAY)


QUANTITY

- TRAY PACKING 100 pcs/ ESD BAG
- BOX PACKING MAX 600 pcs/BOX (1 BAGs)


THE QUANTITY IS FILLED IN THE PACKING SLIP.

PACKING SPECIFICATIONS

- TRAY STORAGE SPECIFICATION



1. PRODUCTION STORAGE DIRECTION



2. BROKEN NUMBER PRODUCTION STORAGE

REGARDING BROKEN NUMBER PRODUCTION STORAGE,
IT IS HOUSED IN FOLLOWING-ORDER.


(A1, A2, ..., A9, A10), (B1, B2, ..., B9, B10), ..., (E1, E2, ..., E9, E10).

3. TRAY MATERIAL, DISPOSED ELECTRICATION PREVENTION.


· TRAY DIMENSION

TRAY A


UNIT	mm
------	----



TRAY B



· PACKING SPECIFICATION



THESE 3 TRAYS WHICH ARE 2 TRAYS WITH PRODUCTS AND EMPTY TRAY AS LID ARE PILED UP. ALSO, THESE TRAYS ARE FIXED BY BAND.


AFTER THAT, PUT INTO SHIELD BAG.

※THIS TRAY HAS TYPE A AND TYPE B. THEY ARE PILED UP ALTERNATELY.

(IT IS POSSIBLE TO USE BOTH TYPE TRAYS AS EMPTY ONE.)

· BOX DIMENSION

UNIT	mm
------	----



PACKING SLIP

PUT MAX 6 BAGS IN THE CARTON BOX.
AFTER PACKING BY TAPE (600 PCS MAX)
PUT THE PACKING SLIP ON THE SIDE OF THE CARTON BOX.

· PACKING SLIP SPECIFICATION


 MITSUMI ELECTRIC CO., LTD. 現品票 PACKING SLIP	
納入先 MESSRS.	
品番 PART NO.	
品名 DESCRIPTION	
注番 P/O NO.	
特記 NOTE <G>	
TOTAL Q' TY/BOXES	Q' TY/BOX
個	個入
荷姿	個口/番
DATE	<G> PBF
LOT NO.	
R 番 SPEC. R.	

CONDITION FOR PACKAGE MOUNTING

Design example of mount pad

PACKAGE : MEMS-4A


UNIT	mm
------	----



The dimension are for reference only and not guaranteed by design.

To design practically, correction should be made for optimized dimensions considering the effects of the board type to be mounted, mount (soldering) method and type of solder.

Pb-Free recommended profile condition



This profile gives recommended values, which are not guaranteed.
For mounting the package, evaluate the profile with the equipment, conditions, and materials to be used.

Mounting by reflow soldering
Reflow soldering cannot be used for mounting of this package.

In the case of cleaning, please use cotton swab, and also please keep soldering-solution from entering into the pressure and atmospheric pressure opening. Please do not use ultrasonic cleaning (dipping).

Cleaning method

Cleaning solution	Isopropyl alcohol
Solvent temperature	Max 45°C
Cleaning time	Within 3 min

NOTE
When insert a tube to this package, please keep direction of a tube at right angle with this package.
If place an extra strain on cover nozzle, it is possible that occur cover nozzle broken, interface delamination between cover nozzle and printed wiring board. It has the potential to become air-leak problem.

Storage method

Storage condition

Store the device under the following conditions.

Temperature: 5~30°C

Humidity: 40~70%RH

Storage life: 1 year

Do not store this device where a large amount of dust or harmful volatile gas exists, electrostatic is easily charged, condensation is generated, or changes in temperature and humidity are wide, or under the direct sunlight.

Handling instructions

Shipping boxes must be handled with care because any drop or shock may damage the device.

Additionally, the device must be handled in the place with the protection against electrostatic charge and without extreme changes of temperature/humidity.

MITSUMI ELECTRIC CO., LTD.

Strategy Engineering Department Semiconductor Business Division

Tel: +81-46-230-3470 / <https://product.minebeamitsumi.com/en/contact/>

Notes:

Any products mentioned this datasheet are subject to any modification in their appearance and others for improvements without prior notification. The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Disclaimers (Handling Precautions)

1. All the information described herein (product data, specifications, figures, tables, programs, algorithms and application circuit examples, etc.) is current as of publishing date of this document and is subject to change without notice.
2. The circuit examples and the usages described herein are for reference only, and do not guarantee the success of any specific mass-production design.
MITSUMI ELECTRIC CO., LTD. is not liable for any losses, damages, claims or demands caused by the reasons other than the products described herein (hereinafter "the products") or infringement of third-party intellectual property right and any other right due to the use of the information described herein.
3. MITSUMI ELECTRIC CO., LTD. is not liable for any losses, damages, claims or demands caused by the incorrect information described herein.
4. Be careful to use the products within their ranges described herein. Pay special attention for use to the absolute maximum ratings, operation voltage range and electrical characteristics, etc.
MITSUMI ELECTRIC CO., LTD. is not liable for any losses, damages, claims or demands caused by failures and / or accidents, etc. due to the use of the products outside their specified ranges.
5. Before using the products, confirm their applications, and the laws and regulations of the region or country where they are used and verify suitability, safety and other factors for the intended use.
6. When exporting the products, comply with the Foreign Exchange and Foreign Trade Act and all other export-related laws, and follow the required procedures.
7. The products are strictly prohibited from using, providing or exporting for the purposes of the development of weapons of mass destruction or military use. MITSUMI ELECTRIC CO., LTD. is not liable for any losses, damages, claims or demands caused by any provision or export to the person or entity who intends to develop, manufacture, use or store nuclear, biological or chemical weapons or missiles, or use any other military purposes.
8. The products are not designed to be used as part of any device or equipment that may affect the human body, human life, or assets (such as medical equipment, disaster prevention systems, security systems, combustion control systems, infrastructure control systems, vehicle equipment, traffic systems, in-vehicle equipment, aviation equipment, aerospace equipment, and nuclear-related equipment), excluding when specified for in-vehicle use or other uses by MITSUMI ELECTRIC CO., LTD. Do not apply the products to the above listed devices and equipment.
MITSUMI ELECTRIC CO., LTD. is not liable for any losses, damages, claims or demands caused by unauthorized or unspecified use of the products.
9. In general, semiconductor products may fail or malfunction with some probability. The user of the products should therefore take responsibility to give thorough consideration to safety design including redundancy, fire spread prevention measures, and malfunction prevention to prevent accidents causing injury or death, fires and social damage, etc. that may ensue from the products' failure or malfunction.
The entire system in which the products are used must be sufficiently evaluated and judged whether the products are allowed to apply for the system on customer's own responsibility.
10. The products are not designed to be radiation-proof. The necessary radiation measures should be taken in the product design by the customer depending on the intended use.
11. The products do not affect human health under normal use. However, they contain chemical substances and heavy metals and should therefore not be put in the mouth. The fracture surfaces of wafers and chips may be sharp. Be careful when handling these with the bare hands to prevent injuries, etc.
12. When disposing of the products, comply with the laws and ordinances of the country or region where they are used.
13. The information described herein contains copyright information and know-how of MITSUMI ELECTRIC CO., LTD.
The information described herein does not convey any license under any intellectual property rights or any other rights belonging to MITSUMI ELECTRIC CO., LTD. or a third party. Reproduction or copying of the information from this document or any part of this document described herein for the purpose of disclosing it to a third-party is strictly prohibited without the express permission of MITSUMI ELECTRIC CO., LTD.
14. For more details on the information described herein or any other questions, please contact MITSUMI ELECTRIC CO., LTD.'s sales representative.
15. This Disclaimers have been delivered in a text using the Japanese language, which text, despite any translations into the English language and the Chinese language, shall be controlling.