TAOGLAS



Datasheet

IP67 Rated Cellular Hinged Terminal Antenna

Part No:
TG.62.A113

Description

WideBand Cellular (600-7125MHz) Monopole IP67 Terminal Antenna with 90° Hinged SMA(M) Connector

Features:

Wideband Cellular Terminal Mount Antenna
Worldwide 5G/4G Bands including Wi-Fi 6
IP67 Waterproof Enclosure
Dimensions: Ø12.7 x 203mm
Connector: SMA(M)
RoHS & Reach Compliant

Downloaded from Arrow.com.

1.	Introduction	2
2.	Specification	3
3.	Antenna Characteristics	4
4.	Radiation Patterns	7
5.	Mechanical Drawing	29
6.	Packaging	30
	Changelog	31

Ireland & USA ISO 9001:2015 Certified | Taiwan ISO 9001:2015 Certified | IATF16949

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Downloaded from Arrow.com.

1. Introduction



The Taoglas TG.62.8113 is a 5G/4G monopole antenna, designed primarily for use with modules and IoT devices that require high efficiency and peak gain from a cellular antenna. It delivers best in class throughput on all major cellular bands worldwide, perfect for access points, terminals, and routers. The TG.62 operates from 600-7125MHz cover all cellular and Wi-Fi bands.

It has an SMA (M) connector as standard and is an ideal solution for any device requiring reliable performance in a slim form factor. The innovative hinge design not only provides flexibility when mounting the antenna, but it is also weatherproof with an IP67 rating, ensuring that it can be used in outdoor locations where potential water ingress would prevent other terminal mount antennas from being used.

Typical Applications include:

- Gateways & Routers
- Exterior Cameras
- Vending Machines
- Industrial IoT
- Smart Home
- Wastewater Monitoring

The TG.62 exhibits an efficiency of up to 80% across wideband 5G/4G bands and is backward compatible with 3G/2G cellular applications. The TG.62 is a fully omnidirectional antenna as seen in the radiation patterns and is stable across all bands, ideal for applications requiring reliable throughput.

The hinged SMA (M) connector mechanism allows the antenna to be rotated into the preferred orientation which helps to avoid objects or other antennas. The antenna can swivel 90 degrees from the connector accommodating different installation configurations helping with antenna isolation by positioning them in alternate directions when using multiple antennas in MIMO systems or on a device.

Contact your regional Taoglas customer support team to request testing services or additional support to integrate and test this antenna's performance in your device.

Downloaded from Arrow.com.

2. Specification

LTE Electrical							
Frequency (MHz)	Test Set-up	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern
617-960	Free space	44.4	-3.52	2.87	50 Ω	Linear	Omni
	on 15x9 Ground	70.4	-1.52	3.34			
	on 9x15 Ground	75.3	-1.23	4.63			
1710-2700	Free space	37.2	-4.30	1.39			
	on 15x9 Ground	56.3	-2.49	5.00			
	on 9x15 Ground	57.6	-2.40	5.23			
3300-3800	Free space	58.7	-2.31	1.45			
	on 15x9 Ground	56.6	-2.48	5.77			
	on 9x15 Ground	51.6	-2.87	4.83			
4400-5000	Free space	40.1	-3.97	2.55			
	on 15x9 Ground	43.5	-3.61	4.36			
	on 9x15 Ground	43.8	-3.58	3.10			
5850-5850	Free space	58.3	-2.35	3.53			
	on 15x9 Ground	41.4	-3.83	3.15			
	on 9x15 Ground	45.5	-3.42	3.30			
5925-7125	Free space	46.8	-3.06	3.87			
	on 15x9 Ground	37.6	-4.11	5.52			
	on 9x15 Ground	37.2	-5.38	5.03			


Mechanical	
Dimensions	Ø12.7 x 203mm
Material	PC+PBT
Connector	SMA(M)


Environmental	
Operation Temperature	-40°C - +85°C
Storage Temperature	-40°C - +85°C
Waterproof Rating	IP67

Downloaded from Arrow.com.


3. Antenna Characteristics

3.1 Test Set-up






Free Space




On 15x9cm Ground




On 9x15cm Ground

Downloaded from Arrow.com.

3.2 Return Loss




3.3 Efficiency




Downloaded from Arrow.com.

3.4 Average Gain




3.5 Peak Gain




Downloaded from Arrow.com.

4. Radiation Patterns

4.1 Test Setup









Free Space | On 15x9cm Ground | On 9x15cm Ground

Downloaded from Arrow.com.


4.2 Free space - Patterns at 824 MHz




XZ Plane	YZ Plane	XY Plane
		


Downloaded from Arrow.com.


4.3 Free space - Patterns at 2170 MHz



XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.4 Free space - Patterns at 3550 MHz



XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.5 Free space - Patterns at 4600 MHz



XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.6 Free space - Patterns at 5490 MHz



XZ Plane	YZ Plane	XY Plane











Downloaded from Arrow.com.


4.7 Free space - Patterns at 6000 MHz




XZ Plane	YZ Plane	XY Plane
		


Downloaded from Arrow.com.


4.8 Free space - Patterns at 6600 MHz



XZ Plane	YZ Plane	XY Plane









Downloaded from Arrow.com.

4.9 On 15x9cm Ground - Patterns at 824 MHz




XZ Plane	YZ Plane	XY Plane



Downloaded from Arrow.com.


4.10 On 15x9cm Ground - Patterns at 2170 MHz









XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.11 On 15x9cm Ground - Patterns at 3550 MHz



XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.12 On 15x9cm Ground - Patterns at 4600 MHz



XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.13 On 15x9cm Ground - Patterns at 5490 MHz



XZ Plane	YZ Plane	XY Plane











Downloaded from Arrow.com.


4.14 On 15x9cm Ground - Patterns at 6000 MHz






XZ Plane	YZ Plane	XY Plane
		

Downloaded from Arrow.com.


4.15 On 15x9cm Ground - Patterns at 6600 MHz




XZ Plane	YZ Plane	XY Plane
		

Downloaded from Arrow.com.

4.16 On 9x15cm Ground - Patterns at 824 MHz







XZ Plane	YZ Plane	XY Plane



Downloaded from Arrow.com.


4.17 On 9x15cm Ground - Patterns at 2170 MHz




XZ Plane	YZ Plane	XY Plane
		


Downloaded from Arrow.com.


4.18 On 9x15cm Ground - Patterns at 3550 MHz



XZ Plane	YZ Plane	XY Plane









Downloaded from Arrow.com.

4.19 On 9x15cm Ground - Patterns at 4600 MHz




XZ Plane	YZ Plane	XY Plane





Downloaded from Arrow.com.


4.20 On 9x15cm Ground - Patterns at 5490 MHz



XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.21 On 9x15cm Ground - Patterns at 6000 MHz



XZ Plane	YZ Plane	XY Plane










Downloaded from Arrow.com.


4.22 On 9x15cm Ground - Patterns at 6600 MHz



XZ Plane	YZ Plane	XY Plane








Downloaded from Arrow.com.


5. Mechanical Drawing



	Name	Material	Finish	QTY
1	Radome	PC+PBT	Black	1
2	RG178 coaxial cable	FEP	Brown	1
3	Lower Holder	PC+PBT	Black	1
4	SMA(M)	PC+PBT	Black	1

Downloaded from Arrow.com.

6. Packaging



☑ 1 PCS / Small PE Bag



☑ 50 PCS / PE Bag

☑ Weight (kg): 1.25 ±3%

☑ SPQ Label



☑ 300 PCS / Carton

☑ Carton(mm): 320x250x290

☑ Weight (kg): 8 ±3%

☑ Carton Label

Downloaded from Arrow.com.

Changelog for the datasheet

SPE-23-8-274 – TG.62.A113

Revision: C (Current Version)	
Date:	2025-06-04
Changes:	Updated packaging information
Changes Made by:	Paul Liu

Previous Revisions

Revision: B (Current Version)	
Date:	2024-02-16
Changes:	Changed from Dipole to Monopole and added packaging information.
Changes Made by:	Jack Conroy

Revision: A (Original First Release)	
Date:	2023-09-27
Notes:	Initial Release
Author:	Gary West

Downloaded from Arrow.com.

TAOGLAS®

www.taoglas.com



Downloaded from Arrow.com.