



MOSFET  
CoolSiC™ Automotive Power Device 750 V G1

The 750 V CoolSiC™ is built over the solid silicon carbide technology developed in Infineon in more than 20 years. Leveraging the wide bandgap SiC material characteristics, the 750V CoolSiC™ MOSFET offers a unique combination of performance, reliability and ease of use. Suitable for high temperature and harsh operations, it enables the simplified and cost effective deployment of the highest system efficiency.

PG-TO247-4



Features

- Highly robust 750V technology, 100% avalanche tested
- Best-in-class  $R_{DS(on)} \times Q_{fr}$
- Excellent  $R_{DS(on)} \times Q_{oss}$  and  $R_{DS(on)} \times Q_G$
- Unique combination of low  $C_{rss}/C_{iss}$  and high  $V_{GS(th)}$
- Infineon proprietary die attach technology
- Driver source pin available
- Best-in-class  $R_{DS(on)}$

Benefits

- Enhanced robustness and reliability for bus voltages beyond 500 V
- Superior efficiency in hard switching
- Higher switching frequency in soft switching topologies
- Robustness against parasitic turn on for unipolar gate driving
- Reduced switching losses through improved gate control

Potential applications

- Uni- and bidirectional On Board Chargers and HV-LV DCDC converters (hard switching half bridges and soft switching topologies)



Product validation

Qualified according to AEC Q101

Please note: The source and driver source pins are not exchangeable. Their exchange might lead to malfunction.

Table 1 Key Performance Parameters

| Parameter                         | Value | Unit |
|-----------------------------------|-------|------|
| $V_{DSS}$ over full $T_{j,range}$ | 750   | V    |
| $R_{DS(on),typ}$                  | 7.8   | mΩ   |
| $R_{DS(on),max}$                  | 10.6  | mΩ   |
| $Q_{G,typ}$                       | 178   | nC   |
| $I_{DM,max}$                      | 708   | A    |
| $Q_{oss,typ} @ 500 V$             | 352   | nC   |
| $E_{oss,typ} @ 500 V$             | 63.1  | μJ   |

| Type/Ordering Code | Package    | Marking  | Related Links  |
|--------------------|------------|----------|----------------|
| AIMZA75R008M1H     | PG-TO247-4 | 75A008M1 | see Appendix A |



Table of Contents

Description ..... 1

Maximum ratings ..... 3

Thermal characteristics ..... 4

Operating range ..... 5

Electrical characteristics ..... 6

Electrical characteristics diagrams ..... 8

Test Circuits ..... 13

Package Outlines ..... 14

Appendix A ..... 15

Revision History ..... 16

Trademarks ..... 16

Disclaimer ..... 16

## 1 Maximum ratings

at  $T_j = 25\text{ °C}$ , unless otherwise specified.

Note: for optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.

**Table 2 Maximum ratings**

| Parameter                                      | Symbol           | Values |      |            | Unit | Note/ Test Condition                                                                                        |
|------------------------------------------------|------------------|--------|------|------------|------|-------------------------------------------------------------------------------------------------------------|
|                                                |                  | Min.   | Typ. | Max.       |      |                                                                                                             |
| Continuous DC drain current <sup>1)</sup>      | $I_{\text{DDC}}$ | -      | -    | 163<br>116 | A    | $T_c = 25\text{ °C}$<br>$T_c = 100\text{ °C}$                                                               |
| Peak drain current <sup>2)</sup>               | $I_{\text{DM}}$  | -      | -    | 708        | A    | $T_c = 25\text{ °C}$ , $V_{\text{GS}} = 18\text{ V}$                                                        |
| Avalanche energy, single pulse                 | $E_{\text{AS}}$  | -      | -    | 926        | mJ   | $I_{\text{D}} = 34.7\text{ A}$ , $V_{\text{DD}} = 50\text{ V}$ ; see table 11                               |
| Avalanche current, single pulse                | $I_{\text{AS}}$  | -      | -    | 34.7       | A    | -                                                                                                           |
| MOSFET $dv/dt$ ruggedness                      | $dv/dt$          | -      | -    | 200        | V/ns | $V_{\text{DS}} = 0 \dots 500\text{ V}$                                                                      |
| Gate source voltage (static)                   | $V_{\text{GS}}$  | -5     | -    | 23         | V    | -                                                                                                           |
| Gate source voltage (transient)                | $V_{\text{GS}}$  | -10    | -    | 25         | V    | $t_p \leq 500\text{ ns}$ , duty cycle $\leq 1\%$                                                            |
| Power dissipation                              | $P_{\text{tot}}$ | -      | -    | 517        | W    | $T_c = 25\text{ °C}$                                                                                        |
| Storage temperature                            | $T_{\text{stg}}$ | -55    | -    | 150        | °C   | -                                                                                                           |
| Operating junction temperature                 | $T_j$            | -55    | -    | 175        | °C   | -                                                                                                           |
| Mounting torque                                | -                | -      | -    | 60         | Ncm  | M3 and M3.5 screws                                                                                          |
| Continuous reverse drain current <sup>1)</sup> | $I_{\text{SDC}}$ | -      | -    | 163<br>98  | A    | $V_{\text{GS}} = 18\text{ V}$ , $T_c = 25\text{ °C}$<br>$V_{\text{GS}} = 0\text{ V}$ , $T_c = 25\text{ °C}$ |
| Peak reverse drain current <sup>2)</sup>       | $I_{\text{SM}}$  | -      | -    | 708<br>232 | A    | $T_c = 25\text{ °C}$ , $t_p \leq 250\text{ ns}$<br>$T_c = 25\text{ °C}$                                     |
| Insulation withstand voltage                   | $V_{\text{ISO}}$ | -      | -    | n.a.       | V    | $V_{\text{rms}}$ , $T_c = 25\text{ °C}$ , $t = 1\text{ min}$                                                |

<sup>1)</sup> Limited by  $T_{j,\text{max}}$

<sup>2)</sup> Pulse width  $t_{\text{pulse}}$  limited by  $T_{j,\text{max}}$ .

## 2 Thermal characteristics

**Table 3 Thermal characteristics**

| Parameter                                                   | Symbol        | Values |      |      | Unit | Note/ Test Condition                                                                                     |
|-------------------------------------------------------------|---------------|--------|------|------|------|----------------------------------------------------------------------------------------------------------|
|                                                             |               | Min.   | Typ. | Max. |      |                                                                                                          |
| Thermal resistance, junction - case                         | $R_{th(j-c)}$ | -      | -    | 0.29 | °C/W | Not subject to production test.<br>Parameter verified by design/characterization according to JESD51-14. |
| Soldering temperature, wave soldering only allowed at leads | $T_{sold}$    | -      | -    | 260  | °C   | 1.6mm (0.063 in.) from case for 10s                                                                      |

### 3 Operating range

**Table 4** Operating range

| Parameter                                                               | Symbol        | Values |      |      | Unit | Note/ Test Condition |
|-------------------------------------------------------------------------|---------------|--------|------|------|------|----------------------|
|                                                                         |               | Min.   | Typ. | Max. |      |                      |
| Gate-source voltage operating range including undershoots <sup>3)</sup> | $V_{GS}$      | -2     | -    | 20   | V    | -                    |
| Recommended turn-on voltage                                             | $V_{GS(on)}$  | -      | 18   | -    | V    | -                    |
| Recommended turn-off voltage                                            | $V_{GS(off)}$ | -      | 0    | -    | V    | -                    |

3)

**Important notice:** If the gate source voltage of the device in application exceeds the operating range (Table 4), the device  $R_{DS(on)}$  and  $V_{GS(th)}$  might exceed the maximum value stated in the datasheet at the end of the lifetime of the device. In order to ensure sound operation of the device over the planned lifetime, the maximum ratings (Table 2) and the application note AN2018-09 must be considered.

## 4 Electrical characteristics

at  $T_j = 25\text{ °C}$ , unless otherwise specified

**Table 5 Static characteristics**

For applications with applied blocking voltage > 525 V, it is required that the customer evaluates the impact of cosmic radiation effect in early design phase and contacts the Infineon sales office for the necessary technical support.

| Parameter                            | Symbol       | Values |                           |                     | Unit          | Note/ Test Condition                                                                                                                                                                                                                                                                              |
|--------------------------------------|--------------|--------|---------------------------|---------------------|---------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                      |              | Min.   | Typ.                      | Max.                |               |                                                                                                                                                                                                                                                                                                   |
| Drain-source voltage <sup>4)</sup>   | $V_{DS}$     | 750    | -                         | -                   | V             | $V_{GS} = 0\text{ V}$ , $I_D = 3.24\text{ mA}$ ,<br>$T_j = -55\text{ °C to }175\text{ °C}$                                                                                                                                                                                                        |
| Gate threshold voltage <sup>5)</sup> | $V_{GS(th)}$ | 3.5    | 4.3                       | 5.6                 | V             | $V_{DS} = V_{GS}$ , $I_D = 32.4\text{ mA}$ , $T_j = 25\text{ °C}$                                                                                                                                                                                                                                 |
| Zero gate voltage drain current      | $I_{DSS}$    | -      | 1<br>10                   | 75<br>-             | $\mu\text{A}$ | $V_{DS} = 750\text{ V}$ , $V_{GS} = 0\text{ V}$ , $T_j = 25\text{ °C}$<br>$V_{DS} = 750\text{ V}$ , $V_{GS} = 0\text{ V}$ , $T_j = 175\text{ °C}$                                                                                                                                                 |
| Gate-source leakage current          | $I_{GSS}$    | -      | -                         | 100                 | nA            | $V_{GS} = 20\text{ V}$ , $V_{DS} = 0\text{ V}$ , $T_j = 25\text{ °C}$                                                                                                                                                                                                                             |
| Drain-source on-state resistance     | $R_{DS(on)}$ | -      | 9.6<br>7.8<br>7.2<br>14.0 | -<br>10.6<br>-<br>- | m $\Omega$    | $V_{GS} = 15\text{ V}$ , $I_D = 90.3\text{ A}$ , $T_j = 25\text{ °C}$<br>$V_{GS} = 18\text{ V}$ , $I_D = 90.3\text{ A}$ , $T_j = 25\text{ °C}$<br>$V_{GS} = 20\text{ V}$ , $I_D = 90.3\text{ A}$ , $T_j = 25\text{ °C}$<br>$V_{GS} = 18\text{ V}$ , $I_D = 90.3\text{ A}$ , $T_j = 175\text{ °C}$ |
| Internal gate resistance             | $R_{G,int}$  | -      | 3.0                       | -                   | $\Omega$      | $f = 1\text{ MHz}$                                                                                                                                                                                                                                                                                |

<sup>4)</sup> Tested at  $T_j = 25\text{ °C}$ , minimum  $V_{DSS}$  verified by design over full junction temperature range.

<sup>5)</sup> Tested after 1 ms pulse at  $V_{GS} = +20\text{ V}$ . "Linear mode" operation is not recommended. For assessment of potential "linear mode" operation, please contact Infineon sales office.

**Table 6 Dynamic characteristics**

External parasitic elements (PCB layout) influence switching behavior significantly. Stray inductances and coupling capacitances must be minimized. For layout recommendations please use provided application notes or contact Infineon sales office.

| Parameter                                                  | Symbol      | Values |      |      | Unit | Note/ Test Condition                                                                                                           |
|------------------------------------------------------------|-------------|--------|------|------|------|--------------------------------------------------------------------------------------------------------------------------------|
|                                                            |             | Min.   | Typ. | Max. |      |                                                                                                                                |
| Input capacitance                                          | $C_{iss}$   | -      | 6137 | -    | pF   | $V_{GS} = 0\text{ V}$ , $V_{DS} = 500\text{ V}$ , $f = 250\text{ kHz}$                                                         |
| Reverse transfer capacitance                               | $C_{rss}$   | -      | 37   | -    | pF   | $V_{GS} = 0\text{ V}$ , $V_{DS} = 500\text{ V}$ , $f = 250\text{ kHz}$                                                         |
| Output capacitance <sup>6)</sup>                           | $C_{oss}$   | -      | 392  | 510  | pF   | $V_{GS} = 0\text{ V}$ , $V_{DS} = 500\text{ V}$ , $f = 250\text{ kHz}$                                                         |
| Output charge <sup>6)</sup>                                | $Q_{oss}$   | -      | 352  | 458  | nC   | calculation based on $C_{oss}$                                                                                                 |
| Effective output capacitance, energy related <sup>7)</sup> | $C_{o(er)}$ | -      | 505  | -    | pF   | $V_{GS} = 0\text{ V}$ , $V_{DS} = 0..500\text{ V}$                                                                             |
| Effective output capacitance, time related <sup>8)</sup>   | $C_{o(tr)}$ | -      | 704  | -    | pF   | $I_D = \text{constant}$ , $V_{GS} = 0\text{ V}$ , $V_{DS} = 0..500\text{ V}$                                                   |
| Turn-on delay time                                         | $t_{d(on)}$ | -      | 22   | -    | ns   | $V_{DD} = 500\text{ V}$ , $V_{GS} = 0/18\text{ V}$ ,<br>$I_D = 90.3\text{ A}$ , $R_{G,ext} = 1.8\text{ }\Omega$ ; see table 10 |

**Table 6 Dynamic characteristics**

External parasitic elements (PCB layout) influence switching behavior significantly. Stray inductances and coupling capacitances must be minimized. For layout recommendations please use provided application notes or contact Infineon sales office.

| Parameter           | Symbol       | Values |      |      | Unit | Note/ Test Condition                                                                                                       |
|---------------------|--------------|--------|------|------|------|----------------------------------------------------------------------------------------------------------------------------|
|                     |              | Min.   | Typ. | Max. |      |                                                                                                                            |
| Rise time           | $t_r$        | -      | 30   | -    | ns   | $V_{DD} = 500 \text{ V}$ , $V_{GS} = 0/18 \text{ V}$ ,<br>$I_D = 90.3 \text{ A}$ , $R_{G,ext} = 1.8 \Omega$ ; see table 10 |
| Turn-off delay time | $t_{d(off)}$ | -      | 50   | -    | ns   | $V_{DD} = 500 \text{ V}$ , $V_{GS} = 0/18 \text{ V}$ ,<br>$I_D = 90.3 \text{ A}$ , $R_{G,ext} = 1.8 \Omega$ ; see table 10 |
| Fall time           | $t_f$        | -      | 16   | -    | ns   | $V_{DD} = 500 \text{ V}$ , $V_{GS} = 0/18 \text{ V}$ ,<br>$I_D = 90.3 \text{ A}$ , $R_{G,ext} = 1.8 \Omega$ ; see table 10 |

6) Maximum specification is defined by calculated six sigma upper confidence bound

7)  $C_{o(er)}$  is a fixed capacitance that gives the same stored energy as  $C_{oss}$  while  $V_{DS}$  is rising from 0 to 500 V.

8)  $C_{o(tr)}$  is a fixed capacitance that gives the same charging time as  $C_{oss}$  while  $V_{DS}$  is rising from 0 to 500 V.

**Table 7 Gate charge characteristics**

| Parameter                     | Symbol       | Values |      |      | Unit | Note/ Test Condition                                                                      |
|-------------------------------|--------------|--------|------|------|------|-------------------------------------------------------------------------------------------|
|                               |              | Min.   | Typ. | Max. |      |                                                                                           |
| Plateau gate to source charge | $Q_{GS(pl)}$ | -      | 50   | -    | nC   | $V_{DD} = 500 \text{ V}$ , $I_D = 90.3 \text{ A}$ , $V_{GS} = 0 \text{ to } 18 \text{ V}$ |
| Gate to drain charge          | $Q_{GD}$     | -      | 45   | -    | nC   | $V_{DD} = 500 \text{ V}$ , $I_D = 90.3 \text{ A}$ , $V_{GS} = 0 \text{ to } 18 \text{ V}$ |
| Total gate charge             | $Q_G$        | -      | 178  | -    | nC   | $V_{DD} = 500 \text{ V}$ , $I_D = 90.3 \text{ A}$ , $V_{GS} = 0 \text{ to } 18 \text{ V}$ |

**Table 8 Reverse diode characteristics**

| Parameter                                    | Symbol    | Values |            |      | Unit | Note/ Test Condition                                                                                                                                                                                                       |
|----------------------------------------------|-----------|--------|------------|------|------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                              |           | Min.   | Typ.       | Max. |      |                                                                                                                                                                                                                            |
| Drain-source reverse voltage                 | $V_{SD}$  | -      | 3.9        | 5.3  | V    | $V_{GS} = 0 \text{ V}$ , $I_S = 90.3 \text{ A}$ , $T_j = 25 \text{ }^\circ\text{C}$                                                                                                                                        |
| MOSFET forward recovery time                 | $t_{fr}$  | -      | 47<br>26   | -    | ns   | $V_{DD} = 500 \text{ V}$ , $I_S = 90.3 \text{ A}$ ,<br>$di_S/dt = 1000 \text{ A}/\mu\text{s}$ ; see table 9<br>$V_{DD} = 500 \text{ V}$ , $I_S = 90.3 \text{ A}$ ,<br>$di_S/dt = 4000 \text{ A}/\mu\text{s}$ ; see table 9 |
| MOSFET forward recovery charge <sup>9)</sup> | $Q_{fr}$  | -      | 418<br>677 | -    | nC   | $V_{DD} = 500 \text{ V}$ , $I_S = 90.3 \text{ A}$ ,<br>$di_S/dt = 1000 \text{ A}/\mu\text{s}$ ; see table 9<br>$V_{DD} = 500 \text{ V}$ , $I_S = 90.3 \text{ A}$ ,<br>$di_S/dt = 4000 \text{ A}/\mu\text{s}$ ; see table 9 |
| MOSFET peak forward recovery current         | $I_{frm}$ | -      | 18<br>52   | -    | A    | $V_{DD} = 500 \text{ V}$ , $I_S = 90.3 \text{ A}$ ,<br>$di_S/dt = 1000 \text{ A}/\mu\text{s}$ ; see table 9<br>$V_{DD} = 500 \text{ V}$ , $I_S = 90.3 \text{ A}$ ,<br>$di_S/dt = 4000 \text{ A}/\mu\text{s}$ ; see table 9 |

<sup>9)</sup>  $Q_{fr}$  includes  $Q_{oss}$

5 Electrical characteristics diagrams






Diagram 5: Typ. output characteristics




$I_{DS}=f(V_{DS})$ ;  $T_j=25\text{ °C}$ ; parameter:  $V_{GS}$

Diagram 6: Typ. output characteristics




$I_{DS}=f(V_{DS})$ ;  $T_j=175\text{ °C}$ ; parameter:  $V_{GS}$

Diagram 7: Typ. drain-source on-state resistance



$R_{DS(on)}=f(I_{DS})$ ;  $T_j=125\text{ °C}$ ; parameter:  $V_{GS}$

Diagram 8: Drain-source on-state resistance



$R_{DS(on)}=f(T_j)$ ;  $I_D=90.3\text{ A}$ ;  $V_{GS}=18\text{ V}$






Diagram 13: Avalanche energy




$E_{AS}=f(T_J); I_D=34.7\text{ A}; V_{DD}=50\text{ V}$

Diagram 14: Drain-source breakdown voltage




$V_{DSS}=f(T_J); I_D=3.24\text{ mA}$

Diagram 15: Typ. capacitances




$C=f(V_{DS}); V_{GS}=0\text{ V}; f=250\text{ kHz}$

Diagram 16: Typ. Coss stored energy



$E_{OSS}=f(V_{DS})$

**Diagram 17: Typ. Qoss output charge**

6 Test Circuits

Table 9 Body diode characteristics (CoolSiC)




Table 10 Switching times (CoolSiC)



Table 11 Unclamped inductive load



7 Package Outlines



NOTES:  
DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURRS

| PACKAGE - GROUP<br>NUMBER: PG-T0247-4-U02 |             |       |            |             |       |
|-------------------------------------------|-------------|-------|------------|-------------|-------|
| DIMENSIONS                                | MILLIMETERS |       | DIMENSIONS | MILLIMETERS |       |
|                                           | MIN.        | MAX.  |            | MIN.        | MAX.  |
| A                                         | 4.90        | 5.10  | E          | 15.70       | 15.90 |
| A1                                        | 2.31        | 2.51  | E1         | 13.10       | 13.50 |
| A2                                        | 1.90        | 2.10  | E2         | 2.40        | 2.60  |
| A3                                        | 0.05        | 0.25  | e          | 5.08        |       |
| b                                         | 1.10        | 1.30  | e1         | 2.79        |       |
| b1                                        | 0.65        | 0.79  | e2         | 2.54        |       |
| b2                                        | ---         | 0.20  | N          | 4           |       |
| b3                                        | 1.34        | 1.44  | L          | 19.80       | 20.10 |
| c                                         | 0.58        | 0.66  | øP         | 3.50        | 3.70  |
| D                                         | 20.90       | 21.10 | øP1        | 7.00        | 7.40  |
| D1                                        | 16.25       | 16.85 | øP2        | 2.40        | 2.60  |
| D2                                        | 1.05        | 1.35  | Q          | 5.60        | 6.00  |
| D3                                        | 24.97       | 25.27 | S          | 6.15        |       |
| D4                                        | 4.90        | 5.10  | T          | 9.80        | 10.20 |
|                                           |             |       | U          | 6.00        | 6.40  |

Figure 1 Outline PG-T0247-4, dimensions in mm

## 8 Appendix A

**Table 12**    **Related Links**

- [IFX CoolSiC CoolSiC™ Automotive Power Device 750 V G1 Webpage](#)
- [IFX CoolSiC CoolSiC™ Automotive Power Device 750 V G1 Application Note](#)
- [IFX CoolSiC CoolSiC™ Automotive Power Device 750 V G1 Simulation Model](#)
- [IFX Design tools](#)

## Revision History

AIMZA75R008M1H

### Revision 2024-07-29, Rev. 2.0

Previous Revision

| Revision | Date       | Subjects (major changes since last revision) |
|----------|------------|----------------------------------------------|
| 2.0      | 2024-07-29 | Release of final version                     |

#### Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**We Listen to Your Comments** Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to: [erratum@infineon.com](mailto:erratum@infineon.com)

#### Published by

Infineon Technologies AG  
81726 München, Germany  
© 2024 Infineon Technologies AG  
All Rights Reserved.

#### Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

#### Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

#### Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office. Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.