



TAOGLAS®



Datasheet

2.4/5.8GHz Terminal Mount Antenna

Part No:
GW.53.A151

Description

2.4/5.8GHz Terminal Mount Antenna RP-SMA(M) Straight

Features:

- 2.4/5.8GHz Band Operation
- Small Factor
- RP-SMA(M) Straight Connector
- IP67 Rated Enclosure
- Dimensions: $\varnothing 8.5\text{mm}$ x 35.8mm
- RoHS & Reach Compliant

1.	Introduction	2
2.	Specification	3
3.	Antenna Characteristics	4
4.	Radiation Patterns	7
5.	Mechanical Drawing	14
6.	Packaging	15
	Changelog	16

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Ireland & USA
ISO 9001:2015
Certified



Taiwan
ISO 9001:2015
Certified



1. Introduction



The GW.53 is one of a range of super small form factor, lightweight, IP67 rated terminal mount antennas from Taoglas. It is ideal for wireless applications operating on Bluetooth® and Wireless LAN bands covering 2.4/5.8GHz. Its robust silicone enclosure is engineered to perform in the most challenging of external environments when connecting IoT devices to smart grid and smart monitoring applications.

With its IP67 rating, the GW.53 can withstand dust, dirt, and even complete submersion in water, making it the perfect choice for any IoT application that demands both reliable connectivity and extreme durability. Whether you're connecting sensors for remote agricultural, monitoring equipment in industrial settings, or building the infrastructure for smart cities, the GW.53 is a great solution.

If you are looking for an antenna that's small, tough, and versatile, look no further than the GW.53. Contact your regional Taoglas Customer Services Team for more information or to discuss your project.

2. Specification

Wi-Fi Electrical							
Band		Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern
Wi-Fi 2.4~2.5GHz	In Free space	21.9	-6.5	-0.61	50 Ω	Linear	Omni
	On 15x9cm Ground plane (Long side)	56.9	-2.45	3.35			
	On 9x15cm Ground plane (Short side)	53	-2.75	4.03			
Wi-Fi 5.1~5.85GHz	In Free space	43.5	-3.62	1.13			
	On 15x9cm Ground plane (Long side)	64.0	-1.94	6.51			
	On 9x15cm Ground plane (Short side)	60.5	-2.18	3.84			


Mechanical	
Dimensions	ø8.5mm x 35.8mm
Weight	5.5g
Material	Silicone
Connector	RP-SMA(M)

Environmental	
Operating Temperature	-40°C ~ +85°C
Waterproof Rating	IP67

3. Antenna Characteristics

3.1 Test Setup

AUT



Vector Network Analyzer




In Free Space


On 15x9cm Ground plane

On 9x15cm Ground plane


3.2 Return Loss




3.3 Efficiency



3.4 Average Gain





3.5 Peak Gain



4. Radiation Patterns

4.1 Test Setup




In Free Space


On 15x9cm Ground plane

On 9x15cm Ground plane


4.2 GW.53.A151 - Patterns at 2450 MHz in Free Space




XZ Plane




YZ Plane




XY Plane




4.3 GW.53.A151 - Patterns at 5550 MHz in Free Space




XZ Plane




YZ Plane




XY Plane




4.4 GW.53.A151 - Patterns at 2450 MHz on 15x9cm ground plane




XZ Plane




YZ Plane




XY Plane




4.5 GW.53.A151 - Patterns at 5550 MHz on 15x9cm ground plane




XZ Plane




YZ Plane




XY Plane




4.6 GW.53.A151 - Patterns at 2450 MHz on 9x15cm ground plane




XZ Plane




YZ Plane




XY Plane




4.7 GW.53.A151 - Patterns at 5550 MHz on 9x15cm ground plane




XZ Plane




YZ Plane



XY Plane




5. Mechanical Drawing




6. Packaging

60pcs GW.53.A151 per Tray
Tray dimension: 300x140x18mm
Weight: 0.38Kg



1200pcs per Carton
Carton dimensions: 328x296x282mm
Weight: 8.5Kg



Changelog for the datasheet

SPE-24-8-016 – GW.53.A151

Revision: A (First Release)	
Date:	2024-02-13
Notes:	
Author:	Cesar Sousa

Previous Revisions

Rev. 01

Rev. 02

Rev. 03

Rev. 04

Rev. 05

Rev. 06

Rev. 07

Rev. 08

Rev. 09

Rev. 10

Rev. 11

Rev. 12

Rev. 13

Rev. 14

Rev. 15

Rev. 16

Rev. 17

Rev. 18

Rev. 19

Rev. 20

Rev. 21

Rev. 22

Rev. 23

Rev. 24

Rev. 25

Rev. 26

Rev. 27

Rev. 28

Rev. 29

Rev. 30

Rev. 31

Rev. 32

Rev. 33

Rev. 34

Rev. 35

Rev. 36

Rev. 37

Rev. 38

Rev. 39

Rev. 40

Rev. 41

Rev. 42

Rev. 43

Rev. 44

Rev. 45

Rev. 46

Rev. 47

Rev. 48

Rev. 49

Rev. 50

Rev. 51

Rev. 52

Rev. 53

Rev. 54

Rev. 55

Rev. 56

Rev. 57

Rev. 58

Rev. 59

Rev. 60

Rev. 61

Rev. 62

Rev. 63

Rev. 64

Rev. 65

Rev. 66

Rev. 67

Rev. 68

Rev. 69

Rev. 70

Rev. 71

Rev. 72

Rev. 73

Rev. 74

Rev. 75

Rev. 76

Rev. 77

Rev. 78

Rev. 79

Rev. 80

Rev. 81

Rev. 82

Rev. 83

Rev. 84

Rev. 85

Rev. 86

Rev. 87

Rev. 88

Rev. 89

Rev. 90

Rev. 91

Rev. 92

Rev. 93

Rev. 94

Rev. 95

Rev. 96

Rev. 97

Rev. 98

Rev. 99

Rev. 100

Rev. 101

Rev. 102

Rev. 103

Rev. 104

Rev. 105

Rev. 106

Rev. 107

Rev. 108

Rev. 109

Rev. 110

Rev. 111

Rev. 112

Rev. 113

Rev. 114

Rev. 115

Rev. 116

Rev. 117

Rev. 118

Rev. 119

Rev. 120

Rev. 121

Rev. 122

Rev. 123

Rev. 124

Rev. 125

Rev. 126

Rev. 127

Rev. 128

Rev. 129

Rev. 130

Rev. 131

Rev. 132

Rev. 133

Rev. 134

Rev. 135

Rev. 136

Rev. 137

Rev. 138

Rev. 139

Rev. 140

Rev. 141

Rev. 142

Rev. 143

Rev. 144

Rev. 145

Rev. 146

Rev. 147

Rev. 148

Rev. 149

Rev. 150

Rev. 151

Rev. 152

Rev. 153

Rev. 154

Rev. 155

Rev. 156

Rev. 157

Rev. 158

Rev. 159

Rev. 160

Rev. 161

Rev. 162

Rev. 163

Rev. 164

Rev. 165

Rev. 166

Rev. 167

Rev. 168

Rev. 169

Rev. 170

Rev. 171

Rev. 172

Rev. 173

Rev. 174

Rev. 175

Rev. 176

Rev. 177

Rev. 178

Rev. 179

Rev. 180

Rev. 181

Rev. 182

Rev. 183

Rev. 184

Rev. 185

Rev. 186

Rev. 187

Rev. 188

Rev. 189

Rev. 190

Rev. 191

Rev. 192

Rev. 193

Rev. 194

Rev. 195

Rev. 196

Rev. 197

Rev. 198

Rev. 199

Rev. 200

Rev. 201

Rev. 202

Rev. 203

Rev. 204

Rev. 205

Rev. 206

Rev. 207

Rev. 208

Rev. 209

Rev. 210

Rev. 211

Rev. 212

Rev. 213

Rev. 214

Rev. 215

Rev. 216

Rev. 217

Rev. 218

Rev. 219

Rev. 220

Rev. 221

Rev. 222

Rev. 223

Rev. 224

Rev. 225

Rev. 226

Rev. 227

Rev. 228

Rev. 229

Rev. 230

Rev. 231

Rev. 232

Rev. 233

Rev. 234

Rev. 235

Rev. 236

Rev. 237

Rev. 238

Rev. 239

Rev. 240

Rev. 241

Rev. 242

Rev. 243

Rev. 244

Rev. 245

Rev. 246

Rev. 247

Rev. 248

Rev. 249

Rev. 250

Rev. 251

Rev. 252

Rev. 253

Rev. 254

Rev. 255

Rev. 256

Rev. 257

Rev. 258

Rev. 259

Rev. 260

Rev. 261

Rev. 262

Rev. 263

Rev. 264

Rev. 265

Rev. 266

Rev. 267

Rev. 268

Rev. 269

Rev. 270

Rev. 271

Rev. 272

Rev. 273

Rev. 274

Rev. 275

Rev. 276

Rev. 277

Rev. 278

Rev. 279

Rev. 280

Rev. 281

Rev. 282

Rev. 283

Rev. 284

Rev. 285

Rev. 286

Rev. 287

Rev. 288

Rev. 289

Rev. 290

Rev. 291

Rev. 292

Rev. 293

Rev. 294

Rev. 295

Rev. 296

Rev. 297

Rev. 298

Rev. 299



www.taoglas.com

