OSRAM KW C3L5L1.TE

Datasheet

Discontinued

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved


Downloaded from Arrow.com.

OSRAM

OSLON® Submount CL

KW C3L5L1.TE

The OSLON Submount CL is able to meet a wide range of requirements in terms of output and adaptability to ambient conditions. It offers a uniform light pattern, thermal stability and great brightness. The high-flux LED is available with two and three chips.



Applications

- Dynamic Forward Lighting
- Static Forward Lighting

Features

- Package: compact lightsource in multi chip on board technology
- Chip technology: UX:3
- Typ. Radiation: 120° (Lambertian emitter)
- Color: Cx = 0.32, Cy = 0.33 acc. to CIE 1931 (● white)
- Corrosion Robustness Class: 3A
- Qualifications: The product qualification test plan is based on the guidelines of AEC-Q101-REV-C, Stress Test Qualification for Automotive Grade Discrete Semiconductors.
- ESD: 8 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)

Discontinued

Downloaded from Arrow.com.

Ordering Information

Type	Luminous Flux [1] I_F = 1000 mA Φ_V	Mounting methode	Ordering Code
KW C3L5L1.TE-Z6QF6-ebvF46fcbB46	849 ... 1250 lm	Top	Q65112A4359
KW C3L5L1.TE-Z6QF9-ebvF46fcbB46	849 ... 1490 lm	Top	Q65112A9362

Discontinued

Downloaded from Arrow.com.

Maximum Ratings

Parameter	Symbol		Values
Operating Temperature	T_{op}	min. max.	-40 °C 135 °C
Storage Temperature	T_{stg}	min. max.	-40 °C 135 °C
Junction Temperature	T_j	max.	150 °C
Junction temperature for short time applications*	T_j	max.	165 °C
Case Temperature	T_{case}	max.	135 °C
Forward Current T_C = 25 °C	I_F	min. max.	50 mA 1500 mA
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)	V_{ESD}		8 kV
Reverse current [2)]	I_R	max.	200 mA

*The median lifetime (L70/B50) for Tj =165°C is 200h.
For Tc testing, please refer to Application Note: “AN085 Thermal measurement point of LEDs”

Discontinued

Downloaded from Arrow.com.

Characteristics

I_F = 1000 mA; T_C = 25 °C

Parameter	Symbol		Values
Chromaticity Coordinate [3]	Cx	typ.	0.32
	Cy	typ.	0.33
Viewing angle at 50% I_V	2φ	typ.	120 °
Radiating surface	A_{color}	typ.	3.3 mm²
Forward Voltage [4]	V_F	min.	8.70 V
I_F = 1000 mA		typ.	9.35 V
		max.	10.70 V
Reverse voltage (ESD device)	$V_{R\ ESD}$	min.	45 V
Reverse voltage [2]	V_R	max.	1.2 V
I_R = 20 mA			
Real thermal resistance junction/board [5]	$R_{thJB\ real}$	typ.	1.6 K / W
		max.	2.6 K / W
Electrical thermal resistance junction/board [5]	$R_{thJB\ elec.}$	typ.	1.1 K / W
with efficiency η_e = 34 %		max.	1.7 K / W

Discontinued

Downloaded from Arrow.com.


Brightness Groups

Group	Luminous Flux [1] I_F = 1000 mA min. Φ_V	Luminous Flux [1] I_F = 1000 mA max. Φ_V
6QF	849 lm	949 lm
7Q	900 lm	1000 lm
7QF	949 lm	1060 lm
8Q	1000 lm	1120 lm
8QF	1060 lm	1180 lm
5R	1120 lm	1250 lm
5RF	1180 lm	1320 lm
6R	1250 lm	1400 lm
6RF	1320 lm	1490 lm

Discontinued

Downloaded from Arrow.com.

Chromaticity Coordinate Groups [3)]



Chromaticity Coordinate Groups [3)]

Group	Cx	Cy	Group	Cx	Cy
ebvF46	0.3104	0.3234	ebzB46	0.3190	0.3430
	0.3199	0.3325		0.3298	0.3526
	0.3212	0.3175		0.3299	0.3361
	0.3127	0.3093		0.3203	0.3274
ebxD46	0.3145	0.3330	fcbB46	0.3241	0.3534
	0.3246	0.3424		0.3355	0.3633
	0.3253	0.3266		0.3350	0.3460
	0.3163	0.3181		0.3248	0.3370

Discontinued

Downloaded from Arrow.com.

Group Name on Label

Example: 5R-ebvF46


Brightness	Color Chromaticity
5R	ebvF46

Discontinued

Downloaded from Arrow.com.

Relative Spectral Emission 6)


$\Phi_{rel} = f(\lambda)$; I_F = 1000 mA; T_C = 25 °C



Note: Percentage of red: >5% acc. to ECE regulation
Percentage of UV: <10-5 W/lm acc. to ECE regulation

Radiation Characteristics 6)

$I_{rel} = f(\phi)$; T_C = 25 °C




Discontinued

Downloaded from Arrow.com.


Forward current 6), 7)

$I_F = f(V_F)$; T_C = 25 °C




Relative Luminous Flux 6), 7)

$\Phi_v/\Phi_v(1000\ mA) = f(I_F)$; T_C = 25 °C



Chromaticity Coordinate Shift 6)

Cx, Cy = $f(I_F)$; T_C = 25 °C




Discontinued

Downloaded from Arrow.com.


Forward Voltage [6]

$\Delta V_F = V_F - V_F(25\ °C) = f(T_j);\ I_F = 1000\ mA$




Relative Luminous Flux [6]

$\Phi_v/\Phi_v(25\ °C) = f(T_j);\ I_F = 1000\ mA$



Chromaticity Coordinate Shift [6]

Cx, Cy = $f(T_j)$; I_F = 1000 mA




Discontinued

Downloaded from Arrow.com.


Max. Permissible Forward Current [5)]

IF = f (T); 0.7 * ΦV min. of bin 6Q; Rth real max.




Permissible Pulse Handling Capability

$I_F = f(t_p)$; D: Duty cycle



Permissible Pulse Handling Capability


$I_F = f(t_p)$; D: Duty cycle



Discontinued

Downloaded from Arrow.com.

Dimensional Drawing [8)]



Further Information:

Approximate Weight: 35.0 mg


Corrosion test: Class: 3A
Test condition: 40°C / 90 % RH / 15 ppm H_2S / 14 days (stricter than IEC 60068-2-43)

ESD advice: The device is protected by ESD device which is connected in parallel to the Chip.

Discontinued

Downloaded from Arrow.com.


Electrical Internal Circuit



Discontinued

Downloaded from Arrow.com.

Taping [8)]





C63062-A4291-B2-01

Discontinued

Downloaded from Arrow.com.

Tape and Reel [9)]





Leader: min. 400mm*
Trailer: min. 160mm*
*)Dimensions acc. to IEC 60286-3; EIA 481-E


Reel Dimensions

A	W	N_{min}	W_1	$W_{2\,max}$	Pieces per PU
180 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	2000

Discontinued


Downloaded from Arrow.com.

Barcode-Product-Label (BPL)



OHA04563

Dry Packing Process and Materials [8)]




OHA00539

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

Discontinued

Downloaded from Arrow.com.



wire bonding scheme:

CB = contact block


Active Area = bond area

Probing Area = used by OSRAM OS

Discontinued

Downloaded from Arrow.com.

Type Designation System



Discontinued

Downloaded from Arrow.com.

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **moderate risk (exposure time 0.25 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers avoid device exposure to aggressive substances during storage, production, and use.

For further application related information please visit https://ams-osram.com/support/application-notes

Discontinued

Downloaded from Arrow.com.

Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics.
Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.
For information on the types in question please contact our Sales Organization.
If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.
Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

Discontinued

Downloaded from Arrow.com.

Glossary

1) **Brightness:** Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of ±8 % and an expanded uncertainty of ±11 % (acc. to GUM with a coverage factor of k = 3).

2) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.

3) **Chromaticity coordinate groups:** Chromaticity coordinates are measured during a current pulse of typically 25 ms, with an internal reproducibility of ±0.005 and an expanded uncertainty of ±0.01 (acc. to GUM with a coverage factor of k = 3).

4) **Forward Voltage:** The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of ±0.05 V and an expanded uncertainty of ±0.1 V (acc. to GUM with a coverage factor of k = 3).

5) **Thermal Resistance:** Rth max is based on statistic values (6σ) used for Derating.

6) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.

7) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.

8) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.

9) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Discontinued

Downloaded from Arrow.com.

Revision History

Version	Date	Change
1.4	2020-06-04	Features Ordering Information Brightness Groups Further Information Reel Dimensions Dry Packing Process and Materials Schematic Transportation Box Dimensions of Transportation Box Disclaimer
1.5	2021-07-26	Features
1.6	2024-02-08	New Layout Applications
1.7	2024-03-07	Discontinued

Discontinued

Downloaded from Arrow.com.

Discontinued

EU RoHS and China RoHS compliant product
此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，
不含有毒有害物质或元素。

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

Downloaded from Arrow.com.