

AW-CU479

IEEE802.15.4 Wireless Microcontroller Zigbee 3.0 Stamp LGA Module (M06)

Datasheet

Rev. H

DF

(For STD)

1

FORM NO.: FR2-015_A

Responsible Department : WBU

Expiry Date: Forever

The information contained herein is the exclusive property of AzureWave and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of AzureWave.

Features

Benefits

- Single chip device to run stack and application
- Very low current solution for long battery life; over 10 years
- Very low RX current for low standby power of mains powered nodes
- Integrated power amplifier for long range and robust communication
- High tolerance to interference from other 2.4 GHz radio sources
- Supports multiple network stacks
- Highly featured 32-bit RISC CPU for high performance and low power
- Large embedded Flash memory to enable over-the-air firmware updates without external Flash memory
- System BOM is low in component count and cost
- Flexible sensor interfacing options

Radio

- Radio link budget 106 dB
- Compensation for temperature drift of crystal oscillator frequency
- 128-bit AES security processor
- MAC accelerator with packet formatting, CRCs, address check, auto-acks, timers
- Integrated ultra low-power RC sleep oscillator (0.7uA)
- 2.0 V to 3.6 V battery operation
- Deep sleep current 50 nA (wake-up from IO)
- Antenna diversity (Auto RX)

Microcontroller

- 32-bit RISC CPU; 1 MHz to 32 MHz clock speed
- Variable instruction width for high coding efficiency
- Multi-stage instruction pipeline
- 512 kB Flash
- 32 kB RAM
- 4 kB EEPROM
- Data EEPROM with guaranteed 100 k write operations
- Zigbee PRO stack with Home Automation, Light Link and Smart Energy profiles
- 2-wire I2C-bus compatible serial interface; can operate as either master or slave
- 5 x PWM (4 timers, 1 timer/counter)
- 2 low-power sleep counters
- 2 x UARTs
- SPI-bus master and slave port, 3 selects
- Supply voltage monitor with 8 programmable thresholds
- 6-input 10-bit ADC, comparator
- Battery and temperature sensors
- Watchdog and Supply Voltage Monitor (SVM)
- Up to 20 Digital IO (DIO) pins

Applications

- Robust and secure low-power wireless applications
- Zigbee 3.0
- Internet of Things (IoT)
- Zigbee Smart Energy networks
- Zigbee Light Link networks
- Zigbee Home Automation networks



- Toys and gaming peripherals
- Energy harvesting

Revision History

Document NO: R2-2479-DST-01

| Version | Revision Date | DCN NO. | Description | Initials | Approved |
|---------|---------------|-----------|--|---------------|----------|
| A | 2020/4/13 | DCN017089 | Initial Version | Shihhua Huang | NC Chen |
| B | 2020/5/6 | DCN017357 | Added more info about chapter 3.2 | Shihhua Huang | NC Chen |
| C | 2020/6/16 | DCN017621 | <ul style="list-style-type: none"> ● Modify pin table ● Modify Storage Temperature | Shihhua Huang | NC Chen |
| D | 2020/8/11 | DCN018074 | <ul style="list-style-type: none"> ● Added certification info at chapter 1.3.1 ● Added power consumption | Shihhua Huang | NC Chen |
| E | 2020/12/24 | DCN019674 | <ul style="list-style-type: none"> ● Update pin table description | Shihhua Huang | NC Chen |
| F | 2021/4/14 | DCN021286 | *Changed to new format <ul style="list-style-type: none"> ● Modify Block Diagram | Shihhua Huang | NC Chen |
| G | 2021/5/12 | DCN021749 | <ul style="list-style-type: none"> ● Correct the typo on chapter 1.3.1 certification info | Shihhua Huang | NC Chen |
| H | 2021/11/24 | DCN024241 | <ul style="list-style-type: none"> ● Modify chapter 1.3.2 TX power tolerance | Shihhua Huang | NC Chen |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |

Table of Contents


| | |
|--|----|
| Revision History..... | 4 |
| Table of Contents..... | 5 |
| 1. Introduction | 6 |
| 1.1 Product Overview | 6 |
| 1.2 Block Diagram..... | 7 |
| 1.3 Specifications Table | 8 |
| 1.3.1 General | 8 |
| 1.3.2 Zigbee..... | 8 |
| 1.3.3 Operating Conditions..... | 9 |
| 2. Pin Definition | 10 |
| 2.1 Pin Map..... | 10 |
| 2.2 Pin Table..... | 11 |
| 3. Electrical Characteristics | 13 |
| 3.1 Absolute Maximum Ratings | 13 |
| 3.2 Recommended Operating Conditions | 13 |
| 3.3 Digital IO Pin DC Characteristics..... | 13 |
| 3.4 AC characteristics | 14 |
| 3.4.1 Reset and Supply Voltage Monitor | 14 |
| 3.4.2 SPI-bus master timing | 15 |
| 3.4.3 SPI-bus slave timing..... | 16 |
| 3.5 Power Consumption* | 17 |
| 4. Mechanical Information | 18 |
| 4.1 Mechanical Drawing | 18 |
| 5. Packaging Information | 19 |

1. Introduction

1.1 Product Overview

AzureWave Technologies, Inc. introduces the pioneer of the IEEE 802.15.4 Zigbee module --- AW-CU479. The AW-CU479 wireless microcontroller that provides a fully integrated solution for applications that use the IEEE802.15.4 standard in the 2.4 GHz to 2.5 GHz ISM frequency band, including Zigbee PRO applications based on the Smart Energy, Light Link and Home Automation profiles. The AW-CU479 features 512 kB embedded Flash, 32 kB RAM and 4 kB EEPROM memory. Applications that transfer data wirelessly tend to be more complex than applications for wired solutions. Wireless protocols make stringent demands on frequencies, data formats, and timing of data transfers, security and other issues. Application development must consider the requirements of the wireless network in addition to the product functionality and user interfaces. To minimize this complexity, AzureWave provides a series of software libraries and interfaces that control the transceiver and peripherals of the AW-CU479. These libraries and interfaces remove the need for the developer to understand wireless protocols and greatly simplifies the programming complexities of power modes, interrupts and hardware functionality. In view of the above, we do not provide the AW-CU479 register details in this data sheet. The device includes a wireless transceiver, RISC CPU, on-chip memory and an extensive range of peripherals.

1.2 Block Diagram



AW-CU479 BLOCK DIAGRAM

1.3 Specifications Table

1.3.1 General

| Features | Description | | |
|---------------------------|--|----------------|----------------|
| Product Description | IEEE 802.15.4 Zigbee 3.0 Module (Stamp LGA) | | |
| Major Chipset | JN5169 (QFN 40p) | | |
| Host Interface | Zigbee <ul style="list-style-type: none">● UART | | |
| Dimension | 16mm x 30mm x 2.95mm (Tolerance remarked in mechanical drawing) | | |
| Form factor | Stamp LGA module | | |
| Antenna | I-PEX MHF1 Connector Receptacle (20279) Main : Zigbee → TX/RX | | |
| Certification information | AW-CU479 are FCC, IC and ANATEL certified. | | |
| | FCC ID | IC ID | ANATEL ID |
| | XXMJN5169M6V2 | 8764A-JN5169M6 | 04453-16-09529 |
| Weight | 2.1437g | | |

1.3.2 Zigbee

| Features | Description | | | | |
|--------------------------------------|---|-----|-----|-----|------|
| WLAN Standard | IEEE 802.15.4 1T1R | | | | |
| WLAN VID/PID | N/A | | | | |
| WLAN SVID/SPID | N/A | | | | |
| Frequency Range | 2.4 GHz : 2.405 ~ 2.480 GHz | | | | |
| Modulation | O-QPSK | | | | |
| Number of Channels | 2.4GHz ■ USA, NORTH AMERICA, Canada and Taiwan – 11 ~ 24 ■ China, Australia, Most European Countries – 11 ~ 26 | | | | |
| Output Power (Board Level Limit)* | 2.4G | | | | |
| | | Min | Typ | Max | Unit |
| | 15.4 (0.25Mbps) @EVM<35% | 19 | 22 | 25 | dBm |

| | | | | | |
|-----------------------------|---|-----|-----|-----|------|
| Receiver Sensitivity | 2.4G | | | | |
| | | Min | Typ | Max | Unit |
| | 15.4 (0.25Mbps) | | -97 | -94 | dBm |
| Data Rate | Zigbee: 802.15.4: 0.25Mbps | | | | |
| Security | ■ 128-bit AES-CCM modes as specified by the IEEE802.15.4 2006 standard. | | | | |


* If you have any certification questions about output power please contact FAE directly.

1.3.3 Operating Conditions

| Features | Description |
|------------------------------|------------------------------------|
| Operating Conditions | |
| Voltage | Power supply for host: 2.0V ~ 3.6V |
| Operating Temperature | -40°C ~ 85°C |
| Operating Humidity | less than 85%R.H. |
| Storage Temperature | -40°C ~ 125°C |
| Storage Humidity | less than 60%R.H. |
| ESD Protection | |
| Human Body Model | 2KV |
| Changed Device Model | 1000V |

2. Pin Definition

2.1 Pin Map



AW-CU479 Pin Map (Top View)

2.2 Pin Table

| Pin No | Definition | Basic Description | Voltage | Type |
|--------|------------|---------------------------------------|---------|------|
| 1 | ADC1 | ADC input | | I |
| 2 | SPICLK | SPI-bus master clock output | | O |
| 3 | SPIMISO | SPI-bus Master In, Slave Out input | | I/O |
| 4 | SPIMOSI | SPI-bus Master Out Slave In output | | I/O |
| 5 | SSZ | SPI-bus master Select Output 0 | | I/O |
| 6 | DIO0 | DIO0 | | I/O |
| 7 | DIO1 | DIO1 | | I/O |
| 8 | DIO2 | DIO2 | | I/O |
| 9 | DIO3 | DIO3 | | I/O |
| 10 | DIO4 | DIO4 UART 0 clear to send input | | I/O |
| 11 | DIO5 | DIO5 UART 0 request to send output | | I/O |
| 12 | DIO6 | DIO6 UART 0 transmit data output | | I/O |
| 13 | DIO7 | DIO7 UART 0 receive data input | | I/O |
| 14 | DIO8 | DIO8 | | I/O |
| 15 | DIO9 | DIO9 | | I/O |
| 16 | DIO10 | DIO10 | | I/O |
| 17 | VDD | Supply voltage | | P |
| 18 | GND | Ground. | | GND |
| 19 | DIO11 | DIO11 | | I/O |

| | | | | |
|----|--------|-------------|--|-----|
| 20 | DIO12 | DIO12 | | I/O |
| 21 | DIO13 | DIO13 | | I/O |
| 22 | RESETN | Reset input | | I |
| 23 | DIO14 | DIO14 | | I/O |
| 24 | DIO15 | DIO15 | | I/O |
| 25 | DIO16 | DIO16 | | I/O |
| 26 | DIO17 | DIO17 | | I/O |
| 27 | ADC2 | ADC2 input | | I |

3. Electrical Characteristics

3.1 Absolute Maximum Ratings

| Symbol | Parameter | Conditions | Minimum | Maximum | Unit |
|----------------------|------------------------------|------------|---------|----------------------|------|
| V _{DD} | Power supply voltage | | -0.3 | 3.6 | V |
| V _{ADC1} | Voltage on pin ADC1 | | -0.3 | V _{DD} +0.3 | V |
| V _{IO(dig)} | Digital input/output voltage | | -0.3 | V _{DD} +0.3 | V |

3.2 Recommended Operating Conditions

| Symbol | Parameter | Minimum | Typical | Maximum | Unit |
|--------------------------------|----------------------|---------|---------|---------|------|
| V _{DD} ^[1] | Power supply voltage | 2 | -- | 3.6 | V |

[1] To reach the maximum TX power, 2.8 V is the minimum and 3.3V is maximum.

3.3 Digital IO Pin DC Characteristics

Table 1. Digital IO DC Characteristics

| Symbol | Parameter | Minimum | Typical | Maximum | Unit |
|---------------------|--------------------------|---------------------|---------|----------------------|------|
| V _{IH} | Input high voltage | 0.7*V _{DD} | -- | V _{DD} | V |
| V _{IL} | Input low voltage | -0.3 | -- | 0.27*V _{DD} | V |
| V _{hys(i)} | Input hysteresis voltage | | | | |

Table 2. Output on pins DIOx^[1]

| Symbol | Parameter | Minimum | Typical | Maximum | Unit |
|-----------------|---------------------|----------------------|---------|-----------------|------|
| V _{OH} | Output high voltage | V _{DD} -0.4 | -- | V _{DD} | V |
| V _{OL} | Output low voltage | 0 | -- | 0.4 | V |

[1] With x = 0, 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18 or 19.

3.4 AC characteristics

3.4.1 Reset and Supply Voltage Monitor




Fig 1. Internal Power-On Reset without showing Brown-Out





Fig 2. Externally applied reset

Table 3. Externally applied reset

| Symbol | Parameter | Conditions | Min | Typical | Max | Unit |
|----------------|----------------------------|---|--------------------|---------|-----|------|
| t_{rst} | Reset time | External reset pulse width to initiate reset sequence | 1 | | | us |
| V_{rst} | Reset voltage | External threshold voltage | $0.7 \cdot V_{DD}$ | | | V |
| $V_{th(POR)}$ | Power-on threshold voltage | Rise time >10ms | | | | |
| | | Rising | - | 1.44 | | V |
| | | Falling | - | 1.41 | | V |
| α spike | Spike rejection | Depth of pulse to trigger reset | | | | |
| | | 1us square wave | | 1.2 | | V |
| | | 10us triangular wave | | 1.3 | | V |
| T_{stab} | Stabilization time | Reset | | 180 | | us |

3.4.2 SPI-bus master timing



(1) With x = 0, 1 or 2.

Table 4. SPI-bus master timing

| Symbol | Parameter | Conditions | Min | Typical | Max | Unit |
|-------------|-------------------------|----------------------------------|------|---------|-----|------|
| T_{clk} | Clock period | | 62.5 | | | ns |
| $T_{su(D)}$ | Data input set-up time | 3.3V | 12.5 | | | ns |
| | | 2.7V | 13 | | | |
| | | 2.0V | 14 | | | |
| $T_{h(D)}$ | Data input hold time | | 0 | | | ns |
| $T_{d(Q)}$ | Data output delay time | On SPIMOSI | | | 15 | ns |
| $T_{su(S)}$ | Chip select set-up time | | 60 | | | ns |
| $T_{h(S)}$ | Chip select hold time | SPICLK = 16MHz | 30 | | | ns |
| | | SPICLK < 16MHz; mode = 0 or 2 | 0 | | | |
| | | SPICLK < 16MHz; mode = 1 or 3 | 60 | | | |

3.4.3 SPI-bus slave timing




Table 5. PERST# Timing Parameters


| Symbol | Parameter | Conditions | Min | Typical | Max | Unit |
|--------------|---------------------------------------|--|-----|---------|-----|------|
| T_{clk} | Clock period | | 125 | - | - | ns |
| t_{idle} | Idle time | | 125 | - | - | ns |
| $t_{su(D)}$ | Data input set-up time | | 10 | - | - | ns |
| $t_{h(D)}$ | Data input hold time | | 10 | - | - | ns |
| $t_{d(C-Q)}$ | Clock to data output delay time | SPISCLK falling edge to SPISMISO output delay time | - | - | 30 | ns |
| $t_{d(S-Q)}$ | Chip select to data output delay time | SPISSEL falling edge to SPISMISO output delay time | - | - | 30 | ns |
| $t_{su(S)}$ | Chip select set-up time | SPISSEL falling edge to SPISCLK rising edge delay time | 30 | - | - | ns |
| $t_{h(S)}$ | Chip select hold time | SPISCLK falling edge to SPISSEL rising edge delay time | 30 | - | - | ns |

3.5 Power Consumption*

| No. | Item | VDD_IN=3.3 V | |
|-----|---|--------------|----------|
| | | Max. | Avg. |
| 1 | Deep sleep mode | 1.7 uA | 0.207 uA |
| 2 | Sleep mode without memory retention (60seconds) | 2.09 uA | 0.819 uA |
| 3 | Transmit mode (23.8dBm) | 241 mA | 240 mA |
| 4 | Receive mode, maximum input level at 0 dBm | 22 mA | 21.9 mA |


4. Mechanical Information

4.1 Mechanical Drawing



5. Packaging Information

1. One reel can pack 600pcs 16x30 stamp LGA modules
2. One production label is pasted on the reel, one desiccant and one humidity indicator card are put on the reel




One desiccant

One production label


One humidity indicator card

3. One reel is put into the anti-static moisture barrier bag, and then one label is pasted on the bag



One production label

4. A bag is put into the anti-static pink bubble wrap



One anti-static pink bubble wrap

5. A bubble wrap is put into the inner box and then one label is pasted on the inner box



One production label

6. **3 inner boxes** could be put into one carton



7. Sealing the carton by AzureWave tape






8. One carton label and one box label are pasted on the carton. If one carton is not full, one balance label pasted on the carton

One carton label
出貨標籤

One box label
箱號標籤



One production label
生產標籤

| | |
|---|--|
| <p>Example of carton label (出貨標籤的範例)</p> |  |
| <p>Example of box label (箱號標籤)</p> |  |
| <p>Example of production label (生產標籤)</p> |  |



| | |
|------------------------------------|--|
| Example of balance label (尾數標籤) |  |
|------------------------------------|--|