


BETA Protecting Miniature Circuit Breakers

1

1





1/2	Product overview
	5SY and 5SP miniature circuit breakers
1/8	6000 A, 5SY6
1/11	10 000 A, 5SY4
1/15	10 000 A, high current, 5SP4
1/16	10 000 A, universal current, 5SP5, 5SY5
1/18	15 000 A, 5SY7
1/21	25 kA, 5SY8
1/24	5SJ6 ...-KS miniature circuit breakers with plug-in terminals
1/27	5SY6 0 miniature circuit breakers, 1+N in 1 MW
1/31	Additional components
	Busbars
1/40	5ST3 6, 5ST3 7 standard
1/48	Acc. to UL 508, 5ST3 7 ...-HG
1/52	5ST3 5 universal
1/57	Configuration and dimensioning
1/84	5SJ4 ...-HG miniature circuit breakers acc. to UL 489 and IEC, and accessories
1/98	SHU, 5SP3 main miniature circuit breakers
1/104	5SK9 circuit breaker terminals

BETA Protecting Miniature Circuit Breakers


Product overview

Overview

Devices		Page	Field of application	Standards	Used in		
					Non-resid. buildings	Residential buildings	Industry
	5SY and 5SP miniature circuit breakers	1/5	For all applications from 0.3 to 125 A with a rated switching capacity of 10 000 A and 15 000 A acc. to EN 60898. Applications for universal current and from 0.3 to 63 A, version 25 kA, acc. to EN 60947-2.	EN 60898 EN 60947-2	✓	✓	✓
	5SJ6 ...-KS miniature circuit breakers with plug-in terminal	1/24	For socket outlet and lighting circuits in all building installations. The plug-in terminals offer easy front connection for manual insertion of conductors, which considerably reduces mounting times.	EN 60898	✓	✓	✓
	5SY6 0 miniature circuit breakers 1+N in 1 MW	1/27	For socket outlet and lighting circuits in all building installations where a switchable neutral conductor is required. The miniature circuit breaker 1+N saves space in the distribution board.	EN 60898	✓	✓	✓
	Additional components	1/31	Auxiliary switches, fault signal contacts, shunt trips, undervoltage releases for higher plant availability, RC units for personal safety and remote controlled mechanisms for remote switching.		✓	--	✓
	Busbars	1/40	Busbars in 10 and 16 mm ² save space in the distribution board and time during mounting.		✓	✓	✓
	Configuration and dimensioning	1/57	Notes for configuration, dimensioning and expanded technical specifications.				
	5SJ4 ...-HG miniature circuit breakers acc. to UL 489 and IEC and accessories	1/84	Miniature circuit breakers can be used as "branch circuit protection" and approved for the connection type "same polarity" and "opposite polarity" in the characteristics B and C and D acc. to UL 489 from 0.3 to 63 A.	UL 489	✓	✓	✓
	SHU, 5SP3 main miniature circuit breakers	1/98	Voltage-independent selective main miniature circuit breakers (SHU) in the precounter sector support downstream miniature circuit breakers by providing better current limitation.	DIN VDE 0641-21	✓	✓	--
	5SK9 circuit breaker terminals	1/104	Circuit breaker terminals are used for short-circuit protection or for protection against overload and short circuits in auxiliary and control circuits downstream of control transformers.		--	--	✓


Characteristic curves

Tripping characteristics acc. to IEC/EN 60898, DIN VDE 0641-11




Tripping characteristic A

For limited semiconductor protection, protection of measuring circuits with transformers. Protection of circuits with tripping in 0.4 s acc. to DIN VDE 0100-410, for long cable lengths.




Tripping characteristic B

MCBs with this tripping characteristic are designed for universal use in socket outlet and lighting circuits. Proof of personal safety acc. to DIN VDE 0100-410 is not required.



Tripping characteristic C

In lamp and motor circuits with higher starting currents, MCBs with tripping characteristic C are generally used.



Tripping characteristic D

For electrical circuits with strong pulse-generating equipment, such as transformers or solenoid valves.

BETA Protecting Miniature Circuit Breakers

Product overview

More information

Approvals

Approvals	VDE	GOST	UR	UL	CCC	IMQ	LCIE (NF)
							
Miniature circuit breakers							
5SY6	✓	✓	✓	--	✓	✓	--
5SY4	✓ ¹⁾²⁾	✓	✓	--	✓	✓	--
5SY7	✓	✓	✓	--	✓	✓	--
5SY8	--	✓	✓	--	--	--	--
5SY5, universal current	✓	✓	--	--	✓	--	--
5SP4	✓	✓	✓	--	✓	--	--
5SP5	✓	✓	--	--	--	--	--
Miniature circuit breakers with plug-in terminal							
5SJ6 ...-KS	✓	✓	--	--	--	--	--
Miniature circuit breakers 1+N							
5SY6 0..	✓	✓	--	--	✓	✓	✓
Miniature circuit breakers acc. to UL 489 and IEC							
5SJ4 ...-HG40	--	✓	--	✓	--	--	--
5SJ4 ...-HG41	--	✓	--	✓	--	--	--
5SJ4 ...-HG42	--	✓	--	✓	--	--	--
Additional components							
5ST3 01.	✓	✓	✓	--	✓	--	--
5ST3 02.	✓	✓	✓	--	✓	--	--
5ST3 0...-OHG	--	--	--	✓	--	--	--
Main miniature circuit breakers							
5SP3	✓	✓	--	--	--	--	--

Ship approvals

Ship approvals	GL			RINA			DNV			BV			LRS		
															
Characteristic	B	C	D	B	C	D	B	C	D	B	C	D	B	C	D
Miniature circuit breakers															
5SY6	✓	✓	--	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	--
5SY4	✓	✓	--	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	✓ ²⁾	--
5SY7	✓	✓	--	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	--
5SP4	✓	✓	✓	--	--	--	--	--	--	--	--	--	✓	✓	✓

¹⁾ Characteristic A, VDE-tested.

²⁾ All types with rated current $I_n \leq 63$ A.

Note:

Further approvals and certifications available on request.

BETA Protecting Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers

Overview


MCBs are used to protect plants in buildings and for industrial applications. The devices can be used as main control switches for the disconnection or isolation of plants.

Used in industrial applications and plant engineering, miniature circuit breakers can be supplemented with additional components, such as auxiliary switches, fault signal contacts, shunt trips, undervoltage releases, remote controls and RC units.

The devices are approved for worldwide use according to IEC standards for systems up to 250/440 V AC. 60 V DC per pole is permitted in DC systems.

For North America, we also have additional certification to UL 1077 for use as "supplementary protectors" in systems up to 480Y/277 V AC. For use in ship building, the devices also have numerous certifications according to shipping classifications; BV, DNV, GL and LRS. Further information can be found on page 1/4.


Benefits




- Optional top or bottom infeed as the terminals are identical
- Clear and visible conductor connection in front of the busbar facilitates controls.
- Large and easily accessible wiring space enables easy insertion of conductor in the terminal.



- Integrated movable terminal covers located at the cable entries ensure the terminals are fully insulated when the screws are tightened.
- The effective touch protection when grasping the device considerably exceeds the requirements of VBG 4/BGV A3.




- Manual snap-on fixing and release systems that require no tools enable fast assembly and disassembly of MCBs.
- Marked labeling field on all modular installation devices for uniform, quick and easy identification.



- Quick and easy manual removal of MCBs from the busbar assembly if connections need to be changed.
- Time-saving replacement of parts as busbars no longer need to be freed from adjacent devices.

BETA Protecting Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers



- Double terminal chambers enable accommodation of 2 wires of different cross-sections (up to 16 mm² in the bottom chamber and 35 mm² in the top chamber).



- Adapted handle locking device for 5SY, 5SJ and 5SP miniature circuit breakers. Suitable for locks 3-6 mm in diameter.

5SY and 5SP miniature circuit breakers

Technical specifications

		5SY6	5SY4	5SY5	5SY7	5SY8	5SP4	5SP5
Standards		EN 60898; EN 60947-2		EN 60898-2; GB 14048.2	EN 60898; EN 60947-2	EN 60947-2	EN 60898; EN 60947-2	EN 60898-2
Approvals		See page 1/4						
Operational voltage	V AC	230/400	230/400	230/400	230/400	230/400	230/400	230/400
	V DC	--	--	220/440/880	--	--	--	220/440
	Min. V AC/DC	24	24	24	24	24	24	24
	Max. V DC/pole	60 ¹⁾	60 ¹⁾	250	60 ¹⁾	60 ¹⁾	60 ¹⁾	250
	Max. V AC	440	440	440	440	440	440	440
Acc. to EN 60898 and EN 60947-2	Max. V AC	440	440	440	440	440	440	440
	Max. V DC/pole	60	60	--	60	60	60	--
Acc. to UL 1077 and CSA C22.2 No.235	Max. V AC	480	480	--	480	480	480	--
	Max. V DC/pole	60	60	--	60	60	60	--
Rated switching capacity²⁾								
• I_{cn} acc. to IEC/EN 60898-1	kA AC	6	10	10	15	--	10	3
• I_{cn} acc. to IEC/EN 60898-2	kA DC	--	--	10	--	--	--	10
• I_{cu} acc. to IEC/EN 60947-2	kA AC	--	--	--	--	25	--	--
	kA DC	--	--	15	--	--	--	15
• Acc. to UL 1077 and CSA C22.2 No.235	kA AC	5	5	--	5	5	5	--
Insulation coordination								
• Rated insulation voltage	V AC	250/440	--	250	--	--	--	250
	V DC/pole	--	--	--	--	--	--	--
Degree of pollution for overvoltage category		3/III						
Touch protection	Acc. to EN 50274	Yes						
Handle end position, sealable		Yes						
Degree of protection	Acc. to EN 60529	IP20, with connected conductors						
CFC and silicone-free		Yes						
Mounting								
• Snap-on fixing system		Yes					--	
• Standard mounting rail and screw fixing		--					Yes	
Terminals								
• Tunnel terminals at both ends		--					Yes	
• Combined terminals at both ends		Yes					--	
• Terminal tightening torque	Nm lb. in	2.5 ... 3 22 ... 26					2.5 ... 3.5 22 ... 31	
Conductor cross-sections								
• Solid and stranded	mm ²	0.75 ... 35					0.75 ... 50	
• Finely stranded, with end sleeve	mm ²	0.75 ... 25					0.75 ... 35	
• AWG cables	AWG	14 ... 4					14 ... 2	
Mains connection								
• AC		Any						
• DC		Any		³⁾	Any		³⁾	
Mounting position		Any						
Service life	Actuations	20 000						
On average, with rated load	Actuations	For 5SY5 at 40 A, 50 A and 63 A 10 000						
Ambient temperature	°C	-25 ... +45, occasionally +55, max. 95 % humidity						
Storage temperature	°C	-40 ... +75						
Resistance to climate	Acc. to IEC 60068-2-30	6 cycles						
Resistance to vibrations	Acc. to IEC 60068-2-6 m/s ²	60 at 10 Hz ... 150 Hz						

¹⁾ The operational voltage 60 V DC/pole takes into account a battery charging voltage with a peak value of 72 V.

²⁾ For further details, please refer to page 1/57.

³⁾ Ensure compliance with the specified polarity when connecting DC.



BETA Protecting Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
6000 A, 5SY6

Selection and ordering data

6000 3	I_n	Mounting width	DT	Characteristic B	Order No.	Price per PU	PU	PS/ P. unit	PG	Weight per PU approx
	A	MW ¹⁾					Unit(s)	Unit(s)		kg
	MCBs 6000 A									
	1P, 230/400 V AC									
	2	1	B	5SY6 102-6		1	1	002	0.165	
	4		B	5SY6 104-6		1	1	002	0.165	
	6		►	5SY6 106-6		1	1/12	002	0.165	
	10		►	5SY6 110-6		1	1/12	002	0.165	
	13		A	5SY6 113-6		1	1/12	002	0.165	
	16		►	5SY6 116-6		1	1/12	002	0.165	
	20		A	5SY6 120-6		1	1/12	002	0.165	
	25		A	5SY6 125-6		1	1/12	002	0.165	
	32		A	5SY6 132-6		1	1/12	002	0.165	
	40		B	5SY6 140-6		1	1	002	0.165	
	50		B	5SY6 150-6		1	1	002	0.165	
	63		B	5SY6 163-6		1	1	002	0.165	
	1P+N, 230 V AC									
	6	2	A	5SY6 506-6		1	1	002	0.330	
	10		A	5SY6 510-6		1	1	002	0.330	
	13		A	5SY6 513-6		1	1/6	002	0.330	
	16		A	5SY6 516-6		1	1/6	002	0.330	
	20		B	5SY6 520-6		1	1	002	0.330	
	25		B	5SY6 525-6		1	1	002	0.330	
	32		B	5SY6 532-6		1	1	002	0.330	
	40		C	5SY6 540-6		1	1	002	0.330	
	50		C	5SY6 550-6		1	1	002	0.330	
	63		C	5SY6 563-6		1	1	002	0.330	
	2P, 400 V AC									
	6	2	A	5SY6 206-6		1	1/6	002	0.330	
	10		A	5SY6 210-6		1	1/6	002	0.330	
	13		B	5SY6 213-6		1	1	002	0.330	
	16		A	5SY6 216-6		1	1/6	002	0.330	
	20		B	5SY6 220-6		1	1	002	0.330	
	25		B	5SY6 225-6		1	1	002	0.330	
	32		A	5SY6 232-6		1	1	002	0.330	
	40		B	5SY6 240-6		1	1	002	0.330	
	50		C	5SY6 250-6		1	1	002	0.330	
	63		C	5SY6 263-6		1	1	002	0.330	
	3P, 400 V AC									
	6	3	A	5SY6 306-6		1	1	002	0.495	
	10		A	5SY6 310-6		1	1/4	002	0.495	
	13		B	5SY6 313-6		1	1	002	0.495	
	16		►	5SY6 316-6		1	1/4	002	0.495	
	20		A	5SY6 320-6		1	1	002	0.495	
	25		A	5SY6 325-6		1	1	002	0.495	
	32		A	5SY6 332-6		1	1/4	002	0.495	
	40		A	5SY6 340-6		1	1	002	0.495	
	50		B	5SY6 350-6		1	1	002	0.495	
	63		B	5SY6 363-6		1	1	002	0.495	
	3P+N, 400 V AC									
	6	4	B	5SY6 606-6		1	1	002	0.660	
	10		B	5SY6 610-6		1	1	002	0.660	
	13		B	5SY6 613-6		1	1	002	0.660	
	16		A	5SY6 616-6		1	1	002	0.660	
	20		A	5SY6 620-6		1	1	002	0.660	
	25		B	5SY6 625-6		1	1	002	0.660	
	32		B	5SY6 632-6		1	1	002	0.660	
	40		C	5SY6 640-6		1	1	002	0.660	
	50		C	5SY6 650-6		1	1	002	0.660	
	63		C	5SY6 663-6		1	1	002	0.660	
	4P, 400 V AC									
	6	4	C	5SY6 406-6		1	1	002	0.660	
	10		B	5SY6 410-6		1	1	002	0.660	
	13		C	5SY6 413-6		1	1	002	0.660	
	16		A	5SY6 416-6		1	1	002	0.660	
	20		A	5SY6 420-6		1	1	002	0.660	
	25		A	5SY6 425-6		1	1	002	0.660	
	32		B	5SY6 432-6		1	1	002	0.660	
	40		B	5SY6 440-6		1	1	002	0.660	
	50		B	5SY6 450-6		1	1	002	0.660	
	63		B	5SY6 463-6		1	1	002	0.660	

¹⁾ 1 MW (modular width) = 18 mm.

5SY and 5SP miniature circuit breakers 6000 A, 5SY6

6000 3		I_n A	Moun- ting width MW ¹⁾	DT	Characteristic C			PG	DT	Characteristic D			Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
					Order No.	Price per PU				Order No.	Price per PU						
	MCBs 6000 A																
	1P, 230/400 V AC																
	0.3	1	A	5SY6 114-7			003	C	5SY6 114-8			1	1	004	0.165		
	0.5		A	5SY6 105-7			003	A	5SY6 105-8			1	1	004	0.165		
	1		▶	5SY6 101-7			003	A	5SY6 101-8			1	1	004	0.165		
	1.6		A	5SY6 115-7			003	C	5SY6 115-8			1	1	004	0.147		
	2		▶	5SY6 102-7			003	A	5SY6 102-8			1	1/12	004	0.165		
	3		A	5SY6 103-7			003	A	5SY6 103-8			1	1	004	0.165		
	4		▶	5SY6 104-7			003	A	5SY6 104-8			1	1	004	0.165		
	6		▶	5SY6 106-7			003	A	5SY6 106-8			1	1/12	004	0.165		
	8		A	5SY6 108-7			003	A	5SY6 108-8			1	1	004	0.165		
	10		▶	5SY6 110-7			003	A	5SY6 110-8			1	1	004	0.165		
	13		A	5SY6 113-7			003	A	5SY6 113-8			1	1	004	0.165		
	16		▶	5SY6 116-7			003	A	5SY6 116-8			1	1	004	0.165		
	20		▶	5SY6 120-7			003	A	5SY6 120-8			1	1	004	0.165		
	25		▶	5SY6 125-7			003	A	5SY6 125-8			1	1	004	0.165		
	32		▶	5SY6 132-7			003	B	5SY6 132-8			1	1	004	0.165		
	40		A	5SY6 140-7			003	B	5SY6 140-8			1	1	004	0.165		
	50		A	5SY6 150-7			003	B	5SY6 150-8			1	1	004	0.165		
	63		A	5SY6 163-7			003	B	5SY6 163-8			1	1	004	0.165		
	1P+N, 230 V AC																
	0.3	2	B	5SY6 514-7			003	C	5SY6 514-8			1	1	004	0.330		
	0.5		A	5SY6 505-7			003	B	5SY6 505-8			1	1	004	0.330		
	1		A	5SY6 501-7			003	C	5SY6 501-8			1	1	004	0.330		
	1.6		B	5SY6 515-7			003	B	5SY6 515-8			1	1	004	0.330		
	2		A	5SY6 502-7			003	B	5SY6 502-8			1	1	004	0.330		
	3		A	5SY6 503-7			003	B	5SY6 503-8			1	1	004	0.330		
	4		A	5SY6 504-7			003	B	5SY6 504-8			1	1	004	0.330		
	6		A	5SY6 506-7			003	A	5SY6 506-8			1	1	004	0.330		
	8		B	5SY6 508-7			003	B	5SY6 508-8			1	1	004	0.330		
	10		A	5SY6 510-7			003	B	5SY6 510-8			1	1	004	0.330		
	13		A	5SY6 513-7			003	C	5SY6 513-8			1	1	004	0.330		
	16		▶	5SY6 516-7			003	A	5SY6 516-8			1	1	004	0.330		
	20		A	5SY6 520-7			003	C	5SY6 520-8			1	1	004	0.330		
	25		A	5SY6 525-7			003	C	5SY6 525-8			1	1	004	0.330		
	32		A	5SY6 532-7			003	C	5SY6 532-8			1	1	004	0.330		
	40		B	5SY6 540-7			003	C	5SY6 540-8			1	1	004	0.330		
	50		B	5SY6 550-7			003	C	5SY6 550-8			1	1	004	0.330		
	63		B	5SY6 563-7			003	C	5SY6 563-8			1	1	004	0.330		
	2P, 400 V AC																
	0.3	2	B	5SY6 214-7			003	B	5SY6 214-8			1	1	004	0.330		
	0.5		A	5SY6 205-7			003	A	5SY6 205-8			1	1	004	0.330		
	1		A	5SY6 201-7			003	A	5SY6 201-8			1	1	004	0.330		
	1.6		A	5SY6 215-7			003	A	5SY6 215-8			1	1	004	0.330		
	2		▶	5SY6 202-7			003	A	5SY6 202-8			1	1/6	004	0.330		
	3		A	5SY6 203-7			003	A	5SY6 203-8			1	1	004	0.330		
	4		▶	5SY6 204-7			003	A	5SY6 204-8			1	1/6	004	0.330		
	6		▶	5SY6 206-7			003	A	5SY6 206-8			1	1/6	004	0.330		
	8		A	5SY6 208-7			003	A	5SY6 208-8			1	1	004	0.330		
	10		▶	5SY6 210-7			003	A	5SY6 210-8			1	1/6	004	0.330		
	13		A	5SY6 213-7			003	B	5SY6 213-8			1	1	004	0.330		
	16		▶	5SY6 216-7			003	A	5SY6 216-8			1	1	004	0.330		
	20		▶	5SY6 220-7			003	A	5SY6 220-8			1	1	004	0.330		
	25		A	5SY6 225-7			003	A	5SY6 225-8			1	1	004	0.330		
	32		A	5SY6 232-7			003	A	5SY6 232-8			1	1	004	0.330		
	40		A	5SY6 240-7			003	B	5SY6 240-8			1	1	004	0.330		
	50		A	5SY6 250-7			003	B	5SY6 250-8			1	1	004	0.330		
	63		A	5SY6 263-7			003	B	5SY6 263-8			1	1	004	0.330		

¹⁾ 1 MW (modular width) = 18 mm.



BETA Protecting

Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
6000 A, 5SY6

6000 3						Characteristic C			Characteristic D						
I_n	Moun- ting width	DT	Order No.	Price per PU	PG	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx			
A	MW ¹⁾								Unit(s)	Unit(s)		kg			
MCBs 6000 A															
3P, 400 V AC															
	0.3	3	C	5SY6 314-7		003	C	5SY6 314-8	1	1	004	0.495			
	0.5		A	5SY6 305-7		003	C	5SY6 305-8	1	1	004	0.495			
	1		A	5SY6 301-7		003	A	5SY6 301-8	1	1	004	0.495			
	1.6		B	5SY6 315-7		003	C	5SY6 315-8	1	1	004	0.495			
	2		A	5SY6 302-7		003	A	5SY6 302-8	1	1	004	0.495			
	3		A	5SY6 303-7		003	A	5SY6 303-8	1	1	004	0.495			
	4		A	5SY6 304-7		003	A	5SY6 304-8	1	1	004	0.495			
	6		►	5SY6 306-7		003	A	5SY6 306-8	1	1	004	0.495			
	8		A	5SY6 308-7		003	B	5SY6 308-8	1	1	004	0.495			
	10		►	5SY6 310-7		003	A	5SY6 310-8	1	1	004	0.495			
	13		A	5SY6 313-7		003	B	5SY6 313-8	1	1	004	0.495			
	16		►	5SY6 316-7		003	A	5SY6 316-8	1	1	004	0.495			
	20		►	5SY6 320-7		003	A	5SY6 320-8	1	1	004	0.495			
	25		►	5SY6 325-7		003	A	5SY6 325-8	1	1	004	0.495			
	32		►	5SY6 332-7		003	A	5SY6 332-8	1	1	004	0.495			
	40		A	5SY6 340-7		003	A	5SY6 340-8	1	1	004	0.495			
	50		A	5SY6 350-7		003	A	5SY6 350-8	1	1	004	0.495			
	63		A	5SY6 363-7		003	A	5SY6 363-8	1	1	004	0.495			
	3P+N, 400 V AC														
	0.3	4	C	5SY6 614-7		003	C	5SY6 614-8	1	1	004	0.660			
	0.5		C	5SY6 605-7		003	C	5SY6 605-8	1	1	004	0.660			
	1		C	5SY6 601-7		003	C	5SY6 601-8	1	1	004	0.660			
	1.6		C	5SY6 615-7		003	C	5SY6 615-8	1	1	004	0.660			
	2		A	5SY6 602-7		003	C	5SY6 602-8	1	1	004	0.660			
	3		C	5SY6 603-7		003	C	5SY6 603-8	1	1	004	0.660			
	4		B	5SY6 604-7		003	C	5SY6 604-8	1	1	004	0.660			
	6		A	5SY6 606-7		003	A	5SY6 606-8	1	1	004	0.660			
	8		C	5SY6 608-7		003	C	5SY6 608-8	1	1	004	0.660			
	10		A	5SY6 610-7		003	B	5SY6 610-8	1	1	004	0.660			
	13		B	5SY6 613-7		003	C	5SY6 613-8	1	1	004	0.660			
	16		►	5SY6 616-7		003	B	5SY6 616-8	1	1	004	0.660			
	20		A	5SY6 620-7		003	B	5SY6 620-8	1	1	004	0.660			
	25		A	5SY6 625-7		003	B	5SY6 625-8	1	1	004	0.660			
	32		A	5SY6 632-7		003	B	5SY6 632-8	1	1	004	0.660			
	40		A	5SY6 640-7		003	B	5SY6 640-8	1	1	004	0.660			
	50		A	5SY6 650-7		003	B	5SY6 650-8	1	1	004	0.660			
	63		A	5SY6 663-7		003	B	5SY6 663-8	1	1	004	0.660			
	4P, 400 V AC														
	0.3	4	C	5SY6 414-7		003	C	5SY6 414-8	1	1	004	0.660			
	0.5		C	5SY6 405-7		003	C	5SY6 405-8	1	1	004	0.660			
	1		B	5SY6 401-7		003	C	5SY6 401-8	1	1	004	0.660			
	1.6		C	5SY6 415-7		003	C	5SY6 415-8	1	1	004	0.660			
	2		A	5SY6 402-7		003	C	5SY6 402-8	1	1	004	0.660			
	3		B	5SY6 403-7		003	C	5SY6 403-8	1	1	004	0.660			
	4		B	5SY6 404-7		003	C	5SY6 404-8	1	1	004	0.660			
	6		A	5SY6 406-7		003	B	5SY6 406-8	1	1	004	0.660			
	8		B	5SY6 408-7		003	C	5SY6 408-8	1	1	004	0.660			
	10		A	5SY6 410-7		003	A	5SY6 410-8	1	1	004	0.660			
	13		A	5SY6 413-7		003	C	5SY6 413-8	1	1	004	0.660			
	16		►	5SY6 416-7		003	A	5SY6 416-8	1	1	004	0.660			
	20		A	5SY6 420-7		003	A	5SY6 420-8	1	1	004	0.660			
	25		►	5SY6 425-7		003	A	5SY6 425-8	1	1	004	0.660			
	32		►	5SY6 432-7		003	A	5SY6 432-8	1	1	004	0.660			
	40		►	5SY6 440-7		003	A	5SY6 440-8	1	1	004	0.660			
	50		A	5SY6 450-7		003	A	5SY6 450-8	1	1	004	0.660			
	63		A	5SY6 463-7		003	►	5SY6 463-8	1	1	004	0.660			

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.

5SY and 5SP miniature circuit breakers 10 000 A, 5SY4

10 000 3		I_n	Moun- ting width MW ¹⁾	DT	Characteristic A		PG	DT	Characteristic B		Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx kg
					Order No.	Price per PU			Order No.	Price per PU					
MCBs 10 000 A															
1P, 230/400 V AC															
	0.5	1	C	5SY4 105-5		001	--				1	1			0.165
	1		A	5SY4 101-5		001	--				1	1			0.165
	1.6		B	5SY4 115-5		001	--				1	1			0.165
	2		A	5SY4 102-5		001	--				1	1			0.165
	3		A	5SY4 103-5		001	--				1	1			0.165
	4		A	5SY4 104-5		001	--				1	1/12			0.165
	6		A	5SY4 106-5		001	A	5SY4 106-6			1	1/12	002		0.165
	8		B	5SY4 108-5		001	--				1	1			0.165
	10		A	5SY4 110-5		001	►	5SY4 110-6			1	1/12	002		0.165
	13		C	5SY4 113-5		001	A	5SY4 113-6			1	1	002		0.165
	16		A	5SY4 116-5		001	►	5SY4 116-6			1	1/12	002		0.165
	20		A	5SY4 120-5		001	A	5SY4 120-6			1	1	002		0.165
	25		A	5SY4 125-5		001	►	5SY4 125-6			1	1	002		0.165
	32		B	5SY4 132-5		001	A	5SY4 132-6			1	1	002		0.165
	40		B	5SY4 140-5		001	B	5SY4 140-6			1	1	002		0.165
	50		C	5SY4 150-5		001	B	5SY4 150-6			1	1	002		0.165
	63		C	5SY4 163-5		001	B	5SY4 163-6			1	1	002		0.165
	80		--				C	5SY4 180-6			1	1	002		0.162
1P+N, 230 V AC															
	1	2	C	5SY4 501-5		001	--				1	1			0.330
	1.6		B	5SY4 515-5		001	--				1	1			0.330
	2		B	5SY4 502-5		001	--				1	1			0.330
	3		C	5SY4 503-5		001	--				1	1			0.330
	4		B	5SY4 504-5		001	--				1	1			0.330
	6		C	5SY4 506-5		001	A	5SY4 506-6			1	1	002		0.330
	8		C	5SY4 508-5		001	--				1	1			0.330
	10		B	5SY4 510-5		001	A	5SY4 510-6			1	1	002		0.330
	13		C	5SY4 513-5		001	A	5SY4 513-6			1	1/6	002		0.330
	16		C	5SY4 516-5		001	A	5SY4 516-6			1	1/6	002		0.330
	20		C	5SY4 520-5		001	B	5SY4 520-6			1	1	002		0.330
	25		C	5SY4 525-5		001	B	5SY4 525-6			1	1	002		0.330
	32		C	5SY4 532-5		001	B	5SY4 532-6			1	1	002		0.330
	40		C	5SY4 540-5		001	C	5SY4 540-6			1	1	002		0.330
	50		C	5SY4 550-5		001	C	5SY4 550-6			1	1	002		0.330
	63		C	5SY4 563-5		001	C	5SY4 563-6			1	1	002		0.330
2P, 400 V AC															
	0.5	2	C	5SY4 205-5		001	--				1	1			0.330
	1		B	5SY4 201-5		001	--				1	1			0.330
	1.6		B	5SY4 215-5		001	--				1	1			0.330
	2		A	5SY4 202-5		001	--				1	1			0.330
	3		B	5SY4 203-5		001	--				1	1			0.330
	4		A	5SY4 204-5		001	--				1	1			0.330
	6		A	5SY4 206-5		001	A	5SY4 206-6			1	1	002		0.330
	8		C	5SY4 208-5		001	--				1	1			0.330
	10		A	5SY4 210-5		001	A	5SY4 210-6			1	1/6	002		0.330
	13		C	5SY4 213-5		001	B	5SY4 213-6			1	1	002		0.330
	16		A	5SY4 216-5		001	►	5SY4 216-6			1	1/6	002		0.330
	20		B	5SY4 220-5		001	A	5SY4 220-6			1	1	002		0.330
	25		B	5SY4 225-5		001	A	5SY4 225-6			1	1	002		0.330
	32		A	5SY4 232-5		001	B	5SY4 232-6			1	1	002		0.330
	40		B	5SY4 240-5		001	B	5SY4 240-6			1	1	002		0.330
	50		C	5SY4 250-5		001	B	5SY4 250-6			1	1	002		0.330
	63		C	5SY4 263-5		001	B	5SY4 263-6			1	1	002		0.330
	80		--				C	5SY4 280-6			1	1	002		0.324

¹⁾ 1 MW (modular width) = 18 mm.



BETA Protecting Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
10 000 A, 5SY4

10 000 3	I_n	Moun- ting width	DT	Characteristic A		PG	DT	Characteristic B		Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	A	MW ¹⁾		Order No.	Price per PU			Order No.	Price per PU		Unit(s)	Unit(s)		kg
	MCBs 10 000 A													
	3P, 400 V AC													
	0.5	3	C	5SY4 305-5		001	--				1	1		0.495
	1		C	5SY4 301-5		001	--				1	1		0.495
	1.6		C	5SY4 315-5		001	--				1	1		0.495
	2		B	5SY4 302-5		001	--				1	1		0.495
	3		C	5SY4 303-5		001	--				1	1		0.495
	4		B	5SY4 304-5		001	--				1	1		0.495
	6		B	5SY4 306-5		001	A	5SY4 306-6			1	1	002	0.495
	8		C	5SY4 308-5		001	--				1	1		0.495
	10		B	5SY4 310-5		001	►	5SY4 310-6			1	1	002	0.495
	13		C	5SY4 313-5		001	B	5SY4 313-6			1	1	002	0.495
	16		A	5SY4 316-5		001	►	5SY4 316-6			1	1/4	002	0.495
	20		B	5SY4 320-5		001	A	5SY4 320-6			1	1	002	0.495
	25		B	5SY4 325-5		001	A	5SY4 325-6			1	1	002	0.495
	32		B	5SY4 332-5		001	►	5SY4 332-6			1	1/4	002	0.495
	40		B	5SY4 340-5		001	A	5SY4 340-6			1	1	002	0.495
	50		B	5SY4 350-5		001	A	5SY4 350-6			1	1	002	0.495
63		C	5SY4 363-5		001	A	5SY4 363-6			1	1	002	0.495	
80		--	--			B	5SY4 380-6			1	1	002	0.486	
	3P+N, 400 V AC													
	1	4	C	5SY4 601-5		001	--				1	1		0.660
	1.6		C	5SY4 615-5		001	--				1	1		0.660
	2		C	5SY4 602-5		001	--				1	1		0.660
	3		C	5SY4 603-5		001	--				1	1		0.660
	4		C	5SY4 604-5		001	--				1	1		0.660
	6		C	5SY4 606-5		001	B	5SY4 606-6			1	1	002	0.660
	8		C	5SY4 608-5		001	--				1	1		0.660
	10		C	5SY4 610-5		001	B	5SY4 610-6			1	1	002	0.660
	13		C	5SY4 613-5		001	C	5SY4 613-6			1	1	002	0.660
	16		C	5SY4 616-5		001	A	5SY4 616-6			1	1	002	0.660
	20		C	5SY4 620-5		001	B	5SY4 620-6			1	1	002	0.660
	25		C	5SY4 625-5		001	A	5SY4 625-6			1	1	002	0.660
	32		C	5SY4 632-5		001	B	5SY4 632-6			1	1	002	0.660
	40		C	5SY4 640-5		001	C	5SY4 640-6			1	1	002	0.660
	50		C	5SY4 650-5		001	C	5SY4 650-6			1	1	002	0.660
	63		C	5SY4 663-5		001	A	5SY4 663-6			1	1	002	0.660
		4P, 400 V AC												
1		4	C	5SY4 401-5		001	--				1	1		0.660
1.6			C	5SY4 415-5		001	--				1	1		0.660
2			C	5SY4 402-5		001	--				1	1		0.660
3			C	5SY4 403-5		001	--				1	1		0.660
4			C	5SY4 404-5		001	--				1	1		0.660
6			C	5SY4 406-5		001	A	5SY4 406-6			1	1	002	0.660
8			C	5SY4 408-5		001	--				1	1		0.660
10			C	5SY4 410-5		001	B	5SY4 410-6			1	1	002	0.660
13			C	5SY4 413-5		001	C	5SY4 413-6			1	1	002	0.660
16			C	5SY4 416-5		001	A	5SY4 416-6			1	1	002	0.660
20			C	5SY4 420-5		001	C	5SY4 420-6			1	1	002	0.660
25			C	5SY4 425-5		001	B	5SY4 425-6			1	1	002	0.660
32			C	5SY4 432-5		001	B	5SY4 432-6			1	1	002	0.660
40			C	5SY4 440-5		001	B	5SY4 440-6			1	1	002	0.660
50			C	5SY4 450-5		001	B	5SY4 450-6			1	1	002	0.660
63			C	5SY4 463-5		001	B	5SY4 463-6			1	1	002	0.660
80			--	--			B	5SY4 480-6			1	1	002	0.648

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.



BETA Protecting Miniature Circuit Breakers

1

5SY and 5SP miniature circuit breakers
10 000 A, 5SY4

10 000 3	I_n A	Mount. width mm ¹⁾	DT	Characteristic C			Characteristic D			PU	PS* P. unit	PG	Weight per PU approx kg
				Order No.	Price per PU	PG	DT	Order No.	Price per PU	Unit(s)	Unit(s)		
	MCBs 10 000 A												
	1P, 230/400 V AC												
	0.3	1	B	5SY4 114-7		003	C	5SY4 114-8		1	1	004	0.165
	0.5		A	5SY4 105-7		003	B	5SY4 105-8		1	1	004	0.165
	1		▶	5SY4 101-7		003	A	5SY4 101-8		1	1	004	0.165
	1.6		A	5SY4 115-7		003	B	5SY4 115-8		1	1	004	0.165
	2		▶	5SY4 102-7		003	A	5SY4 102-8		1	1/12	004	0.165
	3		A	5SY4 103-7		003	A	5SY4 103-8		1	1	004	0.165
	4		▶	5SY4 104-7		003	A	5SY4 104-8		1	1/12	004	0.165
	5		C	5SY4 111-7		003		--		1	1		0.165
	6		▶	5SY4 106-7		003	A	5SY4 106-8		1	1	004	0.165
	8		A	5SY4 108-7		003	A	5SY4 108-8		1	1	004	0.165
	10		▶	5SY4 110-7		003	A	5SY4 110-8		1	1/12	004	0.165
	13		A	5SY4 113-7		003	B	5SY4 113-8		1	1	004	0.165
	15		C	5SY4 118-7		003		--		1	1		0.165
	16		▶	5SY4 116-7		003	A	5SY4 116-8		1	1	004	0.165
	20		▶	5SY4 120-7		003	A	5SY4 120-8		1	1	004	0.165
	25		▶	5SY4 125-7		003	B	5SY4 125-8		1	1	004	0.165
	30		B	5SY4 130-7		003		--		1	1		0.165
	32		▶	5SY4 132-7		003	B	5SY4 132-8		1	1	004	0.165
	35		B	5SY4 135-7		003		--		1	1		0.165
40		A	5SY4 140-7		003	B	5SY4 140-8		1	1	004	0.165	
45		B	5SY4 145-7		003		--		1	1		0.165	
50		A	5SY4 150-7		003	B	5SY4 150-8		1	1	004	0.165	
60		B	5SY4 160-7		003		--		1	1		0.165	
63		B	5SY4 163-7		003	B	5SY4 163-8		1	1	004	0.165	
80		B	5SY4 180-7		003		--		1	1		0.161	
	1P+N, 230 V AC												
	0.3	2	C	5SY4 514-7		003	C	5SY4 514-8		1	1	004	0.330
	0.5		B	5SY4 505-7		003	C	5SY4 505-8		1	1	004	0.330
	1		A	5SY4 501-7		003	B	5SY4 501-8		1	1	004	0.330
	1.6		C	5SY4 515-7		003	C	5SY4 515-8		1	1	004	0.330
	2		A	5SY4 502-7		003	A	5SY4 502-8		1	1	004	0.330
	3		A	5SY4 503-7		003	B	5SY4 503-8		1	1	004	0.330
	4		A	5SY4 504-7		003	B	5SY4 504-8		1	1	004	0.330
	6		A	5SY4 506-7		003	A	5SY4 506-8		1	1	004	0.330
	8		B	5SY4 508-7		003	C	5SY4 508-8		1	1	004	0.330
	10		A	5SY4 510-7		003	A	5SY4 510-8		1	1	004	0.330
	13		A	5SY4 513-7		003	B	5SY4 513-8		1	1	004	0.330
	16		A	5SY4 516-7		003	A	5SY4 516-8		1	1	004	0.330
	20		A	5SY4 520-7		003	B	5SY4 520-8		1	1	004	0.330
	25		A	5SY4 525-7		003	B	5SY4 525-8		1	1	004	0.330
	32		A	5SY4 532-7		003	B	5SY4 532-8		1	1	004	0.330
	40		B	5SY4 540-7		003	C	5SY4 540-8		1	1	004	0.330
	50		C	5SY4 550-7		003	C	5SY4 550-8		1	1	004	0.330
	63		C	5SY4 563-7		003	C	5SY4 563-8		1	1	004	0.330
	80		B	5SY4 580-7		003		--		1	1		0.323
		2P, 400 V AC											
0.3		2	A	5SY4 214-7		003	B	5SY4 214-8		1	1	004	0.330
0.5			A	5SY4 205-7		003	A	5SY4 205-8		1	1	004	0.330
1			A	5SY4 201-7		003	A	5SY4 201-8		1	1	004	0.330
1.6			A	5SY4 215-7		003	A	5SY4 215-8		1	1	004	0.330
2			A	5SY4 202-7		003	A	5SY4 202-8		1	1	004	0.330
3			A	5SY4 203-7		003	A	5SY4 203-8		1	1	004	0.330
4			A	5SY4 204-7		003	A	5SY4 204-8		1	1	004	0.330
5			C	5SY4 211-7		003		--		1	1		0.330
6			A	5SY4 206-7		003	A	5SY4 206-8		1	1	004	0.330
8			A	5SY4 208-7		003	A	5SY4 208-8		1	1	004	0.330
10			▶	5SY4 210-7		003	A	5SY4 210-8		1	1	004	0.330
13			A	5SY4 213-7		003	A	5SY4 213-8		1	1	004	0.330
15			C	5SY4 218-7		003		--		1	1		0.330
16			▶	5SY4 216-7		003	A	5SY4 216-8		1	1	004	0.330
20			A	5SY4 220-7		003	A	5SY4 220-8		1	1	004	0.330
25			A	5SY4 225-7		003	A	5SY4 225-8		1	1	004	0.330
30			C	5SY4 230-7		003		--		1	1		0.330
32			A	5SY4 232-7		003	A	5SY4 232-8		1	1	004	0.330
35			B	5SY4 235-7		003		--		1	1		0.330
40			A	5SY4 240-7		003	A	5SY4 240-8		1	1	004	0.330
45			B	5SY4 245-7		003		--		1	1		0.330
50			A	5SY4 250-7		003	B	5SY4 250-8		1	1	004	0.330
60			B	5SY4 260-7		003		--		1	1		0.330
63			A	5SY4 263-7		003	B	5SY4 263-8		1	1	004	0.330
80		B	5SY4 280-7		003		--		1	1/6		0.323	

* You can order this quantity or a multiple thereof.



BETA Protecting Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
10 000 A, 5SY4

10 000 3	I_n	Moun- ting width MW ¹⁾	DT	Characteristic C		PG	DT	Characteristic D		PU	PS*/ P. unit	PG	Weight per PU approx kg
				Order No.	Price per PU			Order No.	Price per PU				
	A									Unit(s)	Unit(s)		
MCBs 10 000 A													
	3P, 400 V AC												
	0.3	3	C	5SY4 314-7		003	C	5SY4 314-8		1	1	004	0.495
	0.5		B	5SY4 305-7		003	B	5SY4 305-8		1	1	004	0.495
	1		A	5SY4 301-7		003	A	5SY4 301-8		1	1	004	0.495
	1.6		C	5SY4 315-7		003	B	5SY4 315-8		1	1	004	0.495
	2		A	5SY4 302-7		003	A	5SY4 302-8		1	1	004	0.495
	3		A	5SY4 303-7		003	A	5SY4 303-8		1	1	004	0.495
	4		A	5SY4 304-7		003	A	5SY4 304-8		1	1	004	0.495
	5		C	5SY4 311-7		003		--		1	1		0.495
	6		►	5SY4 306-7		003	A	5SY4 306-8		1	1	004	0.495
	8		A	5SY4 308-7		003	B	5SY4 308-8		1	1	004	0.495
	10		►	5SY4 310-7		003	A	5SY4 310-8		1	1	004	0.495
	13		A	5SY4 313-7		003	B	5SY4 313-8		1	1	004	0.495
	15		C	5SY4 318-7		003		--		1	1		0.495
	16		►	5SY4 316-7		003	A	5SY4 316-8		1	1/4	004	0.495
	20		►	5SY4 320-7		003	A	5SY4 320-8		1	1	004	0.495
	25		►	5SY4 325-7		003	A	5SY4 325-8		1	1	004	0.495
	30		C	5SY4 330-7		003		--		1	1		0.495
	32		►	5SY4 332-7		003	A	5SY4 332-8		1	1	004	0.495
	35		C	5SY4 335-7		003		--		1	1		0.495
	40		A	5SY4 340-7		003	A	5SY4 340-8		1	1	004	0.495
	45		B	5SY4 345-7		003		--		1	1		0.495
	50		A	5SY4 350-7		003	A	5SY4 350-8		1	1	004	0.495
	60		C	5SY4 360-7		003		--		1	1		0.495
	63		A	5SY4 363-7		003	A	5SY4 363-8		1	1	004	0.495
	80		B	5SY4 380-7		003		--		1	1		0.482
3P+N, 400 V AC													
	3P+N, 400 V AC												
	0.3	4	C	5SY4 614-7		003	C	5SY4 614-8		1	1	004	0.660
	0.5		C	5SY4 605-7		003	C	5SY4 605-8		1	1	004	0.660
	1		C	5SY4 601-7		003	C	5SY4 601-8		1	1	004	0.660
	1.6		C	5SY4 615-7		003	C	5SY4 615-8		1	1	004	0.660
	2		B	5SY4 602-7		003	C	5SY4 602-8		1	1	004	0.660
	3		B	5SY4 603-7		003	C	5SY4 603-8		1	1	004	0.660
	4		C	5SY4 604-7		003	C	5SY4 604-8		1	1	004	0.660
	6		B	5SY4 606-7		003	C	5SY4 606-8		1	1	004	0.660
	8		C	5SY4 608-7		003	C	5SY4 608-8		1	1	004	0.660
	10		A	5SY4 610-7		003	B	5SY4 610-8		1	1	004	0.660
	13		B	5SY4 613-7		003	C	5SY4 613-8		1	1	004	0.660
	16		A	5SY4 616-7		003	A	5SY4 616-8		1	1	004	0.660
	20		A	5SY4 620-7		003	B	5SY4 620-8		1	1	004	0.660
	25		A	5SY4 625-7		003	A	5SY4 625-8		1	1	004	0.660
	32		A	5SY4 632-7		003	A	5SY4 632-8		1	1	004	0.660
	40		A	5SY4 640-7		003	A	5SY4 640-8		1	1	004	0.660
	50		B	5SY4 650-7		003	A	5SY4 650-8		1	1	004	0.660
	63		A	5SY4 663-7		003	B	5SY4 663-8		1	1	004	0.660
	80		B	5SY4 680-7		003		--		1	1		0.647
4P, 400 V AC													
	4P, 400 V AC												
	0.3	4	C	5SY4 414-7		003	C	5SY4 414-8		1	1	004	0.660
	0.5		C	5SY4 405-7		003	C	5SY4 405-8		1	1	004	0.660
	1		C	5SY4 401-7		003	C	5SY4 401-8		1	1	004	0.660
	1.6		C	5SY4 415-7		003	C	5SY4 415-8		1	1	004	0.660
	2		B	5SY4 402-7		003	C	5SY4 402-8		1	1	004	0.660
	3		C	5SY4 403-7		003	C	5SY4 403-8		1	1	004	0.660
	4		B	5SY4 404-7		003	C	5SY4 404-8		1	1	004	0.660
	6		A	5SY4 406-7		003	B	5SY4 406-8		1	1	004	0.660
	8		C	5SY4 408-7		003	C	5SY4 408-8		1	1	004	0.660
	10		A	5SY4 410-7		003	A	5SY4 410-8		1	1	004	0.660
	13		C	5SY4 413-7		003	C	5SY4 413-8		1	1	004	0.660
	16		A	5SY4 416-7		003	►	5SY4 416-8		1	1	004	0.660
	20		A	5SY4 420-7		003	A	5SY4 420-8		1	1	004	0.660
	25		A	5SY4 425-7		003	A	5SY4 425-8		1	1	004	0.660
	32		A	5SY4 432-7		003	►	5SY4 432-8		1	1	004	0.660
	40		A	5SY4 440-7		003	A	5SY4 440-8		1	1	004	0.660
	50		A	5SY4 450-7		003	A	5SY4 450-8		1	1	004	0.660
	63		A	5SY4 463-7		003	A	5SY4 463-8		1	1	004	0.660
	80		B	5SY4 480-7		003		--		1	1		0.647



¹⁾ 1 MW (modular width) = 18 mm.




BETA Protecting Miniature Circuit Breakers

1

5SY and 5SP miniature circuit breakers
10 000 A, high current, 5SP4

10 000		I_n	Mounting width	DT	Characteristic B	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx			
		A	MW ¹⁾					Unit(s)	Unit(s)		kg			
	MCBs 10 000 A, high current													
	1P, 230/400 V AC													
	80	1.5	B	5SP4 180-6	1							1	002	0.258
	100		C	5SP4 191-6	1							1	002	0.258
		125		B	5SP4 192-6	1	1	002	0.258					
	2P, 400 V AC													
	80	3	C	5SP4 280-6	1							1	002	0.516
	100		C	5SP4 291-6	1							1	002	0.516
	125		C	5SP4 292-6	1							1	002	0.516
	3P, 400 V AC													
	80	4.5	B	5SP4 380-6	1							1	002	0.762
	100		B	5SP4 391-6	1							1	002	0.762
	125		C	5SP4 392-6	1							1	002	0.762
	4P, 400 V AC													
	80	6	B	5SP4 480-6	1							1	002	1.032
	100		C	5SP4 491-6	1							1	002	1.032
	125		C	5SP4 492-6	1							1	002	1.032

10 000		I_n	Mounting width	DT	Characteristic C		PG	DT	Characteristic D		PU	PS*/ P. unit	PG	Weight per PU approx
		A	MW ¹⁾		Order No.	Price per PU			Order No.	Price per PU	Unit(s)	Unit(s)		kg
	MCBs 10 000 A, high current													
	1P, 230/400 V AC													
	80	1.5	A	5SP4 180-7		003	B	5SP4 180-8		1	1	004	0.258	
	100		A	5SP4 191-7		003	C	5SP4 191-8		1	1	004	0.258	
	125		A	5SP4 192-7		003		--		1	1		0.258	
	2P, 400 V AC													
	80	3	A	5SP4 280-7		003	C	5SP4 280-8		1	1	004	0.516	
	100		A	5SP4 291-7		003	C	5SP4 291-8		1	1	004	0.516	
	125		A	5SP4 292-7		003		--		1	1		0.516	
	3P, 400 V AC													
	80	4.5	▶	5SP4 380-7		003	A	5SP4 380-8		1	1	004	0.762	
	100		▶	5SP4 391-7		003	A	5SP4 391-8		1	1	004	0.762	
	125		A	5SP4 392-7		003		--		1	1		0.762	
	4P, 400 V AC													
	80	6	A	5SP4 480-7		003	A	5SP4 480-8		1	1	004	1.032	
	100		A	5SP4 491-7		003	C	5SP4 491-8		1	1	004	1.032	
	125		A	5SP4 492-7		003		--		1	1		1.032	

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.



BETA Protecting

Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
10 000 A, universal current, 5SP5, 5SY5

10 000 3	I_n	Mounting width MW ¹⁾	DT	Characteristic B		PG	DT	Characteristic C		PU	PS*/ P. unit	PG	Weight per PU approx kg
				Order No.	Price per PU			Order No.	Price per PU				
	A									Unit(s)	Unit(s)		
	MCBs 10 000 A, universal current 1P, 230/400 V AC, 220 V DC												
	0.3	1	--				C	5SY5 114-7		1	1	003	0.165
	0.5		--				B	5SY5 105-7		1	1	003	0.165
	1		--				A	5SY5 101-7		1	1	003	0.147
	1.6		--				A	5SY5 115-7		1	1	003	0.165
	2			5SY5 102-6		002	A	5SY5 102-7		1	1	003	0.165
	3			--			A	5SY5 103-7		1	1	003	0.165
	4			5SY5 104-6		002	A	5SY5 104-7		1	1	003	0.165
	6		A	5SY5 106-6		002	▶	5SY5 106-7		1	1	003	0.165
	8			--			A	5SY5 108-7		1	1	003	0.165
	10		A	5SY5 110-6		002	▶	5SY5 110-7		1	1	003	0.165
	13		C	5SY5 113-6		002	B	5SY5 113-7		1	1	003	0.165
	16		A	5SY5 116-6		002	A	5SY5 116-7		1	1	003	0.165
	20		C	5SY5 120-6		002	A	5SY5 120-7		1	1	003	0.165
	25		C	5SY5 125-6		002	B	5SY5 125-7		1	1	003	0.165
	32		C	5SY5 132-6		002	B	5SY5 132-7		1	1	003	0.165
	40		C	5SY5 140-6		002	C	5SY5 140-7		1	1	003	0.165
	50		C	5SY5 150-6		002	C	5SY5 150-7		1	1	003	0.165
	63		C	5SY5 163-6		002	C	5SY5 163-7		1	1	003	0.165
	1P, 230/400 V AC, 220 V DC												
	80	1.5	--				B	5SP5 180-7		1	1	003	0.258
	100		--				B	5SP5 191-7		1	1	003	0.258
	125		--				B	5SP5 192-7		1	1	003	0.258
	2P, 400 V AC, 440 V DC												
	0.3	2	--				C	5SY5 214-7		1	1	003	0.330
	0.5		--				B	5SY5 205-7		1	1	003	0.330
	1		--				A	5SY5 201-7		1	1	003	0.330
	1.6		--				B	5SY5 215-7		1	1	003	0.330
	2			▶			▶	5SY5 202-7		1	1	003	0.330
	3			▶			▶	5SY5 203-7		1	1	003	0.330
	4			--			A	5SY5 204-7		1	1	003	0.330
	6		A	5SY5 206-6		002	▶	5SY5 206-7		1	1/6	003	0.330
	8			--			B	5SY5 208-7		1	1	003	0.330
	10		A	5SY5 210-6		002	▶	5SY5 210-7		1	1	003	0.330
	13		C	5SY5 213-6		002	B	5SY5 213-7		1	1	003	0.330
	16		A	5SY5 216-6		002	▶	5SY5 216-7		1	1	003	0.330
	20		A	5SY5 220-6		002	A	5SY5 220-7		1	1	003	0.330
	25		C	5SY5 225-6		002	A	5SY5 225-7		1	1	003	0.330
	32		B	5SY5 232-6		002	B	5SY5 232-7		1	1	003	0.330
	40		C	5SY5 240-6		002	B	5SY5 240-7		1	1	003	0.330
	50		C	5SY5 250-6		002	A	5SY5 250-7		1	1	003	0.330
	63		C	5SY5 263-6		002	A	5SY5 263-7		1	1	003	0.330
	2P, 400 V AC, 440 V DC												
	80	3	--				B	5SP5 280-7		1	1	003	0.516
	100		--				B	5SP5 291-7		1	1	003	0.516
	125		--				B	5SP5 292-7		1	1	003	0.516

For application examples, see page 1/83.

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.



5SY and 5SP miniature circuit breakers
10 000 A, universal current, 5SP5, 5SY5

10 000 3	I_n	Mounting width MW ¹⁾	DT	Characteristic B		PG	DT	Characteristic C		PU	PS*/ P. unit	PG	Weight per PU approx kg
				Order No.	Price per PU			Order No.	Price per PU				
	A									Unit(s)	Unit(s)		
MCBs 10 000 A, universal current													
4P, 400 V AC, 880 V DC													
	0.3	1		--			C	5SY5 414-7	224,—	1	1	003	0.660
	0.5			--			C	5SY5 405-7	224,—	1	1	003	0.660
	1			--			C	5SY5 401-7	224,—	1	1	003	0.660
	1.6			--			C	5SY5 415-7	224,—	1	1	003	0.660
	2			--			C	5SY5 402-7	224,—	1	1	003	0.660
	3			--			C	5SY5 403-7	224,—	1	1	003	0.660
	4			--			C	5SY5 404-7	224,—	1	1	003	0.660
	6		C	5SY5 406-6	149,—	002	C	5SY5 406-7	224,—	1	1	003	0.660
	8			--			C	5SY5 408-7	224,—	1	1	003	0.660
	10		C	5SY5 410-6	138,—	002	C	5SY5 410-7	198,—	1	1	003	0.660
	13		C	5SY5 413-6	138,—	002	C	5SY5 413-7	198,—	1	1	003	0.660
	16		C	5SY5 416-6	133,—	002	C	5SY5 416-7	198,—	1	1	003	0.660
	20		C	5SY5 420-6	149,—	002	C	5SY5 420-7	198,—	1	1	003	0.660
	25		C	5SY5 425-6	152,—	002	C	5SY5 425-7	221,—	1	1	003	0.660
	32		C	5SY5 432-6	163,—	002	C	5SY5 432-7	224,—	1	1	003	0.660
	40		C	5SY5 440-6	190,—	002	C	5SY5 440-7	259,—	1	1	003	0.660
	50		C	5SY5 450-6	221,—	002	C	5SY5 450-7	299,—	1	1	003	0.660
	63		C	5SY5 463-6	253,—	002	C	5SY5 463-7	349,—	1	1	003	0.660

For application examples, see page 1/83.

¹⁾ 1 MW (modular width) = 18 mm.



BETA Protecting Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
15 000 A, 5SY7

15 000 3	I_n	Mounting width	DT	Characteristic B Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	A	MW ¹⁾				Unit(s)	Unit(s)		kg
MCBs 15 000 A									
	1P, 230/400 V AC								
	6	1	▶	5SY7 106-6		1	1	002	0.165
	10		▶	5SY7 110-6		1	1	002	0.165
	13		C	5SY7 113-6		1	1	002	0.165
	16		▶	5SY7 116-6		1	1	002	0.165
	20		B	5SY7 120-6		1	1	002	0.165
	25		B	5SY7 125-6		1	1	002	0.165
	32		B	5SY7 132-6		1	1	002	0.165
	40		C	5SY7 140-6		1	1	002	0.165
	50		C	5SY7 150-6		1	1	002	0.165
	63		C	5SY7 163-6		1	1	002	0.165
	1P+N, 230 V AC								
	6	2	C	5SY7 506-6		1	1	002	0.330
	10		C	5SY7 510-6		1	1	002	0.330
	13		C	5SY7 513-6		1	1	002	0.330
	16		C	5SY7 516-6		1	1	002	0.330
	20		C	5SY7 520-6		1	1	002	0.330
	25		C	5SY7 525-6		1	1	002	0.330
	32		C	5SY7 532-6		1	1	002	0.330
	40		C	5SY7 540-6		1	1	002	0.330
	50		C	5SY7 550-6		1	1	002	0.330
	63		C	5SY7 563-6		1	1	002	0.330
	2P, 400 V AC								
	6	2	B	5SY7 206-6		1	1	002	0.330
	10		B	5SY7 210-6		1	1	002	0.330
	13		C	5SY7 213-6		1	1	002	0.330
	16		B	5SY7 216-6		1	1	002	0.330
	20		B	5SY7 220-6		1	1	002	0.330
	25		B	5SY7 225-6		1	1	002	0.330
	32		C	5SY7 232-6		1	1	002	0.330
	40		C	5SY7 240-6		1	1	002	0.330
	50		C	5SY7 250-6		1	1	002	0.330
	63		C	5SY7 263-6		1	1	002	0.330
	3P, 400 V AC								
	6	3	B	5SY7 306-6		1	1	002	0.495
	10		B	5SY7 310-6		1	1	002	0.495
	13		C	5SY7 313-6		1	1	002	0.495
	16		A	5SY7 316-6		1	1	002	0.495
	20		B	5SY7 320-6		1	1	002	0.495
	25		B	5SY7 325-6		1	1	002	0.495
	32		B	5SY7 332-6		1	1	002	0.495
	40		B	5SY7 340-6		1	1	002	0.495
	50		B	5SY7 350-6		1	1	002	0.495
	63		C	5SY7 363-6		1	1	002	0.495
	3P+N, 400 V AC								
	6	4	C	5SY7 606-6		1	1	002	0.660
	10		C	5SY7 610-6		1	1	002	0.660
	13		C	5SY7 613-6		1	1	002	0.660
	16		C	5SY7 616-6		1	1	002	0.660
	20		C	5SY7 620-6		1	1	002	0.660
	25		C	5SY7 625-6		1	1	002	0.660
	32		C	5SY7 632-6		1	1	002	0.660
	40		C	5SY7 640-6		1	1	002	0.660
	50		C	5SY7 650-6		1	1	002	0.660
	63		C	5SY7 663-6		1	1	002	0.660
	4P, 400 V AC								
	6	4	C	5SY7 406-6		1	1	002	0.660
	10		B	5SY7 410-6		1	1	002	0.660
	13		C	5SY7 413-6		1	1	002	0.660
	16		B	5SY7 416-6		1	1	002	0.660
	20		B	5SY7 420-6		1	1	002	0.660
	25		C	5SY7 425-6		1	1	002	0.660
	32		C	5SY7 432-6		1	1	002	0.660
	40		C	5SY7 440-6		1	1	002	0.660
	50		C	5SY7 450-6		1	1	002	0.660
	63		C	5SY7 463-6		1	1	002	0.660

¹⁾ 1 MW (modular width) = 18 mm.

5SY and 5SP miniature circuit breakers 15 000 A, 5SY7

15 000 3	I_n	Mounting width MW ¹⁾	DT	Characteristic C			PG	DT	Characteristic D			PU	PS*/ P. unit	PG	Weight per PU approx kg
				Order No.	Price per PU				Order No.	Price per PU					
	A											Unit(s)	Unit(s)		
MCBs 15 000 A															
	1P, 230/400 V AC														
	0.3	1	B	5SY7 114-7			003	C	5SY7 114-8			1	1	004	0.165
	0.5		B	5SY7 105-7			003	C	5SY7 105-8			1	1	004	0.165
	1		A	5SY7 101-7			003	C	5SY7 101-8			1	1	004	0.165
	1.6		B	5SY7 115-7			003	C	5SY7 115-8			1	1	004	0.165
	2		▶	5SY7 102-7			003	C	5SY7 102-8			1	1	004	0.165
	3		A	5SY7 103-7			003	C	5SY7 103-8			1	1	004	0.165
	4		A	5SY7 104-7			003	B	5SY7 104-8			1	1	004	0.165
	6		▶	5SY7 106-7			003	B	5SY7 106-8			1	1	004	0.165
	8		B	5SY7 108-7			003	C	5SY7 108-8			1	1	004	0.165
	10		▶	5SY7 110-7			003	B	5SY7 110-8			1	1	004	0.165
	13		B	5SY7 113-7			003	C	5SY7 113-8			1	1	004	0.165
	16		▶	5SY7 116-7			003	B	5SY7 116-8			1	1	004	0.165
	20		A	5SY7 120-7			003	C	5SY7 120-8			1	1	004	0.165
	25		B	5SY7 125-7			003	C	5SY7 125-8			1	1	004	0.165
	32		B	5SY7 132-7			003	C	5SY7 132-8			1	1	004	0.165
	40		B	5SY7 140-7			003	C	5SY7 140-8			1	1	004	0.165
	50		C	5SY7 150-7			003	C	5SY7 150-8			1	1	004	0.165
	63		B	5SY7 163-7			003	C	5SY7 163-8			1	1	004	0.165
	1P+N, 230 V AC														
	0.3	2	C	5SY7 514-7			003	C	5SY7 514-8			1	1	004	0.330
	0.5		C	5SY7 505-7			003	C	5SY7 505-8			1	1	004	0.330
	1		B	5SY7 501-7			003	C	5SY7 501-8			1	1	004	0.330
	1.6		C	5SY7 515-7			003	C	5SY7 515-8			1	1	004	0.330
	2		B	5SY7 502-7			003	C	5SY7 502-8			1	1	004	0.330
	3		B	5SY7 503-7			003	C	5SY7 503-8			1	1	004	0.330
	4		B	5SY7 504-7			003	B	5SY7 504-8			1	1	004	0.330
	6		A	5SY7 506-7			003	C	5SY7 506-8			1	1	004	0.330
	8		C	5SY7 508-7			003	C	5SY7 508-8			1	1	004	0.330
	10		A	5SY7 510-7			003	C	5SY7 510-8			1	1	004	0.330
	13		B	5SY7 513-7			003	C	5SY7 513-8			1	1	004	0.330
	16		A	5SY7 516-7			003	B	5SY7 516-8			1	1	004	0.330
	20		B	5SY7 520-7			003	C	5SY7 520-8			1	1	004	0.330
	25		B	5SY7 525-7			003	C	5SY7 525-8			1	1	004	0.330
	32		B	5SY7 532-7			003	C	5SY7 532-8			1	1	004	0.330
	40		C	5SY7 540-7			003	C	5SY7 540-8			1	1	004	0.330
	50		C	5SY7 550-7			003	C	5SY7 550-8			1	1	004	0.330
	63		C	5SY7 563-7			003	C	5SY7 563-8			1	1	004	0.330
	2P, 400 V AC														
	0.3	2	C	5SY7 214-7			003	C	5SY7 214-8			1	1	004	0.330
	0.5		B	5SY7 205-7			003	C	5SY7 205-8			1	1	004	0.330
	1		A	5SY7 201-7			003	B	5SY7 201-8			1	1	004	0.330
	1.6		C	5SY7 215-7			003	C	5SY7 215-8			1	1	004	0.330
	2		A	5SY7 202-7			003	A	5SY7 202-8			1	1	004	0.330
	3		A	5SY7 203-7			003	B	5SY7 203-8			1	1	004	0.330
	4		A	5SY7 204-7			003	A	5SY7 204-8			1	1	004	0.330
	6		▶	5SY7 206-7			003	A	5SY7 206-8			1	1	004	0.330
	8		B	5SY7 208-7			003	B	5SY7 208-8			1	1	004	0.330
	10		▶	5SY7 210-7			003	A	5SY7 210-8			1	1	004	0.330
	13		▶	5SY7 213-7			003	C	5SY7 213-8			1	1	004	0.330
	16		B	5SY7 216-7			003	A	5SY7 216-8			1	1	004	0.330
	20		A	5SY7 220-7			003	B	5SY7 220-8			1	1	004	0.330
	25		A	5SY7 225-7			003	B	5SY7 225-8			1	1	004	0.330
	32		A	5SY7 232-7			003	C	5SY7 232-8			1	1	004	0.330
	40		A	5SY7 240-7			003	C	5SY7 240-8			1	1	004	0.330
	50		B	5SY7 250-7			003	C	5SY7 250-8			1	1	004	0.330
	63		B	5SY7 263-7			003	C	5SY7 263-8			1	1	004	0.330

¹⁾ 1 MW (modular width) = 18 mm.



BETA Protecting

Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
15 000 A, 5SY7

15 000 3		I_n	Moun- ting width MW ¹⁾	DT	Characteristic C			PG	DT	Characteristic D			PU	PS*/ P. unit	PG	Weight per PU approx kg
					Order No.	Price per PU				Order No.	Price per PU					
A																
Unit(s)																
Unit(s)																
kg																
	MCBs 15 000 A															
	3P, 400 V AC															
	0.3	3	C	5SY7 314-7			003	C	5SY7 314-8			1	1	004	0.495	
	0.5		C	5SY7 305-7			003	C	5SY7 305-8			1	1	004	0.495	
	1		C	5SY7 301-7			003	C	5SY7 301-8			1	1	004	0.495	
	1.6		C	5SY7 315-7			003	C	5SY7 315-8			1	1	004	0.495	
	2		B	5SY7 302-7			003	C	5SY7 302-8			1	1	004	0.495	
	3		C	5SY7 303-7			003	C	5SY7 303-8			1	1	004	0.495	
	4		A	5SY7 304-7			003	C	5SY7 304-8			1	1	004	0.495	
	6		A	5SY7 306-7			003	C	5SY7 306-8			1	1	004	0.495	
	8		C	5SY7 308-7			003	B	5SY7 308-8			1	1	004	0.495	
	10		A	5SY7 310-7			003	B	5SY7 310-8			1	1	004	0.495	
	13		B	5SY7 313-7			003	C	5SY7 313-8			1	1	004	0.495	
	16		►	5SY7 316-7			003	A	5SY7 316-8			1	1	004	0.495	
	20		►	5SY7 320-7			003	B	5SY7 320-8			1	1	004	0.495	
	25		►	5SY7 325-7			003	A	5SY7 325-8			1	1	004	0.495	
	32		►	5SY7 332-7			003	B	5SY7 332-8			1	1	004	0.495	
	40		►	5SY7 340-7			003	B	5SY7 340-8			1	1	004	0.495	
50		►	5SY7 350-7			003	B	5SY7 350-8			1	1	004	0.495		
63		►	5SY7 363-7			003	B	5SY7 363-8			1	1	004	0.495		
	3P+N, 400 V AC															
	0.3	4	C	5SY7 614-7			003	C	5SY7 614-8			1	1	004	0.660	
	0.5		C	5SY7 605-7			003	C	5SY7 605-8			1	1	004	0.660	
	1		C	5SY7 601-7			003	C	5SY7 601-8			1	1	004	0.660	
	1.6		C	5SY7 615-7			003	C	5SY7 615-8			1	1	004	0.660	
	2		C	5SY7 602-7			003	C	5SY7 602-8			1	1	004	0.660	
	3		C	5SY7 603-7			003	C	5SY7 603-8			1	1	004	0.660	
	4		C	5SY7 604-7			003	C	5SY7 604-8			1	1	004	0.660	
	6		C	5SY7 606-7			003	C	5SY7 606-8			1	1	004	0.660	
	8		C	5SY7 608-7			003	C	5SY7 608-8			1	1	004	0.660	
	10		B	5SY7 610-7			003	C	5SY7 610-8			1	1	004	0.660	
	13		C	5SY7 613-7			003	C	5SY7 613-8			1	1	004	0.660	
	16		A	5SY7 616-7			003	C	5SY7 616-8			1	1	004	0.660	
	20		B	5SY7 620-7			003	C	5SY7 620-8			1	1	004	0.660	
	25		B	5SY7 625-7			003	C	5SY7 625-8			1	1	004	0.660	
	32		B	5SY7 632-7			003	C	5SY7 632-8			1	1	004	0.660	
	40		B	5SY7 640-7			003	C	5SY7 640-8			1	1	004	0.660	
	50		B	5SY7 650-7			003	C	5SY7 650-8			1	1	004	0.660	
63		B	5SY7 663-7			003	C	5SY7 663-8			1	1	004	0.660		
	4P, 400 V AC															
	0.3	4	C	5SY7 414-7			003	C	5SY7 414-8			1	1	004	0.660	
	0.5		C	5SY7 405-7			003	C	5SY7 405-8			1	1	004	0.660	
	1		C	5SY7 401-7			003	C	5SY7 401-8			1	1	004	0.660	
	1.6		C	5SY7 415-7			003	C	5SY7 415-8			1	1	004	0.660	
	2		C	5SY7 402-7			003	C	5SY7 402-8			1	1	004	0.660	
	3		C	5SY7 403-7			003	C	5SY7 403-8			1	1	004	0.660	
	4		B	5SY7 404-7			003	C	5SY7 404-8			1	1	004	0.660	
	6		B	5SY7 406-7			003	C	5SY7 406-8			1	1	004	0.660	
	8		C	5SY7 408-7			003	C	5SY7 408-8			1	1	004	0.660	
	10		►	5SY7 410-7			003	B	5SY7 410-8			1	1	004	0.660	
	13		C	5SY7 413-7			003	C	5SY7 413-8			1	1	004	0.660	
	16		►	5SY7 416-7			003	B	5SY7 416-8			1	1	004	0.660	
	20		A	5SY7 420-7			003	B	5SY7 420-8			1	1	004	0.660	
	25		►	5SY7 425-7			003	B	5SY7 425-8			1	1	004	0.660	
	32		►	5SY7 432-7			003	B	5SY7 432-8			1	1	004	0.660	
	40		A	5SY7 440-7			003	B	5SY7 440-8			1	1	004	0.660	
	50		A	5SY7 450-7			003	B	5SY7 450-8			1	1	004	0.660	
63		►	5SY7 463-7			003	B	5SY7 463-8			1	1	004	0.660		

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.

BETA Protecting Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
25 kA, 5SY8

	I_n	Moun- ting width	DT	Characteristic C	Price per PU	PG	DT	Characteristic D	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	A	MW ¹⁾		Order No.				Order No.		Unit(s)	Unit(s)		kg
	MCBs 25 kA												
	1P, 230/400 V AC												
	0.3	1	C	5SY8 114-7		003	C	5SY8 114-8		1	1	004	0.165
	0.5		C	5SY8 105-7		003	C	5SY8 105-8		1	1	004	0.165
	1		B	5SY8 101-7		003	C	5SY8 101-8		1	1	004	0.165
	1.6		C	5SY8 115-7		003	C	5SY8 115-8		1	1	004	0.165
	2		A	5SY8 102-7		003	B	5SY8 102-8		1	1	004	0.165
	3		C	5SY8 103-7		003	C	5SY8 103-8		1	1	004	0.165
	4		B	5SY8 104-7		003	C	5SY8 104-8		1	1	004	0.165
	6		A	5SY8 106-7		003	C	5SY8 106-8		1	1	004	0.165
	8		C	5SY8 108-7		003	C	5SY8 108-8		1	1	004	0.165
	10		A	5SY8 110-7		003	C	5SY8 110-8		1	1	004	0.165
	13		C	5SY8 113-7		003	C	5SY8 113-8		1	1	004	0.165
	16		A	5SY8 116-7		003	C	5SY8 116-8		1	1	004	0.165
	20		A	5SY8 120-7		003	C	5SY8 120-8		1	1	004	0.165
	25		C	5SY8 125-7		003	C	5SY8 125-8		1	1	004	0.165
	32		B	5SY8 132-7		003	C	5SY8 132-8		1	1	004	0.165
	40		C	5SY8 140-7		003	C	5SY8 140-8		1	1	004	0.165
	50		C	5SY8 150-7		003	C	5SY8 150-8		1	1	004	0.165
	63		C	5SY8 163-7		003	C	5SY8 163-8		1	1	004	0.165
	1P+N, 230 V AC												
	0.3	2	C	5SY8 514-7		003	C	5SY8 514-8		1	1	004	0.330
	0.5		C	5SY8 505-7		003	C	5SY8 505-8		1	1	004	0.330
	1		C	5SY8 501-7		003	C	5SY8 501-8		1	1	004	0.330
	1.6		C	5SY8 515-7		003	C	5SY8 515-8		1	1	004	0.330
	2		C	5SY8 502-7		003	C	5SY8 502-8		1	1	004	0.330
	3		C	5SY8 503-7		003	C	5SY8 503-8		1	1	004	0.330
	4		C	5SY8 504-7		003	C	5SY8 504-8		1	1	004	0.330
	6		B	5SY8 506-7		003	C	5SY8 506-8		1	1	004	0.330
	8		C	5SY8 508-7		003	C	5SY8 508-8		1	1	004	0.330
	10		B	5SY8 510-7		003	C	5SY8 510-8		1	1	004	0.330
	13		C	5SY8 513-7		003	C	5SY8 513-8		1	1	004	0.330
	16		B	5SY8 516-7		003	C	5SY8 516-8		1	1	004	0.330
	20		C	5SY8 520-7		003	C	5SY8 520-8		1	1	004	0.330
	25		C	5SY8 525-7		003	C	5SY8 525-8		1	1	004	0.330
	32		B	5SY8 532-7		003	C	5SY8 532-8		1	1	004	0.330
	40		C	5SY8 540-7		003	B	5SY8 540-8		1	1	004	0.330
	50		B	5SY8 550-7		003	B	5SY8 550-8		1	1	004	0.330
	63		B	5SY8 563-7		003	B	5SY8 563-8		1	1	004	0.330
	2P, 400 V AC												
	0.3	2	C	5SY8 214-7		003	C	5SY8 214-8		1	1	004	0.330
	0.5		C	5SY8 205-7		003	C	5SY8 205-8		1	1	004	0.330
	1		B	5SY8 201-7		003	C	5SY8 201-8		1	1	004	0.330
	1.6		C	5SY8 215-7		003	C	5SY8 215-8		1	1	004	0.330
	2		B	5SY8 202-7		003	B	5SY8 202-8		1	1	004	0.330
	3		C	5SY8 203-7		003	C	5SY8 203-8		1	1	004	0.330
	4		A	5SY8 204-7		003	C	5SY8 204-8		1	1	004	0.330
	6		A	5SY8 206-7		003	A	5SY8 206-8		1	1	004	0.330
	8		C	5SY8 208-7		003	A	5SY8 208-8		1	1	004	0.330
	10		A	5SY8 210-7		003	B	5SY8 210-8		1	1	004	0.330
	13		C	5SY8 213-7		003	C	5SY8 213-8		1	1	004	0.330
	16		A	5SY8 216-7		003	C	5SY8 216-8		1	1	004	0.330
	20		B	5SY8 220-7		003	C	5SY8 220-8		1	1	004	0.330
	25		B	5SY8 225-7		003	B	5SY8 225-8		1	1	004	0.330
	32		B	5SY8 232-7		003	C	5SY8 232-8		1	1	004	0.330
	40		C	5SY8 240-7		003	C	5SY8 240-8		1	1	004	0.330
	50		C	5SY8 250-7		003	C	5SY8 250-8		1	1	004	0.330
	63		C	5SY8 263-7		003	C	5SY8 263-8		1	1	004	0.330

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting

Miniature Circuit Breakers

5SY and 5SP miniature circuit breakers
25 kA, 5SY8

	<i>I</i> _n	Moun- ting width MW ¹⁾	DT	Characteristic C		PG	DT	Characteristic D		PU	PS*/ P. unit	PG	Weight per PU approx kg
				Order No.	Price per PU			Order No.	Price per PU				
	A									Unit(s)	Unit(s)		
	MCBs 25 kA												
	3P, 400 V AC												
	0.3	3	C	5SY8 314-7		003	C	5SY8 314-8		1	1	004	0.495
	0.5		C	5SY8 305-7		003	C	5SY8 305-8		1	1	004	0.495
	1		A	5SY8 301-7		003	C	5SY8 301-8		1	1	004	0.495
	1.6		C	5SY8 315-7		003	C	5SY8 315-8		1	1	004	0.495
	2		C	5SY8 302-7		003	C	5SY8 302-8		1	1	004	0.495
	3		C	5SY8 303-7		003	C	5SY8 303-8		1	1	004	0.495
	4		C	5SY8 304-7		003	C	5SY8 304-8		1	1	004	0.495
	6		B	5SY8 306-7		003	C	5SY8 306-8		1	1	004	0.495
	8		C	5SY8 308-7		003	C	5SY8 308-8		1	1	004	0.495
	10		B	5SY8 310-7		003	C	5SY8 310-8		1	1	004	0.495
	13		C	5SY8 313-7		003	C	5SY8 313-8		1	1	004	0.495
	16		A	5SY8 316-7		003	C	5SY8 316-8		1	1	004	0.495
	20		C	5SY8 320-7		003	C	5SY8 320-8		1	1	004	0.495
	25		A	5SY8 325-7		003	B	5SY8 325-8		1	1	004	0.495
	32		A	5SY8 332-7		003	B	5SY8 332-8		1	1	004	0.495
	40		B	5SY8 340-7		003	C	5SY8 340-8		1	1	004	0.495
50		B	5SY8 350-7		003	B	5SY8 350-8		1	1	004	0.495	
63		B	5SY8 363-7		003	C	5SY8 363-8		1	1	004	0.495	
	3P+N, 400 V AC												
	0.3	4	C	5SY8 614-7		003	C	5SY8 614-8		1	1	004	0.660
	0.5		C	5SY8 605-7		003	C	5SY8 605-8		1	1	004	0.660
	1		C	5SY8 601-7		003	C	5SY8 601-8		1	1	004	0.660
	1.6		C	5SY8 615-7		003	C	5SY8 615-8		1	1	004	0.660
	2		C	5SY8 602-7		003	C	5SY8 602-8		1	1	004	0.660
	3		C	5SY8 603-7		003	C	5SY8 603-8		1	1	004	0.660
	4		C	5SY8 604-7		003	C	5SY8 604-8		1	1	004	0.660
	6		C	5SY8 606-7		003	C	5SY8 606-8		1	1	004	0.660
	8		C	5SY8 608-7		003	C	5SY8 608-8		1	1	004	0.660
	10		C	5SY8 610-7		003	C	5SY8 610-8		1	1	004	0.660
	13		C	5SY8 613-7		003	C	5SY8 613-8		1	1	004	0.660
	16		B	5SY8 616-7		003	C	5SY8 616-8		1	1	004	0.660
	20		C	5SY8 620-7		003	C	5SY8 620-8		1	1	004	0.660
	25		C	5SY8 625-7		003	C	5SY8 625-8		1	1	004	0.660
	32		B	5SY8 632-7		003	C	5SY8 632-8		1	1	004	0.660
	40		C	5SY8 640-7		003	C	5SY8 640-8		1	1	004	0.660
	50		C	5SY8 650-7		003	C	5SY8 650-8		1	1	004	0.660
63		A	5SY8 663-7		003	C	5SY8 663-8		1	1	004	0.660	
	4P, 400 V AC												
	0.3	4	C	5SY8 414-7		003	C	5SY8 414-8		1	1	004	0.660
	0.5		C	5SY8 405-7		003	C	5SY8 405-8		1	1	004	0.660
	1		C	5SY8 401-7		003	C	5SY8 401-8		1	1	004	0.660
	1.6		C	5SY8 415-7		003	C	5SY8 415-8		1	1	004	0.660
	2		C	5SY8 402-7		003	C	5SY8 402-8		1	1	004	0.660
	3		C	5SY8 403-7		003	C	5SY8 403-8		1	1	004	0.660
	4		C	5SY8 404-7		003	C	5SY8 404-8		1	1	004	0.660
	6		C	5SY8 406-7		003	C	5SY8 406-8		1	1	004	0.660
	8		C	5SY8 408-7		003	C	5SY8 408-8		1	1	004	0.660
	10		B	5SY8 410-7		003	C	5SY8 410-8		1	1	004	0.660
	13		C	5SY8 413-7		003	C	5SY8 413-8		1	1	004	0.660
	16		A	5SY8 416-7		003	C	5SY8 416-8		1	1	004	0.660
	20		A	5SY8 420-7		003	C	5SY8 420-8		1	1	004	0.660
	25		A	5SY8 425-7		003	C	5SY8 425-8		1	1	004	0.660
	32		A	5SY8 432-7		003	C	5SY8 432-8		1	1	004	0.660
	40		A	5SY8 440-7		003	C	5SY8 440-8		1	1	004	0.660
	50		A	5SY8 450-7		003	C	5SY8 450-8		1	1	004	0.660
63		A	5SY8 463-7		003	C	5SY8 463-8		1	1	004	0.660	


¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.


5SY and 5SP miniature circuit breakers

Dimensional drawings

5SY




5SP




Schematics

Symbols

5SY6, 5SY4, 5SY7, 5SY8



5SP4



5SY5, 5SP5




BETA Protecting Miniature Circuit Breakers

5SJ6 ...-KS miniature circuit breakers
with plug-in terminals


Overview

Miniature circuit breakers with plug-in terminals are used for the protection of socket outlets and lighting circuits with the most common rated currents of 10 to 20 A.


Benefits



- Double, screwless and mutually independent outgoing terminals for fast connection of conductors.



- The plug-in terminal, offering easily accessible and angled cable entries for manual insertion, saves mounting time.
- Separate removal of individual conductors requires no tools and ensures high operating safety.
- No end sleeves required for finely stranded conductors. This saves mounting time.



- Conventional pin busbars are used for the incoming terminal. This ensures clear, manageable and convenient access to all terminals as part of the uniform Siemens connection concept.

5SJ6 ...-KS miniature circuit breakers with plug-in terminals

Technical specifications

5SJ6 ...-KS			
Standards			EN 60898
Approvals			See page 1/4
Operational voltage			
• Min.	V AC/DC	24	
• Max.	V AC	400	
• Max.	V DC/pole	60 ¹⁾	
Rated switching capacity	Acc. to EN 60898	kA AC	6
Insulation coordination			
• Rated insulation voltage	V AC	250/440	
• Degree of pollution for overvoltage category		2/III	
Touch protection	Acc. to EN 50274		Yes
Handle end position, sealable			Yes
Degree of protection	Acc. to EN 60529		IP20, with connected conductors
CFC and silicone-free			Yes
Terminals			Screwless terminals on the outgoing terminals for 1.5 ... 4 mm ²
Conductor cross-sections			
• Top, plug-in terminals			
- Solid, stranded and finely stranded, without end sleeve	mm ²	1.5 ... 4	
- Finely stranded, with end sleeve	mm ²	1.5 ... 2.5	
• Bottom, tunnel terminal			
- Solid, stranded or finely stranded, with end sleeve	mm ²	0.75 ... 25	
Mounting position			Any
Service life			
On average, with rated load			20 000 actuations
Ambient temperature		°C	-25 ... +45, occasionally +55, max. 95 % humidity, storage temperature: -40 ... +75
Resistance to climate	Acc. to IEC 60068-2-30		6 cycles
Resistance to vibrations	Acc. to IEC 60068-2-6	m/s ²	60 at 10 Hz ... 150 Hz

¹⁾ The operational voltage 60 V DC/pole takes into account a battery charging voltage with a peak value of 72 V.

BETA Protecting Miniature Circuit Breakers


5SJ6 ...-KS miniature circuit breakers
with plug-in terminals

Selection and ordering data

6000 3		I_n A	Moun- ting width MW ¹⁾	DT	Characteristic B			PG	DT	Characteristic C			Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx kg
Order No.					Price per PU	Order No.											
	Miniature circuit breakers with plug-in terminal													Unit(s)	Unit(s)		
	1P																
	10	1	B	5SJ6 110-6KS		002	B	5SJ6 110-7KS		1	1	003	0.111				
	13		B	5SJ6 113-6KS		002	B	5SJ6 113-7KS		1	1/12	003	0.111				
	16		A	5SJ6 116-6KS		002	B	5SJ6 116-7KS		1	1	003	0.111				
	20		B	5SJ6 120-6KS		002	B	5SJ6 120-7KS		1	1/12	003	0.111				
	1P+N																
	10	2	B	5SJ6 510-6KS		002	B	5SJ6 510-7KS		1	1/6	003	0.185				
	13		B	5SJ6 513-6KS		002	B	5SJ6 513-7KS		1	1/6	003	0.185				
	16		B	5SJ6 516-6KS		002	B	5SJ6 516-7KS		1	1/6	003	0.185				
	20		B	5SJ6 520-6KS		002	B	5SJ6 520-7KS		1	1/6	003	0.185				
	2P																
	10	2	B	5SJ6 210-6KS		002	B	5SJ6 210-7KS		1	1/6	003	0.225				
	13		B	5SJ6 213-6KS		002	B	5SJ6 213-7KS		1	1/6	003	0.225				
	16		B	5SJ6 216-6KS		002	B	5SJ6 216-7KS		1	1/6	003	0.225				
	20		B	5SJ6 220-6KS		002	B	5SJ6 220-7KS		1	1/6	003	0.225				
	3P																
	10	3	B	5SJ6 310-6KS		002	B	5SJ6 310-7KS		1	1/4	003	0.345				
	13		B	5SJ6 313-6KS		002	B	5SJ6 313-7KS		1	1/4	003	0.345				
	16		B	5SJ6 316-6KS		002	B	5SJ6 316-7KS		1	1/4	003	0.345				
	20		B	5SJ6 320-6KS		002	B	5SJ6 320-7KS		1	1/4	003	0.345				


¹⁾ 1 MW (modular width) = 18 mm.

Dimensional drawings



Schematics

Symbols



* You can order this quantity or a multiple thereof.

5SY6 0 miniature circuit breakers, 1+N in 1 MW

Overview

These miniature circuit breakers are used for the protection of plants with switched neutral conductors in distribution boards with little space. They are just a single modular width.


Compact busbars facilitate installation in space saving distribution boards.

The devices are approved for worldwide use according to IEC standards for systems up to 250 V AC. 60 V DC per pole is permitted in DC systems according to IEC standards.

Benefits




- Auxiliary switches and fault signal contacts from the high-capacity range can be freely mounted on these miniature circuit breakers. This increases availability and cuts down on logistics.



- For 3-pole busbars, the 5ST3 6 busbar system is used – a universal system suitable for all miniature circuit breakers.



- By actuating the latching slide, the miniature circuit breakers can be quickly and easily removed from the assembly.



- The infed can be implemented either from the top or the bottom. Additional terminals with lateral cable entry facilitate mounting when using large conductor cross-sections.

BETA Protecting Miniature Circuit Breakers

5SY6 0 miniature circuit breakers, 1+N in 1 MW

Technical specifications

		5SY6 0..
Standards		EN 60898-1
Approvals		See page 1/4
Rated voltage U_n	V AC	230
Operational voltage		
• Min.	V AC/DC	24
• Max.	V AC	250
• Max.	V DC/pole	60 ¹⁾
Rated switching capacity I_{cn}		
• Acc. to IEC/EN 60898-1	kA AC	6
	kA AC	6
Insulation coordination		
• Rated insulation voltage	V AC	250
• Degree of pollution for overvoltage category		2/III
Touch protection	Acc. to EN 50274	Yes
Handle end position, sealable		Yes
Degree of protection		IP20, with connected conductors
CFC and silicone-free		Yes
Terminals		
• Solid and stranded, top and bottom terminal	mm ²	0.75 ... 16
• Finely stranded, with end sleeve, top and bottom terminal	mm ²	0.75 ... 10
• Terminal tightening torque	Nm	2.0
Mains connection		Bottom
Mounting position		Any
Service life		
On average, with rated load		20 000 actuations At 40 A: 8000 actuations
Ambient temperature	°C	-25 ... +45, occasionally +55, max. 95 % humidity, storage temperature: -40 ... +75
Resistance to climate	Acc. to IEC 60068-2-30	6 cycles
Resistance to vibrations	Acc. to IEC 60068-2-6 m/s ²	60 at 10 ... 150 Hz

¹⁾ The operational voltage 60 V DC/pole takes into account a battery charging voltage with a peak value of 72 V.



BETA Protecting Miniature Circuit Breakers






1

5SY6 0 miniature circuit breakers, 1+N in 1 MW

Selection and ordering data

6000 3	I_n	MW ¹⁾	DT	Characteristic B			PG	DT	Characteristic C			PU	PS*/ P. unit	PG	Weight per PU approx
				Order No.	Price per PU				Order No.	Price per PU					
	A											Unit(s)	Unit(s)		kg
Miniature circuit breakers, compact, 1+N (1P+N), 230 V AC															
N pole, right															
	2	1		--				A	5SY6 002-7			1	1	003	0.107
	4			--				A	5SY6 004-7			1	1	003	0.106
	6		A	5SY6 006-6			002	A	5SY6 006-7			1	1	003	0.100
	8			--				D	5SY6 008-7			1	1	003	0.100
	10		A	5SY6 010-6			002	A	5SY6 010-7			1	1	003	0.100
	13		A	5SY6 013-6			002	A	5SY6 013-7			1	1	003	0.100
	16		A	5SY6 016-6			002	A	5SY6 016-7			1	1	003	0.100
	20		A	5SY6 020-6			002	A	5SY6 020-7			1	1	003	0.100
	25		A	5SY6 025-6			002	A	5SY6 025-7			1	1	003	0.100
	32		A	5SY6 032-6			002	A	5SY6 032-7			1	1	003	0.100
	40		A	5SY6 040-6			002	D	5SY6 040-7			1	1	003	0.100
N pole, left															
	2	1		--				A	5SY6 002-7KL			1	1	003	0.100
	4			--				A	5SY6 004-7KL			1	1	003	0.100
	6		A	5SY6 006-6KL			002	D	5SY6 006-7KL			1	1	003	0.100
	8			--				D	5SY6 008-7KL			1	1	003	0.100
	10		D	5SY6 010-6KL			002	A	5SY6 010-7KL			1	1	003	0.100
	13		D	5SY6 013-6KL			002	D	5SY6 013-7KL			1	1	003	0.100
	16		A	5SY6 016-6KL			002	D	5SY6 016-7KL			1	1	003	0.100
	20		D	5SY6 020-6KL			002	D	5SY6 020-7KL			1	1	003	0.100
	25		D	5SY6 025-6KL			002	D	5SY6 025-7KL			1	1	003	0.100
	32		D	5SY6 032-6KL			002	D	5SY6 032-7KL			1	1	003	0.100
	40		D	5SY6 040-6KL			002	D	5SY6 040-7KL			1	1	003	0.100

¹⁾ 1 MW (modular width) = 18 mm.

	Pin spacing	Length	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	MW ¹⁾	mm				Unit(s)	Unit(s)		kg
	5ST3 7 busbar systems, 10 mm² 12 MW, for MCBs 1+N in 1 MW of the compact range, can be cut, with end caps								
	Single-phase								
	For 12 MCB 1+N, gray	1	216	A	5ST3 762	1	10	027	0.029
	For 12 MCB 1+N, blue		216	A	5ST3 763	1	10	027	0.029
	5ST3 7 busbar systems, 10 mm², for MCBs 1+N in 1 MW of the compact range, can be cut, without end caps								
	Single-phase								
	For MCB 1+N, gray	1	1016	A	5ST3 764	1	10	027	0.134
	For MCB 1+N, blue		1016	A	5ST3 765	1	10	027	0.134
	End caps for 5ST3 76 busbars								
	1 set comprises a right and a left cap								
	Gray		A	5ST3 766		1 set	10 sets	027	0.001
	Blue		A	5ST3 767		1 set	10 sets	027	0.001
	5ST3 6 busbar systems, 10 mm², for MCBs, fixed lengths, cannot be cut, fully insulated								
	Three-phase								
	For 6 MCB 1+N	1	102	A	5ST3 613	1	10	027	0.039
	For 9 MCB 1+N		257.5	A	5ST3 614	1	10	027	0.060
	For 12 MCB 1+N		210	▶	5ST3 615	1	10	027	0.076
	Terminals for 5ST3 76								
	Side terminals		A	5ST3 768		1	25	027	0.011
	For conductors up to 25 mm ²								


¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.


BETA Protecting Miniature Circuit Breakers

5SY6 0 miniature circuit breakers, 1+N in 1 MW

Dimensional drawings




1P+N
N pole right



1P+N
N pole left

5ST3 6 Pin spacing in MW


Dimensions of side view in mm (approx.).




5ST3 613
5ST3 614
5ST3 615

5ST3 7 Pin spacing in MW

Dimensions of side view in mm (approx.).



5ST3 762
5ST3 764



5ST3 763
5ST3 765

Schematics

Symbols



1P+N
N pole right



1P+N
N pole left

BETA Protecting Miniature Circuit Breakers

Additional components

Overview

The Siemens mounting concept supports the combination of all 5ST3 additional components with Siemens miniature circuit breakers and 5SU1 RCBOs.

Auxiliary switches (AS)

The auxiliary switch (AS) always signals the contact position of the miniature circuit breaker, regardless of whether the miniature circuit breaker was tripped manually or as the result of a fault. An additional version is also available for the switching of small currents and voltages for the control of programmable control systems (PLCs) acc. to EN 61131-2. The auxiliary switch with test button enables the testing of control circuits without the need to switch the miniature circuit breaker.

Fault signal contacts (FC)

The fault signal contact (FC) signals the automatic tripping of the miniature circuit breaker in the event of a fault, such as an overload or a short circuit. If the fault signal contact is activated, the contact position does not change if the miniature circuit breaker is tripped manually. Fault signal contacts with TEST and RESET buttons enable the testing of control circuits without the need to trip the miniature circuit breaker. The red RESET button integrated in the handle also indicates the automatic tripping of the MCB. The signal can be acknowledged manually using the RESET button.

Shunt trips (ST)

Shunt trips are used for the remote tripping of miniature circuit breakers.

Undervoltage releases (UR)

Undervoltage releases are integrated (e. g. in EMERGENCY STOP loops), thus ensuring that the MCB trips in the event of an emergency, which, in turn, ensures disconnection of the control circuit according to EN 60204. In the event that the voltage is interrupted or too low, it also trips, i. e. prevents the MCB from switching on.

Remote controlled mechanisms (RC)

Remote controlled mechanisms are used for the remote ON/OFF switching of miniature circuit breakers and the remote ON switching of RC units, as well as the local manual switching of these devices. A blocking function permits maintenance work. In the event that a miniature circuit breaker or RC unit is tripped, an acknowledgment must be carried out prior to switching back on. The remote controlled mechanism has an operating mode selector switch with the functions: "Locked", "Manual" and "Remote Switching". The mechanism can be mechanically latched and locked, which serves to protect personnel during maintenance work.

RC units

RC units can be combined with miniature circuit breakers of characteristic A, B, C and D. They then form a combination of RCCB and MCB for personnel, fire and line protection. The combinations can be tailored to suit user requirements.

For information on RC units, please refer to the chapter "Residual current protective devices".

Benefits

All additional components can be universally mounted



- The 5SY and 5SP miniature circuit breakers are ideal for the quick and easy mounting of auxiliary switches and fault signal contacts. Captive metal brackets on additional components ensure the quick and easy mounting of devices on the miniature circuit breakers without the need for tools.



- Fault signal contacts with TEST and RESET button enable the simple testing of auxiliary circuits and, in the event of a fault, acknowledgement of the fault over the RESET button, without the need to switch the miniature circuit breakers.



- The auxiliary switches with TEST button enable the simple manual testing of control circuits during operation of the entire plant without the need to switch the miniature circuit breakers.

BETA Protecting Miniature Circuit Breakers

Additional components

Technical specifications

	Auxiliary switches (AS)			Fault signal contacts (FC)
	5ST3 010, 5ST3 010-2	5ST3 013	5ST3 013-2	5ST3 020, 5ST3 020-2
	5ST3 011, 5ST3 011-2	5ST3 014	5ST3 014-2	5ST3 021, 5ST3 021-2
	5ST3 012, 5ST3 012-2	5ST3 015	5ST3 015-2	5ST3 022, 5ST3 022-2
Standards	EN 62019; IEC/EN 60947-5-1; UL 1077; CSA C22.2 No. 235			
Approvals	See page 1/4			
Short-circuit protection	B6 or C6 miniature circuit breakers, or fuse gG 6 A			
Contact load				
• Min.	50 mA, 24 V	1 mA/5 V DC	5 mA/5 V DC	50 mA, 24 V
• Max.	--	50 mA/30 V DC	--	--
• 400 V AC, AC-14, NO	A	2	--	2
• 230 V AC, AC-14, NO	A	6	--	6
• 400 V AC, AC-13, NC	A	2	--	2
• 230 V AC, AC-13, NC	A	6	--	6
• 220 V DC, DC-13, NO+NC	A	1	--	1
• 110 V DC, DC-13, NO+NC	A	1	--	1
• 60 V DC, DC-13, NO+NC	A	3	--	3
• 24 V DC, DC-13, NO+NC	A	6	--	6

		Undervoltage releases (UR)	Shunt trips (ST)		Remote controlled mechanisms (RC)
		5ST3 04.	5ST3 030	5ST3 031	5ST3 050
Standards		EN 60898; EN 60947-1			
Rated voltages U_n	V AC	230	110 ... 415	24 ... 60	230
	V DC	24, 110	110	24 ... 60	--
• Rated frequency f_n	Hz	--	50 ... 60	--	50 ... 60
Response limits					
• Acc. to EN 60947-1, 7.2.1.3					
- Releases		$< 0.35 \dots 0.7 \times U_n$	--	--	--
- Permissible fluctuations of the power supply		$0.85 \dots 1.1 \times U_n$	--	--	--
• Acc. to EN 60947-1, 7.2.1.4		--	$0.7 \dots 1.1 \times U_n$	--	--

For technical data on the RC units, please refer to the chapter "Residual current protective devices".

Selection and ordering data

	MW ¹⁾	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
					Unit(s)	Unit(s)		kg
	Auxiliary switches (AS)							
	For 5SY, 5SP miniature circuit breakers, 5SU1 RCBOs and 5TE8 switches							
	1 NO + 1 NC	0.5	▶ 5ST3 010		1	1	027	0.050
	For small output		▶ 5ST3 013		1	1	027	0.050
	2 NO	A	5ST3 011		1	1	027	0.050
	For small output	B	5ST3 014		1	1	027	0.050
	2 NC	A	5ST3 012		1	1	027	0.050
For small output	B	5ST3 015		1	1	027	0.050	
	Auxiliary switches (AS) with TEST button							
	For 5SY, 5SP miniature circuit breakers, 5SU1 RCBOs and 5TE8 switches							
								
	1 NO + 1 NC	0.5	A 5ST3 010-2		1	1	027	0.045
	For small output		A 5ST3 013-2		1	1	027	0.045
	2 NO	A	5ST3 011-2		1	1	027	0.045
	For small output	A	5ST3 014-2		1	1	027	0.045
2 NC	A	5ST3 012-2		1	1	027	0.045	
For small output	A	5ST3 015-2		1	1	027	0.045	

¹⁾ 1 MW (modular width) = 18 mm.

Additional components


	Rated voltage	MW ¹⁾	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	U_n V					Unit(s)	Unit(s)		kg
	Fault signal contacts (FC)								
	For 5SY, 5SP miniature circuit breakers and 5SU1 RCBOs								
	1 NO + 1 NC	0.5	▶	5ST3 020		1	1	027	0.050
	2 NO		B	5ST3 021		1	1	027	0.050
	Fault signal contacts (FC) with TEST and ACKNOWLEDGE button								
	For 5SY, 5SP miniature circuit breakers and 5SU1 RCBOs								
	1 NO + 1 NC	0.5	A	5ST3 020-2		1	1	027	0.050
	2 NO		A	5ST3 021-2		1	1	027	0.050
	Undervoltage releases (UR)								
	For 5SY, 5SP MCBs and 5SU1 RCBOs – not suitable for use with 5SY6 0..								
	With integrated auxiliary switch								
	230 AC	1	A	5ST3 040		1	1	027	0.115
	110 DC		B	5ST3 041		1	1	027	0.115
	24 DC		B	5ST3 042		1	1	027	0.115
	Without integrated auxiliary switch								
	230 AC	1	A	5ST3 043		1	1	027	0.115
	Shunt trips (ST)								
	For 5SY, 5SP MCBs and 5SU1 RCBOs – not suitable for use with 5SY6 0..								
	2 NO	1	▶	5ST3 030		1	1	027	0.098
	2 NC	1	▶	5ST3 031		1	1	027	0.098
	Remote controlled mechanisms (RC)								
	For 5SY, 5SP miniature circuit breakers and 5SU1 RCBOs								
	230 AC	3.5	A	5ST3 050		1	1	027	0.395

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting

Miniature Circuit Breakers

Additional components

	Rated residual current $I_{\Delta n}$ mA	Rated current I_n A	MW ¹⁾	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
RC units, type A, instantaneous tripping										
For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 2P, 230 ... 400 V AC, 50 ... 60 Hz										
	10	0.3 ... 16	2	B	5SM2 121-6		1	1	007	0.180
	30	0.3 ... 40		▶	5SM2 322-6		1	1	007	0.170
	300			A	5SM2 622-6		1	1	007	0.170
	30	0.3 ... 63		A	5SM2 325-6		1	1	007	0.170
	100			B	5SM2 425-6		1	1	007	0.170
	300			B	5SM2 625-6		1	1	007	0.170
	500			B	5SM2 725-6		1	1	007	0.170
For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 3P, 230 ... 400 V AC, 50 ... 60 Hz										
	30	0.3 ... 40	3	A	5SM2 332-6		1	1	007	0.260
	300			A	5SM2 632-6		1	1	007	0.260
	30	0.3 ... 63		B	5SM2 335-6		1	1	007	0.260
	100			B	5SM2 435-6		1	1	007	0.260
	300			B	5SM2 635-6		1	1	007	0.260
	500			B	5SM2 735-6		1	1	007	0.260
For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 4P, 230 ... 400 V AC, 50 ... 60 Hz										
	30	0.3 ... 40	3	▶	5SM2 342-6		1	1	007	0.290
	300			▶	5SM2 642-6		1	1	007	0.290
	30	0.3 ... 63		A	5SM2 345-6		1	1	007	0.290
	100			B	5SM2 445-6		1	1	007	0.290
	300			A	5SM2 645-6		1	1	007	0.290
	500			A	5SM2 745-6		1	1	007	0.290
For 5SP4 miniature circuit breakers (characteristic B and C) 2P, 125 ... 230 V AC, 50 ... 60 Hz										
	30	80 ... 100	3.5	B	5SM2 327-6		1	1	007	0.410
	300			B	5SM2 627-6		1	1	007	0.410
For 5SP4 miniature circuit breakers (characteristic B and C), 4P, 230 ... 400 V AC, 50 ... 60 Hz										
	30	80 ... 100	5	B	5SM2 347-6		1	1	007	0.630
	300			A	5SM2 647-6		1	1	007	0.630

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.

Additional components

	Rated residual current $I_{\Delta n}$ mA	Rated current I_n A	MW ¹⁾	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
	RC units, type A, super resistant [K] For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 2P, 230 ... 400 V AC, 50 ... 60 Hz									
	30	0.3 ... 40	2	B	5SM2 322-6KK01		1	1	007	0.350
	30	0.3 ... 63		B	5SM2 325-6KK01		1	1	007	0.350
	For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 3P, 230 ... 400 V AC, 50 ... 60 Hz									
	30	0.3 ... 40	3	B	5SM2 332-6KK01		1	1	007	0.365
	30	0.3 ... 63		B	5SM2 335-6KK01		1	1	007	0.365
	RC units, type A, selective [S] For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 2P, 230 ... 400 V AC, 50 ... 60 Hz									
	300	0.3 ... 40	2	A	5SM2 622-8		1	1	007	0.170
	300	0.3 ... 63		B	5SM2 625-8		1	1	007	0.170
	For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 3P, 230 ... 400 V AC, 50 ... 60 Hz									
	300	0.3 ... 63	3	B	5SM2 635-8		1	1	007	0.260
	500			B	5SM2 735-8		1	1	007	0.400
	For 5SY miniature circuit breakers, not suitable for use with 5SY5, 5SY8 and 5SY6 0..., 4P, 230 ... 400 V AC, 50 ... 60 Hz									
	300	0.3 ... 63	3	A	5SM2 645-8		1	1	007	0.290
	500			A	5SM2 745-8		1	1	007	0.400
	1000			A	5SM2 845-8		1	1	007	0.290
	For 5SP4 miniature circuit breakers (characteristic B and C) 2P; 125 ... 230 V AC, 50 ... 60 Hz									
	300	80 ... 100	3.5	B	5SM2 627-8		1	1	007	0.410
	For 5SP4 miniature circuit breakers (characteristic B and C) 4P, 230 ... 400 V AC, 50 ... 60 Hz									
	300	80 ... 100	5	A	5SM2 647-8		1	1	007	0.630
	1000			A	5SM2 847-8		1	1	007	0.630
	For 5SP4 miniature circuit breakers (characteristic B and C) 4P, 230 ... 400 V AC, 50 ... 60 Hz									
	300	80 ... 100	5	A	5SM2 647-8		1	1	007	0.630
	1000			A	5SM2 847-8		1	1	007	0.630

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers

Additional components

Version	MW ¹⁾	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
 Terminal covers For miniature circuit breakers, not suitable for use with 5SY6 0... , for additional covering of the screw openings per pole, sealable. In the case of 5SY, also prevents removal of device from the standard mounting rail.		B	5ST3 800		1	10	027	0.001
 Handle locking devices Can be sealed against unwanted manual ON/OFF switching For 5SP and 5SY miniature circuit breakers For padlock with max. 3 mm shackle		A	5ST3 801		1	1	027	0.008
 For 5SJ, 5SP and 5SY miniature circuit breakers For padlock with max. 3 ... 6 mm shackle		A	5ST3 806		1	5	027	0.007
 Padlocks For 5ST3 801 and 5ST3 806 handle locking devices		▶	5ST3 802		1	1	027	0.027
Locking devices Comprising 5ST3 801 handle locking device and 5ST3 802 padlock		B	5ST3 803		1 set	1 set	027	0.035
 Spacers Can be placed on either side of the standard mounting rail. Two spacers allow for convenient cable routing	0.5	▶	5TG8 240		1	2	027	0.010
 Fixing parts Made of plastic, for use on a mounting plate		B	5ST2 201		1	1	027	0.012
 Inscription labels 15 mm x 9 mm, 3 frames à 44 labels, can be mounted on casing collar, white, self-adhesive		B	5ST2 173		1 set	1 set	027	0.038

Labeling systems

Inscription on self-adhesive labels for a uniform and tidy appearance in electrical power distribution. The labeling program can be downloaded to your PC free of charge at:

www.siemens.com/labeling-tool

Recommended ELAT-3-747 labels for printing out on normal printers can be ordered at:


Brady GmbH
 Otto-Hahn-Str. 5-7
 D-63222 Langen
 Tel: +49 (0) 61 03/75 98-660

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers

1

Additional components


Version	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
 Terminal covers, gray For surface mounting, degree of protection IP40, sealable, with 35 mm standard mounting rail • Up to 2.5 MW • Up to 4.5 MW	B	5SW3 004		1	1	008	0.084
	B	5SW3 005		1	1	008	0.114
 Wall enclosures, gray For flush mounting, degree of protection IP40 with 35 mm standard mounting rail • Up to 2.5 MW • Up to 4.5 MW	B	5SW3 006		1	1/4	008	0.126
	B	5SW3 007		1	1	008	0.147
 Molded-plastic enclosures, gray For surface mounting, degree of protection IP54, with 35 mm standard mounting rail, sealable, with transparent hinged lid For 4.5 MW	A	5SW1 200		1	1	008	0.450
 Covers Can be assembled as mini distribution board, suitable for all devices, cover parts prepared for rail mounting of conventional label caps, comprising: • End plates (for snapping onto standard mounting rail) • Angled profile (approx. 1 m long) • Alternative flat profiles (as a cover between the rows of devices length approx. 1 m)	A	5ST2 134		1	10	027	0.022
	A	5ST2 135		1	5	027	0.330
	B	5ST2 136		1	5	027	0.260
 Holders for front panel installation Universal application for devices from 1 to 6 MW Cutout dimensions: Height 45 ^{+0.5} mm Width: 23, 41, 59, 77, 95 or 113 mm	B	7LF9 006		1	1	027	0.071
 Intermediate frames for 70 mm devices in 55 mm ALPHA SIMBOX distribution boards Versions • 1-tier • 2-tier • 3-tier • 4-tier	A	8GB4 561		1	1	032	0.900
	A	8GB4 562		1	1	032	1.100
	A	8GB4 563		1	1	032	1.300
	A	8GB4 564		1	1	032	1.500

For further information on the ALPHA distribution boards, ALPHA SIMBOX small distribution boards and intermediate frames, please refer to Catalog ET A1, chapter "ALPHA SIMBOX Small Distribution Boards".


BETA Protecting Miniature Circuit Breakers

Additional components


Dimensional drawings




5ST3 010 5ST3 030
5ST3 011 5ST3 031
5ST3 012 5ST3 040
5ST3 013 5ST3 041
5ST3 014 5ST3 042
5ST3 015 5ST3 043
5ST3 020 5ST3 044
5ST3 021 5ST3 045
5ST3 022



5ST3 050



5ST3 010-2
5ST3 011-2
5ST3 012-2
5ST3 013-2
5ST3 014-2
5ST3 015-2



5ST3 020-2
5ST3 021-2
5ST3 022-2

Schematics

Symbols

Auxiliary switches (AS)



5ST3 010
5ST3 013
5ST3 010-2
5ST3 013-2



5ST3 011
5ST3 014
5ST3 011-2
5ST3 014-2



5ST3 012
5ST3 015
5ST3 012-2
5ST3 015-2

Fault signal contacts (FC)



5ST3 020
5ST3 020-2




5ST3 021
5ST3 021-2




5ST3 022
5ST3 022-2

Shunt trips (ST)



5ST3 030
5ST3 031

Undervoltage releases (UR)




5ST3 040
5ST3 041
5ST3 042



5ST3 043
5ST3 044
5ST3 045

Remote controlled mechanisms (RC)



5ST3 050

Additional components

The chart shows which additional components can be mounted on either the right or the left.



BETA Protecting Miniature Circuit Breakers

Busbars
5ST3 6, 5ST3 7 standard

Overview

The busbar system with pin-type connections can be used for all 5SJ6 ...-KS and 5SY miniature circuit breakers with or without mounted auxiliary switch (AS) or fault signal contact (FC).

Busbars are available in 10 mm² and 16 mm² versions.

The 5ST3 7 busbar system with bars that can be cut to length can be tailored to any requirements.


The extremely flexible 5ST3 6 busbar system with fixed lengths also enables installation in any length as the busbars can be overlapped.

No further need for time-consuming tasks, such as cutting, cutting to length, deburring, cleaning of cut surfaces and mounting of end caps.


Any free pins on the busbars can be made safe by covering with touch protection.

For further information on bus-mounting miniature circuit breakers with residual current operated circuit breakers, please refer to the chapter "Residual current protective devices".

Benefits




- Between the devices, the busbar, located at the bottom and behind the conductor, provides an optimum wiring space with easy view of the inserted conductor. This enables easy control of connections.



- The ability to overlap the busbar mounting enables a cross-section enlargement of up to 32 mm² using the respective 10 and 16 mm² components.



- By overlapping the busbars with fixed lengths, it is possible to achieve device combinations with any number of devices.




- The fact that the connection of the conductor is always clearly visible facilitates control and insertion of conductors of all pole types and considerably reduces mounting times.


Technical specifications

5ST3		
Standards	EN 60439-1 (VDE 0660-500): 2005-01	
Busbar material	SF-Cu F 24	
Partition material	Plastic, Cyclicoloy 3600 heat-resistant over 90 °C flame-retardant and self-extinguishing, dioxin and halogen-free	
Rated operational voltage U_c	V AC	400
Rated current I_n		
• Cross-section 10 mm ²	A	63
• Cross-section 16 mm ²	A	80
Rated impulse withstand voltage U_{imp}	kV	4
Test pulse voltage (1.2/50)	kV	6.2
Rated conditional short-circuit current I_{cc}	kA	25
Resistance to climate		
• Constant atmosphere	Acc. to DIN 50015	23/83; 40/92; 55/20
• Humid heat	Acc. to IEC 60068-2-30	28 cycles
Insulation coordination		
• Overvoltage category	III	
• Degree of pollution	2	
Maximum busbar current I_S/phase		
• Infeed at the start of the busbar		
- Cross-section 10 mm ²	A	63
- Cross-section 16 mm ²	A	80
• Infeed at the center of the busbar		
- Cross-section 10 mm ²	A	100
- Cross-section 16 mm ²	A	130

Infeed at the start or end of the busbar



Infeed along the busbar or midpoint infeed



The sum of the output current per branch (1, 2, 3 ... n) must not be greater than the max. busbar current I_S /phase.

BETA Protecting Miniature Circuit Breakers

Busbars
5ST3 6, 5ST3 7 standard

Selection and ordering data

	Pin spacing	Length	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	MW ¹⁾	mm				Unit(s)	Unit(s)		kg
5ST3 6 busbar systems, 10 mm², for MCBs, fixed lengths, cannot be cut, fully insulated									
Single-phase									
For 2 MCBs 1P	1	33	A	5ST3 600		1	10	027	0.005
For 6 MCBs 1P		105	A	5ST3 601		1	10	027	0.018
For 12 MCBs 1P		210	A	5ST3 602		1	10	027	0.036
Single-phase, for MCBs with AS or FC									
For 2 MCBs 1P	1.5	40	A	5ST3 603		1	10	027	0.008
For 6 MCBs 1P		156.5	A	5ST3 604		1	10	027	0.024
For 9 MCBs 1P		237	A	5ST3 605		1	10	027	0.036
Two-phase									
For 2 MCBs 2P	1	75.5	A	5ST3 606		1	10	027	0.016
For 3 MCBs 2P		105	A	5ST3 607		1	10	027	0.024
For 6 MCBs 2P		210	A	5ST3 608		1	10	027	0.048
Three-phase									
For 2 MCBs 3P	1	102	A	5ST3 613		1	10	027	0.039
For 3 MCBs 3P		157.5	A	5ST3 614		1	10	027	0.060
For 4 MCBs 3P		210	▶	5ST3 615		1	10	027	0.076
Three-phase, for MCBs with AS or FC									
For 2 MCBs 3P	1+1+1.5	115	A	5ST3 616		1	10	027	0.040
For 4 MCBs 3P		237	A	5ST3 617		1	10	027	0.080
For 6 MCBs 1P	1.5	125	A	5ST3 618		1	10	027	0.044
For 9 MCBs 1P		229	A	5ST3 620		1	10	027	0.066
Three-phase									
For 1 RCCB 4P N right And 8 MCBs 1P	1	210	A	5ST3 624		1	10	027	0.075
For 1 RCCB 4P N left And 8 MCBs 1P	1	192	A	5ST3 667		1	10	027	0.061
Four-phase									
For 2 MCBs 4P or 3P+N	1	145	A	5ST3 621		1	10	027	0.051
For 3 MCBs 4P or 3P+N		215	A	5ST3 622		1	10	027	0.078
For 6 MCBs 2P or 1P+N		215	A	5ST3 623		1	10	027	0.078
5ST3 6 busbars, 16 mm², for MCBs, fixed lengths, cannot be cut, fully insulated									
Single-phase									
For 2 MCBs 1P	1	33	A	5ST3 630		1	10	027	0.008
For 6 MCBs 1P		105	A	5ST3 631		1	10	027	0.025
For 12 MCBs 1P		210	A	5ST3 632		1	10	027	0.048
Single-phase, for MCBs with AS or FC									
For 2 MCBs 1P	1.5	40	A	5ST3 633		1	10	027	0.013
For 6 MCBs 1P		156.5	A	5ST3 634		1	10	027	0.039
For 9 MCBs 1P		237	A	5ST3 635		1	10	027	0.059
Two-phase									
For 2 MCBs 2P	1	75.5	A	5ST3 636		1	10	027	0.024
For 3 MCBs 2P		105	A	5ST3 637		1	10	027	0.039
For 6 MCBs 2P		210	A	5ST3 638		1	10	027	0.076
Two-phase, for MCBs with AS or FC									
For 2 MCBs 2P	1 + 1.5	75.5	A	5ST3 640		1	10	027	0.026
For 3 MCBs 2P		120.5	A	5ST3 641		1	10	027	0.045
For 5 MCBs 2P		210	A	5ST3 642		1	10	027	0.084

¹⁾ 1 MW (modular width) = 18 mm.



Busbars 5ST3 6, 5ST3 7 standard

	Pin spacing MW ¹⁾	Length mm	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
5ST3 6 busbars, 16 mm², for MCBs, fixed lengths, cannot be cut, fully insulated									
Three-phase									
For 2 MCBs 3P	1	102.5	A	5ST3 643		1	10	027	0.058
For 3 MCBs 3P		157.5	A	5ST3 644		1	10	027	0.083
For 4 MCBs 3P		210	▶	5ST3 645		1	10	027	0.110
Three-phase, for MCB with AS or FC									
For 2 MCBs 3P	1+1+1.5	115	A	5ST3 646		1	10	027	0.060
For 4 MCBs 3P		237	A	5ST3 647		1	10	027	0.120
For 6 MCBs 1P	1.5	156	A	5ST3 648		1	10	027	0.061
For 9 MCBs 1P		245	A	5ST3 650		1	10	027	0.093
5ST3 6 busbars, 16 mm², for MCBs, fixed lengths, cannot be cut, fully insulated									
Three-phase,									
For 1 RCCB 4P N right and 8 MCBs 1P	1	210	A	5ST3 654		1	10	027	0.114
For 1 RCCB 4P N left and 8 MCBs 1P	1	210	A	5ST3 668		1	10	027	0.099
Four-phase									
For 2 MCBs 4P or 3P+N	1		A	5ST3 651		1	10	027	0.080
For 3 MCBs 4P or 3P+N			A	5ST3 652		1	10	027	0.116
For 6 MCBs 2P or 1P+N			A	5ST3 653		1	10	027	0.116
Touch protection for free terminals									
 5 x 1 pin, yellow, RAL 1004			A	5ST3 655		1	10	027	0.003
Range									
10 mm ²									
20 x 5ST3 613 + 10 x 5ST3 614 + 50 x 5ST3 615 + 50 x 5ST3 655			A	5ST3 656		1 set	1 set	027	5.490
16 mm ²									
20 x 5ST3 643 + 10 x 5ST3 644 + 50 x 5ST3 645 + 50 x 5ST3 655			A	5ST3 657		1 set	1 set	027	7.640
5ST3 7 busbar systems, 10 mm² 12 MW, for MCBs, can be cut, with end caps									
Single-phase, angled									
For 12 MCBs 1P	1	214	A	5ST3 730		1	1	027	0.040
For 9 MCB 1P with AS or FC	1.5		A	5ST3 732		1	1	027	0.040
Two-phase									
For 6 MCBs 2P	1		A	5ST3 734		1	1	027	0.060
For 4 MCBs 2P with AS or FC	1+1.5		A	5ST3 736		1	1	027	0.060
Three-phase									
For 4 MCBs 3P	1		▶	5ST3 738		1	1	027	0.100
for 3 MCBs 3P with AS or FC	1+1+1.5		A	5ST3 741		1	1	027	0.100
For 3 MCBs 1P with AS or FC	1.5		A	5ST3 743		1	1	027	0.100
Four-phase									
For 3 MCBs 4P or 3P+N	1		A	5ST3 745		1	1	027	0.150
5ST3 7 busbar systems, 10 mm² 56 MW, for MCBs, can be cut, without end caps									
Single-phase, angled									
For MCBs 1P	1	1016	A	5ST3 731		1	1	027	0.190
For MCBs 1P with AS or FC	1.5		A	5ST3 733		1	1	027	0.190
Two-phase									
For MCBs 2P	1		A	5ST3 735		1	1	027	0.290
For MCBs 2P with AS or FC	1+1.5		A	5ST3 737		1	1	027	0.290
Three-phase									
For MCBs 3P	1		A	5ST3 740		1	1	027	0.430
For MCBs 3P with AS or FC	1+1+1.5		A	5ST3 742		1	1	027	0.430
For MCBs 1P with AS or FC	1.5		A	5ST3 744		1	1	027	0.430
Four-phase									
For MCBs 4P or 3P+N	1		A	5ST3 746		1	1	027	0.700

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers

Busbars 5ST3 6, 5ST3 7 standard




	Pin spacing	Length	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	MW ¹⁾	mm				Unit(s)	Unit(s)		kg
	5ST3 7 busbar systems, 16 mm² 12 MW, for MCBs, can be cut, with end caps								
	Single-phase, angled								
	For MCBs 1P	1	214	▶ 5ST3 700		1	1	027	0.040
	For MCBs 1P with AS or FC	1.5	A	5ST3 702		1	1	027	0.040
	Two-phase								
	For MCBs 2P	1	A	5ST3 704		1	1	027	0.060
	For MCBs 2P with AS or FC	1+1.5	A	5ST3 706		1	1	027	0.060
	Three-phase								
	For MCBs 3P	1	▶	5ST3 708		1	1	027	0.100
	For MCBs 3P with AS or FC	1+1+1.5	A	5ST3 711		1	1	027	0.100
	For MCBs 1P with AS or FC	1.5	A	5ST3 713		1	1	027	0.100
	Four-phase								
	For MCB 4P or 3P+N	1	A	5ST3 715		1	1	027	0.150
	5ST3 7 busbar systems, 16 mm² 56 MW, for MCBs, can be cut, without end caps								
	Single-phase, angled								
	For MCBs 1P	1	1016	A 5ST3 701		1	1	027	0.190
	For MCBs 1P with AS or FC	1.5	A	5ST3 703		1	1	027	0.190
	Two-phase								
	For MCBs 2P	1	A	5ST3 705		1	1	027	0.290
	For MCBs 2P with AS or FC	1+1.5	A	5ST3 707		1	1	027	0.290
	Three-phase								
	For MCBs 3P	1	▶	5ST3 710		1	1	027	0.430
	For MCBs 3P with AS or FC	1+1+1.5	A	5ST3 712		1	1	027	0.430
	For MCBs 1P with AS or FC	1.5	A	5ST3 714		1	1	027	0.430
	Four-phase								
	For MCBs 4P or 3P+N	1	A	5ST3 716		1	1	027	0.700
	5ST3 7 busbar systems, 10 mm² 56 MW, can be cut, with end caps, with touch protection								
	Four-phase								
	For MCBs 2P and RCBOs 1P+N	1	1008	A 5ST3 770-2		1	10	027	0.400
	5ST3 7 busbar systems, 16 mm² 56 MW, can be cut, with end caps, with touch protection								
	Four-phase								
	For MCBs 2P and RCBOs 1P+N	1	1008	A 5ST3 770-3		1	10	027	0.550
	5ST3 7 busbar systems, 10 mm² 16 MW can be cut, with end caps, with touch protection								
	Four-phase								
	For 6 MCBs 1P+N and RCCBs 4P, N connection, right	1	288	A 5ST3 770-4		1	10	027	0.100
	5ST3 7 busbar systems, 16 mm² 16 MW can be cut, with end caps, with touch protection								
	Four-phase								
	For 6 MCBs 1P+N and RCCBs 4P, N connection, right	1	288	A 5ST3 770-5		1	10	027	0.160
	End caps for 5ST3 7, can be cut								
	For single-phase busbars		▶	5ST3 748		1	10	027	0.001
	For two- and three-phase busbars		▶	5ST3 750		1	10	027	0.001
	For four-phase busbars		▶	5ST3 718		1	10	027	0.001

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.

BETA Protecting Miniature Circuit Breakers

Busbars
5ST3 6, 5ST3 7 standard

	Pin spacing	Length	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	MW ¹⁾	mm				Unit(s)	Unit(s)		kg
	5ST3 7 busbar systems, 10 mm² 12 MW, for MCBs 1+N in 1 MW of the compact range, can be cut, with end caps								
	Single-phase								
	For 12 MCBs 1+N, gray	1	216	A	5ST3 762	1	10	027	0.029
	For 12 MCBs 1+N, blue			A	5ST3 763	1	10	027	0.029
	5ST3 7 busbar systems, 10 mm² 56 MW, for MCBs 1+N in 1 MW of the compact range, can be cut, without end caps								
	Single-phase								
	For MCBs 1+N, gray	1	1016	A	5ST3 764	1	10	027	0.134
	For MCBs 1+N, blue			A	5ST3 765	1	10	027	0.134
	End caps for 5ST3 76								
	1 set comprises a right and a left cap								
	Gray			A	5ST3 766	1 set	10 sets	027	0.001
	Blue			A	5ST3 767	1 set	10 sets	027	0.001
	Terminals for 5ST3 76								
	Terminal version S								
	For conductors up to 25 mm ²			A	5ST3 768	1	25	027	0.011

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers


Busbars
5ST3 6, 5ST3 7 standard

Dimensional drawings

5ST3 6

Pin spacings in MW (modular width 1 MW = 18 mm)

Dimensions of side view in mm (approx.)




5ST3 600
5ST3 630


5ST3 601
5ST3 602
5ST3 631
5ST3 632

5ST3 603
5ST3 633

5ST3 604
5ST3 605
5ST3 634
5ST3 635




5ST3 606
5ST3 607
5ST3 608



5ST3 636
5ST3 637
5ST3 638


5ST3 640
5ST3 641
5ST3 642



5ST3 613
5ST3 614
5ST3 615
5ST3 667

5ST3 616
5ST3 617


5ST3 618
5ST3 620



5ST3 643
5ST3 644
5ST3 645
5ST3 668


5ST3 646
5ST3 647

5ST3 648
5ST3 650



5ST3 621
5ST3 622


5ST3 623




5ST3 651
5ST3 652

5ST3 653

Busbars
5ST3 6, 5ST3 7 standard




5ST3 654




5ST3 654


Dimensions of side view in mm (approx.)



5ST3 704	5ST3 706
5ST3 705	5ST3 707
5ST3 734	5ST3 736
5ST3 735	5ST3 737
Two-phase	



5ST3 715
5ST3 716
5ST3 745
5ST3 746



5ST3 763
5ST3 765

BETA Protecting Miniature Circuit Breakers

Busbars
acc. to UL 508, 5ST3 7.. - .HG




Overview

Products according to UL standards are used in North America, but also in several other countries. Acceptance and delivery are possible only if the relevant UL standards are satisfied, particularly when exporting machines or electrical switchgear and equipment to the USA.


The 5ST3 7 busbar system according to UL 508 and CSA is suitable for both universal use worldwide with all 5SY and 5SP miniature circuit breakers for Supplementary Protection certified according to UL 1077 and for 3NW and 3NC fuse holders certified according to UL 512.

The busbars are available in single, two and three-phase version with different pin spacings and with two cross-sections 18 mm² and 25 mm². Infeed can be directly into the terminals of the miniature circuit breaker or through connection terminals. The connection terminals are available in two versions – for direct infeed at the busbar or for infeed directly at the miniature circuit breaker/fuse holder. Pins that are not required can be covered with touch protection covers.


Benefits



- Bus-mounting with infeed through a connection terminal directly on the miniature circuit breaker up to a conductor cross-section of 35 mm²



- Infeed directly on the miniature circuit breaker up to a cross-section of 35 mm² and connection terminal for connection directly on the busbar up to a conductor cross-section of 50 mm²
- Suitable for universal use according to both IEC and UL standards
- Can be used for 5SY, 5SP miniature circuit breakers and for Class CC, cylindrical and SITOP fuse holders
- UL-tested combination – device and busbar
- Different cross-sections 18 mm² and 25 mm².



- Bus-mounting with infeed at the fuse holder for conductor cross-sections up to 35 mm²



Busbars
acc. to UL 508, 5ST3 7.. - .HG


Technical specifications

		5ST3 7...0HG	5ST3 7...2HG	5ST3 770-0HG	5ST3 770-1HG
Standards		UL 508, CSA C22.2 No. 14-M 95			
Approvals		UL 508 File No. E328403 CSA			
Operational voltage					
• Acc. to IEC	V AC	690			
• Acc. to UL 508	V AC	600			
Rated conditional short-circuit current	kA	10			
• Dielectric strength	kV/mm	25			
• Surge strength	kV	> 9.5			
Rated current	A	--	--	115	
Maximum busbar current I_S/phase					
• Infeed at the start of the busbar	A	80	100	--	--
• Infeed at the center of the busbar	A	160	200	--	--
Insulation coordination					
• Overvoltage category		III			
• Degree of pollution		2			
Busbar cross-section	mm ² Cu	18	25	--	--
Infeed		Any			
Conductor cross-sections	AWG mm ²	-- --	-- --	10 ... 1/0 6 ... 35	14 ... 1 6 ... 50
Terminals					
• Terminal tightening torque	Nm lbs/in.	-- --	-- --	5 50	3.5 35

Infeed at the start or end of the busbar



Infeed along the busbar or midpoint infeed



The sum of the output current per branch (1, 2, 3 ... n) must not be greater than the max. busbar current I_S /phase.

BETA Protecting Miniature Circuit Breakers

Busbars
acc. to UL 508, 5ST3 7.. - .HG



Selection and ordering data

	Pin spacing MW ¹⁾	Length mm	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
5ST3 7...-HG busbars acc. to UL 508, 18 mm², can be cut, without end caps									
	Single-phase								
	• For MCB 1P (5SY) or fuse holder 10 x 38 class CC (3NC1 091, 3NW7 513-0HG)	1	1000	A	5ST3 701-0HG	1	10	012	0.330
	Two-phase								
	• For MCB 2P (5SY) or fuse holder 10 x 38 class CC (3NC1 092, 3NW7 523-0HG)	1	1000	A	5ST3 705-0HG	1	10	012	0.508
	Three-phase								
	• For MCB 3P (5SY) or fuse holder 10 x 38 class CC (3NC1 093, 3NW7 533-0HG)	1	1000	A	5ST3 710-0HG	1	10	012	0.800
	• For MCB 3P (5SY) with AS or FC 1+1+1.5 1000 A								
	• For MCB 1P (5SY, 5SP) with AS or FC or fuse holder 14 x 51 (3NC1 491, 3NW7 111)	1.5	1000	A	5ST3 712-0HG 5ST3 714-0HG	1 1	10 10	012 012	0.800 0.820
5ST3 7...-HG busbars acc. to UL 508, 25 mm², can be cut, without end caps									
	Single-phase								
	• For MCB 1P (5SP) or fuse holder 14 x 51 (3NC1 491, 3NW7 111)	1.5	1000	A	5ST3 701-2HG	1	10	012	0.450
	Two-phase								
	• For MCB 2P (5SP) or fuse holder 14 x 51 (3NC1 492, 3NW7 121)	1.5	1000	A	5ST3 705-2HG	1	10	012	0.690
	Three-phase								
	• For MCB 3P (5SP) or fuse holder 14 x 51 (3NC1 493, 3NW7 131)	1.5	1000	A	5ST3 710-2HG	1	10	012	1.090
End caps for 5ST3 7...-HG									
	• For single-phase busbars								
	• For two and three-phase busbars			A	5ST3 748-0HG 5ST3 750-0HG	1 1	10 10	012 012	0.001 0.001
Connection terminals acc. to UL 508									
	Infeed to device								
	• 35 mm ²			A	5ST3 770-0HG	1	10	012	0.035
	Infeed to busbar								
	• 50 mm ²			A	5ST3 770-1HG	1	10	012	0.016
Touch protection covers for busbars acc. to UL 508									
	• 5 x 1 pin			A	5ST3 655-0HG	1	10	012	0.003

¹⁾ 1 MW (modular width) = 18 mm.

* You can order this quantity or a multiple thereof.




Busbars
acc. to UL 508, 5ST3 7.. - .HG

Dimensional drawings


5ST3 7

Pin spacings in MW (modular width 1 MW = 18 mm)


Dimensions of side view in mm (approx.)



5ST3 701-0HG 5ST3 703-0HG




5ST3 705-0HG 5ST3 707-0HG




5ST3 710-0HG

5ST3 712-0HG


5ST3 714-0HG




5ST3 701-2HG




5ST3 705-2HG




5ST3 710-2HG




5ST3 748-0HG



5ST3 750-0HG



5ST3 770-0HG




5ST3 770-1HG

5ST3 6 touch protection cover

pin spacings in MW (modular width; 1 MW = 18 mm)

Dimensions of side view in mm (approx.)



5ST3 655-0HG

BETA Protecting Miniature Circuit Breakers

Busbars
5ST3 5 universal



Overview


Busbars serve the safe and fast connection of modular installation devices, such as miniature circuit breakers, residual current operated circuit breakers and switching and control devices.

The universal busbar system allows different devices of various designs to be connected together quickly and conveniently


using just a few components for a range of different applications. This makes it possible, for example, to combine residual current operated circuit breakers (3 + N) with miniature circuit breakers (1 + N) into one modular width for an advantageous distribution of the phases.

Benefits


- The universal busbar system can be used for all modular installation devices, such as 5SY, 5SM, and 5SU
- The reduced component quantity allows fast configuration of reliable and safe busbar mountings.
- Individual connection of the devices via standardized terminal pins and simple and convenient connection using plug-in technology.
- Free selection of phase sequence.




- Two-phase insulating elements with plug-on mount for implementing double or multiphase busbar mountings.



- Single-phase insulating elements featuring a plug-on mount for implementing single or multiphase busbar mountings.



- Universal multiphase busbar mounting (3 phases + N) with 2x two-phase insulating elements with a plug-on mount for combining the widest variety of different modular installation devices with additional components.



- Single-phase busbar mounting featuring a single-phase insulating element with a plug-on mount for combining RCCB and MCB.



Technical specifications

		5ST3 5
Standards		EN 60947-1 (VDE 0660-100) IEC 60947-1
Plug-on mount material		CuSn, silver-plated
Terminal pin material		E-Cu 58 F25 tinned
Insulating element material		PC/ABS heat-resistant over 90 °C flame-retardant and self-extinguishing, dioxin and halogen-free
Rated operational voltage U_c	V AC	690
Rated current I_n • Cross-section 16 mm ²	A	63
Rated impulse withstand voltage U_{imp}	kV	4
Rated conditional short-circuit current I_{cc}	kA	25
Resistance to climate • Humid heat	Acc. to IEC 60068-2-30	28 cycles
Insulation coordination • Overvoltage category • Degree of pollution		III 2

Selection and ordering data

	Length mm	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
	Universal busbar systems, 16 mm², 1000 mm Can be cut to length, without end caps							
	Single-phase	1000	A	5ST3 500-0	1	12	027	0.433
	Two-phase	1000	A	5ST3 501-0	1	12	027	0.823
	Insulating element with plug-on mount							
	Terminal pins, 1 MW pitch for residual current operated circuit breakers or miniature circuit breakers							
	Terminal pin 6/12 For L/N	12	A	5ST3 510-0	1	50	027	0.007
	Terminal pin 6/21 For L/N	21	A	5ST3 511-0	1	50	027	0.008
	Terminal pins, 0.5 MW pitch for miniature circuit breaker 1 + N in one modular width							
	Terminal pin 4/23 For L1	23	A	5ST3 512-0	1	50	027	0.006
	Terminal pin 4/3 For L2	3	A	5ST3 513-0	1	50	027	0.005
	Terminal pin 4/9 For L3	9	A	5ST3 514-0	1	50	027	0.005
	Terminal pin 4/21 For N	21	A	5ST3 515-0	1	50	027	0.005


BETA Protecting Miniature Circuit Breakers

Busbars
5ST3 5 universal





	Length mm	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
Accessories								
	1000	A	5ST3 507-0		1	12	027	0.003
		A	5ST3 508-0		1	12	027	0.020
1 unit for 3 phases + N or separable into 1x two-phase or 2x single-phase insulating element								



Dimensional drawings





5ST3 500-0
Single-phase




5ST3 501-0
Two-phase



5ST3 507-0




5ST3 508-0




BETA Protecting Miniature Circuit Breakers


Busbars
5ST3 5 universal




5ST3 510-0




5ST3 511-0




5ST3 512-0



5ST3 513-0



5ST3 514-0



5ST3 515-0

More information

Installation and mounting

First mount the 5ST3 51.-0 terminal pins, which are available in a range of heights and widths, on the various modular installation devices.

Then cut the insulating elements, complete with 5ST3 50.-0 plug-on mount, to the appropriate length, making sure that the copper bar is 6 mm shorter than the insulating element.


When mounting the insulating element (with plug-on mount) on the terminals pins, if using a three or four-phase version please ensure that the rear plug-on mount is fitted first, and that the 5ST3 507-0 touch protection profiles, which are required for additional touch protection, are facing inwards.

Furthermore, the plug-on mount must be pushed on to the devices until it touches the limit stop. If additional lug cover is required, the touch protection scheduled also needs to be cut to the appropriate length and included in the channel.

The 5ST3 508-0 end caps are then mounted. These are fitted with integrated premachined breaking points and, depending on the type of busbar – single-phase or two-phase – can be adapted to suit the corresponding insulating element.

BETA Protecting Miniature Circuit Breakers

Busbars
5ST3 5 universal



Overview

Switching capacity

Particular demands are made on miniature circuit breakers with regard to switching capacity.

The values are standardized and are determined according to the test conditions of IEC/EN 60898 or DIN VDE 0641-11.

The values of the rated switching capacity are 6000, 10 000 and 15 000.

For other test conditions, it is also possible to specify values that are higher than those of IEC/EN 60898 or DIN VDE 0641-11.

One such standard is IEC/EN 60947-2 or DIN VDE 0660-101 for circuit breakers.

Rated switching capacity

5SY4, 5SY6, 5SY7, 5SY8, 5SY6 0 and 5SP4 miniature circuit breakers

	I_n [A]	IEC/EN 60898-1 1-pole 230 V AC	2-, 3- and 4-pole 400 V AC	IEC/EN 60947-2 1-pole 230 V AC	2-, 3- and 4-pole 400 V AC
		I_{cn} [kA]	I_{cn} [kA]	I_{cu} [kA]	I_{cu} [kA]
5SY6	0.3 ... 6	6		30	
	8 ... 32	6		15	
	40 ... 63	6		10	
5SY4	0.3 ... 6	10		35	
	8 ... 32	10		20	
	40 ... 63	10		15	
	80	10		10	
5SY7	0.3 ... 2	15		50	
	3 ... 6	15		40	
	8 ... 10	15		30	
	13 ... 32	15		25	
	40 ... 63	15		20 ¹⁾	
5SY8	0.3 ... 2	--		70	
	3 ... 6	--		50	
	8 ... 10	--		40	
	13 ... 32	--		30	
	40 ... 63	--		25 ²⁾	
5SY6 0..	2 ... 40	6	--	6	--
5SP4	80 ... 125	10		20 ³⁾	

¹⁾ D50 and D63: $I_{cu} = 15$ kA.

²⁾ D50 and D63: $I_{cu} = 20$ kA.

³⁾ D80 and D100: $I_{cu} = 15$ kA.

5SP5 and 5SY5 miniature circuit breakers


Miniature circuit breakers, universal current	I_n [A]	IEC/EN 60898-2		IEC/EN 60898-2	
		1-pole 230/400 V AC	2-pole 400 V AC	1-pole 220 V DC	2-pole 440 V DC
	I_{cn} [kA]	I_{cn} [kA]	I_{cn} [kA]	I_{cn} [kA]	I_{cn} [kA]
5SY5	0.3 ... 63	10		15	
5SP5	80 ... 125	3		10	

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning


Characteristic curves

Tripping characteristics acc. to IEC/EN 60898, DIN VDE 0641-11




Tripping characteristic A

For limited semiconductor protection, protection of measuring circuits with transformers. Protection of circuits with tripping in 0.4 s acc. to DIN VDE 0100-410 for long cable lengths.




Tripping characteristic B

MCBs with this tripping characteristic are designed for universal use in socket outlet and lighting circuits. Proof of personal safety acc. to DIN VDE 0100-410 is not required.



Tripping characteristic C

In lamp and motor circuits with higher starting currents, MCBs with tripping characteristic C are generally used.



Tripping characteristic D

For electrical circuits with strong pulse-generating equipment, such as transformers or solenoid valves.


Tripping characteristics

Tripping characteristics at an ambient temperature of 30 °C

Tripping characteristic	Standards	Thermal trips				Electromagnetic trips		
		Limiting test current I_1	Minimum test current I_2	Tripping time		Hold I_4	Latest tripping instant I_5	Tripping time t
				$I_n \leq 63 \text{ A}$	$I_n > 63 \text{ A}$			
A	--	$1.13 \times I_n$	$1.45 \times I_n$	$> 1 \text{ h}$	$> 2 \text{ h}$	$2 \times I_n$	$3 \times I_n$	$\geq 0.1 \text{ s}$
	--			$< 1 \text{ h}$	$< 2 \text{ h}$			$< 0.1 \text{ s}$
B	IEC/EN 60898, DIN VDE 0641-11	$1.13 \times I_n$	$1.45 \times I_n$	$> 1 \text{ h}$	$> 2 \text{ h}$	$3 \times I_n$	$5 \times I_n$	$\geq 0.1 \text{ s}$
				$< 1 \text{ h}$	$< 2 \text{ h}$			$< 0.1 \text{ s}$
C	IEC/EN 60898, DIN VDE 0641-11	$1.13 \times I_n$	$1.45 \times I_n$	$> 1 \text{ h}$	$> 2 \text{ h}$	$5 \times I_n$	$10 \times I_n$	$\geq 0.1 \text{ s}$
				$< 1 \text{ h}$	$< 2 \text{ h}$			$< 0.1 \text{ s}$
D	IEC/EN 60898, DIN VDE 0641-11	$1.13 \times I_n$	$1.45 \times I_n$	$> 1 \text{ h}$	$> 2 \text{ h}$	$10 \times I_n$	$20 \times I_n$	$\geq 0.1 \text{ s}$
				$< 1 \text{ h}$	$< 2 \text{ h}$			$< 0.1 \text{ s}$
							(IEC 60898: $50 \times I_n$)	

Correction factors for rated current of 5SY at different ambient temperatures

Dependence of permissible continuous load current on ambient temperature for 5SY miniature circuit breakers



For the curve of the respective correction factor, please refer to the following table.

Curve for correction factor for 5SY miniature circuit breakers (for curves, please refer to the top left-hand diagram)

Rated current (A)	0.3	0.5	1	1.6	2	3	4	6	8	10	13	16	20	25	32	40	50	63	80
Characteristic	Applicable curve for correction factor for 5SY miniature circuit breakers																		
A	3P/4P	3	2	2	2	3	3	3	2	3	2	2	3	2	2	3	2	3	--
	1P/2P	2	2	1	2	2	2	2	2	2	1	1	2	1	1	1	1	2	--
B	3P/4P	--	--	--	--	--	--	3	--	3	2	2	3	3	2	3	2	3	2
	1P/2P	--	--	--	--	--	--	2	--	2	1	2	2	1	1	1	1	1	1
C	3P/4P	3	3	2	2	3	3	3	3	3	2	3	3	2	2	3	2	3	2
	1P/2P	2	2	2	1	2	2	3	3	3	2	2	2	2	1	1	1	2	1
D	3P/4P	3	3	2	2	3	3	3	3	3	2	3	3	2	2	3	2	3	--
	1P/2P	2	2	2	1	2	2	2	3	3	2	2	2	2	2	2	1	2	--

Curve for correction factor for 5SY6 0.. miniature circuit breakers (for curves, please refer to the top right-hand diagram)

Rated current (A)	2	4	6	8	10	13	16	20	25	32	40
Characteristic	Applicable curve for correction factor for 5SY6 0.. miniature circuit breakers										
B	--	--	1	--	2	2	2	2	1	2	2
C	--	--	1	3	2	2	3	3	1	2	2

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

Correction factors for rated current if bundling

If more than one electrical circuit is loaded in a series of miniature circuit breakers, the resulting increase in ambient temperature affects the characteristic curve. In this case, you need to include an additional correction factor, which is specific to the rated current of the MCB(s).

Number of MCBs	1	2 ... 3	4 ... 6	> 7
Correction factor K	1.00	0.90	0.88	0.85

Correction factors for rated current at different frequencies

The tripping characteristic applies to a frequency of 50 to 60 Hz. In the case of other frequencies, the following correction factors must be taken into account.

In the overrange, the limits of the characteristic curves correspond to the correction factors of the thermal tripping operation. In the case of a short circuit, the limits of the characteristic curves correspond to the correction factors of the magnetic tripping operation.


Thermal tripping operation

Rated current I_n (A)		Correction factor for					
		0 Hz	16 2/3 Hz	50 Hz	125 Hz	400 Hz	1000 Hz
5SY5	0.3 ... 10	1	1	1	1	0.99	0.97
	1 ... 40	1	1	1	0.98	0.97	0.93
	50 ... 63	1	1	1	0.98	0.94	0.86
5SP5	80 ... 125	1	1	1	0.97	0.92	0.85

Magnetic tripping operation

Rated current I_n (A)		Correction factor for					
		0 Hz	16 2/3 Hz	50 Hz	125 Hz	400 Hz	1000 Hz
5SY5	0.3 ... 63	1.4	1	1	1.2	1.4	1.7
5SP5	80 ... 125	1.5	1	1	1.05	1.3	1.8

Dependence of reduction factor on ambient temperature when using 5SP miniature circuit breakers




Legend for curves for 5SP miniature circuit breakers diagram:


- Curve 1: 5SP, multipole, 80 A/100 A, characteristic B/C/D, 5SP, multipole, 125 A, characteristic B/C
- Curve 2: 5SP, 1-pole, 80 A, characteristic B/C/D
- Curve 3: 5SP, 1-pole, 100 A, characteristic B/C/D, 5SP, 1-pole, 125 A, characteristic B/C

Let-through I^2t values 5SY6 (AC)


Characteristic B



Characteristic C



Characteristic D




BETA Protecting Miniature Circuit Breakers


Configuration and dimensioning

Let-through I^2t values 5SY4 (AC)


Characteristic A




Characteristic C



Characteristic B




Characteristic D




Let-through I^2t values 5SP4 (AC)


Characteristic B



Characteristic D




Characteristic C



Let-through I^2t values 5SP5 (DC)

Characteristic C




BETA Protecting Miniature Circuit Breakers


Configuration and dimensioning

Let-through I^2t values 5SY5 (DC)

Characteristic B




Characteristic C




Let-through I^2t values 5SY8 (AC)

Characteristic C




Characteristic D




Let-through I^2t values 5SY7 (AC)


Characteristic B



Characteristic C



Characteristic D




BETA Protecting Miniature Circuit Breakers


Configuration and dimensioning

Let-through I^2t values 5SJ6 . . . - .KS (AC)

Characteristic B




Characteristic C




Let-through I^2t values 5SY6 0 (AC)

Characteristic B



Characteristic C



Selective miniature circuit breakers/fuses

Distribution systems are usually set up as radial networks. An overcurrent protection device is required for each reduction of the conductor cross-section. This produces a series connection staggered according to rated currents, which should be "selective" if possible.

Selectivity means that, in the event of a fault, only the protective device that is directly next to the fault in the current path is tripped. This means that current paths in parallel can maintain a power flow.

In the case of miniature circuit breakers with upstream fuses, the selectivity limit depends largely on the current limitation and tripping characteristics of the miniature circuit breaker and the melting I^2t value of the fuse.

This produces different selectivity limits for miniature circuit breakers with different characteristics and rated switching capacity.

The following tables provide information on the short-circuit currents up to which selectivity exists between miniature circuit breakers and upstream fuse according to DIN VDE 0636-21. The values specified in kA are limit values that were determined under unfavorable test conditions. Under normal practical conditions, you can often expect considerably better values, depending on the upstream fuses.

Limit values of selective line miniature circuit breakers/fuses in kA

Downstream miniature circuit breakers		Upstream fuses							
	I_n [A]	16 A	20 A	25 A	35 A	50 A	63 A	80 A	100 A
5SY6 ...-6									
Characteristic B	6	0.3	0.4	0.7	1.2	3.0	3.2	•	•
	10	--	0.4	0.6	1.0	2.2	3.0	5.0	•
	13	--	--	0.5	1.0	2.2	3.0	5.0	•
	16	--	--	--	1.0	2.0	2.4	4.0	•
	20	--	--	--	--	2.0	2.4	4.0	•
	25	--	--	--	--	--	2.0	3.5	•
	32	--	--	--	--	--	1.7	2.9	•
	40	--	--	--	--	--	--	2.0	4.0
	50	--	--	--	--	--	--	--	4.0
	63	--	--	--	--	--	--	--	--
5SY6 ...-7									
Characteristic C	≤ 2	0.3	0.5	1.2	1.7	•	•	•	•
	3	0.3	0.4	0.8	1.4	4.0	5.0	•	•
	4	0.3	0.4	0.6	1.1	3.0	4.0	•	•
	6	--	0.4	0.6	1.0	2.4	3.2	•	•
	8	--	--	0.5	0.9	1.4	2.6	3.1	•
	10	--	--	0.5	0.9	1.4	2.1	3.1	•
	13	--	--	--	0.8	1.3	2.0	3.0	•
	16	--	--	--	0.8	1.3	2.0	3.0	•
	20	--	--	--	--	1.3	2.0	2.7	•
	25	--	--	--	--	--	2.0	2.4	5.0
	32	--	--	--	--	--	--	2.2	4.0
	40	--	--	--	--	--	--	--	3.5
	50	--	--	--	--	--	--	--	3.0
	63	--	--	--	--	--	--	--	3.0

• $\hat{=}$ rated switching capacity 5SY6 according to EN 60898 6000.

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

Selective miniature circuit breakers/fuses

Distribution systems are usually set up as radial networks. An overcurrent protection device is required for each reduction of the conductor cross-section. This produces a series connection staggered according to rated currents, which should be "selective" if possible.

Selectivity means that, in the event of a fault, only the protective device that is directly next to the fault in the current path is tripped. This means that current paths in parallel can maintain a power flow.

In the case of miniature circuit breakers with upstream fuses, the selectivity limit depends largely on the current limitation and tripping characteristics of the miniature circuit breaker and the melting I^2t value of the fuse.

This produces different selectivity limits for miniature circuit breakers with different characteristics and rated switching capacity.

The following tables provide information on the short-circuit currents up to which selectivity exists between miniature circuit breakers and upstream fuse according to DIN VDE 0636-21. The values specified in kA are limit values that were determined under unfavorable test conditions. Under normal practical conditions, you can often expect considerably better values, depending on the upstream fuses.

In the event of a short-circuit, there is selectivity between the 5SY4, 5SY7, 5SP4 miniature circuit breakers and melting fuses according to DIN VDE 0636-21 up to the specified values in kA.

Limit values of selective line miniature circuit breakers/fuses in kA

Downstream miniature circuit breakers		Upstream fuses								
	I_n [A]	16 A	20 A	25 A	35 A	50 A	63 A	80 A	100 A	125 A
5SY4 ...-5, -6, 5SY7 ...-6										
Characteristic A, B	6	0.3	0.4	0.8	1.4	3.2	4.5	9.0	•	•
	10	--	0.4	0.7	1.2	2.5	3.5	5.0	•	•
	13	--	--	0.7	1.2	2.5	3.5	5.0	•	•
	16	--	--	--	1.0	2.0	2.8	4.2	9.0	•
	20	--	--	--	1.0	2.0	2.6	4.2	9.0	•
	25	--	--	--	--	1.7	2.2	3.7	7.0	•
	32	--	--	--	--	1.7	2.2	3.7	7.0	•
	40	--	--	--	--	--	1.6	2.2	4.0	6.0
	50	--	--	--	--	--	--	2.2	4.0	6.0
	63	--	--	--	--	--	--	--	3.0	5.0
5SY4 ...-7, 5SY7 ...-7										
Characteristic C	≤ 2	0.3	0.5	1.5	2.0	9.0	•	•	•	•
	3	0.3	0.4	1.1	1.6	5.0	6.0	•	•	•
	4	0.3	0.4	0.9	1.4	3.5	5.0	9.0	•	•
	6	--	0.4	0.8	1.4	2.7	4.5	6.0	•	•
	8	--	--	0.6	1.2	2.2	3.5	5.0	7.0	•
	10	--	--	0.5	1.2	2.0	3.0	4.2	7.0	•
	13	--	--	--	1.0	1.6	2.4	3.4	6.0	•
	16	--	--	--	1.0	1.5	2.2	3.0	6.0	•
	20	--	--	--	--	1.3	2.2	3.0	6.0	•
	25	--	--	--	--	--	2.2	2.9	5.0	9.0
	32	--	--	--	--	--	--	2.4	4.0	7.0
	40	--	--	--	--	--	--	2.0	3.5	4.0
	50	--	--	--	--	--	--	--	3.0	4.0
	63	--	--	--	--	--	--	--	3.0	3.5
5SY4 ...-8, 5SY7 ...-8										
Characteristic D	≤ 2	0.3	0.4	1.0	1.8	5.0	7.0	•	•	•
	3	0.3	0.4	0.9	1.5	4.0	5.0	8.0	•	•
	4	--	0.4	0.8	1.2	3.0	3.8	5.5	•	•
	6	--	--	0.7	1.1	2.5	3.1	4.4	8.1	•
	8	--	--	--	0.9	2.1	2.5	3.5	6.2	9.3
	10	--	--	--	--	2.1	2.5	3.5	6.2	9.3
	13	--	--	--	--	--	2.5	3.5	6.2	9.3
	16	--	--	--	--	--	2.2	3.1	5.1	7.5
	20	--	--	--	--	--	--	2.7	4.3	6.3
	25	--	--	--	--	--	--	--	4.0	5.7
	32	--	--	--	--	--	--	--	4.0	5.5
	40	--	--	--	--	--	--	--	3.5	4.8
	50	--	--	--	--	--	--	--	--	4.0
	63	--	--	--	--	--	--	--	--	--

• $\hat{=}$ rated switching capacity 5SY4 according to EN 60898 **10 000**

Limit values of selective line miniature circuit breakers/fuses in kA

Downstream miniature circuit breakers	I_n [A]	Upstream fuses					
		100 A	125 A	160 A	200 A	224 A	250 A
5SP4 ...-6							
Characteristic B	80	2.8	3.8	5.7	8.1	•	•
	100	--	3.5	5.2	7.0	•	•
	125	--	--	5.2	7.0	•	•
5SP4 ...-7							
Characteristic C	80	2.5	3.5	5.1	7.5	9.2	•
	100	--	3.3	4.5	6.5	8.0	•
	125	--	--	4.5	6.5	8.0	•
5SP4 ...-8							
Characteristic D	80	2.3	3.3	4.6	6.9	8.1	•
	100	--	2.8	4.3	6.2	7.5	9.2

- $\geq$ rated switching capacity 5SP4 according to EN 60898 10 000.

Values for 5SY8 on request.

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

Selective miniature circuit breakers/circuit breakers

Distribution systems can also be set up without fuses. In such cases, a circuit breaker acts as an upstream protective device. In this case, the selectivity limit depends on the level of peak current I let through by the miniature circuit breaker and the tripping current of the circuit breaker.

The following tables show the short-circuit current in kA up to which selectivity is guaranteed between miniature circuit breakers and upstream circuit breakers according to IEC/EN 60947-2, at 230/400 V AC, 50 Hz.

Limit values of selective miniature circuit breakers/circuit breakers in kA

Downstream miniature circuit breakers				Upstream circuit breakers								
				3RV1. 1		3RV1. 2						
				10	12	8	10	12.5	16	20	22	25
				120	144	96	120	150	192	240	264	300
	I_n [A]	$I > [A]$	I_{cn} [kA]	50	50	100	100	100	50	50	50	50
Selectivity limits [kA] ¹⁾												
5SY4 ...-5												
Characteristic A	2	6	10	0.2	0.2	--	--	0.2	0.2	0.6	1.2	1.5
	10	30	10	--	--	--	--	--	--	0.3	0.5	0.5
	16	48	10	--	--	--	--	--	--	0.3	0.4	0.5
	32	96	10	--	--	--	--	--	--	--	--	--
	40	120	10	--	--	--	--	--	--	--	--	--
5SY4 ...-6, 5SY6 ...-6, 5SY7 ...-6												
Characteristic B	6	30	6/10/15	0.2	0.2	--	--	0.2	0.2	0.3	0.5	0.5
	10	50	6/10/15	--	0.2	--	--	0.2	0.2	0.3	0.4	0.5
	13	65	6/10/15	--	--	--	--	--	0.2	0.2	0.4	0.4
	16	80	6/10/15	--	--	--	--	--	--	0.2	0.4	0.4
	20	100	6/10/15	--	--	--	--	--	--	--	--	0.4
	25	125	6/10/15	--	--	--	--	--	--	--	--	--
	32	160	6/10/15	--	--	--	--	--	--	--	--	--
	40	200	6/10/15	--	--	--	--	--	--	--	--	--
	50	250	6/10/15	--	--	--	--	--	--	--	--	--
	63	315	6/10/15	--	--	--	--	--	--	--	--	--
	80	400	6/10/15	--	--	--	--	--	--	--	--	--
	5SY4 ...-7, 5SY6 ...-7, 5SY7 ...-7											
Characteristic C	0.5	5	6/10/15	0.2	0.2	0.1	0.1	0.2	0.2	0.5	0.6	0.6
	1	10	6/10/15	0.2	0.2	0.1	0.1	0.2	0.2	0.5	0.6	0.6
	1.6	16	6/10/15	0.2	0.2	0.1	0.1	0.2	0.2	0.5	0.6	0.6
	2	20	6/10/15	0.2	0.2	0.1	0.1	0.2	0.2	0.5	0.6	0.6
	3	30	6/10/15	--	0.2	--	--	0.2	0.2	0.3	0.4	0.5
	4	40	6/10/15	--	0.2	--	--	0.2	0.2	0.3	0.4	0.5
	6	60	6/10/15	--	0.2	--	--	0.2	0.2	0.3	0.4	0.5
	8	80	6/10/15	--	0.2	--	--	0.2	0.2	0.2	0.4	0.4
	10	100	6/10/15	--	0.2	--	--	0.2	0.2	0.2	0.4	0.4
	13	130	6/10/15	--	--	--	--	--	0.2	0.2	0.4	0.4
	16	160	6/10/15	--	--	--	--	--	--	0.2	0.4	0.4
	20	200	6/10/15	--	--	--	--	--	--	--	--	0.4
	25	250	6/10/15	--	--	--	--	--	--	--	--	--
	32	320	6/10/15	--	--	--	--	--	--	--	--	--
	40	400	6/10/15	--	--	--	--	--	--	--	--	--
	50	500	6/10/15	--	--	--	--	--	--	--	--	--
	63	630	6/10/15	--	--	--	--	--	--	--	--	--
	80	800	6/10/15	--	--	--	--	--	--	--	--	--
5SY4 ...-8, 5SY6 ...-8, 5SY7 ...-8												
Characteristic D	2	40	6/10/15	--	--	--	--	0.2	0.2	0.4	0.6	0.6
	6	120	6/10/15	--	--	--	--	--	--	0.3	0.4	0.4
	10	200	6/10/15	--	--	--	--	--	--	0.2	0.4	0.4
	16	320	6/10/15	--	--	--	--	--	--	--	--	--
	32	640	6/10/15	--	--	--	--	--	--	--	--	--
	40	800	6/10/15	--	--	--	--	--	--	--	--	--
	50	1000	6/10/15	--	--	--	--	--	--	--	--	--
	63	1260	6/10/15	--	--	--	--	--	--	--	--	--

Values for 5SY8 on request.

¹⁾ In 240/415 V, 50 Hz systems, the selectivity limits are reduced by 10 %.
 $I > \hat{I}$ tripping current.

Configuration and dimensioning

In the event of a short circuit, there is selectivity between miniature circuit breakers and circuit breakers according to IEC/EN 60947-2 up to the specified values in kA.

Limit values of selective line miniature circuit breakers/fuses in kA

Downstream miniature circuit breakers				Upstream circuit breakers						
	I_n [A]	$I > [A]$	I_{cn} [kA]	3RV1.3						
				16	20	25	32	40	45	50
				192	240	300	384	480	540	600
				50	50	50	50	50	50	50
Selectivity limits [kA] ¹⁾										
5SY4 ...-5										
Characteristic A	2	6	10	0.2	0.8	1.2	2.5	3	6	6
	10	30	10	0.2	0.4	0.5	0.6	0.8	1	1.2
	16	48	10	--	0.3	0.4	0.6	0.8	0.8	1
	32	96	10	--	--	--	--	0.6	0.8	0.8
	40	120	10	--	--	--	--	--	--	0.8
5SY4 ...-6, 5SY7 ...-6										
Characteristic B	6	30	6/10/15	0.2	0.3	0.5	0.6	0.8	1	1.2
	10	50	6/10/15	0.2	0.3	0.4	0.6	0.8	1	1.2
	13	65	6/10/15	0.2	0.3	0.4	0.6	0.8	1	1
	16	80	6/10/15	--	0.3	0.4	0.6	0.8	1	1
	20	100	6/10/15	--	--	0.4	0.6	0.8	1	1
	25	125	6/10/15	--	--	--	0.5	0.6	0.8	0.8
	32	160	6/10/15	--	--	--	--	0.6	0.8	0.8
	40	200	6/10/15	--	--	--	--	--	--	0.8
	50	250	6/10/15	--	--	--	--	--	--	--
	63	315	6/10/15	--	--	--	--	--	--	--
	80	400	6/10/15	--	--	--	--	--	--	--
5SY4 ...-7, 5SY6 ...-7, 5SY7 ...-7										
Characteristic C	0.5	5	6/10/15	0.3	0.5	0.6	1	1	1.5	3
	1	10	6/10/15	0.3	0.5	0.6	1	1	1.5	3
	1.6	16	6/10/15	0.3	0.5	0.6	1	1	1.5	3
	2	20	6/10/15	0.3	0.5	0.6	1	1	1.5	3
	3	30	6/10/15	0.2	0.3	0.4	0.6	0.8	1	1
	4	40	6/10/15	0.2	0.3	0.4	0.6	0.8	1	1
	6	60	6/10/15	0.2	0.3	0.4	0.6	0.8	1	1
	8	80	6/10/15	0.2	0.2	0.4	0.6	0.6	0.8	1
	10	100	6/10/15	0.2	0.2	0.4	0.6	0.6	0.8	1
	13	130	6/10/15	0.2	0.2	0.4	0.6	0.6	0.8	1
	16	160	6/10/15	--	0.2	0.4	0.6	0.6	0.8	1
	20	200	6/10/15	--	--	0.4	0.6	0.6	0.8	1
	25	250	6/10/15	--	--	--	0.5	0.6	0.8	0.8
	32	320	6/10/15	--	--	--	--	0.6	0.8	0.8
	40	400	6/10/15	--	--	--	--	--	--	0.8
	50	500	6/10/15	--	--	--	--	--	--	--
	63	630	6/10/15	--	--	--	--	--	--	--
	80	800	6/10/15	--	--	--	--	--	--	--
5SY4 ...-8, 5SY6 ...-8, 5SY7 ...-8										
Characteristic D	2	40	6/10/15	0.3	0.5	0.6	0.8	1.2	1.5	1.5
	6	120	6/10/15	0.2	0.3	0.4	0.6	0.8	1	1
	10	200	6/10/15	--	0.3	0.4	0.5	0.6	0.8	0.8
	16	320	6/10/15	--	--	--	0.5	0.6	0.6	0.8
	32	640	6/10/15	--	--	--	--	--	0.6	0.6
	40	800	6/10/15	--	--	--	--	--	--	--
	50	1000	6/10/15	--	--	--	--	--	--	--
	63	1260	6/10/15	--	--	--	--	--	--	--

¹⁾ In 240/415 V, 50 Hz systems, the selectivity limits are reduced by 10 %.
 $I > \hat{=}$ tripping current.

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

In the event of a short circuit, there is selectivity between miniature circuit breakers and circuit breakers according to IEC/EN 60947-2 up to the specified values in kA.

Limit values of selective miniature circuit breakers/circuit breakers in kA

Downstream miniature circuit breakers				Upstream circuit breakers									
				3RV1. 4									
	I_n [A]	$I > [A]$	I_{cn} [kA]	16	20	25	32	40	50	63	75	90	100
				192	240	300	384	480	600	756	900	1080	1140
				100	100	100	100	100	100	100	100	100	100
Selectivity limits [kA] ¹⁾													
5SY4 ...-5													
Characteristic A	2	6	10	0.5	0.8	1.5	2.5	3	6/7.5	6/10	6/10	6/10	6/10
	10	30	10	0.3	0.4	0.5	0.6	0.8	1.2	1.5	2.5	3	4
	16	48	10	--	0.3	0.5	0.6	0.6	1	1.5	2	3	3
	32	96	10	--	--	--	--	0.6	0.8	1.5	2	2.5	3
	40	120	10	--	--	--	--	--	0.8	1.2	1.5	2	2
5SY4 ...-6, 5SY6 ...-6, 5SY7 ...-6													
Characteristic B	6	30	6/10/15	0.2	0.4	0.5	0.6	0.8	1.2	2	3	6/10/15	6/10/15
	10	50	6/10/15	0.2	0.3	0.5	0.6	0.8	1	1.5	2.5	4	4
	13	65	6/10/15	0.2	0.3	0.5	0.6	0.8	1	1.5	2	3	3
	16	80	6/10/15	--	0.3	0.5	0.6	0.8	1	1.5	2	3	3
	20	100	6/10/15	--	--	0.5	0.6	0.8	1	1.5	2	3	3
	25	125	6/10/15	--	--	--	0.5	0.8	0.8	1.5	2	3	3
	32	160	6/10/15	--	--	--	--	0.6	0.8	1.5	2	3	3
	40	200	6/10/15	--	--	--	--	0.6	0.8	1.2	1.5	2.5	2.5
	50	250	6/10/15	--	--	--	--	--	--	1.2	1.5	2.5	2.5
5SY4 ...-7, 5SY6 ...-7, 5SY7 ...-7													
Characteristic C	0.5	5	6/10/15	0.4	0.6	0.8	0.8	1	3	6/10/15	6/10/15	6/10/15	6/10/15
	1	10	6/10/15	0.4	0.6	0.8	0.8	1	3	6/10/15	6/10/15	6/10/15	6/10/15
	1.6	16	6/10/15	0.4	0.6	0.8	0.8	1	3	6/10/15	6/10/15	6/10/15	6/10/15
	2	20	6/10/15	0.4	0.6	0.8	0.8	1	3	6/10/15	6/10/15	6/10/15	6/10/15
	3	30	6/10/15	0.2	0.3	0.5	0.6	0.8	1	2	2.5	5	5
	4	40	6/10/15	0.2	0.3	0.5	0.6	0.8	1	2	2.5	5	5
	6	60	6/10/15	0.2	0.3	0.5	0.6	0.8	1	2	2.5	5	5
	8	80	6/10/15	0.2	0.3	0.4	0.6	0.6	1	1.5	2	3	3
	10	100	6/10/15	0.2	0.3	0.4	0.6	0.6	1	1.5	2	3	3
	13	130	6/10/15	0.2	0.3	0.4	0.6	0.6	1	1.5	2	3	3
	16	160	6/10/15	--	0.3	0.4	0.6	0.6	1	1.5	2	3	3
	20	200	6/10/15	--	--	0.4	0.6	0.6	1	1.5	2	3	3
	25	250	6/10/15	--	--	--	0.5	0.6	0.8	1.2	1.5	2.5	2.5
	32	320	6/10/15	--	--	--	--	0.6	0.8	1.2	1.5	2.5	2.5
	40	400	6/10/15	--	--	--	--	--	0.6	1	1.5	2	2
50	500	6/10/15	--	--	--	--	--	--	1	1.2	1.5	2	
63	630	6/10/15	--	--	--	--	--	--	--	--	1.5	1.5	
5SY4 ...-8, 5SY6 ...-8, 5SY7 ...-8													
Characteristic D	2	40	6/10/15	0.4	0.5	0.6	0.8	1	1.5	3	4	6/10/15	6/10/15
	6	120	6/10/15	0.2	0.3	0.4	0.6	0.6	1	1.5	2.5	3	3
	10	200	6/10/15	--	0.3	0.4	0.5	0.6	0.8	1.5	2	3	3
	16	320	6/10/15	--	--	--	0.5	0.6	0.8	1.2	1.5	2.5	2.5
	32	640	6/10/15	--	--	--	--	--	0.6	1	1.5	2	2
	40	800	6/10/15	--	--	--	--	--	--	1	1.2	1.5	1.5
50	1000	6/10/15	--	--	--	--	--	--	1	1.2	1.5	1.5	
5SP4 ...-7													
Characteristic C	80	1600	10	--	--	--	--	--	--	--	--	--	1.2
	100	2000	10	--	--	--	--	--	--	--	--	--	--
5SP4 ...-8													
Characteristic D	80	1600	10	--	--	--	--	--	--	--	--	--	--
	100	2000	10	--	--	--	--	--	--	--	--	--	--

Values for 5SY8 on request.

¹⁾ In 240/415 V, 50 Hz systems, the selectivity limits are reduced by 10 %.

$I > \hat{=}$ tripping current.

Configuration and dimensioning

In the event of a short circuit, there is selectivity between miniature circuit breakers and circuit breakers according to IEC/EN 60947-2 up to the specified values in kA.

Limit values of selective miniature circuit breakers/circuit breakers in kA

Downstream miniature circuit breakers				Upstream circuit breakers											
				3VL1, TM Non-adjustable						3VL2, TM Adjustable					
				I_n [A]	$I > [A]$	I_{cn} [kA]	50	63	80	100	125	160	50	63	80
			500	630	800	1000	1250	1600	400	500	630	800	1000	1280	
			40/70/	40/70/	40/70/	40/70/	40/70/	40/70/	40/70/	40/70/	40/70/	40/70/	40/70/	40/70/	
			100	100	100	100	100	100	100	100	100	100	100	100	
Selectivity limits [kA] ¹⁾															
5SY4 ...-5, 5SY7 ...-5															
Characteristic A	2	6	10	10	10	10	10	10	10	10	10	10	10	10	10
	10	30	10	1.6	4.7	6	10	10	10	2.5	4	4	4.5	4.9	10
	16	48	10	1.4	4.7	6	10	10	10	2.3	3.7	3.7	4.4	5	10
	32	96	10	1.2	3.6	4.6	10	10	10	1.8	3	3	3.5	3.7	6
	40	120	10	1	2.5	3.1	6	10	10	1.5	2	2	2.4	2.7	3.2
5SY4 ...-6, 5SY6 ...-6, 5SY7 ...-6															
Characteristic B	6	30	6/10/15	5.5	5.5	T	T	T	T	2.5	2.5	5.1	7.3	T	T
	10	50	6/10/15	3.1	3.1	6.7	6.7	6.7	6/12/4	2.0	2.0	3.0	3.9	5.0	8.6
	13	65	6/10/15	2.5	2.5	5.0	5.0	5.0	8.0	1.5	1.5	3.1	3.4	4.5	5.8
	16	80	6/10/15	2.5	2.5	4.4	4.4	4.4	7.2	1.5	1.5	2.0	3.1	4.0	5.1
	20	100	6/10/15	2.0	2.0	4.3	4.3	4.3	6.6	1.5	1.5	2.0	2.5	3.9	5.0
	25	125	6/10/15	2.0	2.0	3.9	3.9	3.9	6.1	1.5	1.5	2.0	2.1	3.4	4.6
	32	160	6/10/15	2.0	2.0	3.7	3.7	3.7	5.0	1.5	1.5	2.0	2.1	3.4	4.8
	40	200	6/10/15	2.0	2.0	3.7	3.7	3.7	5.0	1.2	1.2	2.0	2.1	3.3	4.3
	50	250	6/10/15	--	1.5	3.2	3.2	3.2	4.0	--	--	1.5	2.0	2.5	3.6
5SY4 ...-7, 5SY6 ...-7, 5SY7 ...-7															
Characteristic C	0.5	5	6/10/15	T	T	T	T	T	T	T	T	T	T	T	T
	1	10	6/10/15	T	T	T	T	T	T	T	T	T	T	T	T
	1.5	15	6/10/15	T	T	T	T	T	T	T	T	T	T	T	T
	2	20	6/10/15	T	T	T	T	T	T	T	T	T	T	T	T
	3	30	6/10/15	3.2	3.2	T	T	T	T	2.5	T	T	T	T	T
	4	40	6/10/15	3.2	3.2	T	T	T	T	2.5	T	T	T	T	T
	6	60	6/10/15	3.2	3.2	7	7	7	6/10/13.9	2.5	2.5	5.1	7.3	T	T
	8	80	6/10/15	2.5	2.5	5.4	5.4	5.4	6/9/2	2.3	3.7	3.8	3.9	5.6	8.6
	10	100	6/10/15	2.5	2.5	5.4	5.4	5.4	6/9/2	2.0	2.0	3.0	3.4	5.6	8.6
	13	130	6/10/15	2.5	2.5	4.3	4.3	4.3	7.1	1.5	1.5	2.5	3.4	4.5	5.8
	16	160	6/10/15	2.0	2.5	4.0	4.0	4.0	7.1	1.5	1.5	2.5	3.1	4.0	5.1
	20	200	6/10/15	2.0	2.0	3.7	3.7	3.7	6.3	1.5	1.5	2.0	2.5	3.9	5.0
	25	250	6/10/15	2.0	2.0	3.6	3.6	3.6	5.5	1.5	1.5	2.0	2.5	3.5	4.6
	32	320	6/10/15	2.0	2.0	3.5	3.5	3.5	5.5	1.5	1.5	2.0	2.5	3.4	4.5
40	400	6/10/15	1.5	1.5	3.3	3.3	3.3	5.1	1.2	1.2	2.0	2.5	3.3	4.3	
50	500	6/10/15	--	1.5	3.1	3.1	3.1	4.0	--	--	1.5	2.5	2.5	3.6	
5SY4 ...-8, 5SY6 ...-8, 5SY7 ...-8															
Characteristic D	2	40	6/10/15	2.4	6	6	6	6	6	4.2	6	6	6	6	6
	6	120	6/10/15	1.4	1.4	4.8	5	6	6	2.3	4.1	4.2	4.2	4.3	6
	10	200	6/10/15	1.3	1.3	4.5	5	6	6	1.9	3.7	3.7	3.7	4	6
	16	320	6/10/15	1.1	1.1	3.2	3.2	3.2	4.0	1.7	3.3	3.7	3.3	3.5	4.7
	32	640	6/10/15	--	--	2.3	2.3	2.3	4.0	--	--	--	2.4	2.7	3.7
	40	800	6/10/15	--	--	--	2.1	2.1	3.8	--	--	--	--	1.5	3
50	1000	6/10/15	--	--	--	--	2.0	2.8	--	--	--	--	--	2.6	
5SP4 ...-7															
Characteristic C	80	800	10	--	--	--	1.0	1.2	2.0	--	--	--	--	1.2	1.5
	100	1000	10	--	--	--	--	1.2	1.5	--	--	--	--	--	1.5
5SP4 ...-8															
Characteristic D	80	1600	10	--	--	--	--	--	--	--	--	--	--	--	--
	100	1200	10	--	--	--	--	--	--	--	--	--	--	--	--

Values for 5SY8 on request.

T $\hat{=}$ full selectivity up to rated breaking capacity I_{cn} of the downstream protective device.

- ¹⁾ In 240/415 V, 50 Hz systems, the selectivity limits are reduced by 10 %.
The selectivity limits for adjustable releases apply to the maximum value,
 I_n = rated current. $I > \hat{=}$ tripping current.

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

In the event of a short circuit, there is selectivity between miniature circuit breakers and circuit breakers according to IEC/EN 60947-2 up to the specified values in kA.

Limit values of selective miniature circuit breakers/circuit breakers in kA

Downstream miniature circuit breakers	Upstream circuit breakers											
	3VL3, TM			3VL4, TM			3VL6, ETU		3VL7, ETU	3VL8, ETU	3WN1	3WN6
	I_n [A]						315	400 ...	400 ...	800 ...	315 ...	315 ...
	$I > [A]$						3200	800	1250	2500	6300	3200
	I_{cn} [kA]							1575 ...	15000	20000	3780 ...	3780 ...
								6400			75600	48000
								45 ... 100	50 ... 100	70/100	65 ... 100	65/75
								Selectivity limits [kA] ¹⁾				

5SY4 ...-5, 5SY7 ...-5

Characteristic A

2	6	10	T	T	T	T	T	T	T	T	T	T	T
10	30	10	T	T	T	T	T	T	T	T	T	T	T
16	48	10	T	T	T	T	T	T	T	T	T	T	T
32	96	10	T	T	T	T	T	T	T	T	T	T	T
40	120	10	T	T	T	T	T	T	T	T	T	T	T

5SY4 ...-6, 5SY6 ...-6, 5SY7 ...-6

Characteristic B

6	30	6/10/15	T	T	T	T	T	T	T	T	T	T	T
10	50	6/10/15	T	T	T	T	T	T	T	T	T	T	T
13	65	6/10/15	T	T	T	T	T	T	T	T	T	T	T
16	80	6/10/15	T	T	T	T	T	T	T	T	T	T	T
20	100	6/10/15	T	T	T	T	T	T	T	T	T	T	T
25	125	6/10/15	T	T	T	T	T	T	T	T	T	T	T
32	160	6/10/15	T	T	T	T	T	T	T	T	T	T	T
40	200	6/10/15	6	6	6	T	T	T	T	T	T	T	T
50	250	6/10/15	6	6	6/10/14.1	T	T	T	T	T	T	T	T

5SY4 ...-7, 5SY6 ...-7, 5SY7 ...-7

Characteristic C

0.5	5	6/10/15	T	T	T	T	T	T	T	T	T	T	T
1	10	6/10/15	T	T	T	T	T	T	T	T	T	T	T
1.5	15	6/10/15	T	T	T	T	T	T	T	T	T	T	T
2	20	6/10/15	T	T	T	T	T	T	T	T	T	T	T
3	30	6/10/15	T	T	T	T	T	T	T	T	T	T	T
4	40	6/10/15	T	T	T	T	T	T	T	T	T	T	T
6	60	6/10/15	T	T	T	T	T	T	T	T	T	T	T
8	80	6/10/15	T	T	T	T	T	T	T	T	T	T	T
10	100	6/10/15	T	T	T	T	T	T	T	T	T	T	T
13	130	6/10/15	T	T	T	T	T	T	T	T	T	T	T
16	160	6/10/15	T	T	T	T	T	T	T	T	T	T	T
20	200	6/10/15	T	T	T	T	T	T	T	T	T	T	T
25	250	6/10/15	T	T	T	T	T	T	T	T	T	T	T
32	320	6/10/15	6/10/11	T	T	T	T	T	T	T	T	T	T
40	400	6/10/15	6/10	T	T	T	T	T	T	T	T	T	T
50	500	6/10/15	6/10	T	T	T	T	T	6/10/14.2	T	T	T	T

5SY4 ...-8, 5SY6 ...-8, 5SY7 ...-8

Characteristic D

2	40	6/10/15	T	T	T	T	T	T	T	T	T	T	T
6	120	6/10/15	T	T	T	T	T	T	T	T	T	T	T
10	200	6/10/15	T	T	T	T	T	T	T	T	T	T	T
16	320	6/10/15	T	T	T	T	T	T	T	T	T	T	T
32	640	6/10/15	T	T	T	T	T	T	T	T	T	T	T
40	800	6/10/15	T	T	T	T	T	T	T	T	T	T	T
50	1000	6/10/15	T	T	T	T	T	T	T	T	T	T	T

5SP4 ...-7

Characteristic C

80	800	10	3	3	3	3	3	6	8	T	T	T	T	T
100	1000	10	3	3	3	3	3	5	6	T	T	T	T	T

5SP4 ...-8

Characteristic D

80	1600	10	3	3	2.5	3	3	5	6	T	T	T	T	T
100	2000	10	--	2.5	--	3	3	5	6	T	T	T	T	T

Values for 5SY8 on request.

T $\hat{=}$ full selectivity up to rated breaking capacity I_{cn} of the downstream protective device.

¹⁾ In 240/415 V, 50 Hz systems, the selectivity limits are reduced by 10 %.

The selectivity limits for adjustable releases apply to the maximum value,

I_n = rated current. $I >$ = tripping current.

Configuration and dimensioning

Within narrow limits, miniature circuit breakers also offer selectivity between circuit breakers in a fuseless distribution board. The following table shows the short-circuit current in kA up to which there is selectivity between series-connected miniature circuit breakers at 230 V AC.

This depends on the let-through peak current I of the downstream miniature circuit breaker and on the tripping current of the upstream miniature circuit breaker.

Limit values of selective miniature circuit breakers/circuit breakers in kA

Downstream miniature circuit breakers				Upstream miniature circuit breakers									
I_n [A]	$I > [A]$	I_{cn} [kA]		5SY4 ...-7 Characteristic C					5SP4 ...-7 Characteristic C		5SP4 ...-8 Characteristic D		Selectivity limits [kA] ¹⁾
				20	25	32	40	50	80	100	80	100	
				200	250	320	400	500	800	1000	1200	1500	
				10	10	10	10	10	10	10	10	10	
5SY. ...-6													
Characteristic B	6	30	6/10/15	0.2	0.2	0.3	0.5	0.5	0.8	1.5	3	5	
	10	50	6/10/15	0.2	0.2	0.3	0.5	0.5	0.8	1.2	3	4	
	13	65	6/10/15	0.2	0.2	0.3	0.4	0.5	0.8	1.2	2	3	
	16	80	6/10/15	0.2	0.2	0.3	0.4	0.5	0.8	1.2	2	3	
	20	100	6/10/15	--	0.2	0.3	0.4	0.5	0.8	1.2	2	3	
	25	125	6/10/15	--	--	--	0.4	0.4	0.6	1.2	1.5	3	
	32	160	6/10/15	--	--	--	0.4	0.4	0.6	1.2	1.5	3	
	40	200	6/10/15	--	--	--	--	0.4	0.6	1.2	1.5	2.5	
	50	250	6/10/15	--	--	--	--	--	0.6	1	1.5	2.5	
5SY. ...-7													
Characteristic C	0.5	5	6/10/15	0.2	0.3	0.5	0.8	0.8	1.2	4	T	T	
	1	10	6/10/15	0.2	0.3	0.5	0.8	0.8	1.2	4	T	T	
	1.5	15	6/10/15	0.2	0.3	0.5	0.8	0.8	1.2	4	T	T	
	2	20	6/10/15	0.2	0.3	0.5	0.8	0.8	1.2	4	T	T	
	3	30	6/10/15	0.2	0.2	0.3	0.5	0.5	0.8	1.5	3	4	
	4	40	6/10/15	0.2	0.2	0.3	0.5	0.5	0.8	1.5	3	4	
	6	60	6/10/15	0.2	0.2	0.3	0.5	0.5	0.8	1.5	3	4	
	8	80	6/10/15	0.2	0.2	0.3	0.4	0.4	0.6	1.2	2.5	3	
	10	100	6/10/15	0.2	0.2	0.3	0.4	0.4	0.6	1.2	2.5	3	
	13	130	6/10/15	0.2	0.2	0.3	0.4	0.4	0.6	1.2	2	3	
	16	160	6/10/15	0.2	0.2	0.3	0.4	0.4	0.6	1.2	2	3	
	20	200	6/10/15	--	0.2	0.3	0.4	0.4	0.6	1.2	2	3	
	25	250	6/10/15	--	--	--	0.3	0.4	0.6	1	1.5	2.5	
	32	320	6/10/15	--	--	--	0.3	0.4	0.6	1	1.5	2.5	
	40	400	6/10/15	--	--	--	--	--	--	0.8	1.5	2	
	50	500	6/10/15	--	--	--	--	--	--	0.8	1.5	2	
	63	630	6/10/15	--	--	--	--	--	--	0.8	1.2	1.5	

T ≙ full selectivity up to rated breaking capacity I_{cn} of the downstream protective device.

¹⁾ In 240/415 V, 50 Hz systems, the selectivity limits are reduced by 10 %.
The selectivity limits for adjustable releases apply to the maximum value,
 I_n = rated current. $I >$ ≙ tripping current.

BETA Protecting Miniature Circuit Breakers


Configuration and dimensioning

Back-up protection miniature circuit breakers/fuses

If the maximum short-circuit current of the miniature circuit breaker at the installation site is unknown, or if the specified rated switching capacity is exceeded, an additional protective device must be connected upstream as back-up protection to prevent overloading of the miniature circuit breaker. This is usually a fuse.

The following table shows the short-circuit currents in kA up to which back-up protection is guaranteed when using fuses according to DIN VDE 0636-21.

Limit values of back-up protection miniature circuit breakers/fuses in kA

	Downstream miniature circuit breakers		Upstream fuses					
	I_n [A]		50 A	63 A	80 A	100 A	125 A	160 A
5SY6	0.3 ... 4		No back-up protection required up to 50 kA					
	6		50	50	50	50	50	35
	8		50	50	50	50	50	35
	10		50	50	50	50	50	35
	13		50	50	50	35	35	30
	16		50	50	50	35	30	30
	20		50	50	50	35	25	25
	25		50	50	50	35	30	25
	32		50	50	50	35	30	25
	40		50	50	50	50	25	15
	50		50	50	50	50	25	15
	63		50	50	35	25	25	15
5SY4, 5SY7	0.3 ... 6		No back-up protection required					
	8		50	50	50	50	45	45
	10		50	50	50	50	45	45
	13		50	50	50	45	40	35
	16		50	50	50	45	40	35
	20		50	50	50	40	35	30
	25		50	50	50	40	35	30
	32		50	50	50	45	40	30
	40		50	50	50	45	40	30
	50		50	50	50	40	35	25
	63		50	50	45	40	35	25

Test circuit data:

$U_p = 250$ V
p.f. = 0.3 ... 0.5

Test cycle:

Acc. to EN 60947-2 (0 - C0)

Configuration and dimensioning

Back-up protection miniature circuit breakers/circuit breakers

If miniature circuit breakers are installed in fuseless distribution boards, circuit breakers according to IEC/EN 60947-2 must be used as back-up protection.

The following tables show the short-circuit currents in kA up to which back-up protection is guaranteed when using circuit breakers.

Limit values of back-up protection miniature circuit breakers/circuit breakers in kA

Downstream miniature circuit breakers				Upstream circuit breakers																
				3VL1 Non-adjustable												3VL2 adjustable				
	I_n [A]	$I_{>}$ [A]	I_{cu} [kA]	16	20	25	32	40	50	63	80	100	125	160	50	63	80	100	125	160
				160	200	250	320	400	500	630	800	1000	1250	1600	400	500	630	800	1000	1280
				40/ 70	40/ 70	40/ 70	40/ 70	40/ 70	40/ 70	40/ 70	40/ 70	40/ 70	40/ 70	40/ 70	40/70/ 100	40/70/ 100	40/70/ 100	40/70/ 100	40/70/ 100	40/70/ 100
	I_n [A]	I_{cn} [kA]		Back-up protection up to kA																
	5SY6																			
	Characteristic B, C, D	0.3 ... 6	6	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35
		8 ... 32	6	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		40 ... 63	6	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20
	5SY4																			
	Characteristic A, B, C, D	0.3 ... 6	10	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40
		8 ... 32	10	30	30	30	30	30	30	30	30	30	30	30	30	30	30	30	30	30
		40 ... 63	10	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	5SY7																			
	Characteristic B, C	0.3 ... 2	15	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50
	3 ... 10	15	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	
	13 ... 32	15	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	
	40 ... 63	15	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	
	Characteristic D	0.3 ... 2	15	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50
		3 ... 10	15	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45
		13 ... 32	15	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40
		40	15	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35
		50 ... 63	15	30	30	30	30	30	30	30	30	30	30	30	30	30	30	30	30	30
5SY8																				
Characteristic C	0.3 ... 2	25	70	70	70	70	70	70	70	70	70	70	70	70	70	70	70	70	70	70
	3 ... 6	25	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50
	8 ... 32	25	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45
	40 ... 63	25	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40
	Characteristic D	0.3 ... 2	25	70	70	70	70	70	70	70	70	70	70	70	70	70	70	70	70	70
		3 ... 6	25	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50	50
		8 ... 32	25	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45	45
		40	25	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40	40
		50 ... 63	25	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35	35
5SP4																				
Characteristic B, C	80 ... 125	10	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
Characteristic D	80 ... 100	10	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20



BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

Downstream miniature circuit breakers			Upstream circuit breakers													
			3VL3		3VL4				3VL5				3VL6	3VL7	3VL8	3WN1/ 3WS1
	I_n [A]		200	250	200	250	315	400	250 ... 315	315 ... 400	400 ... 500	500 ... 630	320 ... 800	400 ... 1250	1600 ... 2000	315 ... 6300
	$I >$ [A]		2000	2500	2000	2500	3150	4000	2500 ... 3150	3150 ... 4000	4000 ... 5000	5000 ... 6300	3200 ... 6300	15 000	20 000	3780 ... 75 600
	I_{cn} [kA]		40/70/ 100	40/70/ 100	45/70/ 100	45/70/ 100	45/70/ 100	45/70/ 100	45/70/ 100	45/70/ 100	45/70/ 100	45/70/ 100	45/70/ 100	50/70/ 100	70/100	65 ... 100
	I_n [A]	I_{cn} [kA]	Back-up protection up to kA													
5SY6																
Characteristic B, C, D	0.3 ... 6	6	35	35	35	35	35	35	35	35	35	35	35	35	35	35
	8 ... 32	6	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	40 ... 63	6	20	20	20	20	20	20	20	20	20	20	20	20	20	20
5SY4																
Characteristic A, B, C, D	0.3 ... 6	10	40	40	40	40	40	40	40	40	40	40	40	40	40	40
	8 ... 32	10	30	30	30	30	30	30	30	30	30	30	30	30	30	30
	40 ... 63	10	25	25	25	25	25	25	25	25	25	25	25	25	25	25
5SY7																
Characteristic B, C	0.3 ... 2	10	50	50	50	50	50	50	50	50	50	50	50	50	50	50
	3 ... 10	10	45	45	45	45	45	45	45	45	45	45	45	45	45	45
	13 ... 32	10	40	40	40	40	40	40	40	40	40	40	40	40	40	40
	40 ... 63	10	35	35	35	35	35	35	35	35	35	35	35	35	35	35
Characteristic D	0.3 ... 2	10	50	50	50	50	50	50	50	50	50	50	50	50	50	50
	3 ... 10	10	45	45	45	45	45	45	45	45	45	45	45	45	45	45
	13 ... 32	10	40	40	40	40	40	40	40	40	40	40	40	40	40	40
	40	10	35	35	35	35	35	35	35	35	35	35	35	35	35	35
	50 ... 63	10	30	30	30	30	30	30	30	30	30	30	30	30	30	30
5SY8																
Characteristic C	0.3 ... 2	25	70	70	70	70	70	70	70	70	70	70	70	--	--	--
	3 ... 6	25	50	50	50	50	50	50	50	50	50	50	50	--	--	--
	8 ... 32	25	45	45	45	45	45	45	45	45	45	45	45	--	--	--
	40 ... 63	25	40	40	40	40	40	40	40	40	40	40	40	--	--	--
Characteristic D	0.3 ... 2	25	70	70	70	70	70	70	70	70	70	70	70	--	--	--
	3 ... 6	25	50	50	50	50	50	50	50	50	50	50	50	--	--	--
	8 ... 32	25	45	45	45	45	45	45	45	45	45	45	45	--	--	--
	40	25	40	40	40	40	40	40	40	40	40	40	40	--	--	--
	50 ... 63	25	35	35	35	35	35	35	35	35	35	35	35	--	--	--
5SP4																
Characteristic B, C	80 ... 125	10	25	25	25	25	25	25	25	25	25	25	25	--	--	--
Characteristic D	80 ... 100	10	20	20	20	20	20	20	20	20	20	20	20	--	--	--

Configuration and dimensioning

Internal resistance and power loss

Data per pole (with I_n)

I_n A	Characteristic A		Characteristic B		Characteristic C		Characteristic D	
	R_l mΩ	P_v W	R_l mΩ	P_v W	R_l mΩ	P_v W	R_l mΩ	P_v W
5SY4, 5SY6, 5SY7, 5SY8, 5SY5								
0.3	--	--	--	--	10 500	0.9	10 200	1
0.5	--	--	--	--	3400	0.9	3120	0.8
1	1955	2.0	--	--	1210	1.2	1030	1.0
1.6	786	2.0	--	--	459	1.2	409	1.1
2	510	2.0	375	1.5	295	1.2	292	1.2
3	205	1.9	--	--	137	1.2	131	1.2
4	134	2.1	91	1.45	81	1.3	73	1.2
6	58	2.1	55	2.0	44	1.6	43	1.6
8	27	1.7	--	--	14	0.9	12	0.7
10	18.1	1.8	13	1.3	10	1.0	8.4	0.8
13	11.4	1.9	9.5	1.6	8.0	1.4	8.0	1.4
16	8.4	2.2	6.6	1.7	5.9	1.5	5.8	1.5
20	6.2	2.5	5.2	2.1	4.0	1.6	3.8	1.5
25	4.6	2.9	3.4	2.2	3.3	2.1	3.0	1.9
32	3	3.1	2.3	2.4	2.4	2.5	1.9	2.0
35	--	--	--	--	2.0	2.4	--	--
40	2.2	3.5	2.1	3.4	2.1	3.3	1.8	2.8
50	1.7	4.3	1.5	3.8	1.4	3.5	1.4	3.5
63	1.5	5.9	1.4	5.4	1.1	4.4	1.1	4.4
80	--	--	1.0	6.4	1.0	6.4	--	--
5SP4, 5SP5								
80	--	--	1.1	7.0	1.1	6.7	1.1	6.7
100	--	--	0.8	8.0	0.88	8	0.8	8
125	--	--	0.7	10.1	0.7	10.8	--	--

Correction factor for power loss

- Direct current and alternating current up to 60 Hz × 1.0
- Alternating current
 - 200 Hz × 1.1
 - 400 Hz × 1.15
 - 1000 Hz × 1.3

Internal resistance R_l and power loss P_v of the miniature circuit breaker compact range 1+N in 1 MW, 5SY6 0

Data per pole (with I_n)

I_n A	Characteristic B Phase-pole		N pole		Characteristic C Phase-pole		N pole	
	R_l mΩ	P_v mW	R_l mΩ	P_v mW	R_l mΩ	P_v mW	R_l mΩ	P_v mW
5SY6 0								
2	--	--	--	--	290	1161	3.8	15
4	--	--	--	--	110	1766	4.0	64
6	30	1092	4.2	150	26	931	4.3	154
8	--	--	--	--	19.8	1264	3.9	249
10	15	1539	4.1	407	13	1297	4.1	406
13	9.5	1598	4.1	692	9.1	1531	4.4	742
16	8.7	2219	4.0	1018	7.5	1926	3.3	852
20	5.2	2082	1.1	436	5.3	2118	1.2	478
25	3.3	2065	1.3	804	3.0	1906	1.1	674
32	2.6	2625	1.2	1192	2.7	2718	1.3	1310
40	2.3	3619	1.1	1789	2.2	3531	1.1	1820

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

Personnel safety with miniature circuit breakers

According to DIN VDE 0100-410, in order to protect against dangerous electric shocks in the TN system, the cross-sections of the conductors, or their distance from the protective device, must be dimensioned such that if a fault with negligible impedance (i. e. short circuit) occurs at any point between a phase conductor and a PE conductor, or a connected exposed conductive part, the device automatically trips within the specified times of 0.4 s/5 s.

This requirement is met through the following condition:

$$Z_s \times I_a \leq U_0$$

Z_s $\hat{=}$ Impedance of the fault loop of all electrical circuits

I_a $\hat{=}$ Current that trips within the specified times

U_0 $\hat{=}$ Voltage against ground

Maximum permissible impedance of fault loop at $U_0 = 230$ V AC for compliance with trip conditions according to DIN VDE 0100-410

I_n A	Characteristic A		Characteristic B		Characteristic C		Characteristic D	
	$t_a \leq 0.4$ s	≤ 5 s	$t_a \leq 0.4$ s	≤ 5 s	$t_a \leq 0.4$ s	≤ 5 s	$t_a \leq 0.4$ s	≤ 5 s
	Ω	Ω	Ω	Ω	Ω	Ω	Ω	Ω
5SY, 5SP								
0.3	--	--	--	--	76.6	153	--	--
0.5	--	--	--	--	46	92	--	92
1.0	76.6	76.6	--	--	23	46	15.3	46
1.6	47.9	47.9	--	--	14.4	28.8	9.6	28.8
2	38.3	38.3	--	--	11.5	23	7.6	23
3	25.5	25.5	--	--	7.7	15.4	5.1	15.4
4	19.1	19.1	--	--	5.8	11.6	3.8	11.6
6	12.7	12.7	7.6	7.6	3.8	7.6	2.5	7.6
8	--	--	--	--	2.8	5.7	1.9	5.7
10	7.6	7.6	4.6	4.6	2.3	4.6	1.1	4.6
13	--	--	--	3.57	1.7	3.4	0.9	3.4
16	4.7	4.7	2.9	2.9	1.4	2.8	0.7	2.8
20	3.8	3.8	2.3	2.3	1.1	2.2	0.5	2.2
25	3.0	3.0	1.8	1.8	0.9	1.8	0.4	1.8
32	2.4	2.4	1.4	1.4	0.7	1.4	0.3	1.4
40	1.9	1.9	1.1	1.1	0.6	1.2	0.28	1.2
50	--	--	0.9	0.9	0.5	1.0	0.23	1.0
63	--	--	0.7	0.7	0.4	0.8	0.2	0.8
80	--	--	--	--	0.3	0.6	0.14	0.6
100	--	--	--	--	0.2	0.4	0.1	0.4
125	--	--	--	--	0.16	0.3	0.1	0.3

At $U_0 = 240$ V AC, $Z_s \times 1.04$ applies.

At $U_0 = 127$ V AC, $Z_s \times 0.55$ applies.

Configuration and dimensioning

Fusing of luminaire circuits

Maximum permissible lamp load of a miniature circuit breaker when operating fluorescent lamps L 18 W, L 36 W, L 38 W, L 58 W.

Maximum number of fluorescent lamps

I_n [A]	Lamp	Electronic ballast											
		Full switching at 230 V 1 lamp ¹⁾						Group switching at 230 V 1 lamp ²⁾					
2 lamps													
5SY4, 5SY7													
Characteristic		B	C	D	B	C	D	B	C	D	B	C	D
6	L 18 W	17	37	66	17	35	35	66	66	66	35	35	35
	L 36 W	17	37	37	17	19	19	37	37	37	19	19	19
	L 58 W	17	19	19	12	12	12	19	19	19	12	12	12
8	L 18 W	--	50	88	--	47	47	--	88	88	--	--	47
	L 36 W	--	50	50	--	25	25	--	50	50	--	25	25
	L 58 W	--	25	25	--	16	16	--	25	25	--	16	16
10	L 18 W	36	67	111	36	58	58	111	111	111	58	58	58
	L 36 W	36	62	62	32	32	32	62	62	62	32	32	32
	L 58 W	32	32	32	20	20	20	32	32	32	20	20	20
13	L 18 W	44	81	144	44	76	76	144	144	144	76	76	76
	L 36 W	44	81	81	41	41	41	81	81	81	41	41	41
	L 58 W	41	41	41	26	26	26	41	41	41	26	26	26
16	L 18 W	56	100	177	56	94	94	177	177	177	94	94	94
	L 36 W	56	100	100	51	51	51	100	100	100	51	51	51
	L 58 W	51	51	51	32	32	32	51	51	51	32	32	32
20	L 18 W	70	117	222	70	117	117	222	222	222	117	117	117
	L 36 W	70	117	125	64	64	64	125	125	125	64	64	64
	L 58 W	64	64	64	40	40	40	64	64	64	40	40	40
25	L 18 W	85	157	277	85	147	147	277	277	277	147	147	147
	L 36 W	85	156	156	80	80	80	156	156	156	80	80	80
	L 58 W	80	80	80	51	51	51	80	80	80	51	51	51
32	L 18 W	100	144	355	100	144	188	355	355	355	188	188	188
	L 36 W	100	144	200	100	103	103	200	200	200	103	103	103
	L 58 W	100	103	103	65	65	65	103	103	103	65	65	65
40	L 18 W	126	216	444	126	216	235	444	444	444	235	235	235
	L 36 W	126	216	250	126	129	129	250	250	250	129	129	129
	L 58 W	126	129	129	81	81	81	129	129	129	81	81	81
50	L 18 W	180	247	555	180	247	294	555	555	555	294	294	294
	L 36 W	180	247	312	161	161	161	312	312	312	161	161	161
	L 58 W	161	161	161	102	102	102	161	161	161	102	102	102
63	L 18 W	170	340	567	170	340	370	700	700	700	370	370	370
	L 36 W	170	340	393	170	203	203	393	393	393	203	203	203
	L 58 W	170	203	203	128	128	128	203	203	203	128	128	128

¹⁾ All ECGs are turned on simultaneously.

²⁾ The ECGs are turned on in groups one after the other.

Circuit impedance:

The specified lamp load values apply, taking into account a line impedance of 800 mΩ.

At 400 mΩ, the permissible values are reduced by 10 %.

Reduction factors for miniature circuit breakers for the simultaneously switching on of incandescent lamp load, taking into account the rated current of the miniature circuit breaker and the summated current of the lamps

	Reduction factor	
	Switching with miniature circuit breaker	Switching with separate switch
5SY, 5SP4		
Characteristic A	0.3	0.35
Characteristic B	0.5	0.6
Characteristic C	1	1
Characteristic D	1	1

BETA Protecting Miniature Circuit Breakers

Configuration and dimensioning

Current carrying capacity of miniature circuit breakers with corrected and uncorrected HQ, HQI and NAV lamps (number)

		Lamp power [W]							
		35	70	150	250	400	1000	2000	3500
Lamp current	[A]	0.5	1	1.8	3	3.5	9.5	10.3	18
Corrected lamp current	[A]	0.3	0.5	1	1.5	2	6	5.5	9.8
Inrush peak	[A]	10	18	36	60	70	120	125	220

		Lamp power [W]							
		35	70	150	250	400	1000	2000	3500
5SY4 ...-6, 5SY7 ...-6									
Characteristic B	6	2	1	0	0	0	0	0	0
	10	5	3	1	1	0	0	0	0
	13	7	4	2	1	1	0	0	0
	16	8	5	2	1	1	0	0	0
	20	11	6	3	1	1	1	1	0
	25	13	7	3	2	2	1	1	0
	32	16	8	4	2	2	1	1	0
	40	20	11	5	3	3	1	1	1
	50	28	15	7	4	4	2	2	1
	63	26	14	7	4	3	2	2	1
5SY4 ...-7, 5SY7 ...-7									
Characteristic C	6	6	3	1	1	0	0	0	0
	8	8	4	2	1	1	0	0	0
	10	10	6	3	1	1	0	0	0
	13	13	7	3	2	1	1	1	0
	16	16	9	4	2	2	1	1	0
	20	18	10	5	3	2	1	1	0
	25	25	14	7	4	3	2	1	1
	32	22	12	6	3	3	2	1	1
	40	33	18	9	5	4	2	2	1
	50	38	21	10	6	5	3	3	1
	63	53	29	14	9	7	4	4	2
5SY4 ...-8, 5SY7 ...-8									
Characteristic D	6	8	4	2	1	1	0	0	0
	8	11	5	3	2	1	0	0	0
	10	14	7	4	2	2	0	0	0
	13	18	9	5	3	2	1	1	0
	16	22	11	6	3	3	1	1	0
	20	28	14	7	4	4	1	1	0
	25	35	17	9	5	5	2	1	1
	32	44	22	12	7	6	2	2	1
	40	56	28	15	9	8	3	2	1
	50	70	35	19	11	10	4	3	2
	63	88	44	24	14	12	4	4	2
5SP4 ...-7									
Characteristic C	80	76	42	21	12	11	6	6/5	3
	100	98	54	27	16	14	8/7	8/6	4
	125	116	64	32	19	16	9	9/8	5
5SP4 ...-8									
Characteristic D	80	143/112	80/56	40/31	24/18	20/16	9/6	10/5	5/3
	100	186/140	103/70	51/39	31/23	26/20	11/7	12/6	7/4

Different data for corrected/uncorrected lamps.

BETA Protecting Miniature Circuit Breakers


Configuration and dimensioning

Direct current, universal current


All 5SY and 5SP4 miniature circuit breakers are suitable for use in direct current systems up to 60 V¹⁾ (1-pole) or 120 V (2-pole – series connection of two poles). The infeed can be from either the top or the bottom.

For higher voltages, you will require UC (UC = Universal Current) miniature circuit breakers from the 5SY5 and 5SP5 series, which can be used for both AC and DC applications.


The maximum voltage for DC per pole is 250 V. The series connection of individual poles enables 4-pole devices (for example) to be used up to a maximum of 1000 V DC.




Miniature circuit breaker for single-pole tripping
Grounded system (left: - pole grounded, right: + pole grounded)
Rated voltage of miniature circuit breaker: 220 V




Miniature circuit breaker, two-pole for single-pole tripping
Grounded system (left: - pole grounded and bottom infeed, right: + pole grounded and top infeed)
Rated voltage of miniature circuit breaker: 440 V




Miniature circuit breaker, four-pole for single-pole tripping
Non-grounded system (bottom infeed)
Rated voltage of miniature circuit breaker: 880 V



Miniature circuit breaker, two-pole for two-pole tripping
Non-grounded system (left: bottom infeed, right: top infeed)
Rated voltage of miniature circuit breaker: 220 V



Miniature circuit breaker, two-pole for single-pole tripping
Non-grounded system (left: bottom infeed, right: top infeed)
Rated voltage of miniature circuit breaker: 440 V



Miniature circuit breaker, four-pole for two-pole tripping
Non-grounded system (bottom infeed)
Rated voltage of miniature circuit breaker: 880 V

L: Load (e. g. inverter)

SV: Power supply (e. g. solar module or battery)

¹⁾ The operational voltage 60 V DC/pole takes into account a battery charging voltage with a peak value of 72 V.

BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

Overview

UL standards are used in North America, but also in several other countries. This is of particular importance to European exporters of electrical switchgear equipment for machines who export to the USA, as their products will only be accepted if they meet the relevant UL standards.

A wide range of low-voltage circuit protection devices from Siemens comply with UL standards and are therefore suitable for implementation worldwide in both IEC/EN and UL applications within the framework of their specified use.

Miniature circuit breakers certified to UL 489 permit use as an all-round solution for protection tasks in distribution boards, control cabinets and control systems to UL 508A as "branch protectors". In particular, they are also approved for the protection of electrical circuits in heating, ventilating and cooling systems (HVAC), as well as for DC applications up to 60 V/125 V.

This covers a wide range of protection tasks, in residential and non-residential buildings, as well as in industry. The tripping characteristics B, C and D to EN/IEC 60898 have been adapted so that they fall in the permissible tripping range according to UL 489, as well as for applications at 25 °C and 40 °C.

This means that the devices are approved for use according to both standards. The enclosure dimensions of the devices correspond to DIN format. This means that the device series are suitable for universal use worldwide to IEC or UL standards.

The key difference between the three device series is their application in different power supply systems.

- 5SJ4 ...-HG40: 240/120 V AC, 1-pole, "same polarity only",
- 5SJ4 ...-HG41: 240 V AC, 1-, 2- and 3-pole,
- 5SJ4 ...-HG42: 480Y/277 V AC, 1-, 2- and 3-pole.

The terminals are suitable for "field wiring". This means that the devices can be installed not only in factory-finished distribution boards and control cabinets, but also on-site in a customer system.

The Siemens mounting concept supports the combination of all 5ST3 ...-HG additional components with 5SJ4 ...-HG miniature circuit breakers. The auxiliary switch (AS) signals the contact position. In the event of a fault, the fault signal contact (FC) signals the automatic tripping of the MCB as well as the contact position. Shunt trip (unit(s) are used for the remote tripping of miniature circuit breakers. Captive metal brackets on the additional components ensure fast mounting on the devices.

Single, two and three-phase busbars in 3 lengths with 6, 12 or 18 pins are available as accessories for all device series. The in-feed is over connection terminals, which are available in two versions, for direct infeed at either the busbar or the miniature circuit breakers. Pins that are not required can be covered with touch protection covers.

Benefits

- Can be used globally for all applications in residential, non-residential and industrial buildings. This facilitates the planning of plants and enhances export opportunities.
- The devices can be used according to IEC/EN 60898 and UL 489, which means these devices can be installed anywhere in the world.
- Miniature circuit breakers with 480Y/277 V up to 40 A, with 240/120 V and 240 V up to 63 A
- Can be used for both AC voltage and DC voltage up to 125 V
- Rated switching capacity up to 14 kA in acc with UL 489 and up to 15 kA in acc. with IEC 60947-2
- Fast mounting with busbars up to 115 A and feeder terminals up to 50 mm².



- Infeed direct at miniature circuit breaker for conductor cross-sections up to 35 mm².



- Busbar mounting with central infeed directly on the busbar up to conductor cross-section of 50 mm².



- Accessories: Auxiliary switches, fault signal contacts and shunt trips up to 480 V can be easily mounted onto the miniature circuit breaker.

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

Technical specifications

			5SJ4...-HG40	5SJ4...-HG41	5SJ4...-HG42
Standards			EN 60898; EN 60947-2; UL 489; UL-File E243414, CSA C22.2 No. 5-02		
Approvals			See page 1/4		
Tripping characteristic			B, C, D	C, D	
Operational voltage	Min.	V AC/DC	24		
	Max.	V	60		
		DC/pole			
	Max.	V AC	440		
• Acc. to IEC 60898	Max.	V AC	240/120	240	480/277
		V DC/1P	60	60	60
		V DC/2P	--	125	125
Rated breaking capacity					
• I_{cn} acc. to IEC 60898-1 • I_{cn} acc. to IEC 60947-2 • Acc. to UL 489 and CSA C22.2 No. 5-02		kA AC	10		
		kA AC	15		
		kA AC	14/10 ¹⁾	14/10 ¹⁾	10 ¹⁾
Insulation coordination					
• Rated insulation voltage • Degree of pollution for overvoltage category		V AC	250 3/III	250/440	
Touch protection according to EN 50274			Yes		
Handle end position, sealable			Yes		
Degree of protection to EN 60529			IP20, with connected conductors		
CFC and silicone-free			Yes		
Mounting			On standard mounting rail		
Terminals					
• Combined terminals at both ends • Terminal tightening torque for Cu, 60/75 °C			Yes		
		Nm	3.5		
		lb. in	31		
Conductor cross-sections					
• Solid and stranded, acc. to UL 489 and CSA C22.2 No. 5-02 • Solid and stranded, acc. to IEC 60898-1 • Finely stranded, with end sleeve		AWG	14 ... 4		
		mm ²	0.75 ... 35		
		mm2	0.75 ... 25		
Mains connection			Any		
Mounting position			Any		
Average service life, with rated load			20 000 actuations		
Ambient temperature			°C	-25 ... +45, occasionally +55, max. 95 % humidity, storage temperature: -40 ... +75	
Resistance to climate acc. to IEC 60068-2-30			6 cycles		
Resistance to vibrations acc. to IEC 60068-2-6			m/s ²	60 at 10 ... 150 Hz	

¹⁾ For detailed information on rated switching capacity, see page 1/96.

Additional components		Auxiliary switches (AS)		Fault signal contacts (FC)		Shunt trips (ST)		
		5ST3 010-0HG 5ST3 011-0HG 5ST3 012-0HG		5ST3 020-0HG 5ST3 021-0HG 5ST3 022-0HG		5ST3 030-0HG	5ST3 031-0HG	
Standards		UL 489, UL-File E243414, CSA 22.2 No. 5-02 IEC/EN 62019, IEC/EN 60947-5-1IEC/EN 60947-1						
Operational voltage/operational current (load)								
• Acc. to IEC	V AC	400	230			110 ... 415	24 ... 60	
	A AC	2	6 (NC: AC13, NO: AC14)			--	--	
	V DC	220	110	60	24	--	24 ... 60	
	A DC	1	1	3	6 (DC13)	--	--	
• Acc. to UL	V AC	480	277	240	120	110 ... 480	24 ... 60	
	A AC	1.5	3	4	6	--	--	
	V DC	125	60				--	24 ... 60
	A DC	1	3				--	--
Short-circuit protection		Miniature circuit breaker or 6 A fuse						
Minimum contact load		50 mA, 24 V						
Tripping operations		--		--		max. 2000		
Average service life, with rated load		6000		6000		6000		
Operating range		x U _n	--		0.7 ... 1.1			
Conductor cross-sections		AWG mm ²	22 ... 14 0.5 ... 2.5		22 ... 14 0.5 ... 2.5			
Terminals								
• Terminal tightening torque	Nm	Max 0.5				Max 0.8		
	lb/in.	4.5				6.8		

BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

Version Type		Busbars 5ST3 663-.HG 5ST3 664-.HG 5ST3 665-.HG	Terminals 5ST3 666-0HG	5ST3 666-2HG
Standards		UL 489; UL File Nr. E243414		
Operational voltage • Acc. to IEC • Acc. to UL 489	V AC V AC	690 480Y/277 and 240		
Rated conditional short-circuit current • Dielectric strength • Surge strength	kA kV/mm kV	15 kA (with NH3 355A gL/gG 500V) 30 > 9.5		
Rated current at 40 °C ambient temperature	A	115		
Insulation coordination • Degree of pollution • Overvoltage category		2 III		
Busbar cross-section (Cu)	mm ²	16		
Infeed		Any		
Conductor cross-sections • AWG cables • Solid and stranded	AWG mm ²	-- --	14 ... 2 1.5 ... 35	14 ... 1 1.5 ... 50
Terminals • Terminal tightening torque	Nm lb. in	-- --	3.3 30	3.3 30
Temperature resistance	°C	200 – UL 94-V0/0.4 mm		

Selection and ordering data

I_n	Mounting width	DT	Characteristic B		PU	PS*/ P. unit	PG	Weight per PU approx
			Order No.	Price per PU				
A	MW ¹⁾				Unit(s)	Unit(s)		kg
Miniature circuit breakers "same polarity only" 1P, 240 V AC								
6	1	B	5SJ4 106-6HG40		1	1	012	0.120
10		B	5SJ4 110-6HG40		1	1	012	0.120
13		C	5SJ4 113-6HG40		1	1	012	0.120
15		C	5SJ4 118-6HG40		1	1	012	0.120
16		C	5SJ4 116-6HG40		1	1	012	0.120
20		C	5SJ4 120-6HG40		1	1	012	0.120
25		C	5SJ4 125-6HG40		1	1	012	0.120
30		C	5SJ4 130-6HG40		1	1	012	0.120
32		C	5SJ4 132-6HG40		1	1	012	0.120
35		C	5SJ4 135-6HG40		1	1	012	0.120
40		C	5SJ4 140-6HG40		1	1	012	0.120
45		C	5SJ4 145-6HG40		1	1	012	0.120
50		C	5SJ4 150-6HG40		1	1	012	0.120
60		C	5SJ4 160-6HG40		1	1	012	0.120
63		C	5SJ4 163-6HG40		1	1	012	0.120

¹⁾ 1 MW (modular width) = 18 mm.



BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

	I_n	Mount- ing width	DT	Characteristic C		PG	DT	Characteristic D		PU	PS*/ P. unit	PG	Weight per PU approx
	A	MW ¹⁾		Order No.	Price per PU			Order No.	Price per PU				
										Unit(s)	Unit(s)		kg
	Miniature circuit breakers "same polarity only" 1P, 240 V AC												
	0.3	1	C	5SJ4 114-7HG40		012	C	5SJ4 114-8HG40		1	1	012	0.120
	0.5		C	5SJ4 105-7HG40		012	C	5SJ4 105-8HG40		1	1	012	0.120
	1		B	5SJ4 101-7HG40		012	C	5SJ4 101-8HG40		1	1	012	0.120
	1.6		C	5SJ4 115-7HG40		012	C	5SJ4 115-8HG40		1	1	012	0.120
	2		B	5SJ4 102-7HG40		012	C	5SJ4 102-8HG40		1	1	012	0.120
	3		B	5SJ4 103-7HG40		012	C	5SJ4 103-8HG40		1	1	012	0.120
	4		B	5SJ4 104-7HG40		012	C	5SJ4 104-8HG40		1	1	012	0.120
	5		C	5SJ4 111-7HG40		012	C	5SJ4 111-8HG40		1	1	012	0.120
	6		B	5SJ4 106-7HG40		012	C	5SJ4 106-8HG40		1	1	012	0.120
	8		B	5SJ4 108-7HG40		012	C	5SJ4 108-8HG40		1	1	012	0.120
	10		B	5SJ4 110-7HG40		012	C	5SJ4 110-8HG40		1	1	012	0.120
	13		C	5SJ4 113-7HG40		012	C	5SJ4 113-8HG40		1	1	012	0.120
	15		C	5SJ4 118-7HG40		012	C	5SJ4 118-8HG40		1	1	012	0.120
	16		B	5SJ4 116-7HG40		012	C	5SJ4 116-8HG40		1	1	012	0.120
	20		B	5SJ4 120-7HG40		012	C	5SJ4 120-8HG40		1	1	012	0.120
	25		B	5SJ4 125-7HG40		012	C	5SJ4 125-8HG40		1	1	012	0.120
	30		C	5SJ4 130-7HG40		012	C	5SJ4 130-8HG40		1	1	012	0.120
	32		C	5SJ4 132-7HG40		012	C	5SJ4 132-8HG40		1	1	012	0.120
	35		C	5SJ4 135-7HG40		012	C	5SJ4 135-8HG40		1	1	012	0.120
	40		C	5SJ4 140-7HG40		012	C	5SJ4 140-8HG40		1	1	012	0.120
	45		C	5SJ4 145-7HG40		012	C	5SJ4 145-8HG40		1	1	012	0.120
	50		C	5SJ4 150-7HG40		012	C	5SJ4 150-8HG40		1	1	012	0.120
	60		C	5SJ4 160-7HG40		012	C	5SJ4 160-8HG40		1	1	012	0.120
	63		C	5SJ4 163-7HG40		012	C	5SJ4 163-8HG40		1	1	012	0.120
	Miniature circuit breakers 1P, 240 V AC												
	0.3	1	C	5SJ4 114-7HG41		012	C	5SJ4 114-8HG41		1	1	012	0.155
	0.5		C	5SJ4 105-7HG41		012	C	5SJ4 105-8HG41		1	1	012	0.155
	1		C	5SJ4 101-7HG41		012	C	5SJ4 101-8HG41		1	1	012	0.155
	1.6		C	5SJ4 115-7HG41		012	C	5SJ4 115-8HG41		1	1	012	0.155
	2		C	5SJ4 102-7HG41		012	C	5SJ4 102-8HG41		1	1	012	0.155
	3		C	5SJ4 103-7HG41		012	C	5SJ4 103-8HG41		1	1	012	0.155
	4		C	5SJ4 104-7HG41		012	C	5SJ4 104-8HG41		1	1	012	0.155
	5		C	5SJ4 111-7HG41		012	C	5SJ4 111-8HG41		1	1	012	0.155
	6		C	5SJ4 106-7HG41		012	C	5SJ4 106-8HG41		1	1	012	0.155
	8		C	5SJ4 108-7HG41		012	C	5SJ4 108-8HG41		1	1	012	0.155
	10		C	5SJ4 110-7HG41		012	C	5SJ4 110-8HG41		1	1	012	0.155
	13		C	5SJ4 113-7HG41		012	C	5SJ4 113-8HG41		1	1	012	0.155
	15		C	5SJ4 118-7HG41		012	C	5SJ4 118-8HG41		1	1	012	0.155
	16		C	5SJ4 116-7HG41		012	C	5SJ4 116-8HG41		1	1	012	0.155
	20		C	5SJ4 120-7HG41		012	C	5SJ4 120-8HG41		1	1	012	0.155
	25		C	5SJ4 125-7HG41		012	C	5SJ4 125-8HG41		1	1	012	0.155
	30		C	5SJ4 130-7HG41		012	C	5SJ4 130-8HG41		1	1	012	0.155
	32		C	5SJ4 132-7HG41		012	C	5SJ4 132-8HG41		1	1	012	0.155
	35		C	5SJ4 135-7HG41		012	C	5SJ4 135-8HG41		1	1	012	0.155
	40		C	5SJ4 140-7HG41		012	C	5SJ4 140-8HG41		1	1	012	0.155
	45		C	5SJ4 145-7HG41		012	C	5SJ4 145-8HG41		1	1	012	0.155
	50		C	5SJ4 150-7HG41		012	C	5SJ4 150-8HG41		1	1	012	0.155
	60		C	5SJ4 160-7HG41		012	C	5SJ4 160-8HG41		1	1	012	0.155
	63		C	5SJ4 163-7HG41		012	C	5SJ4 163-8HG41		1	1	012	0.155

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

	I_n	Mount- ing width	DT	Characteristic C			Characteristic D			PU	PS*/ P. unit	PG	Weight per PU approx
	A	MW ¹⁾		Order No.	Price per PU	PG DT	Order No.	Price per PU		Unit(s)	Unit(s)		kg
Miniature circuit breakers 2P, 240 V AC													
	0.3	2	C	5SJ4 214-7HG41		012 C	5SJ4 214-8HG41			1	1	012	0.310
	0.5		C	5SJ4 205-7HG41		012 C	5SJ4 205-8HG41			1	1	012	0.310
	1		C	5SJ4 201-7HG41		012 C	5SJ4 201-8HG41			1	1	012	0.310
	1.6		C	5SJ4 215-7HG41		012 C	5SJ4 215-8HG41			1	1	012	0.310
	2		C	5SJ4 202-7HG41		012 C	5SJ4 202-8HG41			1	1	012	0.310
	3		C	5SJ4 203-7HG41		012 C	5SJ4 203-8HG41			1	1	012	0.310
	4		C	5SJ4 204-7HG41		012 C	5SJ4 204-8HG41			1	1	012	0.310
	5		C	5SJ4 211-7HG41		012 C	5SJ4 211-8HG41			1	1	012	0.310
	6		C	5SJ4 206-7HG41		012 C	5SJ4 206-8HG41			1	1	012	0.310
	8		C	5SJ4 208-7HG41		012 C	5SJ4 208-8HG41			1	1	012	0.310
	10		C	5SJ4 210-7HG41		012 C	5SJ4 210-8HG41			1	1	012	0.310
	13		C	5SJ4 213-7HG41		012 C	5SJ4 213-8HG41			1	1	012	0.310
	15		C	5SJ4 218-7HG41		012 C	5SJ4 218-8HG41			1	1	012	0.310
	16		C	5SJ4 216-7HG41		012 C	5SJ4 216-8HG41			1	1	012	0.310
	20		C	5SJ4 220-7HG41		012 C	5SJ4 220-8HG41			1	1	012	0.310
	25		C	5SJ4 225-7HG41		012 C	5SJ4 225-8HG41			1	1	012	0.310
	30		C	5SJ4 230-7HG41		012 C	5SJ4 230-8HG41			1	1	012	0.310
	32		C	5SJ4 232-7HG41		012 C	5SJ4 232-8HG41			1	1	012	0.310
	35		C	5SJ4 235-7HG41		012 C	5SJ4 235-8HG41			1	1	012	0.310
	40		C	5SJ4 240-7HG41		012 C	5SJ4 240-8HG41			1	1	012	0.310
	45		C	5SJ4 245-7HG41		012 C	5SJ4 245-8HG41			1	1	012	0.310
	50		C	5SJ4 250-7HG41		012 C	5SJ4 250-8HG41			1	1	012	0.310
	60		C	5SJ4 260-7HG41		012 C	5SJ4 260-8HG41			1	1	012	0.310
	63		C	5SJ4 263-7HG41		012 C	5SJ4 263-8HG41			1	1	012	0.310
Miniature circuit breakers 3P, 240 V AC													
	0.3	3	C	5SJ4 314-7HG41		012 C	5SJ4 314-8HG41			1	1	012	0.465
	0.5		C	5SJ4 305-7HG41		012 C	5SJ4 305-8HG41			1	1	012	0.465
	1		C	5SJ4 301-7HG41		012 C	5SJ4 301-8HG41			1	1	012	0.465
	1.6		C	5SJ4 315-7HG41		012 C	5SJ4 315-8HG41			1	1	012	0.465
	2		C	5SJ4 302-7HG41		012 C	5SJ4 302-8HG41			1	1	012	0.465
	3		C	5SJ4 303-7HG41		012 C	5SJ4 303-8HG41			1	1	012	0.465
	4		C	5SJ4 304-7HG41		012 C	5SJ4 304-8HG41			1	1	012	0.465
	5		C	5SJ4 311-7HG41		012 C	5SJ4 311-8HG41			1	1	012	0.465
	6		C	5SJ4 306-7HG41		012 C	5SJ4 306-8HG41			1	1	012	0.465
	8		C	5SJ4 308-7HG41		012 C	5SJ4 308-8HG41			1	1	012	0.465
	10		C	5SJ4 310-7HG41		012 C	5SJ4 310-8HG41			1	1	012	0.465
	13		C	5SJ4 313-7HG41		012 C	5SJ4 313-8HG41			1	1	012	0.465
	15		C	5SJ4 318-7HG41		012 C	5SJ4 318-8HG41			1	1	012	0.465
	16		C	5SJ4 316-7HG41		012 C	5SJ4 316-8HG41			1	1	012	0.465
	20		C	5SJ4 320-7HG41		012 C	5SJ4 320-8HG41			1	1	012	0.465
	25		C	5SJ4 325-7HG41		012 C	5SJ4 325-8HG41			1	1	012	0.465
	30		C	5SJ4 330-7HG41		012 C	5SJ4 330-8HG41			1	1	012	0.465
	32		C	5SJ4 332-7HG41		012 C	5SJ4 332-8HG41			1	1	012	0.465
	35		C	5SJ4 335-7HG41		012 C	5SJ4 335-8HG41			1	1	012	0.465
	40		C	5SJ4 340-7HG41		012 C	5SJ4 340-8HG41			1	1	012	0.465
	45		C	5SJ4 345-7HG41		012 C	5SJ4 345-8HG41			1	1	012	0.465
	50		C	5SJ4 350-7HG41		012 C	5SJ4 350-8HG41			1	1	012	0.465
	60		C	5SJ4 360-7HG41		012 C	5SJ4 360-8HG41			1	1	012	0.465
	63		C	5SJ4 363-7HG41		012 C	5SJ4 363-8HG41			1	1	012	0.465

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

	I_n	Mount- ing width	DT	Characteristic C			PG	DT	Characteristic D		PU	PS*/ P. unit	PG	Weight per PU approx
	Order No.			Price per PU	Order No.	Price per PU								
	A	MW ¹⁾	Unit(s)	Unit(s)	kg									
	Miniature circuit breakers 1P, 480Y/277 V AC													
	0.3	1	C	5SJ4 114-7HG42		012	C	5SJ4 114-8HG42		1	1	012	0.155	
	0.5		C	5SJ4 105-7HG42		012	C	5SJ4 105-8HG42		1	1	012	0.155	
	1		C	5SJ4 101-7HG42		012	C	5SJ4 101-8HG42		1	1	012	0.155	
	1.6		C	5SJ4 115-7HG42		012	C	5SJ4 115-8HG42		1	1	012	0.155	
	2		C	5SJ4 102-7HG42		012	C	5SJ4 102-8HG42		1	1	012	0.155	
	3		C	5SJ4 103-7HG42		012	C	5SJ4 103-8HG42		1	1	012	0.155	
	4		C	5SJ4 104-7HG42		012	C	5SJ4 104-8HG42		1	1	012	0.155	
	5		C	5SJ4 111-7HG42		012	C	5SJ4 111-8HG42		1	1	012	0.155	
	6		C	5SJ4 106-7HG42		012	C	5SJ4 106-8HG42		1	1	012	0.155	
	8		C	5SJ4 108-7HG42		012	C	5SJ4 108-8HG42		1	1	012	0.155	
	10		C	5SJ4 110-7HG42		012	C	5SJ4 110-8HG42		1	1	012	0.155	
	13		C	5SJ4 113-7HG42		012	C	5SJ4 113-8HG42		1	1	012	0.155	
	15		C	5SJ4 118-7HG42		012	C	5SJ4 118-8HG42		1	1	012	0.155	
	16		C	5SJ4 116-7HG42		012	C	5SJ4 116-8HG42		1	1	012	0.155	
	20		C	5SJ4 120-7HG42		012	C	5SJ4 120-8HG42		1	1	012	0.155	
	25		C	5SJ4 125-7HG42		012	C	5SJ4 125-8HG42		1	1	012	0.155	
	30		C	5SJ4 130-7HG42		012	C	5SJ4 130-8HG42		1	1	012	0.155	
32		C	5SJ4 132-7HG42		012	C	5SJ4 132-8HG42		1	1	012	0.155		
35		C	5SJ4 135-7HG42		012		--		1	1		0.155		
40		C	5SJ4 140-7HG42		012		--		1	1		0.155		
	Miniature circuit breakers 2P, 480Y/277 V AC													
	0.3	2	C	5SJ4 214-7HG42		012	C	5SJ4 214-8HG42		1	1	012	0.310	
	0.5		C	5SJ4 205-7HG42		012	C	5SJ4 205-8HG42		1	1	012	0.310	
	1		C	5SJ4 201-7HG42		012	C	5SJ4 201-8HG42		1	1	012	0.310	
	1.6		C	5SJ4 215-7HG42		012	C	5SJ4 215-8HG42		1	1	012	0.310	
	2		C	5SJ4 202-7HG42		012	C	5SJ4 202-8HG42		1	1	012	0.310	
	3		C	5SJ4 203-7HG42		012	C	5SJ4 203-8HG42		1	1	012	0.310	
	4		C	5SJ4 204-7HG42		012	C	5SJ4 204-8HG42		1	1	012	0.310	
	5		C	5SJ4 211-7HG42		012	C	5SJ4 211-8HG42		1	1	012	0.310	
	6		C	5SJ4 206-7HG42		012	C	5SJ4 206-8HG42		1	1	012	0.310	
	8		C	5SJ4 208-7HG42		012	C	5SJ4 208-8HG42		1	1	012	0.310	
	10		C	5SJ4 210-7HG42		012	C	5SJ4 210-8HG42		1	1	012	0.310	
	13		C	5SJ4 213-7HG42		012	C	5SJ4 213-8HG42		1	1	012	0.310	
	15		C	5SJ4 218-7HG42		012	C	5SJ4 218-8HG42		1	1	012	0.310	
	16		C	5SJ4 216-7HG42		012	C	5SJ4 216-8HG42		1	1	012	0.310	
	20		C	5SJ4 220-7HG42		012	C	5SJ4 220-8HG42		1	1	012	0.310	
	25		C	5SJ4 225-7HG42		012	C	5SJ4 225-8HG42		1	1	012	0.310	
	30		C	5SJ4 230-7HG42		012	C	5SJ4 230-8HG42		1	1	012	0.310	
32		C	5SJ4 232-7HG42		012	C	5SJ4 232-8HG42		1	1	012	0.310		
35		C	5SJ4 235-7HG42		012		--		1	1		0.310		
40		C	5SJ4 240-7HG42		012		--		1	1		0.310		

¹⁾ 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

	I_n	Mount- ing width	DT	Characteristic C		PG	DT	Characteristic D		PU	PS*/ P. unit	PG	Weight per PU approx
	A	MW ¹⁾		Order No.	Price per PU			Order No.	Price per PU		Unit(s)	Unit(s)	kg
	Miniature circuit breakers 3P, 480Y/277 V AC												
	0.3	3	C	5SJ4 314-7HG42		012	C	5SJ4 314-8HG42		1	1	012	0.465
	0.5		C	5SJ4 305-7HG42		012	C	5SJ4 305-8HG42		1	1	012	0.465
	1		C	5SJ4 301-7HG42		012	C	5SJ4 301-8HG42		1	1	012	0.465
	1.6		C	5SJ4 315-7HG42		012	C	5SJ4 315-8HG42		1	1	012	0.465
	2		C	5SJ4 302-7HG42		012	C	5SJ4 302-8HG42		1	1	012	0.465
	3		C	5SJ4 303-7HG42		012	C	5SJ4 303-8HG42		1	1	012	0.465
	4		C	5SJ4 304-7HG42		012	C	5SJ4 304-8HG42		1	1	012	0.465
	5		C	5SJ4 311-7HG42		012	C	5SJ4 311-8HG42		1	1	012	0.465
	6		C	5SJ4 306-7HG42		012	C	5SJ4 306-8HG42		1	1	012	0.465
	8		C	5SJ4 308-7HG42		012	C	5SJ4 308-8HG42		1	1	012	0.465
	10		C	5SJ4 310-7HG42		012	C	5SJ4 310-8HG42		1	1	012	0.465
	13		C	5SJ4 313-7HG42		012	C	5SJ4 313-8HG42		1	1	012	0.465
	15		C	5SJ4 318-7HG42		012	C	5SJ4 318-8HG42		1	1	012	0.465
	16		C	5SJ4 316-7HG42		012	C	5SJ4 316-8HG42		1	1	012	0.465
	20		C	5SJ4 320-7HG42		012	C	5SJ4 320-8HG42		1	1	012	0.465
	25		C	5SJ4 325-7HG42		012	C	5SJ4 325-8HG42		1	1	012	0.465
	30		C	5SJ4 330-7HG42		012	C	5SJ4 330-8HG42		1	1	012	0.465
	32		C	5SJ4 332-7HG42		012	C	5SJ4 332-8HG42		1	1	012	0.465
	35		C	5SJ4 335-7HG42		012	--			1	1		0.465
	40		C	5SJ4 340-7HG42		012	--			1	1		0.465


¹⁾ 1 MW (modular width) = 18 mm.

		Mount ing width MW ¹⁾	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg	
	Auxiliary switches (AS) acc. to UL 489		0.5	C	5ST3 010-0HG		1	1	012	0.071
	1 NO + 1 NC						1	1	012	0.050
	2 NO						1	1	012	0.050
		2 NC			C	5ST3 012-0HG		1	1	012
	Fault signal contacts (FC) acc. to UL 489		0.5	C	5ST3 020-0HG		1	1	012	0.050
	1 NO + 1 NC						1	1	012	0.050
	2 NO						1	1	012	0.050
		2 NC			C	5ST3 022-0HG		1	1	012
	Shunt trips (ST) acc. to UL 489		1	▶	5ST3 030-0HG		1	1	012	0.098
	110 ... 480 V AC						1	1	012	0.098
		24 ... 60 V AC/DC			▶	5ST3 031-0HG				

¹⁾ 1 MW (modular width) = 18 mm.

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

Accessories

	Pin spacing	Length	DT	Order No.	Price per PU	PU	PS*/ P. unit	PG	Weight per PU approx
	MW ¹⁾	mm				Unit(s)	Unit(s)		kg
	Busbars according to UL 489 specially for 5SJ4 ...-HG.. miniature circuit breakers Fixed lengths, cannot be cut²⁾ UL-File E321559								
	Single-phase								
	For 6 MCB 1P	1	100	A	5ST3 663-0HG	1	10	012	0.056
	For 12 MCB 1P		205	A	5ST3 663-1HG	1	10	012	0.112
	For 18 MCB 1P		310	A	5ST3 663-2HG	1	10	012	0.170
	Two-phase								
	For 3 MCB 2P	1	100	A	5ST3 664-0HG	1	10	012	0.065
	For 6 MCB 2P		205	A	5ST3 664-1HG	1	10	012	0.137
	For 9 MCB 2P		310	A	5ST3 664-2HG	1	10	012	0.211
	Three-phase								
 	Terminals according to UL 489 Specially for 5SJ4 ...-HG.. miniature circuit breakers								
	Infeed at the miniature circuit breaker								
	Max. 35 mm ²		A	5ST3 666-0HG		1	10	012	0.033
	Infeed at the busbar								
	Max. 50 mm ²		A	5ST3 666-2HG		1	10	012	0.034
	Touch protection covers For busbars acc. to UL 489								
	3 x 1 pin		A	5ST3 666-1HG		1	10	012	0.003
	Handle locking devices acc. to UL, UL-File E321559								
	Can be sealed against unwanted manual ON/OFF switching, for padlock With max. 3 mm shackle		A	5ST3 801		1	1	027	0.008
	Padlocks								
	For 5ST3 801 handle locking device		▶	5ST3 802		1	1	027	0.027

¹⁾ 1 MW (modular width) = 18 mm.


²⁾ All unused pins on the busbars must be covered with a 5ST3 666-1HG touch protection cover.

BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories


Characteristic curves

Tripping characteristics acc. to IEC/EN 60898 and UL 489/CSA 22.2 No. 5-02




Tripping characteristic B

MCBs with this tripping characteristic are designed for universal use in socket outlet and lighting circuits. Proof of personal safety acc. to DIN VDE 0100-410 is not required.



Tripping characteristic D

For electrical circuits with strong pulse-generating equipment, such as transformers or solenoid valves.




Tripping characteristic C

Primarily used in lamp and motor circuits with higher starting currents.

Correction factors for rated current at different ambient temperatures

Dependence of permissible continuous load on ambient temperature



BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

Correction factor for 5SJ4 ...-HG miniature circuit breakers
(for curves, please refer to the diagram on page 1/92)

Rated current (A)	0.3	0.5	1	1.6	2	3	4	5	6	8	10	13	15	16	20	25	30	32	35	40	45	50	60	63
Number of poles	Applicable curve for correction factor for 5SJ4 ...-HG miniature circuit breakers																							
1	4	4	4	4	3	3	2	2	2	2	3	3	3	3	3	3	3	3	3	3	2	2	3	2
2	4	4	3	3	3	3	2	2	2	2	3	3	3	2	2	2	2	2	2	2	1	2	2	1
3	4	4	3	3	3	3	2	2	2	2	3	3	3	2	2	2	2	2	2	2	1	1	1	1

Current carrying capacity for ambient temperatures other than 40 °C

For ambient temperatures other than 40 °C, please refer to the following table for the current carrying capacity of the 5SJ4 ...-HG miniature circuit breakers.


Rated current I_n (A) at 40 °C		Permissible rated current I_n (A) depending on ambient temperature						
Rated current I_n (A)	Number of poles	15 °C	20 °C	25 °C	30 °C	40 °C	50 °C	55 °C
0.3	1/2/3	0.35	0.34	0.33	0.32	0.30	0.28	0.26
0.5	1/2/3	0.59	0.57	0.55	0.54	0.50	0.46	0.44
1	1	1.2	1.1	1.1	1.1	1.0	0.9	0.9
	2/3	1.1	1.1	1.1	1.1	1.0	0.9	0.9
1.6	1	1.9	1.8	1.8	1.7	1.6	1.5	1.4
	2/3	1.8	1.8	1.7	1.7	1.6	1.5	1.5
2	1/2/3	2.3	2.2	2.2	2.1	2.0	1.9	1.8
3	1/2/3	3.4	3.3	3.3	3.2	3.0	2.8	2.7
4	1/2/3	4.5	4.4	4.3	4.2	4.0	3.8	3.7
5	1/2/3	5.6	5.5	5.3	5.2	5.0	4.8	4.6
6	1/2/3	6.7	6.5	6.4	6.3	6.0	5.7	5.6
8	1/2/3	8.9	8.7	8.6	8.4	8.0	7.6	7.4
10	1/2/3	11.4	11.1	10.8	10.6	10.0	9.4	9.1
13	1/2/3	14.8	14.4	14.1	13.7	13.0	12.2	11.8
15	1/2/3	17.1	16.7	16.3	15.9	15.0	14.1	13.6
16	1	18.2	17.8	17.4	16.9	16.0	15.0	14.5
	2/3	17.8	17.5	17.1	16.7	16.0	15.2	14.8
20	1	22.8	22.2	21.7	21.1	20.0	18.8	18.1
	2/3	22.3	21.8	21.4	20.9	20.0	19.0	18.5
25	1	28.4	27.8	27.1	26.4	25.0	23.5	22.7
	2/3	27.8	27.3	26.7	26.2	25.0	23.8	23.1
30	1	34.1	33.3	32.5	31.7	30.0	28.2	27.2
	2/3	33.4	32.7	32.1	31.4	30.0	28.5	27.8
32	1	36.4	35.6	34.7	33.8	32.0	30.1	29.0
	2/3	35.6	34.9	34.2	33.5	32.0	30.4	29.6
35	1	39.8	38.9	38.0	37.0	35.0	32.9	31.8
	2/3	38.9	38.2	37.4	36.6	35.0	33.3	32.4
40	1	45.5	44.5	43.4	42.3	40.0	37.6	36.3
	2/3	44.5	43.6	42.8	41.9	40.0	38.0	37.0
45	1	50.1	49.1	48.1	47.1	45.0	42.8	41.7
	2/3	49.3	48.5	47.6	46.8	45.0	43.2	42.2
50	1/2	55.6	54.6	53.5	52.3	50.0	47.6	46.3
	3	54.8	53.9	52.9	52.0	50.0	48.0	46.9
60	1	68.3	66.7	65.1	63.4	60.0	56.4	54.4
	2	66.8	65.5	64.1	62.8	60.0	57.1	55.5
	3	65.7	64.6	63.5	62.4	60.0	57.5	56.3
63	1	70.1	68.7	67.3	65.9	63.0	59.9	58.3
	2/3	69.0	67.9	66.7	65.5	63.0	60.4	59.1

BETA Protecting Miniature Circuit Breakers


5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories

Let-through I^2t values 5SJ4 ...-HG


Characteristic B



Characteristic D




Characteristic C




BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories


Dimensional drawings




5SJ4 ...-HG40




5SJ4 ...-HG41




5SJ4 ...-HG42



5ST3 010-0HG 5ST3 011-0HG 5ST3 012-0HG
5ST3 020-0HG 5ST3 021-0HG 5ST3 022-0HG




5ST3 030-0HG
5ST3 031-0HG



5ST3 663-0HG 5ST3 664-0HG 5ST3 665-0HG
5ST3 663-1HG 5ST3 664-1HG 5ST3 665-1HG
5ST3 663-2HG 5ST3 664-2HG 5ST3 665-2HG

Note:

Pin spacing in MW
Dimensions of side views in mm (approx.)




5ST3 666-1HG

Note:


Pin spacing in MW
Dimensions of side views in mm (approx.)

BETA Protecting Miniature Circuit Breakers

5SJ4 ...-HG miniature circuit breakers
acc. to UL 489 and IEC and accessories



5ST3 666-0HG



5ST3 666-2HG

Schematics

Symbols

Miniature circuit breakers



5SJ4 ...-HG
1P




2P




3P


Additional components




Auxiliary switches (AS)
5ST3 010-0HG




5ST3 011-0HG




5ST3 012-0HG




Fault signal contacts (FC)
5ST3 020-0HG



5ST3 021-0HG



5ST3 022-0HG



Shunt trips (ST)
5ST3 030-0HG
5ST3 031-0HG

More information

Rated switching capacity according to UL 489


Designation	Characteristic	Current A	Rated switching capacity (operational voltage 240 V AC) kA AC	Rated switching capacity (operational voltage 480Y/277 V AC) kA AC
5SJ4 ...-HG40	B	6 ... 63	14	--
	C	0.3 ... 40	14	--
	C	45 ... 63	10	--
	D	0.3 ... 20	14	--
	D	25 ... 63	10	--
5SJ4 ...-HG41	C	0.3 ... 40	14	--
	C	45 ... 63	10	--
	D	0.3 ... 20	14	--
	D	25 ... 63	10	--
5SJ4 ...-HG42	C	0.3 ... 40	14	10
	D	0.3 ... 20	14	10
	D	25 ... 32	10	10

Internal resistance and power loss per pole at I_n

Rated current I_n A	Characteristic B		Characteristic C		Characteristic D	
	R_i mΩ	P_V W	R_i mΩ	P_V W	R_i mΩ	P_V W
0.3	--	--	12 900	1.2	12 600	1.1
0.5	--	--	4900	1.2	4600	1.2
1	--	--	1650	1.7	1480	1.5
1.6	--	--	620	1.6	570	1.5
2	--	--	440	1.8	435	1.8
3	--	--	197	1.8	190	1.7
4	--	--	115	1.8	100	1.6
5	--	--	115	2.9	100	2.5
6	85	3.1	74	2.7	73	2.6
8	--	--	40	2.6	39	2.5
10	16.5	1.7	13.5	1.4	11.9	1.2
13	11.7	2.0	10.2	1.7	10.2	1.7
15	8.5	1.9	7.8	1.8	7.7	1.7
16	8.5	2.2	7.8	2.0	7.7	2.0
20	6.7	2.7	5.5	2.2	5.5	2.2
25	4.3	2.7	4.2	2.6	4.2	2.6
30	3.4	3.1	3.5	3.2	3.0	2.7
32	3.4	3.5	3.5	3.6	3.0	3.1
35	2.8	3.4	2.8	3.4	2.7	3.3
40	2.8	4.5	2.8	4.5	2.5	4.0
45	2.8	5.7	2.7	5.5	2.5	5.1
50	2.1	5.3	2.1	5.0	2.0	5.0
60	1.7	6.1	1.7	6.1	1.7	6.1
63	1.7	6.7	1.7	6.7	1.7	6.7

Mounting concept for 5ST3 0...-0HG accessory on 5SJ4 ...-HG miniature circuit breakers

The chart shows which additional components can be mounted on the right.



BETA Protecting Miniature Circuit Breakers

SHU, 5SP3 main miniature circuit breakers

Overview

Selective main miniature circuit breakers are used as circuit breakers at meter panels and provide an optimum solution.

Characteristic E is adapted to the special application requirements for cascade circuits between melting fuses and miniature circuit breakers in distributor circuits.

An integrated adapter enables quick and easy mounting of the devices on 40-mm busbars. The reduced width of 1.5 MW creates lots of additional space in the meter cabinet. The screwless outgoing terminal ensures optimum user-friendliness.

Used in conjunction with the downstream miniature circuit breaker, selective main miniature circuit breakers ensure effective protection and optimum availability of the system.

Benefits

- Quick and easy installation due to direct busbar mounting
- Space saving field installation due to reduced mounting width
- Tool-free connection of meter cable
- Reliable and high selectivity
- Optimum availability of customer system
- Voltage-independent operation of selective main miniature circuit breakers
- Practical locking options
- Excellent current limitation characteristics enhance plant protection, thanks to the selective main miniature circuit breakers supporting downstream miniature circuit breakers.
- High and safe selectivity between sub-distribution and meter panel ensures the continued supply of the unaffected circuits in the event of a fault, thus improving plant availability
- The selective main miniature circuit breaker prevents the affected circuit from being reconnected until the fault is eliminated, thus providing greater operating safety.
- No previous knowledge required for operation of the selective main miniature circuit breakers. This ensures fast and safe disconnection and reconnection of loads.
- Complies with all the requirements of TAB 2007.

Technical specifications

			5SP3 7... 5SP3 7...-1	5SP3 7...-2	5SP3 8...-2
Standards			DIN VDE 0645		E DIN VDE 0641-21
Rated voltage U_n					
• 1-pole • 3 x 1-pole			V AC V AC	230/400 400	-- 400
Operational voltage	Min. Max.	V AC V AC	110 440		
Rated frequency			Hz	50 ... 60	
Rated current I_n			A	16 ... 100	16 ... 63
Rated insulation voltage U_i			V AC	690	
Rated switching capacity I_{cn}			A	25 000	
Insulation coordination					
• Overvoltage category • Degree of pollution				IV 3	
Surge strength U_{imp}			kV	6	
Impact resistance				30 g, at least 3 impacts, impact duration 11 ms	
Resistance to vibrations				2 g, 20 frequency cycles 5 ... 150 ... 15 Hz	
Switching position indication				OFF = green, ON = red	
Main conductor characteristics	Acc. to EN 60204-1			Yes	
Handle end position, sealable				Yes	
Cutoff			ON/OFF	--	Locking slide with lock, additional wire seal, cable ties and Antilux
Device depth			mm	92	
Degree of protection				IP20, with connected conductors	
Mains connection				Any	
Mounting position				Any	
Mounting				On standard mounting rail or interface adapter	Direct tool-free mounting on the busbar system
Average service life, with rated load			Actuations	20 000	
Wire connection				Saddle terminals at both ends	
• Top					Screwless spring terminal for flexible cables, in particular for meter connecting cables acc. to DIN 43870-3
• Bottom					Box terminal, also for infeed of the busbar system, up to 100 A input terminal current

SHU, 5SP3 main miniature circuit breakers

		5SP3 7..., 5SP3 7...-1	5SP3 7...-2	5SP3 8...-2
Conductor cross-sections	• Top and bottom, solid or stranded	mm ²	2.5 ... 70	--
	• Top and bottom, finely stranded	mm ²	2.5 ... 50	--
	• Top, finely stranded	mm ²	--	2.5 ... 16
	• Bottom, solid, stranded and finely stranded, with end sleeve	mm ²	--	2.5 ... 50
Storage temperature	°C	-40 ... +70		
Ambient temperature	°C	-25 ... +55		


Selection and ordering data

I_n	Mount- ing width MW ¹⁾	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
A								
	Main miniature circuit breakers, 1P each 1x L1, L2, L3, packaged as set For direct busbar mounting (spacing 40 mm), no further accessories necessary							
16	3 x 1.5	C	5SP3 716-2		1 set	1 set	005	1.200
20		C	5SP3 720-2		1 set	1 set	005	1.200
25		C	5SP3 725-2		1 set	1 set	005	1.200
35		C	5SP3 735-2		1 set	1 set	005	1.200
40		C	5SP3 740-2		1 set	1 set	005	1.200
50		C	5SP3 750-2		1 set	1 set	005	1.200
63		C	5SP3 763-2		1 set	1 set	005	1.200
	Main miniature circuit breakers, 3 x 1P single-pole switching For direct busbar mounting (spacing 40 mm), no further accessories necessary							
16	4.5	C	5SP3 816-2		1	1	005	1.275
20		C	5SP3 820-2		1	1	005	1.275
25		C	5SP3 825-2		1	1	005	1.200
35		C	5SP3 835-2		1	1	005	1.200
40		C	5SP3 840-2		1	1	005	1.200
50		C	5SP3 850-2		1	1	005	1.200
63		C	5SP3 863-2		1	1	005	1.200
	Main miniature circuit breakers, 1P For mounting on standard mounting rail, busbar (spacing 40 mm, with 5ST1 busbar adapter), or for screw fixing							
16	2	B	5SP3 716		1	1	005	0.550
20		C	5SP3 720		1	1	005	0.550
25		B	5SP3 725		1	1	005	0.550
32		C	5SP3 732		1	1	005	0.550
35		A	5SP3 735		1	1	005	0.550
40		B	5SP3 740		1	1	005	0.550
50		B	5SP3 750		1	1	005	0.550
63		A	5SP3 763		1	1	005	0.550
80		B	5SP3 780		1	1	005	0.550
100		B	5SP3 791		1	1	005	0.550
	Main miniature circuit breakers, 3 x 1P Premounted on 5ST1 324 busbar adapter; can be clipped onto busbars (spacing: 40 mm); including three transparent 5ST1 323 operating protective covers							
80	6	B	5SP3 780-1		1 set	1 set	005	1.700
100		B	5SP3 791-1		1 set	1 set	005	1.700
	Mounting plates For mounting on standard mounting rails acc. to EN 50022 For 1 or 2 standard mounting rails, suitable for universal use, tier spacing 125 mm		B	5ST1 322	1	1	005	0.021

1) 1 MW (modular width) = 18 mm.

BETA Protecting Miniature Circuit Breakers

SHU, 5SP3 main miniature circuit breakers

I_n	DT	Order No.	Price per PU	PU	PS*/P. unit	PG	Weight per PU approx
A				Unit(s)	Unit(s)		kg
		Busbar adapters for 5SP3 7.. und 5SP3 7..-1 Suitable for busbar spacing 40 mm Can be equipped with 3 selective main miniature circuit breakers					
	B	5ST1 328		1	1	005	0.234
		Breaker blocking covers for 5SP3 7.. and 5SP3 7..-1 To prevent manual off-switching					
	D	5ST1 318		1	10	005	0.001
		Operating protective covers, transparent, for 5SP3 7.. and 5SP3 7..-1 Multiple locking options against accidental and deliberate operation • Padlocks • Phillips screwdrivers • Special wrenches (Antilux) • These can be installed by the operator or the power supply company					
	B	5ST1 323		1	3	005	0.012
		Terminal covers for 5SP3 7.. and 5SP3 7..-1 2 units required per contactor Terminal cover in compliance with cladding dimensions acc. to DIN 43880					
	B	5ST1 316		1	6	005	0.001

Configuration


Internal resistance and power loss

- Internal resistance per pole in mΩ cold state
- Power loss per pole in W for rated current

Type	Rated current A	R_i mΩ	P_{max} W
5SP3 7..-2, 5SP3 8..-2	16	15.3	4.5
	20	11.3	6.0
	25	8.7	6.5
	35	4.5	6.9
	40	3.8	6.4
	50	3.5	8.0
	63	2.3	9.7
5SP3 7.., 5SP3 7..-1	16	15.5	5.2
	20	12.5	6.5
	25	7.4	6.5
	32	5.3	7.2
	35	4.0	7.6
	40	4.0	8.0
	50	2.9	9.5
	63	2.0	9.9
	80	1.5	13.5
	100	1.0	14.4

Selectivity

The operating principle of the selective main miniature circuit breaker means that it always operates selectively up to the rated switching capacity of the downstream miniature circuit breaker, e. g. 6000 A or 10 000 A.




In a cascade circuit with melting fuses, selective main miniature circuit breakers and miniature circuit breakers, the following values apply for the melting fuses:

SHU	6000 3	MCB	gG				
A	A		63 A	80 A	100 A	125 A	
35	≤ 6	10	10	10	10	10	
	8 ... 10	7	10	10	10	10	
	13 ... 16	6	9	10	10	10	
	20	5	8	10	10	10	
		4.5	7	10	10	10	
40	≤ 6	10	10	10	10	10	
	8 ... 10	6	10	10	10	10	
	13 ... 16	6	8	10	10	10	
	20	5	7	10	10	10	
	25	4.5	7	10	10	10	
50	≤ 6	10	10	10	10	10	
	8 ... 10	6	10	10	10	10	
	13 ... 16	6	8	10	10	10	
	20	4.5	7	10	10	10	
	25	4.5	6	10	10	10	
63	≤ 6	10	10	10	10	10	
	8 ... 10	5	8	10	10	10	
	13 ... 16	5	7	10	10	10	
	20	4.5	6.5	10	10	10	
	25	4	6	10	10	10	


Characteristic curves

Characteristic E acc. to E DIN VDE 0641-21




Let-through current

5SP3 7...-1, 5SP3 7...-2



5SP3 7...-2, 5SP3 8...-2




BETA Protecting Miniature Circuit Breakers


SHU, 5SP3 main miniature circuit breakers

Let-through I^2t values

5SP3 7...-1, 5SP3 7...-1




5SP3 7...-2, 5SP3 8...-2




SHU, 5SP3 main miniature circuit breakers

Dimensional drawings



5SP3 7...-2
1P


5SP3 8...-2
3 x 1P



5SP3 7..., 5SP3 7...-1

Schematics

Symbols



5SP3 7...
5SP3 7...-1
5SP3 7...-2
1P

5SP3 8...-2
3 x 1P

BETA Protecting Miniature Circuit Breakers

5SK9 circuit breaker terminals

Overview

Circuit breaker terminals are used for short-circuit protection or for protection against overloading and short-circuiting in auxiliary and control circuits after control transformers. All terminals are designed for 2 wires. The terminal block labeling accessories are used for inscription.

Benefits

- Integration of line protection switching function in the terminal technology of control cabinets in compact 12 mm design
- Display of switching position or the "Tripped" state for the fast detection of faults
- Switching/isolating function facilitates fault locating
- Device versions with integral auxiliary switch (AS) signal the contact position
- Device versions with floating through-type connection parallel to the switching contacts facilitate line connection

These devices are listed as "Supplementary Protectors" according to UL 1077 (UL Recognized Components) and CSA 235 (CSA Component Accepted).

Technical specifications

			5SK9 011-1KK2., 5SK9 011-2KK2.	5SK9 011-4KK2., 5SK9 011-6KK2., 5SK9 011-8KK2.
Standards			IEC/EN 60947-2, UL 1077	
Rated operational voltage	Max.	AC	250 V at 50/60 Hz	
		DC	60 V	
Operational voltage	Min.	V AC/DC	24	
Power loss	Max.	W	1	
Rated impulse withstand voltage		kV	4	
Degree of pollution	Acc. to EN 60664-1		3	
Rated current of through-type connection		A	16	
Rated operational current of auxiliary switch		A	1	
Mechanical service life		Actuations	16 000	
Electrical service life , on average, with rated load		Actuations	8000	
Polarity with direct current			Any	
Mounting position			Any	
Resistance to vibrations			10 g at ≤ 70 Hz	
Enclosure			With thermoplastic insulating body Screw connection at both ends for 2 conductors each Enclosed on both sides	
Touch protection	Acc. to EN 50274-1		Yes	
Terminal size		mm ²	1.5	2.5
Terminal tightening torque , recommended		Nm	0.8	
Conductor cross-sections				
• Solid		mm ²	1 or 2 × (0.75 ... 1.5)	
• Finely stranded, with end sleeve		mm ²	1 or 2 × (1 ... 2.5)	
•  AWG 14-12			Yes	--
•  AWG 14			Yes	--
Stripped length		mm	10	

5SK9 circuit breaker terminals


Selection and ordering data

Version	I_n A	DT	Order No.	Price per PU	PU Unit(s)	PS*/ P. unit Unit(s)	PG	Weight per PU approx kg
	Terminal size 1.5 mm²							
	With short-circuit release							
	1	A	5SK9 011-1KK24		1	10	027	0.053
	2	A	5SK9 011-1KK25		1	10	027	0.052
	4	B	5SK9 011-1KK26		1	10	027	0.053
	6	A	5SK9 011-1KK27		1	10	027	0.053
	10	B	5SK9 011-1KK28		1	10	027	0.050
	With overload and short-circuit release							
	1	A	5SK9 011-2KK24		1	10	027	0.053
	2	A	5SK9 011-2KK25		1	10	027	0.052
	4	A	5SK9 011-2KK26		1	10	027	0.053
	6	A	5SK9 011-2KK27		1	10	027	0.053
	10	B	5SK9 011-2KK28		1	10	027	0.050
	Terminal size 2.5 mm²							
	With short-circuit release, auxiliary switch with 1 NO and 1 NC							
	1	B	5SK9 011-6KK24		1	5	027	0.096
	2	B	5SK9 011-6KK25		1	5	027	0.093
	4	B	5SK9 011-6KK26		1	5	027	0.092
	6	B	5SK9 011-6KK27		1	5	027	0.093
	10	B	5SK9 011-6KK28		1	5	027	0.090
	With overload and short-circuit release, auxiliary switch with 1 NC and through-type connection							
	1	B	5SK9 011-4KK24		1	5	027	0.089
	2	A	5SK9 011-4KK25		1	5	027	0.092
	4	A	5SK9 011-4KK26		1	5	027	0.091
	6	B	5SK9 011-4KK27		1	5	027	0.105
	10	B	5SK9 011-4KK28		1	5	027	0.088
	With overload and short-circuit release, auxiliary switch with 1 NO and 1 NC							
	0.5	B	5SK9 011-8KK23		1	5	027	0.092
	1	A	5SK9 011-8KK24		1	5	027	0.092
	2	A	5SK9 011-8KK25		1	5	027	0.097
	4	A	5SK9 011-8KK26		1	5	027	0.092
	6	A	5SK9 011-8KK27		1	5	027	0.090
	10	B	5SK9 011-8KK28		1	5	027	0.090
 5ST1 822-7KK02	Feeder terminals							
	Rated uninterrupted current 76 A Connection up to 16 mm ²							
		A	5ST1 822-7KK00		1	10	027	0.012
	Link rails, single-phase							
	Rated uninterrupted current 65 A							
	5 connections • 104 mm long • For terminals: 5SK9 011-4KK2., 5SK9 011-6KK2., 5SK9 011-8KK2.							
		A	5ST1 822-7KK02		1	20	027	0.015
	9 connections • 104 mm long • For terminals: 5SK9 011-1KK2., 5SK9 011-2KK2.							
		A	5ST1 822-7KK07		1	20	027	0.013
	10 connections • 206 mm long • For terminals: 5SK9 011-4KK2., 5SK9 011-6KK2.							
 5ST1 822-7KK06		A	5ST1 822-7KK01		1	20	027	0.031
	18 connections • 206 mm long • For terminals: 5SK9 011-1KK2., 5SK9 011-2KK2.							
		A	5ST1 822-7KK06		1	20	027	0.036
	Link rails, two-phase							
	Rated uninterrupted current 120 A for terminal 5SK9 011-4KK2.							
	5 connections/pole • 104 mm long							
		A	5ST1 822-7KK04		1	10	027	0.031
	9 connections/pole • 206 mm long							
		A	5ST1 822-7KK03		1	10	027	0.061
	 5ST1 822-7KK04							


BETA Protecting Miniature Circuit Breakers

5SK9 circuit breaker terminals

Characteristic curves




Tripping characteristics of short-circuit releases




Tripping characteristics of combined overload and short-circuit releases at an ambient temperature of 40 °C

Dimensional drawings




5SK9 011-1KK2.
5SK9 011-2KK2.




5SK9 011-4KK2.
5SK9 011-6KK2.
5SK9 011-8KK2.

Schematics


Symbols




5SK9 011-1KK2.




5SK9 011-2KK2.



5SK9 011-6KK2.



5SK9 011-4KK2.



5SK9 011-8KK2.