






Micro LED[®]


Surface Mount LED Selector Guide



A wide spectrum of package sizes, configurations, colors **+More**



Micro LED[®] Surface Mount LEDs



Micro LED[®] Surface Mount LED product line provides one of the industry's widest range of discrete LEDs. Packaged in chipLED, PLCC, right-angle and reverse-mount configurations, the series is available in a full range of colors and intensities, including the latest AlInGaP and InGaN technology. All products are RoHs compliant, and are perfectly suited to be used with Dialight's wide-range of Optopipe[®] 515 Series Light Pipes.

With such a wide variety of mounting styles, colors, intensities, viewing angles and lens features, the Micro LED[®] Surface Mount series is sure to include a cost-effective solution to any application.

Also available from Dialight

Prism[®] Surface Mount Indicators 591–595 Series Single, BiLevel & TriLevel SMDs

Dialight's Prism[®] indicators are the industry's only SMD indicator series designed to survive 260 °C peak reflow temperature *and* provide the aesthetic appeal of a diffused lens for enhanced viewing. Ideal for limited-space applications and board-edge mounting, the Prism[®] Series is available in a variety of package sizes including single level, bi-level, and tri-level configuration and in 1.6mm, 2mm and 3mm lens size. The integral light pipes used in Prism[®] SMD LEDs are engineered for maximum light transmission and minimal light bleed while the diffused lens is also ideal for bicolor and tricolor applications where color-mixing is desired.

Features & Benefits

- Compatible with automatic placement equipment.
- Compatible with surface mount reflow soldering processes.
- Housing meets UL-94V-0 flammability ratings.
- Patented design provides increased indication without increased space.
- Illumination areas compatible with industry standard 2 mm & 3 mm through hole CBIs.
- Packaged in dry packaging moisture barrier bags per IPC/JEDEC J-STD-033.
- Helps to eliminate mixed technology PC board processing.



Contact your Authorized Dialight Distributor or local Sales Representative for more information or samples.
<http://www.dialightsignalsandcomponents.com/WhereToBuy/Optoelectronic>

The following pages are organized as a product overview. Additional information is available at www.dialightsignalsandcomponents.com including detailed specs and schematics, 3D models, and operating characteristics.

MicroLED® SMDs Typical Applications

- Data center Infrastructure
- Servers: Rack mount; blade; tower
- Storage: High-performance storage subsystems for high-end enterprise
- Storage Networking Hardware
- Fiber channel host bus adapter cards (HBAs); converged network adapter cards (CNAs); SCSI adapter cards; InfiniBand adapter cards
- Next-Gen Wireless
- Wireless Infrastructure
- Electronic Test & Measurement Instruments
- Networking Equipment for enterprise data centers and telecom communication centers
- Switches, routers, and network control equipment interconnected using fiber optic and high speed wiring
- Communications Testing Equipment
- Process controls
- Automation
- Medical
- Handheld devices
- Battery powered applications (2mA version)

Products are listed in this guide first by overall package size; then by variable heights from smallest to highest.

Contents

Top View SMDs

0402	4
/ Single Color	
0404	5
/ BiColor & TriColor	
0603	5–9
/ Single Color with Zener Diode / Single Color with binning / BiColor / Single Color with Lens	
0606	10
/ TriColor with Zener Diode / BiColor & TriColor	
0805	11–13
/ Single Color / Single Color with Zener Diode / with Reflector Cup	
Special ChipLED	13
/ TriColor	
1206	14–15
/ Single Color / Single Color with Lens	
1208	15
/ Single Color with Reflector Cup	
1209	16
/ Single Color with Lens	
1210	16–17
/ BiColor & TriColor / BiColor with Reflector Cup	
Mini PLCC-2	17–18
/ Single Color Low Current / Single Color	
PLCC-2	18–19
/ Single Color Low Current / Single Color / 3528 Single Color	
PLCC-4	20–21
/ Single Color High Current / BiColor Low Current / BiColor & TriColor	


Reverse Mount

1206	22
/ Single Color / Single Color with Zener Diode / BiColor	

Right Angle

0603	23
/ Single Color	
0605	23
/ Single Color	
1208	24–27
/ Single Color, BiColor & TriColor	
1616	27
/ Single Color Low Current / Single Color / Single Color	


Top View | 0402



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


0402 Package ▶ 1.0 x 0.6 x 0.2 mm / Single Color

597-3007-507F	● R : 625	630	635	AlInGaP	20	25	60	100	2.0	—	135	-40 to +85	-40 to +100
597-3027-507F	● R : 615	620	625		20	40	85	160	2.0	—			
597-3207-507F	● O : 602	605	608		20	63	100	250	2.1	—			
597-3327-507F	● G : 520	527	535	InGaP	5	56	110	220	3.0	—			
597-3407-507F	● Y : 587	590	593	AlInGaP	20	40	130	160	2.1	—			
597-3507-507F	● YG : 569	572	575		20	10	25	65	2.2	—			
597-3607-507F	● B : 465	470	475	InGaP	5	9	25	56	2.9	—			
597-3907-507F	○ W : X=0.30 / Y=0.30				5	90	150	360	2.9	—			




0402 ▶ 1.0 x 0.5 x 0.4 mm / Single Color

598-8A10-107F	● R : 630	635	640	AlInGaP	5	28	65	100	1.7	2.4	140	-40 to +85	-40 to +85
598-8A20-107F	● R : 620	625	630			28	47	65	1.8	2.4			
598-8A30-107F	● O : 600	605	610			28	47	65	1.8	2.4			
598-8A40-107F	● Y : 587	591	595			18	42	65	1.8	2.4			
598-8A60-107F	● YG : 568	572	575			8	12	18	1.8	2.4			
598-8A80-107F	● G : 525	528	530	InGaP	5	230	330	430	2.5	3.3	140	-40 to +85	-40 to +85
598-8A90-107F	● B : 465	470	475			43	72	100	2.5	3.3			



NOTE: Top View SMDs are shown in the diagrams in top, side and bottom views. The top and bottom diagrams flip across the x-axis.



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			

0404 Package ▶ 1.0 x 1.0 x 0.2 mm / BiColor and TriColor

597-7707-507F	● R : 615	620	625	AlInGaP	20	25	52	100	2.1	—	128	-40 to +85	-40 to +100
	● G : 569	572	575	AlInGaP		10	21	40	2.2	—			

Top

Side

Bottom

Schematic


597-7717-507F	● R : 619	624	629	AlInGaP	5	14	35	56	2.1	—	120	-40 to +85	-40 to +100
	● G : 520	527	535	InGaN		56	110	220	3.1	—			
	● B : 465	470	475	InGaN		28	45	110	3.0	—			

Top

Side

Bottom

Schematic



0603 Package ▶ 1.6 x 0.8 x 0.35 mm / Single Color with Zener

597-3905-607F	○ W : X=0.294 / Y=0.300	InGaN	5	71	—	146	2.7	3.15	130	-20 to +80	-40 to +85
---------------	-------------------------	-------	---	----	---	-----	-----	------	-----	------------	------------


Top

Side

Bottom

Schematic


Top View | 0603





Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			

0603 ▶ 1.6 x 0.8 x 0.55 mm / Single Color

597-3304-607F	● G : -	569	-	GaP	20	2.8	12	28	2.1	2.6	130	-55 to +85	-55 to +85
---------------	---------	-----	---	-----	----	-----	----	----	-----	-----	-----	------------	------------



597-3901-830F	○ W : X=0.31 / Y=0.32	InGaN	10	112	-	240	2.8	3.4			-20 to +80	-55 to +105
---------------	-----------------------	-------	----	-----	---	-----	-----	-----	--	--	------------	-------------





0603 ▶ 1.6 x 0.8 x 0.55 mm / Single Color 1 Bin

597-3005-507F	● R : 627	630	633	AlInGaP	20	71	90	-	2	160	-40 to +100	-40 to +100
597-3035-507F	● R : 617	620	623			90	112	-	2			
597-3045-507F	● R0 : 612	615	618			112	140	-	2			
597-3205-507F	● O : 603	605	607			112	140	-	2			
597-3405-507F	● Y : 588	590	592			180	224	-	2.1			
597-3505-507F	● YG : 569	571	573			56	71	-	2.1			

0603 ▶ 1.6 x 0.8 x 0.55 mm / Single Color 2+ Bin

597-3324-507F	● G : 520	527	535	InGaN	5	56	140	330	3	3.5	160	-40 to +100	-40 to +100
597-3604-507F	● B : -	470	-			14	40	56	2.9	3.3			
597-3904-507F	○ W : X=0.295 / Y=0.280					56	120	220	2.9	3.3			







Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


0603 ▶ 1.6 x 0.8 x 0.7 mm / Single Color

597-5004-407F	● R : 621	626	632	AlInGaP	20	25	50	200	1.9	2.4	152	-40 to +85	-40 to +100
597-5112-407F	● R : -	647	-	AlGaAs		7	11.7	-	1.7	2.3		-30 to +85	
597-5203-407F	● O : -	606	-	GaAsP		2	3.4	-	2.2	2.8		-30 to +85	
597-5213-407F	● O : -	605	-	AlInGaP		25	65	-	1.9	2.4		-40 to +85	
597-5223-407F	● Y : -	590	-	AlInGaP		25	65	-	1.9	2.4		-40 to +85	
597-5312-407NF	● G : 565	567	572	GaP		4.5	-	15.1	2.1	2.8		-40 to +100	
597-5412-407F	● YG : -	572	-	GaP		7	11.7	-	2.1	2.8		-30 to +85	




0603 ▶ 1.6 x 0.8 x 0.7 mm / Single Color

598-8010-107F	● R : 625	633	640	AlInGaP	20	30	60	90	2.1	2.4	140	-40 to +100	-40 to +100
598-8020-107F	● RO : 620	625	630			120	225	330	2.1	2.4			
598-8030-107F	● O : 600	605	610			70	120	200	2.1	2.4			
598-8040-107F	● Y : 590	592	595			120	160	200	2.1	2.4			
598-8050-107F	● Y : 585	587	590			90	105	120	2.1	2.4			
598-8060-107F	● YG : 570	572	575			43	62	80	2.1	2.4			
598-8070-107F	● G : 562	566	570			12	28	43	2.1	2.4			
598-8081-107F	● G : 517	525	530	InGaN	20	260	580	900	3.1	3.4	140	-40 to +100	-40 to +100
598-8091-107F	● B : 465	470	475			90	150	260	3.2	3.5			




Top View | 0603



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			



0603 ▶ 1.6 x 0.8 x 0.7 mm / Single Color

599-0010-007F	● R : 625	633	640	AlInGaP	20	23	45	—	2.1	2.5	140	-40 to +100	-40 to +100
599-0020-007F	● RO : 620	625	630			90	169	—	2.1	2.5			
599-0030-007F	● O : 600	605	610			53	90	—	2.1	2.5			
599-0040-007F	● Y : 585	590	595			68	105	—	2.1	2.5			
599-0060-007F	● YG : 562	569	575			9	43	—	2.1	2.5			
599-0081-007F	● G : 517	525	530	InGaN	20	195	340	—	3.2	3.6	140	-40 to +100	-40 to +100
599-0091-007F	● B : 465	470	475			70	150	260	3.2	3.5			




0603 ▶ 1.6 x 0.8 x 0.7 mm / BiColor

597-7725-607F	G : 564	—	578	AlInGaP	20	18	45	71	1.8	2.4	130	-30 to +85	-40 to +85
	Y : 582	—	596			28	71	112					
597-7726-607F	G : 565	—	577			18	45	71	1.9	2.4			
	R : 626	—	640			28	71	112					



0603 ▶ 1.6 x 0.8 x 0.8 mm / Single Color

597-3326-607F	● G : 520	525	530	InGaN	20	90	150	280	3.4	3.8	-20 to +80	-30 to +100
597-3607-607F	● B : 465	—	475			28	60	—	2.8	3.8		





AlInGaP and GaP LEDs 2 kV HBM • InGaN, AlGaAs and GaAs LEDs 500 V HBM • LEDs with Zener Diodes not LED sensitive



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


0603 ▶ **1.6 x 0.8 x 0.93 mm / Single Color with Lens**

598-8E20-107F	● R0 : 615	625	630	AlInGaP	20	350	500	650	1.6	2.4	60	-40 to +85	-40 to +85	
598-8E30-107F	● O : 600	605	610			430	615	800	1.6	2.4				
598-8E40-107F	● Y : 585	590	595			350	590	650	1.6	2.4				
598-8E60-107F	● YG : 565	570	575			150	340	530	1.8	2.4				
598-8E80-107F	● G : 515	525	535	InGaN		350	775	1200	2.4	3.6				
598-8E90-107F	● B : 460	470	475			350	440	530	2.6	3.8				




0603 ▶ **1.6 x 0.8 x 1.24 mm / Single Color with Lens**

597-3006-507F	● R : 625	630	635	AlInGaP	20	112	174	355	2.0	—	60	-40 to +100	-40 to +100
597-3036-507F	● R : 615	620	625			140	185	450					
597-3206-507F	● O : 600	605	610			224	405	710					
597-3408-507F	● Y : 585	590	595	AlInGaP/ GaAs		180	320	560					
597-3409-507F	● Y : 584	587	590			180	290	560					
597-3506-507F	● YG : 568	571	575	AlInGaP		56	140	180					
597-3316-507F	● G : 557	560	565			14	34	45					





Top View | 0606



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


0606 Package ▶ 1.6 x 1.6 x 0.5 mm / TriColor with Zener Diode

597-7715-607F	● R : 617	—	629	AllInGaP	5	15		50	1.9	2.3	130	-20 to +80	-30 to +85
	● G : 525	—	540	InGaN		71		145	2.9	3.3			
	● B : 465	—	475	InGaN		10		30	2.8	3.1			





0606 ▶ 1.6 x 1.6 x 0.7 mm / BiColor and TriColor

598-8410-207CF	● R : 625	633	640	AllInGaP	20	35	65	100	2.1	2.4	140	-40 to +100	-40 to +100
	● G : 565	570	575	AllInGaP		18	59	80	2.1	2.4			
598-8430-207CF	● O : 600	605	610	AllInGaP		70	135	200	2.1	2.4			
	● G : 565	570	575	AllInGaP		18	59	100	2.1	2.4			
598-8440-207CF	● Y : 585	590	595	AllInGaP		70	135	200	2.1	2.4			
	● YG : 565	570	575	AllInGaP		18	59	100	2.1	2.4			
598-8450-207CF	● Y : 585	590	595	AllInGaP		70	135	200	2.1	2.4			
	● G : 515	523	530	InGaN		260	580	900	3.0	3.4			
598-8460-207CF	● Y : 585	590	595	AllInGaP		90	145	200	2.1	2.4			
	● R : 625	633	640	AllInGaP		30	60	90	2.1	2.4			




598-8710-307F	● R : 625	630	640	AllInGaP	20	35	67	100	2.1	2.4	140	-40 to +100	-40 to +100
	● G : 515	520	525	InGaN		260	580	900	3.2	3.4			
	● B : 465	470	475	InGaN		60	160	260	3.2	3.4			
598-8720-307F	● RO : 620	625	630	AllInGaP		70	135	200	2.1	2.4			
	● G : 515	523	530	InGaN		260	580	900	3.2	3.4			
	● B : 465	470	475	InGaN		90	175	260	3.2	3.4			
598-8740-307F	● Y : 585	590	595	AllInGaP		70	135	200	2.1	2.4			
	● G : 515	523	530	InGaN		200	350	900	3.2	3.4			
	● B : 465	470	475	InGaN		60	260	260	3.2	3.4			



	Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
	Min	Typ	Max			Min	Typ	Max	Typ	Max			
	0805 Package ▶ 2.0 x 1.25 x 0.7 mm / Single Color												
598-8110-107F	● R : 625	633	640	AlInGaP	20	20	55	90	2.1	2.4	140	-40 to +100	-40 to +100
598-8120-107F	● RO : 620	625	630			120	190	260	2.1	2.4			
598-8130-107F	● O : 600	605	610			70	165	260	2.1	2.4			
598-8140-107F	● Y : 590	592	595			150	205	260	2.1	2.4			
598-8150-107F	● Y : 585	587	590			90	120	150	2.1	2.4			
598-8160-107F	● YG : 570	572	575			43	62	80	2.1	2.4			
598-8170-107F	● G : 562	566	570			12	28	43	2.1	2.4			
598-8181-107F	● G : 520	525	530	InGaN	20	260	580	900	3.2	3.6	140	-40 to +100	-40 to +100
598-8191-107F	● B : 465	470	475			90	145	200	3.2	3.6			

599-0110-007F	● R : 625	633	640	AlInGaP	20	15	29	—	2.1	2.5	140	-40 to +100	-40 to +100
599-0120-007F	● RO : 620	625	630			90	138	—	2.1	2.5			
599-0130-007F	● O : 600	605	610			53	95	—	2.1	2.5			
599-0140-007F	● Y : 585	590	595			68	112	—	2.1	2.5			
599-0160-007F	● YG : 562	569	575			9	43	—	2.1	2.5			
599-0181-007F	● G : 520	525	530	InGaN	20	195	340	—	3.2	3.6	140	-40 to +100	-40 to +100
599-0191-007F	● B : 465	470	475			68	105	—	3.2	3.6			



0805 ▶ 2.0 x 1.25 x 0.8 mm / Single Color with Zener													
597-3605-607F	● B : 465	—	480	InGaN	2	4.5	15	18	2.8	3.05	130	-20 to +80	-30 to +100

LED Dice	Zener Diode												
Top	Side	Bottom	Schematic										


Top

Side

Bottom

Schematic


Top View | 0805



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


0805 Package ▶ 2.0 x 1.25 x 0.8 mm / Single Color


597-3003-407F	● R : 620	626	632	AlInGaP	20	68	91	120	1.9	2.4	140	-40 to +100	-40 to +100
597-3212-407NF	● O : 603	605	609			82	110	150	1.9	2.4	140	-40 to +100	-40 to +105
597-3222-407F	● A : 583	590	597			25	65	105	1.9	2.4	150	-40 to +85	-40 to +100
597-5111-407F	● R : 642	647	653	AlGaAs		7.0	11.7	16.4	1.7	2.3			
597-5202-407F	● O : 600	606	612	GaP		2.2	3.7	5.2	2.2	2.8			
597-5311-407F	● G : 562	567	573			3.8	6.4	9.0	2.1	2.8			
597-5411-407F	● YG : 570	572	577			7	11.7	16.4	2.1	2.8			



0805 ▶ 2.0 x 1.25 x 0.8 mm / Single Color with Reflector Cup

597-5006-507F	● R : 625	630	635	AlInGaP	20	40	75	—	2.0	—	116	-40 to +85	-40 to +100
597-5036-507F	● R : 615	620	625			63	120	—	2.0	—			
597-5206-507F	● O : 602	605	608			100	160	—	2.0	—			
597-5316-507F	● G : 557	560	563			6.3	16	—	2.2	—			
597-5326-507F	● G : 519	527	536	InGaN	5	56	140	—	3.0	—		-40 to +100	
597-5406-507F	● Y : 587	590	593	AlInGaP	20	100	160	—	2.0	—		-40 to +85	
597-5506-507F	● YG : 569	572	575			25	45	—	2.2	—			
597-5606-507F	● B : 464	470	476	InGaN	5	14	36	—	2.9	—		-40 to +100	
597-5906-507F	○ W : X=0.30 / Y=0.28					56	140	—	2.9	—			






Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


0805 ▶ 2.0 x 1.25 x 1.1 mm / Single Color

Fwd V @ 20 mA


597-3006-607F	● R : -	630	-	GaP	10	2	6	-	2.0	2.6	130	-55 to +85	-55 to +85
597-3305-607F	● G : -	569	-			2.8	8	-	2.1	2.6			
597-3405-607F	● Y : -	588	-			2	6	-	2.1	2.6			




Top



Side



Bottom




Schematic




Special ChipLED ▶ 2.1 x 1.6 x 0.55 mm / TriColor

Fwd V @ 20 mA


597-7713-607F	● B : 463	-	477	InGaN	10	45	71	112	3.2	3.8	130	-20 to +80	-30 to +100
	● G : 518	-	532	InGaN		112	180	280	3.25	3.8			
	● O : 598	-	612	AlInGaP	20	71	-	180	2.1	2.5			




Top



Side




Bottom



Schematic

Top View | 1206





Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			

1206 Package ▶ 3.2 x 1.6 x 0.7 mm / Single Color


598-8210-107F	● R : 625	633	640	AlInGaP	20	20	55	90	2.1	2.4	140	-40 to +100	-40 to +100
598-8220-107F	● R0 : 620	625	630			70	120	200	2.1	2.4			
598-8230-107F	● O : 600	605	610			90	175	260	2.1	2.4			
598-8240-107F	● Y : 590	592	595			150	205	260	2.1	2.4			
598-8250-107F	● Y : 585	587	590			90	120	150	2.1	2.4			
598-8260-107F	● YG : 570	572	575			43	70	100	2.1	2.4			
598-8270-107F	● G : 562	566	570			18	30	43	2.1	2.4			
598-8281-107F	● G : 517	525	530	InGaN	20	260	580	900	3.2	3.5	140	-40 to +100	-40 to +100
598-8291-107F	● B : 465	470	475			90	175	260	3.2	3.5			

599-0210-007F	● R : 625	633	640	AlInGaP	20	15	29	—	2.1	2.5	140	-40 to +100	-40 to +100
599-0220-007F	● R0 : 620	625	630			53	90	—	2.1	2.5			
599-0230-007F	● O : 600	605	610			68	112	—	2.1	2.5			
599-0240-007F	● Y : 585	587	590			68	126	—	2.1	2.5			
599-0260-007F	● YG : 562	566	570	InGaN	20	14	54	—	2.1	2.5	140	-40 to +100	-40 to +100
599-0281-007F	● G : 517	525	530			195	340	—	3.2	3.6			
599-0291-007F	● B : 465	470	475			68	105	—	3.2	3.6			




1206 ▶ 3.2 x 1.6 x 1.1 mm / Single Color

597-3007-607F	● R : —	621	—	GaP	20	4.0	8	30	2	2.6	130	-55 to +85	-55 to +85
597-3302-607F	● G :	569	—		10	4	8	30	2.1	2.6		-55 to +85	-55 to +85
597-3403-607F	● Y : 585	—	592	GaAsP on GaP	10	4.5	—	18	2.1	2.6		-40 to +85	-40 to +85




AlInGaP and GaP LEDs 2 kV HBM • InGaP, AlGaAs and GaAs LEDs 500 V HBM • LEDs with Zener Diodes not LED sensitive



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


1206 ▶ 3.0 x 1.5 x 1.5 mm / Single Color with Lens

597-3111-407F	● R : 640	647	655	AlGaAs	20	12	33.6	55.2	1.7	2.0	70	-30 to +85	-40 to +100
597-3311-407NF	● G : 560	567	575	GaP		17	30	48	2.1	2.5		-40 to +100	-40 to +120
597-3401-407NF	● Y : 589	592	595	GaAsP		8.3	20	33.6	2.2	2.5		-40 to +100	-40 to +120
597-3325-407F	● G : -	525	-	InGaN	20	150	-	680	3.3	3.8	50	-40 to +100	-40 to +110
597-3612-407F	● B : -	470	-	InGaN		47	-	220	3.3	3.8		-40 to +100	-40 to +110




1208 Package ▶ 3.0 x 2.0 x 1.3 mm / Single Color with Reflector Cup

597-3002-507F	● R : 625	630	635	AllnGaP	20	25	63	160	2.2	2.7	110	-40 to +85	-40 to +100
597-3021-507F	● R : 646	653	659	GaAsP		2.2	6.3	10.4	2	2.8		-30 to +85	-40 to +85
597-3032-507F	● R : 615	620	625	AllnGaP		40	100	250	2.2	2.7		-40 to +85	-40 to +100
597-3111-507F	● R : 656	662	668	AlGaAs		5.6	16	26.4	1.75	2.5		-30 to +85	-40 to +85
597-3202-507F	● O : 602	605	608	AllnGaP		63	160	400	2.2	2.7		-40 to +85	-40 to +100
597-3211-507F	● O : 604	612	618	GaAsP		3.6	10	16.4	2	2.8		-30 to +85	-40 to +85
597-3301-507F	● G : 565	575	581	GaP		5.6	25	44.4	2.2	2.8		-30 to +85	-40 to +85
597-3312-507F	● G : 558	560	564	AllnGaP		9	18	36	2.1	2.5		-40 to +100	-40 to +100
597-3322-507F	● G : 520	525	535	InGaN		56	140	360	3.2	4.0		-30 to +85	-40 to +100
597-3401-507F	● Y : 580	588	596	GaAsP		2.2	6.3	10.4	2.1	2.8		-30 to +85	-40 to +85
597-3402-507F	● Y : 587	590	593	AllnGaP		63	160	400	2.2	2.7		-40 to +85	-40 to +100
597-3502-507F	● YG : 569	572	575	AllnGaP		10	25	63	2.2	2.7		-40 to +85	-40 to +100
597-3602-507F	● B : 465	470	475	InGaN		36	100	—	3.3	4.2		-30 to +85	-40 to +100
597-3902-507F	○ W : X=0.30 / Y=0.30			InGaN		360	900	1400	3.2	4.3		-30 to +85	-40 to +100




Top View | 1209 & 1210




Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			

1209 Package ▶ 3.2 x 2.4 x 2.38 mm / Single Color with Lens


597-3001-607F	● R :	630		AllInGaP	20	710	850	2800	2.0	2.4	25	-55 to +85	-55 to +85
597-3041-607F	● RO :	615		AllInGaP		710	2605	4500	2.0	2.4		-30 to +85	-40 to +85
597-3201-607F	● O : 600	605	610	AllInGaP		450	1200	4500	2.0	2.4		-55 to +85	-55 to +85
597-3321-607F	● G :	525		InGaN		710	2000	4500	2.8	3.6		-20 to +80	-30 to +100
597-3401-607F	● Y : 587	590	595	AllInGaP		450	710	1800	2.0	2.4		-55 to +85	-55 to +85
597-3501-607F	● YG :	570		AllInGaP		180	600	1800	2.0	2.4		-55 to +85	-55 to +85
597-3601-607F	● B : 465	470	475	InGaN		560	1400	2240	3.4	3.8		-20 to +80	-30 to +100




Top




Side



Bottom




Schematic




1210 Package ▶ 3.2 x 2.7 x 0.7 mm / Bicolor


598-8610-207F	● R : 630	635	640	AllInGaP	20	40	65	90	2.1	2.4	140	-40 to +100	-40 to +100
	● G : 565	570	575	AllInGaP		30	40	50					
598-8621-207F	● RO : 620	625	630	AllInGaP		90	120	150	2.1	2.4			
	● G : 520	525	530	InGaN		260	580	900	3.0	3.4			
598-8640-207F	● Y : 585	590	595	AllInGaP		80	155	230	2.1	2.4			
	● G : 565	570	575	AllInGaP		30	40	50					
598-8660-207F	● Y : 585	590	595	AllInGaP		90	145	200	2.1	2.4			
	● R : 630	635	640	AllInGaP		40	65	90					




Top




Side



Bottom




Schematic




Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			

1210 Package ▶ 3.2 x 2.7 x 0.7 mm / Tricolor


598-8610-307F	● R : 630	635	640	AllInGaP	20	40	65	90	2.1	2.4	140	-40 to +100	-40 to +100
	● G : 515	520	525	InGaP		260	580	900	3.1	3.4			
	● B : 465	470	475	InGaP		60	160	260	3.1	3.4			
598-8920-307F	● RO : 620	625	630	AllInGaP		90	120	150	2.1	2.4			
	● G : 515	520	525	InGaP		260	580	900	3.1	3.4			
	● B : 465	470	475	InGaP		90	175	260	3.1	3.4			
598-8940-307F	● Y : 585	590	595	AllInGaP		60	175	260	2.1	2.4			
	● G : 515	520	525	InGaP		260	580	900	3.1	3.4			
	● B : 465	470	475	InGaP		60	160	260	3.1	3.4			




Top



Side



Bottom




Schematic




1210 ▶ 3.0 x 2.5 x 1.3 mm / BiColor with Reflector Cup


597-7701-507F	● R : 620	630	640	GaAsP	20	3.6	6.3	11	2.0	2.8	100	-30 to +85	-40 to +85
	● G : 560	570	580	GaP		9	20	45	2.2	2.8			
597-7721-507F	● Y : 582	589	596	GaAsP / GaP		5.6	10	18	2.1	2.8			
	● G : 560	570	580	GaP		9	21	45	2.2	2.8			




Top




Side



Bottom




Schematic




Mini PLCC-2 ▶ 2.0 x 1.4 x 1.3 mm / Single Color, Low Current


597C-3008-207F	● R : 624	630	636	AllInGaP	2	3.55	9	14	1.8	2.2	120	-40 to +100	-40 to +100
597C-3208-207F	● O : 600	606	609			5.6	14	22.4	1.8	2.2			
597C-3408-207F	● Y : 580	587	595			4.5	11	18	1.8	2.2			
597C-3608-207F	● IceB : X=0.20 / Y=0.30			InGaP		9	15.7	22.4	2.75	3.1			
597C-3908-207F	● W : X=0.33 / Y=0.33					9	23	36	2.75	3.1			




Top



Side




Bottom




Schematic


AllInGaP and GaP LEDs 2 kV HBM • InGaP, AlGaAs and GaAs LEDs 500 V HBM • LEDs with Zener Diodes not LED sensitive

Top View | Mini PLCC-2 & PLCC-2


	Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
	Min	Typ	Max			Min	Typ	Max	Typ	Max			
	Mini PLCC-2 ▶ 2.2 x 1.4 x 1.3 mm / Single Color												
598-8C10-107F	● R : 620	625	630	AlInGaP	20	280	405	530	1.8	2.4	120	-40 to +85	-40 to +100
598-8C30-107F	● O : 600	605	610			230	290	350	1.8	2.4			
598-8C40-107F	● Y : 585	590	595			280	405	530	1.8	2.4			
598-8C60-107F	● YG : 565	570	575			40	65	90	1.8	2.4			
598-8C80-107F	● G : 520	525	550	InGaN	20	1500	1900	2300	2.8	3.3	120	-40 to +85	-40 to +100
598-8C90-107F	● B : 465	470	475			350	440	530	2.8	3.3			




Top



Side



Bottom



Schematic

PLCC-2 ▶ 3.5 x 2.8 x 1.9 mm / *Single Color Low Current*

597-3008-207F

● R : 624

630

636

AlInGaP

2

7.1

12.6

18

1.8

2.2

120

-40 to +100

-40 to +100

597-3208-207F

● O : 600

606

609

11.2

19.6

28

1.8

2.2

597-3308-207F

● G : 566

570

575

3.55

6.28

9.0

1.8

2.2

597-3408-207F

● Y : 580

587

595

9

15.7

22.4

1.8


2.2

Top

Side

Bottom



Schematic



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


PLCC-2 ▶ 3.5 x 2.8 x 1.9 mm / Single Color

597-3001-207F	● R : -	628	-	GaAsP	10	4.5	-	18	2	2.5	120	-40 to +100	-40 to +100
597-3002-307F	● R : -	633	-	AlInGaP	20	112	160	224	2	2.3		-55 to +100	-55 to +100
597-3211-207F	● O : -	602	-	GaP	20	11.2	15	-	2.2	2.6		-40 to +100	-40 to +100
597-3225-307F	● A : -	592	-	AlInGaP	20	112.5	140	-	2.2	2.6		-55 to +100	-55 to +100
597-3231-207F	● Y : 580	587	595	AlInGaP	20	71	100	140	2	2.4		-40 to +100	-40 to +100
597-3301-207F	● G : 564	570	576	GaAsP/GaP	10	11.2	19.6	28	2	2.5		-55 to +100	-55 to +100
597-3306-207F	● G : 564	570	576	GaAlP	10	14	24	36	2	2.5		-40 to +100	-40 to +100
597-3323-307F	● G : -	525	-	InGaP	20	180	224	-	3.7	4.36		-40 to +100	-40 to +100
597-3401-207F	● Y : 580	587	595	GaAsP/GaP	10	7.1	12.6	18	2	2.5		-40 to +100	-40 to +100
597-3601-207F	● B : 465	471	477	InGaP	10	14	-	34	3.1	3.7		-40 to +100	-40 to +100




3528 Package ▶ 3.5 x 2.8 x 1.9 mm / Single Color

598-8B10-107F	● R : 615	623	630	AlInGaP	20	200	380	560	1.8	2.4	120	-40 to +85	-40 to +100
598-8B30-107F	● O : 600	605	610			260	345	430	1.8	2.4			
598-8B40-107F	● Y : 585	590	595			200	315	430	1.8	2.4			
598-8B60-107F	● YG : 565	570	575			40	80	120	1.8	2.4			
598-8B80-107F	● G : 520	525	530	InGaP	20	1200	1750	2300	2.8	3.5	120	-40 to +85	-40 to +100
598-8B90-107F	● B : 465	470	475			230	395	560	2.8	3.5			





Top View | PLCC-4



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


PLCC-4 ▶ 3.5 x 2.8 x 1.9 mm / Single Color High Current

597-3029-207F	● R : 620	625	630	AlInGaP	50	1120	1800	2800	2.15	2.5	120	-40 to +110	-40 to +110
597-3209-207F	● O : 600	606	609	AlInGaP	50	1400	2240	4500	2.15	2.5			
597-3329-207F	● G : 516	525	540	InGaN	30	1120	1800	2240	3.4	3.8			
597-3409-207F	● Y : 586	589	595	AlInGaP	50	1120	1800	2240	2.15	2.65			
597-3609-207F	● B : 463	469	475	InGaN	30	280	450	710	3.4	3.8			
597-3909-207F	○ W : X=0.30 / Y=0.28			InGaN	30	1120	1600	2240	3.3	3.8			



PLCC-4 ▶ 3.5 x 2.8 x 1.9 mm / Bicolor Low Current

597-7701-207F	● R : 624	630	636	AlInGaP	2	4.5	—	18	1.8	2.2	120	-40 to +100	-40 to +100
	● G : 566	570	575			2.8	—	11.2	1.8	2.2			
597-7721-207F	● Y : 580	587	595	AlInGaP		4.5	—	18	1.8	2.2			
	● G : 566	570	575			2.8	—	11.2	1.8	2.2			



	Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
	Min	Typ	Max			Min	Typ	Max	Typ	Max			
	PLCC-4 ▶ 3.5 x 2.8 x 1.9 mm / Bicolor and Tricolor												

597-7731-207F	● R : 627	633	639	AlInGaP	20	56	112	140	2.0	2.3	120	-40 to +100	-40 to +100
	● Y : 580	587	595			90	140	224	2.0	2.4			
597-7752-007F	● R : 620	—	630	AlInGaP		200	400	600	2.0	2.2			
	● G : 515	520	530	InGaN		650	—	1500	3.2	3.6			

Top	Side	Bottom	Schematic
------------	-------------	---------------	------------------


597-7711-307F	● R :	626		AlInGaP	20	40	80		1.9	2.4	120	-55 to +100	-55 to +100
	● G :	525		InGaN		99	160	180	3.4	4.05			
	● B :	470		InGaN		25	40	60	3.4	4.05			

Top	Side	Bottom	Schematic
------------	-------------	---------------	------------------

597-7714-007F	● RO : 620	625	630	AlInGaP	20	180	230	380	2.1	2.3	120	-20 to +85	-35 to +85
	● G : 520	525	530	InGaN		650	1000	1200	3.2	3.4			
	● B : 465	468	472.5	InGaN		150	230	350	3.2	3.4			
597-7791-907F	● R : 620	625	630	AlInGaP/ GaAs	20	520	850	1150	2.1	2.4	120	-30 to +85	-40 to +100
	● G : 525	530	535	InGaN		800	1650	1900	3.2	3.6			
	● Y : 585	590	595	AlInGaP/ GaAs		520	800	1150	2.1	2.4			

Top	Side	Bottom	Schematic
------------	-------------	---------------	------------------

Reverse Mount | 1206





Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			

1206 Package Reverse Mount ▶ 3.2 x 1.6 x 1.1 mm / Single Color

597-6001-607F	● R : -	631	-	AlInGaP	20	18	-	280	2.0	2.4	70	-55 to +85	-55 to +85
597-6201-607F	● O : -	605	-	AlInGaP		71	-	450	2.0	2.4			
597-6301-607F	● G : -	525	-	InGaP		280	-	1120	3.0	3.8			
597-6401-607F	● Y : -	587	-	AlInGaP		28	-	450	2.0	2.4			
597-6501-607F	● YG : 567	-	577	AlInGaP		28	-	180	2.0	2.4			
597-6601-607F	● B : 465	-	475	InGaP		112	-	280	3.0	3.8			
597-6901-607F	○ W : X=0.304 / Y=0.301			InGaP	5	45		112	3.0	3.15	150	-20 to +80	-40 to +85


1206 Reverse Mount ▶ 3.2 x 1.6 x 1.1 mm / Single Color with Zener Diode

597-6325-607F	● G : 520	-	535	InGaP	20	280	-	1120	3.0	3.8	70	-20 to +80	-30 to +100
---------------	-----------	---	-----	-------	----	-----	---	------	-----	-----	----	------------	-------------



1206 Reverse Mount ▶ 3.2 x 1.6 x 1.1 mm / BiColor

597-7703-607F	● R : -	631	-	AlInGaP	20	28	55	112	2.0	2.4	130	-30 to +85	-40 to +85
	● G : 567	571	577			28	45	112	2.0	2.4			
597-7783-607F	● R : -	631	-	AlInGaP		28	45	112	2.0	2.4	130	-20 to +80	-30 to +100
	● B : -	470	-	InGaP		28	45	180	3.3	3.8			
597-7784-607F	● O : -	605	-	AlInGaP		71	-	180	2.0	2.4	130	-20 to +80	-30 to +100
	● B : -	470	-	InGaP		45	-	112	3.3	3.8			






Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			


0603 Package Right Angle ▶ 1.6 x 1.0 x 0.8 mm / Single Color

598-8D10-107F	● R : 630	635	640	AlInGaP	20	30	—	90	1.8	2.4	140	-40 to +85	-40 to +100
598-8D20-107F	● R0 : 620	625	630			150	240	330	1.8	2.4			
598-8D30-107F	● O : 600	605	610			90	145	200	1.8	2.4			
598-8D40-107F	● Y : 585	590	595			120	160	200	1.8	2.4			
598-8D60-107F	● YG : 565	570	575			28	54	80	1.8	2.4			
598-8D80-107F	● G : 510	525	535	InGaN	20	70	135	200	2.8	3.5	140	-40 to +85	-40 to +100
598-8D90-107F	● B : 460	470	475			350	440	530	2.8	3.5			




0605 Package Right Angle ▶ 1.6 x 1.15 x 0.55 mm / Single Color





597-2003-507F	● R : 625	630	635	AlInGaP	20	16	40	—	2.2	—	135	-40 to +85	-40 to +100
597-2033-507F	● R : 615	620	625	AlInGaP		25	63	—	2.2	—	135		
597-2203-507F	● O : 602	605	608	AlInGaP		40	100	—	2.2	—	135		
597-2323-507F	● G : 520	527	535	InGaN	5	22	56	—	3.0	—	130		
597-2403-507F	● Y : 587	590	593	AlInGaP	20	36	63	—	2.0	—	135		
597-2503-507F	● YG : 569	572	575	AlInGaP		10	25	—	2.2	—	135		
597-2603-507F	● B : 464	470	476	InGaN	10	56	140	—	3.2	—	140		
597-2903-507F	○ W : X=0.31/Y=0.31			InGaN		90	170	—	3.1	—	150		



NOTE: Right Angle SMDs are shown in the diagrams in front, top, and back views, with front and back oriented with the PCB below. The front and back diagrams flip across the y-axis.





Right Angle | 1208


	Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
	Min	Typ	Max			Min	Typ	Max	Typ	Max			
	1208 Package Right Angle ▶ 3.0 x 1.5 x 1.0 mm / TriColor												
597-2712-607F	● R :	624		AlInGaP	20	45	—	180	2.0	2.4	130	-20 to +80	-30 to +100
	● G :	525		InGaP		112	—	450	3.5	3.8			
	● B :	470		InGaP		28	—	180	3.5	3.8			

			
Front	Top	Back	Schematic

PC BOARD


PC BOARD


													
1208 Right Angle ▶ 3.0 x 2.0 x 1.0 mm / Single Color													
597-2002-407NF	● R :	626		AlInGaP	20	—	—	—	1.9	2.4	130	-40 to +85	-40 to +100
597-2111-407F	● R :	647		AlGaAs		6.2	12.4	—	1.7	2.3		-30 to +85	-40 to +100
597-2212-407NF	● O :	606		GaAsP		68	150	—	1.9	2.4		-40 to +85	-40 to +120
597-2222-407F	● Y :	590		AlInGaP		16	65	—	1.9	2.4		-40 to +85	-40 to +100
597-2311-407F	● G :	567		GaP		2.6	5.2	—	2.1	2.8		-30 to +85	-40 to +100
597-2401-407F	● Y : 590	590		GaAsP/GaP		1.5	3	—	2.2	2.8		-30 to +85	-40 to +100
597-2413-407F	● Y :	586		GaP		4.4	8.8	—	2.1	2.8		-30 to +85	-40 to +100
													
													
													
													
Front PC BOARD Top Back PC BOARD Schematic													

	Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
	Min	Typ	Max			Min	Typ	Max	Typ	Max			


1208 Right Angle ▶ 3.0 x 2.0 x 1.0 mm / Single Color

597-2002-607F	● R : —	631	—	AlInGaP	20	71	125	180	2.0	2.4	130	-55 to +85	-55 to +85
597-2211-607F	● O : 598	605	612			71	125	180	2.0	2.4			
597-2222-607F	● Y : 587	589	592			71	125	180	2.0	2.4			
597-2501-607F	● G : 570	572	577			28	50	71	2.0	2.4			
597-2601-607F	● G : 520	525	535	InGaN		112	195	280	3.2	3.6			
597-2901-607F	● B : 465	470	475			71	125	180	3.4	3.8			




													
1208 Right Angle ▶ 3.0 x 2.0 x 1.0 mm / BiColor													

597-2732-607F	● R : 624		638	AlInGaP	20	40	—	112		2.4	130	-30 to +85	-40 to +85
	● Y : 587		594.5			45	—	180		2.4			
597-2771-607F	● R : 624	639	638			40	—	112		2.4		-30 to +85	-40 to +85
	● G : 570.5	574	576.5			28	—	71		2.4			












597-2723-607F	● G : 567	571	576	AlInGaP	20	18	35	112	2.0	2.4	130	-55 to +85	-55 to +85
	● Y : 582	589	597			28	75	118	2.0	2.4			
597-2724-607F	● Y : —	589	—			71	150	280	2.0	2.4		-40 to +85	-40 to +105
Reverse Polarity	● G : —	571	—			18	50	112	2.0	2.4			
597-2751-607F	● R : —	631	—			18	45	—	2.0	2.4	130	-55 to +85	-55 to +85
	● G : 567	571	576			18	35	112	2.0	2.4			




AlInGaP and GaP LEDs 2 kV HBM • InGaN, AlGaAs and GaAs LEDs 500 V HBM • LEDs with Zener Diodes not LED sensitive

Right Angle | 1208

	Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
	Min	Typ	Max			Min	Typ	Max	Typ	Max			
1208 Right Angle ▶ 3.2 x 1.5 x 1.0 mm / Single Color													
598-8310-117F	● R : 625	635	640	AlInGaP	20	40		90	2.1	2.4	140	-40 to +100	-40 to +100
598-8320-117F	● RO : 620	625	630			120	150	200					
598-8330-117F	● O : 600	—	610			70	110	150					
598-8340-117F	● Y : 590	—	595			90	140	200					
598-8350-117F	● Y : 585	—	590			90	140	200					
598-8360-117F	● YG : 570	—	575			43	65	80					
598-8370-117F	● G : 563		570	InGaN	20	18	28	43	3.1	3.4	140	-40 to +100	-40 to +100
598-8380-117F	● G : 515	520	525			260	480	900					
598-8391-117F	● B : 465	470	475			90	170	260					
 Front PC BOARD  Top  Back PC BOARD  Schematic													

																			
1208 Right Angle ▶ 3.2 x 1.5 x 1.0 mm / BiColor																			
598-8510-207F	● R : 625 ● YG:562	632 567	640 575	AlInGaP	20	40 30	80 40	120 50	2	2.4	140	-40 to +100	-40 to +100						
598-8520-207F	● O : 620 ● YG:562	625 567	630 570	AlInGaP		90 30	150 40	200 50											
598-8530-207F	● A : 600 ● YG:562	605 567	610 570	AlInGaP		90 30	150 40	200 50											
598-8540-207F	● Y : 585 ● YG:562	590 567	595 570	AlInGaP		90 30	150 40	200 50											
598-8550-207F	● Y : 587 ● G : 515	590 525	597 530	AlInGaP InGaN		90 260	150 560	200 900						2 3.2	2.4 3.4				
598-8560-207F	● Y : 587 ● R : 630	590 635	597 640	AlInGaP		90 40	150 65	200 90						2.2 2.2	2.4 2.4				
																			
																			
																			


AlInGaP and GaP LEDs 2 kV HBM • InGaP, AlGaAs and GaAs LEDs 500 V HBM • LEDs with Zener Diodes not LED sensitive



Color : Wavelength (nm)			Material	Test Current (mA)	Intensity (mcd)			Typ Fwd Voltage (V)		Viewing Angle	Operating Temp (°C)	Storage Temp (°C)
Min	Typ	Max			Min	Typ	Max	Typ	Max			

1208 Right Angle ▶ 3.2 x 1.5 x 1.0 mm / TriColor

598-8810-307F	● R : 630	640	AllInGaP	20	35	100	2.4	160	-40 to +100	-40 to +100
	● G : 515	530	InGaP		200	560	3.5			
	● B : 465	475	InGaP		60	200	3.5			
598-8820-307F	● RO : 600	610	AllInGaP		70	200	2.4			
	● G : 515	530	InGaP		200	560	3.5			
	● B : 465	475	InGaP		60	200	3.5			
598-8840-307F	● Y : 587	597	AllInGaP		70	200	2.4			
	● G : 515	530	InGaP		200	560	3.5			
	● B : 465	475	InGaP		60	200	3.5			




1616 Package Right Angle ▶ 4.0 x 4.0 x 3.6 mm / Single Color Low Current

597-2001-213F	● R : 624	630	636	AllInGaP	2	20	40	60	1.8	120	-40 to +100	-40 to +100
597-2301-213F	● G : 566	570	575			10	42	50	1.8			
597-2401-213F	● Y : 580	587	595			25	70	115	1.8			


1616 Right Angle ▶ 4.0 x 4.0 x 3.6 mm / Single Color

597-2201-815F	● Y : 580	587	595	AllInGaP	30	280	—	900	2.1	120	-40 to +100	-40 to +100
597-2301-824F	● G : 519	537			20	45	—	900	2			
597-2321-816F	● G : 566	528	575	InGaP	20	355	—	112	3.5			
597-2601-817F	● B : 464	470	476		2	90	—	224	3.6			
597-2901-822F	○ W : X=0.330/Y=0.330				20	355	—	710	3.6			




More Optoelectronic Products from Dialight Signals & Components

Board Mount Indication



Prism® SMD



CBI® Through Hole



Optopipe® Light Pipes

Panel Mount Indication



Military & Relampable



LED PMI



Based LED Bulbs

The Most Reliable, The Most Options.

North American HQ

1501 Route 34 South
Farmingdale, NJ 07727
Tel: 732.919.3119

info@dialightsignalsandcomponents.com

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com
Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.

www.dialightsignalsandcomponents.com

Dialight_SMD_Selector Guide_0626_1