

# 8-Mbit (1024 K × 8/512 K × 16) nvSRAM

## Features

- 20 ns, 25 ns, and 45 ns access times
- Internally organized as 1024 K × 8 (CY14B108L) or 512 K × 16 (CY14B108N)
- Hands off automatic STORE on power-down with only a small capacitor
- STORE to QuantumTrap nonvolatile elements initiated by software, device pin, or AutoStore on power-down
- RECALL to SRAM initiated by software or power-up
- Infinite Read, Write, and RECALL cycles
- 1 million STORE cycles to QuantumTrap
- 20 year data retention
- Single 3 V +20%, -10% operation
- Industrial temperature

## Packages

- 44-/54-pin thin small outline package (TSOP) Type II
- 48-ball fine-pitch ball grid array (FBGA)


## Pb-free and restriction of hazardous substances (RoHS) compliant

## Functional Description

The Cypress CY14B108L/CY14B108N is a fast static RAM (SRAM), with a nonvolatile element in each memory cell. The memory is organized as 1024 Kbytes of 8 bits each or 512 K words of 16 bits each. The embedded nonvolatile elements incorporate QuantumTrap technology, producing the world's most reliable nonvolatile memory. The SRAM provides infinite read and write cycles, while independent nonvolatile data resides in the highly reliable QuantumTrap cell. Data transfers from the SRAM to the nonvolatile elements (the STORE operation) takes place automatically at power-down. On power-up, data is restored to the SRAM (the RECALL operation) from the nonvolatile memory. Both the STORE and RECALL operations are also available under software control.

For a complete list of related documentation, click [here](#).

## Logic Block Diagram [1, 2, 3]



**Errata:** AutoStore Disable feature does not work in the device. For more information, see [Errata on page 24](#). Details include errata trigger conditions, scope of impact, available workarounds, and silicon revision applicability.

## Notes

1. Address A<sub>0</sub>–A<sub>19</sub> for × 8 configuration and Address A<sub>0</sub>–A<sub>18</sub> for × 16 configuration.
2. Data DQ<sub>0</sub>–DQ<sub>7</sub> for × 8 configuration and Data DQ<sub>0</sub>–DQ<sub>15</sub> for × 16 configuration.
3. BHE and BLE are applicable for × 16 configuration only.

## Contents

|                                            |           |                                                      |           |
|--------------------------------------------|-----------|------------------------------------------------------|-----------|
| <b>Pinouts</b> .....                       | <b>3</b>  | <b>Software Controlled STORE/RECALL Cycle</b> .....  | <b>16</b> |
| <b>Pin Definitions</b> .....               | <b>4</b>  | <b>Switching Waveforms</b> .....                     | <b>16</b> |
| <b>Device Operation</b> .....              | <b>5</b>  | <b>Hardware STORE Cycle</b> .....                    | <b>17</b> |
| SRAM Read .....                            | 5         | <b>Switching Waveforms</b> .....                     | <b>17</b> |
| SRAM Write .....                           | 5         | <b>Truth Table For SRAM Operations</b> .....         | <b>18</b> |
| AutoStore Operation .....                  | 5         | <b>Ordering Information</b> .....                    | <b>19</b> |
| Hardware STORE Operation .....             | 5         | Ordering Code Definitions .....                      | 19        |
| Hardware RECALL (Power-Up) .....           | 6         | <b>Package Diagrams</b> .....                        | <b>20</b> |
| Software STORE .....                       | 6         | <b>Acronyms</b> .....                                | <b>23</b> |
| Software RECALL .....                      | 6         | <b>Document Conventions</b> .....                    | <b>23</b> |
| Preventing AutoStore .....                 | 8         | Units of Measure .....                               | 23        |
| Data Protection .....                      | 8         | <b>Errata</b> .....                                  | <b>24</b> |
| <b>Maximum Ratings</b> .....               | <b>9</b>  | Part Numbers Affected .....                          | 24        |
| <b>Operating Range</b> .....               | <b>9</b>  | 8Mb (1024 K × 8, 512 K × 16) nvSRAM .....            | 24        |
| <b>DC Electrical Characteristics</b> ..... | <b>9</b>  | Qualification Status .....                           | 24        |
| <b>Data Retention and Endurance</b> .....  | <b>10</b> | 8Mb (1024 K × 8, 512 K × 16) nvSRAM .....            | 24        |
| <b>Capacitance</b> .....                   | <b>10</b> | Errata Summary .....                                 | 24        |
| <b>Thermal Resistance</b> .....            | <b>10</b> | <b>Document History Page</b> .....                   | <b>25</b> |
| <b>AC Test Loads</b> .....                 | <b>11</b> | <b>Sales, Solutions, and Legal Information</b> ..... | <b>27</b> |
| <b>AC Test Conditions</b> .....            | <b>11</b> | Worldwide Sales and Design Support .....             | 27        |
| <b>AC Switching Characteristics</b> .....  | <b>12</b> | Products .....                                       | 27        |
| <b>Switching Waveforms</b> .....           | <b>12</b> | PSoC® Solutions .....                                | 27        |
| <b>AutoStore/Power-Up RECALL</b> .....     | <b>15</b> | Cypress Developer Community .....                    | 27        |
| <b>Switching Waveforms</b> .....           | <b>15</b> | Technical Support .....                              | 27        |

## Pinouts

Figure 1. Pin Diagram – 48-ball FBGA





Figure 2. Pin Diagram – 44/54-pin TSOP II



### Note

- Address expansion for 16-Mbit. NC pin not connected to die.

## Pin Definitions

| Pin Name                          | I/O Type     | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-----------------------------------|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| A <sub>0</sub> –A <sub>19</sub>   | Input        | Address inputs. Used to select one of the 1,048,576 bytes of the nvSRAM for × 8 configuration.                                                                                                                                                                                                                                                                                                                                                                                         |
| A <sub>0</sub> –A <sub>18</sub>   |              | Address inputs. Used to select one of the 524,288 words of the nvSRAM for × 16 configuration.                                                                                                                                                                                                                                                                                                                                                                                          |
| DQ <sub>0</sub> –DQ <sub>7</sub>  | Input/Output | Bidirectional data I/O lines for × 8 configuration. Used as input or output lines depending on operation.                                                                                                                                                                                                                                                                                                                                                                              |
| DQ <sub>0</sub> –DQ <sub>15</sub> |              | Bidirectional data I/O lines for × 16 configuration. Used as input or output lines depending on operation.                                                                                                                                                                                                                                                                                                                                                                             |
| $\overline{\text{WE}}$            | Input        | Write Enable input, Active LOW. When selected LOW, data on the I/O pins is written to the specific address location.                                                                                                                                                                                                                                                                                                                                                                   |
| $\overline{\text{CE}}$            | Input        | Chip Enable input, Active LOW. When LOW, selects the chip. When HIGH, deselects the chip.                                                                                                                                                                                                                                                                                                                                                                                              |
| $\overline{\text{OE}}$            | Input        | Output Enable, Active LOW. The active LOW $\overline{\text{OE}}$ input enables the data output buffers during read cycles. I/O pins are tristated on deasserting $\overline{\text{OE}}$ HIGH.                                                                                                                                                                                                                                                                                          |
| $\overline{\text{BHE}}$           | Input        | Byte High Enable, Active LOW. Controls DQ <sub>15</sub> –DQ <sub>8</sub> .                                                                                                                                                                                                                                                                                                                                                                                                             |
| $\overline{\text{BLE}}$           | Input        | Byte Low Enable, Active LOW. Controls DQ <sub>7</sub> –DQ <sub>0</sub> .                                                                                                                                                                                                                                                                                                                                                                                                               |
| V <sub>SS</sub>                   | Ground       | Ground for the device. Must be connected to the ground of the system.                                                                                                                                                                                                                                                                                                                                                                                                                  |
| V <sub>CC</sub>                   | Power supply | Power supply inputs to the device.                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| $\overline{\text{HSB}}$           | Input/Output | Hardware STORE Busy ( $\overline{\text{HSB}}$ ). When LOW this output indicates that a Hardware STORE is in progress. When pulled LOW external to the chip it initiates a nonvolatile STORE operation. After each Hardware and Software STORE operation, $\overline{\text{HSB}}$ is driven HIGH for a short time (t <sub>HHHD</sub> ) with standard output high current and then a weak internal pull-up resistor keeps this pin HIGH (external pull-up resistor connection optional). |
| V <sub>CAP</sub>                  | Power supply | AutoStore capacitor. Supplies power to the nvSRAM during power loss to store data from SRAM to nonvolatile elements.                                                                                                                                                                                                                                                                                                                                                                   |
| NC                                | No connect   | No connect. This pin is not connected to the die.                                                                                                                                                                                                                                                                                                                                                                                                                                      |

## Device Operation

The CY14B108L/CY14B108N nvSRAM is made up of two functional components paired in the same physical cell. They are a SRAM memory cell and a nonvolatile QuantumTrap cell. The SRAM memory cell operates as a standard fast static RAM. Data in the SRAM is transferred to the nonvolatile cell (the STORE operation), or from the nonvolatile cell to the SRAM (the RECALL operation). Using this unique architecture, all cells are stored and recalled in parallel. During the STORE and RECALL operations, SRAM read and write operations are inhibited. The CY14B108L/CY14B108N supports infinite reads and writes similar to a typical SRAM. In addition, it provides infinite RECALL operations from the nonvolatile cells and up to 1 million STORE operations. See [Truth Table For SRAM Operations on page 18](#) for a complete description of read and write modes.

### SRAM Read

The CY14B108L/CY14B108N performs a read cycle when  $\overline{CE}$  and  $\overline{OE}$  are LOW and  $\overline{WE}$  and  $\overline{HSB}$  are HIGH. The address specified on pins  $A_{0-19}$  or  $A_{0-18}$  determines which of the 1,048,576 data bytes or 524,288 words of 16 bits each are accessed. Byte enables ( $\overline{BHE}$ ,  $\overline{BLE}$ ) determine which bytes are enabled to the output, in the case of 16-bit words. When the read is initiated by an address transition, the outputs are valid after a delay of  $t_{AA}$  (read cycle 1). If the read is initiated by  $\overline{CE}$  or  $\overline{OE}$ , the outputs are valid at  $t_{ACE}$  or at  $t_{DOE}$ , whichever is later (read cycle 2). The data output repeatedly responds to address changes within the  $t_{AA}$  access time without the need for transitions on any control input pins. This remains valid until another address change or until  $\overline{CE}$  or  $\overline{OE}$  is brought HIGH, or  $\overline{WE}$  or  $\overline{HSB}$  is brought LOW.

### SRAM Write

A write cycle is performed when  $\overline{CE}$  and  $\overline{WE}$  are LOW and  $\overline{HSB}$  is HIGH. The address inputs must be stable before entering the write cycle and must remain stable until  $\overline{CE}$  or  $\overline{WE}$  goes HIGH at the end of the cycle. The data on the common I/O pins  $DQ_{0-15}$  are written into the memory if the data is valid  $t_{SD}$  before the end of a  $\overline{WE}$  controlled write or before the end of an  $\overline{CE}$  controlled write. The Byte Enable inputs ( $\overline{BHE}$ ,  $\overline{BLE}$ ) determine which bytes are written, in the case of 16-bit words. Keep  $\overline{OE}$  HIGH during the entire write cycle to avoid data bus contention on common I/O lines. If  $\overline{OE}$  is left LOW, internal circuitry turns off the output buffers  $t_{HZWE}$  after  $\overline{WE}$  goes LOW.

### AutoStore Operation

The CY14B108L/CY14B108N stores data to the nvSRAM using one of the following three storage operations: Hardware STORE activated by the  $\overline{HSB}$ ; Software STORE activated by an address sequence; AutoStore on device power-down. The AutoStore operation is a unique feature of QuantumTrap technology and is enabled by default on the CY14B108L/CY14B108N.

During a normal operation, the device draws current from  $V_{CC}$  to charge a capacitor connected to the  $V_{CAP}$  pin. This stored charge is used by the chip to perform a single STORE operation. If the voltage on the  $V_{CC}$  pin drops below  $V_{SWITCH}$ , the part automatically disconnects the  $V_{CAP}$  pin from  $V_{CC}$ . A STORE operation is initiated with power provided by the  $V_{CAP}$  capacitor.


**Note** If the capacitor is not connected to  $V_{CAP}$  pin, AutoStore must be disabled using the soft sequence specified in [Preventing](#)

[AutoStore on page 8](#). In case AutoStore is enabled without a capacitor on  $V_{CAP}$  pin, the device attempts an AutoStore operation without sufficient charge to complete the Store. This corrupts the data stored in nvSRAM.

Figure 3 shows the proper connection of the storage capacitor ( $V_{CAP}$ ) for automatic STORE operation. Refer to [DC Electrical Characteristics on page 9](#) for the size of  $V_{CAP}$ . The voltage on the  $V_{CAP}$  pin is driven to  $V_{CC}$  by a regulator on the chip. A pull-up should be placed on  $\overline{WE}$  to hold it inactive during power-up. This pull-up is effective only if the  $\overline{WE}$  signal is tristate during power-up. Many MPUs tristate their controls on power-up. This should be verified when using the pull-up. When the nvSRAM comes out of power-on-RECALL, the MPU must be active or the  $\overline{WE}$  held inactive until the MPU comes out of reset.

To reduce unnecessary nonvolatile STOREs, AutoStore and Hardware STORE operations are ignored unless at least one write operation has taken place since the most recent STORE or RECALL cycle. Software initiated STORE cycles are performed regardless of whether a write operation has taken place. The  $\overline{HSB}$  signal is monitored by the system to detect if an AutoStore cycle is in progress.

**Figure 3. AutoStore Mode**



### Hardware STORE Operation

The CY14B108L/CY14B108N provides the  $\overline{HSB}$  pin to control and acknowledge the STORE operations. Use the  $\overline{HSB}$  pin to request a Hardware STORE cycle. When the  $\overline{HSB}$  pin is driven LOW, the CY14B108L/CY14B108N conditionally initiates a STORE operation after  $t_{DELAY}$ . An actual STORE cycle only begins if a write to the SRAM has taken place since the last STORE or RECALL cycle. The  $\overline{HSB}$  pin also acts as an open drain driver (internal 100 kΩ weak pull-up resistor) that is internally driven LOW to indicate a busy condition when the STORE (initiated by any means) is in progress.

**Note** After each Hardware and Software STORE operation  $\overline{HSB}$  is driven HIGH for a short time ( $t_{HHHD}$ ) with standard output high current and then remains HIGH by internal 100 kΩ pull-up resistor.

SRAM write operations that are in progress when  $\overline{\text{HSB}}$  is driven LOW by any means are given time ( $t_{\text{DELAY}}$ ) to complete before the STORE operation is initiated. However, any SRAM write cycles requested after  $\overline{\text{HSB}}$  goes LOW are inhibited until  $\overline{\text{HSB}}$  returns HIGH. In case the write latch is not set,  $\overline{\text{HSB}}$  is not driven LOW by the CY14B108L/CY14B108N. But any SRAM read and write cycles are inhibited until  $\overline{\text{HSB}}$  is returned HIGH by MPU or other external source.

During any STORE operation, regardless of how it is initiated, the CY14B108L/CY14B108N continues to drive the  $\overline{\text{HSB}}$  pin LOW, releasing it only when the STORE is complete. Upon completion of the STORE operation, the nvSRAM memory access is inhibited for  $t_{\text{LZHSB}}$  time after  $\overline{\text{HSB}}$  pin returns HIGH. Leave the  $\overline{\text{HSB}}$  unconnected if it is not used.

### Hardware RECALL (Power-Up)

During power-up or after any low power condition ( $V_{\text{CC}} < V_{\text{SWITCH}}$ ), an internal RECALL request is latched. When  $V_{\text{CC}}$  again exceeds the  $V_{\text{SWITCH}}$  on power-up, a RECALL cycle is automatically initiated and takes  $t_{\text{HRECALL}}$  to complete. During this time, the  $\overline{\text{HSB}}$  pin is driven LOW by the  $\overline{\text{HSB}}$  driver and all reads and writes to nvSRAM are inhibited.

### Software STORE

Data is transferred from the SRAM to the nonvolatile memory by a software address sequence. The CY14B108L/CY14B108N Software STORE cycle is initiated by executing sequential  $\overline{\text{CE}}$  or  $\overline{\text{OE}}$  controlled read cycles from six specific address locations in exact order. During the STORE cycle an erase of the previous nonvolatile data is first performed, followed by a program of the nonvolatile elements. After a STORE cycle is initiated, further input and output are disabled until the cycle is completed.

Because a sequence of READs from specific addresses is used for STORE initiation, it is important that no other read or write accesses intervene in the sequence, or the sequence is aborted and no STORE or RECALL takes place.

To initiate the Software STORE cycle, the following read sequence must be performed.

1. Read address 0x4E38 Valid READ
2. Read address 0xB1C7 Valid READ
3. Read address 0x83E0 Valid READ
4. Read address 0x7C1F Valid READ
5. Read address 0x703F Valid READ
6. Read address 0x8FC0 Initiate STORE cycle

The software sequence may be clocked with  $\overline{\text{CE}}$  controlled reads or  $\overline{\text{OE}}$  controlled reads, with  $\overline{\text{WE}}$  kept HIGH for all the six READ sequences. After the sixth address in the sequence is entered, the STORE cycle commences and the chip is disabled.  $\overline{\text{HSB}}$  is driven LOW. After the  $t_{\text{STORE}}$  cycle time is fulfilled, the SRAM is activated again for the read and write operation.

### Software RECALL

Data is transferred from the nonvolatile memory to the SRAM by a software address sequence. A software RECALL cycle is initiated with a sequence of read operations in a manner similar to the software STORE initiation. To initiate the RECALL cycle, the following sequence of  $\overline{\text{CE}}$  or  $\overline{\text{OE}}$  controlled read operations must be performed.

1. Read address 0x4E38 Valid READ
2. Read address 0xB1C7 Valid READ
3. Read address 0x83E0 Valid READ
4. Read address 0x7C1F Valid READ
5. Read address 0x703F Valid READ
6. Read address 0x4C63 Initiate RECALL cycle

Internally, RECALL is a two-step procedure. First, the SRAM data is cleared; then, the nonvolatile information is transferred into the SRAM cells. After the  $t_{\text{RECALL}}$  cycle time, the SRAM is again ready for read and write operations. The RECALL operation does not alter the data in the nonvolatile elements.

**Table 1. Mode Selection**

| $\overline{\text{CE}}$ | $\overline{\text{WE}}$ | $\overline{\text{OE}}$ | $\overline{\text{BHE}}, \overline{\text{BLE}}^{[5]}$ | $\text{A}_{15}\text{--}\text{A}_0^{[6]}$                 | Mode                                                                                   | I/O                                                                                      | Power                                |
|------------------------|------------------------|------------------------|------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|--------------------------------------|
| H                      | X                      | X                      | X                                                    | X                                                        | Not Selected                                                                           | Output High Z                                                                            | Standby                              |
| L                      | H                      | L                      | L                                                    | X                                                        | Read SRAM                                                                              | Output data                                                                              | Active                               |
| L                      | L                      | X                      | L                                                    | X                                                        | Write SRAM                                                                             | Input data                                                                               | Active                               |
| L                      | H                      | L                      | X                                                    | 0x4E38<br>0xB1C7<br>0x83E0<br>0x7C1F<br>0x703F<br>0x8B45 | Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>AutoStore<br>Disable  | Output data<br>Output data<br>Output data<br>Output data<br>Output data<br>Output data   | Active <sup>[7]</sup>                |
| L                      | H                      | L                      | X                                                    | 0x4E38<br>0xB1C7<br>0x83E0<br>0x7C1F<br>0x703F<br>0x4B46 | Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>AutoStore<br>Enable   | Output data<br>Output data<br>Output data<br>Output data<br>Output data<br>Output data   | Active <sup>[7]</sup>                |
| L                      | H                      | L                      | X                                                    | 0x4E38<br>0xB1C7<br>0x83E0<br>0x7C1F<br>0x703F<br>0x8FC0 | Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>Nonvolatile<br>STORE  | Output data<br>Output data<br>Output data<br>Output data<br>Output data<br>Output High Z | Active $\text{I}_{\text{CC2}}^{[7]}$ |
| L                      | H                      | L                      | X                                                    | 0x4E38<br>0xB1C7<br>0x83E0<br>0x7C1F<br>0x703F<br>0x4C63 | Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>Read SRAM<br>Nonvolatile<br>RECALL | Output data<br>Output data<br>Output data<br>Output data<br>Output data<br>Output High Z | Active <sup>[7]</sup>                |

**Errata:** AutoStore Disable feature does not work in the device. For more information, see [Errata on page 24](#).

**Notes**

5.  $\overline{\text{BHE}}$  and  $\overline{\text{BLE}}$  are applicable for × 16 configuration only.
6. While there are 20 address lines on the CY14B108L (19 address lines on the CY14B108N), only the 13 address lines ( $\text{A}_{14}\text{--}\text{A}_2$ ) are used to control software modes. Rest of the address lines are don't care.
7. The six consecutive address locations must be in the order listed.  $\overline{\text{WE}}$  must be HIGH during all six cycles to enable a nonvolatile cycle.

### Preventing AutoStore

The AutoStore function is disabled by initiating an AutoStore disable sequence. A sequence of read operations is performed in a manner similar to the Software STORE initiation. To initiate the AutoStore disable sequence, the following sequence of  $\overline{CE}$  or  $\overline{OE}$  controlled read operations must be performed:

1. Read address 0x4E38 Valid READ
2. Read address 0xB1C7 Valid READ
3. Read address 0x83E0 Valid READ
4. Read address 0x7C1F Valid READ
5. Read address 0x703F Valid READ
6. Read address 0x8B45 AutoStore Disable

**Note Errata:** AutoStore Disable feature does not work in the device. For more information, see [Errata on page 24](#).

The AutoStore is re-enabled by initiating an AutoStore enable sequence. A sequence of read operations is performed in a manner similar to the Software RECALL initiation. To initiate the

AutoStore enable sequence, the following sequence of  $\overline{CE}$  or  $\overline{OE}$  controlled read operations must be performed:

1. Read address 0x4E38 Valid READ
2. Read address 0xB1C7 Valid READ
3. Read address 0x83E0 Valid READ
4. Read address 0x7C1F Valid READ
5. Read address 0x703F Valid READ
6. Read address 0x4B46 AutoStore Enable

If the AutoStore function is disabled or re-enabled, a manual STORE operation (Hardware or Software) must be issued to save the AutoStore state through subsequent power-down cycles. The part comes from the factory with AutoStore enabled and 0x00 written in all cells.

### Data Protection

The CY14B108L/CY14B108N protects data from corruption during low voltage conditions by inhibiting all externally initiated STORE and write operations. The low voltage condition is detected when  $V_{CC} < V_{SWITCH}$ . If the CY14B108L/CY14B108N is in a write mode (both  $\overline{CE}$  and  $\overline{WE}$  are LOW) at power-up, after a RECALL or STORE, the write is inhibited until the SRAM is enabled after  $t_{LZHSB}$  (HSB to output active). This protects against inadvertent writes during power-up or brown out conditions.

## Maximum Ratings

Exceeding maximum ratings may impair the useful life of the device. These user guidelines are not tested.

Storage temperature ..... -65 °C to +150 °C

Maximum accumulated storage time

At 150 °C ambient temperature ..... 1000 h

At 85 °C ambient temperature ..... 20 Years

Maximum junction temperature ..... 150 °C

Supply voltage on  $V_{CC}$  relative to  $V_{SS}$  ..... -0.5 V to 4.1 V

Voltage applied to outputs

in High Z state ..... -0.5 V to  $V_{CC} + 0.5$  V

Input voltage ..... -0.5 V to  $V_{CC} + 0.5$  V

Transient voltage (< 20 ns) on

any pin to ground potential ..... -2.0 V to  $V_{CC} + 2.0$  V

Package power dissipation

capability ( $T_A = 25$  °C) ..... 1.0 W

Surface mount Pb soldering

temperature (3 Seconds) ..... +260 °C

DC output current (1 output at a time, 1s duration) .... 15 mA

Static discharge voltage

(per MIL-STD-883, Method 3015) ..... > 2001 V

Latch up current ..... > 200 mA

## Operating Range

| Range      | Ambient Temperature | $V_{CC}$       |
|------------|---------------------|----------------|
| Industrial | -40 °C to +85 °C    | 2.7 V to 3.6 V |

## DC Electrical Characteristics

Over the [Operating Range](#)

| Parameter      | Description                                                          | Test Conditions                                                                                                                                                                    | Min            | Typ <sup>[8]</sup> | Max            | Unit           |
|----------------|----------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|--------------------|----------------|----------------|
| $V_{CC}$       | Power supply                                                         |                                                                                                                                                                                    | 2.7            | 3.0                | 3.6            | V              |
| $I_{CC1}$      | Average $V_{CC}$ current                                             | $t_{RC} = 20$ ns<br>$t_{RC} = 25$ ns<br>$t_{RC} = 45$ ns<br>Values obtained without output loads<br>( $I_{OUT} = 0$ mA)                                                            | —              | —                  | 75<br>75<br>57 | mA<br>mA<br>mA |
| $I_{CC2}$      | Average $V_{CC}$ current during STORE                                | All inputs don't care, $V_{CC} = \text{Max}$<br>Average current for duration $t_{STORE}$                                                                                           | —              | —                  | 20             | mA             |
| $I_{CC3}$      | Average $V_{CC}$ current at $t_{RC} = 200$ ns, $V_{CC(Typ)}$ , 25 °C | All inputs cycling at CMOS levels.<br>Values obtained without output loads<br>( $I_{OUT} = 0$ mA).                                                                                 | —              | 40                 | —              | mA             |
| $I_{CC4}$      | Average $V_{CAP}$ current during AutoStore cycle                     | All inputs don't care. Average current<br>for duration $t_{STORE}$                                                                                                                 | —              | —                  | 10             | mA             |
| $I_{SB}$       | $V_{CC}$ standby current                                             | $CE \geq (V_{CC} - 0.2$ V).<br>$V_{IN} \leq 0.2$ V or $\geq (V_{CC} - 0.2$ V).<br>Standby current level after<br>nonvolatile cycle is complete.<br>Inputs are static. $f = 0$ MHz. | —              | —                  | 10             | mA             |
| $I_{IX}^{[9]}$ | Input leakage current (except HSB)                                   | $V_{CC} = \text{Max}$ , $V_{SS} \leq V_{IN} \leq V_{CC}$                                                                                                                           | -2             | —                  | +2             | μA             |
|                | Input leakage current (for HSB)                                      | $V_{CC} = \text{Max}$ , $V_{SS} \leq V_{IN} \leq V_{CC}$                                                                                                                           | -200           | —                  | +2             | μA             |
| $I_{OZ}$       | Off-state output leakage current                                     | $V_{CC} = \text{Max}$ , $V_{SS} \leq V_{OUT} \leq V_{CC}$ ,<br>$CE$ or $OE \geq V_{IH}$ or<br>$BHE/BLE \geq V_{IH}$ or $WE \leq V_{IL}$                                            | -2             | —                  | +2             | μA             |
| $V_{IH}$       | Input HIGH voltage                                                   |                                                                                                                                                                                    | 2.0            | —                  | $V_{CC} + 0.5$ | V              |
| $V_{IL}$       | Input LOW voltage                                                    |                                                                                                                                                                                    | $V_{SS} - 0.5$ | —                  | 0.8            | V              |
| $V_{OH}$       | Output HIGH voltage                                                  | $I_{OUT} = -2$ mA                                                                                                                                                                  | 2.4            | —                  | —              | V              |
| $V_{OL}$       | Output LOW voltage                                                   | $I_{OUT} = 4$ mA                                                                                                                                                                   | —              | —                  | 0.4            | V              |

### Notes

8. Typical values are at 25 °C,  $V_{CC} = V_{CC(Typ)}$ . Not 100% tested.

9. The HSB pin has  $I_{OUT} = -2$  μA for  $V_{OH}$  of 2.4 V when both active HIGH and LOW drivers are disabled. When they are enabled standard  $V_{OH}$  and  $V_{OL}$  are valid. This parameter is characterized but not tested.

## DC Electrical Characteristics (continued)

Over the [Operating Range](#)

| Parameter             | Description                                           | Test Conditions                    | Min | Typ <sup>[8]</sup> | Max      | Unit    |
|-----------------------|-------------------------------------------------------|------------------------------------|-----|--------------------|----------|---------|
| $V_{CAP}^{[10]}$      | Storage capacitor                                     | Between $V_{CAP}$ pin and $V_{SS}$ | 122 | 150                | 360      | $\mu F$ |
| $V_{VCAP}^{[11, 12]}$ | Maximum voltage driven on $V_{CAP}$ pin by the device | $V_{CC} = \text{Max}$              | –   | –                  | $V_{CC}$ | V       |

## Data Retention and Endurance

Over the [Operating Range](#)

| Parameter | Description                  | Min   | Unit  |
|-----------|------------------------------|-------|-------|
| $DATA_R$  | Data retention               | 20    | Years |
| $NV_C$    | Nonvolatile STORE operations | 1,000 | K     |

## Capacitance

| Parameter <sup>[12]</sup> | Description        | Test Conditions                                                   | Max | Unit |
|---------------------------|--------------------|-------------------------------------------------------------------|-----|------|
| $C_{IN}$                  | Input capacitance  | $T_A = 25^\circ C$ , $f = 1 \text{ MHz}$ , $V_{CC} = V_{CC(Typ)}$ | 14  | pF   |
| $C_{OUT}$                 | Output capacitance |                                                                   | 14  | pF   |

## Thermal Resistance


| Parameter <sup>[12]</sup> | Description                              | Test Conditions                                                                                                             | 48-ball FBGA | 44-pin TSOP II | 54-pin TSOP II | Unit         |
|---------------------------|------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|--------------|----------------|----------------|--------------|
| $\Theta_{JA}$             | Thermal resistance (Junction to ambient) | Test conditions follow standard test methods and procedures for measuring thermal impedance, in accordance with EIA/JESD51. | 42.2         | 45.3           | 44.22          | $^\circ C/W$ |
| $\Theta_{JC}$             | Thermal resistance (Junction to case)    |                                                                                                                             | 6.3          | 5.2            | 8.26           | $^\circ C/W$ |

### Notes

10. Min  $V_{CAP}$  value guarantees that there is a sufficient charge available to complete a successful AutoStore operation. Max  $V_{CAP}$  value guarantees that the capacitor on  $V_{CAP}$  is charged to a minimum voltage during a Power-Up RECALL cycle so that an immediate power-down cycle can complete a successful AutoStore. Therefore it is always recommended to use a capacitor within the specified min and max limits. Refer application note [AN43593](#) for more details on  $V_{CAP}$  options.
11. Maximum voltage on  $V_{CAP}$  pin ( $V_{VCAP}$ ) is provided for guidance when choosing the  $V_{CAP}$  capacitor. The voltage rating of the  $V_{CAP}$  capacitor across the operating temperature range should be higher than the  $V_{VCAP}$  voltage.
12. These parameters are guaranteed by design and are not tested.

## AC Test Loads

Figure 4. AC Test Loads



## AC Test Conditions

Input pulse levels ..... 0 V to 3 V  
 Input rise and fall times (10%–90%) .....  $\leq 3$  ns  
 Input and output timing reference levels ..... 1.5 V


## AC Switching Characteristics

Over the [Operating Range](#)

| Parameters <sup>[13]</sup>                |                  | Description                       | 20 ns |     | 25 ns |     | 45 ns |     | Unit |
|-------------------------------------------|------------------|-----------------------------------|-------|-----|-------|-----|-------|-----|------|
| Cypress Parameter                         | Alt Parameter    |                                   | Min   | Max | Min   | Max | Min   | Max |      |
| SRAM Read Cycle                           |                  |                                   |       |     |       |     |       |     |      |
| t <sub>ACE</sub>                          | t <sub>ACS</sub> | Chip enable access time           | –     | 20  | –     | 25  | –     | 45  | ns   |
| t <sub>RC</sub> <sup>[14]</sup>           | t <sub>RC</sub>  | Read cycle time                   | 20    | –   | 25    | –   | 45    | –   | ns   |
| t <sub>AA</sub> <sup>[15]</sup>           | t <sub>AA</sub>  | Address access time               | –     | 20  | –     | 25  | –     | 45  | ns   |
| t <sub>DOE</sub>                          | t <sub>OE</sub>  | Output enable to data valid       | –     | 10  | –     | 12  | –     | 20  | ns   |
| t <sub>OHA</sub> <sup>[15]</sup>          | t <sub>OH</sub>  | Output hold after address change  | 3     | –   | 3     | –   | 3     | –   | ns   |
| t <sub>LZCE</sub> <sup>[16, 17]</sup>     | t <sub>LZ</sub>  | Chip enable to output active      | 3     | –   | 3     | –   | 3     | –   | ns   |
| t <sub>HZCE</sub> <sup>[16, 17]</sup>     | t <sub>HZ</sub>  | Chip disable to output inactive   | –     | 8   | –     | 10  | –     | 15  | ns   |
| t <sub>LZOE</sub> <sup>[16, 17]</sup>     | t <sub>OLZ</sub> | Output enable to output active    | 0     | –   | 0     | –   | 0     | –   | ns   |
| t <sub>HZOE</sub> <sup>[16, 17]</sup>     | t <sub>OHZ</sub> | Output disable to output inactive | –     | 8   | –     | 10  | –     | 15  | ns   |
| t <sub>PU</sub> <sup>[16]</sup>           | t <sub>PA</sub>  | Chip enable to power active       | 0     | –   | 0     | –   | 0     | –   | ns   |
| t <sub>PD</sub> <sup>[16]</sup>           | t <sub>PS</sub>  | Chip disable to power standby     | –     | 20  | –     | 25  | –     | 45  | ns   |
| t <sub>DBE</sub>                          | –                | Byte enable to data valid         | –     | 10  | –     | 12  | –     | 20  | ns   |
| t <sub>LZBE</sub> <sup>[16]</sup>         | –                | Byte enable to output active      | 0     | –   | 0     | –   | 0     | –   | ns   |
| t <sub>HZBE</sub> <sup>[16]</sup>         | –                | Byte disable to output inactive   | –     | 8   | –     | 10  | –     | 15  | ns   |
| SRAM Write Cycle                          |                  |                                   |       |     |       |     |       |     |      |
| t <sub>WC</sub>                           | t <sub>WC</sub>  | Write cycle time                  | 20    | –   | 25    | –   | 45    | –   | ns   |
| t <sub>PWE</sub>                          | t <sub>WP</sub>  | Write pulse width                 | 15    | –   | 20    | –   | 30    | –   | ns   |
| t <sub>SCE</sub>                          | t <sub>CW</sub>  | Chip enable to end of write       | 15    | –   | 20    | –   | 30    | –   | ns   |
| t <sub>SD</sub>                           | t <sub>DW</sub>  | Data setup to end of write        | 8     | –   | 10    | –   | 15    | –   | ns   |
| t <sub>HD</sub>                           | t <sub>DH</sub>  | Data hold after end of write      | 0     | –   | 0     | –   | 0     | –   | ns   |
| t <sub>AW</sub>                           | t <sub>AW</sub>  | Address setup to end of write     | 15    | –   | 20    | –   | 30    | –   | ns   |
| t <sub>SA</sub>                           | t <sub>AS</sub>  | Address setup to start of write   | 0     | –   | 0     | –   | 0     | –   | ns   |
| t <sub>HA</sub>                           | t <sub>WR</sub>  | Address hold after end of write   | 0     | –   | 0     | –   | 0     | –   | ns   |
| t <sub>HZWE</sub> <sup>[16, 17, 18]</sup> | t <sub>WZ</sub>  | Write enable to output disable    | –     | 8   |       | 10  | –     | 15  | ns   |
| t <sub>LZWE</sub> <sup>[16, 17]</sup>     | t <sub>OW</sub>  | Output active after end of write  | 3     | –   | 3     | –   | 3     | –   | ns   |
| t <sub>BW</sub>                           | –                | Byte enable to end of write       | 15    | –   | 20    | –   | 30    | –   | ns   |

## Switching Waveforms

Figure 5. SRAM Read Cycle #1 (Address Controlled) <sup>[14, 15, 19]</sup>




### Notes


13. Test conditions assume signal transition time of 3 ns or less, timing reference levels of  $V_{CC}/2$ , input pulse levels of 0 to  $V_{CC(typ)}$ , and output loading of the specified  $I_{OL}/I_{OH}$  and load capacitance shown in [Figure 4 on page 11](#).
14. WE must be HIGH during SRAM read cycles.
15. Device is continuously selected with CE, OE and  $\overline{BHE}$  /  $\overline{BLE}$  LOW.
16. These parameters are guaranteed by design but not tested.
17. Measured  $\pm 200$  mV from steady state output voltage.
18. If WE is LOW when CE goes LOW, the outputs remain in the high impedance state.
19. HSB must remain HIGH during READ and WRITE cycles.

## Switching Waveforms (continued)

**Figure 6. SRAM Read Cycle #2 ( $\overline{\text{CE}}$  and  $\overline{\text{OE}}$  Controlled)** [20, 21, 22]



**Figure 7. SRAM Write Cycle #1 ( $\overline{\text{WE}}$  Controlled)** [20, 22, 23, 24]




### Notes


20.  $\overline{\text{BHE}}$  and  $\overline{\text{BLE}}$  are applicable for  $\times 16$  configuration only.
21.  $\overline{\text{WE}}$  must be HIGH during SRAM read cycles.
22.  $\overline{\text{HSB}}$  must remain HIGH during READ and WRITE cycles.
23. If  $\overline{\text{WE}}$  is LOW when  $\overline{\text{CE}}$  goes LOW, the outputs remain in the high impedance state.
24.  $\overline{\text{CE}}$  or  $\overline{\text{WE}}$  must be  $\geq V_{IH}$  during address transitions.

## Switching Waveforms (continued)

**Figure 8. SRAM Write Cycle #2 ( $\overline{\text{CE}}$  Controlled)** [25, 26, 27, 28]



**Figure 9. SRAM Write Cycle #3 ( $\overline{\text{BHE}}$  and  $\overline{\text{BLE}}$  Controlled)** [25, 26, 27, 28]



### Notes

25.  $\overline{\text{BHE}}$  and  $\overline{\text{BLE}}$  are applicable for  $\times 16$  configuration only.
26. If  $\overline{\text{WE}}$  is LOW when  $\overline{\text{CE}}$  goes LOW, the outputs remain in the high impedance state.
27.  $\overline{\text{HSB}}$  must remain HIGH during READ and WRITE cycles.
28.  $\overline{\text{CE}}$  or  $\overline{\text{WE}}$  must be  $\geq V_{IH}$  during address transitions.


## AutoStore/Power-Up RECALL

Over the [Operating Range](#)

| Parameter             | Description                               | 20 ns |      | 25 ns |      | 45 ns |      | Unit |
|-----------------------|-------------------------------------------|-------|------|-------|------|-------|------|------|
|                       |                                           | Min   | Max  | Min   | Max  | Min   | Max  |      |
| $t_{HRECALL}^{[29]}$  | Power-Up RECALL duration                  | –     | 20   | –     | 20   | –     | 20   | ms   |
| $t_{STORE}^{[30]}$    | STORE cycle duration                      | –     | 8    | –     | 8    | –     | 8    | ms   |
| $t_{DELAY}^{[31]}$    | Time allowed to complete SRAM write cycle | –     | 20   | –     | 25   | –     | 25   | ns   |
| $V_{SWITCH}$          | Low voltage trigger level                 | –     | 2.65 | –     | 2.65 | –     | 2.65 | V    |
| $t_{VCCRRISE}^{[32]}$ | $V_{CC}$ rise time                        | 150   | –    | 150   | –    | 150   | –    | μs   |
| $V_{HDS}^{[32]}$      | HSB output disable voltage                | –     | 1.9  | –     | 1.9  | –     | 1.9  | V    |
| $t_{LZHSB}^{[32]}$    | HSB to output active time                 | –     | 5    | –     | 5    | –     | 5    | μs   |
| $t_{HHHD}^{[32]}$     | HSB high active time                      | –     | 500  | –     | 500  | –     | 500  | ns   |

## Switching Waveforms

Figure 10. AutoStore or Power-Up RECALL <sup>[33]</sup>



### Notes

29.  $t_{HRECALL}$  starts from the time  $V_{CC}$  rises above  $V_{SWITCH}$ .
30. If an SRAM write has not taken place since the last nonvolatile cycle, no AutoStore or Hardware STORE takes place.
31. On a Hardware STORE and AutoStore initiation, SRAM write operation continues to be enabled for time  $t_{DELAY}$ .
32. These parameters are guaranteed by design but not tested.
33. Read and Write cycles are ignored during STORE, RECALL, and while  $V_{CC}$  is below  $V_{SWITCH}$ .
34. During power-up and power-down, HSB glitches when HSB pin is pulled up through an external resistor.

## Software Controlled STORE/RECALL Cycle

Over the [Operating Range](#)

| Parameter <sup>[35, 36]</sup> | Description                        | 20 ns |     | 25 ns |     | 45 ns |     | Unit |
|-------------------------------|------------------------------------|-------|-----|-------|-----|-------|-----|------|
|                               |                                    | Min   | Max | Min   | Max | Min   | Max |      |
| $t_{RC}$                      | STORE/RECALL initiation cycle time | 20    | –   | 25    | –   | 45    | –   | ns   |
| $t_{SA}$                      | Address setup time                 | 0     | –   | 0     | –   | 0     | –   | ns   |
| $t_{CW}$                      | Clock pulse width                  | 15    | –   | 20    | –   | 30    | –   | ns   |
| $t_{HA}$                      | Address hold time                  | 0     | –   | 0     | –   | 0     | –   | ns   |
| $t_{RECALL}$                  | RECALL duration                    | –     | 200 | –     | 200 | –     | 200 | μs   |

## Switching Waveforms

Figure 11.  $\overline{CE}$  and  $\overline{OE}$  Controlled Software STORE/RECALL Cycle <sup>[36]</sup>





Figure 12. Autostore Enable/Disable Cycle <sup>[36]</sup>



### Notes

35. The software sequence is clocked with  $\overline{CE}$  controlled or  $\overline{OE}$  controlled reads.

36. The six consecutive addresses must be read in the order listed in [Table 1 on page 7](#).  $\overline{WE}$  must be HIGH during all six consecutive cycles.

37. DQ output data at the sixth read may be invalid since the output is disabled at  $t_{DELAY}$  time.

## Hardware STORE Cycle

Over the [Operating Range](#)

| Parameter                  | Description                                        | 20 ns |     | 25 ns |     | 45 ns |     | Unit |
|----------------------------|----------------------------------------------------|-------|-----|-------|-----|-------|-----|------|
|                            |                                                    | Min   | Max | Min   | Max | Min   | Max |      |
| $t_{\text{DHSB}}$          | HSB to output active time when write latch not set | –     | 20  | –     | 25  | –     | 25  | ns   |
| $t_{\text{PHSB}}$          | Hardware STORE pulse width                         | 15    | –   | 15    | –   | 15    | –   | ns   |
| $t_{\text{SS}}^{[38, 39]}$ | Soft sequence processing time                      | –     | 100 | –     | 100 | –     | 100 | μs   |

## Switching Waveforms

Figure 13. Hardware STORE Cycle <sup>[40]</sup>





Figure 14. Soft Sequence Processing <sup>[38, 39]</sup>



### Notes

38. This is the amount of time it takes to take action on a soft sequence command.  $V_{\text{CC}}$  power must remain HIGH to effectively register command.  
 39. Commands such as STORE and RECALL lock out I/O until operation is complete which further increases this time. See the specific command.  
 40. If an SRAM write has not taken place since the last nonvolatile cycle, no AutoStore or Hardware STORE takes place.

## Truth Table For SRAM Operations

HSB should remain HIGH for SRAM Operations.

**Table 2. Truth Table for × 8 Configuration**

| $\overline{\text{CE}}$ | $\overline{\text{WE}}$ | $\overline{\text{OE}}$ | Inputs/Outputs <sup>[41]</sup>                | Mode                | Power   |
|------------------------|------------------------|------------------------|-----------------------------------------------|---------------------|---------|
| H                      | X                      | X                      | High Z                                        | Deselect/Power-down | Standby |
| L                      | H                      | L                      | Data out (DQ <sub>0</sub> –DQ <sub>7</sub> ); | Read                | Active  |
| L                      | H                      | H                      | High Z                                        | Output disabled     | Active  |
| L                      | L                      | X                      | Data in (DQ <sub>0</sub> –DQ <sub>7</sub> );  | Write               | Active  |

**Table 3. Truth Table for × 16 Configuration**

| $\overline{\text{CE}}$ | $\overline{\text{WE}}$ | $\overline{\text{OE}}$ | $\overline{\text{BHE}}$ <sup>[42]</sup> | $\overline{\text{BLE}}$ <sup>[42]</sup> | Inputs/Outputs <sup>[41]</sup>                                                               | Mode                | Power   |
|------------------------|------------------------|------------------------|-----------------------------------------|-----------------------------------------|----------------------------------------------------------------------------------------------|---------------------|---------|
| H                      | X                      | X                      | X                                       | X                                       | High Z                                                                                       | Deselect/Power-down | Standby |
| L                      | X                      | X                      | H                                       | H                                       | High Z                                                                                       | Output disabled     | Active  |
| L                      | H                      | L                      | L                                       | L                                       | Data out (DQ <sub>0</sub> –DQ <sub>15</sub> )                                                | Read                | Active  |
| L                      | H                      | L                      | H                                       | L                                       | Data out (DQ <sub>0</sub> –DQ <sub>7</sub> );<br>DQ <sub>8</sub> –DQ <sub>15</sub> in High Z | Read                | Active  |
| L                      | H                      | L                      | L                                       | H                                       | Data out (DQ <sub>8</sub> –DQ <sub>15</sub> );<br>DQ <sub>0</sub> –DQ <sub>7</sub> in High Z | Read                | Active  |
| L                      | H                      | H                      | L                                       | L                                       | High Z                                                                                       | Output disabled     | Active  |
| L                      | H                      | H                      | H                                       | L                                       | High Z                                                                                       | Output disabled     | Active  |
| L                      | H                      | H                      | L                                       | H                                       | High Z                                                                                       | Output disabled     | Active  |
| L                      | L                      | X                      | L                                       | L                                       | Data in (DQ <sub>0</sub> –DQ <sub>15</sub> )                                                 | Write               | Active  |
| L                      | L                      | X                      | H                                       | L                                       | Data in (DQ <sub>0</sub> –DQ <sub>7</sub> );<br>DQ <sub>8</sub> –DQ <sub>15</sub> in High Z  | Write               | Active  |
| L                      | L                      | X                      | L                                       | H                                       | Data in (DQ <sub>8</sub> –DQ <sub>15</sub> );<br>DQ <sub>0</sub> –DQ <sub>7</sub> in High Z  | Write               | Active  |

### Notes

41. Data DQ<sub>0</sub>–DQ<sub>7</sub> for × 8 configuration and Data DQ<sub>0</sub>–DQ<sub>15</sub> for × 16 configuration.

42. BHE and BLE are applicable for × 16 configuration only.


## Ordering Information

| Speed (ns) | Ordering Code      | Package Diagram | Package Type   | Operating Range |
|------------|--------------------|-----------------|----------------|-----------------|
| 20         | CY14B108L-ZS20XIT  | 51-85087        | 44-pin TSOP II | Industrial      |
|            | CY14B108L-ZS20XI   | 51-85087        | 44-pin TSOP II |                 |
| 25         | CY14B108L-ZS25XIT  | 51-85087        | 44-pin TSOP II |                 |
|            | CY14B108L-ZS25XI   | 51-85087        | 44-pin TSOP II |                 |
|            | CY14B108L-BA25XIT  | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108L-BA25XI   | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108N-BA25XIT  | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108N-BA25XI   | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108N-ZSP25XIT | 51-85160        | 54-pin TSOP II |                 |
|            | CY14B108N-ZSP25XI  | 51-85160        | 54-pin TSOP II |                 |
| 45         | CY14B108L-ZS45XIT  | 51-85087        | 44-pin TSOP II |                 |
|            | CY14B108L-ZS45XI   | 51-85087        | 44-pin TSOP II |                 |
|            | CY14B108L-BA45XIT  | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108L-BA45XI   | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108N-BA45XIT  | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108N-BA45XI   | 51-85128        | 48-ball FBGA   |                 |
|            | CY14B108N-ZSP45XIT | 51-85160        | 54-pin TSOP II |                 |
|            | CY14B108N-ZSP45XI  | 51-85160        | 54-pin TSOP II |                 |

All the above parts are Pb-free.


## Ordering Code Definitions

### CY 14 B 108 L - ZS 20 X I T




## Package Diagrams

Figure 15. 44-pin TSOP II Package Outline, 51-85087




51-85087 \*E

**Package Diagrams** (continued)

**Figure 16. 48-ball FBGA (6 × 10 × 1.2 mm) Package Outline, 51-85128**


## Package Diagrams (continued)

Figure 17. 54-pin TSOP II (22.4 × 11.84 × 1.0 mm) Package Outline, 51-85160



51-85160 \*E

## Acronyms

| Acronym                 | Description                              |
|-------------------------|------------------------------------------|
| CMOS                    | complementary metal oxide semiconductor  |
| $\overline{\text{BHE}}$ | byte high enable                         |
| $\overline{\text{BLE}}$ | byte low enable                          |
| $\overline{\text{CE}}$  | chip enable                              |
| EIA                     | electronic industries alliance           |
| FBGA                    | fine-pitch ball grid array               |
| $\overline{\text{HSB}}$ | hardware store busy                      |
| I/O                     | input/output                             |
| nvSRAM                  | non-volatile static random access memory |
| $\overline{\text{OE}}$  | output enable                            |
| RoHS                    | restriction of hazardous substances      |
| RWI                     | read and write inhibited                 |
| SRAM                    | static random access memory              |
| TSOP                    | thin small outline package               |
| $\overline{\text{WE}}$  | write enable                             |

## Document Conventions

### Units of Measure

| Symbol        | Unit of Measure |
|---------------|-----------------|
| °C            | degree Celsius  |
| k $\Omega$    | kilohm          |
| kHz           | kilohertz       |
| MHz           | megahertz       |
| $\mu\text{A}$ | microampere     |
| $\mu\text{F}$ | microfarad      |
| $\mu\text{s}$ | microsecond     |
| mA            | milliampere     |
| ms            | millisecond     |
| ns            | nanosecond      |
| $\Omega$      | ohm             |
| %             | percent         |
| pF            | picofarad       |
| s             | second          |
| V             | volt            |
| W             | watt            |

## Errata

This section describes the errata for the 8 Mb (2048 K × 8 and 1024 K × 16) nvSRAM product families. Details include errata trigger conditions, scope of impact, available workarounds, and silicon revision applicability.

Contact your local Cypress Sales Representative if you have questions. You can also send your related queries directly to [nvSRAM@cypress.com](mailto:nvSRAM@cypress.com).

### Part Numbers Affected

| Part Number | Device Characteristics                                                              |
|-------------|-------------------------------------------------------------------------------------|
| CY14B108L   | 1024 K × 8, Asynchronous Interface nvSRAM in 44 TSOP-II and 48 FBGA package options |
| CY14B108N   | 512 K × 16, Asynchronous Interface nvSRAM in 54 TSOP-II and 48 FBGA package options |

### 8Mb (1024 K × 8, 512 K × 16) nvSRAM Qualification Status

Production parts.

### 8Mb (1024 K × 8, 512 K × 16) nvSRAM Errata Summary

The following table defines the errata applicability to available CY14B108L, CY14B108N devices.

| Items                                                                | Part Number            | Silicon Revision | Fix Status                                                              |
|----------------------------------------------------------------------|------------------------|------------------|-------------------------------------------------------------------------|
| 1. <a href="#">AutoStore Disable feature does not work correctly</a> | CY14B108L<br>CY14B108N | Rev 0            | None.<br>This issue is applicable to all 8Mb nvSRAM parts in production |

#### 1. AutoStore Disable feature does not work correctly

##### ■ Problem Definition

The AutoStore Disable soft sequence disables the AutoStore feature in nvSRAMs. The AutoStore Disable feature is used in applications where data written in the SRAM is not required to be saved automatically on power loss. The 8Mb nvSRAM executes the nonvolatile Store automatically in half the memory (4Mb) even after the AutoStore feature is disabled. The reason is as follows:

The 8Mb nvSRAM uses two dice stack of 4Mb with HSB pin of each die are tied together. Each nvSRAM die in the stacked-die monitors the  $V_{CC}$  power independently. When the device  $V_{CC}$  fails, the die which detects the  $V_{CC}$  dropping below  $V_{SWITCH}$  first, internally triggers the power down interrupt and drives its HSB output low. Since the HSB is a bidirectional pin, the low HSB output driven by one die is detected as HSB input by the other die. Therefore, low on the HSB input of other die internally triggers hardware Store and executes unintended nonvolatile Store even though AutoStore was disabled by AutoStore Disable soft sequence.

##### ■ Parameters Affected

None.

##### ■ Trigger Condition(S)

Device  $V_{CC}$  power down with nvSRAM AutoStore disable.

##### ■ Scope of Impact

It can corrupt the data in half of the memory by overwriting the existing data in its nonvolatile memory with unintended data.

##### ■ Workaround

None. AutoStore disable feature should not be used in 8Mb nvSRAMs.

##### ■ Fix Status

This issue is applicable to all 8Mb nvSRAM parts in production and will continue serving with errata. There is no plan to fix this issue in the existing parts in production.

## Document History Page

| Document Title: CY14B108L/CY14B108N, 8-Mbit (1024 K × 8/512 K × 16) nvSRAM<br>Document Number: 001-45523 |         |                 |                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|----------------------------------------------------------------------------------------------------------|---------|-----------------|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Revision                                                                                                 | ECN     | Orig. of Change | Submission Date | Description of Change                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| **                                                                                                       | 2428826 | GVCH            | See ECN         | New Data Sheet                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| *A                                                                                                       | 2520023 | GVCH / PYRS     | 06/23/08        | Updated I <sub>CC1</sub> for t <sub>RC</sub> =20ns, 25ns and 45ns access speed for both industrial and Commercial temperature Grade<br>Updated Thermal resistance values for 48-FBGA, 44-TSOP II and 54-TSOP II packages<br>Changed t <sub>CW</sub> value from 16ns to 15ns                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| *B                                                                                                       | 2676670 | GVCH / PYRS     | 03/20/2009      | Added maximum accumulated storage time for 150°C and 85°C Temperature<br>Added best practices<br>Changed I <sub>CC2</sub> from 12mA to 20mA<br>Changed I <sub>CC3</sub> from 38mA to 40mA<br>Changed I <sub>CC4</sub> from 12mA to 10mA<br>Changed I <sub>SB</sub> from 6mA to 10mA<br>Changed V <sub>CAP</sub> from 164uF to 360uF<br>Changed Input Rise and Fall Times from 5ns to 3ns<br>Updated I <sub>CC1</sub> , I <sub>CC3</sub> , I <sub>SB</sub> and I <sub>OZ</sub> Test conditions<br>Changed t <sub>DELAY</sub> to 20ns, 25ns, 25ns for 15ns, 20ns, 45ns part respectively<br>Changed t <sub>STORE</sub> from 15ms to 8ms<br>Added V <sub>HDIS</sub> , t <sub>HHD</sub> and t <sub>LZHSB</sub> parameters<br>Software controlled STORE/RECALL cycle table: Changed t <sub>AS</sub> to t <sub>SA</sub><br>Changed t <sub>GHAX</sub> to t <sub>HA</sub><br>Added t <sub>DHSB</sub> parameter<br>Changed t <sub>HLHX</sub> to t <sub>PHSB</sub><br>Updated t <sub>SS</sub> from 70us to 100us<br>Added Truth table for SRAM operations<br>Updated ordering information |
| *C                                                                                                       | 2712462 | GVCH / PYRS     | 05/29/2009      | Moved data sheet status from Preliminary to Final<br>Updated AutoStore operation<br>Updated I <sub>SB</sub> test condition<br>Updated footnote 7<br>Referenced footnote 9 to V <sub>CCRISE</sub> , t <sub>HHD</sub> and t <sub>LZHSB</sub> parameters<br>Updated V <sub>HDIS</sub> parameter description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| *D                                                                                                       | 2746310 | GVCH            | 07/29/2009      | Page 4: Updated Hardware STORE (HSB) operation description<br>page 5: Updated Software STORE description<br>Updated t <sub>DELAY</sub> parameter description<br>Updated footnote 18 and added footnote 23<br>Referenced footnote 23 to Figure 11 and Figure 12                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| *E                                                                                                       | 2759948 | GVCH            | 09/04/2009      | Removed commercial temperature related specs                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| *F                                                                                                       | 2828257 | GVCH            | 12/15/2009      | Changed STORE cycles to QuantumTrap from 200K to 1 Million<br>Added Contents on page 2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| *G                                                                                                       | 2894560 | GVCH            | 03/18/2010      | Removed part numbers CY14B108N-ZSP20XIT and CY14B108N-ZSP20XI from ordering information table.<br>Updated Package diagrams 51-85160 and 51-85087.<br>Updated Sales, Solution, and Legal Information Section.<br>Updated copyright section.<br>Updated table of contents.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| *H                                                                                                       | 2923475 | GVCH / AESA     | 04/27/2010      | Table 1: Added more clarity on HSB pin operation<br>Hardware STORE Operation: Added more clarity on HSB pin operation<br>Table 1: Added more clarity on BHE/BLE pin operation<br>Updated HSB pin operation in Figure 10<br>Updated footnote 34                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |

**Document History Page** (continued)

| Document Title: CY14B108L/CY14B108N, 8-Mbit (1024 K × 8/512 K × 16) nvSRAM<br>Document Number: 001-45523 |         |                 |                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|----------------------------------------------------------------------------------------------------------|---------|-----------------|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Revision                                                                                                 | ECN     | Orig. of Change | Submission Date | Description of Change                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| *I                                                                                                       | 3143765 | GVCH            | 01/17/2011      | 48-ball FBGA package: 16 Mb address expansion is not supported<br>Updated thermal resistance values for all packages<br>Added <a href="#">Acronyms</a> table and <a href="#">Document Conventions</a> table                                                                                                                                                                                                                                                                                               |
| *J                                                                                                       | 3311413 | GVCH            | 07/13/2011      | Updated <a href="#">DC Electrical Characteristics</a> (Added Note 9 and referred the same note in V <sub>CAP</sub> parameter).<br>Updated <a href="#">AC Switching Characteristics</a> (Added Note 13 and referred the same note in Parameters).<br>Updated <a href="#">Package Diagrams</a> .                                                                                                                                                                                                            |
| *K                                                                                                       | 3580269 | GVCH            | 04/12/2012      | Updated <a href="#">Package Diagrams</a> .                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| *L                                                                                                       | 3658005 | GVCH            | 08/10/2012      | Updated <a href="#">Maximum Ratings</a> (Changed “Ambient temperature with power applied” to “Maximum junction temperature”).<br>Updated <a href="#">DC Electrical Characteristics</a> (Added V <sub>V<sub>CAP</sub></sub> parameter and its details, added Note 11 and referred the same note in V <sub>V<sub>CAP</sub></sub> parameter, also referred Note 12 in V <sub>V<sub>CAP</sub></sub> parameter).<br>Updated <a href="#">Package Diagrams</a> (spec 51-85160 (Changed revision from *C to *D)). |
| *M                                                                                                       | 4500772 | ZSK             | 09/12/2014      | Updated <a href="#">Package Diagrams</a> :<br>spec 51-85087 – Changed revision from *D to *E.<br>spec 51-85160 – Changed revision from *D to *E.<br><br>Added <a href="#">Errata</a> .<br><br>Updated to new template.                                                                                                                                                                                                                                                                                    |
| *N                                                                                                       | 4563189 | ZSK             | 11/12/2014      | Added related documentation hyperlink in page 1                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| *O                                                                                                       | 4714292 | GVCH            | 04/08/2015      | No technical updates.<br>Completing Sunset Review.                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| *P                                                                                                       | 5705809 | AESATMP7        | 04/21/2017      | Updated Cypress Logo and Copyright.                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |

## Sales, Solutions, and Legal Information

### Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

### Products

|                               |                                                                    |
|-------------------------------|--------------------------------------------------------------------|
| ARM® Cortex® Microcontrollers | <a href="http://cypress.com/arm">cypress.com/arm</a>               |
| Automotive                    | <a href="http://cypress.com/automotive">cypress.com/automotive</a> |
| Clocks & Buffers              | <a href="http://cypress.com/clocks">cypress.com/clocks</a>         |
| Interface                     | <a href="http://cypress.com/interface">cypress.com/interface</a>   |
| Internet of Things            | <a href="http://cypress.com/iot">cypress.com/iot</a>               |
| Memory                        | <a href="http://cypress.com/memory">cypress.com/memory</a>         |
| Microcontrollers              | <a href="http://cypress.com/mcu">cypress.com/mcu</a>               |
| PSoC                          | <a href="http://cypress.com/psoc">cypress.com/psoc</a>             |
| Power Management ICs          | <a href="http://cypress.com/pmic">cypress.com/pmic</a>             |
| Touch Sensing                 | <a href="http://cypress.com/touch">cypress.com/touch</a>           |
| USB Controllers               | <a href="http://cypress.com/usb">cypress.com/usb</a>               |
| Wireless Connectivity         | <a href="http://cypress.com/wireless">cypress.com/wireless</a>     |

### PSoC® Solutions

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#) | [PSoC 6](#)

### Cypress Developer Community

[Forums](#) | [WICED IoT Forums](#) | [Projects](#) | [Video](#) | [Blogs](#) | [Training](#) | [Components](#)

### Technical Support

[cypress.com/support](http://cypress.com/support)

All other trademarks or registered trademarks referenced herein are the property of their respective owners.

© Cypress Semiconductor Corporation, 2008-2017. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit [cypress.com](http://cypress.com). Other names and brands may be claimed as property of their respective owners.